

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331952

Luminaire Tested: **S123DIP-S560D1195U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331952
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D1195U835-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7091.4 lumens
Efficiency: N/A
Efficacy: 143.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331952

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331952

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33
1	94	90	86	82	84	81	78	75	64	62	60	49	48	47	35	35	34	27
2	85	78	72	67	77	71	66	61	56	53	50	43	41	39	31	30	28	23
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	28	26	24	19
4	71	61	53	47	64	55	48	43	44	39	36	34	31	28	25	23	21	17
5	65	54	46	40	58	49	42	37	39	34	31	30	27	24	22	20	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	18	16	13
7	55	43	36	30	50	39	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9590	9590	9590
5°	9634	9502	9568
10°	9570	9419	9477
15°	9458	9313	9331
20°	9328	9160	9170
25°	9152	8980	8961
30°	8959	8779	8712
35°	8757	8566	8456
40°	8546	8331	8202
45°	8315	8115	7917
50°	8081	7850	7633
55°	7777	7576	7345
60°	7470	7255	7025
65°	7200	6907	6691
70°	6798	6508	6219
75°	6213	5989	5735
80°	5604	5368	5318
85°	4915	4730	4545



TEST NUMBER: P331952

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.9	1.2
10°-20°	237.0	3.3
20°-30°	350.0	4.9
30°-40°	408.9	5.8
40°-50°	411.1	5.8
50°-60°	361.1	5.1
60°-70°	269.0	3.8
70°-80°	153.3	2.2
80°-90°	48.4	0.7
90°-100°	56.9	0.8
100°-110°	271.0	3.8
110°-120°	650.9	9.2
120°-130°	828.8	11.7
130°-140°	885.6	12.5
140°-150°	828.1	11.7
150°-160°	668.0	9.4
160°-170°	431.1	6.1
170°-180°	148.6	2.1
0°-30°	670.9	9.5
0°-40°	1079.8	15.2
0°-60°	1851.9	26.1
0°-90°	2322.5	32.8
90°-120°	978.7	13.8
90°-150°	3521.2	49.7
90°-180°	4769.0	67.3
0°-180°	7091.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	891	891	891	891	891	
5°	892	888	879	887	886	84
15°	849	845	836	841	837	239
25°	771	766	756	757	754	355
35°	666	662	652	647	644	417
45°	546	543	533	524	520	421
55°	414	413	404	396	391	371
65°	283	279	271	265	263	279
75°	149	146	144	140	138	160
85°	40	38	38	37	37	44
90°	1	13	28	32	35	6
95°	71	27	36	44	44	88
105°	346	352	254	60	51	367
115°	650	657	667	678	683	641
125°	916	925	929	932	934	817
135°	1140	1147	1151	1154	1151	877
145°	1315	1323	1326	1328	1328	823
155°	1449	1447	1448	1453	1446	667
165°	1528	1524	1523	1531	1524	431
175°	1564	1558	1559	1566	1558	149
180°	1564	1564	1564	1564	1564	



TEST NUMBER: P331952

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9
2.5°	893.9	893.4	892.9	892.3	891.8	890.7	889.2	887.7	886.3	884.8	886.1
5°	891.6	890.8	889.9	889.1	888.2	886.9	885.0	883.1	881.3	879.4	881.1
7.5°	882.9	882.1	881.2	880.4	879.5	878.1	876.2	874.2	872.3	870.4	871.9
10°	875.6	874.7	873.9	873.0	872.2	870.6	868.4	866.2	864.0	861.8	863.3
12.5°	865.8	865.0	864.3	863.6	862.9	861.5	859.4	857.3	855.3	853.2	854.3
15°	848.7	848.1	847.4	846.7	846.0	844.6	842.4	840.2	837.9	835.7	837.1
17.5°	829.0	828.1	827.2	826.3	825.4	823.9	821.7	819.5	817.3	815.0	816.0
20°	814.3	813.3	812.2	811.2	810.2	808.6	806.4	804.2	801.9	799.7	800.4
22.5°	797.7	796.7	795.7	794.7	793.6	792.0	789.8	787.6	785.4	783.2	783.7
25°	770.6	769.6	768.6	767.6	766.5	764.9	762.7	760.5	758.3	756.1	756.2
27.5°	741.7	740.7	739.7	738.7	737.7	736.0	733.6	731.3	728.9	726.5	726.6
30°	720.8	720.0	719.1	718.3	717.4	715.8	713.4	711.0	708.7	706.3	706.3
32.5°	700.0	698.9	697.7	696.6	695.5	694.0	692.2	690.3	688.5	686.7	685.7
35°	666.4	665.4	664.4	663.4	662.4	660.7	658.5	656.3	654.1	651.9	650.9
37.5°	632.1	630.8	629.5	628.2	626.9	625.2	622.9	620.7	618.4	616.2	615.0
40°	608.2	607.2	606.2	605.2	604.1	602.4	600.0	597.7	595.3	592.9	591.5
42.5°	584.3	583.2	582.0	580.8	579.7	577.9	575.5	573.2	570.8	568.4	567.0
45°	546.2	545.5	544.8	544.1	543.4	542.0	539.8	537.6	535.4	533.1	531.1
47.5°	508.3	507.3	506.4	505.4	504.4	502.8	500.8	498.7	496.6	494.5	492.5
50°	482.6	481.7	480.9	480.0	479.2	477.7	475.4	473.2	471.0	468.8	466.9
52.5°	455.6	455.0	454.5	453.9	453.3	451.8	449.5	447.2	444.8	442.5	440.9
55°	414.4	414.2	414.1	413.9	413.7	412.5	410.3	408.1	405.9	403.7	401.8
57.5°	375.2	374.6	374.0	373.5	372.9	371.7	369.9	368.2	366.4	364.6	363.0
60°	347.0	346.8	346.7	346.5	346.3	345.2	343.2	341.1	339.1	337.0	335.5
62.5°	321.9	321.4	321.0	320.6	320.1	318.9	316.8	314.8	312.7	310.7	309.2
65°	282.7	281.8	281.0	280.1	279.3	278.0	276.3	274.6	272.9	271.2	269.8
67.5°	241.1	240.4	239.6	238.9	238.1	237.1	235.8	234.5	233.2	232.0	230.8
70°	216.0	215.0	214.0	213.0	211.9	210.9	209.9	208.9	207.8	206.8	205.6
72.5°	189.7	188.9	188.2	187.4	186.7	185.7	184.6	183.4	182.2	181.1	180.0
75°	149.4	148.7	148.0	147.3	146.7	146.1	145.5	145.0	144.5	144.0	143.2
77.5°	113.7	113.3	112.9	112.6	112.2	111.7	111.1	110.5	109.8	109.2	108.7
80°	90.4	89.9	89.4	88.9	88.3	87.9	87.6	87.2	86.9	86.6	86.4
82.5°	67.7	67.6	67.5	67.4	67.3	67.2	67.2	67.1	67.0	67.0	66.6
85°	39.8	39.5	39.2	38.8	38.5	38.3	38.3	38.3	38.3	38.3	38.0
87.5°	16.2	16.3	16.4	16.5	16.6	16.9	17.5	18.0	18.5	19.1	19.1
90°	1.2	3.7	6.3	8.9	11.5	14.5	17.8	21.2	24.5	27.9	28.9
92.5°	21.6	20.9	20.2	19.4	18.7	19.6	22.2	24.7	27.2	29.7	31.4
95°	70.9	60.3	49.7	39.1	28.5	24.7	27.5	30.3	33.2	36.0	37.8
97.5°	142.4	137.7	132.9	128.2	123.4	111.8	93.2	74.6	56.0	37.4	39.5
100°	196.3	201.5	206.7	211.8	217.0	199.4	159.2	118.9	78.6	38.3	40.4
102.5°	257.7	261.4	265.1	268.8	272.6	252.4	208.4	164.4	120.4	76.4	70.0
105°	346.2	349.1	351.9	354.7	357.6	347.4	324.1	300.9	277.7	254.4	208.7
107.5°	439.6	441.9	444.2	446.4	448.7	451.7	455.4	459.0	462.7	466.4	432.8
110°	501.9	504.0	506.0	508.1	510.2	512.6	515.5	518.3	521.1	524.0	515.5



TEST NUMBER: P331952

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	561.4	563.2	565.1	567.0	568.8	571.2	574.0	576.9	579.7	582.5	582.7
115°	649.5	651.0	652.5	654.1	655.6	657.6	659.9	662.2	664.6	666.9	669.5
117.5°	734.7	736.6	738.5	740.5	742.4	743.9	745.1	746.3	747.5	748.7	750.7
120°	787.7	790.0	792.4	794.7	797.0	798.6	799.3	800.1	800.9	801.6	803.7
122.5°	841.6	843.5	845.4	847.3	849.3	850.7	851.7	852.7	853.6	854.6	856.1
125°	915.5	917.6	919.6	921.7	923.8	925.3	926.3	927.4	928.4	929.4	930.0
127.5°	987.1	989.1	991.2	993.3	995.3	997.0	998.2	999.5	1000.7	1001.9	1002.8
130°	1031.7	1033.8	1035.8	1037.9	1039.9	1041.5	1042.5	1043.6	1044.6	1045.6	1046.7
132.5°	1074.4	1076.5	1078.6	1080.6	1082.7	1084.1	1085.0	1085.8	1086.6	1087.5	1088.5
135°	1139.7	1141.3	1142.8	1144.4	1145.9	1147.2	1148.3	1149.3	1150.3	1151.4	1152.1
137.5°	1195.5	1197.5	1199.4	1201.4	1203.4	1204.6	1205.2	1205.8	1206.3	1206.9	1208.1
140°	1232.7	1234.2	1235.8	1237.3	1238.9	1240.0	1240.8	1241.6	1242.4	1243.1	1244.2
142.5°	1267.1	1268.6	1270.2	1271.7	1273.3	1274.4	1275.2	1276.0	1276.8	1277.5	1278.4
145°	1315.2	1317.0	1318.8	1320.6	1322.4	1323.6	1324.1	1324.6	1325.1	1325.6	1326.1
147.5°	1360.5	1361.7	1362.9	1364.0	1365.2	1366.1	1366.6	1367.1	1367.6	1368.1	1368.7
150°	1388.4	1389.1	1389.9	1390.7	1391.5	1392.1	1392.6	1393.1	1393.7	1394.2	1394.7
152.5°	1413.5	1413.8	1414.2	1414.5	1414.9	1415.2	1415.5	1415.9	1416.2	1416.5	1417.4
155°	1448.8	1448.3	1447.7	1447.2	1446.7	1446.6	1446.8	1447.1	1447.4	1447.6	1448.9
157.5°	1476.2	1476.1	1476.1	1476.0	1476.0	1475.8	1475.6	1475.3	1475.1	1474.8	1476.4
160°	1492.9	1492.7	1492.4	1492.2	1491.9	1491.6	1491.4	1491.1	1490.9	1490.6	1492.2
162.5°	1508.7	1508.1	1507.4	1506.7	1506.0	1505.6	1505.3	1505.1	1504.8	1504.5	1506.3
165°	1527.8	1527.0	1526.2	1525.5	1524.7	1524.2	1523.9	1523.6	1523.4	1523.1	1525.2
167.5°	1542.7	1541.6	1540.6	1539.6	1538.5	1538.0	1538.0	1538.0	1538.0	1538.0	1540.1
170°	1551.0	1550.0	1549.0	1547.9	1546.9	1546.4	1546.4	1546.4	1546.4	1546.4	1548.4
172.5°	1556.6	1555.4	1554.1	1552.9	1551.6	1551.1	1551.3	1551.5	1551.7	1551.9	1554.0
175°	1563.8	1562.5	1561.2	1559.9	1558.6	1558.1	1558.4	1558.6	1558.9	1559.1	1561.0
177.5°	1565.7	1564.6	1563.6	1562.6	1561.5	1561.1	1561.3	1561.5	1561.7	1561.9	1563.6
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P331952

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9
2.5°	887.5	888.8	890.2	890.8	890.7	890.5	890.4	890.3
5°	882.8	884.5	886.2	886.9	886.5	886.2	885.9	885.5
7.5°	873.4	874.9	876.5	877.1	876.9	876.7	876.5	876.3
10°	864.8	866.4	867.9	868.5	868.2	867.8	867.5	867.1
12.5°	855.4	856.6	857.7	858.1	857.9	857.7	857.5	857.3
15°	838.5	839.8	841.2	841.3	840.3	839.3	838.3	837.3
17.5°	817.0	817.9	818.9	819.1	818.8	818.4	818.0	817.6
20°	801.1	801.8	802.4	802.5	802.0	801.5	801.0	800.5
22.5°	784.3	784.8	785.4	785.3	784.7	784.0	783.4	782.7
25°	756.4	756.6	756.7	756.6	756.1	755.6	755.0	754.5
27.5°	726.8	726.9	727.0	726.8	726.1	725.5	724.8	724.2
30°	706.3	706.3	706.3	705.7	704.5	703.3	702.1	700.9
32.5°	684.8	683.8	682.8	682.0	681.4	680.8	680.1	679.5
35°	649.8	648.8	647.8	646.9	646.0	645.2	644.3	643.5
37.5°	613.7	612.5	611.3	610.4	609.9	609.3	608.8	608.2
40°	590.2	588.8	587.5	586.4	585.7	585.1	584.4	583.7
42.5°	565.7	564.3	562.9	561.9	561.2	560.6	559.9	559.2
45°	529.1	527.0	525.0	523.5	522.7	521.8	521.0	520.1
47.5°	490.5	488.5	486.5	485.1	484.4	483.6	482.9	482.1
50°	465.1	463.2	461.3	459.9	458.8	457.8	456.8	455.8
52.5°	439.3	437.7	436.1	434.7	433.7	432.7	431.7	430.7
55°	399.9	398.1	396.2	394.8	394.0	393.1	392.3	391.4
57.5°	361.3	359.6	358.0	356.6	355.6	354.7	353.7	352.7
60°	334.0	332.5	330.9	329.7	328.9	328.0	327.2	326.3
62.5°	307.6	306.1	304.6	303.5	302.9	302.4	301.8	301.2
65°	268.4	267.1	265.7	264.8	264.3	263.8	263.3	262.7
67.5°	229.6	228.4	227.2	226.2	225.5	224.8	224.1	223.4
70°	204.4	203.3	202.1	201.0	200.2	199.3	198.5	197.6
72.5°	179.0	177.9	176.9	176.1	175.7	175.2	174.8	174.3
75°	142.3	141.5	140.6	139.9	139.4	138.9	138.4	137.9
77.5°	108.1	107.5	106.9	106.6	106.6	106.6	106.6	106.6
80°	86.2	86.0	85.9	85.8	85.8	85.8	85.8	85.8
82.5°	66.3	66.0	65.7	65.5	65.4	65.2	65.1	65.0
85°	37.6	37.3	36.9	36.8	36.8	36.8	36.8	36.8
87.5°	19.2	19.3	19.3	19.4	19.5	19.6	19.7	19.8
90°	29.9	31.0	32.0	32.8	33.3	33.8	34.3	34.9
92.5°	33.0	34.7	36.4	37.3	37.6	38.0	38.3	38.6
95°	39.6	41.4	43.2	44.1	44.1	44.1	44.1	44.1
97.5°	41.5	43.6	45.7	46.8	47.1	47.4	47.6	47.9
100°	42.5	44.5	46.6	47.8	48.0	48.3	48.5	48.8
102.5°	63.6	57.2	50.8	47.9	48.3	48.8	49.3	49.7
105°	163.0	117.3	71.6	49.1	49.6	50.1	50.6	51.1
107.5°	399.3	365.8	332.3	298.3	263.9	229.4	195.0	160.6
110°	506.9	498.4	489.9	467.2	430.3	393.3	356.4	319.5



TEST NUMBER: P331952

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	582.8	583.0	583.2	579.3	571.5	563.7	555.9	548.1
115°	672.0	674.6	677.2	679.0	680.0	681.1	682.1	683.1
117.5°	752.8	754.9	756.9	758.1	758.3	758.5	758.7	758.9
120°	805.8	807.8	809.9	810.9	810.9	810.9	810.9	810.9
122.5°	857.5	859.0	860.4	861.2	861.4	861.6	861.9	862.1
125°	930.5	931.0	931.5	932.0	932.5	933.1	933.6	934.1
127.5°	1003.6	1004.4	1005.2	1005.4	1004.9	1004.4	1003.9	1003.3
130°	1047.7	1048.7	1049.8	1050.0	1049.5	1049.0	1048.5	1048.0
132.5°	1089.5	1090.6	1091.6	1091.7	1091.0	1090.3	1089.6	1088.8
135°	1152.9	1153.7	1154.5	1154.5	1153.7	1152.9	1152.1	1151.4
137.5°	1209.4	1210.6	1211.8	1212.2	1211.7	1211.2	1210.7	1210.1
140°	1245.2	1246.2	1247.3	1247.5	1247.0	1246.5	1246.0	1245.5
142.5°	1279.2	1280.0	1280.8	1280.9	1280.2	1279.4	1278.7	1278.0
145°	1326.7	1327.2	1327.7	1327.9	1327.9	1327.9	1327.9	1327.9
147.5°	1369.2	1369.7	1370.2	1369.9	1368.7	1367.5	1366.3	1365.1
150°	1395.2	1395.7	1396.2	1396.1	1395.3	1394.6	1393.8	1393.0
152.5°	1418.3	1419.3	1420.2	1420.1	1418.9	1417.7	1416.5	1415.3
155°	1450.2	1451.5	1452.8	1452.6	1451.1	1449.6	1448.0	1446.5
157.5°	1477.9	1479.4	1481.0	1480.8	1478.8	1476.7	1474.7	1472.7
160°	1493.7	1495.2	1496.8	1496.7	1494.9	1493.1	1491.2	1489.4
162.5°	1508.1	1509.8	1511.6	1511.6	1510.0	1508.4	1506.8	1505.2
165°	1527.3	1529.3	1531.4	1531.5	1529.7	1527.9	1526.1	1524.3
167.5°	1542.1	1544.2	1546.3	1546.3	1544.2	1542.1	1540.1	1538.0
170°	1550.5	1552.6	1554.6	1554.6	1552.6	1550.5	1548.4	1546.4
172.5°	1556.1	1558.1	1560.2	1560.1	1557.8	1555.6	1553.3	1551.0
175°	1562.8	1564.6	1566.4	1566.2	1564.2	1562.1	1560.1	1558.0
177.5°	1565.2	1566.9	1568.5	1568.3	1566.3	1564.2	1562.1	1560.1
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8

(END OF REPORT)