

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332028-830

Luminaire Tested: **S123DIP-S1000D1025U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332028-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D1025U830-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7317.6 lumens
Efficiency: N/A
Efficacy: 121.0 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332028-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332028-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55				
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52	47				
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	40				
3	83	73	66	60	77	68	62	57	59	54	50	51	47	44	43	40	38	34				
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	38	35	33	29				
5	70	58	50	44	64	54	47	42	47	42	37	41	36	33	34	31	29	25				
6	64	52	44	38	59	49	42	36	43	37	33	37	32	29	31	28	25	22				
7	59	47	39	34	55	44	37	32	39	33	29	33	29	26	29	25	22	20				
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	26	23	20	18				
9	51	39	32	27	48	37	30	25	32	27	23	28	24	21	24	21	18	16				
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	17	15				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14249	14249	14249	14249
5°	16993	14311	12682	14311
10°	21270	14238	11455	14238
15°	26088	14123	10664	14123
20°	31078	13945	10153	13945
25°	32999	13726	10041	13726
30°	28285	13569	10092	13569
35°	19671	13341	10198	13341
40°	14816	13078	10166	13078
45°	12301	12683	10036	12683
50°	11020	11879	9945	11879
55°	10303	11012	9822	11012
60°	9664	10107	9722	10107
65°	9085	9212	9411	9212
70°	8519	8195	8960	8195
75°	7627	7178	8218	7178
80°	6676	5883	7073	5883
85°	5224	4273	4755	4273



TEST NUMBER: P332028-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.4	1.8
10°-20°	418.2	5.7
20°-30°	701.8	9.6
30°-40°	794.6	10.9
40°-50°	712.6	9.7
50°-60°	575.1	7.9
60°-70°	400.7	5.5
70°-80°	210.6	2.9
80°-90°	55.1	0.8
90°-100°	78.0	1.1
100°-110°	233.5	3.2
110°-120°	397.2	5.4
120°-130°	522.5	7.1
130°-140°	587.2	8.0
140°-150°	577.2	7.9
150°-160°	486.0	6.6
160°-170°	323.5	4.4
170°-180°	113.3	1.5
0°-30°	1250.4	17.1
0°-40°	2045.0	27.9
0°-60°	3332.7	45.5
0°-90°	3999.1	54.7
90°-120°	708.8	9.7
90°-150°	2395.7	32.7
90°-180°	3318.0	45.3
0°-180°	7317.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1324	1324	1324	1324	1324	
5°	1573	1324	1174	1324	1573	163
15°	2341	1267	957	1267	2341	676
25°	2778	1156	845	1156	2778	1219
35°	1497	1015	776	1015	1497	973
45°	808	833	659	833	808	640
55°	549	587	523	587	549	493
65°	357	362	370	362	357	355
75°	183	173	198	173	183	196
85°	42	35	38	35	42	51
90°	28	1	28	1	28	16
95°	73	56	73	56	73	75
105°	224	212	224	212	224	238
115°	401	400	401	400	401	397
125°	579	585	579	585	579	517
135°	758	759	758	759	758	583
145°	921	921	921	921	921	575
155°	1053	1055	1053	1055	1053	485
165°	1145	1149	1145	1149	1145	323
175°	1190	1195	1190	1195	1190	113
180°	1198	1198	1198	1198	1198	



TEST NUMBER: P332028-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8
2.5°	1404.9	1403.9	1401.3	1403.4	1399.3	1393.6	1393.1	1388.0	1373.1	1372.1	1368.0
5°	1572.7	1567.5	1566.9	1566.3	1557.3	1545.1	1522.0	1520.1	1489.3	1473.9	1455.3
7.5°	1790.0	1792.7	1783.3	1775.1	1747.7	1729.6	1704.8	1673.1	1635.3	1596.9	1571.4
10°	1946.0	1967.2	1940.9	1922.9	1906.2	1874.8	1838.2	1792.7	1747.2	1693.9	1653.5
12.5°	2113.3	2123.6	2118.4	2101.5	2075.6	2027.7	1962.9	1912.8	1870.9	1782.2	1746.3
15°	2341.1	2380.2	2355.2	2297.4	2298.8	2253.2	2168.5	2075.6	2026.2	1948.5	1842.8
17.5°	2583.8	2588.7	2578.0	2529.9	2497.8	2435.2	2357.1	2267.9	2167.9	2074.0	1961.8
20°	2713.1	2709.2	2686.8	2661.7	2606.6	2557.9	2472.6	2373.1	2244.9	2152.5	2030.0
22.5°	2784.9	2778.5	2767.9	2746.9	2701.0	2648.7	2572.1	2463.4	2341.4	2214.1	2072.6
25°	2778.5	2786.8	2788.1	2782.4	2766.4	2734.9	2674.6	2588.0	2466.2	2302.6	2155.1
27.5°	2527.1	2538.9	2573.1	2603.6	2637.5	2672.2	2667.6	2624.6	2534.4	2393.1	2212.8
30°	2275.7	2250.0	2313.5	2393.7	2448.2	2544.4	2598.3	2601.5	2550.8	2429.6	2253.8
32.5°	1926.7	1954.9	1983.0	2081.7	2200.8	2308.9	2416.1	2502.5	2512.3	2431.7	2277.9
35°	1497.0	1532.3	1583.6	1634.9	1763.2	1873.5	2062.1	2226.3	2357.1	2374.5	2280.1
37.5°	1206.4	1223.8	1256.2	1307.7	1391.6	1522.4	1668.3	1875.8	2065.4	2206.4	2212.5
40°	1054.4	1059.6	1096.2	1135.3	1203.2	1311.0	1442.5	1625.9	1852.9	2049.9	2132.0
42.5°	940.6	951.8	967.3	1004.9	1059.0	1140.1	1262.3	1414.0	1622.1	1848.7	2009.3
45°	808.1	821.0	830.6	855.6	894.1	948.6	1034.0	1172.4	1330.9	1565.0	1781.1
47.5°	720.7	721.7	728.9	747.7	773.9	814.8	875.2	964.1	1109.6	1299.5	1521.4
50°	658.1	668.4	670.9	685.6	706.2	736.3	786.4	862.0	981.4	1148.1	1352.1
52.5°	614.0	617.0	624.2	634.9	652.8	676.3	719.6	778.9	872.5	1014.6	1202.2
55°	549.0	549.0	556.1	564.4	574.7	595.9	624.7	668.4	739.5	849.9	1005.0
57.5°	489.0	492.2	497.2	499.7	508.5	522.5	546.6	579.7	632.8	717.7	841.1
60°	448.9	454.8	454.1	459.2	466.9	477.9	498.3	525.3	572.8	640.7	744.7
62.5°	414.1	413.7	413.6	419.7	427.4	437.8	451.2	474.5	514.8	575.0	663.5
65°	356.7	355.3	359.9	363.6	366.3	373.9	384.2	404.7	431.7	476.5	545.2
67.5°	305.6	301.8	304.3	305.6	309.9	315.9	325.6	338.3	359.7	395.8	447.4
70°	270.7	267.5	266.8	268.1	271.9	276.4	283.5	295.7	315.6	344.4	382.3
72.5°	234.8	232.5	232.4	235.3	237.0	240.0	245.0	256.2	271.9	293.6	328.9
75°	183.4	183.4	183.4	184.1	186.0	188.6	192.4	198.2	210.4	225.7	249.5
77.5°	137.5	137.4	136.6	136.5	139.3	140.4	141.4	146.8	153.5	163.9	181.3
80°	107.7	104.5	105.8	107.7	109.1	109.7	111.6	112.9	118.7	124.4	136.6
82.5°	80.0	77.4	77.6	80.6	80.8	81.4	83.4	85.2	87.4	92.7	99.2
85°	42.3	42.3	43.0	43.0	43.6	43.0	44.9	45.5	45.5	48.7	52.6
87.5°	21.0	19.9	20.4	20.8	20.2	20.5	20.9	21.3	21.6	22.0	22.0
90°	28.2	27.8	27.4	27.0	26.6	25.9	25.1	24.2	23.4	22.6	19.9
92.5°	38.0	38.3	38.5	38.7	39.0	38.8	38.2	37.5	36.8	36.1	34.6
95°	73.4	73.4	73.4	73.4	73.4	73.0	72.1	71.3	70.5	69.7	68.0
97.5°	112.9	113.0	113.1	113.2	113.2	112.8	111.9	110.8	109.9	109.0	107.7
100°	143.0	142.6	142.1	141.8	141.4	140.8	140.2	139.6	138.9	138.3	137.2
102.5°	173.9	174.0	174.0	174.1	174.2	173.9	173.3	172.7	172.0	171.4	170.0
105°	223.9	223.5	223.1	222.6	222.3	222.1	222.1	222.1	222.1	222.1	220.2
107.5°	276.1	276.3	276.5	276.8	277.0	276.8	276.2	275.5	274.8	274.2	273.4
110°	311.4	311.9	312.3	312.6	313.1	312.9	312.1	311.2	310.4	309.5	309.2



TEST NUMBER: P332028-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	349.0	349.1	349.2	349.3	349.4	348.9	347.9	346.9	345.9	344.9	344.9
115°	400.8	401.1	401.2	401.4	401.6	401.6	401.4	401.2	401.1	400.8	401.2
117.5°	453.3	453.9	454.5	455.1	455.6	456.0	456.0	456.0	456.1	456.1	456.7
120°	490.2	490.6	491.1	491.4	491.8	492.2	492.4	492.6	492.8	493.0	494.1
122.5°	525.6	526.1	526.7	527.4	527.9	528.5	529.0	529.5	530.1	530.7	531.2
125°	578.6	579.5	580.3	581.2	581.9	582.8	583.6	584.5	585.3	586.2	586.5
127.5°	631.5	632.4	633.4	634.4	635.4	636.4	637.6	638.8	639.9	641.1	641.6
130°	666.1	667.6	669.0	670.5	671.9	673.2	673.9	674.8	675.6	676.5	677.1
132.5°	702.3	703.4	704.6	705.7	706.8	707.8	708.9	709.8	710.9	711.8	712.3
135°	758.4	758.7	759.1	759.6	760.0	760.6	761.5	762.3	763.2	763.9	764.2
137.5°	807.9	808.6	809.4	810.2	811.0	811.8	812.8	813.6	814.5	815.3	814.8
140°	840.2	841.7	843.1	844.6	846.0	846.9	847.1	847.3	847.5	847.7	847.5
142.5°	873.3	874.4	875.5	876.7	877.8	878.4	878.7	878.9	879.1	879.3	878.9
145°	921.1	921.9	922.7	923.6	924.4	924.9	925.2	925.4	925.6	925.8	925.2
147.5°	963.7	964.9	966.1	967.4	968.7	969.3	969.3	969.3	969.3	969.3	968.7
150°	990.7	991.9	993.3	994.5	995.7	996.4	996.4	996.4	996.4	996.4	996.0
152.5°	1017.1	1018.1	1019.3	1020.3	1021.4	1021.8	1021.4	1021.2	1020.8	1020.5	1020.2
155°	1052.8	1054.2	1055.7	1057.2	1058.7	1058.9	1058.2	1057.3	1056.5	1055.6	1055.5
157.5°	1085.3	1086.6	1087.7	1088.9	1090.1	1090.2	1089.3	1088.4	1087.6	1086.7	1086.6
160°	1106.5	1107.3	1108.1	1109.0	1109.7	1109.7	1108.6	1107.6	1106.5	1105.5	1105.5
162.5°	1122.3	1123.6	1124.9	1126.2	1127.6	1127.8	1126.7	1125.7	1124.6	1123.6	1123.4
165°	1145.0	1146.5	1147.9	1149.4	1150.8	1150.9	1149.7	1148.5	1147.2	1145.9	1145.9
167.5°	1164.4	1165.7	1167.0	1168.3	1169.6	1169.6	1168.3	1167.0	1165.7	1164.4	1164.2
170°	1174.2	1175.6	1177.1	1178.6	1180.1	1180.1	1178.6	1177.1	1175.6	1174.2	1174.2
172.5°	1181.7	1183.2	1184.7	1186.1	1187.6	1187.6	1186.4	1185.1	1183.7	1182.4	1182.4
175°	1190.1	1191.7	1193.1	1194.6	1196.0	1196.2	1194.9	1193.6	1192.4	1191.1	1191.1
177.5°	1194.7	1195.9	1197.0	1198.3	1199.4	1199.5	1198.4	1197.5	1196.5	1195.4	1195.4
180°	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7



TEST NUMBER: P332028-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8
2.5°	1364.9	1360.7	1356.7	1349.5	1343.3	1334.6	1332.0	1329.0	1319.7	1311.5	1305.3
5°	1448.2	1432.9	1410.4	1389.9	1373.2	1350.8	1337.9	1324.5	1305.2	1287.9	1273.8
7.5°	1535.5	1505.2	1470.4	1432.6	1397.5	1363.6	1336.2	1311.9	1285.0	1259.4	1239.5
10°	1604.8	1561.1	1512.4	1459.8	1414.9	1371.3	1334.7	1302.7	1268.0	1237.8	1212.9
12.5°	1683.8	1619.1	1551.9	1488.0	1434.9	1374.4	1330.1	1289.3	1250.1	1213.8	1185.7
15°	1777.3	1695.2	1615.7	1527.8	1447.0	1371.3	1318.7	1267.4	1221.8	1184.7	1148.8
17.5°	1862.5	1769.4	1664.6	1557.8	1460.3	1370.6	1296.9	1238.9	1181.9	1136.4	1100.6
20°	1910.7	1804.9	1686.2	1575.3	1467.5	1367.4	1286.7	1217.4	1155.7	1107.7	1067.2
22.5°	1952.3	1828.4	1705.7	1587.1	1467.0	1359.2	1267.6	1196.4	1129.6	1082.5	1039.5
25°	1995.4	1847.2	1724.1	1584.9	1450.9	1339.3	1236.6	1155.7	1089.1	1034.0	989.7
27.5°	2032.3	1846.0	1699.8	1550.1	1425.4	1313.5	1204.0	1117.3	1046.5	986.6	941.7
30°	2056.9	1848.5	1674.7	1526.5	1400.8	1285.3	1178.8	1091.7	1017.3	956.3	914.0
32.5°	2072.4	1846.9	1651.6	1493.6	1361.8	1259.7	1151.7	1061.4	985.0	925.0	884.2
35°	2081.3	1835.7	1611.8	1425.8	1298.8	1199.4	1109.0	1015.3	935.2	879.4	833.2
37.5°	2063.3	1811.9	1565.7	1360.4	1221.3	1123.4	1047.4	967.6	890.9	829.4	789.7
40°	2035.1	1796.6	1529.7	1314.2	1168.0	1073.7	1008.9	930.7	855.0	796.6	759.4
42.5°	1981.2	1765.2	1490.3	1262.9	1112.6	1018.2	958.7	893.2	821.6	766.9	729.6
45°	1849.7	1697.1	1431.0	1185.9	1030.7	933.2	880.6	833.2	768.4	715.1	683.1
47.5°	1667.4	1594.6	1345.3	1104.8	945.3	851.5	796.8	758.7	711.3	668.4	637.5
50°	1540.6	1510.5	1287.2	1049.3	888.3	796.6	744.0	709.4	675.4	632.4	604.2
52.5°	1394.4	1413.0	1219.6	991.8	830.4	740.2	690.7	663.2	632.3	597.0	572.4
55°	1188.5	1255.8	1102.6	895.4	744.0	658.1	611.2	586.8	568.9	542.6	521.4
57.5°	995.7	1081.4	976.1	796.0	659.2	585.0	540.2	513.6	502.1	488.3	471.6
60°	881.3	965.9	885.8	729.2	602.3	531.7	491.9	469.5	458.0	448.4	434.2
62.5°	779.2	864.9	797.5	661.6	546.3	480.9	446.3	424.3	415.4	410.4	398.3
65°	638.9	712.6	667.7	556.1	466.3	408.6	377.1	361.7	353.5	351.5	343.7
67.5°	519.9	576.1	543.4	461.3	390.6	340.7	314.1	301.0	294.5	293.9	288.1
70°	442.0	494.6	469.5	395.1	334.1	295.0	271.9	260.4	256.6	255.9	252.7
72.5°	381.4	418.0	398.1	336.1	289.0	253.4	236.6	224.5	220.1	221.0	218.9
75°	282.2	309.8	298.2	255.2	217.4	194.4	180.2	172.6	168.7	170.6	168.1
77.5°	203.0	220.6	210.1	180.4	157.0	140.3	130.0	125.2	121.8	121.6	120.5
80°	153.3	163.5	157.8	139.8	120.6	106.5	98.1	94.9	93.0	92.4	91.7
82.5°	109.1	117.9	111.1	98.8	85.7	77.2	72.5	68.2	66.8	67.2	66.5
85°	55.1	58.3	55.8	48.1	43.0	39.1	36.6	34.6	33.4	34.0	32.7
87.5°	22.4	22.3	20.3	17.8	16.3	14.3	13.9	12.5	11.9	12.3	12.3
90°	17.2	14.4	11.7	9.3	7.3	5.1	3.0	0.9	3.0	5.1	7.3
92.5°	33.0	31.5	30.0	28.5	27.1	25.6	24.2	22.8	24.2	25.6	27.1
95°	66.3	64.6	63.0	61.4	59.9	58.4	56.9	55.5	56.9	58.4	59.9
97.5°	106.5	105.3	104.1	102.9	101.9	100.8	99.7	98.6	99.7	100.8	101.9
100°	136.2	135.2	134.1	133.0	131.7	130.4	129.2	128.0	129.2	130.4	131.7
102.5°	168.6	167.3	165.9	164.9	164.1	163.3	162.6	161.8	162.6	163.3	164.1
105°	218.3	216.4	214.5	213.4	212.9	212.5	212.1	211.7	212.1	212.5	212.9
107.5°	272.7	271.9	271.2	270.7	270.4	270.1	269.9	269.7	269.9	270.1	270.4
110°	308.7	308.3	307.8	307.5	307.0	306.6	306.2	305.8	306.2	306.6	307.0



TEST NUMBER: P332028-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	344.8	344.7	344.6	344.4	344.1	343.9	343.7	343.4	343.7	343.9	344.1
115°	401.6	402.1	402.5	402.4	401.7	401.1	400.5	399.8	400.5	401.1	401.7
117.5°	457.2	457.8	458.3	458.4	458.0	457.5	457.1	456.7	457.1	457.5	458.0
120°	495.1	496.2	497.2	497.1	495.9	494.6	493.3	492.1	493.3	494.6	495.9
122.5°	531.7	532.3	532.8	532.6	531.7	530.7	529.9	529.0	529.9	530.7	531.7
125°	587.0	587.4	587.9	587.7	587.1	586.4	585.9	585.2	585.9	586.4	587.1
127.5°	642.1	642.4	642.9	642.5	641.1	639.8	638.5	637.2	638.5	639.8	641.1
130°	677.7	678.3	679.0	678.4	676.7	675.1	673.4	671.8	673.4	675.1	676.7
132.5°	712.8	713.2	713.7	713.1	711.4	709.7	708.0	706.4	708.0	709.7	711.4
135°	764.4	764.6	764.8	764.3	763.0	761.8	760.5	759.3	760.5	761.8	763.0
137.5°	814.3	813.7	813.1	812.4	811.3	810.3	809.3	808.2	809.3	810.3	811.3
140°	847.3	847.1	846.9	846.2	845.2	844.1	843.1	842.1	843.1	844.1	845.2
142.5°	878.5	878.2	877.8	877.1	876.1	875.1	873.9	872.9	873.9	875.1	876.1
145°	924.5	923.9	923.3	922.7	922.4	921.9	921.5	921.1	921.5	921.9	922.4
147.5°	968.1	967.5	967.0	966.3	965.5	964.8	964.0	963.3	964.0	964.8	965.5
150°	995.5	995.1	994.7	994.3	993.8	993.4	993.1	992.6	993.1	993.4	993.8
152.5°	1019.9	1019.7	1019.5	1019.0	1018.4	1017.9	1017.3	1016.7	1017.3	1017.9	1018.4
155°	1055.2	1055.0	1054.8	1054.7	1054.7	1054.7	1054.7	1054.7	1054.7	1054.7	1054.7
157.5°	1086.4	1086.2	1086.0	1086.1	1086.3	1086.6	1086.8	1087.0	1086.8	1086.6	1086.3
160°	1105.5	1105.5	1105.5	1105.7	1106.2	1106.5	1106.9	1107.4	1106.9	1106.5	1106.2
162.5°	1123.2	1123.0	1122.9	1123.1	1123.7	1124.3	1124.8	1125.5	1124.8	1124.3	1123.7
165°	1145.9	1145.9	1145.9	1146.3	1146.9	1147.5	1148.1	1148.8	1148.1	1147.5	1146.9
167.5°	1164.0	1163.9	1163.8	1164.0	1164.9	1165.7	1166.6	1167.4	1166.6	1165.7	1164.9
170°	1174.2	1174.2	1174.2	1174.6	1175.4	1176.3	1177.1	1178.0	1177.1	1176.3	1175.4
172.5°	1182.4	1182.4	1182.4	1182.9	1183.7	1184.6	1185.4	1186.2	1185.4	1184.6	1183.7
175°	1191.1	1191.1	1191.1	1191.6	1192.4	1193.2	1194.0	1194.9	1194.0	1193.2	1192.4
177.5°	1195.4	1195.4	1195.4	1195.8	1196.5	1197.1	1197.8	1198.4	1197.8	1197.1	1196.5
180°	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7



TEST NUMBER: P332028-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8
2.5°	1301.7	1298.2	1293.1	1285.3	1279.2	1269.4	1269.4	1271.0	1271.0	1270.5	1269.4
5°	1262.3	1252.6	1241.1	1227.7	1213.5	1199.4	1196.8	1191.8	1187.9	1185.2	1182.0
7.5°	1220.6	1203.5	1186.7	1167.8	1150.7	1136.4	1126.5	1118.3	1113.0	1107.4	1103.3
10°	1192.3	1171.2	1151.3	1131.4	1109.6	1092.3	1081.4	1073.7	1067.9	1062.8	1060.3
12.5°	1159.0	1134.7	1112.9	1093.9	1070.1	1052.3	1041.9	1038.3	1031.5	1020.7	1015.0
15°	1110.2	1087.8	1061.5	1032.6	1021.1	999.3	987.1	981.4	977.5	969.1	966.6
17.5°	1068.6	1039.2	1009.7	988.2	966.7	949.0	942.2	935.0	929.9	923.1	921.1
20°	1035.2	1008.9	981.9	958.8	936.4	917.2	911.4	906.3	901.2	898.0	895.4
22.5°	1001.4	975.1	952.7	931.1	907.2	894.6	888.3	882.7	879.1	876.9	874.3
25°	953.8	930.7	905.7	886.4	867.1	858.8	855.0	851.8	849.2	846.0	845.4
27.5°	911.2	886.0	865.7	847.8	834.0	827.0	823.3	821.7	822.3	823.4	824.2
30°	879.4	856.3	839.6	824.2	811.3	804.9	804.3	804.3	806.9	807.5	808.8
32.5°	850.1	831.1	814.5	799.6	789.9	785.4	787.9	787.9	789.9	791.6	793.9
35°	807.5	790.8	778.0	765.2	756.9	758.7	760.1	761.3	764.5	768.4	771.0
37.5°	766.9	752.3	739.0	729.0	725.2	728.6	731.7	734.4	738.1	741.0	743.7
40°	737.6	726.7	713.9	704.9	706.2	708.1	710.7	713.9	717.1	719.0	721.6
42.5°	710.4	699.0	689.3	681.8	683.6	686.1	687.6	689.3	693.0	696.4	698.0
45°	669.0	660.0	651.0	646.5	647.8	649.1	650.4	652.3	655.5	658.1	658.7
47.5°	622.4	616.1	610.1	605.8	607.8	607.3	609.0	613.0	614.1	615.6	619.2
50°	592.7	586.8	579.9	578.5	578.5	578.5	579.2	584.3	584.3	586.8	589.5
52.5°	559.8	556.1	551.6	549.3	548.3	548.3	550.9	553.6	554.6	558.2	560.7
55°	511.2	507.4	503.5	501.5	500.3	501.5	506.7	507.9	511.2	513.1	515.0
57.5°	460.5	457.6	454.5	453.5	453.2	454.9	457.7	461.6	462.3	468.3	471.2
60°	427.2	422.6	420.1	420.1	418.9	424.6	423.3	429.7	431.0	434.9	439.3
62.5°	392.8	386.7	385.7	385.7	387.6	389.2	391.0	393.8	397.2	402.0	405.5
65°	337.3	334.1	338.7	338.0	336.8	340.5	340.5	343.7	347.6	352.1	359.2
67.5°	284.9	283.2	283.6	283.6	285.6	287.8	289.5	292.4	297.0	301.7	306.3
70°	249.5	251.5	248.3	250.8	252.7	253.4	254.7	258.4	263.6	266.8	271.9
72.5°	215.1	215.0	215.4	216.4	218.3	219.5	220.7	225.2	230.7	233.5	237.6
75°	165.5	164.9	166.7	166.7	169.9	171.3	172.6	174.5	179.6	183.4	186.6
77.5°	120.8	121.6	121.2	123.4	122.5	122.7	126.8	128.7	129.2	136.8	138.5
80°	91.0	92.4	93.0	93.7	94.3	93.0	97.5	99.4	99.4	103.9	107.1
82.5°	65.4	66.2	67.9	68.5	68.6	69.9	70.3	71.7	73.2	75.2	79.4
85°	32.7	34.6	35.3	34.6	35.3	34.0	35.9	36.6	37.2	37.2	37.2
87.5°	12.2	13.1	13.1	14.2	14.2	15.3	15.5	14.6	14.8	16.5	14.5
90°	9.3	11.7	14.4	17.2	19.9	22.6	23.4	24.2	25.1	25.9	26.6
92.5°	28.5	30.0	31.5	33.0	34.6	36.1	36.8	37.5	38.2	38.8	39.0
95°	61.4	63.0	64.6	66.3	68.0	69.7	70.5	71.3	72.1	73.0	73.4
97.5°	102.9	104.1	105.3	106.5	107.7	109.0	109.9	110.8	111.9	112.8	113.2
100°	133.0	134.1	135.2	136.2	137.2	138.3	138.9	139.6	140.2	140.8	141.4
102.5°	164.9	165.9	167.3	168.6	170.0	171.4	172.0	172.7	173.3	173.9	174.2
105°	213.4	214.5	216.4	218.3	220.2	222.1	222.1	222.1	222.1	222.1	222.3
107.5°	270.7	271.2	271.9	272.7	273.4	274.2	274.8	275.5	276.2	276.8	277.0
110°	307.5	307.8	308.3	308.7	309.2	309.5	310.4	311.2	312.1	312.9	313.1



TEST NUMBER: P332028-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	344.4	344.6	344.7	344.8	344.9	344.9	345.9	346.9	347.9	348.9	349.4
115°	402.4	402.5	402.1	401.6	401.2	400.8	401.1	401.2	401.4	401.6	401.6
117.5°	458.4	458.3	457.8	457.2	456.7	456.1	456.1	456.0	456.0	456.0	455.6
120°	497.1	497.2	496.2	495.1	494.1	493.0	492.8	492.6	492.4	492.2	491.8
122.5°	532.6	532.8	532.3	531.7	531.2	530.7	530.1	529.5	529.0	528.5	527.9
125°	587.7	587.9	587.4	587.0	586.5	586.2	585.3	584.5	583.6	582.8	581.9
127.5°	642.5	642.9	642.4	642.1	641.6	641.1	639.9	638.8	637.6	636.4	635.4
130°	678.4	679.0	678.3	677.7	677.1	676.5	675.6	674.8	673.9	673.2	671.9
132.5°	713.1	713.7	713.2	712.8	712.3	711.8	710.9	709.8	708.9	707.8	706.8
135°	764.3	764.8	764.6	764.4	764.2	763.9	763.2	762.3	761.5	760.6	760.0
137.5°	812.4	813.1	813.7	814.3	814.8	815.3	814.5	813.6	812.8	811.8	811.0
140°	846.2	846.9	847.1	847.3	847.5	847.7	847.5	847.3	847.1	846.9	846.0
142.5°	877.1	877.8	878.2	878.5	878.9	879.3	879.1	878.9	878.7	878.4	877.8
145°	922.7	923.3	923.9	924.5	925.2	925.8	925.6	925.4	925.2	924.9	924.4
147.5°	966.3	967.0	967.5	968.1	968.7	969.3	969.3	969.3	969.3	969.3	968.7
150°	994.3	994.7	995.1	995.5	996.0	996.4	996.4	996.4	996.4	996.4	995.7
152.5°	1019.0	1019.5	1019.7	1019.9	1020.2	1020.5	1020.8	1021.2	1021.4	1021.8	1021.4
155°	1054.7	1054.8	1055.0	1055.2	1055.5	1055.6	1056.5	1057.3	1058.2	1058.9	1058.7
157.5°	1086.1	1086.0	1086.2	1086.4	1086.6	1086.7	1087.6	1088.4	1089.3	1090.2	1090.1
160°	1105.7	1105.5	1105.5	1105.5	1105.5	1105.5	1106.5	1107.6	1108.6	1109.7	1109.7
162.5°	1123.1	1122.9	1123.0	1123.2	1123.4	1123.6	1124.6	1125.7	1126.7	1127.8	1127.6
165°	1146.3	1145.9	1145.9	1145.9	1145.9	1145.9	1147.2	1148.5	1149.7	1150.9	1150.8
167.5°	1164.0	1163.8	1163.9	1164.0	1164.2	1164.4	1165.7	1167.0	1168.3	1169.6	1169.6
170°	1174.6	1174.2	1174.2	1174.2	1174.2	1174.2	1175.6	1177.1	1178.6	1180.1	1180.1
172.5°	1182.9	1182.4	1182.4	1182.4	1182.4	1182.4	1183.7	1185.1	1186.4	1187.6	1187.6
175°	1191.6	1191.1	1191.1	1191.1	1191.1	1191.1	1192.4	1193.6	1194.9	1196.2	1196.0
177.5°	1195.8	1195.4	1195.4	1195.4	1195.4	1195.4	1196.5	1197.5	1198.4	1199.5	1199.4
180°	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7



TEST NUMBER: P332028-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8
2.5°	1265.8	1265.4	1268.9	1266.4	1268.9	1265.4	1265.8	1269.4	1270.5	1271.0	1271.0
5°	1178.3	1180.2	1173.7	1173.7	1173.7	1180.2	1178.3	1182.0	1185.2	1187.9	1191.8
7.5°	1100.2	1097.4	1097.7	1094.2	1097.7	1097.4	1100.2	1103.3	1107.4	1113.0	1118.3
10°	1052.5	1048.7	1047.4	1048.0	1047.4	1048.7	1052.5	1060.3	1062.8	1067.9	1073.7
12.5°	1013.0	1012.3	1003.8	1003.9	1003.8	1012.3	1013.0	1015.0	1020.7	1031.5	1038.3
15°	966.6	954.4	953.1	957.0	953.1	954.4	966.6	966.6	969.1	977.5	981.4
17.5°	920.0	913.6	914.0	912.1	914.0	913.6	920.0	921.1	923.1	929.9	935.0
20°	895.4	891.6	890.9	886.4	890.9	891.6	895.4	895.4	898.0	901.2	906.3
22.5°	872.8	871.6	871.9	867.0	871.9	871.6	872.8	874.3	876.9	879.1	882.7
25°	844.7	847.9	845.4	845.4	845.4	847.9	844.7	845.4	846.0	849.2	851.8
27.5°	825.8	825.6	824.3	824.3	824.3	825.6	825.8	824.2	823.4	822.3	821.7
30°	811.3	810.7	812.0	812.0	812.0	810.7	811.3	808.8	807.5	806.9	804.3
32.5°	797.0	797.9	798.1	798.6	798.1	797.9	797.0	793.9	791.6	789.9	787.9
35°	774.8	775.4	777.4	776.1	777.4	775.4	774.8	771.0	768.4	764.5	761.3
37.5°	744.8	747.7	747.1	748.1	747.1	747.7	744.8	743.7	741.0	738.1	734.4
40°	722.2	724.2	723.5	723.5	723.5	724.2	722.2	721.6	719.0	717.1	713.9
42.5°	699.1	700.5	698.9	697.9	698.9	700.5	699.1	698.0	696.4	693.0	689.3
45°	661.3	660.0	661.9	659.3	661.9	660.0	661.3	658.7	658.1	655.5	652.3
47.5°	619.0	620.2	620.8	622.6	620.8	620.2	619.0	619.2	615.6	614.1	613.0
50°	590.7	594.6	594.6	593.9	594.6	594.6	590.7	589.5	586.8	584.3	584.3
52.5°	563.0	564.8	567.4	567.2	567.4	564.8	563.0	560.7	558.2	554.6	553.6
55°	520.2	521.4	522.7	523.4	522.7	521.4	520.2	515.0	513.1	511.2	507.9
57.5°	475.8	475.2	478.3	479.3	478.3	475.2	475.8	471.2	468.3	462.3	461.6
60°	444.5	444.5	449.6	451.6	449.6	444.5	444.5	439.3	434.9	431.0	429.7
62.5°	411.1	413.2	418.3	415.7	418.3	413.2	411.1	405.5	402.0	397.2	393.8
65°	362.4	367.5	366.8	369.5	366.8	367.5	362.4	359.2	352.1	347.6	343.7
67.5°	311.4	314.6	319.2	319.7	319.2	314.6	311.4	306.3	301.7	297.0	292.4
70°	277.1	280.3	282.9	284.7	282.9	280.3	277.1	271.9	266.8	263.6	258.4
72.5°	243.7	245.4	251.6	248.8	251.6	245.4	243.7	237.6	233.5	230.7	225.2
75°	191.1	195.6	199.4	197.6	199.4	195.6	191.1	186.6	183.4	179.6	174.5
77.5°	141.4	145.8	147.6	146.0	147.6	145.8	141.4	138.5	136.8	129.2	128.7
80°	111.6	110.9	114.8	114.1	114.8	110.9	111.6	107.1	103.9	99.4	99.4
82.5°	81.8	81.2	83.0	83.4	83.0	81.2	81.8	79.4	75.2	73.2	71.7
85°	39.8	41.7	39.1	38.5	39.1	41.7	39.8	37.2	37.2	37.2	36.6
87.5°	14.6	14.7	14.3	13.9	14.3	14.7	14.6	14.5	16.5	14.8	14.6
90°	27.0	27.4	27.8	28.2	27.8	27.4	27.0	26.6	25.9	25.1	24.2
92.5°	38.7	38.5	38.3	38.0	38.3	38.5	38.7	39.0	38.8	38.2	37.5
95°	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.0	72.1	71.3
97.5°	113.2	113.1	113.0	112.9	113.0	113.1	113.2	113.2	112.8	111.9	110.8
100°	141.8	142.1	142.6	143.0	142.6	142.1	141.8	141.4	140.8	140.2	139.6
102.5°	174.1	174.0	174.0	173.9	174.0	174.0	174.1	174.2	173.9	173.3	172.7
105°	222.6	223.1	223.5	223.9	223.5	223.1	222.6	222.3	222.1	222.1	222.1
107.5°	276.8	276.5	276.3	276.1	276.3	276.5	276.8	277.0	276.8	276.2	275.5
110°	312.6	312.3	311.9	311.4	311.9	312.3	312.6	313.1	312.9	312.1	311.2



TEST NUMBER: P332028-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	349.3	349.2	349.1	349.0	349.1	349.2	349.3	349.4	348.9	347.9	346.9
115°	401.4	401.2	401.1	400.8	401.1	401.2	401.4	401.6	401.6	401.4	401.2
117.5°	455.1	454.5	453.9	453.3	453.9	454.5	455.1	455.6	456.0	456.0	456.0
120°	491.4	491.1	490.6	490.2	490.6	491.1	491.4	491.8	492.2	492.4	492.6
122.5°	527.4	526.7	526.1	525.6	526.1	526.7	527.4	527.9	528.5	529.0	529.5
125°	581.2	580.3	579.5	578.6	579.5	580.3	581.2	581.9	582.8	583.6	584.5
127.5°	634.4	633.4	632.4	631.5	632.4	633.4	634.4	635.4	636.4	637.6	638.8
130°	670.5	669.0	667.6	666.1	667.6	669.0	670.5	671.9	673.2	673.9	674.8
132.5°	705.7	704.6	703.4	702.3	703.4	704.6	705.7	706.8	707.8	708.9	709.8
135°	759.6	759.1	758.7	758.4	758.7	759.1	759.6	760.0	760.6	761.5	762.3
137.5°	810.2	809.4	808.6	807.9	808.6	809.4	810.2	811.0	811.8	812.8	813.6
140°	844.6	843.1	841.7	840.2	841.7	843.1	844.6	846.0	846.9	847.1	847.3
142.5°	876.7	875.5	874.4	873.3	874.4	875.5	876.7	877.8	878.4	878.7	878.9
145°	923.6	922.7	921.9	921.1	921.9	922.7	923.6	924.4	924.9	925.2	925.4
147.5°	967.4	966.1	964.9	963.7	964.9	966.1	967.4	968.7	969.3	969.3	969.3
150°	994.5	993.3	991.9	990.7	991.9	993.3	994.5	995.7	996.4	996.4	996.4
152.5°	1020.3	1019.3	1018.1	1017.1	1018.1	1019.3	1020.3	1021.4	1021.8	1021.4	1021.2
155°	1057.2	1055.7	1054.2	1052.8	1054.2	1055.7	1057.2	1058.7	1058.9	1058.2	1057.3
157.5°	1088.9	1087.7	1086.6	1085.3	1086.6	1087.7	1088.9	1090.1	1090.2	1089.3	1088.4
160°	1109.0	1108.1	1107.3	1106.5	1107.3	1108.1	1109.0	1109.7	1109.7	1108.6	1107.6
162.5°	1126.2	1124.9	1123.6	1122.3	1123.6	1124.9	1126.2	1127.6	1127.8	1126.7	1125.7
165°	1149.4	1147.9	1146.5	1145.0	1146.5	1147.9	1149.4	1150.8	1150.9	1149.7	1148.5
167.5°	1168.3	1167.0	1165.7	1164.4	1165.7	1167.0	1168.3	1169.6	1169.6	1168.3	1167.0
170°	1178.6	1177.1	1175.6	1174.2	1175.6	1177.1	1178.6	1180.1	1180.1	1178.6	1177.1
172.5°	1186.1	1184.7	1183.2	1181.7	1183.2	1184.7	1186.1	1187.6	1187.6	1186.4	1185.1
175°	1194.6	1193.1	1191.7	1190.1	1191.7	1193.1	1194.6	1196.0	1196.2	1194.9	1193.6
177.5°	1198.3	1197.0	1195.9	1194.7	1195.9	1197.0	1198.3	1199.4	1199.5	1198.4	1197.5
180°	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7



TEST NUMBER: P332028-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8
2.5°	1269.4	1269.4	1279.2	1285.3	1293.1	1298.2	1301.7	1305.3	1311.5	1319.7	1329.0
5°	1196.8	1199.4	1213.5	1227.7	1241.1	1252.6	1262.3	1273.8	1287.9	1305.2	1324.5
7.5°	1126.5	1136.4	1150.7	1167.8	1186.7	1203.5	1220.6	1239.5	1259.4	1285.0	1311.9
10°	1081.4	1092.3	1109.6	1131.4	1151.3	1171.2	1192.3	1212.9	1237.8	1268.0	1302.7
12.5°	1041.9	1052.3	1070.1	1093.9	1112.9	1134.7	1159.0	1185.7	1213.8	1250.1	1289.3
15°	987.1	999.3	1021.1	1032.6	1061.5	1087.8	1110.2	1148.8	1184.7	1221.8	1267.4
17.5°	942.2	949.0	966.7	988.2	1009.7	1039.2	1068.6	1100.6	1136.4	1181.9	1238.9
20°	911.4	917.2	936.4	958.8	981.9	1008.9	1035.2	1067.2	1107.7	1155.7	1217.4
22.5°	888.3	894.6	907.2	931.1	952.7	975.1	1001.4	1039.5	1082.5	1129.6	1196.4
25°	855.0	858.8	867.1	886.4	905.7	930.7	953.8	989.7	1034.0	1089.1	1155.7
27.5°	823.3	827.0	834.0	847.8	865.7	886.0	911.2	941.7	986.6	1046.5	1117.3
30°	804.3	804.9	811.3	824.2	839.6	856.3	879.4	914.0	956.3	1017.3	1091.7
32.5°	787.9	785.4	789.9	799.6	814.5	831.1	850.1	884.2	925.0	985.0	1061.4
35°	760.1	758.7	756.9	765.2	778.0	790.8	807.5	833.2	879.4	935.2	1015.3
37.5°	731.7	728.6	725.2	729.0	739.0	752.3	766.9	789.7	829.4	890.9	967.6
40°	710.7	708.1	706.2	704.9	713.9	726.7	737.6	759.4	796.6	855.0	930.7
42.5°	687.6	686.1	683.6	681.8	689.3	699.0	710.4	729.6	766.9	821.6	893.2
45°	650.4	649.1	647.8	646.5	651.0	660.0	669.0	683.1	715.1	768.4	833.2
47.5°	609.0	607.3	607.8	605.8	610.1	616.1	622.4	637.5	668.4	711.3	758.7
50°	579.2	578.5	578.5	578.5	579.9	586.8	592.7	604.2	632.4	675.4	709.4
52.5°	550.9	548.3	548.3	549.3	551.6	556.1	559.8	572.4	597.0	632.3	663.2
55°	506.7	501.5	500.3	501.5	503.5	507.4	511.2	521.4	542.6	568.9	586.8
57.5°	457.7	454.9	453.2	453.5	454.5	457.6	460.5	471.6	488.3	502.1	513.6
60°	423.3	424.6	418.9	420.1	420.1	422.6	427.2	434.2	448.4	458.0	469.5
62.5°	391.0	389.2	387.6	385.7	385.7	386.7	392.8	398.3	410.4	415.4	424.3
65°	340.5	340.5	336.8	338.0	338.7	334.1	337.3	343.7	351.5	353.5	361.7
67.5°	289.5	287.8	285.6	283.6	283.6	283.2	284.9	288.1	293.9	294.5	301.0
70°	254.7	253.4	252.7	250.8	248.3	251.5	249.5	252.7	255.9	256.6	260.4
72.5°	220.7	219.5	218.3	216.4	215.4	215.0	215.1	218.9	221.0	220.1	224.5
75°	172.6	171.3	169.9	166.7	166.7	164.9	165.5	168.1	170.6	168.7	172.6
77.5°	126.8	122.7	122.5	123.4	121.2	121.6	120.8	120.5	121.6	121.8	125.2
80°	97.5	93.0	94.3	93.7	93.0	92.4	91.0	91.7	92.4	93.0	94.9
82.5°	70.3	69.9	68.6	68.5	67.9	66.2	65.4	66.5	67.2	66.8	68.2
85°	35.9	34.0	35.3	34.6	35.3	34.6	32.7	32.7	34.0	33.4	34.6
87.5°	15.5	15.3	14.2	14.2	13.1	13.1	12.2	12.3	12.3	11.9	12.5
90°	23.4	22.6	19.9	17.2	14.4	11.7	9.3	7.3	5.1	3.0	0.9
92.5°	36.8	36.1	34.6	33.0	31.5	30.0	28.5	27.1	25.6	24.2	22.8
95°	70.5	69.7	68.0	66.3	64.6	63.0	61.4	59.9	58.4	56.9	55.5
97.5°	109.9	109.0	107.7	106.5	105.3	104.1	102.9	101.9	100.8	99.7	98.6
100°	138.9	138.3	137.2	136.2	135.2	134.1	133.0	131.7	130.4	129.2	128.0
102.5°	172.0	171.4	170.0	168.6	167.3	165.9	164.9	164.1	163.3	162.6	161.8
105°	222.1	222.1	220.2	218.3	216.4	214.5	213.4	212.9	212.5	212.1	211.7
107.5°	274.8	274.2	273.4	272.7	271.9	271.2	270.7	270.4	270.1	269.9	269.7
110°	310.4	309.5	309.2	308.7	308.3	307.8	307.5	307.0	306.6	306.2	305.8



TEST NUMBER: P332028-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	345.9	344.9	344.9	344.8	344.7	344.6	344.4	344.1	343.9	343.7	343.4
115°	401.1	400.8	401.2	401.6	402.1	402.5	402.4	401.7	401.1	400.5	399.8
117.5°	456.1	456.1	456.7	457.2	457.8	458.3	458.4	458.0	457.5	457.1	456.7
120°	492.8	493.0	494.1	495.1	496.2	497.2	497.1	495.9	494.6	493.3	492.1
122.5°	530.1	530.7	531.2	531.7	532.3	532.8	532.6	531.7	530.7	529.9	529.0
125°	585.3	586.2	586.5	587.0	587.4	587.9	587.7	587.1	586.4	585.9	585.2
127.5°	639.9	641.1	641.6	642.1	642.4	642.9	642.5	641.1	639.8	638.5	637.2
130°	675.6	676.5	677.1	677.7	678.3	679.0	678.4	676.7	675.1	673.4	671.8
132.5°	710.9	711.8	712.3	712.8	713.2	713.7	713.1	711.4	709.7	708.0	706.4
135°	763.2	763.9	764.2	764.4	764.6	764.8	764.3	763.0	761.8	760.5	759.3
137.5°	814.5	815.3	814.8	814.3	813.7	813.1	812.4	811.3	810.3	809.3	808.2
140°	847.5	847.7	847.5	847.3	847.1	846.9	846.2	845.2	844.1	843.1	842.1
142.5°	879.1	879.3	878.9	878.5	878.2	877.8	877.1	876.1	875.1	873.9	872.9
145°	925.6	925.8	925.2	924.5	923.9	923.3	922.7	922.4	921.9	921.5	921.1
147.5°	969.3	969.3	968.7	968.1	967.5	967.0	966.3	965.5	964.8	964.0	963.3
150°	996.4	996.4	996.0	995.5	995.1	994.7	994.3	993.8	993.4	993.1	992.6
152.5°	1020.8	1020.5	1020.2	1019.9	1019.7	1019.5	1019.0	1018.4	1017.9	1017.3	1016.7
155°	1056.5	1055.6	1055.5	1055.2	1055.0	1054.8	1054.7	1054.7	1054.7	1054.7	1054.7
157.5°	1087.6	1086.7	1086.6	1086.4	1086.2	1086.0	1086.1	1086.3	1086.6	1086.8	1087.0
160°	1106.5	1105.5	1105.5	1105.5	1105.5	1105.5	1105.7	1106.2	1106.5	1106.9	1107.4
162.5°	1124.6	1123.6	1123.4	1123.2	1123.0	1122.9	1123.1	1123.7	1124.3	1124.8	1125.5
165°	1147.2	1145.9	1145.9	1145.9	1145.9	1145.9	1146.3	1146.9	1147.5	1148.1	1148.8
167.5°	1165.7	1164.4	1164.2	1164.0	1163.9	1163.8	1164.0	1164.9	1165.7	1166.6	1167.4
170°	1175.6	1174.2	1174.2	1174.2	1174.2	1174.2	1174.6	1175.4	1176.3	1177.1	1178.0
172.5°	1183.7	1182.4	1182.4	1182.4	1182.4	1182.4	1182.9	1183.7	1184.6	1185.4	1186.2
175°	1192.4	1191.1	1191.1	1191.1	1191.1	1191.1	1191.6	1192.4	1193.2	1194.0	1194.9
177.5°	1196.5	1195.4	1195.4	1195.4	1195.4	1195.4	1195.8	1196.5	1197.1	1197.8	1198.4
180°	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7



TEST NUMBER: P332028-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8
2.5°	1332.0	1334.6	1343.3	1349.5	1356.7	1360.7	1364.9	1368.0	1372.1	1373.1	1388.0
5°	1337.9	1350.8	1373.2	1389.9	1410.4	1432.9	1448.2	1455.3	1473.9	1489.3	1520.1
7.5°	1336.2	1363.6	1397.5	1432.6	1470.4	1505.2	1535.5	1571.4	1596.9	1635.3	1673.1
10°	1334.7	1371.3	1414.9	1459.8	1512.4	1561.1	1604.8	1653.5	1693.9	1747.2	1792.7
12.5°	1330.1	1374.4	1434.9	1488.0	1551.9	1619.1	1683.8	1746.3	1782.2	1870.9	1912.8
15°	1318.7	1371.3	1447.0	1527.8	1615.7	1695.2	1777.3	1842.8	1948.5	2026.2	2075.6
17.5°	1296.9	1370.6	1460.3	1557.8	1664.6	1769.4	1862.5	1961.8	2074.0	2167.9	2267.9
20°	1286.7	1367.4	1467.5	1575.3	1686.2	1804.9	1910.7	2030.0	2152.5	2244.9	2373.1
22.5°	1267.6	1359.2	1467.0	1587.1	1705.7	1828.4	1952.3	2072.6	2214.1	2341.4	2463.4
25°	1236.6	1339.3	1450.9	1584.9	1724.1	1847.2	1995.4	2155.1	2302.6	2466.2	2588.0
27.5°	1204.0	1313.5	1425.4	1550.1	1699.8	1846.0	2032.3	2212.8	2393.1	2534.4	2624.6
30°	1178.8	1285.3	1400.8	1526.5	1674.7	1848.5	2056.9	2253.8	2429.6	2550.8	2601.5
32.5°	1151.7	1259.7	1361.8	1493.6	1651.6	1846.9	2072.4	2277.9	2431.7	2512.3	2502.5
35°	1109.0	1199.4	1298.8	1425.8	1611.8	1835.7	2081.3	2280.1	2374.5	2357.1	2226.3
37.5°	1047.4	1123.4	1221.3	1360.4	1565.7	1811.9	2063.3	2212.5	2206.4	2065.4	1875.8
40°	1008.9	1073.7	1168.0	1314.2	1529.7	1796.6	2035.1	2132.0	2049.9	1852.9	1625.9
42.5°	958.7	1018.2	1112.6	1262.9	1490.3	1765.2	1981.2	2009.3	1848.7	1622.1	1414.0
45°	880.6	933.2	1030.7	1185.9	1431.0	1697.1	1849.7	1781.1	1565.0	1330.9	1172.4
47.5°	796.8	851.5	945.3	1104.8	1345.3	1594.6	1667.4	1521.4	1299.5	1109.6	964.1
50°	744.0	796.6	888.3	1049.3	1287.2	1510.5	1540.6	1352.1	1148.1	981.4	862.0
52.5°	690.7	740.2	830.4	991.8	1219.6	1413.0	1394.4	1202.2	1014.6	872.5	778.9
55°	611.2	658.1	744.0	895.4	1102.6	1255.8	1188.5	1005.0	849.9	739.5	668.4
57.5°	540.2	585.0	659.2	796.0	976.1	1081.4	995.7	841.1	717.7	632.8	579.7
60°	491.9	531.7	602.3	729.2	885.8	965.9	881.3	744.7	640.7	572.8	525.3
62.5°	446.3	480.9	546.3	661.6	797.5	864.9	779.2	663.5	575.0	514.8	474.5
65°	377.1	408.6	466.3	556.1	667.7	712.6	638.9	545.2	476.5	431.7	404.7
67.5°	314.1	340.7	390.6	461.3	543.4	576.1	519.9	447.4	395.8	359.7	338.3
70°	271.9	295.0	334.1	395.1	469.5	494.6	442.0	382.3	344.4	315.6	295.7
72.5°	236.6	253.4	289.0	336.1	398.1	418.0	381.4	328.9	293.6	271.9	256.2
75°	180.2	194.4	217.4	255.2	298.2	309.8	282.2	249.5	225.7	210.4	198.2
77.5°	130.0	140.3	157.0	180.4	210.1	220.6	203.0	181.3	163.9	153.5	146.8
80°	98.1	106.5	120.6	139.8	157.8	163.5	153.3	136.6	124.4	118.7	112.9
82.5°	72.5	77.2	85.7	98.8	111.1	117.9	109.1	99.2	92.7	87.4	85.2
85°	36.6	39.1	43.0	48.1	55.8	58.3	55.1	52.6	48.7	45.5	45.5
87.5°	13.9	14.3	16.3	17.8	20.3	22.3	22.4	22.0	22.0	21.6	21.3
90°	3.0	5.1	7.3	9.3	11.7	14.4	17.2	19.9	22.6	23.4	24.2
92.5°	24.2	25.6	27.1	28.5	30.0	31.5	33.0	34.6	36.1	36.8	37.5
95°	56.9	58.4	59.9	61.4	63.0	64.6	66.3	68.0	69.7	70.5	71.3
97.5°	99.7	100.8	101.9	102.9	104.1	105.3	106.5	107.7	109.0	109.9	110.8
100°	129.2	130.4	131.7	133.0	134.1	135.2	136.2	137.2	138.3	138.9	139.6
102.5°	162.6	163.3	164.1	164.9	165.9	167.3	168.6	170.0	171.4	172.0	172.7
105°	212.1	212.5	212.9	213.4	214.5	216.4	218.3	220.2	222.1	222.1	222.1
107.5°	269.9	270.1	270.4	270.7	271.2	271.9	272.7	273.4	274.2	274.8	275.5
110°	306.2	306.6	307.0	307.5	307.8	308.3	308.7	309.2	309.5	310.4	311.2



TEST NUMBER: P332028-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	343.7	343.9	344.1	344.4	344.6	344.7	344.8	344.9	344.9	345.9	346.9
115°	400.5	401.1	401.7	402.4	402.5	402.1	401.6	401.2	400.8	401.1	401.2
117.5°	457.1	457.5	458.0	458.4	458.3	457.8	457.2	456.7	456.1	456.1	456.0
120°	493.3	494.6	495.9	497.1	497.2	496.2	495.1	494.1	493.0	492.8	492.6
122.5°	529.9	530.7	531.7	532.6	532.8	532.3	531.7	531.2	530.7	530.1	529.5
125°	585.9	586.4	587.1	587.7	587.9	587.4	587.0	586.5	586.2	585.3	584.5
127.5°	638.5	639.8	641.1	642.5	642.9	642.4	642.1	641.6	641.1	639.9	638.8
130°	673.4	675.1	676.7	678.4	679.0	678.3	677.7	677.1	676.5	675.6	674.8
132.5°	708.0	709.7	711.4	713.1	713.7	713.2	712.8	712.3	711.8	710.9	709.8
135°	760.5	761.8	763.0	764.3	764.8	764.6	764.4	764.2	763.9	763.2	762.3
137.5°	809.3	810.3	811.3	812.4	813.1	813.7	814.3	814.8	815.3	814.5	813.6
140°	843.1	844.1	845.2	846.2	846.9	847.1	847.3	847.5	847.7	847.5	847.3
142.5°	873.9	875.1	876.1	877.1	877.8	878.2	878.5	878.9	879.3	879.1	878.9
145°	921.5	921.9	922.4	922.7	923.3	923.9	924.5	925.2	925.8	925.6	925.4
147.5°	964.0	964.8	965.5	966.3	967.0	967.5	968.1	968.7	969.3	969.3	969.3
150°	993.1	993.4	993.8	994.3	994.7	995.1	995.5	996.0	996.4	996.4	996.4
152.5°	1017.3	1017.9	1018.4	1019.0	1019.5	1019.7	1019.9	1020.2	1020.5	1020.8	1021.2
155°	1054.7	1054.7	1054.7	1054.7	1054.8	1055.0	1055.2	1055.5	1055.6	1056.5	1057.3
157.5°	1086.8	1086.6	1086.3	1086.1	1086.0	1086.2	1086.4	1086.6	1086.7	1087.6	1088.4
160°	1106.9	1106.5	1106.2	1105.7	1105.5	1105.5	1105.5	1105.5	1105.5	1106.5	1107.6
162.5°	1124.8	1124.3	1123.7	1123.1	1122.9	1123.0	1123.2	1123.4	1123.6	1124.6	1125.7
165°	1148.1	1147.5	1146.9	1146.3	1145.9	1145.9	1145.9	1145.9	1145.9	1147.2	1148.5
167.5°	1166.6	1165.7	1164.9	1164.0	1163.8	1163.9	1164.0	1164.2	1164.4	1165.7	1167.0
170°	1177.1	1176.3	1175.4	1174.6	1174.2	1174.2	1174.2	1174.2	1174.2	1175.6	1177.1
172.5°	1185.4	1184.6	1183.7	1182.9	1182.4	1182.4	1182.4	1182.4	1182.4	1183.7	1185.1
175°	1194.0	1193.2	1192.4	1191.6	1191.1	1191.1	1191.1	1191.1	1191.1	1192.4	1193.6
177.5°	1197.8	1197.1	1196.5	1195.8	1195.4	1195.4	1195.4	1195.4	1195.4	1196.5	1197.5
180°	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7



TEST NUMBER: P332028-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8
2.5°	1393.1	1393.6	1399.3	1403.4	1401.3	1403.9	1404.9
5°	1522.0	1545.1	1557.3	1566.3	1566.9	1567.5	1572.7
7.5°	1704.8	1729.6	1747.7	1775.1	1783.3	1792.7	1790.0
10°	1838.2	1874.8	1906.2	1922.9	1940.9	1967.2	1946.0
12.5°	1962.9	2027.7	2075.6	2101.5	2118.4	2123.6	2113.3
15°	2168.5	2253.2	2298.8	2297.4	2355.2	2380.2	2341.1
17.5°	2357.1	2435.2	2497.8	2529.9	2578.0	2588.7	2583.8
20°	2472.6	2557.9	2606.6	2661.7	2686.8	2709.2	2713.1
22.5°	2572.1	2648.7	2701.0	2746.9	2767.9	2778.5	2784.9
25°	2674.6	2734.9	2766.4	2782.4	2788.1	2786.8	2778.5
27.5°	2667.6	2672.2	2637.5	2603.6	2573.1	2538.9	2527.1
30°	2598.3	2544.4	2448.2	2393.7	2313.5	2250.0	2275.7
32.5°	2416.1	2308.9	2200.8	2081.7	1983.0	1954.9	1926.7
35°	2062.1	1873.5	1763.2	1634.9	1583.6	1532.3	1497.0
37.5°	1668.3	1522.4	1391.6	1307.7	1256.2	1223.8	1206.4
40°	1442.5	1311.0	1203.2	1135.3	1096.2	1059.6	1054.4
42.5°	1262.3	1140.1	1059.0	1004.9	967.3	951.8	940.6
45°	1034.0	948.6	894.1	855.6	830.6	821.0	808.1
47.5°	875.2	814.8	773.9	747.7	728.9	721.7	720.7
50°	786.4	736.3	706.2	685.6	670.9	668.4	658.1
52.5°	719.6	676.3	652.8	634.9	624.2	617.0	614.0
55°	624.7	595.9	574.7	564.4	556.1	549.0	549.0
57.5°	546.6	522.5	508.5	499.7	497.2	492.2	489.0
60°	498.3	477.9	466.9	459.2	454.1	454.8	448.9
62.5°	451.2	437.8	427.4	419.7	413.6	413.7	414.1
65°	384.2	373.9	366.3	363.6	359.9	355.3	356.7
67.5°	325.6	315.9	309.9	305.6	304.3	301.8	305.6
70°	283.5	276.4	271.9	268.1	266.8	267.5	270.7
72.5°	245.0	240.0	237.0	235.3	232.4	232.5	234.8
75°	192.4	188.6	186.0	184.1	183.4	183.4	183.4
77.5°	141.4	140.4	139.3	136.5	136.6	137.4	137.5
80°	111.6	109.7	109.1	107.7	105.8	104.5	107.7
82.5°	83.4	81.4	80.8	80.6	77.6	77.4	80.0
85°	44.9	43.0	43.6	43.0	43.0	42.3	42.3
87.5°	20.9	20.5	20.2	20.8	20.4	19.9	21.0
90°	25.1	25.9	26.6	27.0	27.4	27.8	28.2
92.5°	38.2	38.8	39.0	38.7	38.5	38.3	38.0
95°	72.1	73.0	73.4	73.4	73.4	73.4	73.4
97.5°	111.9	112.8	113.2	113.2	113.1	113.0	112.9
100°	140.2	140.8	141.4	141.8	142.1	142.6	143.0
102.5°	173.3	173.9	174.2	174.1	174.0	174.0	173.9
105°	222.1	222.1	222.3	222.6	223.1	223.5	223.9
107.5°	276.2	276.8	277.0	276.8	276.5	276.3	276.1
110°	312.1	312.9	313.1	312.6	312.3	311.9	311.4



TEST NUMBER: P332028-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	347.9	348.9	349.4	349.3	349.2	349.1	349.0
115°	401.4	401.6	401.6	401.4	401.2	401.1	400.8
117.5°	456.0	456.0	455.6	455.1	454.5	453.9	453.3
120°	492.4	492.2	491.8	491.4	491.1	490.6	490.2
122.5°	529.0	528.5	527.9	527.4	526.7	526.1	525.6
125°	583.6	582.8	581.9	581.2	580.3	579.5	578.6
127.5°	637.6	636.4	635.4	634.4	633.4	632.4	631.5
130°	673.9	673.2	671.9	670.5	669.0	667.6	666.1
132.5°	708.9	707.8	706.8	705.7	704.6	703.4	702.3
135°	761.5	760.6	760.0	759.6	759.1	758.7	758.4
137.5°	812.8	811.8	811.0	810.2	809.4	808.6	807.9
140°	847.1	846.9	846.0	844.6	843.1	841.7	840.2
142.5°	878.7	878.4	877.8	876.7	875.5	874.4	873.3
145°	925.2	924.9	924.4	923.6	922.7	921.9	921.1
147.5°	969.3	969.3	968.7	967.4	966.1	964.9	963.7
150°	996.4	996.4	995.7	994.5	993.3	991.9	990.7
152.5°	1021.4	1021.8	1021.4	1020.3	1019.3	1018.1	1017.1
155°	1058.2	1058.9	1058.7	1057.2	1055.7	1054.2	1052.8
157.5°	1089.3	1090.2	1090.1	1088.9	1087.7	1086.6	1085.3
160°	1108.6	1109.7	1109.7	1109.0	1108.1	1107.3	1106.5
162.5°	1126.7	1127.8	1127.6	1126.2	1124.9	1123.6	1122.3
165°	1149.7	1150.9	1150.8	1149.4	1147.9	1146.5	1145.0
167.5°	1168.3	1169.6	1169.6	1168.3	1167.0	1165.7	1164.4
170°	1178.6	1180.1	1180.1	1178.6	1177.1	1175.6	1174.2
172.5°	1186.4	1187.6	1187.6	1186.1	1184.7	1183.2	1181.7
175°	1194.9	1196.2	1196.0	1194.6	1193.1	1191.7	1190.1
177.5°	1198.4	1199.5	1199.4	1198.3	1197.0	1195.9	1194.7
180°	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7

(END OF REPORT)