

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332034-830

Luminaire Tested: **S123DIP-S1000D1025U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332034-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D1025U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7204.1 lumens
Efficiency: N/A
Efficacy: 119.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332034-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332034-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	94	90	87	91	87	84	81	75	72	70	63	62	60	53	51	50
2	90	82	76	71	83	76	71	66	66	62	58	56	53	50	46	44	42
3	82	72	65	59	76	67	61	55	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	34	31
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27
6	63	51	43	37	59	48	40	35	41	36	31	36	31	27	30	26	24
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	24	30	25	22	25	22	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16060	16060	16060
5°	16134	15913	16024
10°	16027	15774	15872
15°	15840	15597	15624
20°	15621	15341	15356
25°	15327	15037	15007
30°	15003	14701	14588
35°	14666	14345	14160
40°	14313	13952	13735
45°	13922	13592	13259
50°	13534	13147	12782
55°	13024	12688	12301
60°	12510	12152	11765
65°	12055	11566	11207
70°	11383	10902	10414
75°	10405	10031	9603
80°	9385	8988	8901
85°	8238	7929	7595



TEST NUMBER: P332034-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.5	2.0
10°-20°	396.8	5.5
20°-30°	586.2	8.1
30°-40°	684.7	9.5
40°-50°	688.4	9.6
50°-60°	604.7	8.4
60°-70°	450.5	6.3
70°-80°	256.7	3.6
80°-90°	77.2	1.1
90°-100°	78.0	1.1
100°-110°	233.5	3.2
110°-120°	397.2	5.5
120°-130°	522.5	7.3
130°-140°	587.2	8.2
140°-150°	577.2	8.0
150°-160°	486.0	6.7
160°-170°	323.5	4.5
170°-180°	113.3	1.6
0°-30°	1123.5	15.6
0°-40°	1808.2	25.1
0°-60°	3101.3	43.0
0°-90°	3885.7	53.9
90°-120°	708.8	9.8
90°-150°	2395.7	33.3
90°-180°	3318.0	46.1
0°-180°	7204.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1492	1492	1492	1492	1492	
5°	1493	1486	1473	1485	1483	141
15°	1421	1416	1400	1409	1402	401
25°	1290	1282	1266	1267	1264	594
35°	1116	1108	1092	1084	1078	698
45°	915	909	893	878	871	706
55°	694	692	676	662	656	621
65°	473	467	454	444	440	467
75°	250	245	241	235	231	267
85°	67	64	64	62	62	73
90°	1	10	23	26	28	7
95°	56	62	70	73	73	62
105°	212	214	222	222	224	227
115°	400	402	401	402	401	395
125°	585	588	586	582	579	522
135°	759	765	764	760	758	585
145°	921	923	926	925	921	575
155°	1055	1055	1056	1059	1053	485
165°	1149	1146	1146	1151	1145	324
175°	1195	1191	1191	1196	1190	113
180°	1198	1198	1198	1198	1198	



TEST NUMBER: P332034-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0
2.5°	1497.0	1496.2	1495.2	1494.3	1493.5	1491.7	1489.2	1486.7	1484.2	1481.7	1483.9
5°	1493.2	1491.8	1490.3	1488.9	1487.5	1485.3	1482.1	1478.9	1475.8	1472.7	1475.6
7.5°	1478.6	1477.2	1475.7	1474.3	1472.9	1470.6	1467.4	1464.1	1460.8	1457.5	1460.1
10°	1466.3	1464.9	1463.4	1462.0	1460.6	1458.0	1454.3	1450.6	1446.9	1443.2	1445.8
12.5°	1449.8	1448.7	1447.5	1446.2	1445.1	1442.7	1439.3	1435.8	1432.3	1428.8	1430.7
15°	1421.4	1420.2	1419.1	1418.0	1416.8	1414.4	1410.7	1407.0	1403.3	1399.6	1401.8
17.5°	1388.3	1386.8	1385.3	1383.8	1382.3	1379.8	1376.0	1372.3	1368.7	1364.9	1366.5
20°	1363.7	1362.0	1360.3	1358.5	1356.8	1354.1	1350.4	1346.7	1343.0	1339.3	1340.4
22.5°	1336.0	1334.3	1332.6	1330.8	1329.1	1326.4	1322.7	1319.0	1315.3	1311.5	1312.5
25°	1290.5	1288.8	1287.1	1285.4	1283.6	1281.0	1277.2	1273.6	1269.9	1266.1	1266.4
27.5°	1242.1	1240.4	1238.7	1237.1	1235.4	1232.6	1228.6	1224.6	1220.6	1216.6	1216.8
30°	1207.1	1205.7	1204.3	1202.9	1201.5	1198.7	1194.8	1190.7	1186.8	1182.8	1182.8
32.5°	1172.2	1170.4	1168.5	1166.6	1164.7	1162.2	1159.1	1156.1	1153.0	1149.9	1148.3
35°	1116.1	1114.4	1112.7	1111.0	1109.2	1106.5	1102.8	1099.1	1095.4	1091.7	1090.0
37.5°	1058.6	1056.4	1054.2	1052.1	1049.9	1047.0	1043.2	1039.4	1035.7	1031.9	1029.8
40°	1018.6	1016.8	1015.1	1013.4	1011.7	1008.9	1004.8	1000.9	996.9	992.9	990.6
42.5°	978.5	976.6	974.7	972.7	970.8	967.8	963.8	959.9	955.8	951.9	949.6
45°	914.6	913.5	912.4	911.3	910.1	907.7	904.0	900.2	896.5	892.9	889.5
47.5°	851.3	849.6	848.0	846.3	844.7	842.1	838.7	835.2	831.7	828.2	824.8
50°	808.2	806.7	805.3	803.9	802.5	799.9	796.2	792.5	788.8	785.1	781.9
52.5°	763.0	762.0	761.1	760.2	759.1	756.7	752.8	748.9	744.9	740.9	738.3
55°	694.0	693.7	693.4	693.1	692.9	690.9	687.2	683.4	679.8	676.1	672.9
57.5°	628.3	627.4	626.4	625.5	624.4	622.5	619.5	616.5	613.6	610.7	607.8
60°	581.1	580.8	580.5	580.2	579.9	578.2	574.7	571.3	567.9	564.5	561.8
62.5°	539.0	538.3	537.5	536.8	536.1	534.0	530.6	527.2	523.8	520.3	517.7
65°	473.3	471.9	470.5	469.1	467.7	465.5	462.7	459.9	456.9	454.1	451.9
67.5°	403.9	402.6	401.3	400.1	398.8	397.1	394.9	392.8	390.6	388.4	386.4
70°	361.7	360.1	358.4	356.7	355.0	353.2	351.5	349.8	348.1	346.4	344.4
72.5°	317.6	316.4	315.1	313.9	312.6	311.0	309.1	307.2	305.2	303.2	301.5
75°	250.2	249.0	247.9	246.8	245.6	244.6	243.7	242.9	242.0	241.2	239.8
77.5°	190.4	189.7	189.1	188.5	187.8	187.0	186.1	185.0	184.0	182.9	182.0
80°	151.4	150.5	149.7	148.8	148.0	147.2	146.7	146.1	145.5	145.0	144.7
82.5°	113.4	113.2	113.1	112.9	112.7	112.5	112.4	112.4	112.3	112.2	111.6
85°	66.7	66.2	65.6	65.0	64.5	64.2	64.2	64.2	64.2	64.2	63.5
87.5°	26.9	26.6	26.3	26.1	25.8	25.8	26.1	26.5	26.8	27.1	27.1
90°	0.9	3.0	5.1	7.3	9.3	11.7	14.4	17.2	19.9	22.6	23.4
92.5°	22.8	24.2	25.6	27.1	28.5	30.0	31.5	33.0	34.6	36.1	36.8
95°	55.5	56.9	58.4	59.9	61.4	63.0	64.6	66.3	68.0	69.7	70.5
97.5°	98.6	99.7	100.8	101.9	102.9	104.1	105.3	106.5	107.7	109.0	109.9
100°	128.0	129.2	130.4	131.7	133.0	134.1	135.2	136.2	137.2	138.3	138.9
102.5°	161.8	162.6	163.3	164.1	164.9	165.9	167.3	168.6	170.0	171.4	172.0
105°	211.7	212.1	212.5	212.9	213.4	214.5	216.4	218.3	220.2	222.1	222.1
107.5°	269.7	269.9	270.1	270.4	270.7	271.2	271.9	272.7	273.4	274.2	274.8
110°	305.8	306.2	306.6	307.0	307.5	307.8	308.3	308.7	309.2	309.5	310.4



TEST NUMBER: P332034-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	343.4	343.7	343.9	344.1	344.4	344.6	344.7	344.8	344.9	344.9	345.9
115°	399.8	400.5	401.1	401.7	402.4	402.5	402.1	401.6	401.2	400.8	401.1
117.5°	456.7	457.1	457.5	458.0	458.4	458.3	457.8	457.2	456.7	456.1	456.1
120°	492.1	493.3	494.6	495.9	497.1	497.2	496.2	495.1	494.1	493.0	492.8
122.5°	529.0	529.9	530.7	531.7	532.6	532.8	532.3	531.7	531.2	530.7	530.1
125°	585.2	585.9	586.4	587.1	587.7	587.9	587.4	587.0	586.5	586.2	585.3
127.5°	637.2	638.5	639.8	641.1	642.5	642.9	642.4	642.1	641.6	641.1	639.9
130°	671.8	673.4	675.1	676.7	678.4	679.0	678.3	677.7	677.1	676.5	675.6
132.5°	706.4	708.0	709.7	711.4	713.1	713.7	713.2	712.8	712.3	711.8	710.9
135°	759.3	760.5	761.8	763.0	764.3	764.8	764.6	764.4	764.2	763.9	763.2
137.5°	808.2	809.3	810.3	811.3	812.4	813.1	813.7	814.3	814.8	815.3	814.5
140°	842.1	843.1	844.1	845.2	846.2	846.9	847.1	847.3	847.5	847.7	847.5
142.5°	872.9	873.9	875.1	876.1	877.1	877.8	878.2	878.5	878.9	879.3	879.1
145°	921.1	921.5	921.9	922.4	922.7	923.3	923.9	924.5	925.2	925.8	925.6
147.5°	963.3	964.0	964.8	965.5	966.3	967.0	967.5	968.1	968.7	969.3	969.3
150°	992.6	993.1	993.4	993.8	994.3	994.7	995.1	995.5	996.0	996.4	996.4
152.5°	1016.7	1017.3	1017.9	1018.4	1019.0	1019.5	1019.7	1019.9	1020.2	1020.5	1020.8
155°	1054.7	1054.7	1054.7	1054.7	1054.7	1054.8	1055.0	1055.2	1055.5	1055.6	1056.5
157.5°	1087.0	1086.8	1086.6	1086.3	1086.1	1086.0	1086.2	1086.4	1086.6	1086.7	1087.6
160°	1107.4	1106.9	1106.5	1106.2	1105.7	1105.5	1105.5	1105.5	1105.5	1105.5	1106.5
162.5°	1125.5	1124.8	1124.3	1123.7	1123.1	1122.9	1123.0	1123.2	1123.4	1123.6	1124.6
165°	1148.8	1148.1	1147.5	1146.9	1146.3	1145.9	1145.9	1145.9	1145.9	1145.9	1147.2
167.5°	1167.4	1166.6	1165.7	1164.9	1164.0	1163.8	1163.9	1164.0	1164.2	1164.4	1165.7
170°	1178.0	1177.1	1176.3	1175.4	1174.6	1174.2	1174.2	1174.2	1174.2	1174.2	1175.6
172.5°	1186.2	1185.4	1184.6	1183.7	1182.9	1182.4	1182.4	1182.4	1182.4	1182.4	1183.7
175°	1194.9	1194.0	1193.2	1192.4	1191.6	1191.1	1191.1	1191.1	1191.1	1191.1	1192.4
177.5°	1198.4	1197.8	1197.1	1196.5	1195.8	1195.4	1195.4	1195.4	1195.4	1195.4	1196.5
180°	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7



TEST NUMBER: P332034-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0
2.5°	1486.2	1488.6	1490.8	1491.9	1491.6	1491.4	1491.1	1490.9
5°	1478.4	1481.2	1484.1	1485.3	1484.7	1484.1	1483.6	1483.0
7.5°	1462.7	1465.3	1467.8	1469.0	1468.6	1468.3	1467.9	1467.5
10°	1448.3	1450.9	1453.5	1454.4	1453.9	1453.3	1452.7	1452.2
12.5°	1432.6	1434.5	1436.3	1437.1	1436.8	1436.4	1436.1	1435.8
15°	1404.1	1406.4	1408.7	1409.0	1407.3	1405.5	1403.8	1402.1
17.5°	1368.1	1369.7	1371.3	1371.8	1371.2	1370.6	1369.9	1369.3
20°	1341.5	1342.7	1343.9	1344.0	1343.1	1342.3	1341.4	1340.6
22.5°	1313.4	1314.3	1315.2	1315.1	1314.1	1313.0	1311.9	1310.8
25°	1266.7	1267.1	1267.3	1267.1	1266.1	1265.3	1264.4	1263.6
27.5°	1217.1	1217.3	1217.6	1217.1	1216.1	1214.9	1213.9	1212.8
30°	1182.8	1182.8	1182.8	1181.8	1179.8	1177.8	1175.8	1173.7
32.5°	1146.7	1145.2	1143.6	1142.2	1141.1	1140.0	1139.0	1137.8
35°	1088.3	1086.6	1084.9	1083.3	1081.9	1080.4	1079.0	1077.6
37.5°	1027.8	1025.8	1023.7	1022.2	1021.3	1020.4	1019.5	1018.6
40°	988.4	986.1	983.8	982.0	980.9	979.8	978.6	977.5
42.5°	947.3	945.0	942.7	941.0	939.9	938.8	937.6	936.5
45°	886.0	882.6	879.2	876.8	875.3	873.9	872.5	871.0
47.5°	821.4	818.1	814.7	812.5	811.2	809.9	808.7	807.4
50°	778.8	775.7	772.5	770.2	768.5	766.7	765.0	763.3
52.5°	735.6	732.9	730.3	728.0	726.3	724.6	722.9	721.2
55°	669.8	666.7	663.5	661.2	659.8	658.4	657.0	655.5
57.5°	605.0	602.3	599.5	597.2	595.6	593.9	592.3	590.6
60°	559.3	556.8	554.2	552.2	550.7	549.3	547.9	546.5
62.5°	515.2	512.6	510.0	508.3	507.3	506.3	505.4	504.4
65°	449.6	447.2	445.0	443.5	442.6	441.8	440.8	440.0
67.5°	384.5	382.5	380.5	378.9	377.7	376.5	375.2	374.1
70°	342.3	340.4	338.4	336.7	335.3	333.8	332.4	330.9
72.5°	299.7	297.9	296.1	294.9	294.2	293.4	292.8	292.0
75°	238.4	236.9	235.4	234.3	233.5	232.6	231.8	230.9
77.5°	181.0	180.0	179.1	178.6	178.6	178.6	178.6	178.6
80°	144.4	144.1	143.8	143.6	143.6	143.6	143.6	143.6
82.5°	111.1	110.6	110.1	109.7	109.4	109.2	109.1	108.8
85°	63.0	62.4	61.8	61.5	61.5	61.5	61.5	61.5
87.5°	27.0	27.0	26.9	26.9	27.0	27.1	27.1	27.2
90°	24.2	25.1	25.9	26.6	27.0	27.4	27.8	28.2
92.5°	37.5	38.2	38.8	39.0	38.7	38.5	38.3	38.0
95°	71.3	72.1	73.0	73.4	73.4	73.4	73.4	73.4
97.5°	110.8	111.9	112.8	113.2	113.2	113.1	113.0	112.9
100°	139.6	140.2	140.8	141.4	141.8	142.1	142.6	143.0
102.5°	172.7	173.3	173.9	174.2	174.1	174.0	174.0	173.9
105°	222.1	222.1	222.1	222.3	222.6	223.1	223.5	223.9
107.5°	275.5	276.2	276.8	277.0	276.8	276.5	276.3	276.1
110°	311.2	312.1	312.9	313.1	312.6	312.3	311.9	311.4



TEST NUMBER: P332034-830

CATALOG NUMBER: S123DIP-S1000D1025U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	346.9	347.9	348.9	349.4	349.3	349.2	349.1	349.0
115°	401.2	401.4	401.6	401.6	401.4	401.2	401.1	400.8
117.5°	456.0	456.0	456.0	455.6	455.1	454.5	453.9	453.3
120°	492.6	492.4	492.2	491.8	491.4	491.1	490.6	490.2
122.5°	529.5	529.0	528.5	527.9	527.4	526.7	526.1	525.6
125°	584.5	583.6	582.8	581.9	581.2	580.3	579.5	578.6
127.5°	638.8	637.6	636.4	635.4	634.4	633.4	632.4	631.5
130°	674.8	673.9	673.2	671.9	670.5	669.0	667.6	666.1
132.5°	709.8	708.9	707.8	706.8	705.7	704.6	703.4	702.3
135°	762.3	761.5	760.6	760.0	759.6	759.1	758.7	758.4
137.5°	813.6	812.8	811.8	811.0	810.2	809.4	808.6	807.9
140°	847.3	847.1	846.9	846.0	844.6	843.1	841.7	840.2
142.5°	878.9	878.7	878.4	877.8	876.7	875.5	874.4	873.3
145°	925.4	925.2	924.9	924.4	923.6	922.7	921.9	921.1
147.5°	969.3	969.3	969.3	968.7	967.4	966.1	964.9	963.7
150°	996.4	996.4	996.4	995.7	994.5	993.3	991.9	990.7
152.5°	1021.2	1021.4	1021.8	1021.4	1020.3	1019.3	1018.1	1017.1
155°	1057.3	1058.2	1058.9	1058.7	1057.2	1055.7	1054.2	1052.8
157.5°	1088.4	1089.3	1090.2	1090.1	1088.9	1087.7	1086.6	1085.3
160°	1107.6	1108.6	1109.7	1109.7	1109.0	1108.1	1107.3	1106.5
162.5°	1125.7	1126.7	1127.8	1127.6	1126.2	1124.9	1123.6	1122.3
165°	1148.5	1149.7	1150.9	1150.8	1149.4	1147.9	1146.5	1145.0
167.5°	1167.0	1168.3	1169.6	1169.6	1168.3	1167.0	1165.7	1164.4
170°	1177.1	1178.6	1180.1	1180.1	1178.6	1177.1	1175.6	1174.2
172.5°	1185.1	1186.4	1187.6	1187.6	1186.1	1184.7	1183.2	1181.7
175°	1193.6	1194.9	1196.2	1196.0	1194.6	1193.1	1191.7	1190.1
177.5°	1197.5	1198.4	1199.5	1199.4	1198.3	1197.0	1195.9	1194.7
180°	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7

(END OF REPORT)