

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831482

Luminaire Tested: S123DIP-S560D1195U835-4F0-1E-UDD-G4

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831482
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-17)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D1195U835-4F0-1E-UDD-G4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6915.2 lumens
Efficiency: N/A
Efficacy: 136.7 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 50.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831482

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-G4

Luminous Intensity Polar Plot





TEST NUMBER: P831482

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-G4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	76	76	76	60	60	60	45	45	45	38				
1	95	91	88	84	86	83	80	77	67	65	63	53	52	51	40	39	38	32				
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	34	33	28				
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29	24				
4	73	63	55	50	66	58	51	46	47	43	39	38	35	32	29	27	25	21				
5	67	56	49	43	61	52	45	40	43	38	34	34	31	28	26	24	22	19				
6	62	51	43	37	56	46	40	35	39	34	30	31	28	25	24	22	20	17				
7	58	46	38	33	52	42	36	31	35	30	26	28	25	22	22	20	18	15				
8	54	42	34	29	49	38	32	27	32	27	24	26	23	20	21	18	16	14				
9	50	38	31	26	45	35	29	25	30	25	21	24	21	18	19	17	15	13				
10	47	35	28	24	43	32	26	22	27	23	19	22	19	16	18	15	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	17374	17374	17374	17374	17374
5°	21973	20738	17530	14126	12981
10°	22186	22857	17413	11261	9840
15°	16710	21222	17295	9536	8322
20°	11643	17172	17073	8339	7559
25°	8878	13206	16697	7672	7090
30°	7680	10491	16096	7201	6712
35°	7126	8858	15403	6861	6447
40°	6746	7946	14429	6535	6357
45°	6521	7354	13192	6282	6317
50°	6409	6886	11727	6052	6285
55°	6170	6544	10290	5833	6311
60°	5950	6176	8869	5627	6209
65°	5591	5827	7651	5407	6085
70°	5161	5385	6505	5045	5728
75°	4675	4828	5577	4687	5232
80°	3856	4228	4413	4085	4413
85°	3051	3421	3236	3470	3520

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 15061 cd/sqm



TEST NUMBER: P831482

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-G4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.6	2.2
10°-20°	379.6	5.5
20°-30°	449.5	6.5
30°-40°	452.0	6.5
40°-50°	414.7	6.0
50°-60°	342.3	4.9
60°-70°	242.1	3.5
70°-80°	129.2	1.9
80°-90°	36.0	0.5
90°-100°	311.5	4.5
100°-110°	911.8	13.2
110°-120°	890.4	12.9
120°-130°	709.1	10.3
130°-140°	559.5	8.1
140°-150°	417.4	6.0
150°-160°	291.0	4.2
160°-170°	171.0	2.5
170°-180°	55.6	0.8
0°-30°	981.7	14.2
0°-40°	1433.7	20.7
0°-60°	2190.6	31.7
0°-90°	2597.9	37.6
90°-120°	2113.7	30.6
90°-150°	3799.8	54.9
90°-180°	4317.0	62.4
0°-180°	6915.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1614	1614	1614	1614	1614	
5°	2034	1919	1622	1307	1201	194
15°	1500	1904	1552	856	747	414
25°	748	1112	1406	646	597	353
35°	542	674	1172	522	491	341
45°	428	483	867	413	415	332
55°	329	349	548	311	336	294
65°	220	229	300	212	239	218
75°	112	116	134	113	126	118
85°	25	28	26	28	28	28
90°	34	29	2	29	34	19
95°	135	689	40	689	135	219
105°	1478	934	135	934	1478	1474
115°	1797	714	238	714	1797	1753
125°	1418	667	331	667	1418	1283
135°	1149	658	388	658	1149	891
145°	898	650	443	650	898	570
155°	745	629	503	629	745	347
165°	650	602	550	602	650	185
175°	584	577	573	577	584	57
180°	574	574	574	574	574	



TEST NUMBER: P831482

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1
2.5°	1819.3	1817.5	1815.6	1806.2	1796.9	1792.4	1787.9	1774.4	1760.9	1745.9	1731.0
5°	2033.6	2038.8	2044.1	2038.1	2032.1	2013.7	1995.4	1971.0	1946.7	1919.3	1892.0
7.5°	2132.4	2135.4	2138.4	2134.7	2130.9	2126.1	2121.2	2099.5	2077.8	2049.7	2021.6
10°	2029.8	2036.6	2043.3	2057.9	2072.5	2089.0	2105.5	2102.5	2099.5	2091.2	2083.0
12.5°	1804.4	1812.6	1820.8	1850.1	1879.3	1916.7	1954.2	1986.4	2018.6	2041.1	2063.5
15°	1499.5	1522.4	1545.2	1571.8	1598.4	1653.4	1708.5	1776.3	1844.1	1904.4	1964.7
17.5°	1235.1	1243.7	1252.3	1280.8	1309.3	1378.6	1447.8	1526.1	1604.4	1704.4	1804.4
20°	1016.4	1024.3	1032.1	1069.6	1107.0	1161.3	1215.6	1303.7	1391.7	1499.1	1606.6
22.5°	853.9	866.2	878.6	899.6	920.5	972.6	1024.6	1102.9	1181.2	1299.9	1418.6
25°	747.5	756.5	765.5	778.2	791.0	832.5	874.1	938.5	1002.9	1111.9	1220.9
27.5°	674.9	678.6	682.3	695.1	707.8	734.8	761.7	817.2	872.6	965.1	1057.6
30°	617.9	620.6	623.2	634.4	645.6	664.0	682.3	722.4	762.5	844.1	925.8
32.5°	578.2	580.1	582.0	590.6	599.2	612.3	625.4	654.6	683.8	751.3	818.7
35°	542.3	543.4	544.5	550.9	557.3	567.0	576.7	598.8	620.9	674.1	727.3
37.5°	510.8	512.3	513.8	517.6	521.3	529.9	538.5	556.1	573.7	614.6	655.4
40°	480.1	482.7	485.4	488.0	490.6	497.7	504.8	518.3	531.8	565.5	599.2
42.5°	453.9	456.5	459.1	460.3	461.4	465.5	469.6	482.0	494.3	519.4	544.5
45°	428.4	429.6	430.7	431.8	432.9	436.3	439.7	450.5	461.4	483.1	504.8
47.5°	405.2	405.2	405.2	406.0	406.7	409.7	412.7	420.6	428.4	445.3	462.1
50°	382.7	382.7	382.7	381.6	380.5	382.4	384.2	390.2	396.2	411.2	426.2
52.5°	355.8	355.8	355.8	356.2	356.5	356.5	356.5	361.8	367.0	380.5	394.0
55°	328.8	330.3	331.8	330.7	329.6	330.3	331.1	334.4	337.8	348.7	359.5
57.5°	301.9	302.6	303.3	303.0	302.6	303.0	303.3	306.3	309.3	317.6	325.8
60°	276.4	276.4	276.4	275.6	274.9	275.6	276.4	277.9	279.4	286.9	294.4
62.5°	247.9	248.3	248.7	249.0	249.4	248.7	247.9	249.8	251.7	257.3	262.9
65°	219.5	219.8	220.2	221.3	222.5	221.7	221.0	222.8	224.7	228.8	232.9
67.5°	194.0	193.2	192.5	192.9	193.2	194.4	195.5	195.9	196.2	200.7	205.2
70°	164.0	164.8	165.5	165.2	164.8	165.2	165.5	166.7	167.8	171.1	174.5
72.5°	137.1	137.4	137.8	137.8	137.8	138.6	139.3	140.4	141.6	143.4	145.3
75°	112.4	112.4	112.4	113.1	113.8	114.2	114.6	114.6	114.6	116.1	117.6
77.5°	85.4	87.3	89.1	88.8	88.4	89.1	89.9	91.0	92.1	92.9	93.6
80°	62.2	62.2	62.2	62.5	62.9	64.0	65.2	65.9	66.7	68.2	69.7
82.5°	39.7	40.1	40.4	41.6	42.7	43.4	44.2	45.3	46.4	46.4	46.4
85°	24.7	24.0	23.2	24.0	24.7	25.5	26.2	26.6	27.0	27.7	28.5
87.5°	12.0	12.0	12.0	12.0	12.0	12.4	12.7	12.7	12.7	12.7	12.7
90°	33.7	34.9	33.7	32.5	33.7	31.4	30.2	29.0	27.9	29.0	25.6
92.5°	61.6	63.9	62.7	67.4	69.7	77.8	89.5	115.0	161.5	216.1	239.3
95°	134.8	139.4	147.6	158.0	180.1	221.9	283.5	418.3	558.8	689.0	613.5
97.5°	276.5	289.3	317.2	361.3	439.2	571.6	725.0	960.8	1095.6	1059.6	791.2
100°	728.5	727.3	772.6	857.4	974.8	1139.8	1275.7	1369.8	1329.2	1100.3	743.6
102.5°	1153.7	1187.4	1223.4	1286.2	1371.0	1460.4	1525.5	1505.8	1340.8	1024.7	673.9
105°	1477.9	1483.7	1520.9	1565.0	1618.5	1648.7	1626.6	1510.4	1267.6	934.1	619.3
107.5°	1689.3	1702.1	1717.2	1738.1	1745.1	1713.7	1623.1	1440.7	1163.0	854.0	579.8
110°	1810.2	1812.5	1814.8	1805.5	1773.0	1691.7	1545.3	1331.5	1065.4	787.7	558.8



TEST NUMBER: P831482

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1834.6	1833.4	1821.8	1788.1	1721.9	1611.5	1443.0	1223.4	980.6	743.6	547.2
115°	1797.4	1791.6	1768.3	1717.2	1630.1	1503.4	1332.6	1130.5	915.5	714.5	546.1
117.5°	1716.0	1707.9	1673.1	1616.1	1525.5	1394.2	1237.4	1058.4	872.5	694.8	547.2
120°	1609.2	1602.2	1574.3	1509.2	1417.5	1300.1	1160.7	1003.8	840.0	682.0	551.9
122.5°	1509.2	1499.9	1468.6	1411.6	1332.6	1225.7	1099.1	960.8	813.3	673.9	560.0
125°	1417.5	1409.3	1380.3	1329.2	1254.8	1161.8	1050.3	923.7	791.2	666.9	568.1
127.5°	1338.4	1331.5	1304.8	1260.6	1193.2	1107.2	1005.0	890.0	770.3	663.4	577.4
130°	1273.4	1264.1	1239.7	1197.9	1136.3	1057.3	963.2	858.6	754.0	659.9	586.7
132.5°	1209.5	1203.7	1182.8	1140.9	1084.0	1009.6	923.7	829.6	738.9	658.8	593.7
135°	1149.1	1140.9	1120.0	1085.2	1028.2	962.0	886.5	804.0	726.2	657.6	600.7
137.5°	1085.2	1078.2	1060.8	1024.7	976.0	916.7	849.3	779.6	714.5	655.3	605.3
140°	1017.8	1018.9	1000.4	967.8	923.7	873.7	817.9	758.7	704.1	654.1	610.0
142.5°	955.0	956.2	939.9	912.1	876.0	834.2	787.7	738.9	694.8	651.8	613.5
145°	898.1	895.8	886.5	862.1	833.0	799.4	762.2	723.8	686.7	649.5	614.6
147.5°	849.3	848.1	838.9	821.4	798.2	773.8	742.4	711.1	678.5	646.0	614.6
150°	807.5	807.5	800.5	787.7	770.3	748.2	723.8	697.1	670.4	641.3	614.6
152.5°	772.6	772.6	769.1	757.5	744.7	727.3	706.4	684.3	661.1	635.5	611.1
155°	744.7	743.6	741.3	732.0	721.5	707.6	690.1	671.5	651.8	628.6	608.8
157.5°	718.0	718.0	715.7	708.7	699.4	687.8	673.9	657.6	641.3	622.8	605.3
160°	692.5	693.6	693.6	686.7	678.5	670.4	658.8	646.0	630.9	615.8	603.0
162.5°	669.2	670.4	670.4	664.6	659.9	653.0	642.5	632.0	620.4	608.8	598.4
165°	649.5	649.5	650.6	646.0	641.3	635.5	627.4	620.4	611.1	601.8	593.7
167.5°	629.7	629.7	630.9	627.4	625.1	620.4	615.8	610.0	601.8	594.9	589.1
170°	612.3	612.3	613.5	611.1	610.0	607.6	603.0	599.5	593.7	587.9	584.4
172.5°	596.0	597.2	599.5	597.2	597.2	596.0	592.5	590.2	585.6	582.1	580.9
175°	584.4	585.6	586.7	585.6	585.6	585.6	583.2	582.1	579.8	577.4	577.4
177.5°	576.3	576.3	578.6	577.4	578.6	578.6	577.4	576.3	575.1	574.0	575.1
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0



TEST NUMBER: P831482

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1
2.5°	1726.5	1722.0	1705.5	1689.0	1670.3	1651.6	1637.7	1623.9	1603.3	1582.7	1565.8
5°	1871.0	1850.1	1815.2	1780.4	1733.2	1686.0	1654.2	1622.4	1579.7	1537.0	1502.9
7.5°	1985.6	1949.7	1901.0	1852.3	1790.5	1728.7	1670.3	1611.9	1546.7	1481.5	1428.4
10°	2058.7	2034.3	1978.1	1922.0	1839.2	1756.4	1674.8	1593.1	1509.3	1425.4	1355.0
12.5°	2065.8	2068.0	2016.3	1964.7	1871.0	1777.4	1678.2	1578.9	1473.3	1367.7	1285.7
15°	2003.2	2041.8	2013.3	1984.9	1890.5	1796.1	1674.0	1552.0	1430.2	1308.5	1213.8
17.5°	1887.1	1969.9	1974.0	1978.1	1883.8	1789.4	1654.2	1519.0	1381.2	1243.4	1143.7
20°	1728.7	1850.8	1892.8	1934.7	1857.9	1781.2	1635.8	1490.5	1336.2	1181.9	1077.5
22.5°	1566.9	1715.2	1792.0	1868.8	1811.9	1754.9	1600.3	1445.6	1282.7	1119.8	1013.8
25°	1382.7	1544.5	1662.4	1780.4	1745.6	1710.7	1558.3	1405.9	1232.5	1059.1	950.9
27.5°	1222.0	1386.4	1528.7	1671.0	1663.6	1656.1	1504.8	1353.5	1175.9	998.4	893.9
30°	1079.0	1232.1	1391.3	1550.5	1568.8	1587.2	1441.1	1295.0	1117.2	939.3	838.5
32.5°	952.4	1086.1	1256.8	1427.6	1463.6	1499.5	1367.7	1235.9	1059.9	883.8	786.8
35°	848.6	970.0	1140.7	1311.5	1356.5	1401.4	1286.8	1172.2	1000.7	829.2	736.7
37.5°	756.9	858.4	1025.0	1191.7	1246.7	1301.8	1199.2	1096.6	935.9	775.2	690.2
40°	680.9	762.5	915.7	1068.8	1132.5	1196.2	1111.5	1026.9	874.5	722.0	643.8
42.5°	617.2	689.8	828.8	967.7	1028.8	1089.8	1018.3	946.8	811.2	675.6	604.1
45°	562.9	620.9	747.1	873.3	931.4	989.4	928.0	866.6	747.1	627.7	561.0
47.5°	511.9	561.8	669.6	777.5	829.2	880.8	832.9	785.0	683.8	582.7	522.4
50°	466.3	506.3	600.7	695.1	740.0	785.0	742.6	700.3	617.2	534.0	481.6
52.5°	426.6	459.1	538.2	617.2	655.8	694.3	658.0	621.7	555.8	489.9	444.2
55°	387.2	415.0	483.5	552.0	578.2	604.5	576.4	548.3	495.1	441.9	403.3
57.5°	350.5	375.3	431.4	487.6	507.8	528.1	502.6	477.1	437.0	397.0	364.8
60°	314.6	334.8	381.6	428.4	440.8	453.2	432.6	412.0	383.9	355.8	326.9
62.5°	281.3	299.6	334.4	369.3	377.5	385.7	370.0	354.3	332.9	311.6	289.1
65°	246.8	260.7	289.1	317.6	322.8	328.1	314.2	300.4	284.2	268.1	251.7
67.5°	215.0	224.7	247.9	271.1	271.5	271.9	260.7	249.4	240.4	231.4	218.3
70°	183.9	193.2	208.6	224.0	224.3	224.7	215.7	206.7	200.0	193.2	183.5
72.5°	152.0	158.8	170.4	182.0	181.3	180.5	174.9	169.3	164.0	158.8	151.7
75°	123.2	128.8	136.7	144.6	142.3	140.1	137.1	134.1	129.6	125.1	120.6
77.5°	97.0	100.4	104.9	109.4	107.9	106.4	103.7	101.1	97.7	94.4	92.5
80°	71.2	72.7	75.7	78.6	77.9	77.1	74.2	71.2	70.4	69.7	67.0
82.5°	48.3	50.2	50.9	51.7	51.3	50.9	48.7	46.4	45.7	44.9	44.6
85°	28.8	29.2	29.6	30.0	28.8	27.7	27.0	26.2	26.2	26.2	25.8
87.5°	13.1	13.5	13.5	13.5	13.1	12.7	12.0	11.2	11.6	12.0	12.0
90°	22.1	18.6	15.1	12.8	10.5	7.0	4.6	2.3	4.6	7.0	10.5
92.5°	178.9	117.3	80.2	59.3	47.6	37.2	25.6	17.4	25.6	37.2	47.6
95°	422.9	249.8	151.0	105.7	75.5	55.8	43.0	39.5	43.0	55.8	75.5
97.5°	470.5	269.5	172.0	122.0	91.8	74.4	63.9	62.7	63.9	74.4	91.8
100°	438.0	266.1	184.7	139.4	111.5	95.3	87.1	86.0	87.1	95.3	111.5
102.5°	410.1	270.7	199.8	159.2	134.8	119.7	112.7	110.4	112.7	119.7	134.8
105°	399.7	280.0	217.3	181.2	159.2	145.2	138.3	134.8	138.3	145.2	159.2
107.5°	397.4	295.1	239.3	205.6	184.7	170.8	163.8	160.3	163.8	170.8	184.7
110°	403.2	314.9	262.6	230.0	210.3	197.5	191.7	188.2	191.7	197.5	210.3



TEST NUMBER: P831482

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	414.8	334.6	287.0	255.6	235.9	223.1	217.3	213.8	217.3	223.1	235.9
115°	427.6	356.7	312.5	281.2	261.4	249.8	242.8	238.2	242.8	249.8	261.4
117.5°	443.8	379.9	335.8	306.7	284.7	274.2	268.4	262.6	268.4	274.2	284.7
120°	462.4	402.0	360.2	331.1	309.1	297.4	291.6	288.1	291.6	297.4	309.1
122.5°	479.8	425.2	384.6	353.2	332.3	319.5	313.7	310.2	313.7	319.5	332.3
125°	498.4	447.3	406.6	375.3	353.2	340.4	333.5	331.1	333.5	340.4	353.2
127.5°	513.5	467.1	427.6	396.2	371.8	359.0	350.9	347.4	350.9	359.0	371.8
130°	528.6	484.5	446.1	414.8	390.4	376.4	366.0	362.5	366.0	376.4	390.4
132.5°	542.6	499.6	462.4	432.2	407.8	390.4	378.8	374.1	378.8	390.4	407.8
135°	554.2	514.7	478.7	447.3	422.9	405.5	392.7	388.1	392.7	405.5	422.9
137.5°	563.5	525.2	490.3	461.3	436.9	418.3	405.5	400.8	405.5	418.3	436.9
140°	570.5	535.6	501.9	472.9	449.6	431.0	419.4	413.6	419.4	431.0	449.6
142.5°	577.4	543.7	511.2	484.5	461.3	445.0	432.2	427.6	432.2	445.0	461.3
145°	582.1	550.7	520.5	493.8	474.0	456.6	446.1	442.7	446.1	456.6	474.0
147.5°	585.6	556.5	528.6	505.4	485.7	470.5	460.1	457.8	460.1	470.5	485.7
150°	586.7	562.3	535.6	514.7	498.4	483.3	474.0	472.9	474.0	483.3	498.4
152.5°	589.1	565.8	543.7	524.0	510.1	497.3	488.0	488.0	488.0	497.3	510.1
155°	589.1	570.5	550.7	534.4	521.7	510.1	503.1	503.1	503.1	510.1	521.7
157.5°	590.2	572.8	556.5	543.7	532.1	521.7	515.9	514.7	515.9	521.7	532.1
160°	590.2	576.3	562.3	550.7	542.6	533.3	528.6	528.6	528.6	533.3	542.6
162.5°	589.1	577.4	565.8	556.5	549.6	542.6	539.1	539.1	539.1	542.6	549.6
165°	586.7	578.6	569.3	561.2	556.5	550.7	548.4	549.6	548.4	550.7	556.5
167.5°	585.6	578.6	571.6	565.8	562.3	557.7	556.5	557.7	556.5	557.7	562.3
170°	582.1	577.4	571.6	569.3	567.0	563.5	562.3	564.7	562.3	563.5	567.0
172.5°	580.9	577.4	572.8	571.6	570.5	568.1	568.1	569.3	568.1	568.1	570.5
175°	578.6	576.3	574.0	572.8	572.8	570.5	571.6	572.8	571.6	570.5	572.8
177.5°	577.4	575.1	574.0	574.0	574.0	572.8	574.0	575.1	574.0	572.8	574.0
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0



TEST NUMBER: P831482

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1
2.5°	1549.0	1534.4	1519.7	1508.5	1497.3	1478.2	1459.1	1454.6	1450.1	1443.7	1437.4
5°	1468.8	1432.9	1396.9	1364.7	1332.5	1307.4	1282.3	1265.8	1249.4	1237.4	1225.4
7.5°	1375.2	1321.3	1267.3	1229.1	1190.9	1154.6	1118.3	1106.7	1095.1	1079.3	1063.6
10°	1284.6	1225.0	1165.5	1115.7	1065.8	1030.3	994.7	980.5	966.2	946.4	926.5
12.5°	1203.7	1138.5	1073.3	1023.2	973.0	938.5	904.1	883.5	862.9	851.6	840.4
15°	1119.0	1049.4	979.7	933.3	886.8	855.7	824.7	806.7	788.7	777.8	767.0
17.5°	1044.1	975.2	906.3	861.7	817.2	788.7	760.2	744.5	728.8	720.5	712.3
20°	973.0	905.6	838.1	794.7	751.3	728.0	704.8	694.7	684.6	677.9	671.1
22.5°	907.8	841.5	775.2	738.2	701.1	682.3	663.6	656.5	649.4	643.8	638.2
25°	842.6	783.5	724.3	692.8	661.4	646.0	630.7	623.6	616.4	610.8	605.2
27.5°	789.5	732.9	676.4	649.4	622.4	610.4	598.5	592.8	587.2	582.0	576.7
30°	737.8	687.2	636.7	613.4	590.2	579.4	568.5	562.9	557.3	552.4	547.5
32.5°	689.8	646.4	603.0	581.6	560.3	551.3	542.3	535.5	528.8	525.1	521.3
35°	644.2	605.2	566.3	548.7	531.0	522.1	513.1	507.5	501.8	498.8	495.8
37.5°	605.2	570.4	535.5	518.7	501.8	493.2	484.6	479.7	474.9	473.7	472.6
40°	565.5	535.5	505.6	489.1	472.6	465.1	457.6	454.7	451.7	450.9	450.2
42.5°	532.5	503.3	474.1	459.1	444.2	437.8	431.4	429.9	428.4	429.6	430.7
45°	494.3	470.0	445.7	431.8	417.9	412.7	407.5	406.3	405.2	407.5	409.7
47.5°	462.1	439.7	417.2	404.1	391.0	387.2	383.5	383.1	382.7	385.7	388.7
50°	429.2	407.5	385.7	375.3	364.8	361.4	358.0	359.2	360.3	365.1	370.0
52.5°	398.5	378.3	358.0	348.3	338.6	336.3	334.1	336.7	339.3	344.5	349.8
55°	364.8	346.4	328.1	320.6	313.1	310.8	308.6	313.8	319.1	323.9	328.8
57.5°	332.6	316.5	300.4	293.6	286.9	286.5	286.1	291.0	295.9	301.1	306.3
60°	298.1	284.6	271.1	265.9	260.7	261.4	262.2	267.8	273.4	277.5	281.6
62.5°	266.6	255.4	244.2	239.3	234.4	236.3	238.2	243.8	249.4	254.3	259.2
65°	235.2	225.8	216.5	213.1	209.7	212.3	215.0	219.8	224.7	228.1	231.4
67.5°	205.2	197.4	189.5	186.9	184.3	186.9	189.5	194.4	199.2	202.6	206.0
70°	173.8	167.4	161.0	159.2	157.3	160.3	163.3	167.4	171.5	174.9	178.3
72.5°	144.6	139.7	134.8	134.4	134.1	136.7	139.3	143.4	147.6	149.8	152.0
75°	116.1	113.5	110.9	110.5	110.1	112.7	115.3	117.6	119.8	121.7	123.6
77.5°	90.6	88.4	86.1	86.5	86.9	88.8	90.6	92.9	95.1	96.2	97.4
80°	64.4	63.7	62.9	63.7	64.4	65.9	67.4	68.9	70.4	71.2	71.9
82.5°	44.2	43.4	42.7	43.8	44.9	46.1	47.2	48.3	49.4	49.8	50.2
85°	25.5	26.6	27.7	27.7	27.7	28.1	28.5	28.8	29.2	28.8	28.5
87.5°	12.0	12.4	12.7	12.7	12.7	13.1	13.5	13.5	13.5	13.1	12.7
90°	12.8	15.1	18.6	22.1	25.6	29.0	27.9	29.0	30.2	31.4	33.7
92.5°	59.3	80.2	117.3	178.9	239.3	216.1	161.5	115.0	89.5	77.8	69.7
95°	105.7	151.0	249.8	422.9	613.5	689.0	558.8	418.3	283.5	221.9	180.1
97.5°	122.0	172.0	269.5	470.5	791.2	1059.6	1095.6	960.8	725.0	571.6	439.2
100°	139.4	184.7	266.1	438.0	743.6	1100.3	1329.2	1369.8	1275.7	1139.8	974.8
102.5°	159.2	199.8	270.7	410.1	673.9	1024.7	1340.8	1505.8	1525.5	1460.4	1371.0
105°	181.2	217.3	280.0	399.7	619.3	934.1	1267.6	1510.4	1626.6	1648.7	1618.5
107.5°	205.6	239.3	295.1	397.4	579.8	854.0	1163.0	1440.7	1623.1	1713.7	1745.1
110°	230.0	262.6	314.9	403.2	558.8	787.7	1065.4	1331.5	1545.3	1691.7	1773.0



TEST NUMBER: P831482

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	255.6	287.0	334.6	414.8	547.2	743.6	980.6	1223.4	1443.0	1611.5	1721.9
115°	281.2	312.5	356.7	427.6	546.1	714.5	915.5	1130.5	1332.6	1503.4	1630.1
117.5°	306.7	335.8	379.9	443.8	547.2	694.8	872.5	1058.4	1237.4	1394.2	1525.5
120°	331.1	360.2	402.0	462.4	551.9	682.0	840.0	1003.8	1160.7	1300.1	1417.5
122.5°	353.2	384.6	425.2	479.8	560.0	673.9	813.3	960.8	1099.1	1225.7	1332.6
125°	375.3	406.6	447.3	498.4	568.1	666.9	791.2	923.7	1050.3	1161.8	1254.8
127.5°	396.2	427.6	467.1	513.5	577.4	663.4	770.3	890.0	1005.0	1107.2	1193.2
130°	414.8	446.1	484.5	528.6	586.7	659.9	754.0	858.6	963.2	1057.3	1136.3
132.5°	432.2	462.4	499.6	542.6	593.7	658.8	738.9	829.6	923.7	1009.6	1084.0
135°	447.3	478.7	514.7	554.2	600.7	657.6	726.2	804.0	886.5	962.0	1028.2
137.5°	461.3	490.3	525.2	563.5	605.3	655.3	714.5	779.6	849.3	916.7	976.0
140°	472.9	501.9	535.6	570.5	610.0	654.1	704.1	758.7	817.9	873.7	923.7
142.5°	484.5	511.2	543.7	577.4	613.5	651.8	694.8	738.9	787.7	834.2	876.0
145°	493.8	520.5	550.7	582.1	614.6	649.5	686.7	723.8	762.2	799.4	833.0
147.5°	505.4	528.6	556.5	585.6	614.6	646.0	678.5	711.1	742.4	773.8	798.2
150°	514.7	535.6	562.3	586.7	614.6	641.3	670.4	697.1	723.8	748.2	770.3
152.5°	524.0	543.7	565.8	589.1	611.1	635.5	661.1	684.3	706.4	727.3	744.7
155°	534.4	550.7	570.5	589.1	608.8	628.6	651.8	671.5	690.1	707.6	721.5
157.5°	543.7	556.5	572.8	590.2	605.3	622.8	641.3	657.6	673.9	687.8	699.4
160°	550.7	562.3	576.3	590.2	603.0	615.8	630.9	646.0	658.8	670.4	678.5
162.5°	556.5	565.8	577.4	589.1	598.4	608.8	620.4	632.0	642.5	653.0	659.9
165°	561.2	569.3	578.6	586.7	593.7	601.8	611.1	620.4	627.4	635.5	641.3
167.5°	565.8	571.6	578.6	585.6	589.1	594.9	601.8	610.0	615.8	620.4	625.1
170°	569.3	571.6	577.4	582.1	584.4	587.9	593.7	599.5	603.0	607.6	610.0
172.5°	571.6	572.8	577.4	580.9	580.9	582.1	585.6	590.2	592.5	596.0	597.2
175°	572.8	574.0	576.3	578.6	577.4	577.4	579.8	582.1	583.2	585.6	585.6
177.5°	574.0	574.0	575.1	577.4	575.1	574.0	575.1	576.3	577.4	578.6	578.6
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0



TEST NUMBER: P831482

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1614.1	1614.1	1614.1	1614.1
2.5°	1434.7	1432.1	1421.6	1411.1
5°	1216.4	1207.4	1204.4	1201.4
7.5°	1062.8	1062.1	1046.4	1030.6
10°	927.7	928.8	914.5	900.3
12.5°	831.0	821.7	820.5	819.4
15°	758.4	749.8	748.3	746.8
17.5°	707.1	701.8	700.3	698.8
20°	668.1	665.1	662.5	659.9
22.5°	634.4	630.7	628.4	626.2
25°	601.8	598.5	597.7	597.0
27.5°	572.6	568.5	568.5	568.5
30°	544.9	542.3	541.2	540.0
32.5°	519.1	516.8	516.8	516.8
35°	494.7	493.6	492.1	490.6
37.5°	472.6	472.6	471.9	471.1
40°	451.3	452.4	452.4	452.4
42.5°	431.8	432.9	432.9	432.9
45°	411.6	413.5	414.2	415.0
47.5°	391.7	394.7	395.5	396.2
50°	372.3	374.5	374.9	375.3
52.5°	352.4	355.0	356.9	358.8
55°	331.4	334.1	335.2	336.3
57.5°	309.0	311.6	312.0	312.3
60°	284.2	286.9	287.6	288.4
62.5°	260.7	262.2	262.9	263.7
65°	233.7	235.9	237.4	238.9
67.5°	207.9	209.7	209.7	209.7
70°	179.0	179.8	180.9	182.0
72.5°	152.4	152.8	152.8	152.8
75°	124.3	125.1	125.5	125.8
77.5°	97.7	98.1	98.1	98.1
80°	71.5	71.2	71.2	71.2
82.5°	49.1	47.9	47.9	47.9
85°	28.1	27.7	28.1	28.5
87.5°	12.7	12.7	12.7	12.7
90°	32.5	33.7	34.9	33.7
92.5°	67.4	62.7	63.9	61.6
95°	158.0	147.6	139.4	134.8
97.5°	361.3	317.2	289.3	276.5
100°	857.4	772.6	727.3	728.5
102.5°	1286.2	1223.4	1187.4	1153.7
105°	1565.0	1520.9	1483.7	1477.9
107.5°	1738.1	1717.2	1702.1	1689.3
110°	1805.5	1814.8	1812.5	1810.2



TEST NUMBER: P831482

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	1788.1	1821.8	1833.4	1834.6
115°	1717.2	1768.3	1791.6	1797.4
117.5°	1616.1	1673.1	1707.9	1716.0
120°	1509.2	1574.3	1602.2	1609.2
122.5°	1411.6	1468.6	1499.9	1509.2
125°	1329.2	1380.3	1409.3	1417.5
127.5°	1260.6	1304.8	1331.5	1338.4
130°	1197.9	1239.7	1264.1	1273.4
132.5°	1140.9	1182.8	1203.7	1209.5
135°	1085.2	1120.0	1140.9	1149.1
137.5°	1024.7	1060.8	1078.2	1085.2
140°	967.8	1000.4	1018.9	1017.8
142.5°	912.1	939.9	956.2	955.0
145°	862.1	886.5	895.8	898.1
147.5°	821.4	838.9	848.1	849.3
150°	787.7	800.5	807.5	807.5
152.5°	757.5	769.1	772.6	772.6
155°	732.0	741.3	743.6	744.7
157.5°	708.7	715.7	718.0	718.0
160°	686.7	693.6	693.6	692.5
162.5°	664.6	670.4	670.4	669.2
165°	646.0	650.6	649.5	649.5
167.5°	627.4	630.9	629.7	629.7
170°	611.1	613.5	612.3	612.3
172.5°	597.2	599.5	597.2	596.0
175°	585.6	586.7	585.6	584.4
177.5°	577.4	578.6	576.3	576.3
180°	574.0	574.0	574.0	574.0



TEST NUMBER: P831482

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-G4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.20	12.94	13.26	14.00	15.44	14.44	15.17	15.50	16.23	17.67
	3H	13.84	14.50	14.91	15.57	17.03	15.85	16.51	16.93	17.58	19.04
	4H	14.41	15.03	15.49	16.11	17.57	16.30	16.92	17.38	17.99	19.46
	6H	14.77	15.35	15.87	16.42	17.90	16.57	17.14	17.66	18.22	19.69
	8H	14.87	15.41	15.96	16.50	17.98	16.63	17.17	17.72	18.26	19.73
	12H	14.91	15.43	16.01	16.51	18.01	16.64	17.16	17.74	18.24	19.74
4H	2H	12.76	13.38	13.85	14.46	15.92	14.59	15.21	15.68	16.28	17.75
	3H	14.58	15.10	15.68	16.20	17.68	16.19	16.71	17.29	17.81	19.29
	4H	15.27	15.75	16.37	16.84	18.34	16.77	17.25	17.87	18.34	19.84
	6H	15.74	16.15	16.85	17.26	18.75	17.17	17.58	18.28	18.69	20.18
	8H	15.87	16.26	16.98	17.36	18.87	17.28	17.66	18.39	18.77	20.27
	12H	15.94	16.28	17.06	17.40	18.91	17.32	17.66	18.44	18.78	20.29
8H	4H	15.53	15.91	16.64	17.01	18.52	16.87	17.25	17.98	18.35	19.86
	6H	16.11	16.43	17.24	17.57	19.08	17.37	17.68	18.50	18.83	20.33
	8H	16.32	16.59	17.46	17.72	19.25	17.55	17.82	18.68	18.95	20.47
	12H	16.44	16.68	17.58	17.80	19.37	17.64	17.88	18.78	19.01	20.57
12H	4H	15.52	15.87	16.65	16.99	18.50	16.84	17.18	17.96	18.30	19.81
	6H	16.16	16.44	17.30	17.57	19.09	17.38	17.66	18.52	18.78	20.31
	8H	16.39	16.63	17.53	17.76	19.32	17.57	17.82	18.71	18.94	20.50