

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332006-830

Luminaire Tested: **S123DIP-S1000D365U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332006-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1000D365U830-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5250.5 lumens  
Efficiency: N/A  
Efficacy: 120.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332006-830

CATALOG NUMBER: S123DIP-S1000D365U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332006-830

CATALOG NUMBER: S123DIP-S1000D365U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78
1	103	99	94	91	98	94	90	87	85	82	79	77	74	72	69	67	66
2	94	86	80	74	89	82	76	71	74	70	66	67	64	60	61	58	55
3	86	76	68	62	81	72	65	60	66	60	55	59	55	51	54	50	47
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	41
5	72	60	51	45	68	57	49	44	52	46	41	48	42	38	43	39	35
6	67	54	45	39	63	52	44	38	47	41	36	43	38	33	39	35	31
7	62	49	40	35	58	47	39	34	43	36	32	39	34	30	36	31	28
8	57	44	36	31	54	43	35	30	39	33	28	36	31	27	33	28	25
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	23
10	50	37	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16060	16060	16060
5°	16134	15913	16024
10°	16027	15774	15872
15°	15840	15597	15624
20°	15621	15341	15356
25°	15327	15037	15007
30°	15003	14701	14588
35°	14666	14345	14160
40°	14313	13952	13735
45°	13922	13592	13259
50°	13534	13147	12782
55°	13024	12688	12301
60°	12510	12152	11765
65°	12055	11566	11207
70°	11383	10902	10414
75°	10405	10031	9603
80°	9385	8988	8901
85°	8238	7929	7595



TEST NUMBER: P332006-830

CATALOG NUMBER: S123DIP-S1000D365U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	140.5	2.7
10°-20°	396.8	7.6
20°-30°	586.2	11.2
30°-40°	684.7	13.0
40°-50°	688.4	13.1
50°-60°	604.7	11.5
60°-70°	450.5	8.6
70°-80°	256.7	4.9
80°-90°	74.9	1.4
90°-100°	16.3	0.3
100°-110°	77.7	1.5
110°-120°	186.6	3.6
120°-130°	237.6	4.5
130°-140°	253.9	4.8
140°-150°	237.4	4.5
150°-160°	191.5	3.6
160°-170°	123.6	2.4
170°-180°	42.6	0.8
0°-30°	1123.5	21.4
0°-40°	1808.2	34.4
0°-60°	3101.3	59.1
0°-90°	3883.4	74.0
90°-120°	280.6	5.3
90°-150°	1009.4	19.2
90°-180°	1367.0	26.0
0°-180°	5250.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1492	1492	1492	1492	1492	
5°	1493	1486	1473	1485	1483	141
15°	1421	1416	1400	1409	1402	401
25°	1290	1282	1266	1267	1264	594
35°	1116	1108	1092	1084	1078	698
45°	915	909	893	878	871	706
55°	694	692	676	662	656	621
65°	473	467	454	444	440	467
75°	250	245	241	235	231	267
85°	67	64	64	62	62	73
90°	0	4	8	9	10	5
95°	20	8	10	12	13	25
105°	99	101	73	17	15	105
115°	186	188	191	194	196	184
125°	262	265	266	267	268	234
135°	327	329	330	331	330	251
145°	377	379	380	381	381	236
155°	415	415	415	416	415	191
165°	438	437	437	439	437	124
175°	448	447	447	449	447	43
180°	448	448	448	448	448	



TEST NUMBER: P332006-830

CATALOG NUMBER: S123DIP-S1000D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0
2.5°	1497.0	1496.2	1495.2	1494.3	1493.5	1491.7	1489.2	1486.7	1484.2	1481.7	1483.9
5°	1493.2	1491.8	1490.3	1488.9	1487.5	1485.3	1482.1	1478.9	1475.8	1472.7	1475.6
7.5°	1478.6	1477.2	1475.7	1474.3	1472.9	1470.6	1467.4	1464.1	1460.8	1457.5	1460.1
10°	1466.3	1464.9	1463.4	1462.0	1460.6	1458.0	1454.3	1450.6	1446.9	1443.2	1445.8
12.5°	1449.8	1448.7	1447.5	1446.2	1445.1	1442.7	1439.3	1435.8	1432.3	1428.8	1430.7
15°	1421.4	1420.2	1419.1	1418.0	1416.8	1414.4	1410.7	1407.0	1403.3	1399.6	1401.8
17.5°	1388.3	1386.8	1385.3	1383.8	1382.3	1379.8	1376.0	1372.3	1368.7	1364.9	1366.5
20°	1363.7	1362.0	1360.3	1358.5	1356.8	1354.1	1350.4	1346.7	1343.0	1339.3	1340.4
22.5°	1336.0	1334.3	1332.6	1330.8	1329.1	1326.4	1322.7	1319.0	1315.3	1311.5	1312.5
25°	1290.5	1288.8	1287.1	1285.4	1283.6	1281.0	1277.2	1273.6	1269.9	1266.1	1266.4
27.5°	1242.1	1240.4	1238.7	1237.1	1235.4	1232.6	1228.6	1224.6	1220.6	1216.6	1216.8
30°	1207.1	1205.7	1204.3	1202.9	1201.5	1198.7	1194.8	1190.7	1186.8	1182.8	1182.8
32.5°	1172.2	1170.4	1168.5	1166.6	1164.7	1162.2	1159.1	1156.1	1153.0	1149.9	1148.3
35°	1116.1	1114.4	1112.7	1111.0	1109.2	1106.5	1102.8	1099.1	1095.4	1091.7	1090.0
37.5°	1058.6	1056.4	1054.2	1052.1	1049.9	1047.0	1043.2	1039.4	1035.7	1031.9	1029.8
40°	1018.6	1016.8	1015.1	1013.4	1011.7	1008.9	1004.8	1000.9	996.9	992.9	990.6
42.5°	978.5	976.6	974.7	972.7	970.8	967.8	963.8	959.9	955.8	951.9	949.6
45°	914.6	913.5	912.4	911.3	910.1	907.7	904.0	900.2	896.5	892.9	889.5
47.5°	851.3	849.6	848.0	846.3	844.7	842.1	838.7	835.2	831.7	828.2	824.8
50°	808.2	806.7	805.3	803.9	802.5	799.9	796.2	792.5	788.8	785.1	781.9
52.5°	763.0	762.0	761.1	760.2	759.1	756.7	752.8	748.9	744.9	740.9	738.3
55°	694.0	693.7	693.4	693.1	692.9	690.9	687.2	683.4	679.8	676.1	672.9
57.5°	628.3	627.4	626.4	625.5	624.4	622.5	619.5	616.5	613.6	610.7	607.8
60°	581.1	580.8	580.5	580.2	579.9	578.2	574.7	571.3	567.9	564.5	561.8
62.5°	539.0	538.3	537.5	536.8	536.1	534.0	530.6	527.2	523.8	520.3	517.7
65°	473.3	471.9	470.5	469.1	467.7	465.5	462.7	459.9	456.9	454.1	451.9
67.5°	403.9	402.6	401.3	400.1	398.8	397.1	394.9	392.8	390.6	388.4	386.4
70°	361.7	360.1	358.4	356.7	355.0	353.2	351.5	349.8	348.1	346.4	344.4
72.5°	317.6	316.4	315.1	313.9	312.6	311.0	309.1	307.2	305.2	303.2	301.5
75°	250.2	249.0	247.9	246.8	245.6	244.6	243.7	242.9	242.0	241.2	239.8
77.5°	190.4	189.7	189.1	188.5	187.8	187.0	186.1	185.0	184.0	182.9	182.0
80°	151.4	150.5	149.7	148.8	148.0	147.2	146.7	146.1	145.5	145.0	144.7
82.5°	113.4	113.2	113.1	112.9	112.7	112.5	112.4	112.4	112.3	112.2	111.6
85°	66.7	66.2	65.6	65.0	64.5	64.2	64.2	64.2	64.2	64.2	63.5
87.5°	26.8	26.2	25.6	25.2	24.6	24.3	24.3	24.2	24.2	24.2	24.0
90°	0.4	1.0	1.8	2.5	3.3	4.1	5.1	6.0	7.1	8.0	8.3
92.5°	6.2	6.0	5.7	5.6	5.4	5.7	6.3	7.1	7.8	8.5	9.0
95°	20.4	17.2	14.2	11.2	8.2	7.1	7.9	8.7	9.5	10.4	10.8
97.5°	40.8	39.5	38.1	36.8	35.3	32.0	26.7	21.4	16.0	10.7	11.3
100°	56.3	57.8	59.3	60.7	62.2	57.2	45.6	34.1	22.5	11.0	11.6
102.5°	73.9	74.9	76.0	77.1	78.1	72.4	59.8	47.1	34.5	22.0	20.1
105°	99.2	100.1	100.9	101.7	102.5	99.6	92.9	86.2	79.6	73.0	59.9
107.5°	126.0	126.7	127.3	128.0	128.7	129.5	130.5	131.6	132.6	133.7	124.0
110°	143.9	144.5	145.1	145.6	146.3	146.9	147.8	148.5	149.4	150.2	147.8



TEST NUMBER: P332006-830

CATALOG NUMBER: S123DIP-S1000D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	160.9	161.5	162.0	162.5	163.1	163.7	164.6	165.4	166.2	167.0	167.0
115°	186.2	186.6	187.1	187.5	187.9	188.5	189.2	189.8	190.5	191.1	191.9
117.5°	210.7	211.2	211.7	212.3	212.8	213.3	213.6	214.0	214.3	214.6	215.2
120°	225.8	226.5	227.2	227.8	228.5	228.9	229.1	229.4	229.6	229.8	230.5
122.5°	241.3	241.9	242.3	242.9	243.5	243.8	244.1	244.4	244.7	245.0	245.4
125°	262.5	263.1	263.6	264.2	264.9	265.2	265.6	265.9	266.2	266.5	266.6
127.5°	283.0	283.6	284.2	284.7	285.3	285.8	286.2	286.5	286.9	287.2	287.5
130°	295.8	296.3	296.9	297.6	298.1	298.6	298.9	299.2	299.4	299.7	300.0
132.5°	308.0	308.6	309.2	309.8	310.4	310.8	311.0	311.3	311.5	311.8	312.1
135°	326.8	327.2	327.6	328.1	328.5	328.9	329.1	329.5	329.8	330.1	330.3
137.5°	342.7	343.3	343.8	344.4	345.0	345.3	345.5	345.6	345.8	346.0	346.4
140°	353.4	353.8	354.3	354.7	355.2	355.5	355.7	355.9	356.2	356.4	356.7
142.5°	363.3	363.7	364.1	364.6	365.0	365.3	365.6	365.8	366.0	366.3	366.5
145°	377.0	377.6	378.1	378.6	379.1	379.5	379.6	379.8	379.8	380.0	380.2
147.5°	390.0	390.4	390.7	391.1	391.3	391.6	391.8	391.9	392.1	392.2	392.4
150°	398.0	398.2	398.4	398.7	398.9	399.1	399.3	399.4	399.5	399.6	399.8
152.5°	405.2	405.3	405.4	405.5	405.6	405.8	405.8	405.9	406.0	406.0	406.3
155°	415.4	415.2	415.0	414.9	414.7	414.7	414.8	414.8	414.9	415.0	415.4
157.5°	423.2	423.2	423.2	423.1	423.1	423.1	423.0	422.9	422.8	422.8	423.2
160°	428.0	427.9	427.8	427.7	427.7	427.6	427.5	427.4	427.4	427.3	427.7
162.5°	432.5	432.3	432.2	432.0	431.8	431.6	431.5	431.5	431.4	431.3	431.8
165°	438.0	437.7	437.5	437.3	437.1	437.0	436.9	436.8	436.7	436.7	437.2
167.5°	442.2	442.0	441.7	441.4	441.0	440.9	440.9	440.9	440.9	440.9	441.5
170°	444.6	444.3	444.0	443.7	443.5	443.3	443.3	443.3	443.3	443.3	443.9
172.5°	446.2	445.9	445.5	445.2	444.8	444.7	444.7	444.8	444.9	444.9	445.5
175°	448.3	447.9	447.5	447.2	446.9	446.7	446.8	446.9	446.9	447.0	447.5
177.5°	448.8	448.6	448.3	448.0	447.6	447.5	447.6	447.6	447.7	447.8	448.3
180°	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3



TEST NUMBER: P332006-830

CATALOG NUMBER: S123DIP-S1000D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0
2.5°	1486.2	1488.6	1490.8	1491.9	1491.6	1491.4	1491.1	1490.9
5°	1478.4	1481.2	1484.1	1485.3	1484.7	1484.1	1483.6	1483.0
7.5°	1462.7	1465.3	1467.8	1469.0	1468.6	1468.3	1467.9	1467.5
10°	1448.3	1450.9	1453.5	1454.4	1453.9	1453.3	1452.7	1452.2
12.5°	1432.6	1434.5	1436.3	1437.1	1436.8	1436.4	1436.1	1435.8
15°	1404.1	1406.4	1408.7	1409.0	1407.3	1405.5	1403.8	1402.1
17.5°	1368.1	1369.7	1371.3	1371.8	1371.2	1370.6	1369.9	1369.3
20°	1341.5	1342.7	1343.9	1344.0	1343.1	1342.3	1341.4	1340.6
22.5°	1313.4	1314.3	1315.2	1315.1	1314.1	1313.0	1311.9	1310.8
25°	1266.7	1267.1	1267.3	1267.1	1266.1	1265.3	1264.4	1263.6
27.5°	1217.1	1217.3	1217.6	1217.1	1216.1	1214.9	1213.9	1212.8
30°	1182.8	1182.8	1182.8	1181.8	1179.8	1177.8	1175.8	1173.7
32.5°	1146.7	1145.2	1143.6	1142.2	1141.1	1140.0	1139.0	1137.8
35°	1088.3	1086.6	1084.9	1083.3	1081.9	1080.4	1079.0	1077.6
37.5°	1027.8	1025.8	1023.7	1022.2	1021.3	1020.4	1019.5	1018.6
40°	988.4	986.1	983.8	982.0	980.9	979.8	978.6	977.5
42.5°	947.3	945.0	942.7	941.0	939.9	938.8	937.6	936.5
45°	886.0	882.6	879.2	876.8	875.3	873.9	872.5	871.0
47.5°	821.4	818.1	814.7	812.5	811.2	809.9	808.7	807.4
50°	778.8	775.7	772.5	770.2	768.5	766.7	765.0	763.3
52.5°	735.6	732.9	730.3	728.0	726.3	724.6	722.9	721.2
55°	669.8	666.7	663.5	661.2	659.8	658.4	657.0	655.5
57.5°	605.0	602.3	599.5	597.2	595.6	593.9	592.3	590.6
60°	559.3	556.8	554.2	552.2	550.7	549.3	547.9	546.5
62.5°	515.2	512.6	510.0	508.3	507.3	506.3	505.4	504.4
65°	449.6	447.2	445.0	443.5	442.6	441.8	440.8	440.0
67.5°	384.5	382.5	380.5	378.9	377.7	376.5	375.2	374.1
70°	342.3	340.4	338.4	336.7	335.3	333.8	332.4	330.9
72.5°	299.7	297.9	296.1	294.9	294.2	293.4	292.8	292.0
75°	238.4	236.9	235.4	234.3	233.5	232.6	231.8	230.9
77.5°	181.0	180.0	179.1	178.6	178.6	178.6	178.6	178.6
80°	144.4	144.1	143.8	143.6	143.6	143.6	143.6	143.6
82.5°	111.1	110.6	110.1	109.7	109.4	109.2	109.1	108.8
85°	63.0	62.4	61.8	61.5	61.5	61.5	61.5	61.5
87.5°	23.8	23.7	23.5	23.5	23.5	23.5	23.6	23.6
90°	8.6	8.9	9.1	9.4	9.5	9.7	9.8	10.0
92.5°	9.5	10.0	10.5	10.7	10.7	10.8	10.9	11.0
95°	11.4	11.9	12.4	12.6	12.6	12.6	12.6	12.6
97.5°	11.9	12.5	13.1	13.4	13.5	13.6	13.7	13.8
100°	12.2	12.7	13.4	13.7	13.8	13.9	13.9	13.9
102.5°	18.3	16.4	14.6	13.8	13.9	13.9	14.1	14.2
105°	46.8	33.6	20.5	14.0	14.2	14.3	14.5	14.6
107.5°	114.5	104.9	95.3	85.5	75.7	65.8	55.9	46.0
110°	145.3	142.9	140.4	133.9	123.4	112.7	102.2	91.6





TEST NUMBER: P332006-830

CATALOG NUMBER: S123DIP-S1000D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	167.1	167.1	167.2	166.1	163.8	161.6	159.4	157.1
115°	192.7	193.4	194.2	194.6	194.9	195.3	195.6	195.9
117.5°	215.8	216.4	217.0	217.4	217.4	217.4	217.5	217.5
120°	231.0	231.6	232.1	232.5	232.5	232.5	232.5	232.5
122.5°	245.8	246.3	246.7	246.9	246.9	247.0	247.0	247.1
125°	266.7	266.9	267.0	267.2	267.3	267.5	267.7	267.8
127.5°	287.7	287.9	288.2	288.2	288.0	287.9	287.8	287.7
130°	300.4	300.7	301.0	301.0	300.9	300.8	300.6	300.4
132.5°	312.4	312.6	312.9	313.0	312.7	312.5	312.4	312.2
135°	330.5	330.7	330.9	330.9	330.7	330.5	330.3	330.1
137.5°	346.7	347.0	347.4	347.5	347.3	347.2	347.0	346.9
140°	356.9	357.2	357.6	357.6	357.5	357.3	357.2	357.0
142.5°	366.7	366.9	367.2	367.2	367.0	366.7	366.6	366.4
145°	380.3	380.5	380.6	380.7	380.7	380.7	380.7	380.7
147.5°	392.5	392.7	392.9	392.8	392.4	392.0	391.7	391.3
150°	400.0	400.1	400.3	400.2	400.0	399.8	399.5	399.4
152.5°	406.6	406.9	407.2	407.1	406.8	406.4	406.0	405.8
155°	415.8	416.1	416.5	416.4	416.0	415.6	415.1	414.6
157.5°	423.7	424.1	424.6	424.5	424.0	423.4	422.7	422.2
160°	428.2	428.7	429.1	429.0	428.6	428.0	427.5	427.0
162.5°	432.3	432.8	433.3	433.4	432.9	432.4	432.0	431.5
165°	437.8	438.5	439.0	439.0	438.6	438.0	437.5	437.0
167.5°	442.1	442.7	443.3	443.3	442.7	442.1	441.5	440.9
170°	444.5	445.1	445.6	445.6	445.1	444.5	443.9	443.3
172.5°	446.1	446.7	447.2	447.2	446.6	445.9	445.3	444.6
175°	448.0	448.6	449.0	449.0	448.5	447.8	447.2	446.7
177.5°	448.7	449.2	449.7	449.6	449.0	448.5	447.8	447.2
180°	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3

(END OF REPORT)