

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332007-830

Luminaire Tested: **S123DIP-S1000D365U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332007-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1000D365U830-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5058.2 lumens  
Efficiency: N/A  
Efficacy: 116.3 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332007-830

CATALOG NUMBER: S123DIP-S1000D365U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332007-830

CATALOG NUMBER: S123DIP-S1000D365U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77
1	104	99	95	91	99	95	91	88	86	83	81	78	76	74	71	70	68	64
2	94	87	80	75	90	83	77	72	75	71	67	69	65	62	63	60	57	54
3	86	76	68	62	82	73	66	60	67	61	56	61	56	52	55	52	49	46
4	79	67	59	53	75	65	57	51	59	53	48	54	49	45	50	45	42	39
5	73	60	52	45	69	58	50	44	53	47	42	49	43	39	45	40	37	34
6	67	54	46	40	64	52	44	39	48	41	36	44	39	34	41	36	32	30
7	62	49	41	35	59	47	39	34	44	37	32	40	35	30	37	32	29	26
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26	24
9	54	41	33	28	51	40	32	27	37	30	26	34	29	25	32	27	23	21
10	50	38	30	25	48	36	29	25	34	28	23	32	26	22	29	25	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16060	16060	16060
5°	16134	15913	16024
10°	16027	15774	15872
15°	15840	15597	15624
20°	15621	15341	15356
25°	15327	15037	15007
30°	15003	14701	14588
35°	14666	14345	14160
40°	14313	13952	13735
45°	13922	13592	13259
50°	13534	13147	12782
55°	13024	12688	12301
60°	12510	12152	11765
65°	12055	11566	11207
70°	11383	10902	10414
75°	10405	10031	9603
80°	9385	8988	8901
85°	8238	7929	7595



TEST NUMBER: P332007-830

CATALOG NUMBER: S123DIP-S1000D365U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	140.5	2.8
10°-20°	396.8	7.8
20°-30°	586.2	11.6
30°-40°	684.7	13.5
40°-50°	688.4	13.6
50°-60°	604.7	12.0
60°-70°	450.5	8.9
70°-80°	256.7	5.1
80°-90°	74.9	1.5
90°-100°	27.6	0.5
100°-110°	82.7	1.6
110°-120°	140.6	2.8
120°-130°	185.0	3.7
130°-140°	207.9	4.1
140°-150°	204.4	4.0
150°-160°	172.0	3.4
160°-170°	114.5	2.3
170°-180°	40.1	0.8
0°-30°	1123.5	22.2
0°-40°	1808.2	35.7
0°-60°	3101.3	61.3
0°-90°	3883.4	76.8
90°-120°	250.9	5.0
90°-150°	848.1	16.8
90°-180°	1175.0	23.2
0°-180°	5058.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1492	1492	1492	1492	1492	
5°	1493	1486	1473	1485	1483	141
15°	1421	1416	1400	1409	1402	401
25°	1290	1282	1266	1267	1264	594
35°	1116	1108	1092	1084	1078	698
45°	915	909	893	878	871	706
55°	694	692	676	662	656	621
65°	473	467	454	444	440	467
75°	250	245	241	235	231	267
85°	67	64	64	62	62	73
90°	0	4	8	9	10	5
95°	20	22	25	26	26	22
105°	75	76	79	79	79	80
115°	142	142	142	142	142	140
125°	207	208	208	206	205	185
135°	269	271	270	269	268	207
145°	326	327	328	327	326	204
155°	373	373	374	375	373	172
165°	407	406	406	408	405	115
175°	423	422	422	423	421	40
180°	424	424	424	424	424	



TEST NUMBER: P332007-830

CATALOG NUMBER: S123DIP-S1000D365U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0
2.5°	1497.0	1496.2	1495.2	1494.3	1493.5	1491.7	1489.2	1486.7	1484.2	1481.7	1483.9
5°	1493.2	1491.8	1490.3	1488.9	1487.5	1485.3	1482.1	1478.9	1475.8	1472.7	1475.6
7.5°	1478.6	1477.2	1475.7	1474.3	1472.9	1470.6	1467.4	1464.1	1460.8	1457.5	1460.1
10°	1466.3	1464.9	1463.4	1462.0	1460.6	1458.0	1454.3	1450.6	1446.9	1443.2	1445.8
12.5°	1449.8	1448.7	1447.5	1446.2	1445.1	1442.7	1439.3	1435.8	1432.3	1428.8	1430.7
15°	1421.4	1420.2	1419.1	1418.0	1416.8	1414.4	1410.7	1407.0	1403.3	1399.6	1401.8
17.5°	1388.3	1386.8	1385.3	1383.8	1382.3	1379.8	1376.0	1372.3	1368.7	1364.9	1366.5
20°	1363.7	1362.0	1360.3	1358.5	1356.8	1354.1	1350.4	1346.7	1343.0	1339.3	1340.4
22.5°	1336.0	1334.3	1332.6	1330.8	1329.1	1326.4	1322.7	1319.0	1315.3	1311.5	1312.5
25°	1290.5	1288.8	1287.1	1285.4	1283.6	1281.0	1277.2	1273.6	1269.9	1266.1	1266.4
27.5°	1242.1	1240.4	1238.7	1237.1	1235.4	1232.6	1228.6	1224.6	1220.6	1216.6	1216.8
30°	1207.1	1205.7	1204.3	1202.9	1201.5	1198.7	1194.8	1190.7	1186.8	1182.8	1182.8
32.5°	1172.2	1170.4	1168.5	1166.6	1164.7	1162.2	1159.1	1156.1	1153.0	1149.9	1148.3
35°	1116.1	1114.4	1112.7	1111.0	1109.2	1106.5	1102.8	1099.1	1095.4	1091.7	1090.0
37.5°	1058.6	1056.4	1054.2	1052.1	1049.9	1047.0	1043.2	1039.4	1035.7	1031.9	1029.8
40°	1018.6	1016.8	1015.1	1013.4	1011.7	1008.9	1004.8	1000.9	996.9	992.9	990.6
42.5°	978.5	976.6	974.7	972.7	970.8	967.8	963.8	959.9	955.8	951.9	949.6
45°	914.6	913.5	912.4	911.3	910.1	907.7	904.0	900.2	896.5	892.9	889.5
47.5°	851.3	849.6	848.0	846.3	844.7	842.1	838.7	835.2	831.7	828.2	824.8
50°	808.2	806.7	805.3	803.9	802.5	799.9	796.2	792.5	788.8	785.1	781.9
52.5°	763.0	762.0	761.1	760.2	759.1	756.7	752.8	748.9	744.9	740.9	738.3
55°	694.0	693.7	693.4	693.1	692.9	690.9	687.2	683.4	679.8	676.1	672.9
57.5°	628.3	627.4	626.4	625.5	624.4	622.5	619.5	616.5	613.6	610.7	607.8
60°	581.1	580.8	580.5	580.2	579.9	578.2	574.7	571.3	567.9	564.5	561.8
62.5°	539.0	538.3	537.5	536.8	536.1	534.0	530.6	527.2	523.8	520.3	517.7
65°	473.3	471.9	470.5	469.1	467.7	465.5	462.7	459.9	456.9	454.1	451.9
67.5°	403.9	402.6	401.3	400.1	398.8	397.1	394.9	392.8	390.6	388.4	386.4
70°	361.7	360.1	358.4	356.7	355.0	353.2	351.5	349.8	348.1	346.4	344.4
72.5°	317.6	316.4	315.1	313.9	312.6	311.0	309.1	307.2	305.2	303.2	301.5
75°	250.2	249.0	247.9	246.8	245.6	244.6	243.7	242.9	242.0	241.2	239.8
77.5°	190.4	189.7	189.1	188.5	187.8	187.0	186.1	185.0	184.0	182.9	182.0
80°	151.4	150.5	149.7	148.8	148.0	147.2	146.7	146.1	145.5	145.0	144.7
82.5°	113.4	113.2	113.1	112.9	112.7	112.5	112.4	112.4	112.3	112.2	111.6
85°	66.7	66.2	65.6	65.0	64.5	64.2	64.2	64.2	64.2	64.2	63.5
87.5°	26.8	26.2	25.6	25.2	24.6	24.3	24.3	24.2	24.2	24.2	24.0
90°	0.4	1.0	1.8	2.5	3.3	4.1	5.1	6.0	7.1	8.0	8.3
92.5°	8.1	8.6	9.0	9.6	10.1	10.6	11.1	11.7	12.3	12.8	13.0
95°	19.7	20.2	20.6	21.2	21.7	22.2	22.9	23.5	24.0	24.7	25.0
97.5°	34.9	35.3	35.7	36.1	36.5	36.9	37.3	37.7	38.2	38.5	38.9
100°	45.3	45.7	46.2	46.7	47.0	47.5	47.9	48.3	48.6	48.9	49.2
102.5°	57.3	57.6	57.8	58.1	58.3	58.7	59.2	59.8	60.2	60.7	60.9
105°	74.9	75.1	75.2	75.4	75.5	76.0	76.6	77.3	77.9	78.6	78.6
107.5°	95.5	95.6	95.7	95.8	95.9	96.0	96.2	96.5	96.8	97.1	97.3
110°	108.3	108.4	108.6	108.7	108.9	109.0	109.1	109.3	109.4	109.6	109.9



TEST NUMBER: P332007-830

CATALOG NUMBER: S123DIP-S1000D365U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	121.6	121.7	121.8	121.9	122.0	122.0	122.1	122.1	122.1	122.2	122.4
115°	141.6	141.8	142.0	142.2	142.4	142.5	142.3	142.2	142.0	141.9	141.9
117.5°	161.6	161.8	162.0	162.1	162.3	162.2	162.0	161.8	161.6	161.5	161.5
120°	174.2	174.7	175.1	175.5	176.0	176.0	175.7	175.3	174.9	174.6	174.5
122.5°	187.3	187.6	187.9	188.2	188.6	188.6	188.4	188.2	188.0	187.8	187.7
125°	207.2	207.4	207.6	207.8	208.1	208.1	207.9	207.8	207.6	207.5	207.2
127.5°	225.6	226.0	226.5	227.0	227.4	227.6	227.4	227.2	227.2	227.0	226.6
130°	237.8	238.4	239.0	239.6	240.2	240.3	240.2	240.0	239.7	239.5	239.2
132.5°	250.1	250.7	251.3	251.8	252.4	252.7	252.5	252.3	252.1	252.0	251.7
135°	268.8	269.3	269.7	270.1	270.6	270.8	270.7	270.6	270.5	270.5	270.1
137.5°	286.2	286.5	286.8	287.2	287.6	287.9	288.0	288.2	288.4	288.6	288.3
140°	298.1	298.5	298.9	299.3	299.6	299.8	299.9	299.9	300.0	300.1	300.0
142.5°	309.1	309.4	309.8	310.2	310.5	310.8	310.9	311.0	311.1	311.3	311.2
145°	326.1	326.2	326.4	326.5	326.7	326.9	327.1	327.3	327.5	327.7	327.7
147.5°	341.0	341.3	341.6	341.9	342.0	342.3	342.5	342.7	342.9	343.2	343.2
150°	351.4	351.6	351.7	351.9	352.0	352.1	352.3	352.4	352.6	352.7	352.7
152.5°	360.0	360.1	360.3	360.5	360.8	360.9	361.0	361.1	361.2	361.3	361.4
155°	373.4	373.4	373.4	373.4	373.4	373.4	373.5	373.5	373.6	373.7	374.0
157.5°	384.8	384.7	384.7	384.6	384.5	384.5	384.6	384.6	384.7	384.7	385.0
160°	392.0	391.9	391.7	391.6	391.4	391.3	391.3	391.3	391.3	391.3	391.7
162.5°	398.4	398.2	398.0	397.8	397.6	397.6	397.6	397.7	397.8	397.8	398.1
165°	406.7	406.5	406.2	406.0	405.8	405.7	405.7	405.7	405.7	405.7	406.1
167.5°	413.3	413.0	412.7	412.4	412.1	412.0	412.1	412.1	412.2	412.3	412.6
170°	417.0	416.7	416.4	416.1	415.8	415.7	415.7	415.7	415.7	415.7	416.2
172.5°	420.0	419.6	419.3	419.1	418.8	418.6	418.6	418.6	418.6	418.6	419.1
175°	423.0	422.7	422.4	422.2	421.9	421.7	421.7	421.7	421.7	421.7	422.2
177.5°	424.2	424.0	423.8	423.6	423.3	423.2	423.2	423.2	423.2	423.2	423.6
180°	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0



TEST NUMBER: P332007-830

CATALOG NUMBER: S123DIP-S1000D365U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0
2.5°	1486.2	1488.6	1490.8	1491.9	1491.6	1491.4	1491.1	1490.9
5°	1478.4	1481.2	1484.1	1485.3	1484.7	1484.1	1483.6	1483.0
7.5°	1462.7	1465.3	1467.8	1469.0	1468.6	1468.3	1467.9	1467.5
10°	1448.3	1450.9	1453.5	1454.4	1453.9	1453.3	1452.7	1452.2
12.5°	1432.6	1434.5	1436.3	1437.1	1436.8	1436.4	1436.1	1435.8
15°	1404.1	1406.4	1408.7	1409.0	1407.3	1405.5	1403.8	1402.1
17.5°	1368.1	1369.7	1371.3	1371.8	1371.2	1370.6	1369.9	1369.3
20°	1341.5	1342.7	1343.9	1344.0	1343.1	1342.3	1341.4	1340.6
22.5°	1313.4	1314.3	1315.2	1315.1	1314.1	1313.0	1311.9	1310.8
25°	1266.7	1267.1	1267.3	1267.1	1266.1	1265.3	1264.4	1263.6
27.5°	1217.1	1217.3	1217.6	1217.1	1216.1	1214.9	1213.9	1212.8
30°	1182.8	1182.8	1182.8	1181.8	1179.8	1177.8	1175.8	1173.7
32.5°	1146.7	1145.2	1143.6	1142.2	1141.1	1140.0	1139.0	1137.8
35°	1088.3	1086.6	1084.9	1083.3	1081.9	1080.4	1079.0	1077.6
37.5°	1027.8	1025.8	1023.7	1022.2	1021.3	1020.4	1019.5	1018.6
40°	988.4	986.1	983.8	982.0	980.9	979.8	978.6	977.5
42.5°	947.3	945.0	942.7	941.0	939.9	938.8	937.6	936.5
45°	886.0	882.6	879.2	876.8	875.3	873.9	872.5	871.0
47.5°	821.4	818.1	814.7	812.5	811.2	809.9	808.7	807.4
50°	778.8	775.7	772.5	770.2	768.5	766.7	765.0	763.3
52.5°	735.6	732.9	730.3	728.0	726.3	724.6	722.9	721.2
55°	669.8	666.7	663.5	661.2	659.8	658.4	657.0	655.5
57.5°	605.0	602.3	599.5	597.2	595.6	593.9	592.3	590.6
60°	559.3	556.8	554.2	552.2	550.7	549.3	547.9	546.5
62.5°	515.2	512.6	510.0	508.3	507.3	506.3	505.4	504.4
65°	449.6	447.2	445.0	443.5	442.6	441.8	440.8	440.0
67.5°	384.5	382.5	380.5	378.9	377.7	376.5	375.2	374.1
70°	342.3	340.4	338.4	336.7	335.3	333.8	332.4	330.9
72.5°	299.7	297.9	296.1	294.9	294.2	293.4	292.8	292.0
75°	238.4	236.9	235.4	234.3	233.5	232.6	231.8	230.9
77.5°	181.0	180.0	179.1	178.6	178.6	178.6	178.6	178.6
80°	144.4	144.1	143.8	143.6	143.6	143.6	143.6	143.6
82.5°	111.1	110.6	110.1	109.7	109.4	109.2	109.1	108.8
85°	63.0	62.4	61.8	61.5	61.5	61.5	61.5	61.5
87.5°	23.8	23.7	23.5	23.5	23.5	23.5	23.6	23.6
90°	8.6	8.9	9.1	9.4	9.5	9.7	9.8	10.0
92.5°	13.3	13.5	13.8	13.9	13.8	13.7	13.6	13.5
95°	25.3	25.5	25.8	26.0	26.0	26.0	26.0	26.0
97.5°	39.2	39.6	40.0	40.1	40.1	40.1	40.0	40.0
100°	49.4	49.7	49.9	50.0	50.1	50.3	50.5	50.6
102.5°	61.2	61.4	61.5	61.6	61.6	61.6	61.5	61.5
105°	78.6	78.6	78.6	78.7	78.8	79.0	79.2	79.3
107.5°	97.6	97.7	98.0	98.1	98.0	97.9	97.8	97.7
110°	110.2	110.5	110.7	110.8	110.7	110.6	110.4	110.3





TEST NUMBER: P332007-830

CATALOG NUMBER: S123DIP-S1000D365U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	122.8	123.2	123.6	123.7	123.7	123.7	123.6	123.6
115°	142.0	142.1	142.2	142.2	142.1	142.0	141.9	141.9
117.5°	161.5	161.5	161.5	161.3	161.1	160.9	160.7	160.5
120°	174.4	174.3	174.3	174.1	174.0	173.8	173.7	173.5
122.5°	187.5	187.3	187.1	186.9	186.7	186.4	186.2	186.1
125°	206.9	206.6	206.3	206.0	205.8	205.5	205.1	204.8
127.5°	226.1	225.7	225.3	224.9	224.6	224.2	223.9	223.6
130°	238.9	238.6	238.3	237.9	237.4	236.9	236.4	235.8
132.5°	251.3	250.9	250.6	250.2	249.8	249.4	249.0	248.6
135°	269.8	269.6	269.3	269.1	268.9	268.7	268.6	268.4
137.5°	288.0	287.8	287.4	287.1	286.8	286.5	286.3	286.0
140°	299.9	299.9	299.8	299.5	299.0	298.5	297.9	297.5
142.5°	311.1	311.0	311.0	310.8	310.4	310.0	309.5	309.2
145°	327.6	327.5	327.4	327.3	327.0	326.7	326.4	326.1
147.5°	343.2	343.2	343.2	342.9	342.5	342.0	341.6	341.1
150°	352.7	352.7	352.7	352.5	352.0	351.7	351.2	350.7
152.5°	361.5	361.7	361.7	361.6	361.2	360.8	360.4	360.1
155°	374.3	374.6	374.9	374.8	374.3	373.7	373.2	372.7
157.5°	385.3	385.7	386.0	385.9	385.5	385.1	384.7	384.3
160°	392.1	392.5	392.9	392.9	392.6	392.3	392.0	391.7
162.5°	398.5	398.9	399.3	399.2	398.7	398.2	397.8	397.3
165°	406.6	407.0	407.5	407.5	406.9	406.4	405.9	405.4
167.5°	413.1	413.6	414.1	414.1	413.6	413.1	412.6	412.3
170°	416.7	417.3	417.7	417.7	417.3	416.7	416.2	415.7
172.5°	419.5	420.0	420.5	420.5	419.9	419.4	418.9	418.4
175°	422.5	423.0	423.5	423.4	422.9	422.4	421.9	421.3
177.5°	424.0	424.2	424.6	424.6	424.2	423.8	423.4	422.9
180°	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0

(END OF REPORT)