

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331916

Luminaire Tested: **S123DIP-S560D365U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331916
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D365U835-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3770.0 lumens
Efficiency: N/A
Efficacy: 137.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331916

CATALOG NUMBER: S123DIP-S560D365U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331916

CATALOG NUMBER: S123DIP-S560D365U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	100	96	92	88	94	90	86	83	79	76	74	68	66	65	59	57	56	52
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	49	47	43
3	83	74	66	60	78	69	62	57	61	56	51	53	49	46	46	43	40	37
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	37	35	31
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	27
6	65	52	44	38	60	49	42	36	44	38	33	38	33	30	33	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24	21
8	55	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9590	9590	9590
5°	9634	9502	9568
10°	9570	9419	9477
15°	9458	9313	9331
20°	9328	9160	9170
25°	9152	8980	8961
30°	8959	8779	8712
35°	8757	8566	8456
40°	8546	8331	8202
45°	8315	8115	7917
50°	8081	7850	7633
55°	7777	7576	7345
60°	7470	7255	7025
65°	7200	6907	6691
70°	6798	6508	6219
75°	6213	5989	5735
80°	5604	5368	5318
85°	4915	4730	4545



TEST NUMBER: P331916

CATALOG NUMBER: S123DIP-S560D365U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.9	2.2
10°-20°	237.0	6.3
20°-30°	350.0	9.3
30°-40°	408.9	10.8
40°-50°	411.1	10.9
50°-60°	361.1	9.6
60°-70°	269.0	7.1
70°-80°	153.3	4.1
80°-90°	45.3	1.2
90°-100°	17.3	0.5
100°-110°	82.4	2.2
110°-120°	198.0	5.3
120°-130°	252.1	6.7
130°-140°	269.3	7.1
140°-150°	251.9	6.7
150°-160°	203.2	5.4
160°-170°	131.1	3.5
170°-180°	45.2	1.2
0°-30°	670.9	17.8
0°-40°	1079.8	28.6
0°-60°	1851.9	49.1
0°-90°	2319.5	61.5
90°-120°	297.7	7.9
90°-150°	1071.0	28.4
90°-180°	1450.0	38.5
0°-180°	3770.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	891	891	891	891	891	
5°	892	888	879	887	886	84
15°	849	845	836	841	837	239
25°	771	766	756	757	754	355
35°	666	662	652	647	644	417
45°	546	543	533	524	520	421
55°	414	413	404	396	391	371
65°	283	279	271	265	263	279
75°	149	146	144	140	138	160
85°	40	38	38	37	37	44
90°	0	4	8	10	11	3
95°	22	8	11	13	13	27
105°	105	107	77	18	16	112
115°	198	200	203	206	208	195
125°	278	281	283	283	284	249
135°	347	349	350	351	350	267
145°	400	402	403	404	404	250
155°	441	440	440	442	440	203
165°	465	464	463	466	464	131
175°	476	474	474	476	474	45
180°	476	476	476	476	476	



TEST NUMBER: P331916

CATALOG NUMBER: S123DIP-S560D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9
2.5°	893.9	893.4	892.9	892.3	891.8	890.7	889.2	887.7	886.3	884.8	886.1
5°	891.6	890.8	889.9	889.1	888.2	886.9	885.0	883.1	881.3	879.4	881.1
7.5°	882.9	882.1	881.2	880.4	879.5	878.1	876.2	874.2	872.3	870.4	871.9
10°	875.6	874.7	873.9	873.0	872.2	870.6	868.4	866.2	864.0	861.8	863.3
12.5°	865.8	865.0	864.3	863.6	862.9	861.5	859.4	857.3	855.3	853.2	854.3
15°	848.7	848.1	847.4	846.7	846.0	844.6	842.4	840.2	837.9	835.7	837.1
17.5°	829.0	828.1	827.2	826.3	825.4	823.9	821.7	819.5	817.3	815.0	816.0
20°	814.3	813.3	812.2	811.2	810.2	808.6	806.4	804.2	801.9	799.7	800.4
22.5°	797.7	796.7	795.7	794.7	793.6	792.0	789.8	787.6	785.4	783.2	783.7
25°	770.6	769.6	768.6	767.6	766.5	764.9	762.7	760.5	758.3	756.1	756.2
27.5°	741.7	740.7	739.7	738.7	737.7	736.0	733.6	731.3	728.9	726.5	726.6
30°	720.8	720.0	719.1	718.3	717.4	715.8	713.4	711.0	708.7	706.3	706.3
32.5°	700.0	698.9	697.7	696.6	695.5	694.0	692.2	690.3	688.5	686.7	685.7
35°	666.4	665.4	664.4	663.4	662.4	660.7	658.5	656.3	654.1	651.9	650.9
37.5°	632.1	630.8	629.5	628.2	626.9	625.2	622.9	620.7	618.4	616.2	615.0
40°	608.2	607.2	606.2	605.2	604.1	602.4	600.0	597.7	595.3	592.9	591.5
42.5°	584.3	583.2	582.0	580.8	579.7	577.9	575.5	573.2	570.8	568.4	567.0
45°	546.2	545.5	544.8	544.1	543.4	542.0	539.8	537.6	535.4	533.1	531.1
47.5°	508.3	507.3	506.4	505.4	504.4	502.8	500.8	498.7	496.6	494.5	492.5
50°	482.6	481.7	480.9	480.0	479.2	477.7	475.4	473.2	471.0	468.8	466.9
52.5°	455.6	455.0	454.5	453.9	453.3	451.8	449.5	447.2	444.8	442.5	440.9
55°	414.4	414.2	414.1	413.9	413.7	412.5	410.3	408.1	405.9	403.7	401.8
57.5°	375.2	374.6	374.0	373.5	372.9	371.7	369.9	368.2	366.4	364.6	363.0
60°	347.0	346.8	346.7	346.5	346.3	345.2	343.2	341.1	339.1	337.0	335.5
62.5°	321.9	321.4	321.0	320.6	320.1	318.9	316.8	314.8	312.7	310.7	309.2
65°	282.7	281.8	281.0	280.1	279.3	278.0	276.3	274.6	272.9	271.2	269.8
67.5°	241.1	240.4	239.6	238.9	238.1	237.1	235.8	234.5	233.2	232.0	230.8
70°	216.0	215.0	214.0	213.0	211.9	210.9	209.9	208.9	207.8	206.8	205.6
72.5°	189.7	188.9	188.2	187.4	186.7	185.7	184.6	183.4	182.2	181.1	180.0
75°	149.4	148.7	148.0	147.3	146.7	146.1	145.5	145.0	144.5	144.0	143.2
77.5°	113.7	113.3	112.9	112.6	112.2	111.7	111.1	110.5	109.8	109.2	108.7
80°	90.4	89.9	89.4	88.9	88.3	87.9	87.6	87.2	86.9	86.6	86.4
82.5°	67.7	67.6	67.5	67.4	67.3	67.2	67.2	67.1	67.0	67.0	66.6
85°	39.8	39.5	39.2	38.8	38.5	38.3	38.3	38.3	38.3	38.3	38.0
87.5°	16.0	15.8	15.5	15.2	15.0	14.9	15.0	15.0	15.1	15.2	15.1
90°	0.4	1.1	1.9	2.7	3.5	4.4	5.4	6.4	7.5	8.5	8.8
92.5°	6.6	6.4	6.1	5.9	5.7	6.0	6.7	7.5	8.3	9.0	9.5
95°	21.6	18.3	15.1	11.9	8.7	7.5	8.4	9.2	10.1	11.0	11.5
97.5°	43.3	41.9	40.4	39.0	37.5	34.0	28.3	22.7	17.0	11.4	12.0
100°	59.7	61.3	62.9	64.4	66.0	60.7	48.4	36.2	23.9	11.7	12.3
102.5°	78.4	79.5	80.6	81.8	82.9	76.8	63.4	50.0	36.6	23.3	21.3
105°	105.3	106.2	107.0	107.9	108.8	105.7	98.6	91.5	84.5	77.4	63.5
107.5°	133.7	134.4	135.1	135.8	136.5	137.4	138.5	139.6	140.7	141.8	131.6
110°	152.7	153.3	153.9	154.5	155.2	155.9	156.8	157.6	158.5	159.4	156.8



TEST NUMBER: P331916

CATALOG NUMBER: S123DIP-S560D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	170.7	171.3	171.9	172.4	173.0	173.7	174.6	175.5	176.3	177.2	177.2
115°	197.5	198.0	198.5	198.9	199.4	200.0	200.7	201.4	202.1	202.8	203.6
117.5°	223.5	224.1	224.6	225.2	225.8	226.3	226.6	227.0	227.4	227.7	228.3
120°	239.6	240.3	241.0	241.7	242.4	242.9	243.1	243.4	243.6	243.8	244.5
122.5°	256.0	256.6	257.1	257.7	258.3	258.7	259.0	259.3	259.6	259.9	260.4
125°	278.5	279.1	279.7	280.3	281.0	281.4	281.8	282.1	282.4	282.7	282.9
127.5°	300.2	300.9	301.5	302.1	302.7	303.2	303.6	304.0	304.4	304.7	305.0
130°	313.8	314.4	315.0	315.7	316.3	316.8	317.1	317.4	317.7	318.0	318.3
132.5°	326.8	327.4	328.1	328.7	329.3	329.7	330.0	330.3	330.5	330.8	331.1
135°	346.7	347.1	347.6	348.1	348.5	348.9	349.2	349.6	349.9	350.2	350.4
137.5°	363.6	364.2	364.8	365.4	366.0	366.4	366.6	366.7	366.9	367.1	367.5
140°	374.9	375.4	375.9	376.3	376.8	377.2	377.4	377.6	377.9	378.1	378.4
142.5°	385.4	385.9	386.3	386.8	387.3	387.6	387.9	388.1	388.3	388.6	388.8
145°	400.0	400.6	401.1	401.7	402.2	402.6	402.7	402.9	403.0	403.2	403.4
147.5°	413.8	414.2	414.5	414.9	415.2	415.5	415.7	415.8	416.0	416.1	416.3
150°	422.3	422.5	422.7	423.0	423.2	423.4	423.6	423.7	423.9	424.0	424.2
152.5°	429.9	430.0	430.1	430.2	430.3	430.5	430.5	430.6	430.7	430.8	431.1
155°	440.7	440.5	440.3	440.2	440.0	440.0	440.1	440.1	440.2	440.3	440.7
157.5°	449.0	449.0	449.0	448.9	448.9	448.9	448.8	448.7	448.6	448.6	449.0
160°	454.1	454.0	453.9	453.8	453.8	453.7	453.6	453.5	453.5	453.4	453.8
162.5°	458.9	458.7	458.5	458.3	458.1	457.9	457.8	457.8	457.7	457.6	458.1
165°	464.7	464.4	464.2	464.0	463.7	463.6	463.5	463.4	463.3	463.3	463.9
167.5°	469.2	468.9	468.6	468.3	467.9	467.8	467.8	467.8	467.8	467.8	468.4
170°	471.7	471.4	471.1	470.8	470.5	470.3	470.3	470.3	470.3	470.3	471.0
172.5°	473.4	473.1	472.7	472.3	471.9	471.8	471.8	471.9	472.0	472.0	472.7
175°	475.6	475.2	474.8	474.5	474.1	473.9	474.0	474.1	474.1	474.2	474.8
177.5°	476.2	475.9	475.6	475.3	474.9	474.8	474.9	474.9	475.0	475.1	475.6
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6



TEST NUMBER: P331916

CATALOG NUMBER: S123DIP-S560D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9
2.5°	887.5	888.8	890.2	890.8	890.7	890.5	890.4	890.3
5°	882.8	884.5	886.2	886.9	886.5	886.2	885.9	885.5
7.5°	873.4	874.9	876.5	877.1	876.9	876.7	876.5	876.3
10°	864.8	866.4	867.9	868.5	868.2	867.8	867.5	867.1
12.5°	855.4	856.6	857.7	858.1	857.9	857.7	857.5	857.3
15°	838.5	839.8	841.2	841.3	840.3	839.3	838.3	837.3
17.5°	817.0	817.9	818.9	819.1	818.8	818.4	818.0	817.6
20°	801.1	801.8	802.4	802.5	802.0	801.5	801.0	800.5
22.5°	784.3	784.8	785.4	785.3	784.7	784.0	783.4	782.7
25°	756.4	756.6	756.7	756.6	756.1	755.6	755.0	754.5
27.5°	726.8	726.9	727.0	726.8	726.1	725.5	724.8	724.2
30°	706.3	706.3	706.3	705.7	704.5	703.3	702.1	700.9
32.5°	684.8	683.8	682.8	682.0	681.4	680.8	680.1	679.5
35°	649.8	648.8	647.8	646.9	646.0	645.2	644.3	643.5
37.5°	613.7	612.5	611.3	610.4	609.9	609.3	608.8	608.2
40°	590.2	588.8	587.5	586.4	585.7	585.1	584.4	583.7
42.5°	565.7	564.3	562.9	561.9	561.2	560.6	559.9	559.2
45°	529.1	527.0	525.0	523.5	522.7	521.8	521.0	520.1
47.5°	490.5	488.5	486.5	485.1	484.4	483.6	482.9	482.1
50°	465.1	463.2	461.3	459.9	458.8	457.8	456.8	455.8
52.5°	439.3	437.7	436.1	434.7	433.7	432.7	431.7	430.7
55°	399.9	398.1	396.2	394.8	394.0	393.1	392.3	391.4
57.5°	361.3	359.6	358.0	356.6	355.6	354.7	353.7	352.7
60°	334.0	332.5	330.9	329.7	328.9	328.0	327.2	326.3
62.5°	307.6	306.1	304.6	303.5	302.9	302.4	301.8	301.2
65°	268.4	267.1	265.7	264.8	264.3	263.8	263.3	262.7
67.5°	229.6	228.4	227.2	226.2	225.5	224.8	224.1	223.4
70°	204.4	203.3	202.1	201.0	200.2	199.3	198.5	197.6
72.5°	179.0	177.9	176.9	176.1	175.7	175.2	174.8	174.3
75°	142.3	141.5	140.6	139.9	139.4	138.9	138.4	137.9
77.5°	108.1	107.5	106.9	106.6	106.6	106.6	106.6	106.6
80°	86.2	86.0	85.9	85.8	85.8	85.8	85.8	85.8
82.5°	66.3	66.0	65.7	65.5	65.4	65.2	65.1	65.0
85°	37.6	37.3	36.9	36.8	36.8	36.8	36.8	36.8
87.5°	15.0	15.0	14.9	14.9	14.9	14.9	15.0	15.0
90°	9.1	9.4	9.7	10.0	10.1	10.3	10.4	10.6
92.5°	10.1	10.6	11.1	11.4	11.4	11.5	11.6	11.7
95°	12.1	12.6	13.2	13.4	13.4	13.4	13.4	13.4
97.5°	12.6	13.3	13.9	14.2	14.3	14.4	14.5	14.6
100°	12.9	13.5	14.2	14.5	14.6	14.7	14.8	14.8
102.5°	19.4	17.4	15.5	14.6	14.7	14.8	15.0	15.1
105°	49.6	35.7	21.8	14.9	15.1	15.2	15.4	15.5
107.5°	121.5	111.3	101.1	90.7	80.3	69.8	59.3	48.8
110°	154.2	151.6	149.0	142.1	130.9	119.6	108.4	97.2



TEST NUMBER: P331916

CATALOG NUMBER: S123DIP-S560D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	177.3	177.3	177.4	176.2	173.8	171.5	169.1	166.7
115°	204.4	205.2	206.0	206.5	206.8	207.2	207.5	207.8
117.5°	229.0	229.6	230.2	230.6	230.6	230.7	230.8	230.8
120°	245.1	245.7	246.3	246.7	246.7	246.7	246.7	246.7
122.5°	260.8	261.3	261.7	261.9	262.0	262.1	262.1	262.2
125°	283.0	283.2	283.3	283.5	283.6	283.8	284.0	284.1
127.5°	305.2	305.5	305.8	305.8	305.6	305.5	305.3	305.2
130°	318.7	319.0	319.3	319.4	319.2	319.1	318.9	318.7
132.5°	331.4	331.7	332.0	332.1	331.8	331.6	331.4	331.2
135°	350.7	350.9	351.1	351.1	350.9	350.7	350.4	350.2
137.5°	367.8	368.2	368.6	368.7	368.5	368.4	368.2	368.1
140°	378.7	379.0	379.4	379.4	379.3	379.1	379.0	378.8
142.5°	389.1	389.3	389.6	389.6	389.4	389.1	388.9	388.7
145°	403.5	403.7	403.8	403.9	403.9	403.9	403.9	403.9
147.5°	416.4	416.6	416.8	416.7	416.3	415.9	415.6	415.2
150°	424.4	424.5	424.7	424.6	424.4	424.2	423.9	423.7
152.5°	431.4	431.7	432.0	431.9	431.6	431.2	430.8	430.5
155°	441.1	441.5	441.9	441.8	441.4	440.9	440.4	439.9
157.5°	449.5	450.0	450.5	450.4	449.8	449.2	448.5	447.9
160°	454.3	454.8	455.3	455.2	454.7	454.1	453.6	453.0
162.5°	458.7	459.2	459.7	459.8	459.3	458.8	458.3	457.8
165°	464.5	465.2	465.8	465.8	465.3	464.7	464.2	463.6
167.5°	469.0	469.7	470.3	470.3	469.7	469.0	468.4	467.8
170°	471.6	472.2	472.8	472.8	472.2	471.6	471.0	470.3
172.5°	473.3	473.9	474.5	474.5	473.8	473.1	472.4	471.7
175°	475.3	475.9	476.4	476.4	475.8	475.1	474.5	473.9
177.5°	476.1	476.6	477.1	477.0	476.4	475.8	475.1	474.5
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6

(END OF REPORT)