

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331917

Luminaire Tested: **S123DIP-S560D365U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331917
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D365U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3565.9 lumens
Efficiency: N/A
Efficacy: 129.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331917

CATALOG NUMBER: S123DIP-S560D365U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331917

CATALOG NUMBER: S123DIP-S560D365U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65
1	101	97	93	89	95	91	87	84	80	78	75	71	69	67	62	60	59	55
2	92	84	78	73	86	80	74	69	70	66	62	62	59	56	54	52	50	46
3	84	74	67	61	79	70	63	58	62	57	52	55	51	47	48	45	42	39
4	77	66	58	51	72	62	55	49	55	49	45	49	44	40	43	39	36	33
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	39	35	32	29
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28	25
7	60	48	39	34	56	45	38	32	41	34	30	36	31	27	32	28	25	22
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9590	9590	9590
5°	9634	9502	9568
10°	9570	9419	9477
15°	9458	9313	9331
20°	9328	9160	9170
25°	9152	8980	8961
30°	8959	8779	8712
35°	8757	8566	8456
40°	8546	8331	8202
45°	8315	8115	7917
50°	8081	7850	7633
55°	7777	7576	7345
60°	7470	7255	7025
65°	7200	6907	6691
70°	6798	6508	6219
75°	6213	5989	5735
80°	5604	5368	5318
85°	4915	4730	4545



TEST NUMBER: P331917

CATALOG NUMBER: S123DIP-S560D365U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.9	2.4
10°-20°	237.0	6.6
20°-30°	350.0	9.8
30°-40°	408.9	11.5
40°-50°	411.1	11.5
50°-60°	361.1	10.1
60°-70°	269.0	7.5
70°-80°	153.3	4.3
80°-90°	45.3	1.3
90°-100°	29.3	0.8
100°-110°	87.7	2.5
110°-120°	149.2	4.2
120°-130°	196.2	5.5
130°-140°	220.6	6.2
140°-150°	216.8	6.1
150°-160°	182.5	5.1
160°-170°	121.5	3.4
170°-180°	42.5	1.2
0°-30°	670.9	18.8
0°-40°	1079.8	30.3
0°-60°	1851.9	51.9
0°-90°	2319.5	65.0
90°-120°	266.2	7.5
90°-150°	899.9	25.2
90°-180°	1246.0	34.9
0°-180°	3565.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	891	891	891	891	891	
5°	892	888	879	887	886	84
15°	849	845	836	841	837	239
25°	771	766	756	757	754	355
35°	666	662	652	647	644	417
45°	546	543	533	524	520	421
55°	414	413	404	396	391	371
65°	283	279	271	265	263	279
75°	149	146	144	140	138	160
85°	40	38	38	37	37	44
90°	0	4	8	10	11	3
95°	21	23	26	28	28	23
105°	80	80	83	83	84	85
115°	150	151	150	151	150	149
125°	220	221	220	219	217	196
135°	285	287	287	286	285	220
145°	346	347	348	347	346	216
155°	396	396	396	398	395	182
165°	432	430	430	432	430	122
175°	449	448	447	449	447	43
180°	450	450	450	450	450	



TEST NUMBER: P331917

CATALOG NUMBER: S123DIP-S560D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9
2.5°	893.9	893.4	892.9	892.3	891.8	890.7	889.2	887.7	886.3	884.8	886.1
5°	891.6	890.8	889.9	889.1	888.2	886.9	885.0	883.1	881.3	879.4	881.1
7.5°	882.9	882.1	881.2	880.4	879.5	878.1	876.2	874.2	872.3	870.4	871.9
10°	875.6	874.7	873.9	873.0	872.2	870.6	868.4	866.2	864.0	861.8	863.3
12.5°	865.8	865.0	864.3	863.6	862.9	861.5	859.4	857.3	855.3	853.2	854.3
15°	848.7	848.1	847.4	846.7	846.0	844.6	842.4	840.2	837.9	835.7	837.1
17.5°	829.0	828.1	827.2	826.3	825.4	823.9	821.7	819.5	817.3	815.0	816.0
20°	814.3	813.3	812.2	811.2	810.2	808.6	806.4	804.2	801.9	799.7	800.4
22.5°	797.7	796.7	795.7	794.7	793.6	792.0	789.8	787.6	785.4	783.2	783.7
25°	770.6	769.6	768.6	767.6	766.5	764.9	762.7	760.5	758.3	756.1	756.2
27.5°	741.7	740.7	739.7	738.7	737.7	736.0	733.6	731.3	728.9	726.5	726.6
30°	720.8	720.0	719.1	718.3	717.4	715.8	713.4	711.0	708.7	706.3	706.3
32.5°	700.0	698.9	697.7	696.6	695.5	694.0	692.2	690.3	688.5	686.7	685.7
35°	666.4	665.4	664.4	663.4	662.4	660.7	658.5	656.3	654.1	651.9	650.9
37.5°	632.1	630.8	629.5	628.2	626.9	625.2	622.9	620.7	618.4	616.2	615.0
40°	608.2	607.2	606.2	605.2	604.1	602.4	600.0	597.7	595.3	592.9	591.5
42.5°	584.3	583.2	582.0	580.8	579.7	577.9	575.5	573.2	570.8	568.4	567.0
45°	546.2	545.5	544.8	544.1	543.4	542.0	539.8	537.6	535.4	533.1	531.1
47.5°	508.3	507.3	506.4	505.4	504.4	502.8	500.8	498.7	496.6	494.5	492.5
50°	482.6	481.7	480.9	480.0	479.2	477.7	475.4	473.2	471.0	468.8	466.9
52.5°	455.6	455.0	454.5	453.9	453.3	451.8	449.5	447.2	444.8	442.5	440.9
55°	414.4	414.2	414.1	413.9	413.7	412.5	410.3	408.1	405.9	403.7	401.8
57.5°	375.2	374.6	374.0	373.5	372.9	371.7	369.9	368.2	366.4	364.6	363.0
60°	347.0	346.8	346.7	346.5	346.3	345.2	343.2	341.1	339.1	337.0	335.5
62.5°	321.9	321.4	321.0	320.6	320.1	318.9	316.8	314.8	312.7	310.7	309.2
65°	282.7	281.8	281.0	280.1	279.3	278.0	276.3	274.6	272.9	271.2	269.8
67.5°	241.1	240.4	239.6	238.9	238.1	237.1	235.8	234.5	233.2	232.0	230.8
70°	216.0	215.0	214.0	213.0	211.9	210.9	209.9	208.9	207.8	206.8	205.6
72.5°	189.7	188.9	188.2	187.4	186.7	185.7	184.6	183.4	182.2	181.1	180.0
75°	149.4	148.7	148.0	147.3	146.7	146.1	145.5	145.0	144.5	144.0	143.2
77.5°	113.7	113.3	112.9	112.6	112.2	111.7	111.1	110.5	109.8	109.2	108.7
80°	90.4	89.9	89.4	88.9	88.3	87.9	87.6	87.2	86.9	86.6	86.4
82.5°	67.7	67.6	67.5	67.4	67.3	67.2	67.2	67.1	67.0	67.0	66.6
85°	39.8	39.5	39.2	38.8	38.5	38.3	38.3	38.3	38.3	38.3	38.0
87.5°	16.0	15.8	15.5	15.2	15.0	14.9	15.0	15.0	15.1	15.2	15.1
90°	0.4	1.1	1.9	2.7	3.5	4.4	5.4	6.4	7.5	8.5	8.8
92.5°	8.6	9.1	9.6	10.2	10.7	11.2	11.8	12.4	13.0	13.6	13.8
95°	20.9	21.4	21.9	22.5	23.0	23.6	24.3	24.9	25.5	26.2	26.5
97.5°	37.0	37.4	37.9	38.3	38.7	39.1	39.6	40.0	40.5	40.9	41.3
100°	48.1	48.5	49.0	49.5	49.9	50.4	50.8	51.2	51.6	51.9	52.2
102.5°	60.8	61.1	61.3	61.6	61.9	62.3	62.8	63.4	63.9	64.4	64.6
105°	79.5	79.7	79.8	80.0	80.1	80.6	81.3	82.0	82.7	83.4	83.4
107.5°	101.3	101.4	101.5	101.6	101.7	101.8	102.1	102.4	102.7	103.0	103.2
110°	114.9	115.0	115.2	115.3	115.5	115.6	115.8	116.0	116.1	116.3	116.6



TEST NUMBER: P331917

CATALOG NUMBER: S123DIP-S560D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	129.0	129.1	129.2	129.3	129.4	129.4	129.5	129.5	129.5	129.6	129.9
115°	150.2	150.4	150.7	150.9	151.1	151.2	151.0	150.9	150.7	150.5	150.6
117.5°	171.5	171.7	171.9	172.0	172.2	172.1	171.9	171.7	171.5	171.3	171.3
120°	184.8	185.3	185.8	186.2	186.7	186.7	186.4	186.0	185.6	185.2	185.1
122.5°	198.7	199.0	199.4	199.7	200.1	200.1	199.9	199.7	199.5	199.3	199.1
125°	219.8	220.0	220.3	220.5	220.8	220.8	220.6	220.5	220.3	220.2	219.8
127.5°	239.3	239.8	240.3	240.8	241.3	241.5	241.3	241.1	241.0	240.8	240.4
130°	252.3	252.9	253.6	254.2	254.8	255.0	254.8	254.6	254.3	254.1	253.8
132.5°	265.3	266.0	266.6	267.2	267.8	268.1	267.9	267.7	267.5	267.4	267.0
135°	285.2	285.7	286.1	286.6	287.1	287.3	287.2	287.1	287.0	287.0	286.6
137.5°	303.6	304.0	304.3	304.7	305.1	305.4	305.6	305.8	306.0	306.2	305.9
140°	316.3	316.7	317.1	317.5	317.9	318.1	318.2	318.2	318.3	318.4	318.3
142.5°	327.9	328.3	328.7	329.1	329.4	329.7	329.9	330.0	330.1	330.3	330.2
145°	346.0	346.1	346.3	346.4	346.6	346.8	347.0	347.3	347.5	347.7	347.7
147.5°	361.8	362.1	362.4	362.7	362.9	363.2	363.4	363.6	363.8	364.1	364.1
150°	372.8	373.0	373.1	373.3	373.5	373.6	373.8	373.9	374.1	374.2	374.2
152.5°	381.9	382.1	382.3	382.5	382.8	382.9	383.0	383.1	383.2	383.3	383.4
155°	396.2	396.2	396.2	396.2	396.2	396.2	396.3	396.3	396.4	396.5	396.8
157.5°	408.3	408.2	408.1	408.0	407.9	407.9	408.0	408.0	408.1	408.2	408.5
160°	415.9	415.8	415.6	415.5	415.3	415.2	415.2	415.2	415.2	415.2	415.6
162.5°	422.7	422.5	422.3	422.1	421.8	421.8	421.8	421.9	422.0	422.0	422.4
165°	431.5	431.3	431.0	430.8	430.5	430.4	430.4	430.4	430.4	430.4	430.9
167.5°	438.5	438.2	437.9	437.5	437.2	437.1	437.2	437.2	437.3	437.4	437.8
170°	442.4	442.1	441.8	441.5	441.2	441.0	441.0	441.0	441.0	441.0	441.6
172.5°	445.6	445.2	444.9	444.6	444.3	444.1	444.1	444.1	444.1	444.1	444.6
175°	448.8	448.5	448.2	447.9	447.6	447.4	447.4	447.4	447.4	447.4	447.9
177.5°	450.1	449.9	449.6	449.4	449.1	449.0	449.0	449.0	449.0	449.0	449.4
180°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9



TEST NUMBER: P331917

CATALOG NUMBER: S123DIP-S560D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9
2.5°	887.5	888.8	890.2	890.8	890.7	890.5	890.4	890.3
5°	882.8	884.5	886.2	886.9	886.5	886.2	885.9	885.5
7.5°	873.4	874.9	876.5	877.1	876.9	876.7	876.5	876.3
10°	864.8	866.4	867.9	868.5	868.2	867.8	867.5	867.1
12.5°	855.4	856.6	857.7	858.1	857.9	857.7	857.5	857.3
15°	838.5	839.8	841.2	841.3	840.3	839.3	838.3	837.3
17.5°	817.0	817.9	818.9	819.1	818.8	818.4	818.0	817.6
20°	801.1	801.8	802.4	802.5	802.0	801.5	801.0	800.5
22.5°	784.3	784.8	785.4	785.3	784.7	784.0	783.4	782.7
25°	756.4	756.6	756.7	756.6	756.1	755.6	755.0	754.5
27.5°	726.8	726.9	727.0	726.8	726.1	725.5	724.8	724.2
30°	706.3	706.3	706.3	705.7	704.5	703.3	702.1	700.9
32.5°	684.8	683.8	682.8	682.0	681.4	680.8	680.1	679.5
35°	649.8	648.8	647.8	646.9	646.0	645.2	644.3	643.5
37.5°	613.7	612.5	611.3	610.4	609.9	609.3	608.8	608.2
40°	590.2	588.8	587.5	586.4	585.7	585.1	584.4	583.7
42.5°	565.7	564.3	562.9	561.9	561.2	560.6	559.9	559.2
45°	529.1	527.0	525.0	523.5	522.7	521.8	521.0	520.1
47.5°	490.5	488.5	486.5	485.1	484.4	483.6	482.9	482.1
50°	465.1	463.2	461.3	459.9	458.8	457.8	456.8	455.8
52.5°	439.3	437.7	436.1	434.7	433.7	432.7	431.7	430.7
55°	399.9	398.1	396.2	394.8	394.0	393.1	392.3	391.4
57.5°	361.3	359.6	358.0	356.6	355.6	354.7	353.7	352.7
60°	334.0	332.5	330.9	329.7	328.9	328.0	327.2	326.3
62.5°	307.6	306.1	304.6	303.5	302.9	302.4	301.8	301.2
65°	268.4	267.1	265.7	264.8	264.3	263.8	263.3	262.7
67.5°	229.6	228.4	227.2	226.2	225.5	224.8	224.1	223.4
70°	204.4	203.3	202.1	201.0	200.2	199.3	198.5	197.6
72.5°	179.0	177.9	176.9	176.1	175.7	175.2	174.8	174.3
75°	142.3	141.5	140.6	139.9	139.4	138.9	138.4	137.9
77.5°	108.1	107.5	106.9	106.6	106.6	106.6	106.6	106.6
80°	86.2	86.0	85.9	85.8	85.8	85.8	85.8	85.8
82.5°	66.3	66.0	65.7	65.5	65.4	65.2	65.1	65.0
85°	37.6	37.3	36.9	36.8	36.8	36.8	36.8	36.8
87.5°	15.0	15.0	14.9	14.9	14.9	14.9	15.0	15.0
90°	9.1	9.4	9.7	10.0	10.1	10.3	10.4	10.6
92.5°	14.1	14.3	14.6	14.7	14.6	14.5	14.4	14.3
95°	26.8	27.1	27.4	27.6	27.6	27.6	27.6	27.6
97.5°	41.6	42.0	42.4	42.5	42.5	42.5	42.4	42.4
100°	52.4	52.7	52.9	53.1	53.2	53.4	53.6	53.7
102.5°	64.9	65.1	65.3	65.4	65.4	65.4	65.3	65.3
105°	83.4	83.4	83.4	83.5	83.6	83.8	84.0	84.1
107.5°	103.5	103.7	104.0	104.1	104.0	103.9	103.8	103.7
110°	116.9	117.2	117.5	117.6	117.4	117.3	117.1	117.0



TEST NUMBER: P331917

CATALOG NUMBER: S123DIP-S560D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	130.3	130.7	131.1	131.2	131.2	131.2	131.1	131.1
115°	150.7	150.8	150.9	150.9	150.8	150.7	150.6	150.5
117.5°	171.3	171.3	171.3	171.1	170.9	170.7	170.5	170.3
120°	185.0	184.9	184.9	184.7	184.6	184.4	184.3	184.1
122.5°	198.9	198.7	198.5	198.3	198.1	197.8	197.6	197.4
125°	219.5	219.2	218.9	218.6	218.3	218.0	217.6	217.3
127.5°	239.9	239.5	239.0	238.6	238.3	237.9	237.6	237.2
130°	253.5	253.1	252.8	252.4	251.9	251.3	250.8	250.2
132.5°	266.6	266.2	265.9	265.5	265.0	264.6	264.2	263.8
135°	286.3	286.0	285.7	285.5	285.3	285.1	285.0	284.8
137.5°	305.6	305.3	304.9	304.6	304.3	304.0	303.7	303.4
140°	318.2	318.2	318.1	317.8	317.2	316.7	316.1	315.6
142.5°	330.1	330.0	330.0	329.7	329.3	328.9	328.4	328.0
145°	347.6	347.5	347.4	347.2	346.9	346.6	346.3	346.0
147.5°	364.1	364.1	364.1	363.8	363.4	362.9	362.4	361.9
150°	374.2	374.2	374.2	374.0	373.5	373.1	372.6	372.1
152.5°	383.5	383.7	383.8	383.6	383.2	382.8	382.4	382.0
155°	397.1	397.4	397.8	397.6	397.1	396.5	396.0	395.4
157.5°	408.8	409.2	409.5	409.4	409.0	408.6	408.1	407.7
160°	416.0	416.4	416.8	416.8	416.5	416.2	415.9	415.6
162.5°	422.8	423.2	423.6	423.5	423.0	422.5	422.0	421.5
165°	431.4	431.8	432.3	432.3	431.7	431.2	430.6	430.1
167.5°	438.3	438.8	439.3	439.3	438.8	438.3	437.8	437.4
170°	442.1	442.7	443.2	443.2	442.7	442.1	441.6	441.0
172.5°	445.1	445.6	446.1	446.1	445.5	445.0	444.4	443.9
175°	448.3	448.8	449.3	449.2	448.7	448.1	447.6	447.0
177.5°	449.8	450.1	450.5	450.5	450.1	449.6	449.2	448.7
180°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9

(END OF REPORT)