

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831507

Luminaire Tested: S123DIP-S560D365U835-4F0-1E-UDD-G

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P831507  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S560D365U835-4F0-1E-UDD-G  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4045.6 lumens  
Efficiency: N/A  
Efficacy: 136.7 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 29.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P831507

CATALOG NUMBER: S123DIP-S560D365U835-4F0-1E-UDD-G

### Luminous Intensity Polar Plot





TEST NUMBER: P831507

CATALOG NUMBER: S123DIP-S560D365U835-4F0-1E-UDD-G

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64				
1	102	97	94	90	95	92	88	86	81	79	76	71	69	68	62	61	60	55				
2	93	86	80	75	87	81	76	71	72	68	64	63	60	58	56	53	51	48				
3	86	76	69	64	80	72	66	61	64	59	55	57	53	50	50	47	45	41				
4	79	68	60	55	74	65	58	52	58	52	48	51	47	44	45	42	39	36				
5	73	61	53	48	68	58	51	46	52	46	42	47	42	38	41	38	35	32				
6	67	56	48	42	63	53	46	40	47	42	37	43	38	34	38	34	31	29				
7	63	51	43	37	59	48	41	36	43	38	33	39	34	31	35	31	28	26				
8	58	46	39	34	55	44	37	32	40	34	30	36	31	28	32	29	26	24				
9	55	43	35	30	52	41	34	29	37	31	27	34	29	26	30	26	24	22				
10	51	40	32	28	49	38	31	27	34	29	25	31	27	23	28	24	22	20				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	17374	17374	17374	17374	17374
5°	21973	20738	17530	14126	12981
10°	22186	22857	17413	11261	9840
15°	16710	21222	17295	9536	8322
20°	11643	17172	17073	8339	7559
25°	8878	13206	16697	7672	7090
30°	7680	10491	16096	7201	6712
35°	7126	8858	15403	6861	6447
40°	6746	7946	14429	6535	6357
45°	6521	7354	13192	6282	6317
50°	6409	6886	11727	6052	6285
55°	6170	6544	10290	5833	6311
60°	5950	6176	8869	5627	6209
65°	5591	5827	7651	5407	6085
70°	5161	5385	6505	5045	5728
75°	4675	4828	5577	4687	5232
80°	3856	4228	4413	4085	4413
85°	3051	3421	3236	3470	3520

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 15061 cd/sqm



TEST NUMBER: P831507

CATALOG NUMBER: S123DIP-S560D365U835-4F0-1E-UDD-G

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	152.6	3.8
10°-20°	379.6	9.4
20°-30°	449.5	11.1
30°-40°	452.0	11.2
40°-50°	414.7	10.2
50°-60°	342.3	8.5
60°-70°	242.1	6.0
70°-80°	129.2	3.2
80°-90°	33.7	0.8
90°-100°	16.8	0.4
100°-110°	81.1	2.0
110°-120°	198.7	4.9
120°-130°	252.3	6.2
130°-140°	269.5	6.7
140°-150°	252.0	6.2
150°-160°	203.3	5.0
160°-170°	131.2	3.2
170°-180°	45.2	1.1
0°-30°	981.7	24.3
0°-40°	1433.7	35.4
0°-60°	2190.6	54.1
0°-90°	2595.7	64.2
90°-120°	296.5	7.3
90°-150°	1070.3	26.5
90°-180°	1450.0	35.8
0°-180°	4045.6	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1614	1614	1614	1614	1614	
5°	2034	1919	1622	1307	1201	194
15°	1500	1904	1552	856	747	414
25°	748	1112	1406	646	597	353
35°	542	674	1172	522	491	341
45°	428	483	867	413	415	332
55°	329	349	548	311	336	294
65°	220	229	300	212	239	218
75°	112	116	134	113	126	118
85°	25	28	26	28	28	28
90°	11	8	0	8	11	6
95°	13	11	22	11	13	11
105°	16	77	105	77	16	32
115°	208	203	198	203	208	195
125°	284	283	278	283	284	254
135°	350	350	347	350	350	270
145°	404	403	400	403	404	252
155°	440	440	441	440	440	203
165°	464	463	465	463	464	131
175°	474	474	476	474	474	45
180°	476	476	476	476	476	



TEST NUMBER: P831507

CATALOG NUMBER: S123DIP-S560D365U835-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1
2.5°	1819.3	1817.5	1815.6	1806.2	1796.9	1792.4	1787.9	1774.4	1760.9	1745.9	1731.0
5°	2033.6	2038.8	2044.1	2038.1	2032.1	2013.7	1995.4	1971.0	1946.7	1919.3	1892.0
7.5°	2132.4	2135.4	2138.4	2134.7	2130.9	2126.1	2121.2	2099.5	2077.8	2049.7	2021.6
10°	2029.8	2036.6	2043.3	2057.9	2072.5	2089.0	2105.5	2102.5	2099.5	2091.2	2083.0
12.5°	1804.4	1812.6	1820.8	1850.1	1879.3	1916.7	1954.2	1986.4	2018.6	2041.1	2063.5
15°	1499.5	1522.4	1545.2	1571.8	1598.4	1653.4	1708.5	1776.3	1844.1	1904.4	1964.7
17.5°	1235.1	1243.7	1252.3	1280.8	1309.3	1378.6	1447.8	1526.1	1604.4	1704.4	1804.4
20°	1016.4	1024.3	1032.1	1069.6	1107.0	1161.3	1215.6	1303.7	1391.7	1499.1	1606.6
22.5°	853.9	866.2	878.6	899.6	920.5	972.6	1024.6	1102.9	1181.2	1299.9	1418.6
25°	747.5	756.5	765.5	778.2	791.0	832.5	874.1	938.5	1002.9	1111.9	1220.9
27.5°	674.9	678.6	682.3	695.1	707.8	734.8	761.7	817.2	872.6	965.1	1057.6
30°	617.9	620.6	623.2	634.4	645.6	664.0	682.3	722.4	762.5	844.1	925.8
32.5°	578.2	580.1	582.0	590.6	599.2	612.3	625.4	654.6	683.8	751.3	818.7
35°	542.3	543.4	544.5	550.9	557.3	567.0	576.7	598.8	620.9	674.1	727.3
37.5°	510.8	512.3	513.8	517.6	521.3	529.9	538.5	556.1	573.7	614.6	655.4
40°	480.1	482.7	485.4	488.0	490.6	497.7	504.8	518.3	531.8	565.5	599.2
42.5°	453.9	456.5	459.1	460.3	461.4	465.5	469.6	482.0	494.3	519.4	544.5
45°	428.4	429.6	430.7	431.8	432.9	436.3	439.7	450.5	461.4	483.1	504.8
47.5°	405.2	405.2	405.2	406.0	406.7	409.7	412.7	420.6	428.4	445.3	462.1
50°	382.7	382.7	382.7	381.6	380.5	382.4	384.2	390.2	396.2	411.2	426.2
52.5°	355.8	355.8	355.8	356.2	356.5	356.5	356.5	361.8	367.0	380.5	394.0
55°	328.8	330.3	331.8	330.7	329.6	330.3	331.1	334.4	337.8	348.7	359.5
57.5°	301.9	302.6	303.3	303.0	302.6	303.0	303.3	306.3	309.3	317.6	325.8
60°	276.4	276.4	276.4	275.6	274.9	275.6	276.4	277.9	279.4	286.9	294.4
62.5°	247.9	248.3	248.7	249.0	249.4	248.7	247.9	249.8	251.7	257.3	262.9
65°	219.5	219.8	220.2	221.3	222.5	221.7	221.0	222.8	224.7	228.8	232.9
67.5°	194.0	193.2	192.5	192.9	193.2	194.4	195.5	195.9	196.2	200.7	205.2
70°	164.0	164.8	165.5	165.2	164.8	165.2	165.5	166.7	167.8	171.1	174.5
72.5°	137.1	137.4	137.8	137.8	137.8	138.6	139.3	140.4	141.6	143.4	145.3
75°	112.4	112.4	112.4	113.1	113.8	114.2	114.6	114.6	114.6	116.1	117.6
77.5°	85.4	87.3	89.1	88.8	88.4	89.1	89.9	91.0	92.1	92.9	93.6
80°	62.2	62.2	62.2	62.5	62.9	64.0	65.2	65.9	66.7	68.2	69.7
82.5°	39.7	40.1	40.4	41.6	42.7	43.4	44.2	45.3	46.4	46.4	46.4
85°	24.7	24.0	23.2	24.0	24.7	25.5	26.2	26.6	27.0	27.7	28.5
87.5°	12.0	12.0	12.0	12.0	12.0	12.4	12.7	12.7	12.7	12.7	12.7
90°	10.6	10.4	10.3	10.1	10.0	9.7	9.4	9.1	8.8	8.5	7.5
92.5°	12.0	11.9	11.9	11.8	11.7	11.4	10.8	10.3	9.7	9.2	8.5
95°	13.4	13.4	13.4	13.4	13.4	13.2	12.6	12.1	11.5	11.0	10.1
97.5°	14.5	14.4	14.3	14.3	14.2	13.8	13.2	12.6	11.9	11.3	15.3
100°	14.8	14.8	14.7	14.6	14.5	14.2	13.5	12.9	12.3	11.7	23.9
102.5°	15.2	15.0	14.9	14.7	14.6	15.8	18.4	21.0	23.6	26.1	39.8
105°	15.5	15.4	15.2	15.1	14.9	21.8	35.7	49.6	63.5	77.4	84.5
107.5°	36.8	47.0	57.3	67.6	77.9	89.1	101.2	113.3	125.4	137.5	136.3
110°	97.2	108.4	119.6	130.9	142.1	149.0	151.6	154.2	156.8	159.4	158.5



TEST NUMBER: P831507

CATALOG NUMBER: S123DIP-S560D365U835-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	184.1	184.3	184.4	184.6	184.7	184.5	183.8	183.0	182.3	181.6	180.8
115°	207.8	207.5	207.2	206.8	206.5	206.0	205.2	204.4	203.6	202.8	202.1
117.5°	226.9	226.8	226.7	226.6	226.5	226.2	225.6	224.9	224.3	223.7	223.3
120°	246.7	246.7	246.7	246.7	246.7	246.3	245.7	245.1	244.5	243.8	243.6
122.5°	266.1	266.0	265.9	265.9	265.8	265.5	265.1	264.8	264.4	264.0	263.7
125°	284.1	284.0	283.8	283.6	283.5	283.3	283.2	283.0	282.9	282.7	282.4
127.5°	301.8	301.9	302.1	302.2	302.4	302.4	302.1	301.9	301.7	301.4	301.0
130°	318.7	318.9	319.1	319.2	319.4	319.3	319.0	318.7	318.3	318.0	317.7
132.5°	334.3	334.5	334.8	335.0	335.2	335.2	334.9	334.6	334.2	333.9	333.7
135°	350.2	350.4	350.7	350.9	351.1	351.1	350.9	350.7	350.4	350.2	349.9
137.5°	365.4	365.5	365.7	365.9	366.0	365.9	365.5	365.1	364.7	364.3	364.2
140°	378.8	379.0	379.1	379.3	379.4	379.4	379.0	378.7	378.4	378.1	377.9
142.5°	391.2	391.4	391.7	391.9	392.1	392.1	391.9	391.7	391.4	391.2	390.9
145°	403.9	403.9	403.9	403.9	403.9	403.8	403.7	403.5	403.4	403.2	403.0
147.5°	413.1	413.5	413.9	414.3	414.7	414.8	414.6	414.5	414.3	414.1	414.0
150°	423.7	423.9	424.2	424.4	424.6	424.7	424.5	424.4	424.2	424.0	423.9
152.5°	432.2	432.6	433.0	433.3	433.7	433.8	433.5	433.2	432.8	432.5	432.4
155°	439.9	440.4	440.9	441.4	441.8	441.9	441.5	441.1	440.7	440.3	440.2
157.5°	446.7	447.3	447.9	448.5	449.2	449.3	448.8	448.3	447.8	447.4	447.4
160°	453.0	453.6	454.1	454.7	455.2	455.3	454.8	454.3	453.8	453.4	453.5
162.5°	459.0	459.5	460.0	460.4	460.9	460.9	460.3	459.8	459.2	458.7	458.8
165°	463.6	464.2	464.7	465.3	465.8	465.8	465.2	464.5	463.9	463.3	463.3
167.5°	467.2	467.8	468.4	469.0	469.7	469.7	469.0	468.4	467.8	467.2	467.2
170°	470.3	471.0	471.6	472.2	472.8	472.8	472.2	471.6	471.0	470.3	470.3
172.5°	472.1	472.8	473.5	474.2	474.9	475.0	474.3	473.7	473.1	472.5	472.4
175°	473.9	474.5	475.1	475.8	476.4	476.4	475.9	475.3	474.8	474.2	474.1
177.5°	474.2	475.0	475.8	476.6	477.4	477.4	476.8	476.2	475.6	474.9	474.8
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6



TEST NUMBER: P831507

CATALOG NUMBER: S123DIP-S560D365U835-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1
2.5°	1726.5	1722.0	1705.5	1689.0	1670.3	1651.6	1637.7	1623.9	1603.3	1582.7	1565.8
5°	1871.0	1850.1	1815.2	1780.4	1733.2	1686.0	1654.2	1622.4	1579.7	1537.0	1502.9
7.5°	1985.6	1949.7	1901.0	1852.3	1790.5	1728.7	1670.3	1611.9	1546.7	1481.5	1428.4
10°	2058.7	2034.3	1978.1	1922.0	1839.2	1756.4	1674.8	1593.1	1509.3	1425.4	1355.0
12.5°	2065.8	2068.0	2016.3	1964.7	1871.0	1777.4	1678.2	1578.9	1473.3	1367.7	1285.7
15°	2003.2	2041.8	2013.3	1984.9	1890.5	1796.1	1674.0	1552.0	1430.2	1308.5	1213.8
17.5°	1887.1	1969.9	1974.0	1978.1	1883.8	1789.4	1654.2	1519.0	1381.2	1243.4	1143.7
20°	1728.7	1850.8	1892.8	1934.7	1857.9	1781.2	1635.8	1490.5	1336.2	1181.9	1077.5
22.5°	1566.9	1715.2	1792.0	1868.8	1811.9	1754.9	1600.3	1445.6	1282.7	1119.8	1013.8
25°	1382.7	1544.5	1662.4	1780.4	1745.6	1710.7	1558.3	1405.9	1232.5	1059.1	950.9
27.5°	1222.0	1386.4	1528.7	1671.0	1663.6	1656.1	1504.8	1353.5	1175.9	998.4	893.9
30°	1079.0	1232.1	1391.3	1550.5	1568.8	1587.2	1441.1	1295.0	1117.2	939.3	838.5
32.5°	952.4	1086.1	1256.8	1427.6	1463.6	1499.5	1367.7	1235.9	1059.9	883.8	786.8
35°	848.6	970.0	1140.7	1311.5	1356.5	1401.4	1286.8	1172.2	1000.7	829.2	736.7
37.5°	756.9	858.4	1025.0	1191.7	1246.7	1301.8	1199.2	1096.6	935.9	775.2	690.2
40°	680.9	762.5	915.7	1068.8	1132.5	1196.2	1111.5	1026.9	874.5	722.0	643.8
42.5°	617.2	689.8	828.8	967.7	1028.8	1089.8	1018.3	946.8	811.2	675.6	604.1
45°	562.9	620.9	747.1	873.3	931.4	989.4	928.0	866.6	747.1	627.7	561.0
47.5°	511.9	561.8	669.6	777.5	829.2	880.8	832.9	785.0	683.8	582.7	522.4
50°	466.3	506.3	600.7	695.1	740.0	785.0	742.6	700.3	617.2	534.0	481.6
52.5°	426.6	459.1	538.2	617.2	655.8	694.3	658.0	621.7	555.8	489.9	444.2
55°	387.2	415.0	483.5	552.0	578.2	604.5	576.4	548.3	495.1	441.9	403.3
57.5°	350.5	375.3	431.4	487.6	507.8	528.1	502.6	477.1	437.0	397.0	364.8
60°	314.6	334.8	381.6	428.4	440.8	453.2	432.6	412.0	383.9	355.8	326.9
62.5°	281.3	299.6	334.4	369.3	377.5	385.7	370.0	354.3	332.9	311.6	289.1
65°	246.8	260.7	289.1	317.6	322.8	328.1	314.2	300.4	284.2	268.1	251.7
67.5°	215.0	224.7	247.9	271.1	271.5	271.9	260.7	249.4	240.4	231.4	218.3
70°	183.9	193.2	208.6	224.0	224.3	224.7	215.7	206.7	200.0	193.2	183.5
72.5°	152.0	158.8	170.4	182.0	181.3	180.5	174.9	169.3	164.0	158.8	151.7
75°	123.2	128.8	136.7	144.6	142.3	140.1	137.1	134.1	129.6	125.1	120.6
77.5°	97.0	100.4	104.9	109.4	107.9	106.4	103.7	101.1	97.7	94.4	92.5
80°	71.2	72.7	75.7	78.6	77.9	77.1	74.2	71.2	70.4	69.7	67.0
82.5°	48.3	50.2	50.9	51.7	51.3	50.9	48.7	46.4	45.7	44.9	44.6
85°	28.8	29.2	29.6	30.0	28.8	27.7	27.0	26.2	26.2	26.2	25.8
87.5°	13.1	13.5	13.5	13.5	13.1	12.7	12.0	11.2	11.6	12.0	12.0
90°	6.4	5.4	4.4	3.5	2.7	1.9	1.1	0.4	1.1	1.9	2.7
92.5°	7.8	7.1	6.4	6.2	6.7	7.2	7.7	8.1	7.7	7.2	6.7
95°	9.2	8.4	7.5	8.7	11.9	15.1	18.3	21.6	18.3	15.1	11.9
97.5°	19.3	23.3	27.3	30.4	32.6	34.8	37.0	39.2	37.0	34.8	32.6
100°	36.2	48.4	60.7	66.0	64.4	62.9	61.3	59.7	61.3	62.9	64.4
102.5°	53.5	67.1	80.8	87.1	86.1	85.1	84.1	83.0	84.1	85.1	86.1
105°	91.5	98.6	105.7	108.8	107.9	107.0	106.2	105.3	106.2	107.0	107.9
107.5°	135.1	133.9	132.7	131.8	131.1	130.4	129.7	129.0	129.7	130.4	131.1
110°	157.6	156.8	155.9	155.2	154.5	153.9	153.3	152.7	153.3	153.9	154.5





TEST NUMBER: P831507

CATALOG NUMBER: S123DIP-S560D365U835-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	179.9	179.0	178.2	177.5	176.9	176.4	175.8	175.3	175.8	176.4	176.9
115°	201.4	200.7	200.0	199.4	198.9	198.5	198.0	197.5	198.0	198.5	198.9
117.5°	222.9	222.5	222.1	221.6	221.1	220.5	220.0	219.4	220.0	220.5	221.1
120°	243.4	243.1	242.9	242.4	241.7	241.0	240.3	239.6	240.3	241.0	241.7
122.5°	263.3	263.0	262.7	262.3	261.7	261.2	260.6	260.1	260.6	261.2	261.7
125°	282.1	281.8	281.4	281.0	280.3	279.7	279.1	278.5	279.1	279.7	280.3
127.5°	300.6	300.2	299.9	299.3	298.7	298.1	297.5	296.8	297.5	298.1	298.7
130°	317.4	317.1	316.8	316.3	315.7	315.0	314.4	313.8	314.4	315.0	315.7
132.5°	333.5	333.2	333.0	332.6	331.9	331.3	330.7	330.0	330.7	331.3	331.9
135°	349.6	349.2	348.9	348.5	348.1	347.6	347.1	346.7	347.1	347.6	348.1
137.5°	364.0	363.9	363.7	363.3	362.7	362.0	361.4	360.8	361.4	362.0	362.7
140°	377.6	377.4	377.2	376.8	376.3	375.9	375.4	374.9	375.4	375.9	376.3
142.5°	390.7	390.5	390.2	389.9	389.4	388.9	388.5	388.0	388.5	388.9	389.4
145°	402.9	402.7	402.6	402.2	401.7	401.1	400.6	400.0	400.6	401.1	401.7
147.5°	413.8	413.7	413.5	413.2	412.9	412.5	412.1	411.7	412.1	412.5	412.9
150°	423.7	423.6	423.4	423.2	423.0	422.7	422.5	422.3	422.5	422.7	423.0
152.5°	432.4	432.3	432.2	432.1	432.1	432.0	431.9	431.8	431.9	432.0	432.1
155°	440.1	440.1	440.0	440.0	440.2	440.3	440.5	440.7	440.5	440.3	440.2
157.5°	447.5	447.6	447.7	447.7	447.7	447.7	447.7	447.7	447.7	447.7	447.7
160°	453.5	453.6	453.7	453.8	453.8	453.9	454.0	454.1	454.0	453.9	453.8
162.5°	458.8	458.9	459.0	459.1	459.4	459.6	459.9	460.1	459.9	459.6	459.4
165°	463.4	463.5	463.6	463.7	464.0	464.2	464.4	464.7	464.4	464.2	464.0
167.5°	467.2	467.2	467.2	467.3	467.6	467.9	468.3	468.6	468.3	467.9	467.6
170°	470.3	470.3	470.3	470.5	470.8	471.1	471.4	471.7	471.4	471.1	470.8
172.5°	472.3	472.2	472.1	472.3	472.7	473.1	473.5	473.9	473.5	473.1	472.7
175°	474.1	474.0	473.9	474.1	474.5	474.8	475.2	475.6	475.2	474.8	474.5
177.5°	474.8	474.7	474.6	474.8	475.2	475.6	475.9	476.3	475.9	475.6	475.2
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6



TEST NUMBER: P831507

CATALOG NUMBER: S123DIP-S560D365U835-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1
2.5°	1549.0	1534.4	1519.7	1508.5	1497.3	1478.2	1459.1	1454.6	1450.1	1443.7	1437.4
5°	1468.8	1432.9	1396.9	1364.7	1332.5	1307.4	1282.3	1265.8	1249.4	1237.4	1225.4
7.5°	1375.2	1321.3	1267.3	1229.1	1190.9	1154.6	1118.3	1106.7	1095.1	1079.3	1063.6
10°	1284.6	1225.0	1165.5	1115.7	1065.8	1030.3	994.7	980.5	966.2	946.4	926.5
12.5°	1203.7	1138.5	1073.3	1023.2	973.0	938.5	904.1	883.5	862.9	851.6	840.4
15°	1119.0	1049.4	979.7	933.3	886.8	855.7	824.7	806.7	788.7	777.8	767.0
17.5°	1044.1	975.2	906.3	861.7	817.2	788.7	760.2	744.5	728.8	720.5	712.3
20°	973.0	905.6	838.1	794.7	751.3	728.0	704.8	694.7	684.6	677.9	671.1
22.5°	907.8	841.5	775.2	738.2	701.1	682.3	663.6	656.5	649.4	643.8	638.2
25°	842.6	783.5	724.3	692.8	661.4	646.0	630.7	623.6	616.4	610.8	605.2
27.5°	789.5	732.9	676.4	649.4	622.4	610.4	598.5	592.8	587.2	582.0	576.7
30°	737.8	687.2	636.7	613.4	590.2	579.4	568.5	562.9	557.3	552.4	547.5
32.5°	689.8	646.4	603.0	581.6	560.3	551.3	542.3	535.5	528.8	525.1	521.3
35°	644.2	605.2	566.3	548.7	531.0	522.1	513.1	507.5	501.8	498.8	495.8
37.5°	605.2	570.4	535.5	518.7	501.8	493.2	484.6	479.7	474.9	473.7	472.6
40°	565.5	535.5	505.6	489.1	472.6	465.1	457.6	454.7	451.7	450.9	450.2
42.5°	532.5	503.3	474.1	459.1	444.2	437.8	431.4	429.9	428.4	429.6	430.7
45°	494.3	470.0	445.7	431.8	417.9	412.7	407.5	406.3	405.2	407.5	409.7
47.5°	462.1	439.7	417.2	404.1	391.0	387.2	383.5	383.1	382.7	385.7	388.7
50°	429.2	407.5	385.7	375.3	364.8	361.4	358.0	359.2	360.3	365.1	370.0
52.5°	398.5	378.3	358.0	348.3	338.6	336.3	334.1	336.7	339.3	344.5	349.8
55°	364.8	346.4	328.1	320.6	313.1	310.8	308.6	313.8	319.1	323.9	328.8
57.5°	332.6	316.5	300.4	293.6	286.9	286.5	286.1	291.0	295.9	301.1	306.3
60°	298.1	284.6	271.1	265.9	260.7	261.4	262.2	267.8	273.4	277.5	281.6
62.5°	266.6	255.4	244.2	239.3	234.4	236.3	238.2	243.8	249.4	254.3	259.2
65°	235.2	225.8	216.5	213.1	209.7	212.3	215.0	219.8	224.7	228.1	231.4
67.5°	205.2	197.4	189.5	186.9	184.3	186.9	189.5	194.4	199.2	202.6	206.0
70°	173.8	167.4	161.0	159.2	157.3	160.3	163.3	167.4	171.5	174.9	178.3
72.5°	144.6	139.7	134.8	134.4	134.1	136.7	139.3	143.4	147.6	149.8	152.0
75°	116.1	113.5	110.9	110.5	110.1	112.7	115.3	117.6	119.8	121.7	123.6
77.5°	90.6	88.4	86.1	86.5	86.9	88.8	90.6	92.9	95.1	96.2	97.4
80°	64.4	63.7	62.9	63.7	64.4	65.9	67.4	68.9	70.4	71.2	71.9
82.5°	44.2	43.4	42.7	43.8	44.9	46.1	47.2	48.3	49.4	49.8	50.2
85°	25.5	26.6	27.7	27.7	27.7	28.1	28.5	28.8	29.2	28.8	28.5
87.5°	12.0	12.4	12.7	12.7	12.7	13.1	13.5	13.5	13.5	13.1	12.7
90°	3.5	4.4	5.4	6.4	7.5	8.5	8.8	9.1	9.4	9.7	10.0
92.5°	6.2	6.4	7.1	7.8	8.5	9.2	9.7	10.3	10.8	11.4	11.7
95°	8.7	7.5	8.4	9.2	10.1	11.0	11.5	12.1	12.6	13.2	13.4
97.5°	30.4	27.3	23.3	19.3	15.3	11.3	11.9	12.6	13.2	13.8	14.2
100°	66.0	60.7	48.4	36.2	23.9	11.7	12.3	12.9	13.5	14.2	14.5
102.5°	87.1	80.8	67.1	53.5	39.8	26.1	23.6	21.0	18.4	15.8	14.6
105°	108.8	105.7	98.6	91.5	84.5	77.4	63.5	49.6	35.7	21.8	14.9
107.5°	131.8	132.7	133.9	135.1	136.3	137.5	125.4	113.3	101.2	89.1	77.9
110°	155.2	155.9	156.8	157.6	158.5	159.4	156.8	154.2	151.6	149.0	142.1



TEST NUMBER: P831507

CATALOG NUMBER: S123DIP-S560D365U835-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	177.5	178.2	179.0	179.9	180.8	181.6	182.3	183.0	183.8	184.5	184.7
115°	199.4	200.0	200.7	201.4	202.1	202.8	203.6	204.4	205.2	206.0	206.5
117.5°	221.6	222.1	222.5	222.9	223.3	223.7	224.3	224.9	225.6	226.2	226.5
120°	242.4	242.9	243.1	243.4	243.6	243.8	244.5	245.1	245.7	246.3	246.7
122.5°	262.3	262.7	263.0	263.3	263.7	264.0	264.4	264.8	265.1	265.5	265.8
125°	281.0	281.4	281.8	282.1	282.4	282.7	282.9	283.0	283.2	283.3	283.5
127.5°	299.3	299.9	300.2	300.6	301.0	301.4	301.7	301.9	302.1	302.4	302.4
130°	316.3	316.8	317.1	317.4	317.7	318.0	318.3	318.7	319.0	319.3	319.4
132.5°	332.6	333.0	333.2	333.5	333.7	333.9	334.2	334.6	334.9	335.2	335.2
135°	348.5	348.9	349.2	349.6	349.9	350.2	350.4	350.7	350.9	351.1	351.1
137.5°	363.3	363.7	363.9	364.0	364.2	364.3	364.7	365.1	365.5	365.9	366.0
140°	376.8	377.2	377.4	377.6	377.9	378.1	378.4	378.7	379.0	379.4	379.4
142.5°	389.9	390.2	390.5	390.7	390.9	391.2	391.4	391.7	391.9	392.1	392.1
145°	402.2	402.6	402.7	402.9	403.0	403.2	403.4	403.5	403.7	403.8	403.9
147.5°	413.2	413.5	413.7	413.8	414.0	414.1	414.3	414.5	414.6	414.8	414.7
150°	423.2	423.4	423.6	423.7	423.9	424.0	424.2	424.4	424.5	424.7	424.6
152.5°	432.1	432.2	432.3	432.4	432.4	432.5	432.8	433.2	433.5	433.8	433.7
155°	440.0	440.0	440.1	440.1	440.2	440.3	440.7	441.1	441.5	441.9	441.8
157.5°	447.7	447.7	447.6	447.5	447.4	447.4	447.8	448.3	448.8	449.3	449.2
160°	453.8	453.7	453.6	453.5	453.5	453.4	453.8	454.3	454.8	455.3	455.2
162.5°	459.1	459.0	458.9	458.8	458.8	458.7	459.2	459.8	460.3	460.9	460.9
165°	463.7	463.6	463.5	463.4	463.3	463.3	463.9	464.5	465.2	465.8	465.8
167.5°	467.3	467.2	467.2	467.2	467.2	467.2	467.8	468.4	469.0	469.7	469.7
170°	470.5	470.3	470.3	470.3	470.3	470.3	471.0	471.6	472.2	472.8	472.8
172.5°	472.3	472.1	472.2	472.3	472.4	472.5	473.1	473.7	474.3	475.0	474.9
175°	474.1	473.9	474.0	474.1	474.1	474.2	474.8	475.3	475.9	476.4	476.4
177.5°	474.8	474.6	474.7	474.8	474.8	474.9	475.6	476.2	476.8	477.4	477.4
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6



TEST NUMBER: P831507

CATALOG NUMBER: S123DIP-S560D365U835-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	1614.1	1614.1	1614.1	1614.1
2.5°	1434.7	1432.1	1421.6	1411.1
5°	1216.4	1207.4	1204.4	1201.4
7.5°	1062.8	1062.1	1046.4	1030.6
10°	927.7	928.8	914.5	900.3
12.5°	831.0	821.7	820.5	819.4
15°	758.4	749.8	748.3	746.8
17.5°	707.1	701.8	700.3	698.8
20°	668.1	665.1	662.5	659.9
22.5°	634.4	630.7	628.4	626.2
25°	601.8	598.5	597.7	597.0
27.5°	572.6	568.5	568.5	568.5
30°	544.9	542.3	541.2	540.0
32.5°	519.1	516.8	516.8	516.8
35°	494.7	493.6	492.1	490.6
37.5°	472.6	472.6	471.9	471.1
40°	451.3	452.4	452.4	452.4
42.5°	431.8	432.9	432.9	432.9
45°	411.6	413.5	414.2	415.0
47.5°	391.7	394.7	395.5	396.2
50°	372.3	374.5	374.9	375.3
52.5°	352.4	355.0	356.9	358.8
55°	331.4	334.1	335.2	336.3
57.5°	309.0	311.6	312.0	312.3
60°	284.2	286.9	287.6	288.4
62.5°	260.7	262.2	262.9	263.7
65°	233.7	235.9	237.4	238.9
67.5°	207.9	209.7	209.7	209.7
70°	179.0	179.8	180.9	182.0
72.5°	152.4	152.8	152.8	152.8
75°	124.3	125.1	125.5	125.8
77.5°	97.7	98.1	98.1	98.1
80°	71.5	71.2	71.2	71.2
82.5°	49.1	47.9	47.9	47.9
85°	28.1	27.7	28.1	28.5
87.5°	12.7	12.7	12.7	12.7
90°	10.1	10.3	10.4	10.6
92.5°	11.8	11.9	11.9	12.0
95°	13.4	13.4	13.4	13.4
97.5°	14.3	14.3	14.4	14.5
100°	14.6	14.7	14.8	14.8
102.5°	14.7	14.9	15.0	15.2
105°	15.1	15.2	15.4	15.5
107.5°	67.6	57.3	47.0	36.8
110°	130.9	119.6	108.4	97.2



TEST NUMBER: P831507

CATALOG NUMBER: S123DIP-S560D365U835-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	184.6	184.4	184.3	184.1
115°	206.8	207.2	207.5	207.8
117.5°	226.6	226.7	226.8	226.9
120°	246.7	246.7	246.7	246.7
122.5°	265.9	265.9	266.0	266.1
125°	283.6	283.8	284.0	284.1
127.5°	302.2	302.1	301.9	301.8
130°	319.2	319.1	318.9	318.7
132.5°	335.0	334.8	334.5	334.3
135°	350.9	350.7	350.4	350.2
137.5°	365.9	365.7	365.5	365.4
140°	379.3	379.1	379.0	378.8
142.5°	391.9	391.7	391.4	391.2
145°	403.9	403.9	403.9	403.9
147.5°	414.3	413.9	413.5	413.1
150°	424.4	424.2	423.9	423.7
152.5°	433.3	433.0	432.6	432.2
155°	441.4	440.9	440.4	439.9
157.5°	448.5	447.9	447.3	446.7
160°	454.7	454.1	453.6	453.0
162.5°	460.4	460.0	459.5	459.0
165°	465.3	464.7	464.2	463.6
167.5°	469.0	468.4	467.8	467.2
170°	472.2	471.6	471.0	470.3
172.5°	474.2	473.5	472.8	472.1
175°	475.8	475.1	474.5	473.9
177.5°	476.6	475.8	475.0	474.2
180°	475.6	475.6	475.6	475.6



TEST NUMBER: P831507

CATALOG NUMBER: S123DIP-S560D365U835-4F0-1E-UDD-G

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.72	15.67	15.55	16.52	17.58	16.95	17.91	17.79	18.76	19.82
	3H	16.37	17.23	17.22	18.09	19.17	18.39	19.24	19.23	20.10	21.18
	4H	16.95	17.76	17.82	18.63	19.72	18.84	19.65	19.70	20.51	21.61
	6H	17.33	18.07	18.20	18.95	20.05	19.12	19.86	20.00	20.74	21.85
	8H	17.43	18.14	18.31	19.03	20.13	19.19	19.89	20.07	20.78	21.89
	12H	17.48	18.15	18.36	19.03	20.17	19.21	19.88	20.10	20.77	21.90
4H	2H	15.30	16.11	16.17	16.98	18.07	17.13	17.94	18.00	18.80	19.90
	3H	17.14	17.81	18.02	18.71	19.82	18.76	19.43	19.63	20.33	21.44
	4H	17.84	18.45	18.73	19.35	20.49	19.34	19.95	20.23	20.85	21.99
	6H	18.32	18.85	19.23	19.77	20.91	19.75	20.28	20.66	21.20	22.34
	8H	18.46	18.95	19.37	19.87	21.02	19.87	20.36	20.77	21.27	22.42
	12H	18.53	18.97	19.46	19.91	21.06	19.92	20.36	20.84	21.29	22.45
8H	4H	18.12	18.61	19.02	19.52	20.67	19.46	19.95	20.36	20.86	22.01
	6H	18.71	19.11	19.64	20.07	21.22	19.96	20.37	20.90	21.32	22.47
	8H	18.92	19.27	19.86	20.22	21.39	20.14	20.50	21.09	21.45	22.62
	12H	19.04	19.36	19.99	20.30	21.52	20.25	20.56	21.19	21.50	22.72
12H	4H	18.12	18.56	19.05	19.50	20.65	19.44	19.88	20.36	20.81	21.97
	6H	18.76	19.12	19.70	20.07	21.23	19.98	20.34	20.92	21.28	22.45
	8H	19.00	19.31	19.94	20.25	21.47	20.18	20.50	21.13	21.44	22.66