

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332017-830

Luminaire Tested: **S123DIP-S1000D585U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332017-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D585U830-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5882.3 lumens
Efficiency: N/A
Efficacy: 120.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332017-830

CATALOG NUMBER: S123DIP-S1000D585U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332017-830

CATALOG NUMBER: S123DIP-S1000D585U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	101	97	93	89	95	91	88	85	81	78	76	71	69	67	63	61	60	55
2	92	85	78	73	87	80	74	69	71	66	63	63	59	56	55	52	50	46
3	84	74	67	61	79	70	63	58	62	57	53	55	51	48	49	45	43	39
4	77	66	58	51	72	62	55	49	56	50	45	49	45	41	44	40	37	34
5	71	59	50	44	66	56	48	42	50	44	39	44	39	35	39	35	32	29
6	65	53	44	38	61	50	42	37	45	39	34	40	35	31	36	31	28	26
7	60	48	40	34	57	45	38	33	41	35	30	37	31	28	33	28	25	23
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	23	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	23	20	18
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16060	16060	16060
5°	16134	15913	16024
10°	16027	15774	15872
15°	15840	15597	15624
20°	15621	15341	15356
25°	15327	15037	15007
30°	15003	14701	14588
35°	14666	14345	14160
40°	14313	13952	13735
45°	13922	13592	13259
50°	13534	13147	12782
55°	13024	12688	12301
60°	12510	12152	11765
65°	12055	11566	11207
70°	11383	10902	10414
75°	10405	10031	9603
80°	9385	8988	8901
85°	8238	7929	7595



TEST NUMBER: P332017-830

CATALOG NUMBER: S123DIP-S1000D585U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.5	2.4
10°-20°	396.8	6.7
20°-30°	586.2	10.0
30°-40°	684.7	11.6
40°-50°	688.4	11.7
50°-60°	604.7	10.3
60°-70°	450.5	7.7
70°-80°	256.7	4.4
80°-90°	75.7	1.3
90°-100°	147.8	2.5
100°-110°	418.5	7.1
110°-120°	411.7	7.0
120°-130°	328.4	5.6
130°-140°	258.9	4.4
140°-150°	193.2	3.3
150°-160°	134.7	2.3
160°-170°	79.1	1.3
170°-180°	25.7	0.4
0°-30°	1123.5	19.1
0°-40°	1808.2	30.7
0°-60°	3101.3	52.7
0°-90°	3884.2	66.0
90°-120°	978.0	16.6
90°-150°	1758.5	29.9
90°-180°	1998.0	34.0
0°-180°	5882.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1492	1492	1492	1492	1492	
5°	1493	1486	1473	1485	1483	141
15°	1421	1416	1400	1409	1402	401
25°	1290	1282	1266	1267	1264	594
35°	1116	1108	1092	1084	1078	698
45°	915	909	893	878	871	706
55°	694	692	676	662	656	621
65°	473	467	454	444	440	467
75°	250	245	241	235	231	267
85°	67	64	64	62	62	73
90°	1	6	14	15	16	5
95°	18	59	319	93	62	20
105°	62	92	432	756	684	66
115°	110	137	331	725	832	109
125°	153	181	309	559	656	136
135°	180	214	304	460	532	139
145°	205	235	300	378	416	128
155°	233	251	291	331	345	107
165°	254	262	278	295	300	72
175°	265	265	267	271	270	25
180°	266	266	266	266	266	



TEST NUMBER: P332017-830

CATALOG NUMBER: S123DIP-S1000D585U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0
2.5°	1497.0	1496.2	1495.2	1494.3	1493.5	1491.7	1489.2	1486.7	1484.2	1481.7	1483.9
5°	1493.2	1491.8	1490.3	1488.9	1487.5	1485.3	1482.1	1478.9	1475.8	1472.7	1475.6
7.5°	1478.6	1477.2	1475.7	1474.3	1472.9	1470.6	1467.4	1464.1	1460.8	1457.5	1460.1
10°	1466.3	1464.9	1463.4	1462.0	1460.6	1458.0	1454.3	1450.6	1446.9	1443.2	1445.8
12.5°	1449.8	1448.7	1447.5	1446.2	1445.1	1442.7	1439.3	1435.8	1432.3	1428.8	1430.7
15°	1421.4	1420.2	1419.1	1418.0	1416.8	1414.4	1410.7	1407.0	1403.3	1399.6	1401.8
17.5°	1388.3	1386.8	1385.3	1383.8	1382.3	1379.8	1376.0	1372.3	1368.7	1364.9	1366.5
20°	1363.7	1362.0	1360.3	1358.5	1356.8	1354.1	1350.4	1346.7	1343.0	1339.3	1340.4
22.5°	1336.0	1334.3	1332.6	1330.8	1329.1	1326.4	1322.7	1319.0	1315.3	1311.5	1312.5
25°	1290.5	1288.8	1287.1	1285.4	1283.6	1281.0	1277.2	1273.6	1269.9	1266.1	1266.4
27.5°	1242.1	1240.4	1238.7	1237.1	1235.4	1232.6	1228.6	1224.6	1220.6	1216.6	1216.8
30°	1207.1	1205.7	1204.3	1202.9	1201.5	1198.7	1194.8	1190.7	1186.8	1182.8	1182.8
32.5°	1172.2	1170.4	1168.5	1166.6	1164.7	1162.2	1159.1	1156.1	1153.0	1149.9	1148.3
35°	1116.1	1114.4	1112.7	1111.0	1109.2	1106.5	1102.8	1099.1	1095.4	1091.7	1090.0
37.5°	1058.6	1056.4	1054.2	1052.1	1049.9	1047.0	1043.2	1039.4	1035.7	1031.9	1029.8
40°	1018.6	1016.8	1015.1	1013.4	1011.7	1008.9	1004.8	1000.9	996.9	992.9	990.6
42.5°	978.5	976.6	974.7	972.7	970.8	967.8	963.8	959.9	955.8	951.9	949.6
45°	914.6	913.5	912.4	911.3	910.1	907.7	904.0	900.2	896.5	892.9	889.5
47.5°	851.3	849.6	848.0	846.3	844.7	842.1	838.7	835.2	831.7	828.2	824.8
50°	808.2	806.7	805.3	803.9	802.5	799.9	796.2	792.5	788.8	785.1	781.9
52.5°	763.0	762.0	761.1	760.2	759.1	756.7	752.8	748.9	744.9	740.9	738.3
55°	694.0	693.7	693.4	693.1	692.9	690.9	687.2	683.4	679.8	676.1	672.9
57.5°	628.3	627.4	626.4	625.5	624.4	622.5	619.5	616.5	613.6	610.7	607.8
60°	581.1	580.8	580.5	580.2	579.9	578.2	574.7	571.3	567.9	564.5	561.8
62.5°	539.0	538.3	537.5	536.8	536.1	534.0	530.6	527.2	523.8	520.3	517.7
65°	473.3	471.9	470.5	469.1	467.7	465.5	462.7	459.9	456.9	454.1	451.9
67.5°	403.9	402.6	401.3	400.1	398.8	397.1	394.9	392.8	390.6	388.4	386.4
70°	361.7	360.1	358.4	356.7	355.0	353.2	351.5	349.8	348.1	346.4	344.4
72.5°	317.6	316.4	315.1	313.9	312.6	311.0	309.1	307.2	305.2	303.2	301.5
75°	250.2	249.0	247.9	246.8	245.6	244.6	243.7	242.9	242.0	241.2	239.8
77.5°	190.4	189.7	189.1	188.5	187.8	187.0	186.1	185.0	184.0	182.9	182.0
80°	151.4	150.5	149.7	148.8	148.0	147.2	146.7	146.1	145.5	145.0	144.7
82.5°	113.4	113.2	113.1	112.9	112.7	112.5	112.4	112.4	112.3	112.2	111.6
85°	66.7	66.2	65.6	65.0	64.5	64.2	64.2	64.2	64.2	64.2	63.5
87.5°	26.9	26.4	25.9	25.6	25.2	24.9	25.0	25.1	25.2	25.3	25.0
90°	1.0	2.2	3.2	4.8	5.9	7.0	8.6	10.2	11.8	13.5	12.9
92.5°	6.7	9.9	14.4	18.6	23.1	31.1	45.1	68.2	91.0	82.7	62.4
95°	18.3	19.9	25.8	35.0	48.9	69.8	115.6	195.7	283.9	318.8	258.5
97.5°	31.2	31.8	36.4	44.3	58.1	80.8	124.4	214.7	361.7	494.1	528.6
100°	39.8	40.3	44.1	51.7	64.5	85.5	123.1	202.6	344.0	509.1	615.0
102.5°	48.8	49.8	53.2	60.2	71.8	91.0	124.8	192.4	318.3	481.2	619.3
105°	62.4	64.0	67.2	73.6	83.9	100.6	129.6	184.9	286.5	432.3	586.5
107.5°	76.7	78.4	81.5	87.8	97.5	112.9	138.4	184.4	266.4	389.0	529.1
110°	87.1	88.7	91.4	97.3	106.4	121.5	145.7	186.5	258.5	364.5	492.9



TEST NUMBER: P332017-830

CATALOG NUMBER: S123DIP-S1000D585U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	96.5	98.2	100.9	106.8	115.9	130.5	153.0	190.9	254.3	348.2	461.6
115°	110.2	112.4	115.6	120.9	130.1	144.6	165.0	197.8	252.7	330.6	423.7
117.5°	123.9	126.3	129.0	133.9	144.2	157.6	177.9	207.1	253.6	320.3	400.8
120°	133.4	135.0	137.6	143.0	153.3	166.6	186.0	214.0	255.3	315.6	388.7
122.5°	141.5	143.1	145.8	151.6	161.4	175.7	194.6	220.5	258.4	312.5	378.8
125°	153.3	154.3	157.5	163.4	173.6	188.1	207.0	230.6	262.9	308.6	366.1
127.5°	162.1	163.7	167.8	173.7	185.0	199.5	217.7	239.0	268.1	306.6	355.0
130°	167.8	169.4	174.2	180.6	191.9	206.4	224.1	244.6	271.5	305.4	348.9
132.5°	172.0	174.1	179.4	187.1	198.4	212.4	229.8	249.8	274.1	304.9	343.3
135°	179.6	181.7	187.7	195.7	207.0	221.5	238.2	256.5	278.0	304.3	336.0
137.5°	186.6	188.9	194.7	203.3	214.5	227.9	243.9	261.4	280.5	303.1	329.7
140°	191.4	194.1	199.4	208.0	218.8	232.2	247.8	264.0	282.2	302.7	325.7
142.5°	196.5	198.8	204.6	212.4	223.1	235.7	250.8	266.6	283.5	301.8	322.3
145°	204.8	206.4	211.3	219.3	228.5	240.8	254.9	269.4	284.4	300.5	317.7
147.5°	213.2	214.1	219.0	225.9	234.7	245.2	258.1	271.1	284.4	298.5	313.2
150°	218.8	219.3	223.7	230.6	238.2	247.8	260.2	271.5	284.4	296.7	310.2
152.5°	224.4	224.5	228.8	235.0	241.6	250.8	261.5	272.4	283.1	294.6	306.8
155°	232.8	232.8	236.0	241.4	247.3	254.9	264.0	272.6	281.7	290.9	301.6
157.5°	239.4	239.9	242.4	247.2	252.2	258.1	265.3	273.1	279.8	287.5	295.8
160°	244.6	244.6	246.8	251.1	254.9	260.2	266.6	273.1	279.0	284.9	291.9
162.5°	248.5	248.5	250.2	253.6	256.9	261.5	267.1	272.7	277.3	282.4	288.0
165°	254.3	253.7	254.9	257.5	259.7	263.4	267.7	271.5	274.8	278.5	282.8
167.5°	258.7	258.1	258.5	260.6	262.1	264.5	267.6	270.6	272.1	274.6	277.8
170°	261.3	260.2	260.7	262.3	263.4	264.5	267.2	269.4	270.4	272.0	274.8
172.5°	263.0	262.3	262.5	263.6	264.3	264.9	267.2	268.9	269.1	269.8	271.7
175°	265.0	264.5	264.0	265.0	265.0	265.6	266.6	267.7	267.2	267.2	268.2
177.5°	266.0	265.6	265.1	265.6	265.6	265.6	266.0	266.8	266.0	265.6	266.0
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6



TEST NUMBER: P332017-830

CATALOG NUMBER: S123DIP-S1000D585U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0
2.5°	1486.2	1488.6	1490.8	1491.9	1491.6	1491.4	1491.1	1490.9
5°	1478.4	1481.2	1484.1	1485.3	1484.7	1484.1	1483.6	1483.0
7.5°	1462.7	1465.3	1467.8	1469.0	1468.6	1468.3	1467.9	1467.5
10°	1448.3	1450.9	1453.5	1454.4	1453.9	1453.3	1452.7	1452.2
12.5°	1432.6	1434.5	1436.3	1437.1	1436.8	1436.4	1436.1	1435.8
15°	1404.1	1406.4	1408.7	1409.0	1407.3	1405.5	1403.8	1402.1
17.5°	1368.1	1369.7	1371.3	1371.8	1371.2	1370.6	1369.9	1369.3
20°	1341.5	1342.7	1343.9	1344.0	1343.1	1342.3	1341.4	1340.6
22.5°	1313.4	1314.3	1315.2	1315.1	1314.1	1313.0	1311.9	1310.8
25°	1266.7	1267.1	1267.3	1267.1	1266.1	1265.3	1264.4	1263.6
27.5°	1217.1	1217.3	1217.6	1217.1	1216.1	1214.9	1213.9	1212.8
30°	1182.8	1182.8	1182.8	1181.8	1179.8	1177.8	1175.8	1173.7
32.5°	1146.7	1145.2	1143.6	1142.2	1141.1	1140.0	1139.0	1137.8
35°	1088.3	1086.6	1084.9	1083.3	1081.9	1080.4	1079.0	1077.6
37.5°	1027.8	1025.8	1023.7	1022.2	1021.3	1020.4	1019.5	1018.6
40°	988.4	986.1	983.8	982.0	980.9	979.8	978.6	977.5
42.5°	947.3	945.0	942.7	941.0	939.9	938.8	937.6	936.5
45°	886.0	882.6	879.2	876.8	875.3	873.9	872.5	871.0
47.5°	821.4	818.1	814.7	812.5	811.2	809.9	808.7	807.4
50°	778.8	775.7	772.5	770.2	768.5	766.7	765.0	763.3
52.5°	735.6	732.9	730.3	728.0	726.3	724.6	722.9	721.2
55°	669.8	666.7	663.5	661.2	659.8	658.4	657.0	655.5
57.5°	605.0	602.3	599.5	597.2	595.6	593.9	592.3	590.6
60°	559.3	556.8	554.2	552.2	550.7	549.3	547.9	546.5
62.5°	515.2	512.6	510.0	508.3	507.3	506.3	505.4	504.4
65°	449.6	447.2	445.0	443.5	442.6	441.8	440.8	440.0
67.5°	384.5	382.5	380.5	378.9	377.7	376.5	375.2	374.1
70°	342.3	340.4	338.4	336.7	335.3	333.8	332.4	330.9
72.5°	299.7	297.9	296.1	294.9	294.2	293.4	292.8	292.0
75°	238.4	236.9	235.4	234.3	233.5	232.6	231.8	230.9
77.5°	181.0	180.0	179.1	178.6	178.6	178.6	178.6	178.6
80°	144.4	144.1	143.8	143.6	143.6	143.6	143.6	143.6
82.5°	111.1	110.6	110.1	109.7	109.4	109.2	109.1	108.8
85°	63.0	62.4	61.8	61.5	61.5	61.5	61.5	61.5
87.5°	24.8	24.7	24.6	24.7	24.6	24.7	24.8	24.7
90°	13.5	13.9	14.5	15.6	15.1	15.6	16.1	15.6
92.5°	45.2	35.9	31.8	28.9	28.0	26.3	26.9	25.9
95°	193.5	131.2	102.6	83.3	73.1	68.2	64.5	62.4
97.5°	482.5	386.4	317.1	252.8	213.1	188.9	174.4	169.8
100°	633.9	590.3	527.4	451.0	396.7	357.5	336.6	337.1
102.5°	684.2	682.8	646.1	597.7	555.4	524.3	506.8	494.5
105°	698.9	752.6	762.9	748.9	724.2	703.7	686.5	683.8
107.5°	656.5	743.9	790.9	810.0	810.5	803.6	797.8	792.9
110°	616.0	715.0	782.8	820.4	835.5	839.7	838.7	837.5



TEST NUMBER: P332017-830

CATALOG NUMBER: S123DIP-S1000D585U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	576.1	677.1	753.1	801.4	829.0	842.4	846.4	846.6
115°	523.1	616.6	695.7	754.2	794.6	818.2	829.0	831.7
117.5°	484.7	565.4	636.4	695.9	737.9	765.0	780.5	784.1
120°	464.5	537.1	601.5	655.9	698.3	728.5	741.3	744.6
122.5°	448.6	514.3	574.0	624.4	662.2	689.3	703.5	707.6
125°	427.3	486.0	537.6	580.6	615.0	638.7	652.1	655.9
127.5°	408.9	461.2	507.7	546.9	577.5	597.7	609.8	613.3
130°	397.3	445.6	489.2	525.8	554.3	573.6	584.9	589.2
132.5°	386.5	431.0	471.6	506.4	533.2	552.5	562.5	565.5
135°	372.0	410.2	445.2	475.8	502.1	518.2	527.9	531.7
137.5°	358.8	390.1	420.2	446.8	468.9	485.2	493.4	495.9
140°	351.1	378.4	404.3	427.3	447.8	462.9	471.5	470.9
142.5°	343.7	367.3	389.6	409.7	427.2	440.5	448.3	447.7
145°	334.9	352.7	369.9	385.5	398.9	410.2	414.5	415.6
147.5°	327.7	341.8	355.7	366.7	376.9	384.6	388.7	389.1
150°	322.5	334.9	346.2	356.5	364.5	370.4	373.6	373.6
152.5°	317.8	328.5	338.5	346.9	353.3	358.8	360.7	360.7
155°	310.8	319.3	327.4	333.8	338.7	343.0	344.0	344.6
157.5°	303.2	310.4	316.7	321.7	325.9	329.1	330.0	329.9
160°	298.9	304.8	310.2	314.0	317.7	320.9	320.9	320.4
162.5°	293.8	298.8	303.8	307.1	309.5	312.4	312.4	311.8
165°	287.1	290.3	294.1	296.7	298.9	301.0	300.5	300.5
167.5°	281.3	283.7	285.9	287.9	288.8	290.3	289.7	289.7
170°	277.4	279.0	281.2	282.2	282.8	283.9	283.3	283.3
172.5°	274.0	275.1	276.8	277.5	277.6	278.7	277.8	277.3
175°	269.4	269.8	271.0	271.0	271.0	271.5	271.0	270.4
177.5°	266.5	266.8	267.3	267.3	266.8	267.3	266.5	266.5
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6

(END OF REPORT)