

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332025-830

Luminaire Tested: **S123DIP-S1000D805U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332025-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D805U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6484.1 lumens
Efficiency: N/A
Efficacy: 119.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332025-830

CATALOG NUMBER: S123DIP-S1000D805U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332025-830

CATALOG NUMBER: S123DIP-S1000D805U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60
1	100	95	92	88	93	89	86	83	78	75	73	67	65	64	58	56	55	50
2	91	83	77	72	85	78	73	68	68	64	60	59	56	53	51	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	39	36
4	76	65	57	51	71	61	54	48	53	48	43	47	42	38	40	37	34	31
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	33	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	30	26	30	26	23	21
8	55	43	35	29	52	40	33	28	36	30	26	31	27	23	27	24	21	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	22	19	17
10	48	36	28	24	45	34	27	23	30	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16060	16060	16060
5°	16134	15913	16024
10°	16027	15774	15872
15°	15840	15597	15624
20°	15621	15341	15356
25°	15327	15037	15007
30°	15003	14701	14588
35°	14666	14345	14160
40°	14313	13952	13735
45°	13922	13592	13259
50°	13534	13147	12782
55°	13024	12688	12301
60°	12510	12152	11765
65°	12055	11566	11207
70°	11383	10902	10414
75°	10405	10031	9603
80°	9385	8988	8901
85°	8238	7929	7595



TEST NUMBER: P332025-830

CATALOG NUMBER: S123DIP-S1000D805U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.5	2.2
10°-20°	396.8	6.1
20°-30°	586.2	9.0
30°-40°	684.7	10.6
40°-50°	688.4	10.6
50°-60°	604.7	9.3
60°-70°	450.5	6.9
70°-80°	256.7	4.0
80°-90°	76.4	1.2
90°-100°	61.1	0.9
100°-110°	182.9	2.8
110°-120°	311.1	4.8
120°-130°	409.2	6.3
130°-140°	460.0	7.1
140°-150°	452.1	7.0
150°-160°	380.6	5.9
160°-170°	253.4	3.9
170°-180°	88.7	1.4
0°-30°	1123.5	17.3
0°-40°	1808.2	27.9
0°-60°	3101.3	47.8
0°-90°	3884.9	59.9
90°-120°	555.1	8.6
90°-150°	1876.4	28.9
90°-180°	2599.0	40.1
0°-180°	6484.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1492	1492	1492	1492	1492	
5°	1493	1486	1473	1485	1483	141
15°	1421	1416	1400	1409	1402	401
25°	1290	1282	1266	1267	1264	594
35°	1116	1108	1092	1084	1078	698
45°	915	909	893	878	871	706
55°	694	692	676	662	656	621
65°	473	467	454	444	440	467
75°	250	245	241	235	231	267
85°	67	64	64	62	62	73
90°	1	8	18	21	22	6
95°	44	49	55	57	58	49
105°	166	168	174	174	175	178
115°	313	315	314	315	314	310
125°	458	460	459	456	453	409
135°	595	599	598	596	594	458
145°	721	723	725	724	721	450
155°	826	826	827	829	825	380
165°	900	898	898	901	897	254
175°	936	933	933	937	932	89
180°	938	938	938	938	938	



TEST NUMBER: P332025-830

CATALOG NUMBER: S123DIP-S1000D805U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0
2.5°	1497.0	1496.2	1495.2	1494.3	1493.5	1491.7	1489.2	1486.7	1484.2	1481.7	1483.9
5°	1493.2	1491.8	1490.3	1488.9	1487.5	1485.3	1482.1	1478.9	1475.8	1472.7	1475.6
7.5°	1478.6	1477.2	1475.7	1474.3	1472.9	1470.6	1467.4	1464.1	1460.8	1457.5	1460.1
10°	1466.3	1464.9	1463.4	1462.0	1460.6	1458.0	1454.3	1450.6	1446.9	1443.2	1445.8
12.5°	1449.8	1448.7	1447.5	1446.2	1445.1	1442.7	1439.3	1435.8	1432.3	1428.8	1430.7
15°	1421.4	1420.2	1419.1	1418.0	1416.8	1414.4	1410.7	1407.0	1403.3	1399.6	1401.8
17.5°	1388.3	1386.8	1385.3	1383.8	1382.3	1379.8	1376.0	1372.3	1368.7	1364.9	1366.5
20°	1363.7	1362.0	1360.3	1358.5	1356.8	1354.1	1350.4	1346.7	1343.0	1339.3	1340.4
22.5°	1336.0	1334.3	1332.6	1330.8	1329.1	1326.4	1322.7	1319.0	1315.3	1311.5	1312.5
25°	1290.5	1288.8	1287.1	1285.4	1283.6	1281.0	1277.2	1273.6	1269.9	1266.1	1266.4
27.5°	1242.1	1240.4	1238.7	1237.1	1235.4	1232.6	1228.6	1224.6	1220.6	1216.6	1216.8
30°	1207.1	1205.7	1204.3	1202.9	1201.5	1198.7	1194.8	1190.7	1186.8	1182.8	1182.8
32.5°	1172.2	1170.4	1168.5	1166.6	1164.7	1162.2	1159.1	1156.1	1153.0	1149.9	1148.3
35°	1116.1	1114.4	1112.7	1111.0	1109.2	1106.5	1102.8	1099.1	1095.4	1091.7	1090.0
37.5°	1058.6	1056.4	1054.2	1052.1	1049.9	1047.0	1043.2	1039.4	1035.7	1031.9	1029.8
40°	1018.6	1016.8	1015.1	1013.4	1011.7	1008.9	1004.8	1000.9	996.9	992.9	990.6
42.5°	978.5	976.6	974.7	972.7	970.8	967.8	963.8	959.9	955.8	951.9	949.6
45°	914.6	913.5	912.4	911.3	910.1	907.7	904.0	900.2	896.5	892.9	889.5
47.5°	851.3	849.6	848.0	846.3	844.7	842.1	838.7	835.2	831.7	828.2	824.8
50°	808.2	806.7	805.3	803.9	802.5	799.9	796.2	792.5	788.8	785.1	781.9
52.5°	763.0	762.0	761.1	760.2	759.1	756.7	752.8	748.9	744.9	740.9	738.3
55°	694.0	693.7	693.4	693.1	692.9	690.9	687.2	683.4	679.8	676.1	672.9
57.5°	628.3	627.4	626.4	625.5	624.4	622.5	619.5	616.5	613.6	610.7	607.8
60°	581.1	580.8	580.5	580.2	579.9	578.2	574.7	571.3	567.9	564.5	561.8
62.5°	539.0	538.3	537.5	536.8	536.1	534.0	530.6	527.2	523.8	520.3	517.7
65°	473.3	471.9	470.5	469.1	467.7	465.5	462.7	459.9	456.9	454.1	451.9
67.5°	403.9	402.6	401.3	400.1	398.8	397.1	394.9	392.8	390.6	388.4	386.4
70°	361.7	360.1	358.4	356.7	355.0	353.2	351.5	349.8	348.1	346.4	344.4
72.5°	317.6	316.4	315.1	313.9	312.6	311.0	309.1	307.2	305.2	303.2	301.5
75°	250.2	249.0	247.9	246.8	245.6	244.6	243.7	242.9	242.0	241.2	239.8
77.5°	190.4	189.7	189.1	188.5	187.8	187.0	186.1	185.0	184.0	182.9	182.0
80°	151.4	150.5	149.7	148.8	148.0	147.2	146.7	146.1	145.5	145.0	144.7
82.5°	113.4	113.2	113.1	112.9	112.7	112.5	112.4	112.4	112.3	112.2	111.6
85°	66.7	66.2	65.6	65.0	64.5	64.2	64.2	64.2	64.2	64.2	63.5
87.5°	26.9	26.5	26.1	25.7	25.4	25.4	25.5	25.7	25.9	26.1	26.0
90°	0.8	2.4	4.1	5.7	7.3	9.1	11.3	13.4	15.6	17.7	18.4
92.5°	17.8	18.9	20.1	21.2	22.2	23.5	24.7	25.9	27.1	28.3	28.8
95°	43.5	44.6	45.8	46.9	48.1	49.3	50.6	51.9	53.3	54.6	55.2
97.5°	77.2	78.0	78.9	79.7	80.7	81.5	82.5	83.4	84.4	85.3	86.1
100°	100.2	101.2	102.2	103.2	104.2	105.1	105.8	106.7	107.5	108.3	108.9
102.5°	126.8	127.3	127.9	128.6	129.1	130.0	131.0	132.1	133.2	134.3	134.8
105°	165.8	166.2	166.5	166.8	167.1	168.1	169.5	171.0	172.5	173.9	173.9
107.5°	211.2	211.4	211.6	211.8	212.0	212.4	213.0	213.6	214.1	214.7	215.3
110°	239.5	239.8	240.2	240.4	240.8	241.1	241.5	241.8	242.1	242.4	243.1



TEST NUMBER: P332025-830

CATALOG NUMBER: S123DIP-S1000D805U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	269.0	269.2	269.4	269.6	269.8	269.8	269.9	270.0	270.1	270.1	271.0
115°	313.2	313.7	314.1	314.6	315.2	315.3	314.9	314.6	314.2	314.0	314.1
117.5°	357.7	358.1	358.4	358.6	359.0	358.9	358.5	358.1	357.7	357.2	357.2
120°	385.4	386.3	387.4	388.3	389.4	389.5	388.6	387.8	387.0	386.2	386.0
122.5°	414.3	415.0	415.8	416.4	417.2	417.4	416.9	416.5	416.0	415.7	415.2
125°	458.4	458.8	459.3	459.9	460.3	460.4	460.1	459.8	459.4	459.1	458.5
127.5°	499.1	500.1	501.1	502.2	503.2	503.6	503.2	502.8	502.5	502.1	501.2
130°	526.1	527.4	528.8	530.1	531.4	531.8	531.3	530.8	530.4	529.8	529.1
132.5°	553.3	554.6	555.9	557.2	558.6	559.0	558.6	558.3	557.9	557.5	556.8
135°	594.7	595.7	596.6	597.7	598.6	599.1	598.9	598.7	598.5	598.4	597.8
137.5°	633.0	633.9	634.6	635.5	636.3	636.9	637.3	637.7	638.2	638.6	637.9
140°	659.5	660.3	661.2	662.0	662.8	663.3	663.5	663.6	663.8	663.9	663.8
142.5°	683.7	684.6	685.3	686.2	687.0	687.6	687.9	688.2	688.4	688.7	688.5
145°	721.4	721.8	722.1	722.5	722.7	723.1	723.7	724.2	724.6	725.1	725.0
147.5°	754.5	755.1	755.6	756.2	756.9	757.3	757.8	758.3	758.7	759.2	759.2
150°	777.4	777.8	778.1	778.4	778.7	779.1	779.4	779.8	780.0	780.4	780.4
152.5°	796.4	796.7	797.2	797.7	798.1	798.5	798.7	798.9	799.1	799.3	799.6
155°	826.0	826.0	826.0	826.0	826.0	826.1	826.3	826.5	826.7	826.8	827.5
157.5°	851.4	851.2	851.0	850.8	850.6	850.6	850.7	850.9	851.0	851.1	851.9
160°	867.3	867.0	866.7	866.4	866.0	865.9	865.9	865.9	865.9	865.9	866.7
162.5°	881.5	881.1	880.6	880.1	879.7	879.5	879.7	879.8	879.9	880.1	880.8
165°	899.8	899.3	898.8	898.3	897.8	897.6	897.6	897.6	897.6	897.6	898.5
167.5°	914.4	913.7	913.0	912.4	911.7	911.5	911.6	911.7	911.9	912.0	913.0
170°	922.7	922.0	921.3	920.7	920.0	919.6	919.6	919.6	919.6	919.6	920.9
172.5°	929.1	928.5	927.8	927.2	926.5	926.1	926.1	926.1	926.1	926.1	927.2
175°	935.9	935.2	934.6	934.0	933.3	932.9	932.9	932.9	932.9	932.9	934.0
177.5°	938.7	938.2	937.6	937.1	936.6	936.3	936.3	936.3	936.3	936.3	937.1
180°	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1



TEST NUMBER: P332025-830

CATALOG NUMBER: S123DIP-S1000D805U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0
2.5°	1486.2	1488.6	1490.8	1491.9	1491.6	1491.4	1491.1	1490.9
5°	1478.4	1481.2	1484.1	1485.3	1484.7	1484.1	1483.6	1483.0
7.5°	1462.7	1465.3	1467.8	1469.0	1468.6	1468.3	1467.9	1467.5
10°	1448.3	1450.9	1453.5	1454.4	1453.9	1453.3	1452.7	1452.2
12.5°	1432.6	1434.5	1436.3	1437.1	1436.8	1436.4	1436.1	1435.8
15°	1404.1	1406.4	1408.7	1409.0	1407.3	1405.5	1403.8	1402.1
17.5°	1368.1	1369.7	1371.3	1371.8	1371.2	1370.6	1369.9	1369.3
20°	1341.5	1342.7	1343.9	1344.0	1343.1	1342.3	1341.4	1340.6
22.5°	1313.4	1314.3	1315.2	1315.1	1314.1	1313.0	1311.9	1310.8
25°	1266.7	1267.1	1267.3	1267.1	1266.1	1265.3	1264.4	1263.6
27.5°	1217.1	1217.3	1217.6	1217.1	1216.1	1214.9	1213.9	1212.8
30°	1182.8	1182.8	1182.8	1181.8	1179.8	1177.8	1175.8	1173.7
32.5°	1146.7	1145.2	1143.6	1142.2	1141.1	1140.0	1139.0	1137.8
35°	1088.3	1086.6	1084.9	1083.3	1081.9	1080.4	1079.0	1077.6
37.5°	1027.8	1025.8	1023.7	1022.2	1021.3	1020.4	1019.5	1018.6
40°	988.4	986.1	983.8	982.0	980.9	979.8	978.6	977.5
42.5°	947.3	945.0	942.7	941.0	939.9	938.8	937.6	936.5
45°	886.0	882.6	879.2	876.8	875.3	873.9	872.5	871.0
47.5°	821.4	818.1	814.7	812.5	811.2	809.9	808.7	807.4
50°	778.8	775.7	772.5	770.2	768.5	766.7	765.0	763.3
52.5°	735.6	732.9	730.3	728.0	726.3	724.6	722.9	721.2
55°	669.8	666.7	663.5	661.2	659.8	658.4	657.0	655.5
57.5°	605.0	602.3	599.5	597.2	595.6	593.9	592.3	590.6
60°	559.3	556.8	554.2	552.2	550.7	549.3	547.9	546.5
62.5°	515.2	512.6	510.0	508.3	507.3	506.3	505.4	504.4
65°	449.6	447.2	445.0	443.5	442.6	441.8	440.8	440.0
67.5°	384.5	382.5	380.5	378.9	377.7	376.5	375.2	374.1
70°	342.3	340.4	338.4	336.7	335.3	333.8	332.4	330.9
72.5°	299.7	297.9	296.1	294.9	294.2	293.4	292.8	292.0
75°	238.4	236.9	235.4	234.3	233.5	232.6	231.8	230.9
77.5°	181.0	180.0	179.1	178.6	178.6	178.6	178.6	178.6
80°	144.4	144.1	143.8	143.6	143.6	143.6	143.6	143.6
82.5°	111.1	110.6	110.1	109.7	109.4	109.2	109.1	108.8
85°	63.0	62.4	61.8	61.5	61.5	61.5	61.5	61.5
87.5°	25.9	25.8	25.7	25.7	25.7	25.8	25.9	26.0
90°	19.0	19.6	20.3	20.8	21.1	21.5	21.8	22.1
92.5°	29.3	29.9	30.3	30.5	30.3	30.2	30.0	29.8
95°	55.8	56.5	57.1	57.5	57.5	57.5	57.5	57.5
97.5°	86.8	87.6	88.3	88.7	88.6	88.6	88.5	88.4
100°	109.3	109.8	110.3	110.7	111.0	111.3	111.7	112.0
102.5°	135.3	135.7	136.2	136.5	136.4	136.3	136.3	136.2
105°	173.9	173.9	173.9	174.1	174.4	174.7	175.0	175.4
107.5°	215.7	216.3	216.9	217.0	216.8	216.6	216.4	216.2
110°	243.7	244.4	245.1	245.2	244.9	244.6	244.2	243.9



TEST NUMBER: P332025-830

CATALOG NUMBER: S123DIP-S1000D805U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	271.7	272.5	273.3	273.6	273.6	273.5	273.4	273.4
115°	314.2	314.4	314.6	314.6	314.4	314.2	314.1	314.0
117.5°	357.2	357.1	357.1	356.8	356.5	356.0	355.5	355.1
120°	385.8	385.7	385.5	385.2	384.9	384.6	384.3	383.9
122.5°	414.8	414.3	414.0	413.5	413.0	412.6	412.1	411.6
125°	457.8	457.1	456.5	455.8	455.2	454.5	453.8	453.2
127.5°	500.3	499.4	498.5	497.7	496.9	496.2	495.4	494.6
130°	528.6	527.9	527.3	526.3	525.2	524.1	522.9	521.7
132.5°	556.0	555.2	554.4	553.6	552.7	551.8	550.9	550.1
135°	597.1	596.4	595.8	595.3	594.9	594.7	594.3	594.0
137.5°	637.3	636.6	635.8	635.2	634.6	634.0	633.4	632.7
140°	663.6	663.5	663.3	662.7	661.5	660.3	659.2	658.1
142.5°	688.4	688.2	688.1	687.6	686.6	685.8	684.9	684.0
145°	724.8	724.6	724.4	724.1	723.4	722.7	722.1	721.4
147.5°	759.2	759.2	759.2	758.7	757.7	756.7	755.7	754.8
150°	780.4	780.4	780.4	780.0	778.9	778.0	776.9	776.0
152.5°	799.7	800.0	800.3	800.0	799.2	798.3	797.5	796.6
155°	828.1	828.8	829.4	829.2	828.0	826.9	825.8	824.6
157.5°	852.5	853.2	853.8	853.8	852.9	852.0	851.0	850.1
160°	867.5	868.4	869.1	869.2	868.6	867.9	867.2	866.6
162.5°	881.7	882.5	883.4	883.2	882.1	881.1	880.1	879.0
165°	899.6	900.5	901.5	901.4	900.3	899.1	898.0	896.8
167.5°	914.1	915.0	916.1	916.1	915.0	914.1	913.0	912.0
170°	922.0	923.1	924.3	924.3	923.1	922.0	920.9	919.6
172.5°	928.2	929.3	930.2	930.2	929.0	927.8	926.7	925.6
175°	934.9	935.9	936.9	936.8	935.7	934.5	933.3	932.2
177.5°	937.9	938.7	939.4	939.4	938.5	937.5	936.7	935.8
180°	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1

(END OF REPORT)