

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331934

Luminaire Tested: **S123DIP-S560D805U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331934
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D805U835-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5530.1 lumens
Efficiency: N/A
Efficacy: 144.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331934

CATALOG NUMBER: S123DIP-S560D805U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331934

CATALOG NUMBER: S123DIP-S560D805U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	84	87	84	80	77	69	67	65	55	54	52	43	42	41	35
2	87	80	74	69	79	73	68	64	60	57	53	49	46	44	38	36	34	29
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29	25
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	27	25	21
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	19
6	61	49	41	36	56	46	38	33	38	33	29	31	27	24	24	22	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	18	15	13
9	49	37	29	24	45	34	27	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9590	9590	9590
5°	9634	9502	9568
10°	9570	9419	9477
15°	9458	9313	9331
20°	9328	9160	9170
25°	9152	8980	8961
30°	8959	8779	8712
35°	8757	8566	8456
40°	8546	8331	8202
45°	8315	8115	7917
50°	8081	7850	7633
55°	7777	7576	7345
60°	7470	7255	7025
65°	7200	6907	6691
70°	6798	6508	6219
75°	6213	5989	5735
80°	5604	5368	5318
85°	4915	4730	4545



TEST NUMBER: P331934

CATALOG NUMBER: S123DIP-S560D805U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.9	1.5
10°-20°	237.0	4.3
20°-30°	350.0	6.3
30°-40°	408.9	7.4
40°-50°	411.1	7.4
50°-60°	361.1	6.5
60°-70°	269.0	4.9
70°-80°	153.3	2.8
80°-90°	46.9	0.8
90°-100°	38.3	0.7
100°-110°	182.3	3.3
110°-120°	438.0	7.9
120°-130°	557.7	10.1
130°-140°	595.9	10.8
140°-150°	557.2	10.1
150°-160°	449.5	8.1
160°-170°	290.1	5.2
170°-180°	100.0	1.8
0°-30°	670.9	12.1
0°-40°	1079.8	19.5
0°-60°	1851.9	33.5
0°-90°	2321.1	42.0
90°-120°	658.6	11.9
90°-150°	2369.4	42.8
90°-180°	3209.0	58.0
0°-180°	5530.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	891	891	891	891	891	
5°	892	888	879	887	886	84
15°	849	845	836	841	837	239
25°	771	766	756	757	754	355
35°	666	662	652	647	644	417
45°	546	543	533	524	520	421
55°	414	413	404	396	391	371
65°	283	279	271	265	263	279
75°	149	146	144	140	138	160
85°	40	38	38	37	37	44
90°	1	9	19	22	24	4
95°	48	18	24	29	30	59
105°	233	237	171	41	34	247
115°	437	442	449	456	460	431
125°	616	622	625	627	629	550
135°	767	772	775	777	775	590
145°	885	890	892	894	894	554
155°	975	973	974	978	973	449
165°	1028	1026	1025	1031	1026	290
175°	1052	1049	1049	1054	1048	100
180°	1052	1052	1052	1052	1052	



TEST NUMBER: P331934

CATALOG NUMBER: S123DIP-S560D805U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9
2.5°	893.9	893.4	892.9	892.3	891.8	890.7	889.2	887.7	886.3	884.8	886.1
5°	891.6	890.8	889.9	889.1	888.2	886.9	885.0	883.1	881.3	879.4	881.1
7.5°	882.9	882.1	881.2	880.4	879.5	878.1	876.2	874.2	872.3	870.4	871.9
10°	875.6	874.7	873.9	873.0	872.2	870.6	868.4	866.2	864.0	861.8	863.3
12.5°	865.8	865.0	864.3	863.6	862.9	861.5	859.4	857.3	855.3	853.2	854.3
15°	848.7	848.1	847.4	846.7	846.0	844.6	842.4	840.2	837.9	835.7	837.1
17.5°	829.0	828.1	827.2	826.3	825.4	823.9	821.7	819.5	817.3	815.0	816.0
20°	814.3	813.3	812.2	811.2	810.2	808.6	806.4	804.2	801.9	799.7	800.4
22.5°	797.7	796.7	795.7	794.7	793.6	792.0	789.8	787.6	785.4	783.2	783.7
25°	770.6	769.6	768.6	767.6	766.5	764.9	762.7	760.5	758.3	756.1	756.2
27.5°	741.7	740.7	739.7	738.7	737.7	736.0	733.6	731.3	728.9	726.5	726.6
30°	720.8	720.0	719.1	718.3	717.4	715.8	713.4	711.0	708.7	706.3	706.3
32.5°	700.0	698.9	697.7	696.6	695.5	694.0	692.2	690.3	688.5	686.7	685.7
35°	666.4	665.4	664.4	663.4	662.4	660.7	658.5	656.3	654.1	651.9	650.9
37.5°	632.1	630.8	629.5	628.2	626.9	625.2	622.9	620.7	618.4	616.2	615.0
40°	608.2	607.2	606.2	605.2	604.1	602.4	600.0	597.7	595.3	592.9	591.5
42.5°	584.3	583.2	582.0	580.8	579.7	577.9	575.5	573.2	570.8	568.4	567.0
45°	546.2	545.5	544.8	544.1	543.4	542.0	539.8	537.6	535.4	533.1	531.1
47.5°	508.3	507.3	506.4	505.4	504.4	502.8	500.8	498.7	496.6	494.5	492.5
50°	482.6	481.7	480.9	480.0	479.2	477.7	475.4	473.2	471.0	468.8	466.9
52.5°	455.6	455.0	454.5	453.9	453.3	451.8	449.5	447.2	444.8	442.5	440.9
55°	414.4	414.2	414.1	413.9	413.7	412.5	410.3	408.1	405.9	403.7	401.8
57.5°	375.2	374.6	374.0	373.5	372.9	371.7	369.9	368.2	366.4	364.6	363.0
60°	347.0	346.8	346.7	346.5	346.3	345.2	343.2	341.1	339.1	337.0	335.5
62.5°	321.9	321.4	321.0	320.6	320.1	318.9	316.8	314.8	312.7	310.7	309.2
65°	282.7	281.8	281.0	280.1	279.3	278.0	276.3	274.6	272.9	271.2	269.8
67.5°	241.1	240.4	239.6	238.9	238.1	237.1	235.8	234.5	233.2	232.0	230.8
70°	216.0	215.0	214.0	213.0	211.9	210.9	209.9	208.9	207.8	206.8	205.6
72.5°	189.7	188.9	188.2	187.4	186.7	185.7	184.6	183.4	182.2	181.1	180.0
75°	149.4	148.7	148.0	147.3	146.7	146.1	145.5	145.0	144.5	144.0	143.2
77.5°	113.7	113.3	112.9	112.6	112.2	111.7	111.1	110.5	109.8	109.2	108.7
80°	90.4	89.9	89.4	88.9	88.3	87.9	87.6	87.2	86.9	86.6	86.4
82.5°	67.7	67.6	67.5	67.4	67.3	67.2	67.2	67.1	67.0	67.0	66.6
85°	39.8	39.5	39.2	38.8	38.5	38.3	38.3	38.3	38.3	38.3	38.0
87.5°	16.1	16.0	16.0	15.9	15.8	16.0	16.3	16.6	16.9	17.2	17.2
90°	0.8	2.5	4.3	6.0	7.7	9.7	12.0	14.2	16.5	18.8	19.5
92.5°	14.5	14.1	13.6	13.1	12.6	13.2	14.9	16.6	18.3	20.0	21.1
95°	47.7	40.6	33.4	26.3	19.2	16.6	18.5	20.4	22.3	24.2	25.5
97.5°	95.8	92.7	89.5	86.3	83.1	75.2	62.7	50.2	37.7	25.2	26.6
100°	132.1	135.6	139.1	142.5	146.0	134.2	107.1	80.0	52.9	25.8	27.2
102.5°	173.4	175.9	178.4	180.9	183.4	169.9	140.3	110.6	81.0	51.4	47.1
105°	233.0	234.9	236.8	238.7	240.6	233.8	218.1	202.5	186.8	171.2	140.5
107.5°	295.8	297.4	298.9	300.4	301.9	303.9	306.4	308.9	311.3	313.8	291.3
110°	337.7	339.1	340.5	341.9	343.3	344.9	346.9	348.8	350.7	352.6	346.9



TEST NUMBER: P331934

CATALOG NUMBER: S123DIP-S560D805U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	377.8	379.0	380.3	381.5	382.8	384.3	386.3	388.2	390.1	392.0	392.1
115°	437.0	438.1	439.1	440.2	441.2	442.5	444.1	445.6	447.2	448.8	450.5
117.5°	494.4	495.7	497.0	498.3	499.5	500.6	501.4	502.2	503.0	503.8	505.2
120°	530.1	531.6	533.2	534.7	536.3	537.4	537.9	538.4	538.9	539.4	540.8
122.5°	566.3	567.6	568.9	570.2	571.5	572.4	573.1	573.8	574.4	575.1	576.1
125°	616.1	617.4	618.8	620.2	621.6	622.7	623.4	624.0	624.7	625.4	625.8
127.5°	664.2	665.6	667.0	668.4	669.8	670.9	671.7	672.6	673.4	674.2	674.8
130°	694.2	695.6	697.0	698.4	699.8	700.8	701.5	702.2	702.9	703.6	704.3
132.5°	723.0	724.4	725.8	727.2	728.6	729.5	730.1	730.6	731.2	731.8	732.5
135°	766.9	768.0	769.0	770.1	771.1	772.0	772.7	773.4	774.1	774.8	775.3
137.5°	804.5	805.8	807.1	808.4	809.7	810.6	811.0	811.4	811.7	812.1	813.0
140°	829.5	830.5	831.6	832.6	833.7	834.4	835.0	835.5	836.0	836.5	837.2
142.5°	852.6	853.7	854.7	855.8	856.8	857.6	858.1	858.6	859.1	859.7	860.2
145°	885.0	886.2	887.4	888.6	889.9	890.6	891.0	891.3	891.7	892.0	892.4
147.5°	915.5	916.3	917.1	917.9	918.7	919.3	919.6	919.9	920.3	920.6	921.0
150°	934.2	934.8	935.3	935.8	936.3	936.8	937.1	937.5	937.8	938.2	938.5
152.5°	951.1	951.4	951.6	951.9	952.1	952.3	952.5	952.7	953.0	953.2	953.8
155°	974.9	974.6	974.2	973.9	973.5	973.4	973.6	973.8	973.9	974.1	975.0
157.5°	993.3	993.3	993.3	993.2	993.2	993.1	992.9	992.8	992.6	992.4	993.5
160°	1004.6	1004.4	1004.3	1004.1	1003.9	1003.7	1003.6	1003.4	1003.2	1003.0	1004.1
162.5°	1015.2	1014.8	1014.3	1013.9	1013.4	1013.1	1012.9	1012.8	1012.6	1012.4	1013.6
165°	1028.1	1027.5	1027.0	1026.5	1026.0	1025.6	1025.5	1025.3	1025.1	1024.9	1026.3
167.5°	1038.1	1037.4	1036.7	1036.0	1035.3	1034.9	1034.9	1034.9	1034.9	1034.9	1036.3
170°	1043.7	1043.0	1042.3	1041.6	1040.9	1040.6	1040.6	1040.6	1040.6	1040.6	1042.0
172.5°	1047.4	1046.6	1045.8	1044.9	1044.1	1043.8	1043.9	1044.0	1044.2	1044.3	1045.7
175°	1052.3	1051.4	1050.6	1049.7	1048.8	1048.5	1048.6	1048.8	1049.0	1049.2	1050.4
177.5°	1053.5	1052.9	1052.2	1051.5	1050.8	1050.5	1050.6	1050.8	1050.9	1051.0	1052.2
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P331934

CATALOG NUMBER: S123DIP-S560D805U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9
2.5°	887.5	888.8	890.2	890.8	890.7	890.5	890.4	890.3
5°	882.8	884.5	886.2	886.9	886.5	886.2	885.9	885.5
7.5°	873.4	874.9	876.5	877.1	876.9	876.7	876.5	876.3
10°	864.8	866.4	867.9	868.5	868.2	867.8	867.5	867.1
12.5°	855.4	856.6	857.7	858.1	857.9	857.7	857.5	857.3
15°	838.5	839.8	841.2	841.3	840.3	839.3	838.3	837.3
17.5°	817.0	817.9	818.9	819.1	818.8	818.4	818.0	817.6
20°	801.1	801.8	802.4	802.5	802.0	801.5	801.0	800.5
22.5°	784.3	784.8	785.4	785.3	784.7	784.0	783.4	782.7
25°	756.4	756.6	756.7	756.6	756.1	755.6	755.0	754.5
27.5°	726.8	726.9	727.0	726.8	726.1	725.5	724.8	724.2
30°	706.3	706.3	706.3	705.7	704.5	703.3	702.1	700.9
32.5°	684.8	683.8	682.8	682.0	681.4	680.8	680.1	679.5
35°	649.8	648.8	647.8	646.9	646.0	645.2	644.3	643.5
37.5°	613.7	612.5	611.3	610.4	609.9	609.3	608.8	608.2
40°	590.2	588.8	587.5	586.4	585.7	585.1	584.4	583.7
42.5°	565.7	564.3	562.9	561.9	561.2	560.6	559.9	559.2
45°	529.1	527.0	525.0	523.5	522.7	521.8	521.0	520.1
47.5°	490.5	488.5	486.5	485.1	484.4	483.6	482.9	482.1
50°	465.1	463.2	461.3	459.9	458.8	457.8	456.8	455.8
52.5°	439.3	437.7	436.1	434.7	433.7	432.7	431.7	430.7
55°	399.9	398.1	396.2	394.8	394.0	393.1	392.3	391.4
57.5°	361.3	359.6	358.0	356.6	355.6	354.7	353.7	352.7
60°	334.0	332.5	330.9	329.7	328.9	328.0	327.2	326.3
62.5°	307.6	306.1	304.6	303.5	302.9	302.4	301.8	301.2
65°	268.4	267.1	265.7	264.8	264.3	263.8	263.3	262.7
67.5°	229.6	228.4	227.2	226.2	225.5	224.8	224.1	223.4
70°	204.4	203.3	202.1	201.0	200.2	199.3	198.5	197.6
72.5°	179.0	177.9	176.9	176.1	175.7	175.2	174.8	174.3
75°	142.3	141.5	140.6	139.9	139.4	138.9	138.4	137.9
77.5°	108.1	107.5	106.9	106.6	106.6	106.6	106.6	106.6
80°	86.2	86.0	85.9	85.8	85.8	85.8	85.8	85.8
82.5°	66.3	66.0	65.7	65.5	65.4	65.2	65.1	65.0
85°	37.6	37.3	36.9	36.8	36.8	36.8	36.8	36.8
87.5°	17.2	17.2	17.2	17.3	17.4	17.4	17.5	17.6
90°	20.2	20.8	21.5	22.1	22.4	22.8	23.1	23.5
92.5°	22.2	23.3	24.5	25.1	25.3	25.5	25.7	26.0
95°	26.7	27.9	29.1	29.7	29.7	29.7	29.7	29.7
97.5°	28.0	29.3	30.7	31.5	31.7	31.9	32.0	32.2
100°	28.6	30.0	31.4	32.1	32.3	32.5	32.7	32.8
102.5°	42.8	38.5	34.2	32.2	32.5	32.8	33.1	33.5
105°	109.7	79.0	48.2	33.0	33.4	33.7	34.1	34.4
107.5°	268.7	246.2	223.6	200.7	177.6	154.4	131.2	108.0
110°	341.1	335.4	329.7	314.4	289.5	264.7	239.8	215.0



TEST NUMBER: P331934

CATALOG NUMBER: S123DIP-S560D805U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	392.2	392.3	392.4	389.8	384.6	379.3	374.1	368.9
115°	452.2	454.0	455.7	456.9	457.6	458.3	459.0	459.7
117.5°	506.6	508.0	509.3	510.1	510.3	510.4	510.5	510.7
120°	542.2	543.6	545.0	545.7	545.7	545.7	545.7	545.7
122.5°	577.0	578.0	579.0	579.5	579.7	579.8	580.0	580.1
125°	626.1	626.5	626.8	627.2	627.5	627.9	628.2	628.6
127.5°	675.3	675.9	676.4	676.5	676.2	675.9	675.5	675.2
130°	705.0	705.7	706.4	706.6	706.2	705.9	705.5	705.2
132.5°	733.1	733.8	734.5	734.6	734.2	733.7	733.2	732.7
135°	775.8	776.3	776.8	776.8	776.3	775.8	775.3	774.8
137.5°	813.8	814.6	815.5	815.7	815.4	815.0	814.7	814.3
140°	837.9	838.6	839.3	839.5	839.1	838.8	838.4	838.1
142.5°	860.8	861.3	861.9	861.9	861.4	860.9	860.5	860.0
145°	892.7	893.1	893.4	893.6	893.6	893.6	893.6	893.6
147.5°	921.3	921.7	922.0	921.8	921.0	920.2	919.4	918.6
150°	938.8	939.2	939.5	939.5	938.9	938.4	937.9	937.4
152.5°	954.4	955.0	955.7	955.6	954.8	954.0	953.2	952.4
155°	975.9	976.7	977.6	977.5	976.5	975.4	974.4	973.3
157.5°	994.5	995.5	996.6	996.4	995.1	993.7	992.4	991.0
160°	1005.1	1006.2	1007.2	1007.1	1005.9	1004.7	1003.5	1002.3
162.5°	1014.8	1016.0	1017.1	1017.2	1016.1	1015.0	1014.0	1012.9
165°	1027.7	1029.1	1030.5	1030.6	1029.4	1028.1	1026.9	1025.7
167.5°	1037.7	1039.1	1040.5	1040.5	1039.1	1037.7	1036.3	1034.9
170°	1043.3	1044.7	1046.1	1046.1	1044.7	1043.3	1042.0	1040.6
172.5°	1047.1	1048.5	1049.9	1049.8	1048.3	1046.8	1045.2	1043.7
175°	1051.6	1052.8	1054.0	1053.9	1052.6	1051.2	1049.8	1048.4
177.5°	1053.3	1054.4	1055.5	1055.4	1054.0	1052.6	1051.2	1049.8
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3

(END OF REPORT)