

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331935

Luminaire Tested: **S123DIP-S560D805U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D805U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5078.7 lumens
Efficiency: N/A
Efficacy: 132.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331935

CATALOG NUMBER: S123DIP-S560D805U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331935

CATALOG NUMBER: S123DIP-S560D805U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46
1	97	92	89	85	89	85	82	79	71	68	66	58	56	55	46	45	44	38
2	88	81	75	69	81	74	69	64	62	58	55	51	48	46	40	39	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	36	33	31	27
4	73	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27	23
5	67	56	48	42	62	52	44	39	43	38	34	36	32	29	29	26	24	20
6	62	50	42	36	57	46	39	34	39	34	29	32	28	25	26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9590	9590	9590
5°	9634	9502	9568
10°	9570	9419	9477
15°	9458	9313	9331
20°	9328	9160	9170
25°	9152	8980	8961
30°	8959	8779	8712
35°	8757	8566	8456
40°	8546	8331	8202
45°	8315	8115	7917
50°	8081	7850	7633
55°	7777	7576	7345
60°	7470	7255	7025
65°	7200	6907	6691
70°	6798	6508	6219
75°	6213	5989	5735
80°	5604	5368	5318
85°	4915	4730	4545



TEST NUMBER: P331935

CATALOG NUMBER: S123DIP-S560D805U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.9	1.7
10°-20°	237.0	4.7
20°-30°	350.0	6.9
30°-40°	408.9	8.1
40°-50°	411.1	8.1
50°-60°	361.1	7.1
60°-70°	269.0	5.3
70°-80°	153.3	3.0
80°-90°	46.9	0.9
90°-100°	64.8	1.3
100°-110°	194.1	3.8
110°-120°	330.1	6.5
120°-130°	434.2	8.5
130°-140°	488.0	9.6
140°-150°	479.7	9.4
150°-160°	403.8	8.0
160°-170°	268.8	5.3
170°-180°	94.1	1.9
0°-30°	670.9	13.2
0°-40°	1079.8	21.3
0°-60°	1851.9	36.5
0°-90°	2321.1	45.7
90°-120°	589.0	11.6
90°-150°	1990.8	39.2
90°-180°	2758.0	54.3
0°-180°	5078.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	891	891	891	891	891	
5°	892	888	879	887	886	84
15°	849	845	836	841	837	239
25°	771	766	756	757	754	355
35°	666	662	652	647	644	417
45°	546	543	533	524	520	421
55°	414	413	404	396	391	371
65°	283	279	271	265	263	279
75°	149	146	144	140	138	160
85°	40	38	38	37	37	44
90°	1	9	19	22	24	5
95°	46	52	58	61	61	52
105°	176	178	184	185	186	188
115°	332	334	333	334	333	329
125°	486	488	487	484	481	434
135°	631	635	635	632	630	486
145°	765	767	769	768	765	478
155°	876	876	877	880	875	403
165°	955	952	952	956	952	269
175°	993	990	990	994	989	94
180°	995	995	995	995	995	



TEST NUMBER: P331935

CATALOG NUMBER: S123DIP-S560D805U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9
2.5°	893.9	893.4	892.9	892.3	891.8	890.7	889.2	887.7	886.3	884.8	886.1
5°	891.6	890.8	889.9	889.1	888.2	886.9	885.0	883.1	881.3	879.4	881.1
7.5°	882.9	882.1	881.2	880.4	879.5	878.1	876.2	874.2	872.3	870.4	871.9
10°	875.6	874.7	873.9	873.0	872.2	870.6	868.4	866.2	864.0	861.8	863.3
12.5°	865.8	865.0	864.3	863.6	862.9	861.5	859.4	857.3	855.3	853.2	854.3
15°	848.7	848.1	847.4	846.7	846.0	844.6	842.4	840.2	837.9	835.7	837.1
17.5°	829.0	828.1	827.2	826.3	825.4	823.9	821.7	819.5	817.3	815.0	816.0
20°	814.3	813.3	812.2	811.2	810.2	808.6	806.4	804.2	801.9	799.7	800.4
22.5°	797.7	796.7	795.7	794.7	793.6	792.0	789.8	787.6	785.4	783.2	783.7
25°	770.6	769.6	768.6	767.6	766.5	764.9	762.7	760.5	758.3	756.1	756.2
27.5°	741.7	740.7	739.7	738.7	737.7	736.0	733.6	731.3	728.9	726.5	726.6
30°	720.8	720.0	719.1	718.3	717.4	715.8	713.4	711.0	708.7	706.3	706.3
32.5°	700.0	698.9	697.7	696.6	695.5	694.0	692.2	690.3	688.5	686.7	685.7
35°	666.4	665.4	664.4	663.4	662.4	660.7	658.5	656.3	654.1	651.9	650.9
37.5°	632.1	630.8	629.5	628.2	626.9	625.2	622.9	620.7	618.4	616.2	615.0
40°	608.2	607.2	606.2	605.2	604.1	602.4	600.0	597.7	595.3	592.9	591.5
42.5°	584.3	583.2	582.0	580.8	579.7	577.9	575.5	573.2	570.8	568.4	567.0
45°	546.2	545.5	544.8	544.1	543.4	542.0	539.8	537.6	535.4	533.1	531.1
47.5°	508.3	507.3	506.4	505.4	504.4	502.8	500.8	498.7	496.6	494.5	492.5
50°	482.6	481.7	480.9	480.0	479.2	477.7	475.4	473.2	471.0	468.8	466.9
52.5°	455.6	455.0	454.5	453.9	453.3	451.8	449.5	447.2	444.8	442.5	440.9
55°	414.4	414.2	414.1	413.9	413.7	412.5	410.3	408.1	405.9	403.7	401.8
57.5°	375.2	374.6	374.0	373.5	372.9	371.7	369.9	368.2	366.4	364.6	363.0
60°	347.0	346.8	346.7	346.5	346.3	345.2	343.2	341.1	339.1	337.0	335.5
62.5°	321.9	321.4	321.0	320.6	320.1	318.9	316.8	314.8	312.7	310.7	309.2
65°	282.7	281.8	281.0	280.1	279.3	278.0	276.3	274.6	272.9	271.2	269.8
67.5°	241.1	240.4	239.6	238.9	238.1	237.1	235.8	234.5	233.2	232.0	230.8
70°	216.0	215.0	214.0	213.0	211.9	210.9	209.9	208.9	207.8	206.8	205.6
72.5°	189.7	188.9	188.2	187.4	186.7	185.7	184.6	183.4	182.2	181.1	180.0
75°	149.4	148.7	148.0	147.3	146.7	146.1	145.5	145.0	144.5	144.0	143.2
77.5°	113.7	113.3	112.9	112.6	112.2	111.7	111.1	110.5	109.8	109.2	108.7
80°	90.4	89.9	89.4	88.9	88.3	87.9	87.6	87.2	86.9	86.6	86.4
82.5°	67.7	67.6	67.5	67.4	67.3	67.2	67.2	67.1	67.0	67.0	66.6
85°	39.8	39.5	39.2	38.8	38.5	38.3	38.3	38.3	38.3	38.3	38.0
87.5°	16.1	16.0	16.0	15.9	15.8	16.0	16.3	16.6	16.9	17.2	17.2
90°	0.8	2.5	4.3	6.0	7.7	9.7	12.0	14.2	16.5	18.8	19.5
92.5°	18.9	20.1	21.3	22.5	23.6	24.9	26.2	27.5	28.7	30.0	30.6
95°	46.1	47.3	48.6	49.8	51.0	52.3	53.7	55.1	56.5	57.9	58.6
97.5°	81.9	82.8	83.7	84.6	85.6	86.5	87.5	88.5	89.5	90.5	91.3
100°	106.3	107.4	108.4	109.5	110.5	111.5	112.3	113.2	114.1	114.9	115.5
102.5°	134.5	135.1	135.7	136.4	137.0	137.9	139.0	140.2	141.3	142.5	143.0
105°	175.9	176.3	176.6	177.0	177.3	178.3	179.8	181.4	183.0	184.5	184.5
107.5°	224.1	224.3	224.5	224.7	224.9	225.3	226.0	226.6	227.2	227.8	228.4
110°	254.1	254.4	254.8	255.1	255.5	255.8	256.2	256.5	256.9	257.2	257.9



TEST NUMBER: P331935

CATALOG NUMBER: S123DIP-S560D805U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	285.4	285.6	285.8	286.0	286.2	286.3	286.4	286.5	286.6	286.6	287.5
115°	332.3	332.8	333.3	333.8	334.4	334.5	334.1	333.8	333.4	333.1	333.2
117.5°	379.5	379.9	380.2	380.5	380.9	380.8	380.4	379.9	379.5	379.0	379.0
120°	408.9	409.9	411.0	412.0	413.1	413.2	412.3	411.4	410.6	409.7	409.5
122.5°	439.6	440.3	441.1	441.8	442.6	442.8	442.3	441.9	441.4	441.0	440.5
125°	486.3	486.8	487.3	487.9	488.4	488.5	488.1	487.8	487.4	487.1	486.4
127.5°	529.5	530.6	531.7	532.8	533.9	534.3	533.9	533.5	533.1	532.7	531.8
130°	558.2	559.6	561.0	562.4	563.8	564.2	563.7	563.2	562.7	562.1	561.4
132.5°	587.0	588.4	589.8	591.2	592.6	593.1	592.7	592.3	591.9	591.5	590.7
135°	630.9	632.0	633.0	634.1	635.1	635.6	635.4	635.2	635.0	634.9	634.2
137.5°	671.6	672.5	673.3	674.2	675.1	675.7	676.2	676.6	677.1	677.5	676.8
140°	699.7	700.6	701.5	702.4	703.2	703.7	703.9	704.1	704.3	704.4	704.3
142.5°	725.4	726.3	727.1	728.0	728.9	729.5	729.8	730.1	730.4	730.7	730.5
145°	765.4	765.8	766.1	766.5	766.8	767.2	767.8	768.3	768.8	769.3	769.2
147.5°	800.5	801.1	801.7	802.3	803.0	803.5	804.0	804.5	805.0	805.5	805.5
150°	824.8	825.2	825.5	825.9	826.2	826.6	826.9	827.3	827.6	828.0	828.0
152.5°	844.9	845.3	845.8	846.3	846.8	847.2	847.4	847.6	847.8	848.0	848.3
155°	876.4	876.4	876.4	876.4	876.4	876.5	876.7	876.9	877.1	877.2	877.9
157.5°	903.3	903.1	902.9	902.7	902.5	902.5	902.6	902.8	902.9	903.0	903.8
160°	920.2	919.9	919.5	919.2	918.8	918.7	918.7	918.7	918.7	918.7	919.5
162.5°	935.2	934.8	934.3	933.8	933.3	933.1	933.3	933.4	933.5	933.7	934.5
165°	954.6	954.1	953.6	953.1	952.5	952.3	952.3	952.3	952.3	952.3	953.3
167.5°	970.1	969.4	968.7	968.0	967.3	967.1	967.2	967.3	967.5	967.6	968.7
170°	978.9	978.2	977.5	976.8	976.1	975.7	975.7	975.7	975.7	975.7	977.0
172.5°	985.7	985.1	984.4	983.7	983.0	982.6	982.6	982.6	982.6	982.6	983.7
175°	992.9	992.2	991.6	990.9	990.2	989.8	989.8	989.8	989.8	989.8	990.9
177.5°	995.9	995.4	994.8	994.2	993.7	993.4	993.4	993.4	993.4	993.4	994.2
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3



TEST NUMBER: P331935

CATALOG NUMBER: S123DIP-S560D805U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9
2.5°	887.5	888.8	890.2	890.8	890.7	890.5	890.4	890.3
5°	882.8	884.5	886.2	886.9	886.5	886.2	885.9	885.5
7.5°	873.4	874.9	876.5	877.1	876.9	876.7	876.5	876.3
10°	864.8	866.4	867.9	868.5	868.2	867.8	867.5	867.1
12.5°	855.4	856.6	857.7	858.1	857.9	857.7	857.5	857.3
15°	838.5	839.8	841.2	841.3	840.3	839.3	838.3	837.3
17.5°	817.0	817.9	818.9	819.1	818.8	818.4	818.0	817.6
20°	801.1	801.8	802.4	802.5	802.0	801.5	801.0	800.5
22.5°	784.3	784.8	785.4	785.3	784.7	784.0	783.4	782.7
25°	756.4	756.6	756.7	756.6	756.1	755.6	755.0	754.5
27.5°	726.8	726.9	727.0	726.8	726.1	725.5	724.8	724.2
30°	706.3	706.3	706.3	705.7	704.5	703.3	702.1	700.9
32.5°	684.8	683.8	682.8	682.0	681.4	680.8	680.1	679.5
35°	649.8	648.8	647.8	646.9	646.0	645.2	644.3	643.5
37.5°	613.7	612.5	611.3	610.4	609.9	609.3	608.8	608.2
40°	590.2	588.8	587.5	586.4	585.7	585.1	584.4	583.7
42.5°	565.7	564.3	562.9	561.9	561.2	560.6	559.9	559.2
45°	529.1	527.0	525.0	523.5	522.7	521.8	521.0	520.1
47.5°	490.5	488.5	486.5	485.1	484.4	483.6	482.9	482.1
50°	465.1	463.2	461.3	459.9	458.8	457.8	456.8	455.8
52.5°	439.3	437.7	436.1	434.7	433.7	432.7	431.7	430.7
55°	399.9	398.1	396.2	394.8	394.0	393.1	392.3	391.4
57.5°	361.3	359.6	358.0	356.6	355.6	354.7	353.7	352.7
60°	334.0	332.5	330.9	329.7	328.9	328.0	327.2	326.3
62.5°	307.6	306.1	304.6	303.5	302.9	302.4	301.8	301.2
65°	268.4	267.1	265.7	264.8	264.3	263.8	263.3	262.7
67.5°	229.6	228.4	227.2	226.2	225.5	224.8	224.1	223.4
70°	204.4	203.3	202.1	201.0	200.2	199.3	198.5	197.6
72.5°	179.0	177.9	176.9	176.1	175.7	175.2	174.8	174.3
75°	142.3	141.5	140.6	139.9	139.4	138.9	138.4	137.9
77.5°	108.1	107.5	106.9	106.6	106.6	106.6	106.6	106.6
80°	86.2	86.0	85.9	85.8	85.8	85.8	85.8	85.8
82.5°	66.3	66.0	65.7	65.5	65.4	65.2	65.1	65.0
85°	37.6	37.3	36.9	36.8	36.8	36.8	36.8	36.8
87.5°	17.2	17.2	17.2	17.3	17.4	17.4	17.5	17.6
90°	20.2	20.8	21.5	22.1	22.4	22.8	23.1	23.5
92.5°	31.1	31.7	32.2	32.4	32.2	32.0	31.8	31.6
95°	59.2	59.9	60.6	61.0	61.0	61.0	61.0	61.0
97.5°	92.1	92.9	93.7	94.1	94.0	94.0	93.9	93.8
100°	116.0	116.5	117.0	117.5	117.8	118.1	118.5	118.8
102.5°	143.5	144.0	144.5	144.8	144.7	144.6	144.6	144.5
105°	184.5	184.5	184.5	184.7	185.0	185.4	185.7	186.1
107.5°	228.9	229.5	230.1	230.2	230.0	229.8	229.6	229.4
110°	258.6	259.3	260.0	260.2	259.8	259.5	259.1	258.8



TEST NUMBER: P331935

CATALOG NUMBER: S123DIP-S560D805U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	288.3	289.1	290.0	290.3	290.3	290.2	290.1	290.1
115°	333.4	333.6	333.8	333.8	333.6	333.4	333.2	333.1
117.5°	379.0	378.9	378.9	378.6	378.2	377.7	377.2	376.7
120°	409.3	409.2	409.0	408.7	408.4	408.0	407.7	407.3
122.5°	440.1	439.6	439.2	438.7	438.2	437.7	437.2	436.7
125°	485.7	485.0	484.3	483.6	482.9	482.2	481.5	480.8
127.5°	530.8	529.8	528.9	528.0	527.2	526.4	525.6	524.8
130°	560.8	560.1	559.4	558.4	557.2	556.0	554.8	553.5
132.5°	589.9	589.0	588.2	587.3	586.4	585.4	584.5	583.6
135°	633.5	632.8	632.1	631.6	631.2	630.9	630.5	630.2
137.5°	676.1	675.4	674.6	673.9	673.3	672.6	672.0	671.3
140°	704.1	703.9	703.7	703.1	701.8	700.6	699.4	698.2
142.5°	730.4	730.2	730.0	729.5	728.5	727.6	726.6	725.7
145°	769.0	768.8	768.6	768.2	767.5	766.8	766.1	765.4
147.5°	805.5	805.5	805.5	804.9	803.9	802.8	801.8	800.8
150°	828.0	828.0	828.0	827.5	826.4	825.4	824.3	823.3
152.5°	848.5	848.8	849.1	848.8	847.9	847.0	846.1	845.2
155°	878.6	879.3	880.0	879.7	878.5	877.3	876.1	874.9
157.5°	904.5	905.2	905.9	905.8	904.9	903.9	902.9	901.9
160°	920.4	921.3	922.1	922.2	921.5	920.8	920.1	919.4
162.5°	935.4	936.3	937.2	937.0	935.9	934.8	933.7	932.6
165°	954.4	955.4	956.5	956.4	955.2	953.9	952.7	951.5
167.5°	969.8	970.8	971.9	971.9	970.8	969.8	968.7	967.6
170°	978.2	979.4	980.6	980.6	979.4	978.2	977.0	975.7
172.5°	984.8	985.9	986.9	986.9	985.6	984.4	983.2	982.0
175°	991.9	992.9	994.0	993.9	992.7	991.5	990.2	989.0
177.5°	995.1	995.9	996.7	996.7	995.7	994.7	993.8	992.8
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3

(END OF REPORT)