

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332051-830

Luminaire Tested: **S123DIP-S1165D365U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332051-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1165D365U830-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5852.0 lumens  
Efficiency: N/A  
Efficacy: 117.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 49.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332051-830

CATALOG NUMBER: S123DIP-S1165D365U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332051-830

CATALOG NUMBER: S123DIP-S1165D365U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	81	81	81	77
1	104	99	95	91	99	95	91	88	86	83	81	78	76	74	71	69	68	64
2	94	87	80	75	90	83	77	72	75	71	67	69	65	62	63	60	57	54
3	86	76	68	62	82	73	66	60	67	61	56	61	56	52	55	52	49	46
4	79	67	59	53	75	65	57	51	59	53	48	54	49	45	50	45	42	39
5	73	60	52	45	69	58	50	44	53	47	42	49	43	39	45	40	37	34
6	67	54	46	40	64	52	44	38	48	41	36	44	39	34	41	36	32	30
7	62	49	41	35	59	47	39	34	44	37	32	40	35	30	37	32	29	26
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26	24
9	54	41	33	28	51	40	32	27	37	30	26	34	28	25	31	27	23	21
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	25	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18547	18547	18547
5°	18634	18377	18506
10°	18510	18218	18332
15°	18293	18013	18046
20°	18040	17718	17734
25°	17701	17368	17332
30°	17329	16978	16850
35°	16938	16567	16353
40°	16530	16114	15864
45°	16081	15696	15314
50°	15630	15183	14763
55°	15041	14653	14208
60°	14449	14034	13586
65°	13924	13359	12944
70°	13149	12589	12032
75°	12015	11582	11088
80°	10835	10377	10290
85°	9510	9152	8793



TEST NUMBER: P332051-830

CATALOG NUMBER: S123DIP-S1165D365U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	162.3	2.8
10°-20°	458.3	7.8
20°-30°	677.0	11.6
30°-40°	790.8	13.5
40°-50°	795.1	13.6
50°-60°	698.4	11.9
60°-70°	520.3	8.9
70°-80°	296.4	5.1
80°-90°	86.3	1.5
90°-100°	16.3	0.3
100°-110°	77.7	1.3
110°-120°	186.6	3.2
120°-130°	237.6	4.1
130°-140°	253.9	4.3
140°-150°	237.4	4.1
150°-160°	191.5	3.3
160°-170°	123.6	2.1
170°-180°	42.6	0.7
0°-30°	1297.6	22.2
0°-40°	2088.4	35.7
0°-60°	3581.8	61.2
0°-90°	4484.9	76.6
90°-120°	280.6	4.8
90°-150°	1009.4	17.2
90°-180°	1367.0	23.4
0°-180°	5852.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1723	1723	1723	1723	1723	
5°	1725	1717	1701	1715	1713	163
15°	1642	1635	1616	1627	1619	463
25°	1490	1481	1462	1464	1459	686
35°	1289	1280	1261	1252	1244	806
45°	1056	1050	1031	1014	1006	815
55°	802	799	781	765	757	718
65°	547	539	524	513	508	539
75°	289	283	278	271	267	309
85°	77	74	74	71	71	85
90°	0	4	8	9	10	5
95°	20	8	10	12	13	25
105°	99	101	73	17	15	105
115°	186	188	191	194	196	184
125°	262	265	266	267	268	234
135°	327	329	330	331	330	251
145°	377	379	380	381	381	236
155°	415	415	415	416	415	191
165°	438	437	437	439	437	124
175°	448	447	447	449	447	43
180°	448	448	448	448	448	



TEST NUMBER: P332051-830

CATALOG NUMBER: S123DIP-S1165D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1
2.5°	1729.0	1728.0	1726.9	1725.9	1724.8	1722.8	1720.0	1717.0	1714.1	1711.2	1713.8
5°	1724.6	1723.0	1721.3	1719.7	1718.0	1715.3	1711.8	1708.1	1704.5	1700.8	1704.1
7.5°	1707.7	1706.0	1704.4	1702.7	1701.1	1698.4	1694.6	1690.9	1687.2	1683.4	1686.3
10°	1693.5	1691.8	1690.2	1688.5	1686.9	1683.9	1679.6	1675.4	1671.0	1666.8	1669.7
12.5°	1674.5	1673.1	1671.7	1670.4	1669.0	1666.2	1662.3	1658.2	1654.2	1650.2	1652.4
15°	1641.6	1640.3	1639.0	1637.7	1636.3	1633.5	1629.3	1624.9	1620.7	1616.4	1619.0
17.5°	1603.4	1601.7	1600.0	1598.3	1596.5	1593.6	1589.2	1585.0	1580.6	1576.4	1578.3
20°	1574.9	1572.9	1570.9	1569.0	1567.1	1563.9	1559.6	1555.4	1551.0	1546.8	1548.1
22.5°	1542.9	1541.0	1539.0	1537.0	1535.0	1531.9	1527.6	1523.3	1519.1	1514.8	1515.8
25°	1490.4	1488.5	1486.5	1484.5	1482.6	1479.4	1475.2	1470.9	1466.6	1462.4	1462.6
27.5°	1434.5	1432.6	1430.7	1428.7	1426.8	1423.6	1419.0	1414.4	1409.8	1405.1	1405.4
30°	1394.2	1392.5	1390.9	1389.2	1387.6	1384.5	1379.9	1375.3	1370.6	1366.0	1366.0
32.5°	1353.9	1351.7	1349.5	1347.4	1345.2	1342.3	1338.8	1335.2	1331.6	1328.1	1326.3
35°	1289.0	1287.0	1285.1	1283.1	1281.1	1278.0	1273.7	1269.4	1265.1	1260.8	1258.9
37.5°	1222.6	1220.1	1217.6	1215.1	1212.6	1209.2	1204.9	1200.5	1196.2	1191.8	1189.4
40°	1176.4	1174.4	1172.4	1170.4	1168.5	1165.2	1160.6	1155.9	1151.3	1146.8	1144.2
42.5°	1130.1	1127.9	1125.7	1123.4	1121.2	1117.8	1113.1	1108.5	1103.9	1099.4	1096.7
45°	1056.4	1055.1	1053.8	1052.4	1051.1	1048.3	1044.1	1039.7	1035.5	1031.1	1027.3
47.5°	983.2	981.3	979.4	977.4	975.5	972.6	968.6	964.5	960.5	956.5	952.6
50°	933.4	931.8	930.1	928.5	926.8	923.9	919.5	915.3	911.0	906.7	903.1
52.5°	881.3	880.1	879.0	877.9	876.8	873.9	869.4	864.9	860.4	855.7	852.6
55°	801.5	801.3	800.9	800.6	800.2	798.0	793.6	789.4	785.0	780.8	777.2
57.5°	725.7	724.5	723.4	722.4	721.2	719.0	715.5	712.1	708.7	705.2	702.0
60°	671.2	670.8	670.5	670.1	669.9	667.7	663.7	659.8	655.8	651.9	648.9
62.5°	622.5	621.7	620.9	620.0	619.2	616.7	612.7	608.8	604.9	601.0	597.9
65°	546.7	545.1	543.4	541.8	540.1	537.6	534.3	531.0	527.7	524.5	521.9
67.5°	466.4	465.0	463.5	462.0	460.6	458.6	456.1	453.6	451.1	448.7	446.3
70°	417.8	415.8	413.9	411.9	409.9	407.9	406.0	404.0	402.0	400.0	397.8
72.5°	366.8	365.4	363.9	362.5	361.1	359.2	356.9	354.7	352.5	350.2	348.2
75°	288.9	287.6	286.3	284.9	283.6	282.5	281.5	280.5	279.6	278.5	276.9
77.5°	219.9	219.1	218.4	217.7	217.0	216.0	214.8	213.7	212.4	211.3	210.2
80°	174.8	173.8	172.9	171.8	170.9	170.0	169.4	168.7	168.1	167.4	167.1
82.5°	131.0	130.7	130.5	130.4	130.2	130.0	129.9	129.8	129.6	129.5	128.9
85°	77.0	76.3	75.7	75.0	74.4	74.1	74.1	74.1	74.1	74.1	73.4
87.5°	30.9	30.3	29.6	28.9	28.3	28.0	27.9	27.8	27.7	27.7	27.4
90°	0.4	1.0	1.8	2.5	3.3	4.1	5.1	6.0	7.1	8.0	8.3
92.5°	6.2	6.0	5.7	5.6	5.4	5.7	6.3	7.1	7.8	8.5	9.0
95°	20.4	17.2	14.2	11.2	8.2	7.1	7.9	8.7	9.5	10.4	10.8
97.5°	40.8	39.5	38.1	36.8	35.3	32.0	26.7	21.4	16.0	10.7	11.3
100°	56.3	57.8	59.3	60.7	62.2	57.2	45.6	34.1	22.5	11.0	11.6
102.5°	73.9	74.9	76.0	77.1	78.1	72.4	59.8	47.1	34.5	22.0	20.1
105°	99.2	100.1	100.9	101.7	102.5	99.6	92.9	86.2	79.6	73.0	59.9
107.5°	126.0	126.7	127.3	128.0	128.7	129.5	130.5	131.6	132.6	133.7	124.0
110°	143.9	144.5	145.1	145.6	146.3	146.9	147.8	148.5	149.4	150.2	147.8



TEST NUMBER: P332051-830

CATALOG NUMBER: S123DIP-S1165D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	160.9	161.5	162.0	162.5	163.1	163.7	164.6	165.4	166.2	167.0	167.0
115°	186.2	186.6	187.1	187.5	187.9	188.5	189.2	189.8	190.5	191.1	191.9
117.5°	210.7	211.2	211.7	212.3	212.8	213.3	213.6	214.0	214.3	214.6	215.2
120°	225.8	226.5	227.2	227.8	228.5	228.9	229.1	229.4	229.6	229.8	230.5
122.5°	241.3	241.9	242.3	242.9	243.5	243.8	244.1	244.4	244.7	245.0	245.4
125°	262.5	263.1	263.6	264.2	264.9	265.2	265.6	265.9	266.2	266.5	266.6
127.5°	283.0	283.6	284.2	284.7	285.3	285.8	286.2	286.5	286.9	287.2	287.5
130°	295.8	296.3	296.9	297.6	298.1	298.6	298.9	299.2	299.4	299.7	300.0
132.5°	308.0	308.6	309.2	309.8	310.4	310.8	311.0	311.3	311.5	311.8	312.1
135°	326.8	327.2	327.6	328.1	328.5	328.9	329.1	329.5	329.8	330.1	330.3
137.5°	342.7	343.3	343.8	344.4	345.0	345.3	345.5	345.6	345.8	346.0	346.4
140°	353.4	353.8	354.3	354.7	355.2	355.5	355.7	355.9	356.2	356.4	356.7
142.5°	363.3	363.7	364.1	364.6	365.0	365.3	365.6	365.8	366.0	366.3	366.5
145°	377.0	377.6	378.1	378.6	379.1	379.5	379.6	379.8	379.8	380.0	380.2
147.5°	390.0	390.4	390.7	391.1	391.3	391.6	391.8	391.9	392.1	392.2	392.4
150°	398.0	398.2	398.4	398.7	398.9	399.1	399.3	399.4	399.5	399.6	399.8
152.5°	405.2	405.3	405.4	405.5	405.6	405.8	405.8	405.9	406.0	406.0	406.3
155°	415.4	415.2	415.0	414.9	414.7	414.7	414.8	414.8	414.9	415.0	415.4
157.5°	423.2	423.2	423.2	423.1	423.1	423.1	423.0	422.9	422.8	422.8	423.2
160°	428.0	427.9	427.8	427.7	427.7	427.6	427.5	427.4	427.4	427.3	427.7
162.5°	432.5	432.3	432.2	432.0	431.8	431.6	431.5	431.5	431.4	431.3	431.8
165°	438.0	437.7	437.5	437.3	437.1	437.0	436.9	436.8	436.7	436.7	437.2
167.5°	442.2	442.0	441.7	441.4	441.0	440.9	440.9	440.9	440.9	440.9	441.5
170°	444.6	444.3	444.0	443.7	443.5	443.3	443.3	443.3	443.3	443.3	443.9
172.5°	446.2	445.9	445.5	445.2	444.8	444.7	444.7	444.8	444.9	444.9	445.5
175°	448.3	447.9	447.5	447.2	446.9	446.7	446.8	446.9	446.9	447.0	447.5
177.5°	448.8	448.6	448.3	448.0	447.6	447.5	447.6	447.6	447.7	447.8	448.3
180°	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3



TEST NUMBER: P332051-830

CATALOG NUMBER: S123DIP-S1165D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1
2.5°	1716.5	1719.1	1721.7	1723.0	1722.7	1722.4	1722.1	1721.9
5°	1707.4	1710.7	1714.0	1715.3	1714.7	1714.0	1713.4	1712.7
7.5°	1689.3	1692.2	1695.3	1696.5	1696.1	1695.7	1695.4	1695.0
10°	1672.7	1675.7	1678.7	1679.8	1679.1	1678.5	1677.8	1677.2
12.5°	1654.5	1656.7	1658.9	1659.8	1659.3	1659.0	1658.6	1658.2
15°	1621.6	1624.3	1626.9	1627.3	1625.3	1623.3	1621.4	1619.4
17.5°	1580.1	1582.0	1583.8	1584.3	1583.7	1582.9	1582.2	1581.5
20°	1549.4	1550.8	1552.1	1552.2	1551.2	1550.2	1549.3	1548.2
22.5°	1516.9	1518.0	1519.0	1518.9	1517.7	1516.4	1515.1	1513.9
25°	1463.0	1463.3	1463.7	1463.3	1462.4	1461.3	1460.4	1459.3
27.5°	1405.7	1405.9	1406.2	1405.7	1404.5	1403.2	1401.9	1400.7
30°	1366.0	1366.0	1366.0	1364.9	1362.5	1360.3	1357.9	1355.7
32.5°	1324.4	1322.6	1320.7	1319.2	1318.0	1316.6	1315.4	1314.2
35°	1256.9	1254.9	1252.9	1251.1	1249.4	1247.8	1246.1	1244.5
37.5°	1187.0	1184.7	1182.3	1180.6	1179.5	1178.5	1177.4	1176.4
40°	1141.5	1138.9	1136.2	1134.3	1132.9	1131.6	1130.3	1129.0
42.5°	1094.1	1091.5	1088.8	1086.8	1085.5	1084.2	1082.9	1081.6
45°	1023.3	1019.4	1015.4	1012.6	1011.0	1009.3	1007.7	1006.0
47.5°	948.8	944.9	940.9	938.3	936.9	935.4	934.0	932.6
50°	899.5	895.9	892.2	889.5	887.5	885.5	883.5	881.6
52.5°	849.6	846.5	843.4	840.8	838.9	836.9	834.9	832.9
55°	773.5	770.0	766.3	763.6	762.0	760.3	758.7	757.1
57.5°	698.8	695.6	692.3	689.8	687.9	686.0	684.0	682.1
60°	646.0	643.0	640.1	637.7	636.1	634.4	632.8	631.1
62.5°	595.0	592.0	589.1	587.0	585.9	584.8	583.7	582.6
65°	519.2	516.6	514.0	512.2	511.1	510.2	509.2	508.2
67.5°	444.0	441.7	439.4	437.5	436.2	434.8	433.4	432.1
70°	395.4	393.1	390.8	388.8	387.2	385.5	383.9	382.3
72.5°	346.2	344.1	342.0	340.6	339.8	338.9	338.1	337.2
75°	275.2	273.6	271.9	270.6	269.7	268.6	267.7	266.6
77.5°	209.1	207.9	206.8	206.2	206.2	206.2	206.2	206.2
80°	166.7	166.5	166.1	166.0	166.0	166.0	166.0	166.0
82.5°	128.3	127.7	127.1	126.7	126.4	126.2	125.9	125.6
85°	72.8	72.1	71.4	71.2	71.2	71.2	71.2	71.2
87.5°	27.2	27.1	26.9	26.8	26.8	26.9	26.9	26.9
90°	8.6	8.9	9.1	9.4	9.5	9.7	9.8	10.0
92.5°	9.5	10.0	10.5	10.7	10.7	10.8	10.9	11.0
95°	11.4	11.9	12.4	12.6	12.6	12.6	12.6	12.6
97.5°	11.9	12.5	13.1	13.4	13.5	13.6	13.7	13.8
100°	12.2	12.7	13.4	13.7	13.8	13.9	13.9	13.9
102.5°	18.3	16.4	14.6	13.8	13.9	13.9	14.1	14.2
105°	46.8	33.6	20.5	14.0	14.2	14.3	14.5	14.6
107.5°	114.5	104.9	95.3	85.5	75.7	65.8	55.9	46.0
110°	145.3	142.9	140.4	133.9	123.4	112.7	102.2	91.6





TEST NUMBER: P332051-830

CATALOG NUMBER: S123DIP-S1165D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	167.1	167.1	167.2	166.1	163.8	161.6	159.4	157.1
115°	192.7	193.4	194.2	194.6	194.9	195.3	195.6	195.9
117.5°	215.8	216.4	217.0	217.4	217.4	217.4	217.5	217.5
120°	231.0	231.6	232.1	232.5	232.5	232.5	232.5	232.5
122.5°	245.8	246.3	246.7	246.9	246.9	247.0	247.0	247.1
125°	266.7	266.9	267.0	267.2	267.3	267.5	267.7	267.8
127.5°	287.7	287.9	288.2	288.2	288.0	287.9	287.8	287.7
130°	300.4	300.7	301.0	301.0	300.9	300.8	300.6	300.4
132.5°	312.4	312.6	312.9	313.0	312.7	312.5	312.4	312.2
135°	330.5	330.7	330.9	330.9	330.7	330.5	330.3	330.1
137.5°	346.7	347.0	347.4	347.5	347.3	347.2	347.0	346.9
140°	356.9	357.2	357.6	357.6	357.5	357.3	357.2	357.0
142.5°	366.7	366.9	367.2	367.2	367.0	366.7	366.6	366.4
145°	380.3	380.5	380.6	380.7	380.7	380.7	380.7	380.7
147.5°	392.5	392.7	392.9	392.8	392.4	392.0	391.7	391.3
150°	400.0	400.1	400.3	400.2	400.0	399.8	399.5	399.4
152.5°	406.6	406.9	407.2	407.1	406.8	406.4	406.0	405.8
155°	415.8	416.1	416.5	416.4	416.0	415.6	415.1	414.6
157.5°	423.7	424.1	424.6	424.5	424.0	423.4	422.7	422.2
160°	428.2	428.7	429.1	429.0	428.6	428.0	427.5	427.0
162.5°	432.3	432.8	433.3	433.4	432.9	432.4	432.0	431.5
165°	437.8	438.5	439.0	439.0	438.6	438.0	437.5	437.0
167.5°	442.1	442.7	443.3	443.3	442.7	442.1	441.5	440.9
170°	444.5	445.1	445.6	445.6	445.1	444.5	443.9	443.3
172.5°	446.1	446.7	447.2	447.2	446.6	445.9	445.3	444.6
175°	448.0	448.6	449.0	449.0	448.5	447.8	447.2	446.7
177.5°	448.7	449.2	449.7	449.6	449.0	448.5	447.8	447.2
180°	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3

(END OF REPORT)