

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331982

Luminaire Tested: **S123DIP-S775D1025U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331982  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S775D1025U835-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1025 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7362.1 lumens  
Efficiency: N/A  
Efficacy: 141.6 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331982  
CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331982

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	93	89	85	88	85	82	79	71	68	66	57	56	55	45	44	43	38
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	38	37	32
3	81	71	64	59	74	66	60	55	55	50	47	45	42	39	36	34	32	27
4	74	63	56	50	67	58	52	46	49	44	40	40	37	34	32	30	27	24
5	68	56	48	43	62	52	45	40	44	39	34	36	32	29	29	26	24	21
6	62	51	43	37	57	47	40	35	39	34	30	33	29	26	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16
8	54	41	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17	14
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	35	28	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	11630	11630	11630	11630
5°	13870	11681	10351	11681
10°	17361	11622	9349	11622
15°	21293	11528	8704	11528
20°	25366	11381	8287	11381
25°	26935	11204	8195	11204
30°	23086	11074	8238	11074
35°	16056	10889	8324	10889
40°	12094	10673	8297	10673
45°	10041	10353	8193	10353
50°	8994	9696	8118	9696
55°	8409	8989	8017	8989
60°	7890	8249	7935	8249
65°	7414	7521	7679	7521
70°	6952	6688	7314	6688
75°	6226	5856	6704	5856
80°	5455	4804	5777	4804
85°	4273	3495	3878	3495



TEST NUMBER: P331982

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	106.4	1.4
10°-20°	341.3	4.6
20°-30°	572.8	7.8
30°-40°	648.6	8.8
40°-50°	581.7	7.9
50°-60°	469.4	6.4
60°-70°	327.1	4.4
70°-80°	171.9	2.3
80°-90°	45.8	0.6
90°-100°	48.8	0.7
100°-110°	232.8	3.2
110°-120°	559.2	7.6
120°-130°	712.1	9.7
130°-140°	760.8	10.3
140°-150°	711.5	9.7
150°-160°	573.9	7.8
160°-170°	370.4	5.0
170°-180°	127.6	1.7
0°-30°	1020.6	13.9
0°-40°	1669.2	22.7
0°-60°	2720.2	36.9
0°-90°	3265.0	44.3
90°-120°	840.8	11.4
90°-150°	3025.2	41.1
90°-180°	4097.0	55.6
0°-180°	7362.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1080	1080	1080	1080	1080	
5°	1284	1081	958	1081	1284	133
15°	1911	1034	781	1034	1911	552
25°	2268	943	690	943	2268	995
35°	1222	829	634	829	1222	794
45°	660	680	538	680	660	522
55°	448	479	427	479	448	402
65°	291	295	302	295	291	290
75°	150	141	161	141	150	160
85°	35	28	31	28	35	42
90°	30	1	30	1	30	15
95°	38	61	38	61	38	32
105°	44	297	44	297	44	100
115°	587	558	587	558	587	542
125°	802	786	802	786	802	717
135°	989	979	989	979	989	763
145°	1141	1130	1141	1130	1141	712
155°	1243	1245	1243	1245	1243	573
165°	1310	1313	1310	1313	1310	370
175°	1338	1344	1338	1344	1338	127
180°	1344	1344	1344	1344	1344	



TEST NUMBER: P331982

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1146.7	1145.9	1143.8	1145.5	1142.1	1137.5	1137.1	1132.9	1120.7	1119.9	1116.6
5°	1283.7	1279.5	1279.0	1278.4	1271.1	1261.2	1242.3	1240.7	1215.6	1203.0	1187.9
7.5°	1461.0	1463.2	1455.6	1448.9	1426.5	1411.7	1391.5	1365.6	1334.8	1303.5	1282.6
10°	1588.4	1605.6	1584.2	1569.5	1555.9	1530.2	1500.4	1463.2	1426.1	1382.6	1349.6
12.5°	1724.9	1733.4	1729.1	1715.3	1694.1	1655.1	1602.2	1561.2	1527.0	1454.6	1425.4
15°	1910.8	1942.8	1922.4	1875.2	1876.3	1839.1	1770.0	1694.1	1653.8	1590.4	1504.1
17.5°	2108.9	2112.9	2104.2	2065.0	2038.8	1987.7	1923.9	1851.2	1769.5	1692.8	1601.2
20°	2214.5	2211.3	2193.0	2172.6	2127.6	2087.8	2018.2	1937.0	1832.3	1756.9	1656.9
22.5°	2273.1	2267.9	2259.2	2242.1	2204.6	2161.9	2099.4	2010.7	1911.1	1807.2	1691.7
25°	2267.9	2274.7	2275.7	2271.0	2257.9	2232.3	2183.1	2112.4	2012.9	1879.4	1759.0
27.5°	2062.7	2072.3	2100.3	2125.1	2152.8	2181.1	2177.3	2142.2	2068.6	1953.4	1806.1
30°	1857.4	1836.5	1888.3	1953.8	1998.3	2076.8	2120.8	2123.4	2082.0	1983.1	1839.6
32.5°	1572.6	1595.7	1618.6	1699.1	1796.4	1884.6	1972.1	2042.6	2050.6	1984.8	1859.3
35°	1221.9	1250.7	1292.6	1334.4	1439.2	1529.2	1683.1	1817.1	1923.9	1938.1	1861.1
37.5°	984.6	998.9	1025.4	1067.3	1135.8	1242.6	1361.7	1531.1	1685.8	1800.9	1805.9
40°	860.7	864.9	894.7	926.6	982.1	1070.1	1177.4	1327.1	1512.4	1673.2	1740.2
42.5°	767.7	776.9	789.6	820.2	864.4	930.6	1030.4	1154.1	1324.0	1509.0	1640.1
45°	659.6	670.1	678.0	698.4	729.8	774.3	843.9	957.0	1086.3	1277.4	1453.8
47.5°	588.2	589.1	594.9	610.3	631.7	665.1	714.3	787.0	905.7	1060.6	1241.8
50°	537.1	545.5	547.6	559.6	576.4	601.0	641.8	703.6	801.0	937.1	1103.6
52.5°	501.1	503.6	509.5	518.2	532.8	552.0	587.4	635.8	712.2	828.2	981.3
55°	448.1	448.1	453.9	460.7	469.1	486.3	509.9	545.5	603.6	693.7	820.4
57.5°	399.1	401.7	405.8	407.9	415.0	426.5	446.1	473.2	516.5	585.8	686.5
60°	366.5	371.2	370.7	374.8	381.1	390.0	406.8	428.8	467.5	523.0	607.8
62.5°	338.0	337.7	337.6	342.6	348.9	357.4	368.2	387.3	420.2	469.4	541.6
65°	291.1	290.0	293.7	296.8	298.9	305.2	313.6	330.3	352.3	389.0	445.0
67.5°	249.4	246.4	248.4	249.4	253.0	257.9	265.7	276.1	293.6	323.0	365.2
70°	220.9	218.3	217.8	218.8	222.0	225.6	231.4	241.3	257.6	281.1	312.0
72.5°	191.6	189.8	189.7	192.0	193.5	195.9	200.0	209.1	222.0	239.7	268.5
75°	149.7	149.7	149.7	150.2	151.8	153.9	157.1	161.8	171.7	184.3	203.6
77.5°	112.2	112.1	111.5	111.4	113.7	114.7	115.4	119.8	125.3	133.8	147.9
80°	88.0	85.3	86.4	88.0	89.0	89.5	91.1	92.1	96.9	101.6	111.5
82.5°	65.3	63.1	63.3	65.8	66.0	66.5	68.1	69.5	71.3	75.6	80.9
85°	34.6	34.6	35.1	35.1	35.6	35.1	36.6	37.2	37.2	39.8	42.9
87.5°	18.6	17.6	18.0	18.3	17.8	18.1	18.3	18.5	18.8	19.0	18.9
90°	29.9	29.5	29.1	28.6	28.2	27.5	26.6	25.7	24.8	24.0	21.1
92.5°	33.1	32.9	32.6	32.3	32.1	31.2	29.8	28.4	27.0	25.6	23.4
95°	37.9	37.9	37.9	37.9	37.9	37.2	35.6	34.0	32.5	30.9	28.5
97.5°	41.1	40.9	40.7	40.5	40.2	39.2	37.5	35.7	33.9	32.1	48.1
100°	41.9	41.7	41.5	41.3	41.0	40.0	38.3	36.5	34.7	32.9	67.5
102.5°	42.7	42.3	41.9	41.5	41.1	43.7	49.2	54.7	60.2	65.7	103.5
105°	43.9	43.5	43.0	42.6	42.1	61.6	100.8	140.1	179.3	218.6	238.6
107.5°	137.9	167.5	197.1	226.7	256.3	285.5	314.3	343.1	371.9	400.7	397.5
110°	274.5	306.2	337.9	369.6	401.4	420.9	428.2	435.5	442.8	450.2	447.7



TEST NUMBER: P331982

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	470.9	477.6	484.3	491.0	497.7	501.0	500.9	500.7	500.6	500.5	498.0
115°	586.9	586.0	585.1	584.2	583.4	581.8	579.6	577.4	575.2	572.9	570.9
117.5°	652.0	651.8	651.6	651.5	651.3	650.3	648.5	646.8	645.0	643.2	642.2
120°	696.7	696.7	696.7	696.7	696.7	695.8	694.0	692.3	690.5	688.7	688.1
122.5°	740.6	740.4	740.3	740.1	739.9	739.2	738.0	736.7	735.5	734.2	733.4
125°	802.5	802.1	801.6	801.2	800.7	800.3	799.8	799.4	799.0	798.5	797.6
127.5°	862.0	862.4	862.9	863.3	863.8	863.6	862.9	862.2	861.5	860.8	859.7
130°	900.3	900.8	901.2	901.7	902.1	901.9	901.0	900.1	899.2	898.3	897.4
132.5°	935.5	936.1	936.7	937.3	937.9	937.8	936.9	936.0	935.2	934.3	933.6
135°	989.2	989.8	990.5	991.2	991.8	991.8	991.2	990.5	989.8	989.2	988.3
137.5°	1039.7	1040.1	1040.6	1041.0	1041.4	1041.1	1040.1	1039.0	1037.9	1036.9	1036.4
140°	1070.0	1070.5	1070.9	1071.3	1071.8	1071.6	1070.7	1069.8	1068.9	1068.0	1067.4
142.5°	1098.0	1098.6	1099.2	1099.8	1100.4	1100.4	1099.7	1099.0	1098.3	1097.6	1096.9
145°	1140.9	1140.9	1140.9	1140.9	1140.9	1140.7	1140.2	1139.8	1139.3	1138.9	1138.4
147.5°	1172.8	1173.8	1174.9	1175.9	1176.9	1177.2	1176.7	1176.3	1175.9	1175.4	1175.0
150°	1196.8	1197.4	1198.1	1198.8	1199.4	1199.6	1199.1	1198.7	1198.2	1197.8	1197.3
152.5°	1215.9	1217.0	1218.0	1219.0	1220.0	1220.1	1219.3	1218.5	1217.7	1216.9	1216.7
155°	1242.7	1244.0	1245.4	1246.7	1248.0	1248.1	1247.0	1245.9	1244.8	1243.7	1243.5
157.5°	1265.3	1267.0	1268.7	1270.4	1272.2	1272.4	1271.0	1269.7	1268.4	1267.0	1267.3
160°	1279.6	1281.2	1282.7	1284.3	1285.8	1285.9	1284.6	1283.3	1282.0	1280.6	1280.8
162.5°	1293.2	1294.6	1295.9	1297.3	1298.7	1298.6	1297.1	1295.6	1294.1	1292.6	1292.8
165°	1309.6	1311.1	1312.7	1314.2	1315.8	1315.7	1313.9	1312.1	1310.3	1308.6	1308.8
167.5°	1321.3	1323.1	1324.9	1326.7	1328.4	1328.4	1326.7	1324.9	1323.1	1321.3	1321.3
170°	1328.5	1330.3	1332.1	1333.9	1335.6	1335.6	1333.9	1332.1	1330.3	1328.5	1328.5
172.5°	1332.5	1334.5	1336.4	1338.4	1340.3	1340.4	1338.6	1336.9	1335.1	1333.3	1333.1
175°	1338.5	1340.3	1342.1	1343.8	1345.6	1345.7	1344.2	1342.6	1341.1	1339.5	1339.3
177.5°	1340.3	1342.1	1343.9	1345.6	1347.4	1347.6	1346.2	1344.7	1343.3	1341.9	1341.7
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P331982

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1114.0	1110.7	1107.3	1101.5	1096.5	1089.3	1087.2	1084.7	1077.2	1070.5	1065.5
5°	1182.1	1169.5	1151.2	1134.5	1120.9	1102.5	1092.1	1081.1	1065.4	1051.2	1039.7
7.5°	1253.3	1228.6	1200.1	1169.3	1140.6	1113.0	1090.7	1070.8	1048.8	1028.0	1011.8
10°	1309.8	1274.2	1234.5	1191.5	1154.9	1119.3	1089.4	1063.3	1035.0	1010.4	990.0
12.5°	1374.3	1321.6	1266.7	1214.6	1171.2	1121.8	1085.7	1052.4	1020.3	990.7	967.8
15°	1450.7	1383.7	1318.7	1247.0	1181.1	1119.3	1076.4	1034.5	997.3	966.9	937.6
17.5°	1520.2	1444.3	1358.7	1271.5	1191.9	1118.7	1058.6	1011.2	964.7	927.6	898.4
20°	1559.6	1473.2	1376.3	1285.8	1197.8	1116.1	1050.2	993.6	943.4	904.1	871.1
22.5°	1593.5	1492.4	1392.2	1295.4	1197.4	1109.4	1034.7	976.5	922.0	883.6	848.5
25°	1628.7	1507.7	1407.2	1293.6	1184.2	1093.1	1009.3	943.4	888.9	843.9	807.8
27.5°	1658.8	1506.7	1387.4	1265.2	1163.5	1072.2	982.7	912.0	854.2	805.3	768.6
30°	1678.9	1508.8	1366.9	1246.0	1143.4	1049.1	962.2	891.0	830.3	780.6	746.0
32.5°	1691.5	1507.5	1348.1	1219.2	1111.5	1028.2	940.0	866.3	803.9	755.0	721.7
35°	1698.8	1498.3	1315.6	1163.8	1060.1	979.0	905.2	828.7	763.3	717.7	680.1
37.5°	1684.2	1478.9	1277.9	1110.4	996.9	917.0	854.9	789.8	727.2	677.0	644.6
40°	1661.1	1466.4	1248.6	1072.7	953.3	876.4	823.5	759.6	697.8	650.2	619.8
42.5°	1617.1	1440.8	1216.3	1030.8	908.1	831.1	782.5	729.1	670.6	625.9	595.6
45°	1509.8	1385.2	1168.0	968.0	841.3	761.7	718.8	680.1	627.2	583.7	557.5
47.5°	1360.9	1301.6	1098.0	901.7	771.6	695.0	650.4	619.2	580.6	545.5	520.4
50°	1257.5	1232.9	1050.7	856.5	725.1	650.2	607.3	579.0	551.3	516.2	493.2
52.5°	1138.1	1153.3	995.4	809.6	677.7	604.1	563.7	541.3	516.1	487.3	467.2
55°	970.1	1025.0	899.9	730.8	607.3	537.1	498.9	479.0	464.4	442.9	425.6
57.5°	812.7	882.7	796.7	649.7	538.1	477.6	440.9	419.2	409.8	398.6	385.0
60°	719.3	788.4	723.0	595.2	491.6	434.0	401.5	383.2	373.8	365.9	354.4
62.5°	636.0	705.9	650.9	540.0	445.9	392.5	364.3	346.4	339.0	334.9	325.1
65°	521.4	581.6	545.0	453.9	380.6	333.5	307.8	295.3	288.5	286.9	280.6
67.5°	424.4	470.2	443.5	376.5	318.8	278.1	256.3	245.6	240.4	239.9	235.2
70°	360.7	403.6	383.2	322.5	272.8	240.8	222.0	212.5	209.4	208.9	206.3
72.5°	311.3	341.2	325.0	274.3	235.9	206.9	193.1	183.2	179.7	180.4	178.6
75°	230.3	252.9	243.4	208.4	177.5	158.6	147.1	140.8	137.7	139.3	137.2
77.5°	165.7	180.0	171.5	147.2	128.2	114.5	106.1	102.2	99.4	99.3	98.3
80°	125.1	133.5	128.8	114.1	98.4	86.9	80.1	77.5	75.9	75.4	74.9
82.5°	89.1	96.2	90.7	80.6	69.9	63.0	59.2	55.7	54.6	54.9	54.3
85°	45.0	47.6	45.5	39.3	35.1	31.9	29.8	28.3	27.2	27.7	26.7
87.5°	19.1	19.0	17.1	15.0	13.7	12.0	11.5	10.3	9.9	10.3	10.3
90°	18.2	15.3	12.4	9.9	7.7	5.4	3.2	1.0	3.2	5.4	7.7
92.5°	21.2	19.0	16.9	16.1	16.7	17.3	17.9	18.6	17.9	17.3	16.7
95°	26.1	23.6	21.2	24.5	33.6	42.7	51.8	60.9	51.8	42.7	33.6
97.5°	64.1	80.1	96.0	106.0	110.1	114.2	118.3	122.4	118.3	114.2	110.1
100°	102.1	136.7	171.3	186.4	182.0	177.6	173.1	168.7	173.1	177.6	182.0
102.5°	141.3	179.1	216.9	234.2	231.0	227.8	224.6	221.4	224.6	227.8	231.0
105°	258.5	278.5	298.4	307.2	304.8	302.3	299.9	297.4	299.9	302.3	304.8
107.5°	394.4	391.2	388.1	385.5	383.6	381.6	379.7	377.7	379.7	381.6	383.6
110°	445.3	442.8	440.4	438.3	436.5	434.7	433.0	431.2	433.0	434.7	436.5





TEST NUMBER: P331982

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	495.6	493.2	490.7	488.7	487.1	485.5	483.9	482.3	483.9	485.5	487.1
115°	568.9	566.9	565.0	563.3	562.0	560.6	559.3	558.0	559.3	560.6	562.0
117.5°	641.2	640.1	639.1	637.8	636.2	634.5	632.9	631.2	632.9	634.5	636.2
120°	687.4	686.7	686.1	684.7	682.7	680.7	678.7	676.7	678.7	680.7	682.7
122.5°	732.6	731.7	730.9	729.6	728.0	726.3	724.7	723.1	724.7	726.3	728.0
125°	796.7	795.9	795.0	793.6	791.9	790.1	788.3	786.5	788.3	790.1	791.9
127.5°	858.7	857.6	856.5	855.1	853.3	851.6	849.8	848.0	849.8	851.6	853.3
130°	896.6	895.7	894.8	893.5	891.7	889.9	888.1	886.4	888.1	889.9	891.7
132.5°	932.8	932.1	931.4	930.2	928.4	926.6	924.9	923.1	924.9	926.6	928.4
135°	987.4	986.5	985.6	984.5	983.2	981.8	980.5	979.2	980.5	981.8	983.2
137.5°	1035.9	1035.4	1034.9	1033.8	1032.2	1030.5	1028.8	1027.1	1028.8	1030.5	1032.2
140°	1066.7	1066.0	1065.4	1064.4	1063.0	1061.7	1060.4	1059.0	1060.4	1061.7	1063.0
142.5°	1096.2	1095.6	1094.9	1093.9	1092.6	1091.2	1089.9	1088.6	1089.9	1091.2	1092.6
145°	1138.0	1137.6	1137.1	1136.1	1134.6	1133.0	1131.5	1129.9	1131.5	1133.0	1134.6
147.5°	1174.5	1174.1	1173.6	1172.9	1171.9	1170.9	1169.9	1168.8	1169.9	1170.9	1171.9
150°	1196.9	1196.4	1196.0	1195.4	1194.8	1194.1	1193.5	1192.8	1193.5	1194.1	1194.8
152.5°	1216.4	1216.1	1215.9	1215.6	1215.3	1215.0	1214.7	1214.3	1214.7	1215.0	1215.3
155°	1243.2	1243.0	1242.8	1242.9	1243.4	1243.8	1244.2	1244.7	1244.2	1243.8	1243.4
157.5°	1267.5	1267.7	1267.9	1268.1	1268.1	1268.2	1268.2	1268.2	1268.2	1268.2	1268.1
160°	1281.1	1281.3	1281.5	1281.7	1282.0	1282.2	1282.4	1282.6	1282.4	1282.2	1282.0
162.5°	1293.0	1293.3	1293.5	1293.9	1294.5	1295.0	1295.6	1296.2	1295.6	1295.0	1294.5
165°	1309.0	1309.2	1309.5	1309.9	1310.6	1311.2	1311.9	1312.6	1311.9	1311.2	1310.6
167.5°	1321.3	1321.3	1321.3	1321.8	1322.7	1323.6	1324.5	1325.3	1324.5	1323.6	1322.7
170°	1328.5	1328.5	1328.5	1329.0	1329.9	1330.8	1331.6	1332.5	1331.6	1330.8	1329.9
172.5°	1333.0	1332.8	1332.6	1333.1	1334.1	1335.2	1336.3	1337.3	1336.3	1335.2	1334.1
175°	1339.1	1338.8	1338.6	1339.1	1340.2	1341.3	1342.4	1343.5	1342.4	1341.3	1340.2
177.5°	1341.6	1341.4	1341.2	1341.6	1342.4	1343.3	1344.2	1345.1	1344.2	1343.3	1342.4
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P331982

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1062.5	1059.6	1055.4	1049.1	1044.1	1036.1	1036.1	1037.4	1037.4	1037.0	1036.1
5°	1030.3	1022.4	1013.0	1002.0	990.5	979.0	976.9	972.7	969.6	967.5	964.8
7.5°	996.3	982.3	968.6	953.2	939.2	927.6	919.5	912.8	908.5	903.9	900.6
10°	973.2	955.9	939.7	923.5	905.7	891.6	882.7	876.4	871.7	867.5	865.4
12.5°	946.0	926.2	908.3	892.9	873.4	858.9	850.4	847.5	841.9	833.1	828.5
15°	906.2	887.9	866.4	842.9	833.4	815.6	805.7	801.0	797.8	791.0	788.9
17.5°	872.2	848.2	824.1	806.5	789.0	774.6	769.0	763.2	759.0	753.4	751.8
20°	845.0	823.5	801.5	782.7	764.3	748.6	743.9	739.7	735.5	732.9	730.8
22.5°	817.3	795.9	777.6	760.0	740.5	730.2	725.1	720.5	717.5	715.8	713.7
25°	778.5	759.6	739.2	723.5	707.8	701.0	697.8	695.2	693.1	690.5	690.0
27.5°	743.7	723.2	706.6	692.0	680.7	675.0	672.0	670.7	671.2	672.1	672.7
30°	717.7	698.9	685.3	672.7	662.3	657.0	656.5	656.5	658.6	659.1	660.2
32.5°	693.9	678.4	664.8	652.6	644.7	641.1	643.1	643.1	644.8	646.1	648.0
35°	659.1	645.5	635.0	624.6	617.8	619.3	620.4	621.4	624.0	627.2	629.3
37.5°	625.9	614.1	603.2	595.0	591.9	594.7	597.2	599.4	602.5	604.9	607.0
40°	602.0	593.1	582.7	575.3	576.4	578.0	580.1	582.7	585.3	586.9	589.0
42.5°	579.8	570.5	562.6	556.5	558.0	560.0	561.2	562.6	565.6	568.4	569.7
45°	546.0	538.7	531.4	527.7	528.8	529.8	530.8	532.4	535.0	537.1	537.7
47.5°	508.0	502.9	498.0	494.4	496.1	495.7	497.0	500.4	501.2	502.5	505.4
50°	483.7	479.0	473.3	472.2	472.2	472.2	472.7	476.9	476.9	479.0	481.1
52.5°	456.9	453.9	450.2	448.3	447.5	447.5	449.7	451.8	452.6	455.6	457.7
55°	417.2	414.1	411.0	409.4	408.3	409.4	413.6	414.6	417.2	418.8	420.4
57.5°	375.9	373.5	371.0	370.1	369.9	371.3	373.6	376.7	377.4	382.2	384.6
60°	348.7	345.0	342.9	342.9	341.9	346.6	345.5	350.8	351.8	354.9	358.6
62.5°	320.6	315.7	314.8	314.8	316.3	317.7	319.1	321.4	324.2	328.1	331.0
65°	275.4	272.8	276.4	275.9	274.8	278.0	278.0	280.6	283.7	287.4	293.2
67.5°	232.5	231.2	231.5	231.5	233.1	234.9	236.3	238.6	242.4	246.3	250.0
70°	203.6	205.2	202.6	204.7	206.3	206.8	207.8	211.0	215.2	217.8	222.0
72.5°	175.6	175.5	175.8	176.6	178.2	179.1	180.2	183.8	188.4	190.6	193.9
75°	135.1	134.5	136.1	136.1	138.7	139.8	140.8	142.4	146.6	149.7	152.3
77.5°	98.6	99.3	98.9	100.7	100.0	100.2	103.4	105.0	105.4	111.6	113.0
80°	74.3	75.4	75.9	76.4	77.0	75.9	79.6	81.1	81.1	84.8	87.4
82.5°	53.4	54.0	55.4	55.9	56.0	57.1	57.4	58.5	59.8	61.4	64.8
85°	26.7	28.3	28.8	28.3	28.8	27.7	29.3	29.8	30.4	30.4	30.4
87.5°	10.4	11.3	11.4	12.4	12.6	13.6	13.8	13.1	13.3	14.7	13.2
90°	9.9	12.4	15.3	18.2	21.1	24.0	24.8	25.7	26.6	27.5	28.2
92.5°	16.1	16.9	19.0	21.2	23.4	25.6	27.0	28.4	29.8	31.2	32.1
95°	24.5	21.2	23.6	26.1	28.5	30.9	32.5	34.0	35.6	37.2	37.9
97.5°	106.0	96.0	80.1	64.1	48.1	32.1	33.9	35.7	37.5	39.2	40.2
100°	186.4	171.3	136.7	102.1	67.5	32.9	34.7	36.5	38.3	40.0	41.0
102.5°	234.2	216.9	179.1	141.3	103.5	65.7	60.2	54.7	49.2	43.7	41.1
105°	307.2	298.4	278.5	258.5	238.6	218.6	179.3	140.1	100.8	61.6	42.1
107.5°	385.5	388.1	391.2	394.4	397.5	400.7	371.9	343.1	314.3	285.5	256.3
110°	438.3	440.4	442.8	445.3	447.7	450.2	442.8	435.5	428.2	420.9	401.4



TEST NUMBER: P331982

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	488.7	490.7	493.2	495.6	498.0	500.5	500.6	500.7	500.9	501.0	497.7
115°	563.3	565.0	566.9	568.9	570.9	572.9	575.2	577.4	579.6	581.8	583.4
117.5°	637.8	639.1	640.1	641.2	642.2	643.2	645.0	646.8	648.5	650.3	651.3
120°	684.7	686.1	686.7	687.4	688.1	688.7	690.5	692.3	694.0	695.8	696.7
122.5°	729.6	730.9	731.7	732.6	733.4	734.2	735.5	736.7	738.0	739.2	739.9
125°	793.6	795.0	795.9	796.7	797.6	798.5	799.0	799.4	799.8	800.3	800.7
127.5°	855.1	856.5	857.6	858.7	859.7	860.8	861.5	862.2	862.9	863.6	863.8
130°	893.5	894.8	895.7	896.6	897.4	898.3	899.2	900.1	901.0	901.9	902.1
132.5°	930.2	931.4	932.1	932.8	933.6	934.3	935.2	936.0	936.9	937.8	937.9
135°	984.5	985.6	986.5	987.4	988.3	989.2	989.8	990.5	991.2	991.8	991.8
137.5°	1033.8	1034.9	1035.4	1035.9	1036.4	1036.9	1037.9	1039.0	1040.1	1041.1	1041.4
140°	1064.4	1065.4	1066.0	1066.7	1067.4	1068.0	1068.9	1069.8	1070.7	1071.6	1071.8
142.5°	1093.9	1094.9	1095.6	1096.2	1096.9	1097.6	1098.3	1099.0	1099.7	1100.4	1100.4
145°	1136.1	1137.1	1137.6	1138.0	1138.4	1138.9	1139.3	1139.8	1140.2	1140.7	1140.9
147.5°	1172.9	1173.6	1174.1	1174.5	1175.0	1175.4	1175.9	1176.3	1176.7	1177.2	1176.9
150°	1195.4	1196.0	1196.4	1196.9	1197.3	1197.8	1198.2	1198.7	1199.1	1199.6	1199.4
152.5°	1215.6	1215.9	1216.1	1216.4	1216.7	1216.9	1217.7	1218.5	1219.3	1220.1	1220.0
155°	1242.9	1242.8	1243.0	1243.2	1243.5	1243.7	1244.8	1245.9	1247.0	1248.1	1248.0
157.5°	1268.1	1267.9	1267.7	1267.5	1267.3	1267.0	1268.4	1269.7	1271.0	1272.4	1272.2
160°	1281.7	1281.5	1281.3	1281.1	1280.8	1280.6	1282.0	1283.3	1284.6	1285.9	1285.8
162.5°	1293.9	1293.5	1293.3	1293.0	1292.8	1292.6	1294.1	1295.6	1297.1	1298.6	1298.7
165°	1309.9	1309.5	1309.2	1309.0	1308.8	1308.6	1310.3	1312.1	1313.9	1315.7	1315.8
167.5°	1321.8	1321.3	1321.3	1321.3	1321.3	1321.3	1323.1	1324.9	1326.7	1328.4	1328.4
170°	1329.0	1328.5	1328.5	1328.5	1328.5	1328.5	1330.3	1332.1	1333.9	1335.6	1335.6
172.5°	1333.1	1332.6	1332.8	1333.0	1333.1	1333.3	1335.1	1336.9	1338.6	1340.4	1340.3
175°	1339.1	1338.6	1338.8	1339.1	1339.3	1339.5	1341.1	1342.6	1344.2	1345.7	1345.6
177.5°	1341.6	1341.2	1341.4	1341.6	1341.7	1341.9	1343.3	1344.7	1346.2	1347.6	1347.4
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P331982

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1033.2	1032.8	1035.7	1033.6	1035.7	1032.8	1033.2	1036.1	1037.0	1037.4	1037.4
5°	961.7	963.3	958.0	958.0	958.0	963.3	961.7	964.8	967.5	969.6	972.7
7.5°	898.0	895.7	895.9	893.1	895.9	895.7	898.0	900.6	903.9	908.5	912.8
10°	859.1	856.0	854.9	855.4	854.9	856.0	859.1	865.4	867.5	871.7	876.4
12.5°	826.8	826.2	819.3	819.4	819.3	826.2	826.8	828.5	833.1	841.9	847.5
15°	788.9	779.0	777.9	781.1	777.9	779.0	788.9	788.9	791.0	797.8	801.0
17.5°	750.9	745.7	746.0	744.4	746.0	745.7	750.9	751.8	753.4	759.0	763.2
20°	730.8	727.7	727.2	723.5	727.2	727.7	730.8	730.8	732.9	735.5	739.7
22.5°	712.4	711.4	711.7	707.6	711.7	711.4	712.4	713.7	715.8	717.5	720.5
25°	689.5	692.1	690.0	690.0	690.0	692.1	689.5	690.0	690.5	693.1	695.2
27.5°	674.0	673.9	672.8	672.8	672.8	673.9	674.0	672.7	672.1	671.2	670.7
30°	662.3	661.7	662.8	662.8	662.8	661.7	662.3	660.2	659.1	658.6	656.5
32.5°	650.5	651.3	651.5	651.9	651.5	651.3	650.5	648.0	646.1	644.8	643.1
35°	632.4	632.9	634.5	633.5	634.5	632.9	632.4	629.3	627.2	624.0	621.4
37.5°	607.9	610.3	609.8	610.6	609.8	610.3	607.9	607.0	604.9	602.5	599.4
40°	589.5	591.1	590.5	590.5	590.5	591.1	589.5	589.0	586.9	585.3	582.7
42.5°	570.6	571.8	570.4	569.6	570.4	571.8	570.6	569.7	568.4	565.6	562.6
45°	539.7	538.7	540.3	538.2	540.3	538.7	539.7	537.7	537.1	535.0	532.4
47.5°	505.2	506.2	506.7	508.2	506.7	506.2	505.2	505.4	502.5	501.2	500.4
50°	482.2	485.3	485.3	484.8	485.3	485.3	482.2	481.1	479.0	476.9	476.9
52.5°	459.5	461.0	463.1	463.0	463.1	461.0	459.5	457.7	455.6	452.6	451.8
55°	424.6	425.6	426.7	427.2	426.7	425.6	424.6	420.4	418.8	417.2	414.6
57.5°	388.3	387.9	390.4	391.2	390.4	387.9	388.3	384.6	382.2	377.4	376.7
60°	362.8	362.8	367.0	368.6	367.0	362.8	362.8	358.6	354.9	351.8	350.8
62.5°	335.6	337.3	341.4	339.2	341.4	337.3	335.6	331.0	328.1	324.2	321.4
65°	295.8	300.0	299.5	301.5	299.5	300.0	295.8	293.2	287.4	283.7	280.6
67.5°	254.2	256.8	260.6	260.9	260.6	256.8	254.2	250.0	246.3	242.4	238.6
70°	226.2	228.8	230.9	232.4	230.9	228.8	226.2	222.0	217.8	215.2	211.0
72.5°	198.9	200.3	205.3	203.1	205.3	200.3	198.9	193.9	190.6	188.4	183.8
75°	156.0	159.7	162.8	161.2	162.8	159.7	156.0	152.3	149.7	146.6	142.4
77.5°	115.4	119.0	120.5	119.2	120.5	119.0	115.4	113.0	111.6	105.4	105.0
80°	91.1	90.6	93.7	93.2	93.7	90.6	91.1	87.4	84.8	81.1	81.1
82.5°	66.8	66.3	67.7	68.1	67.7	66.3	66.8	64.8	61.4	59.8	58.5
85°	32.5	34.0	31.9	31.4	31.9	34.0	32.5	30.4	30.4	30.4	29.8
87.5°	13.3	13.4	13.0	12.7	13.0	13.4	13.3	13.2	14.7	13.3	13.1
90°	28.6	29.1	29.5	29.9	29.5	29.1	28.6	28.2	27.5	26.6	25.7
92.5°	32.3	32.6	32.9	33.1	32.9	32.6	32.3	32.1	31.2	29.8	28.4
95°	37.9	37.9	37.9	37.9	37.9	37.9	37.9	37.9	37.2	35.6	34.0
97.5°	40.5	40.7	40.9	41.1	40.9	40.7	40.5	40.2	39.2	37.5	35.7
100°	41.3	41.5	41.7	41.9	41.7	41.5	41.3	41.0	40.0	38.3	36.5
102.5°	41.5	41.9	42.3	42.7	42.3	41.9	41.5	41.1	43.7	49.2	54.7
105°	42.6	43.0	43.5	43.9	43.5	43.0	42.6	42.1	61.6	100.8	140.1
107.5°	226.7	197.1	167.5	137.9	167.5	197.1	226.7	256.3	285.5	314.3	343.1
110°	369.6	337.9	306.2	274.5	306.2	337.9	369.6	401.4	420.9	428.2	435.5



TEST NUMBER: P331982

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	491.0	484.3	477.6	470.9	477.6	484.3	491.0	497.7	501.0	500.9	500.7
115°	584.2	585.1	586.0	586.9	586.0	585.1	584.2	583.4	581.8	579.6	577.4
117.5°	651.5	651.6	651.8	652.0	651.8	651.6	651.5	651.3	650.3	648.5	646.8
120°	696.7	696.7	696.7	696.7	696.7	696.7	696.7	696.7	695.8	694.0	692.3
122.5°	740.1	740.3	740.4	740.6	740.4	740.3	740.1	739.9	739.2	738.0	736.7
125°	801.2	801.6	802.1	802.5	802.1	801.6	801.2	800.7	800.3	799.8	799.4
127.5°	863.3	862.9	862.4	862.0	862.4	862.9	863.3	863.8	863.6	862.9	862.2
130°	901.7	901.2	900.8	900.3	900.8	901.2	901.7	902.1	901.9	901.0	900.1
132.5°	937.3	936.7	936.1	935.5	936.1	936.7	937.3	937.9	937.8	936.9	936.0
135°	991.2	990.5	989.8	989.2	989.8	990.5	991.2	991.8	991.8	991.2	990.5
137.5°	1041.0	1040.6	1040.1	1039.7	1040.1	1040.6	1041.0	1041.4	1041.1	1040.1	1039.0
140°	1071.3	1070.9	1070.5	1070.0	1070.5	1070.9	1071.3	1071.8	1071.6	1070.7	1069.8
142.5°	1099.8	1099.2	1098.6	1098.0	1098.6	1099.2	1099.8	1100.4	1100.4	1099.7	1099.0
145°	1140.9	1140.9	1140.9	1140.9	1140.9	1140.9	1140.9	1140.9	1140.7	1140.2	1139.8
147.5°	1175.9	1174.9	1173.8	1172.8	1173.8	1174.9	1175.9	1176.9	1177.2	1176.7	1176.3
150°	1198.8	1198.1	1197.4	1196.8	1197.4	1198.1	1198.8	1199.4	1199.6	1199.1	1198.7
152.5°	1219.0	1218.0	1217.0	1215.9	1217.0	1218.0	1219.0	1220.0	1220.1	1219.3	1218.5
155°	1246.7	1245.4	1244.0	1242.7	1244.0	1245.4	1246.7	1248.0	1248.1	1247.0	1245.9
157.5°	1270.4	1268.7	1267.0	1265.3	1267.0	1268.7	1270.4	1272.2	1272.4	1271.0	1269.7
160°	1284.3	1282.7	1281.2	1279.6	1281.2	1282.7	1284.3	1285.8	1285.9	1284.6	1283.3
162.5°	1297.3	1295.9	1294.6	1293.2	1294.6	1295.9	1297.3	1298.7	1298.6	1297.1	1295.6
165°	1314.2	1312.7	1311.1	1309.6	1311.1	1312.7	1314.2	1315.8	1315.7	1313.9	1312.1
167.5°	1326.7	1324.9	1323.1	1321.3	1323.1	1324.9	1326.7	1328.4	1328.4	1326.7	1324.9
170°	1333.9	1332.1	1330.3	1328.5	1330.3	1332.1	1333.9	1335.6	1335.6	1333.9	1332.1
172.5°	1338.4	1336.4	1334.5	1332.5	1334.5	1336.4	1338.4	1340.3	1340.4	1338.6	1336.9
175°	1343.8	1342.1	1340.3	1338.5	1340.3	1342.1	1343.8	1345.6	1345.7	1344.2	1342.6
177.5°	1345.6	1343.9	1342.1	1340.3	1342.1	1343.9	1345.6	1347.4	1347.6	1346.2	1344.7
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P331982

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1036.1	1036.1	1044.1	1049.1	1055.4	1059.6	1062.5	1065.5	1070.5	1077.2	1084.7
5°	976.9	979.0	990.5	1002.0	1013.0	1022.4	1030.3	1039.7	1051.2	1065.4	1081.1
7.5°	919.5	927.6	939.2	953.2	968.6	982.3	996.3	1011.8	1028.0	1048.8	1070.8
10°	882.7	891.6	905.7	923.5	939.7	955.9	973.2	990.0	1010.4	1035.0	1063.3
12.5°	850.4	858.9	873.4	892.9	908.3	926.2	946.0	967.8	990.7	1020.3	1052.4
15°	805.7	815.6	833.4	842.9	866.4	887.9	906.2	937.6	966.9	997.3	1034.5
17.5°	769.0	774.6	789.0	806.5	824.1	848.2	872.2	898.4	927.6	964.7	1011.2
20°	743.9	748.6	764.3	782.7	801.5	823.5	845.0	871.1	904.1	943.4	993.6
22.5°	725.1	730.2	740.5	760.0	777.6	795.9	817.3	848.5	883.6	922.0	976.5
25°	697.8	701.0	707.8	723.5	739.2	759.6	778.5	807.8	843.9	888.9	943.4
27.5°	672.0	675.0	680.7	692.0	706.6	723.2	743.7	768.6	805.3	854.2	912.0
30°	656.5	657.0	662.3	672.7	685.3	698.9	717.7	746.0	780.6	830.3	891.0
32.5°	643.1	641.1	644.7	652.6	664.8	678.4	693.9	721.7	755.0	803.9	866.3
35°	620.4	619.3	617.8	624.6	635.0	645.5	659.1	680.1	717.7	763.3	828.7
37.5°	597.2	594.7	591.9	595.0	603.2	614.1	625.9	644.6	677.0	727.2	789.8
40°	580.1	578.0	576.4	575.3	582.7	593.1	602.0	619.8	650.2	697.8	759.6
42.5°	561.2	560.0	558.0	556.5	562.6	570.5	579.8	595.6	625.9	670.6	729.1
45°	530.8	529.8	528.8	527.7	531.4	538.7	546.0	557.5	583.7	627.2	680.1
47.5°	497.0	495.7	496.1	494.4	498.0	502.9	508.0	520.4	545.5	580.6	619.2
50°	472.7	472.2	472.2	472.2	473.3	479.0	483.7	493.2	516.2	551.3	579.0
52.5°	449.7	447.5	447.5	448.3	450.2	453.9	456.9	467.2	487.3	516.1	541.3
55°	413.6	409.4	408.3	409.4	411.0	414.1	417.2	425.6	442.9	464.4	479.0
57.5°	373.6	371.3	369.9	370.1	371.0	373.5	375.9	385.0	398.6	409.8	419.2
60°	345.5	346.6	341.9	342.9	342.9	345.0	348.7	354.4	365.9	373.8	383.2
62.5°	319.1	317.7	316.3	314.8	314.8	315.7	320.6	325.1	334.9	339.0	346.4
65°	278.0	278.0	274.8	275.9	276.4	272.8	275.4	280.6	286.9	288.5	295.3
67.5°	236.3	234.9	233.1	231.5	231.5	231.2	232.5	235.2	239.9	240.4	245.6
70°	207.8	206.8	206.3	204.7	202.6	205.2	203.6	206.3	208.9	209.4	212.5
72.5°	180.2	179.1	178.2	176.6	175.8	175.5	175.6	178.6	180.4	179.7	183.2
75°	140.8	139.8	138.7	136.1	136.1	134.5	135.1	137.2	139.3	137.7	140.8
77.5°	103.4	100.2	100.0	100.7	98.9	99.3	98.6	98.3	99.3	99.4	102.2
80°	79.6	75.9	77.0	76.4	75.9	75.4	74.3	74.9	75.4	75.9	77.5
82.5°	57.4	57.1	56.0	55.9	55.4	54.0	53.4	54.3	54.9	54.6	55.7
85°	29.3	27.7	28.8	28.3	28.8	28.3	26.7	26.7	27.7	27.2	28.3
87.5°	13.8	13.6	12.6	12.4	11.4	11.3	10.4	10.3	10.3	9.9	10.3
90°	24.8	24.0	21.1	18.2	15.3	12.4	9.9	7.7	5.4	3.2	1.0
92.5°	27.0	25.6	23.4	21.2	19.0	16.9	16.1	16.7	17.3	17.9	18.6
95°	32.5	30.9	28.5	26.1	23.6	21.2	24.5	33.6	42.7	51.8	60.9
97.5°	33.9	32.1	48.1	64.1	80.1	96.0	106.0	110.1	114.2	118.3	122.4
100°	34.7	32.9	67.5	102.1	136.7	171.3	186.4	182.0	177.6	173.1	168.7
102.5°	60.2	65.7	103.5	141.3	179.1	216.9	234.2	231.0	227.8	224.6	221.4
105°	179.3	218.6	238.6	258.5	278.5	298.4	307.2	304.8	302.3	299.9	297.4
107.5°	371.9	400.7	397.5	394.4	391.2	388.1	385.5	383.6	381.6	379.7	377.7
110°	442.8	450.2	447.7	445.3	442.8	440.4	438.3	436.5	434.7	433.0	431.2



TEST NUMBER: P331982

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	500.6	500.5	498.0	495.6	493.2	490.7	488.7	487.1	485.5	483.9	482.3
115°	575.2	572.9	570.9	568.9	566.9	565.0	563.3	562.0	560.6	559.3	558.0
117.5°	645.0	643.2	642.2	641.2	640.1	639.1	637.8	636.2	634.5	632.9	631.2
120°	690.5	688.7	688.1	687.4	686.7	686.1	684.7	682.7	680.7	678.7	676.7
122.5°	735.5	734.2	733.4	732.6	731.7	730.9	729.6	728.0	726.3	724.7	723.1
125°	799.0	798.5	797.6	796.7	795.9	795.0	793.6	791.9	790.1	788.3	786.5
127.5°	861.5	860.8	859.7	858.7	857.6	856.5	855.1	853.3	851.6	849.8	848.0
130°	899.2	898.3	897.4	896.6	895.7	894.8	893.5	891.7	889.9	888.1	886.4
132.5°	935.2	934.3	933.6	932.8	932.1	931.4	930.2	928.4	926.6	924.9	923.1
135°	989.8	989.2	988.3	987.4	986.5	985.6	984.5	983.2	981.8	980.5	979.2
137.5°	1037.9	1036.9	1036.4	1035.9	1035.4	1034.9	1033.8	1032.2	1030.5	1028.8	1027.1
140°	1068.9	1068.0	1067.4	1066.7	1066.0	1065.4	1064.4	1063.0	1061.7	1060.4	1059.0
142.5°	1098.3	1097.6	1096.9	1096.2	1095.6	1094.9	1093.9	1092.6	1091.2	1089.9	1088.6
145°	1139.3	1138.9	1138.4	1138.0	1137.6	1137.1	1136.1	1134.6	1133.0	1131.5	1129.9
147.5°	1175.9	1175.4	1175.0	1174.5	1174.1	1173.6	1172.9	1171.9	1170.9	1169.9	1168.8
150°	1198.2	1197.8	1197.3	1196.9	1196.4	1196.0	1195.4	1194.8	1194.1	1193.5	1192.8
152.5°	1217.7	1216.9	1216.7	1216.4	1216.1	1215.9	1215.6	1215.3	1215.0	1214.7	1214.3
155°	1244.8	1243.7	1243.5	1243.2	1243.0	1242.8	1242.9	1243.4	1243.8	1244.2	1244.7
157.5°	1268.4	1267.0	1267.3	1267.5	1267.7	1267.9	1268.1	1268.1	1268.2	1268.2	1268.2
160°	1282.0	1280.6	1280.8	1281.1	1281.3	1281.5	1281.7	1282.0	1282.2	1282.4	1282.6
162.5°	1294.1	1292.6	1292.8	1293.0	1293.3	1293.5	1293.9	1294.5	1295.0	1295.6	1296.2
165°	1310.3	1308.6	1308.8	1309.0	1309.2	1309.5	1309.9	1310.6	1311.2	1311.9	1312.6
167.5°	1323.1	1321.3	1321.3	1321.3	1321.3	1321.3	1321.8	1322.7	1323.6	1324.5	1325.3
170°	1330.3	1328.5	1328.5	1328.5	1328.5	1328.5	1329.0	1329.9	1330.8	1331.6	1332.5
172.5°	1335.1	1333.3	1333.1	1333.0	1332.8	1332.6	1333.1	1334.1	1335.2	1336.3	1337.3
175°	1341.1	1339.5	1339.3	1339.1	1338.8	1338.6	1339.1	1340.2	1341.3	1342.4	1343.5
177.5°	1343.3	1341.9	1341.7	1341.6	1341.4	1341.2	1341.6	1342.4	1343.3	1344.2	1345.1
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P331982

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1087.2	1089.3	1096.5	1101.5	1107.3	1110.7	1114.0	1116.6	1119.9	1120.7	1132.9
5°	1092.1	1102.5	1120.9	1134.5	1151.2	1169.5	1182.1	1187.9	1203.0	1215.6	1240.7
7.5°	1090.7	1113.0	1140.6	1169.3	1200.1	1228.6	1253.3	1282.6	1303.5	1334.8	1365.6
10°	1089.4	1119.3	1154.9	1191.5	1234.5	1274.2	1309.8	1349.6	1382.6	1426.1	1463.2
12.5°	1085.7	1121.8	1171.2	1214.6	1266.7	1321.6	1374.3	1425.4	1454.6	1527.0	1561.2
15°	1076.4	1119.3	1181.1	1247.0	1318.7	1383.7	1450.7	1504.1	1590.4	1653.8	1694.1
17.5°	1058.6	1118.7	1191.9	1271.5	1358.7	1444.3	1520.2	1601.2	1692.8	1769.5	1851.2
20°	1050.2	1116.1	1197.8	1285.8	1376.3	1473.2	1559.6	1656.9	1756.9	1832.3	1937.0
22.5°	1034.7	1109.4	1197.4	1295.4	1392.2	1492.4	1593.5	1691.7	1807.2	1911.1	2010.7
25°	1009.3	1093.1	1184.2	1293.6	1407.2	1507.7	1628.7	1759.0	1879.4	2012.9	2112.4
27.5°	982.7	1072.2	1163.5	1265.2	1387.4	1506.7	1658.8	1806.1	1953.4	2068.6	2142.2
30°	962.2	1049.1	1143.4	1246.0	1366.9	1508.8	1678.9	1839.6	1983.1	2082.0	2123.4
32.5°	940.0	1028.2	1111.5	1219.2	1348.1	1507.5	1691.5	1859.3	1984.8	2050.6	2042.6
35°	905.2	979.0	1060.1	1163.8	1315.6	1498.3	1698.8	1861.1	1938.1	1923.9	1817.1
37.5°	854.9	917.0	996.9	1110.4	1277.9	1478.9	1684.2	1805.9	1800.9	1685.8	1531.1
40°	823.5	876.4	953.3	1072.7	1248.6	1466.4	1661.1	1740.2	1673.2	1512.4	1327.1
42.5°	782.5	831.1	908.1	1030.8	1216.3	1440.8	1617.1	1640.1	1509.0	1324.0	1154.1
45°	718.8	761.7	841.3	968.0	1168.0	1385.2	1509.8	1453.8	1277.4	1086.3	957.0
47.5°	650.4	695.0	771.6	901.7	1098.0	1301.6	1360.9	1241.8	1060.6	905.7	787.0
50°	607.3	650.2	725.1	856.5	1050.7	1232.9	1257.5	1103.6	937.1	801.0	703.6
52.5°	563.7	604.1	677.7	809.6	995.4	1153.3	1138.1	981.3	828.2	712.2	635.8
55°	498.9	537.1	607.3	730.8	899.9	1025.0	970.1	820.4	693.7	603.6	545.5
57.5°	440.9	477.6	538.1	649.7	796.7	882.7	812.7	686.5	585.8	516.5	473.2
60°	401.5	434.0	491.6	595.2	723.0	788.4	719.3	607.8	523.0	467.5	428.8
62.5°	364.3	392.5	445.9	540.0	650.9	705.9	636.0	541.6	469.4	420.2	387.3
65°	307.8	333.5	380.6	453.9	545.0	581.6	521.4	445.0	389.0	352.3	330.3
67.5°	256.3	278.1	318.8	376.5	443.5	470.2	424.4	365.2	323.0	293.6	276.1
70°	222.0	240.8	272.8	322.5	383.2	403.6	360.7	312.0	281.1	257.6	241.3
72.5°	193.1	206.9	235.9	274.3	325.0	341.2	311.3	268.5	239.7	222.0	209.1
75°	147.1	158.6	177.5	208.4	243.4	252.9	230.3	203.6	184.3	171.7	161.8
77.5°	106.1	114.5	128.2	147.2	171.5	180.0	165.7	147.9	133.8	125.3	119.8
80°	80.1	86.9	98.4	114.1	128.8	133.5	125.1	111.5	101.6	96.9	92.1
82.5°	59.2	63.0	69.9	80.6	90.7	96.2	89.1	80.9	75.6	71.3	69.5
85°	29.8	31.9	35.1	39.3	45.5	47.6	45.0	42.9	39.8	37.2	37.2
87.5°	11.5	12.0	13.7	15.0	17.1	19.0	19.1	18.9	19.0	18.8	18.5
90°	3.2	5.4	7.7	9.9	12.4	15.3	18.2	21.1	24.0	24.8	25.7
92.5°	17.9	17.3	16.7	16.1	16.9	19.0	21.2	23.4	25.6	27.0	28.4
95°	51.8	42.7	33.6	24.5	21.2	23.6	26.1	28.5	30.9	32.5	34.0
97.5°	118.3	114.2	110.1	106.0	96.0	80.1	64.1	48.1	32.1	33.9	35.7
100°	173.1	177.6	182.0	186.4	171.3	136.7	102.1	67.5	32.9	34.7	36.5
102.5°	224.6	227.8	231.0	234.2	216.9	179.1	141.3	103.5	65.7	60.2	54.7
105°	299.9	302.3	304.8	307.2	298.4	278.5	258.5	238.6	218.6	179.3	140.1
107.5°	379.7	381.6	383.6	385.5	388.1	391.2	394.4	397.5	400.7	371.9	343.1
110°	433.0	434.7	436.5	438.3	440.4	442.8	445.3	447.7	450.2	442.8	435.5





TEST NUMBER: P331982

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	483.9	485.5	487.1	488.7	490.7	493.2	495.6	498.0	500.5	500.6	500.7
115°	559.3	560.6	562.0	563.3	565.0	566.9	568.9	570.9	572.9	575.2	577.4
117.5°	632.9	634.5	636.2	637.8	639.1	640.1	641.2	642.2	643.2	645.0	646.8
120°	678.7	680.7	682.7	684.7	686.1	686.7	687.4	688.1	688.7	690.5	692.3
122.5°	724.7	726.3	728.0	729.6	730.9	731.7	732.6	733.4	734.2	735.5	736.7
125°	788.3	790.1	791.9	793.6	795.0	795.9	796.7	797.6	798.5	799.0	799.4
127.5°	849.8	851.6	853.3	855.1	856.5	857.6	858.7	859.7	860.8	861.5	862.2
130°	888.1	889.9	891.7	893.5	894.8	895.7	896.6	897.4	898.3	899.2	900.1
132.5°	924.9	926.6	928.4	930.2	931.4	932.1	932.8	933.6	934.3	935.2	936.0
135°	980.5	981.8	983.2	984.5	985.6	986.5	987.4	988.3	989.2	989.8	990.5
137.5°	1028.8	1030.5	1032.2	1033.8	1034.9	1035.4	1035.9	1036.4	1036.9	1037.9	1039.0
140°	1060.4	1061.7	1063.0	1064.4	1065.4	1066.0	1066.7	1067.4	1068.0	1068.9	1069.8
142.5°	1089.9	1091.2	1092.6	1093.9	1094.9	1095.6	1096.2	1096.9	1097.6	1098.3	1099.0
145°	1131.5	1133.0	1134.6	1136.1	1137.1	1137.6	1138.0	1138.4	1138.9	1139.3	1139.8
147.5°	1169.9	1170.9	1171.9	1172.9	1173.6	1174.1	1174.5	1175.0	1175.4	1175.9	1176.3
150°	1193.5	1194.1	1194.8	1195.4	1196.0	1196.4	1196.9	1197.3	1197.8	1198.2	1198.7
152.5°	1214.7	1215.0	1215.3	1215.6	1215.9	1216.1	1216.4	1216.7	1216.9	1217.7	1218.5
155°	1244.2	1243.8	1243.4	1242.9	1242.8	1243.0	1243.2	1243.5	1243.7	1244.8	1245.9
157.5°	1268.2	1268.2	1268.1	1268.1	1267.9	1267.7	1267.5	1267.3	1267.0	1268.4	1269.7
160°	1282.4	1282.2	1282.0	1281.7	1281.5	1281.3	1281.1	1280.8	1280.6	1282.0	1283.3
162.5°	1295.6	1295.0	1294.5	1293.9	1293.5	1293.3	1293.0	1292.8	1292.6	1294.1	1295.6
165°	1311.9	1311.2	1310.6	1309.9	1309.5	1309.2	1309.0	1308.8	1308.6	1310.3	1312.1
167.5°	1324.5	1323.6	1322.7	1321.8	1321.3	1321.3	1321.3	1321.3	1321.3	1323.1	1324.9
170°	1331.6	1330.8	1329.9	1329.0	1328.5	1328.5	1328.5	1328.5	1328.5	1330.3	1332.1
172.5°	1336.3	1335.2	1334.1	1333.1	1332.6	1332.8	1333.0	1333.1	1333.3	1335.1	1336.9
175°	1342.4	1341.3	1340.2	1339.1	1338.6	1338.8	1339.1	1339.3	1339.5	1341.1	1342.6
177.5°	1344.2	1343.3	1342.4	1341.6	1341.2	1341.4	1341.6	1341.7	1341.9	1343.3	1344.7
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P331982

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1137.1	1137.5	1142.1	1145.5	1143.8	1145.9	1146.7
5°	1242.3	1261.2	1271.1	1278.4	1279.0	1279.5	1283.7
7.5°	1391.5	1411.7	1426.5	1448.9	1455.6	1463.2	1461.0
10°	1500.4	1530.2	1555.9	1569.5	1584.2	1605.6	1588.4
12.5°	1602.2	1655.1	1694.1	1715.3	1729.1	1733.4	1724.9
15°	1770.0	1839.1	1876.3	1875.2	1922.4	1942.8	1910.8
17.5°	1923.9	1987.7	2038.8	2065.0	2104.2	2112.9	2108.9
20°	2018.2	2087.8	2127.6	2172.6	2193.0	2211.3	2214.5
22.5°	2099.4	2161.9	2204.6	2242.1	2259.2	2267.9	2273.1
25°	2183.1	2232.3	2257.9	2271.0	2275.7	2274.7	2267.9
27.5°	2177.3	2181.1	2152.8	2125.1	2100.3	2072.3	2062.7
30°	2120.8	2076.8	1998.3	1953.8	1888.3	1836.5	1857.4
32.5°	1972.1	1884.6	1796.4	1699.1	1618.6	1595.7	1572.6
35°	1683.1	1529.2	1439.2	1334.4	1292.6	1250.7	1221.9
37.5°	1361.7	1242.6	1135.8	1067.3	1025.4	998.9	984.6
40°	1177.4	1070.1	982.1	926.6	894.7	864.9	860.7
42.5°	1030.4	930.6	864.4	820.2	789.6	776.9	767.7
45°	843.9	774.3	729.8	698.4	678.0	670.1	659.6
47.5°	714.3	665.1	631.7	610.3	594.9	589.1	588.2
50°	641.8	601.0	576.4	559.6	547.6	545.5	537.1
52.5°	587.4	552.0	532.8	518.2	509.5	503.6	501.1
55°	509.9	486.3	469.1	460.7	453.9	448.1	448.1
57.5°	446.1	426.5	415.0	407.9	405.8	401.7	399.1
60°	406.8	390.0	381.1	374.8	370.7	371.2	366.5
62.5°	368.2	357.4	348.9	342.6	337.6	337.7	338.0
65°	313.6	305.2	298.9	296.8	293.7	290.0	291.1
67.5°	265.7	257.9	253.0	249.4	248.4	246.4	249.4
70°	231.4	225.6	222.0	218.8	217.8	218.3	220.9
72.5°	200.0	195.9	193.5	192.0	189.7	189.8	191.6
75°	157.1	153.9	151.8	150.2	149.7	149.7	149.7
77.5°	115.4	114.7	113.7	111.4	111.5	112.1	112.2
80°	91.1	89.5	89.0	88.0	86.4	85.3	88.0
82.5°	68.1	66.5	66.0	65.8	63.3	63.1	65.3
85°	36.6	35.1	35.6	35.1	35.1	34.6	34.6
87.5°	18.3	18.1	17.8	18.3	18.0	17.6	18.6
90°	26.6	27.5	28.2	28.6	29.1	29.5	29.9
92.5°	29.8	31.2	32.1	32.3	32.6	32.9	33.1
95°	35.6	37.2	37.9	37.9	37.9	37.9	37.9
97.5°	37.5	39.2	40.2	40.5	40.7	40.9	41.1
100°	38.3	40.0	41.0	41.3	41.5	41.7	41.9
102.5°	49.2	43.7	41.1	41.5	41.9	42.3	42.7
105°	100.8	61.6	42.1	42.6	43.0	43.5	43.9
107.5°	314.3	285.5	256.3	226.7	197.1	167.5	137.9
110°	428.2	420.9	401.4	369.6	337.9	306.2	274.5



TEST NUMBER: P331982

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	500.9	501.0	497.7	491.0	484.3	477.6	470.9
115°	579.6	581.8	583.4	584.2	585.1	586.0	586.9
117.5°	648.5	650.3	651.3	651.5	651.6	651.8	652.0
120°	694.0	695.8	696.7	696.7	696.7	696.7	696.7
122.5°	738.0	739.2	739.9	740.1	740.3	740.4	740.6
125°	799.8	800.3	800.7	801.2	801.6	802.1	802.5
127.5°	862.9	863.6	863.8	863.3	862.9	862.4	862.0
130°	901.0	901.9	902.1	901.7	901.2	900.8	900.3
132.5°	936.9	937.8	937.9	937.3	936.7	936.1	935.5
135°	991.2	991.8	991.8	991.2	990.5	989.8	989.2
137.5°	1040.1	1041.1	1041.4	1041.0	1040.6	1040.1	1039.7
140°	1070.7	1071.6	1071.8	1071.3	1070.9	1070.5	1070.0
142.5°	1099.7	1100.4	1100.4	1099.8	1099.2	1098.6	1098.0
145°	1140.2	1140.7	1140.9	1140.9	1140.9	1140.9	1140.9
147.5°	1176.7	1177.2	1176.9	1175.9	1174.9	1173.8	1172.8
150°	1199.1	1199.6	1199.4	1198.8	1198.1	1197.4	1196.8
152.5°	1219.3	1220.1	1220.0	1219.0	1218.0	1217.0	1215.9
155°	1247.0	1248.1	1248.0	1246.7	1245.4	1244.0	1242.7
157.5°	1271.0	1272.4	1272.2	1270.4	1268.7	1267.0	1265.3
160°	1284.6	1285.9	1285.8	1284.3	1282.7	1281.2	1279.6
162.5°	1297.1	1298.6	1298.7	1297.3	1295.9	1294.6	1293.2
165°	1313.9	1315.7	1315.8	1314.2	1312.7	1311.1	1309.6
167.5°	1326.7	1328.4	1328.4	1326.7	1324.9	1323.1	1321.3
170°	1333.9	1335.6	1335.6	1333.9	1332.1	1330.3	1328.5
172.5°	1338.6	1340.4	1340.3	1338.4	1336.4	1334.5	1332.5
175°	1344.2	1345.7	1345.6	1343.8	1342.1	1340.3	1338.5
177.5°	1346.2	1347.6	1347.4	1345.6	1343.9	1342.1	1340.3
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5

(END OF REPORT)