

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332062-830

Luminaire Tested: **S123DIP-S1165D585U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332062-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D585U830-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6483.7 lumens
Efficiency: N/A
Efficacy: 117.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332062-830

CATALOG NUMBER: S123DIP-S1165D585U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332062-830

CATALOG NUMBER: S123DIP-S1165D585U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74	69
1	102	98	93	90	96	92	89	85	82	80	77	73	71	69	65	64	62	58
2	93	85	79	73	87	81	75	70	72	68	64	64	61	58	57	55	52	49
3	85	75	67	61	80	71	64	59	64	58	54	57	53	49	51	47	44	41
4	78	66	58	52	73	63	56	50	57	51	46	51	46	42	45	41	38	35
5	71	59	51	45	67	56	49	43	51	44	40	46	40	36	41	37	33	31
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	33	29	27
7	61	48	40	34	57	46	38	33	42	35	31	38	32	28	34	29	26	24
8	57	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23	21
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	24	21	19
10	49	37	29	24	47	35	28	24	32	26	22	29	24	21	27	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18547	18547	18547
5°	18634	18377	18506
10°	18510	18218	18332
15°	18293	18013	18046
20°	18040	17718	17734
25°	17701	17368	17332
30°	17329	16978	16850
35°	16938	16567	16353
40°	16530	16114	15864
45°	16081	15696	15314
50°	15630	15183	14763
55°	15041	14653	14208
60°	14449	14034	13586
65°	13924	13359	12944
70°	13149	12589	12032
75°	12015	11582	11088
80°	10835	10377	10290
85°	9510	9152	8793



TEST NUMBER: P332062-830

CATALOG NUMBER: S123DIP-S1165D585U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.3	2.5
10°-20°	458.3	7.1
20°-30°	677.0	10.4
30°-40°	790.8	12.2
40°-50°	795.1	12.3
50°-60°	698.4	10.8
60°-70°	520.3	8.0
70°-80°	296.4	4.6
80°-90°	87.1	1.3
90°-100°	147.8	2.3
100°-110°	418.5	6.5
110°-120°	411.7	6.3
120°-130°	328.4	5.1
130°-140°	258.9	4.0
140°-150°	193.2	3.0
150°-160°	134.7	2.1
160°-170°	79.1	1.2
170°-180°	25.7	0.4
0°-30°	1297.6	20.0
0°-40°	2088.4	32.2
0°-60°	3581.8	55.2
0°-90°	4485.7	69.2
90°-120°	978.0	15.1
90°-150°	1758.5	27.1
90°-180°	1998.0	30.8
0°-180°	6483.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1723	1723	1723	1723	1723	
5°	1725	1717	1701	1715	1713	163
15°	1642	1635	1616	1627	1619	463
25°	1490	1481	1462	1464	1459	686
35°	1289	1280	1261	1252	1244	806
45°	1056	1050	1031	1014	1006	815
55°	802	799	781	765	757	718
65°	547	539	524	513	508	539
75°	289	283	278	271	267	309
85°	77	74	74	71	71	85
90°	1	6	14	15	16	5
95°	18	59	319	93	62	20
105°	62	92	432	756	684	66
115°	110	137	331	725	832	109
125°	153	181	309	559	656	136
135°	180	214	304	460	532	139
145°	205	235	300	378	416	128
155°	233	251	291	331	345	107
165°	254	262	278	295	300	72
175°	265	265	267	271	270	25
180°	266	266	266	266	266	



TEST NUMBER: P332062-830

CATALOG NUMBER: S123DIP-S1165D585U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1
2.5°	1729.0	1728.0	1726.9	1725.9	1724.8	1722.8	1720.0	1717.0	1714.1	1711.2	1713.8
5°	1724.6	1723.0	1721.3	1719.7	1718.0	1715.3	1711.8	1708.1	1704.5	1700.8	1704.1
7.5°	1707.7	1706.0	1704.4	1702.7	1701.1	1698.4	1694.6	1690.9	1687.2	1683.4	1686.3
10°	1693.5	1691.8	1690.2	1688.5	1686.9	1683.9	1679.6	1675.4	1671.0	1666.8	1669.7
12.5°	1674.5	1673.1	1671.7	1670.4	1669.0	1666.2	1662.3	1658.2	1654.2	1650.2	1652.4
15°	1641.6	1640.3	1639.0	1637.7	1636.3	1633.5	1629.3	1624.9	1620.7	1616.4	1619.0
17.5°	1603.4	1601.7	1600.0	1598.3	1596.5	1593.6	1589.2	1585.0	1580.6	1576.4	1578.3
20°	1574.9	1572.9	1570.9	1569.0	1567.1	1563.9	1559.6	1555.4	1551.0	1546.8	1548.1
22.5°	1542.9	1541.0	1539.0	1537.0	1535.0	1531.9	1527.6	1523.3	1519.1	1514.8	1515.8
25°	1490.4	1488.5	1486.5	1484.5	1482.6	1479.4	1475.2	1470.9	1466.6	1462.4	1462.6
27.5°	1434.5	1432.6	1430.7	1428.7	1426.8	1423.6	1419.0	1414.4	1409.8	1405.1	1405.4
30°	1394.2	1392.5	1390.9	1389.2	1387.6	1384.5	1379.9	1375.3	1370.6	1366.0	1366.0
32.5°	1353.9	1351.7	1349.5	1347.4	1345.2	1342.3	1338.8	1335.2	1331.6	1328.1	1326.3
35°	1289.0	1287.0	1285.1	1283.1	1281.1	1278.0	1273.7	1269.4	1265.1	1260.8	1258.9
37.5°	1222.6	1220.1	1217.6	1215.1	1212.6	1209.2	1204.9	1200.5	1196.2	1191.8	1189.4
40°	1176.4	1174.4	1172.4	1170.4	1168.5	1165.2	1160.6	1155.9	1151.3	1146.8	1144.2
42.5°	1130.1	1127.9	1125.7	1123.4	1121.2	1117.8	1113.1	1108.5	1103.9	1099.4	1096.7
45°	1056.4	1055.1	1053.8	1052.4	1051.1	1048.3	1044.1	1039.7	1035.5	1031.1	1027.3
47.5°	983.2	981.3	979.4	977.4	975.5	972.6	968.6	964.5	960.5	956.5	952.6
50°	933.4	931.8	930.1	928.5	926.8	923.9	919.5	915.3	911.0	906.7	903.1
52.5°	881.3	880.1	879.0	877.9	876.8	873.9	869.4	864.9	860.4	855.7	852.6
55°	801.5	801.3	800.9	800.6	800.2	798.0	793.6	789.4	785.0	780.8	777.2
57.5°	725.7	724.5	723.4	722.4	721.2	719.0	715.5	712.1	708.7	705.2	702.0
60°	671.2	670.8	670.5	670.1	669.9	667.7	663.7	659.8	655.8	651.9	648.9
62.5°	622.5	621.7	620.9	620.0	619.2	616.7	612.7	608.8	604.9	601.0	597.9
65°	546.7	545.1	543.4	541.8	540.1	537.6	534.3	531.0	527.7	524.5	521.9
67.5°	466.4	465.0	463.5	462.0	460.6	458.6	456.1	453.6	451.1	448.7	446.3
70°	417.8	415.8	413.9	411.9	409.9	407.9	406.0	404.0	402.0	400.0	397.8
72.5°	366.8	365.4	363.9	362.5	361.1	359.2	356.9	354.7	352.5	350.2	348.2
75°	288.9	287.6	286.3	284.9	283.6	282.5	281.5	280.5	279.6	278.5	276.9
77.5°	219.9	219.1	218.4	217.7	217.0	216.0	214.8	213.7	212.4	211.3	210.2
80°	174.8	173.8	172.9	171.8	170.9	170.0	169.4	168.7	168.1	167.4	167.1
82.5°	131.0	130.7	130.5	130.4	130.2	130.0	129.9	129.8	129.6	129.5	128.9
85°	77.0	76.3	75.7	75.0	74.4	74.1	74.1	74.1	74.1	74.1	73.4
87.5°	31.0	30.4	29.9	29.4	28.8	28.6	28.6	28.7	28.7	28.7	28.4
90°	1.0	2.2	3.2	4.8	5.9	7.0	8.6	10.2	11.8	13.5	12.9
92.5°	6.7	9.9	14.4	18.6	23.1	31.1	45.1	68.2	91.0	82.7	62.4
95°	18.3	19.9	25.8	35.0	48.9	69.8	115.6	195.7	283.9	318.8	258.5
97.5°	31.2	31.8	36.4	44.3	58.1	80.8	124.4	214.7	361.7	494.1	528.6
100°	39.8	40.3	44.1	51.7	64.5	85.5	123.1	202.6	344.0	509.1	615.0
102.5°	48.8	49.8	53.2	60.2	71.8	91.0	124.8	192.4	318.3	481.2	619.3
105°	62.4	64.0	67.2	73.6	83.9	100.6	129.6	184.9	286.5	432.3	586.5
107.5°	76.7	78.4	81.5	87.8	97.5	112.9	138.4	184.4	266.4	389.0	529.1
110°	87.1	88.7	91.4	97.3	106.4	121.5	145.7	186.5	258.5	364.5	492.9



TEST NUMBER: P332062-830

CATALOG NUMBER: S123DIP-S1165D585U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	96.5	98.2	100.9	106.8	115.9	130.5	153.0	190.9	254.3	348.2	461.6
115°	110.2	112.4	115.6	120.9	130.1	144.6	165.0	197.8	252.7	330.6	423.7
117.5°	123.9	126.3	129.0	133.9	144.2	157.6	177.9	207.1	253.6	320.3	400.8
120°	133.4	135.0	137.6	143.0	153.3	166.6	186.0	214.0	255.3	315.6	388.7
122.5°	141.5	143.1	145.8	151.6	161.4	175.7	194.6	220.5	258.4	312.5	378.8
125°	153.3	154.3	157.5	163.4	173.6	188.1	207.0	230.6	262.9	308.6	366.1
127.5°	162.1	163.7	167.8	173.7	185.0	199.5	217.7	239.0	268.1	306.6	355.0
130°	167.8	169.4	174.2	180.6	191.9	206.4	224.1	244.6	271.5	305.4	348.9
132.5°	172.0	174.1	179.4	187.1	198.4	212.4	229.8	249.8	274.1	304.9	343.3
135°	179.6	181.7	187.7	195.7	207.0	221.5	238.2	256.5	278.0	304.3	336.0
137.5°	186.6	188.9	194.7	203.3	214.5	227.9	243.9	261.4	280.5	303.1	329.7
140°	191.4	194.1	199.4	208.0	218.8	232.2	247.8	264.0	282.2	302.7	325.7
142.5°	196.5	198.8	204.6	212.4	223.1	235.7	250.8	266.6	283.5	301.8	322.3
145°	204.8	206.4	211.3	219.3	228.5	240.8	254.9	269.4	284.4	300.5	317.7
147.5°	213.2	214.1	219.0	225.9	234.7	245.2	258.1	271.1	284.4	298.5	313.2
150°	218.8	219.3	223.7	230.6	238.2	247.8	260.2	271.5	284.4	296.7	310.2
152.5°	224.4	224.5	228.8	235.0	241.6	250.8	261.5	272.4	283.1	294.6	306.8
155°	232.8	232.8	236.0	241.4	247.3	254.9	264.0	272.6	281.7	290.9	301.6
157.5°	239.4	239.9	242.4	247.2	252.2	258.1	265.3	273.1	279.8	287.5	295.8
160°	244.6	244.6	246.8	251.1	254.9	260.2	266.6	273.1	279.0	284.9	291.9
162.5°	248.5	248.5	250.2	253.6	256.9	261.5	267.1	272.7	277.3	282.4	288.0
165°	254.3	253.7	254.9	257.5	259.7	263.4	267.7	271.5	274.8	278.5	282.8
167.5°	258.7	258.1	258.5	260.6	262.1	264.5	267.6	270.6	272.1	274.6	277.8
170°	261.3	260.2	260.7	262.3	263.4	264.5	267.2	269.4	270.4	272.0	274.8
172.5°	263.0	262.3	262.5	263.6	264.3	264.9	267.2	268.9	269.1	269.8	271.7
175°	265.0	264.5	264.0	265.0	265.0	265.6	266.6	267.7	267.2	267.2	268.2
177.5°	266.0	265.6	265.1	265.6	265.6	265.6	266.0	266.8	266.0	265.6	266.0
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6



TEST NUMBER: P332062-830

CATALOG NUMBER: S123DIP-S1165D585U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1
2.5°	1716.5	1719.1	1721.7	1723.0	1722.7	1722.4	1722.1	1721.9
5°	1707.4	1710.7	1714.0	1715.3	1714.7	1714.0	1713.4	1712.7
7.5°	1689.3	1692.2	1695.3	1696.5	1696.1	1695.7	1695.4	1695.0
10°	1672.7	1675.7	1678.7	1679.8	1679.1	1678.5	1677.8	1677.2
12.5°	1654.5	1656.7	1658.9	1659.8	1659.3	1659.0	1658.6	1658.2
15°	1621.6	1624.3	1626.9	1627.3	1625.3	1623.3	1621.4	1619.4
17.5°	1580.1	1582.0	1583.8	1584.3	1583.7	1582.9	1582.2	1581.5
20°	1549.4	1550.8	1552.1	1552.2	1551.2	1550.2	1549.3	1548.2
22.5°	1516.9	1518.0	1519.0	1518.9	1517.7	1516.4	1515.1	1513.9
25°	1463.0	1463.3	1463.7	1463.3	1462.4	1461.3	1460.4	1459.3
27.5°	1405.7	1405.9	1406.2	1405.7	1404.5	1403.2	1401.9	1400.7
30°	1366.0	1366.0	1366.0	1364.9	1362.5	1360.3	1357.9	1355.7
32.5°	1324.4	1322.6	1320.7	1319.2	1318.0	1316.6	1315.4	1314.2
35°	1256.9	1254.9	1252.9	1251.1	1249.4	1247.8	1246.1	1244.5
37.5°	1187.0	1184.7	1182.3	1180.6	1179.5	1178.5	1177.4	1176.4
40°	1141.5	1138.9	1136.2	1134.3	1132.9	1131.6	1130.3	1129.0
42.5°	1094.1	1091.5	1088.8	1086.8	1085.5	1084.2	1082.9	1081.6
45°	1023.3	1019.4	1015.4	1012.6	1011.0	1009.3	1007.7	1006.0
47.5°	948.8	944.9	940.9	938.3	936.9	935.4	934.0	932.6
50°	899.5	895.9	892.2	889.5	887.5	885.5	883.5	881.6
52.5°	849.6	846.5	843.4	840.8	838.9	836.9	834.9	832.9
55°	773.5	770.0	766.3	763.6	762.0	760.3	758.7	757.1
57.5°	698.8	695.6	692.3	689.8	687.9	686.0	684.0	682.1
60°	646.0	643.0	640.1	637.7	636.1	634.4	632.8	631.1
62.5°	595.0	592.0	589.1	587.0	585.9	584.8	583.7	582.6
65°	519.2	516.6	514.0	512.2	511.1	510.2	509.2	508.2
67.5°	444.0	441.7	439.4	437.5	436.2	434.8	433.4	432.1
70°	395.4	393.1	390.8	388.8	387.2	385.5	383.9	382.3
72.5°	346.2	344.1	342.0	340.6	339.8	338.9	338.1	337.2
75°	275.2	273.6	271.9	270.6	269.7	268.6	267.7	266.6
77.5°	209.1	207.9	206.8	206.2	206.2	206.2	206.2	206.2
80°	166.7	166.5	166.1	166.0	166.0	166.0	166.0	166.0
82.5°	128.3	127.7	127.1	126.7	126.4	126.2	125.9	125.6
85°	72.8	72.1	71.4	71.2	71.2	71.2	71.2	71.2
87.5°	28.3	28.1	27.9	28.0	27.9	28.0	28.1	28.0
90°	13.5	13.9	14.5	15.6	15.1	15.6	16.1	15.6
92.5°	45.2	35.9	31.8	28.9	28.0	26.3	26.9	25.9
95°	193.5	131.2	102.6	83.3	73.1	68.2	64.5	62.4
97.5°	482.5	386.4	317.1	252.8	213.1	188.9	174.4	169.8
100°	633.9	590.3	527.4	451.0	396.7	357.5	336.6	337.1
102.5°	684.2	682.8	646.1	597.7	555.4	524.3	506.8	494.5
105°	698.9	752.6	762.9	748.9	724.2	703.7	686.5	683.8
107.5°	656.5	743.9	790.9	810.0	810.5	803.6	797.8	792.9
110°	616.0	715.0	782.8	820.4	835.5	839.7	838.7	837.5



TEST NUMBER: P332062-830

CATALOG NUMBER: S123DIP-S1165D585U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	576.1	677.1	753.1	801.4	829.0	842.4	846.4	846.6
115°	523.1	616.6	695.7	754.2	794.6	818.2	829.0	831.7
117.5°	484.7	565.4	636.4	695.9	737.9	765.0	780.5	784.1
120°	464.5	537.1	601.5	655.9	698.3	728.5	741.3	744.6
122.5°	448.6	514.3	574.0	624.4	662.2	689.3	703.5	707.6
125°	427.3	486.0	537.6	580.6	615.0	638.7	652.1	655.9
127.5°	408.9	461.2	507.7	546.9	577.5	597.7	609.8	613.3
130°	397.3	445.6	489.2	525.8	554.3	573.6	584.9	589.2
132.5°	386.5	431.0	471.6	506.4	533.2	552.5	562.5	565.5
135°	372.0	410.2	445.2	475.8	502.1	518.2	527.9	531.7
137.5°	358.8	390.1	420.2	446.8	468.9	485.2	493.4	495.9
140°	351.1	378.4	404.3	427.3	447.8	462.9	471.5	470.9
142.5°	343.7	367.3	389.6	409.7	427.2	440.5	448.3	447.7
145°	334.9	352.7	369.9	385.5	398.9	410.2	414.5	415.6
147.5°	327.7	341.8	355.7	366.7	376.9	384.6	388.7	389.1
150°	322.5	334.9	346.2	356.5	364.5	370.4	373.6	373.6
152.5°	317.8	328.5	338.5	346.9	353.3	358.8	360.7	360.7
155°	310.8	319.3	327.4	333.8	338.7	343.0	344.0	344.6
157.5°	303.2	310.4	316.7	321.7	325.9	329.1	330.0	329.9
160°	298.9	304.8	310.2	314.0	317.7	320.9	320.9	320.4
162.5°	293.8	298.8	303.8	307.1	309.5	312.4	312.4	311.8
165°	287.1	290.3	294.1	296.7	298.9	301.0	300.5	300.5
167.5°	281.3	283.7	285.9	287.9	288.8	290.3	289.7	289.7
170°	277.4	279.0	281.2	282.2	282.8	283.9	283.3	283.3
172.5°	274.0	275.1	276.8	277.5	277.6	278.7	277.8	277.3
175°	269.4	269.8	271.0	271.0	271.0	271.5	271.0	270.4
177.5°	266.5	266.8	267.3	267.3	266.8	267.3	266.5	266.5
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6

(END OF REPORT)