

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331984

Luminaire Tested: **S123DIP-S775D1025U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331984
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1025U835-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6975.0 lumens
Efficiency: N/A
Efficacy: 134.1 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331984

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331984

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	97	93	89	86	89	86	82	80	72	70	67	59	58	56	47	46	45	40
2	89	82	76	71	81	75	70	66	63	59	56	52	50	47	42	40	39	34
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	35	33	29
4	74	64	56	50	68	59	52	47	50	45	41	41	38	35	34	31	29	25
5	68	57	49	43	62	53	46	40	45	39	35	37	33	30	30	27	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	24	22	19
7	58	46	38	33	53	43	36	31	36	31	27	31	26	23	25	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	35	29	24	30	25	21	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11630	11630	11630	11630
5°	13870	11681	10351	11681
10°	17361	11622	9349	11622
15°	21293	11528	8704	11528
20°	25366	11381	8287	11381
25°	26935	11204	8195	11204
30°	23086	11074	8238	11074
35°	16056	10889	8324	10889
40°	12094	10673	8297	10673
45°	10041	10353	8193	10353
50°	8994	9696	8118	9696
55°	8409	8989	8017	8989
60°	7890	8249	7935	8249
65°	7414	7521	7679	7521
70°	6952	6688	7314	6688
75°	6226	5856	6704	5856
80°	5455	4804	5777	4804
85°	4273	3495	3878	3495



TEST NUMBER: P331984

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.4	1.5
10°-20°	341.3	4.9
20°-30°	572.8	8.2
30°-40°	648.6	9.3
40°-50°	581.7	8.3
50°-60°	469.4	6.7
60°-70°	327.1	4.7
70°-80°	171.9	2.5
80°-90°	45.9	0.7
90°-100°	274.4	3.9
100°-110°	777.0	11.1
110°-120°	764.4	11.0
120°-130°	609.7	8.7
130°-140°	480.7	6.9
140°-150°	358.8	5.1
150°-160°	250.1	3.6
160°-170°	146.9	2.1
170°-180°	47.8	0.7
0°-30°	1020.6	14.6
0°-40°	1669.2	23.9
0°-60°	2720.2	39.0
0°-90°	3265.1	46.8
90°-120°	1815.8	26.0
90°-150°	3265.1	46.8
90°-180°	3710.0	53.2
0°-180°	6975.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1080	1080	1080	1080	1080	
5°	1284	1081	958	1081	1284	133
15°	1911	1034	781	1034	1911	552
25°	2268	943	690	943	2268	995
35°	1222	829	634	829	1222	794
45°	660	680	538	680	660	522
55°	448	479	427	479	448	402
65°	291	295	302	295	291	290
75°	150	141	161	141	150	160
85°	35	28	31	28	35	42
90°	29	2	29	2	29	17
95°	116	34	116	34	116	209
105°	1270	116	1270	116	1270	1253
115°	1544	205	1544	205	1544	1500
125°	1218	284	1218	284	1218	1104
135°	987	333	987	333	987	766
145°	772	380	772	380	772	491
155°	640	432	640	432	640	298
165°	558	472	558	472	558	159
175°	502	492	502	492	502	49
180°	493	493	493	493	493	



TEST NUMBER: P331984

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1146.7	1145.9	1143.8	1145.5	1142.1	1137.5	1137.1	1132.9	1120.7	1119.9	1116.6
5°	1283.7	1279.5	1279.0	1278.4	1271.1	1261.2	1242.3	1240.7	1215.6	1203.0	1187.9
7.5°	1461.0	1463.2	1455.6	1448.9	1426.5	1411.7	1391.5	1365.6	1334.8	1303.5	1282.6
10°	1588.4	1605.6	1584.2	1569.5	1555.9	1530.2	1500.4	1463.2	1426.1	1382.6	1349.6
12.5°	1724.9	1733.4	1729.1	1715.3	1694.1	1655.1	1602.2	1561.2	1527.0	1454.6	1425.4
15°	1910.8	1942.8	1922.4	1875.2	1876.3	1839.1	1770.0	1694.1	1653.8	1590.4	1504.1
17.5°	2108.9	2112.9	2104.2	2065.0	2038.8	1987.7	1923.9	1851.2	1769.5	1692.8	1601.2
20°	2214.5	2211.3	2193.0	2172.6	2127.6	2087.8	2018.2	1937.0	1832.3	1756.9	1656.9
22.5°	2273.1	2267.9	2259.2	2242.1	2204.6	2161.9	2099.4	2010.7	1911.1	1807.2	1691.7
25°	2267.9	2274.7	2275.7	2271.0	2257.9	2232.3	2183.1	2112.4	2012.9	1879.4	1759.0
27.5°	2062.7	2072.3	2100.3	2125.1	2152.8	2181.1	2177.3	2142.2	2068.6	1953.4	1806.1
30°	1857.4	1836.5	1888.3	1953.8	1998.3	2076.8	2120.8	2123.4	2082.0	1983.1	1839.6
32.5°	1572.6	1595.7	1618.6	1699.1	1796.4	1884.6	1972.1	2042.6	2050.6	1984.8	1859.3
35°	1221.9	1250.7	1292.6	1334.4	1439.2	1529.2	1683.1	1817.1	1923.9	1938.1	1861.1
37.5°	984.6	998.9	1025.4	1067.3	1135.8	1242.6	1361.7	1531.1	1685.8	1800.9	1805.9
40°	860.7	864.9	894.7	926.6	982.1	1070.1	1177.4	1327.1	1512.4	1673.2	1740.2
42.5°	767.7	776.9	789.6	820.2	864.4	930.6	1030.4	1154.1	1324.0	1509.0	1640.1
45°	659.6	670.1	678.0	698.4	729.8	774.3	843.9	957.0	1086.3	1277.4	1453.8
47.5°	588.2	589.1	594.9	610.3	631.7	665.1	714.3	787.0	905.7	1060.6	1241.8
50°	537.1	545.5	547.6	559.6	576.4	601.0	641.8	703.6	801.0	937.1	1103.6
52.5°	501.1	503.6	509.5	518.2	532.8	552.0	587.4	635.8	712.2	828.2	981.3
55°	448.1	448.1	453.9	460.7	469.1	486.3	509.9	545.5	603.6	693.7	820.4
57.5°	399.1	401.7	405.8	407.9	415.0	426.5	446.1	473.2	516.5	585.8	686.5
60°	366.5	371.2	370.7	374.8	381.1	390.0	406.8	428.8	467.5	523.0	607.8
62.5°	338.0	337.7	337.6	342.6	348.9	357.4	368.2	387.3	420.2	469.4	541.6
65°	291.1	290.0	293.7	296.8	298.9	305.2	313.6	330.3	352.3	389.0	445.0
67.5°	249.4	246.4	248.4	249.4	253.0	257.9	265.7	276.1	293.6	323.0	365.2
70°	220.9	218.3	217.8	218.8	222.0	225.6	231.4	241.3	257.6	281.1	312.0
72.5°	191.6	189.8	189.7	192.0	193.5	195.9	200.0	209.1	222.0	239.7	268.5
75°	149.7	149.7	149.7	150.2	151.8	153.9	157.1	161.8	171.7	184.3	203.6
77.5°	112.2	112.1	111.5	111.4	113.7	114.7	115.4	119.8	125.3	133.8	147.9
80°	88.0	85.3	86.4	88.0	89.0	89.5	91.1	92.1	96.9	101.6	111.5
82.5°	65.3	63.1	63.3	65.8	66.0	66.5	68.1	69.5	71.3	75.6	80.9
85°	34.6	34.6	35.1	35.1	35.6	35.1	36.6	37.2	37.2	39.8	42.9
87.5°	18.4	17.7	17.9	18.2	17.9	18.0	18.2	18.4	18.6	19.2	19.1
90°	28.9	29.9	28.9	27.9	28.9	27.0	26.0	25.0	24.0	25.0	22.0
92.5°	48.1	49.9	48.9	51.9	53.7	58.9	66.7	84.0	115.8	153.5	168.9
95°	115.8	119.8	126.8	135.8	154.7	190.7	243.6	359.3	480.1	591.9	527.0
97.5°	315.2	323.8	350.8	395.7	469.3	588.7	717.5	895.8	981.4	917.3	671.6
100°	625.9	624.9	663.8	736.7	837.5	979.2	1096.0	1176.9	1141.9	945.3	638.8
102.5°	918.1	941.1	973.6	1031.3	1109.8	1199.6	1267.7	1270.3	1149.9	893.4	590.9
105°	1269.7	1274.7	1306.6	1344.5	1390.5	1416.4	1397.5	1297.6	1089.0	802.5	532.0
107.5°	1472.1	1481.3	1492.1	1504.9	1504.1	1468.5	1381.1	1219.0	982.4	722.3	494.5
110°	1555.2	1557.2	1559.2	1551.2	1523.2	1453.3	1327.6	1143.9	915.3	676.8	480.1



TEST NUMBER: P331984

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1571.9	1571.5	1563.9	1539.2	1488.1	1398.2	1257.3	1069.6	857.0	646.4	472.1
115°	1544.2	1539.2	1519.2	1475.3	1400.4	1291.6	1144.9	971.2	786.6	613.9	469.1
117.5°	1455.9	1449.2	1420.4	1370.1	1292.0	1181.6	1049.9	900.0	744.0	594.7	470.9
120°	1382.5	1376.5	1352.5	1296.6	1217.8	1117.0	997.2	862.4	721.7	585.9	474.1
122.5°	1313.8	1306.2	1279.9	1229.6	1159.5	1065.9	954.9	832.9	703.3	580.3	479.7
125°	1217.8	1210.8	1185.8	1141.9	1078.0	998.2	902.4	793.6	679.8	573.0	488.1
127.5°	1138.7	1132.3	1109.8	1072.2	1015.3	942.7	856.2	759.2	659.0	569.4	497.7
130°	1094.0	1086.0	1065.1	1029.1	976.2	908.3	827.5	737.7	647.8	567.0	504.1
132.5°	1050.1	1044.5	1025.9	990.0	940.3	875.6	800.3	717.7	637.4	566.2	508.9
135°	987.2	980.2	962.2	932.3	883.4	826.5	761.6	690.7	623.9	565.0	516.1
137.5°	920.7	916.1	901.0	870.6	829.5	780.2	724.3	666.2	612.1	562.8	520.8
140°	874.4	875.4	859.4	831.5	793.6	750.6	702.7	651.8	604.9	562.0	524.0
142.5°	831.3	832.3	817.9	793.2	760.8	723.5	682.0	638.2	598.5	560.4	526.4
145°	771.6	769.6	761.6	740.6	715.7	686.7	654.8	621.9	589.9	558.0	528.0
147.5°	722.5	721.7	714.1	699.9	681.0	660.4	634.6	608.5	581.5	554.2	528.0
150°	693.7	693.7	687.7	676.8	661.8	642.8	621.9	598.9	575.9	551.0	528.0
152.5°	669.8	669.8	666.2	656.0	644.2	628.5	609.9	590.1	569.6	547.0	525.6
155°	639.8	638.8	636.8	628.9	619.9	607.9	592.9	576.9	560.0	540.0	523.0
157.5°	612.5	612.7	611.1	605.1	597.3	587.9	576.3	563.0	549.2	533.8	519.7
160°	594.9	595.9	595.9	589.9	582.9	575.9	566.0	555.0	542.0	529.0	518.1
162.5°	578.9	579.9	579.9	574.8	570.2	564.0	554.8	545.4	534.8	524.2	514.9
165°	558.0	558.0	559.0	555.0	551.0	546.0	539.0	533.0	525.0	517.1	510.1
167.5°	538.0	538.0	539.0	536.2	534.4	530.8	526.8	522.2	515.7	509.9	505.3
170°	526.0	526.0	527.0	525.0	524.0	522.0	518.1	515.1	510.1	505.1	502.1
172.5°	514.9	515.7	517.5	515.5	515.3	514.1	510.9	508.7	504.5	501.1	499.7
175°	502.1	503.1	504.1	503.1	503.1	503.1	501.1	500.1	498.1	496.1	496.1
177.5°	494.7	494.7	496.3	495.5	496.3	496.3	495.5	494.7	493.9	493.1	493.9
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P331984

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1114.0	1110.7	1107.3	1101.5	1096.5	1089.3	1087.2	1084.7	1077.2	1070.5	1065.5
5°	1182.1	1169.5	1151.2	1134.5	1120.9	1102.5	1092.1	1081.1	1065.4	1051.2	1039.7
7.5°	1253.3	1228.6	1200.1	1169.3	1140.6	1113.0	1090.7	1070.8	1048.8	1028.0	1011.8
10°	1309.8	1274.2	1234.5	1191.5	1154.9	1119.3	1089.4	1063.3	1035.0	1010.4	990.0
12.5°	1374.3	1321.6	1266.7	1214.6	1171.2	1121.8	1085.7	1052.4	1020.3	990.7	967.8
15°	1450.7	1383.7	1318.7	1247.0	1181.1	1119.3	1076.4	1034.5	997.3	966.9	937.6
17.5°	1520.2	1444.3	1358.7	1271.5	1191.9	1118.7	1058.6	1011.2	964.7	927.6	898.4
20°	1559.6	1473.2	1376.3	1285.8	1197.8	1116.1	1050.2	993.6	943.4	904.1	871.1
22.5°	1593.5	1492.4	1392.2	1295.4	1197.4	1109.4	1034.7	976.5	922.0	883.6	848.5
25°	1628.7	1507.7	1407.2	1293.6	1184.2	1093.1	1009.3	943.4	888.9	843.9	807.8
27.5°	1658.8	1506.7	1387.4	1265.2	1163.5	1072.2	982.7	912.0	854.2	805.3	768.6
30°	1678.9	1508.8	1366.9	1246.0	1143.4	1049.1	962.2	891.0	830.3	780.6	746.0
32.5°	1691.5	1507.5	1348.1	1219.2	1111.5	1028.2	940.0	866.3	803.9	755.0	721.7
35°	1698.8	1498.3	1315.6	1163.8	1060.1	979.0	905.2	828.7	763.3	717.7	680.1
37.5°	1684.2	1478.9	1277.9	1110.4	996.9	917.0	854.9	789.8	727.2	677.0	644.6
40°	1661.1	1466.4	1248.6	1072.7	953.3	876.4	823.5	759.6	697.8	650.2	619.8
42.5°	1617.1	1440.8	1216.3	1030.8	908.1	831.1	782.5	729.1	670.6	625.9	595.6
45°	1509.8	1385.2	1168.0	968.0	841.3	761.7	718.8	680.1	627.2	583.7	557.5
47.5°	1360.9	1301.6	1098.0	901.7	771.6	695.0	650.4	619.2	580.6	545.5	520.4
50°	1257.5	1232.9	1050.7	856.5	725.1	650.2	607.3	579.0	551.3	516.2	493.2
52.5°	1138.1	1153.3	995.4	809.6	677.7	604.1	563.7	541.3	516.1	487.3	467.2
55°	970.1	1025.0	899.9	730.8	607.3	537.1	498.9	479.0	464.4	442.9	425.6
57.5°	812.7	882.7	796.7	649.7	538.1	477.6	440.9	419.2	409.8	398.6	385.0
60°	719.3	788.4	723.0	595.2	491.6	434.0	401.5	383.2	373.8	365.9	354.4
62.5°	636.0	705.9	650.9	540.0	445.9	392.5	364.3	346.4	339.0	334.9	325.1
65°	521.4	581.6	545.0	453.9	380.6	333.5	307.8	295.3	288.5	286.9	280.6
67.5°	424.4	470.2	443.5	376.5	318.8	278.1	256.3	245.6	240.4	239.9	235.2
70°	360.7	403.6	383.2	322.5	272.8	240.8	222.0	212.5	209.4	208.9	206.3
72.5°	311.3	341.2	325.0	274.3	235.9	206.9	193.1	183.2	179.7	180.4	178.6
75°	230.3	252.9	243.4	208.4	177.5	158.6	147.1	140.8	137.7	139.3	137.2
77.5°	165.7	180.0	171.5	147.2	128.2	114.5	106.1	102.2	99.4	99.3	98.3
80°	125.1	133.5	128.8	114.1	98.4	86.9	80.1	77.5	75.9	75.4	74.9
82.5°	89.1	96.2	90.7	80.6	69.9	63.0	59.2	55.7	54.6	54.9	54.3
85°	45.0	47.6	45.5	39.3	35.1	31.9	29.8	28.3	27.2	27.7	26.7
87.5°	19.3	19.1	17.3	15.2	13.9	12.1	11.7	10.5	10.0	10.4	10.6
90°	19.0	16.0	13.0	11.0	9.0	6.0	4.0	2.0	4.0	6.0	9.0
92.5°	126.8	83.8	57.7	42.9	34.5	26.8	18.4	12.4	18.4	26.8	34.5
95°	363.3	214.6	129.8	90.8	64.9	47.9	36.9	33.9	36.9	47.9	64.9
97.5°	398.7	231.0	149.9	107.8	82.2	67.5	58.9	57.9	58.9	67.5	82.2
100°	376.3	228.6	158.7	119.8	95.8	81.9	74.9	73.9	74.9	81.9	95.8
102.5°	357.1	231.8	169.1	133.4	111.8	98.6	92.4	90.6	92.4	98.6	111.8
105°	343.4	240.6	186.7	155.7	136.8	124.8	118.8	115.8	118.8	124.8	136.8
107.5°	342.4	256.9	209.6	180.9	163.1	151.3	145.5	142.5	145.5	151.3	163.1
110°	346.4	270.5	225.6	197.6	180.7	169.7	164.7	161.7	164.7	169.7	180.7



TEST NUMBER: P331984

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	354.4	284.1	242.4	215.2	198.2	187.3	182.3	179.3	182.3	187.3	198.2
115°	367.3	306.4	268.5	241.6	224.6	214.6	208.6	204.6	208.6	214.6	224.6
117.5°	384.5	330.2	292.7	267.7	248.7	239.6	234.6	230.0	234.6	239.6	248.7
120°	397.3	345.4	309.4	284.5	265.5	255.5	250.5	247.5	250.5	255.5	265.5
122.5°	409.3	361.3	326.2	299.7	281.5	270.7	265.7	262.7	265.7	270.7	281.5
125°	428.2	384.3	349.4	322.4	303.4	292.5	286.5	284.5	286.5	292.5	303.4
127.5°	443.8	404.3	370.5	343.6	322.6	311.4	304.0	301.1	304.0	311.4	322.6
130°	454.2	416.2	383.3	356.3	335.4	323.4	314.4	311.4	314.4	323.4	335.4
132.5°	463.8	426.6	394.5	368.3	347.4	333.0	323.2	319.4	323.2	333.0	347.4
135°	476.1	442.2	411.2	384.3	363.3	348.4	337.4	333.4	337.4	348.4	363.3
137.5°	485.3	453.0	423.2	398.3	377.5	361.5	350.8	346.6	350.8	361.5	377.5
140°	490.1	460.2	431.2	406.3	386.3	370.3	360.3	355.4	360.3	370.3	386.3
142.5°	494.9	465.8	437.6	414.2	394.3	379.9	369.1	364.9	369.1	379.9	394.3
145°	500.1	473.1	447.2	424.2	407.3	392.3	383.3	380.3	383.3	392.3	407.3
147.5°	503.3	479.1	455.4	435.8	419.4	406.5	397.7	395.9	397.7	406.5	419.4
150°	504.1	483.1	460.2	442.2	428.2	415.2	407.3	406.3	407.3	415.2	428.2
152.5°	505.7	485.5	465.8	448.6	436.2	424.8	416.8	416.6	416.8	424.8	436.2
155°	506.1	490.1	473.1	459.2	448.2	438.2	432.2	432.2	432.2	438.2	448.2
157.5°	507.1	492.7	479.1	468.3	459.0	450.2	445.4	444.6	445.4	450.2	459.0
160°	507.1	495.1	483.1	473.1	466.1	458.2	454.2	454.2	454.2	458.2	466.1
162.5°	506.3	495.9	485.5	477.1	470.9	464.6	461.4	461.4	461.4	464.6	470.9
165°	504.1	497.1	489.1	482.1	478.1	473.1	471.1	472.1	471.1	473.1	478.1
167.5°	502.5	496.9	491.1	486.7	483.9	480.1	479.1	480.3	479.1	480.1	483.9
170°	500.1	496.1	491.1	489.1	487.1	484.1	483.1	485.1	483.1	484.1	487.1
172.5°	499.3	496.1	491.9	490.7	489.5	487.3	487.1	488.3	487.1	487.3	489.5
175°	497.1	495.1	493.1	492.1	492.1	490.1	491.1	492.1	491.1	490.1	492.1
177.5°	495.5	493.9	493.1	493.1	493.1	492.3	493.1	493.9	493.1	492.3	493.1
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P331984

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1062.5	1059.6	1055.4	1049.1	1044.1	1036.1	1036.1	1037.4	1037.4	1037.0	1036.1
5°	1030.3	1022.4	1013.0	1002.0	990.5	979.0	976.9	972.7	969.6	967.5	964.8
7.5°	996.3	982.3	968.6	953.2	939.2	927.6	919.5	912.8	908.5	903.9	900.6
10°	973.2	955.9	939.7	923.5	905.7	891.6	882.7	876.4	871.7	867.5	865.4
12.5°	946.0	926.2	908.3	892.9	873.4	858.9	850.4	847.5	841.9	833.1	828.5
15°	906.2	887.9	866.4	842.9	833.4	815.6	805.7	801.0	797.8	791.0	788.9
17.5°	872.2	848.2	824.1	806.5	789.0	774.6	769.0	763.2	759.0	753.4	751.8
20°	845.0	823.5	801.5	782.7	764.3	748.6	743.9	739.7	735.5	732.9	730.8
22.5°	817.3	795.9	777.6	760.0	740.5	730.2	725.1	720.5	717.5	715.8	713.7
25°	778.5	759.6	739.2	723.5	707.8	701.0	697.8	695.2	693.1	690.5	690.0
27.5°	743.7	723.2	706.6	692.0	680.7	675.0	672.0	670.7	671.2	672.1	672.7
30°	717.7	698.9	685.3	672.7	662.3	657.0	656.5	656.5	658.6	659.1	660.2
32.5°	693.9	678.4	664.8	652.6	644.7	641.1	643.1	643.1	644.8	646.1	648.0
35°	659.1	645.5	635.0	624.6	617.8	619.3	620.4	621.4	624.0	627.2	629.3
37.5°	625.9	614.1	603.2	595.0	591.9	594.7	597.2	599.4	602.5	604.9	607.0
40°	602.0	593.1	582.7	575.3	576.4	578.0	580.1	582.7	585.3	586.9	589.0
42.5°	579.8	570.5	562.6	556.5	558.0	560.0	561.2	562.6	565.6	568.4	569.7
45°	546.0	538.7	531.4	527.7	528.8	529.8	530.8	532.4	535.0	537.1	537.7
47.5°	508.0	502.9	498.0	494.4	496.1	495.7	497.0	500.4	501.2	502.5	505.4
50°	483.7	479.0	473.3	472.2	472.2	472.2	472.7	476.9	476.9	479.0	481.1
52.5°	456.9	453.9	450.2	448.3	447.5	447.5	449.7	451.8	452.6	455.6	457.7
55°	417.2	414.1	411.0	409.4	408.3	409.4	413.6	414.6	417.2	418.8	420.4
57.5°	375.9	373.5	371.0	370.1	369.9	371.3	373.6	376.7	377.4	382.2	384.6
60°	348.7	345.0	342.9	342.9	341.9	346.6	345.5	350.8	351.8	354.9	358.6
62.5°	320.6	315.7	314.8	314.8	316.3	317.7	319.1	321.4	324.2	328.1	331.0
65°	275.4	272.8	276.4	275.9	274.8	278.0	278.0	280.6	283.7	287.4	293.2
67.5°	232.5	231.2	231.5	231.5	233.1	234.9	236.3	238.6	242.4	246.3	250.0
70°	203.6	205.2	202.6	204.7	206.3	206.8	207.8	211.0	215.2	217.8	222.0
72.5°	175.6	175.5	175.8	176.6	178.2	179.1	180.2	183.8	188.4	190.6	193.9
75°	135.1	134.5	136.1	136.1	138.7	139.8	140.8	142.4	146.6	149.7	152.3
77.5°	98.6	99.3	98.9	100.7	100.0	100.2	103.4	105.0	105.4	111.6	113.0
80°	74.3	75.4	75.9	76.4	77.0	75.9	79.6	81.1	81.1	84.8	87.4
82.5°	53.4	54.0	55.4	55.9	56.0	57.1	57.4	58.5	59.8	61.4	64.8
85°	26.7	28.3	28.8	28.3	28.8	27.7	29.3	29.8	30.4	30.4	30.4
87.5°	10.6	11.4	11.6	12.6	12.8	13.8	13.6	12.9	13.1	14.6	13.3
90°	11.0	13.0	16.0	19.0	22.0	25.0	24.0	25.0	26.0	27.0	28.9
92.5°	42.9	57.7	83.8	126.8	168.9	153.5	115.8	84.0	66.7	58.9	53.7
95°	90.8	129.8	214.6	363.3	527.0	591.9	480.1	359.3	243.6	190.7	154.7
97.5°	107.8	149.9	231.0	398.7	671.6	917.3	981.4	895.8	717.5	588.7	469.3
100°	119.8	158.7	228.6	376.3	638.8	945.3	1141.9	1176.9	1096.0	979.2	837.5
102.5°	133.4	169.1	231.8	357.1	590.9	893.4	1149.9	1270.3	1267.7	1199.6	1109.8
105°	155.7	186.7	240.6	343.4	532.0	802.5	1089.0	1297.6	1397.5	1416.4	1390.5
107.5°	180.9	209.6	256.9	342.4	494.5	722.3	982.4	1219.0	1381.1	1468.5	1504.1
110°	197.6	225.6	270.5	346.4	480.1	676.8	915.3	1143.9	1327.6	1453.3	1523.2



TEST NUMBER: P331984

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	215.2	242.4	284.1	354.4	472.1	646.4	857.0	1069.6	1257.3	1398.2	1488.1
115°	241.6	268.5	306.4	367.3	469.1	613.9	786.6	971.2	1144.9	1291.6	1400.4
117.5°	267.7	292.7	330.2	384.5	470.9	594.7	744.0	900.0	1049.9	1181.6	1292.0
120°	284.5	309.4	345.4	397.3	474.1	585.9	721.7	862.4	997.2	1117.0	1217.8
122.5°	299.7	326.2	361.3	409.3	479.7	580.3	703.3	832.9	954.9	1065.9	1159.5
125°	322.4	349.4	384.3	428.2	488.1	573.0	679.8	793.6	902.4	998.2	1078.0
127.5°	343.6	370.5	404.3	443.8	497.7	569.4	659.0	759.2	856.2	942.7	1015.3
130°	356.3	383.3	416.2	454.2	504.1	567.0	647.8	737.7	827.5	908.3	976.2
132.5°	368.3	394.5	426.6	463.8	508.9	566.2	637.4	717.7	800.3	875.6	940.3
135°	384.3	411.2	442.2	476.1	516.1	565.0	623.9	690.7	761.6	826.5	883.4
137.5°	398.3	423.2	453.0	485.3	520.8	562.8	612.1	666.2	724.3	780.2	829.5
140°	406.3	431.2	460.2	490.1	524.0	562.0	604.9	651.8	702.7	750.6	793.6
142.5°	414.2	437.6	465.8	494.9	526.4	560.4	598.5	638.2	682.0	723.5	760.8
145°	424.2	447.2	473.1	500.1	528.0	558.0	589.9	621.9	654.8	686.7	715.7
147.5°	435.8	455.4	479.1	503.3	528.0	554.2	581.5	608.5	634.6	660.4	681.0
150°	442.2	460.2	483.1	504.1	528.0	551.0	575.9	598.9	621.9	642.8	661.8
152.5°	448.6	465.8	485.5	505.7	525.6	547.0	569.6	590.1	609.9	628.5	644.2
155°	459.2	473.1	490.1	506.1	523.0	540.0	560.0	576.9	592.9	607.9	619.9
157.5°	468.3	479.1	492.7	507.1	519.7	533.8	549.2	563.0	576.3	587.9	597.3
160°	473.1	483.1	495.1	507.1	518.1	529.0	542.0	555.0	566.0	575.9	582.9
162.5°	477.1	485.5	495.9	506.3	514.9	524.2	534.8	545.4	554.8	564.0	570.2
165°	482.1	489.1	497.1	504.1	510.1	517.1	525.0	533.0	539.0	546.0	551.0
167.5°	486.7	491.1	496.9	502.5	505.3	509.9	515.7	522.2	526.8	530.8	534.4
170°	489.1	491.1	496.1	500.1	502.1	505.1	510.1	515.1	518.1	522.0	524.0
172.5°	490.7	491.9	496.1	499.3	499.7	501.1	504.5	508.7	510.9	514.1	515.3
175°	492.1	493.1	495.1	497.1	496.1	496.1	498.1	500.1	501.1	503.1	503.1
177.5°	493.1	493.1	493.9	495.5	493.9	493.1	493.9	494.7	495.5	496.3	496.3
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P331984

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1033.2	1032.8	1035.7	1033.6	1035.7	1032.8	1033.2	1036.1	1037.0	1037.4	1037.4
5°	961.7	963.3	958.0	958.0	958.0	963.3	961.7	964.8	967.5	969.6	972.7
7.5°	898.0	895.7	895.9	893.1	895.9	895.7	898.0	900.6	903.9	908.5	912.8
10°	859.1	856.0	854.9	855.4	854.9	856.0	859.1	865.4	867.5	871.7	876.4
12.5°	826.8	826.2	819.3	819.4	819.3	826.2	826.8	828.5	833.1	841.9	847.5
15°	788.9	779.0	777.9	781.1	777.9	779.0	788.9	788.9	791.0	797.8	801.0
17.5°	750.9	745.7	746.0	744.4	746.0	745.7	750.9	751.8	753.4	759.0	763.2
20°	730.8	727.7	727.2	723.5	727.2	727.7	730.8	730.8	732.9	735.5	739.7
22.5°	712.4	711.4	711.7	707.6	711.7	711.4	712.4	713.7	715.8	717.5	720.5
25°	689.5	692.1	690.0	690.0	690.0	692.1	689.5	690.0	690.5	693.1	695.2
27.5°	674.0	673.9	672.8	672.8	672.8	673.9	674.0	672.7	672.1	671.2	670.7
30°	662.3	661.7	662.8	662.8	662.8	661.7	662.3	660.2	659.1	658.6	656.5
32.5°	650.5	651.3	651.5	651.9	651.5	651.3	650.5	648.0	646.1	644.8	643.1
35°	632.4	632.9	634.5	633.5	634.5	632.9	632.4	629.3	627.2	624.0	621.4
37.5°	607.9	610.3	609.8	610.6	609.8	610.3	607.9	607.0	604.9	602.5	599.4
40°	589.5	591.1	590.5	590.5	590.5	591.1	589.5	589.0	586.9	585.3	582.7
42.5°	570.6	571.8	570.4	569.6	570.4	571.8	570.6	569.7	568.4	565.6	562.6
45°	539.7	538.7	540.3	538.2	540.3	538.7	539.7	537.7	537.1	535.0	532.4
47.5°	505.2	506.2	506.7	508.2	506.7	506.2	505.2	505.4	502.5	501.2	500.4
50°	482.2	485.3	485.3	484.8	485.3	485.3	482.2	481.1	479.0	476.9	476.9
52.5°	459.5	461.0	463.1	463.0	463.1	461.0	459.5	457.7	455.6	452.6	451.8
55°	424.6	425.6	426.7	427.2	426.7	425.6	424.6	420.4	418.8	417.2	414.6
57.5°	388.3	387.9	390.4	391.2	390.4	387.9	388.3	384.6	382.2	377.4	376.7
60°	362.8	362.8	367.0	368.6	367.0	362.8	362.8	358.6	354.9	351.8	350.8
62.5°	335.6	337.3	341.4	339.2	341.4	337.3	335.6	331.0	328.1	324.2	321.4
65°	295.8	300.0	299.5	301.5	299.5	300.0	295.8	293.2	287.4	283.7	280.6
67.5°	254.2	256.8	260.6	260.9	260.6	256.8	254.2	250.0	246.3	242.4	238.6
70°	226.2	228.8	230.9	232.4	230.9	228.8	226.2	222.0	217.8	215.2	211.0
72.5°	198.9	200.3	205.3	203.1	205.3	200.3	198.9	193.9	190.6	188.4	183.8
75°	156.0	159.7	162.8	161.2	162.8	159.7	156.0	152.3	149.7	146.6	142.4
77.5°	115.4	119.0	120.5	119.2	120.5	119.0	115.4	113.0	111.6	105.4	105.0
80°	91.1	90.6	93.7	93.2	93.7	90.6	91.1	87.4	84.8	81.1	81.1
82.5°	66.8	66.3	67.7	68.1	67.7	66.3	66.8	64.8	61.4	59.8	58.5
85°	32.5	34.0	31.9	31.4	31.9	34.0	32.5	30.4	30.4	30.4	29.8
87.5°	13.1	13.3	13.1	12.5	13.1	13.3	13.1	13.3	14.6	13.1	12.9
90°	27.9	28.9	29.9	28.9	29.9	28.9	27.9	28.9	27.0	26.0	25.0
92.5°	51.9	48.9	49.9	48.1	49.9	48.9	51.9	53.7	58.9	66.7	84.0
95°	135.8	126.8	119.8	115.8	119.8	126.8	135.8	154.7	190.7	243.6	359.3
97.5°	395.7	350.8	323.8	315.2	323.8	350.8	395.7	469.3	588.7	717.5	895.8
100°	736.7	663.8	624.9	625.9	624.9	663.8	736.7	837.5	979.2	1096.0	1176.9
102.5°	1031.3	973.6	941.1	918.1	941.1	973.6	1031.3	1109.8	1199.6	1267.7	1270.3
105°	1344.5	1306.6	1274.7	1269.7	1274.7	1306.6	1344.5	1390.5	1416.4	1397.5	1297.6
107.5°	1504.9	1492.1	1481.3	1472.1	1481.3	1492.1	1504.9	1504.1	1468.5	1381.1	1219.0
110°	1551.2	1559.2	1557.2	1555.2	1557.2	1559.2	1551.2	1523.2	1453.3	1327.6	1143.9



TEST NUMBER: P331984

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1539.2	1563.9	1571.5	1571.9	1571.5	1563.9	1539.2	1488.1	1398.2	1257.3	1069.6
115°	1475.3	1519.2	1539.2	1544.2	1539.2	1519.2	1475.3	1400.4	1291.6	1144.9	971.2
117.5°	1370.1	1420.4	1449.2	1455.9	1449.2	1420.4	1370.1	1292.0	1181.6	1049.9	900.0
120°	1296.6	1352.5	1376.5	1382.5	1376.5	1352.5	1296.6	1217.8	1117.0	997.2	862.4
122.5°	1229.6	1279.9	1306.2	1313.8	1306.2	1279.9	1229.6	1159.5	1065.9	954.9	832.9
125°	1141.9	1185.8	1210.8	1217.8	1210.8	1185.8	1141.9	1078.0	998.2	902.4	793.6
127.5°	1072.2	1109.8	1132.3	1138.7	1132.3	1109.8	1072.2	1015.3	942.7	856.2	759.2
130°	1029.1	1065.1	1086.0	1094.0	1086.0	1065.1	1029.1	976.2	908.3	827.5	737.7
132.5°	990.0	1025.9	1044.5	1050.1	1044.5	1025.9	990.0	940.3	875.6	800.3	717.7
135°	932.3	962.2	980.2	987.2	980.2	962.2	932.3	883.4	826.5	761.6	690.7
137.5°	870.6	901.0	916.1	920.7	916.1	901.0	870.6	829.5	780.2	724.3	666.2
140°	831.5	859.4	875.4	874.4	875.4	859.4	831.5	793.6	750.6	702.7	651.8
142.5°	793.2	817.9	832.3	831.3	832.3	817.9	793.2	760.8	723.5	682.0	638.2
145°	740.6	761.6	769.6	771.6	769.6	761.6	740.6	715.7	686.7	654.8	621.9
147.5°	699.9	714.1	721.7	722.5	721.7	714.1	699.9	681.0	660.4	634.6	608.5
150°	676.8	687.7	693.7	693.7	693.7	687.7	676.8	661.8	642.8	621.9	598.9
152.5°	656.0	666.2	669.8	669.8	669.8	666.2	656.0	644.2	628.5	609.9	590.1
155°	628.9	636.8	638.8	639.8	638.8	636.8	628.9	619.9	607.9	592.9	576.9
157.5°	605.1	611.1	612.7	612.5	612.7	611.1	605.1	597.3	587.9	576.3	563.0
160°	589.9	595.9	595.9	594.9	595.9	595.9	589.9	582.9	575.9	566.0	555.0
162.5°	574.8	579.9	579.9	578.9	579.9	579.9	574.8	570.2	564.0	554.8	545.4
165°	555.0	559.0	558.0	558.0	558.0	559.0	555.0	551.0	546.0	539.0	533.0
167.5°	536.2	539.0	538.0	538.0	538.0	539.0	536.2	534.4	530.8	526.8	522.2
170°	525.0	527.0	526.0	526.0	526.0	527.0	525.0	524.0	522.0	518.1	515.1
172.5°	515.5	517.5	515.7	514.9	515.7	517.5	515.5	515.3	514.1	510.9	508.7
175°	503.1	504.1	503.1	502.1	503.1	504.1	503.1	503.1	503.1	501.1	500.1
177.5°	495.5	496.3	494.7	494.7	494.7	496.3	495.5	496.3	496.3	495.5	494.7
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P331984

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1036.1	1036.1	1044.1	1049.1	1055.4	1059.6	1062.5	1065.5	1070.5	1077.2	1084.7
5°	976.9	979.0	990.5	1002.0	1013.0	1022.4	1030.3	1039.7	1051.2	1065.4	1081.1
7.5°	919.5	927.6	939.2	953.2	968.6	982.3	996.3	1011.8	1028.0	1048.8	1070.8
10°	882.7	891.6	905.7	923.5	939.7	955.9	973.2	990.0	1010.4	1035.0	1063.3
12.5°	850.4	858.9	873.4	892.9	908.3	926.2	946.0	967.8	990.7	1020.3	1052.4
15°	805.7	815.6	833.4	842.9	866.4	887.9	906.2	937.6	966.9	997.3	1034.5
17.5°	769.0	774.6	789.0	806.5	824.1	848.2	872.2	898.4	927.6	964.7	1011.2
20°	743.9	748.6	764.3	782.7	801.5	823.5	845.0	871.1	904.1	943.4	993.6
22.5°	725.1	730.2	740.5	760.0	777.6	795.9	817.3	848.5	883.6	922.0	976.5
25°	697.8	701.0	707.8	723.5	739.2	759.6	778.5	807.8	843.9	888.9	943.4
27.5°	672.0	675.0	680.7	692.0	706.6	723.2	743.7	768.6	805.3	854.2	912.0
30°	656.5	657.0	662.3	672.7	685.3	698.9	717.7	746.0	780.6	830.3	891.0
32.5°	643.1	641.1	644.7	652.6	664.8	678.4	693.9	721.7	755.0	803.9	866.3
35°	620.4	619.3	617.8	624.6	635.0	645.5	659.1	680.1	717.7	763.3	828.7
37.5°	597.2	594.7	591.9	595.0	603.2	614.1	625.9	644.6	677.0	727.2	789.8
40°	580.1	578.0	576.4	575.3	582.7	593.1	602.0	619.8	650.2	697.8	759.6
42.5°	561.2	560.0	558.0	556.5	562.6	570.5	579.8	595.6	625.9	670.6	729.1
45°	530.8	529.8	528.8	527.7	531.4	538.7	546.0	557.5	583.7	627.2	680.1
47.5°	497.0	495.7	496.1	494.4	498.0	502.9	508.0	520.4	545.5	580.6	619.2
50°	472.7	472.2	472.2	472.2	473.3	479.0	483.7	493.2	516.2	551.3	579.0
52.5°	449.7	447.5	447.5	448.3	450.2	453.9	456.9	467.2	487.3	516.1	541.3
55°	413.6	409.4	408.3	409.4	411.0	414.1	417.2	425.6	442.9	464.4	479.0
57.5°	373.6	371.3	369.9	370.1	371.0	373.5	375.9	385.0	398.6	409.8	419.2
60°	345.5	346.6	341.9	342.9	342.9	345.0	348.7	354.4	365.9	373.8	383.2
62.5°	319.1	317.7	316.3	314.8	314.8	315.7	320.6	325.1	334.9	339.0	346.4
65°	278.0	278.0	274.8	275.9	276.4	272.8	275.4	280.6	286.9	288.5	295.3
67.5°	236.3	234.9	233.1	231.5	231.5	231.2	232.5	235.2	239.9	240.4	245.6
70°	207.8	206.8	206.3	204.7	202.6	205.2	203.6	206.3	208.9	209.4	212.5
72.5°	180.2	179.1	178.2	176.6	175.8	175.5	175.6	178.6	180.4	179.7	183.2
75°	140.8	139.8	138.7	136.1	136.1	134.5	135.1	137.2	139.3	137.7	140.8
77.5°	103.4	100.2	100.0	100.7	98.9	99.3	98.6	98.3	99.3	99.4	102.2
80°	79.6	75.9	77.0	76.4	75.9	75.4	74.3	74.9	75.4	75.9	77.5
82.5°	57.4	57.1	56.0	55.9	55.4	54.0	53.4	54.3	54.9	54.6	55.7
85°	29.3	27.7	28.8	28.3	28.8	28.3	26.7	26.7	27.7	27.2	28.3
87.5°	13.6	13.8	12.8	12.6	11.6	11.4	10.6	10.6	10.4	10.0	10.5
90°	24.0	25.0	22.0	19.0	16.0	13.0	11.0	9.0	6.0	4.0	2.0
92.5°	115.8	153.5	168.9	126.8	83.8	57.7	42.9	34.5	26.8	18.4	12.4
95°	480.1	591.9	527.0	363.3	214.6	129.8	90.8	64.9	47.9	36.9	33.9
97.5°	981.4	917.3	671.6	398.7	231.0	149.9	107.8	82.2	67.5	58.9	57.9
100°	1141.9	945.3	638.8	376.3	228.6	158.7	119.8	95.8	81.9	74.9	73.9
102.5°	1149.9	893.4	590.9	357.1	231.8	169.1	133.4	111.8	98.6	92.4	90.6
105°	1089.0	802.5	532.0	343.4	240.6	186.7	155.7	136.8	124.8	118.8	115.8
107.5°	982.4	722.3	494.5	342.4	256.9	209.6	180.9	163.1	151.3	145.5	142.5
110°	915.3	676.8	480.1	346.4	270.5	225.6	197.6	180.7	169.7	164.7	161.7



TEST NUMBER: P331984

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	857.0	646.4	472.1	354.4	284.1	242.4	215.2	198.2	187.3	182.3	179.3
115°	786.6	613.9	469.1	367.3	306.4	268.5	241.6	224.6	214.6	208.6	204.6
117.5°	744.0	594.7	470.9	384.5	330.2	292.7	267.7	248.7	239.6	234.6	230.0
120°	721.7	585.9	474.1	397.3	345.4	309.4	284.5	265.5	255.5	250.5	247.5
122.5°	703.3	580.3	479.7	409.3	361.3	326.2	299.7	281.5	270.7	265.7	262.7
125°	679.8	573.0	488.1	428.2	384.3	349.4	322.4	303.4	292.5	286.5	284.5
127.5°	659.0	569.4	497.7	443.8	404.3	370.5	343.6	322.6	311.4	304.0	301.1
130°	647.8	567.0	504.1	454.2	416.2	383.3	356.3	335.4	323.4	314.4	311.4
132.5°	637.4	566.2	508.9	463.8	426.6	394.5	368.3	347.4	333.0	323.2	319.4
135°	623.9	565.0	516.1	476.1	442.2	411.2	384.3	363.3	348.4	337.4	333.4
137.5°	612.1	562.8	520.8	485.3	453.0	423.2	398.3	377.5	361.5	350.8	346.6
140°	604.9	562.0	524.0	490.1	460.2	431.2	406.3	386.3	370.3	360.3	355.4
142.5°	598.5	560.4	526.4	494.9	465.8	437.6	414.2	394.3	379.9	369.1	364.9
145°	589.9	558.0	528.0	500.1	473.1	447.2	424.2	407.3	392.3	383.3	380.3
147.5°	581.5	554.2	528.0	503.3	479.1	455.4	435.8	419.4	406.5	397.7	395.9
150°	575.9	551.0	528.0	504.1	483.1	460.2	442.2	428.2	415.2	407.3	406.3
152.5°	569.6	547.0	525.6	505.7	485.5	465.8	448.6	436.2	424.8	416.8	416.6
155°	560.0	540.0	523.0	506.1	490.1	473.1	459.2	448.2	438.2	432.2	432.2
157.5°	549.2	533.8	519.7	507.1	492.7	479.1	468.3	459.0	450.2	445.4	444.6
160°	542.0	529.0	518.1	507.1	495.1	483.1	473.1	466.1	458.2	454.2	454.2
162.5°	534.8	524.2	514.9	506.3	495.9	485.5	477.1	470.9	464.6	461.4	461.4
165°	525.0	517.1	510.1	504.1	497.1	489.1	482.1	478.1	473.1	471.1	472.1
167.5°	515.7	509.9	505.3	502.5	496.9	491.1	486.7	483.9	480.1	479.1	480.3
170°	510.1	505.1	502.1	500.1	496.1	491.1	489.1	487.1	484.1	483.1	485.1
172.5°	504.5	501.1	499.7	499.3	496.1	491.9	490.7	489.5	487.3	487.1	488.3
175°	498.1	496.1	496.1	497.1	495.1	493.1	492.1	492.1	490.1	491.1	492.1
177.5°	493.9	493.1	493.9	495.5	493.9	493.1	493.1	493.1	492.3	493.1	493.9
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P331984

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1087.2	1089.3	1096.5	1101.5	1107.3	1110.7	1114.0	1116.6	1119.9	1120.7	1132.9
5°	1092.1	1102.5	1120.9	1134.5	1151.2	1169.5	1182.1	1187.9	1203.0	1215.6	1240.7
7.5°	1090.7	1113.0	1140.6	1169.3	1200.1	1228.6	1253.3	1282.6	1303.5	1334.8	1365.6
10°	1089.4	1119.3	1154.9	1191.5	1234.5	1274.2	1309.8	1349.6	1382.6	1426.1	1463.2
12.5°	1085.7	1121.8	1171.2	1214.6	1266.7	1321.6	1374.3	1425.4	1454.6	1527.0	1561.2
15°	1076.4	1119.3	1181.1	1247.0	1318.7	1383.7	1450.7	1504.1	1590.4	1653.8	1694.1
17.5°	1058.6	1118.7	1191.9	1271.5	1358.7	1444.3	1520.2	1601.2	1692.8	1769.5	1851.2
20°	1050.2	1116.1	1197.8	1285.8	1376.3	1473.2	1559.6	1656.9	1756.9	1832.3	1937.0
22.5°	1034.7	1109.4	1197.4	1295.4	1392.2	1492.4	1593.5	1691.7	1807.2	1911.1	2010.7
25°	1009.3	1093.1	1184.2	1293.6	1407.2	1507.7	1628.7	1759.0	1879.4	2012.9	2112.4
27.5°	982.7	1072.2	1163.5	1265.2	1387.4	1506.7	1658.8	1806.1	1953.4	2068.6	2142.2
30°	962.2	1049.1	1143.4	1246.0	1366.9	1508.8	1678.9	1839.6	1983.1	2082.0	2123.4
32.5°	940.0	1028.2	1111.5	1219.2	1348.1	1507.5	1691.5	1859.3	1984.8	2050.6	2042.6
35°	905.2	979.0	1060.1	1163.8	1315.6	1498.3	1698.8	1861.1	1938.1	1923.9	1817.1
37.5°	854.9	917.0	996.9	1110.4	1277.9	1478.9	1684.2	1805.9	1800.9	1685.8	1531.1
40°	823.5	876.4	953.3	1072.7	1248.6	1466.4	1661.1	1740.2	1673.2	1512.4	1327.1
42.5°	782.5	831.1	908.1	1030.8	1216.3	1440.8	1617.1	1640.1	1509.0	1324.0	1154.1
45°	718.8	761.7	841.3	968.0	1168.0	1385.2	1509.8	1453.8	1277.4	1086.3	957.0
47.5°	650.4	695.0	771.6	901.7	1098.0	1301.6	1360.9	1241.8	1060.6	905.7	787.0
50°	607.3	650.2	725.1	856.5	1050.7	1232.9	1257.5	1103.6	937.1	801.0	703.6
52.5°	563.7	604.1	677.7	809.6	995.4	1153.3	1138.1	981.3	828.2	712.2	635.8
55°	498.9	537.1	607.3	730.8	899.9	1025.0	970.1	820.4	693.7	603.6	545.5
57.5°	440.9	477.6	538.1	649.7	796.7	882.7	812.7	686.5	585.8	516.5	473.2
60°	401.5	434.0	491.6	595.2	723.0	788.4	719.3	607.8	523.0	467.5	428.8
62.5°	364.3	392.5	445.9	540.0	650.9	705.9	636.0	541.6	469.4	420.2	387.3
65°	307.8	333.5	380.6	453.9	545.0	581.6	521.4	445.0	389.0	352.3	330.3
67.5°	256.3	278.1	318.8	376.5	443.5	470.2	424.4	365.2	323.0	293.6	276.1
70°	222.0	240.8	272.8	322.5	383.2	403.6	360.7	312.0	281.1	257.6	241.3
72.5°	193.1	206.9	235.9	274.3	325.0	341.2	311.3	268.5	239.7	222.0	209.1
75°	147.1	158.6	177.5	208.4	243.4	252.9	230.3	203.6	184.3	171.7	161.8
77.5°	106.1	114.5	128.2	147.2	171.5	180.0	165.7	147.9	133.8	125.3	119.8
80°	80.1	86.9	98.4	114.1	128.8	133.5	125.1	111.5	101.6	96.9	92.1
82.5°	59.2	63.0	69.9	80.6	90.7	96.2	89.1	80.9	75.6	71.3	69.5
85°	29.8	31.9	35.1	39.3	45.5	47.6	45.0	42.9	39.8	37.2	37.2
87.5°	11.7	12.1	13.9	15.2	17.3	19.1	19.3	19.1	19.2	18.6	18.4
90°	4.0	6.0	9.0	11.0	13.0	16.0	19.0	22.0	25.0	24.0	25.0
92.5°	18.4	26.8	34.5	42.9	57.7	83.8	126.8	168.9	153.5	115.8	84.0
95°	36.9	47.9	64.9	90.8	129.8	214.6	363.3	527.0	591.9	480.1	359.3
97.5°	58.9	67.5	82.2	107.8	149.9	231.0	398.7	671.6	917.3	981.4	895.8
100°	74.9	81.9	95.8	119.8	158.7	228.6	376.3	638.8	945.3	1141.9	1176.9
102.5°	92.4	98.6	111.8	133.4	169.1	231.8	357.1	590.9	893.4	1149.9	1270.3
105°	118.8	124.8	136.8	155.7	186.7	240.6	343.4	532.0	802.5	1089.0	1297.6
107.5°	145.5	151.3	163.1	180.9	209.6	256.9	342.4	494.5	722.3	982.4	1219.0
110°	164.7	169.7	180.7	197.6	225.6	270.5	346.4	480.1	676.8	915.3	1143.9



TEST NUMBER: P331984

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	182.3	187.3	198.2	215.2	242.4	284.1	354.4	472.1	646.4	857.0	1069.6
115°	208.6	214.6	224.6	241.6	268.5	306.4	367.3	469.1	613.9	786.6	971.2
117.5°	234.6	239.6	248.7	267.7	292.7	330.2	384.5	470.9	594.7	744.0	900.0
120°	250.5	255.5	265.5	284.5	309.4	345.4	397.3	474.1	585.9	721.7	862.4
122.5°	265.7	270.7	281.5	299.7	326.2	361.3	409.3	479.7	580.3	703.3	832.9
125°	286.5	292.5	303.4	322.4	349.4	384.3	428.2	488.1	573.0	679.8	793.6
127.5°	304.0	311.4	322.6	343.6	370.5	404.3	443.8	497.7	569.4	659.0	759.2
130°	314.4	323.4	335.4	356.3	383.3	416.2	454.2	504.1	567.0	647.8	737.7
132.5°	323.2	333.0	347.4	368.3	394.5	426.6	463.8	508.9	566.2	637.4	717.7
135°	337.4	348.4	363.3	384.3	411.2	442.2	476.1	516.1	565.0	623.9	690.7
137.5°	350.8	361.5	377.5	398.3	423.2	453.0	485.3	520.8	562.8	612.1	666.2
140°	360.3	370.3	386.3	406.3	431.2	460.2	490.1	524.0	562.0	604.9	651.8
142.5°	369.1	379.9	394.3	414.2	437.6	465.8	494.9	526.4	560.4	598.5	638.2
145°	383.3	392.3	407.3	424.2	447.2	473.1	500.1	528.0	558.0	589.9	621.9
147.5°	397.7	406.5	419.4	435.8	455.4	479.1	503.3	528.0	554.2	581.5	608.5
150°	407.3	415.2	428.2	442.2	460.2	483.1	504.1	528.0	551.0	575.9	598.9
152.5°	416.8	424.8	436.2	448.6	465.8	485.5	505.7	525.6	547.0	569.6	590.1
155°	432.2	438.2	448.2	459.2	473.1	490.1	506.1	523.0	540.0	560.0	576.9
157.5°	445.4	450.2	459.0	468.3	479.1	492.7	507.1	519.7	533.8	549.2	563.0
160°	454.2	458.2	466.1	473.1	483.1	495.1	507.1	518.1	529.0	542.0	555.0
162.5°	461.4	464.6	470.9	477.1	485.5	495.9	506.3	514.9	524.2	534.8	545.4
165°	471.1	473.1	478.1	482.1	489.1	497.1	504.1	510.1	517.1	525.0	533.0
167.5°	479.1	480.1	483.9	486.7	491.1	496.9	502.5	505.3	509.9	515.7	522.2
170°	483.1	484.1	487.1	489.1	491.1	496.1	500.1	502.1	505.1	510.1	515.1
172.5°	487.1	487.3	489.5	490.7	491.9	496.1	499.3	499.7	501.1	504.5	508.7
175°	491.1	490.1	492.1	492.1	493.1	495.1	497.1	496.1	496.1	498.1	500.1
177.5°	493.1	492.3	493.1	493.1	493.1	493.9	495.5	493.9	493.1	493.9	494.7
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P331984

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1137.1	1137.5	1142.1	1145.5	1143.8	1145.9	1146.7
5°	1242.3	1261.2	1271.1	1278.4	1279.0	1279.5	1283.7
7.5°	1391.5	1411.7	1426.5	1448.9	1455.6	1463.2	1461.0
10°	1500.4	1530.2	1555.9	1569.5	1584.2	1605.6	1588.4
12.5°	1602.2	1655.1	1694.1	1715.3	1729.1	1733.4	1724.9
15°	1770.0	1839.1	1876.3	1875.2	1922.4	1942.8	1910.8
17.5°	1923.9	1987.7	2038.8	2065.0	2104.2	2112.9	2108.9
20°	2018.2	2087.8	2127.6	2172.6	2193.0	2211.3	2214.5
22.5°	2099.4	2161.9	2204.6	2242.1	2259.2	2267.9	2273.1
25°	2183.1	2232.3	2257.9	2271.0	2275.7	2274.7	2267.9
27.5°	2177.3	2181.1	2152.8	2125.1	2100.3	2072.3	2062.7
30°	2120.8	2076.8	1998.3	1953.8	1888.3	1836.5	1857.4
32.5°	1972.1	1884.6	1796.4	1699.1	1618.6	1595.7	1572.6
35°	1683.1	1529.2	1439.2	1334.4	1292.6	1250.7	1221.9
37.5°	1361.7	1242.6	1135.8	1067.3	1025.4	998.9	984.6
40°	1177.4	1070.1	982.1	926.6	894.7	864.9	860.7
42.5°	1030.4	930.6	864.4	820.2	789.6	776.9	767.7
45°	843.9	774.3	729.8	698.4	678.0	670.1	659.6
47.5°	714.3	665.1	631.7	610.3	594.9	589.1	588.2
50°	641.8	601.0	576.4	559.6	547.6	545.5	537.1
52.5°	587.4	552.0	532.8	518.2	509.5	503.6	501.1
55°	509.9	486.3	469.1	460.7	453.9	448.1	448.1
57.5°	446.1	426.5	415.0	407.9	405.8	401.7	399.1
60°	406.8	390.0	381.1	374.8	370.7	371.2	366.5
62.5°	368.2	357.4	348.9	342.6	337.6	337.7	338.0
65°	313.6	305.2	298.9	296.8	293.7	290.0	291.1
67.5°	265.7	257.9	253.0	249.4	248.4	246.4	249.4
70°	231.4	225.6	222.0	218.8	217.8	218.3	220.9
72.5°	200.0	195.9	193.5	192.0	189.7	189.8	191.6
75°	157.1	153.9	151.8	150.2	149.7	149.7	149.7
77.5°	115.4	114.7	113.7	111.4	111.5	112.1	112.2
80°	91.1	89.5	89.0	88.0	86.4	85.3	88.0
82.5°	68.1	66.5	66.0	65.8	63.3	63.1	65.3
85°	36.6	35.1	35.6	35.1	35.1	34.6	34.6
87.5°	18.2	18.0	17.9	18.2	17.9	17.7	18.4
90°	26.0	27.0	28.9	27.9	28.9	29.9	28.9
92.5°	66.7	58.9	53.7	51.9	48.9	49.9	48.1
95°	243.6	190.7	154.7	135.8	126.8	119.8	115.8
97.5°	717.5	588.7	469.3	395.7	350.8	323.8	315.2
100°	1096.0	979.2	837.5	736.7	663.8	624.9	625.9
102.5°	1267.7	1199.6	1109.8	1031.3	973.6	941.1	918.1
105°	1397.5	1416.4	1390.5	1344.5	1306.6	1274.7	1269.7
107.5°	1381.1	1468.5	1504.1	1504.9	1492.1	1481.3	1472.1
110°	1327.6	1453.3	1523.2	1551.2	1559.2	1557.2	1555.2



TEST NUMBER: P331984

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1257.3	1398.2	1488.1	1539.2	1563.9	1571.5	1571.9
115°	1144.9	1291.6	1400.4	1475.3	1519.2	1539.2	1544.2
117.5°	1049.9	1181.6	1292.0	1370.1	1420.4	1449.2	1455.9
120°	997.2	1117.0	1217.8	1296.6	1352.5	1376.5	1382.5
122.5°	954.9	1065.9	1159.5	1229.6	1279.9	1306.2	1313.8
125°	902.4	998.2	1078.0	1141.9	1185.8	1210.8	1217.8
127.5°	856.2	942.7	1015.3	1072.2	1109.8	1132.3	1138.7
130°	827.5	908.3	976.2	1029.1	1065.1	1086.0	1094.0
132.5°	800.3	875.6	940.3	990.0	1025.9	1044.5	1050.1
135°	761.6	826.5	883.4	932.3	962.2	980.2	987.2
137.5°	724.3	780.2	829.5	870.6	901.0	916.1	920.7
140°	702.7	750.6	793.6	831.5	859.4	875.4	874.4
142.5°	682.0	723.5	760.8	793.2	817.9	832.3	831.3
145°	654.8	686.7	715.7	740.6	761.6	769.6	771.6
147.5°	634.6	660.4	681.0	699.9	714.1	721.7	722.5
150°	621.9	642.8	661.8	676.8	687.7	693.7	693.7
152.5°	609.9	628.5	644.2	656.0	666.2	669.8	669.8
155°	592.9	607.9	619.9	628.9	636.8	638.8	639.8
157.5°	576.3	587.9	597.3	605.1	611.1	612.7	612.5
160°	566.0	575.9	582.9	589.9	595.9	595.9	594.9
162.5°	554.8	564.0	570.2	574.8	579.9	579.9	578.9
165°	539.0	546.0	551.0	555.0	559.0	558.0	558.0
167.5°	526.8	530.8	534.4	536.2	539.0	538.0	538.0
170°	518.1	522.0	524.0	525.0	527.0	526.0	526.0
172.5°	510.9	514.1	515.3	515.5	517.5	515.7	514.9
175°	501.1	503.1	503.1	503.1	504.1	503.1	502.1
177.5°	495.5	496.3	496.3	495.5	496.3	494.7	494.7
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1

(END OF REPORT)