

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831342

Luminaire Tested: S123DIP-S340D1195U830-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831342
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D1195U830-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5983.8 lumens
Efficiency: N/A
Efficacy: 137.9 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 43.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831342

CATALOG NUMBER: S123DIP-S340D1195U830-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P831342

CATALOG NUMBER: S123DIP-S340D1195U830-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	25
1	92	88	85	81	82	79	76	73	61	59	57	45	43	42	30	29	28	21
2	84	77	72	67	75	69	64	60	54	51	48	40	37	36	26	25	24	18
3	77	68	61	56	68	61	55	51	48	44	40	35	33	31	24	22	21	16
4	71	60	53	47	63	54	48	43	42	38	35	31	29	26	21	20	18	14
5	65	54	46	41	58	48	42	37	38	33	30	28	25	23	19	18	16	12
6	60	48	41	35	53	44	37	32	34	30	26	26	23	20	18	16	14	11
7	55	44	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10
8	51	40	32	27	46	36	29	25	28	24	21	21	18	16	15	13	12	9
9	48	36	29	24	42	33	27	22	26	22	18	20	17	15	14	12	11	8
10	44	33	26	22	40	30	24	20	24	20	17	18	15	13	13	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	9961	9961	9961	9961	9961
5°	12598	11890	10050	8099	7443
10°	12719	13105	9983	6456	5642
15°	9580	12167	9916	5467	4771
20°	6675	9845	9789	4781	4333
25°	5090	7571	9573	4399	4065
30°	4404	6016	9229	4129	3848
35°	4085	5079	8832	3933	3696
40°	3868	4555	8272	3747	3645
45°	3739	4217	7563	3602	3621
50°	3674	3949	6723	3470	3602
55°	3537	3751	5898	3344	3618
60°	3412	3541	5085	3227	3559
65°	3204	3342	4386	3100	3489
70°	2958	3087	3729	2892	3286
75°	2678	2770	3198	2687	2999
80°	2207	2424	2529	2343	2529
85°	1754	1964	1853	1988	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 8636 cd/sqm



TEST NUMBER: P831342

CATALOG NUMBER: S123DIP-S340D1195U830-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.5	1.5
10°-20°	217.7	3.6
20°-30°	257.7	4.3
30°-40°	259.1	4.3
40°-50°	237.7	4.0
50°-60°	196.2	3.3
60°-70°	138.8	2.3
70°-80°	74.1	1.2
80°-90°	21.7	0.4
90°-100°	52.0	0.9
100°-110°	251.2	4.2
110°-120°	615.8	10.3
120°-130°	781.7	13.1
130°-140°	835.1	14.0
140°-150°	780.9	13.1
150°-160°	629.9	10.5
160°-170°	406.5	6.8
170°-180°	140.1	2.3
0°-30°	562.9	9.4
0°-40°	822.0	13.7
0°-60°	1255.9	21.0
0°-90°	1490.6	24.9
90°-120°	918.9	15.4
90°-150°	3316.8	55.4
90°-180°	4493.0	75.1
0°-180°	5983.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	925	925	925	925	925	
5°	1166	1100	930	750	689	111
15°	860	1092	890	491	428	237
25°	429	638	806	370	342	202
35°	311	386	672	299	281	195
45°	246	277	497	237	238	190
55°	188	200	314	178	193	169
65°	126	131	172	122	137	125
75°	64	67	77	65	72	68
85°	14	16	15	16	16	16
90°	33	26	1	26	33	15
95°	42	34	67	34	42	35
105°	48	240	326	240	48	100
115°	644	629	612	629	644	606
125°	880	876	863	876	880	787
135°	1085	1085	1074	1085	1085	837
145°	1252	1250	1240	1250	1252	782
155°	1363	1364	1366	1364	1363	629
165°	1437	1436	1440	1436	1437	406
175°	1468	1470	1474	1470	1468	140
180°	1474	1474	1474	1474	1474	



TEST NUMBER: P831342

CATALOG NUMBER: S123DIP-S340D1195U830-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	1043.1	1042.0	1040.9	1035.6	1030.2	1027.6	1025.0	1017.3	1009.6	1001.0	992.4
5°	1165.9	1168.9	1171.9	1168.5	1165.0	1154.5	1144.0	1130.0	1116.1	1100.4	1084.7
7.5°	1222.6	1224.3	1226.0	1223.9	1221.7	1218.9	1216.1	1203.7	1191.2	1175.1	1159.0
10°	1163.7	1167.6	1171.5	1179.8	1188.2	1197.7	1207.1	1205.4	1203.7	1199.0	1194.2
12.5°	1034.5	1039.2	1043.9	1060.7	1077.4	1098.9	1120.4	1138.8	1157.3	1170.2	1183.1
15°	859.7	872.8	885.9	901.1	916.4	948.0	979.5	1018.4	1057.2	1091.8	1126.4
17.5°	708.1	713.1	718.0	734.3	750.6	790.4	830.1	875.0	919.8	977.2	1034.5
20°	582.7	587.2	591.7	613.2	634.7	665.8	697.0	747.4	797.9	859.5	921.1
22.5°	489.5	496.6	503.7	515.7	527.8	557.6	587.5	632.3	677.2	745.3	813.3
25°	428.6	433.7	438.9	446.2	453.5	477.3	501.1	538.1	575.0	637.5	700.0
27.5°	386.9	389.1	391.2	398.5	405.8	421.3	436.7	468.5	500.3	553.3	606.3
30°	354.3	355.8	357.3	363.7	370.2	380.7	391.2	414.2	437.2	484.0	530.8
32.5°	331.5	332.6	333.7	338.6	343.5	351.1	358.6	375.3	392.1	430.7	469.4
35°	310.9	311.5	312.2	315.8	319.5	325.1	330.7	343.3	356.0	386.5	417.0
37.5°	292.9	293.7	294.6	296.7	298.9	303.8	308.8	318.8	328.9	352.3	375.7
40°	275.3	276.8	278.3	279.8	281.3	285.4	289.4	297.2	304.9	324.2	343.5
42.5°	260.2	261.7	263.2	263.9	264.5	266.9	269.2	276.3	283.4	297.8	312.2
45°	245.6	246.3	246.9	247.6	248.2	250.1	252.1	258.3	264.5	277.0	289.4
47.5°	232.3	232.3	232.3	232.7	233.2	234.9	236.6	241.1	245.6	255.3	265.0
50°	219.4	219.4	219.4	218.8	218.1	219.2	220.3	223.7	227.2	235.8	244.3
52.5°	204.0	204.0	204.0	204.2	204.4	204.4	204.4	207.4	210.4	218.1	225.9
55°	188.5	189.4	190.2	189.6	188.9	189.4	189.8	191.7	193.7	199.9	206.1
57.5°	173.1	173.5	173.9	173.7	173.5	173.7	173.9	175.6	177.4	182.1	186.8
60°	158.5	158.5	158.5	158.0	157.6	158.0	158.5	159.3	160.2	164.5	168.8
62.5°	142.1	142.4	142.6	142.8	143.0	142.6	142.1	143.2	144.3	147.5	150.7
65°	125.8	126.0	126.3	126.9	127.5	127.1	126.7	127.8	128.8	131.2	133.6
67.5°	111.2	110.8	110.4	110.6	110.8	111.4	112.1	112.3	112.5	115.1	117.7
70°	94.0	94.5	94.9	94.7	94.5	94.7	94.9	95.5	96.2	98.1	100.1
72.5°	78.6	78.8	79.0	79.0	79.0	79.4	79.9	80.5	81.2	82.2	83.3
75°	64.4	64.4	64.4	64.8	65.3	65.5	65.7	65.7	65.7	66.6	67.4
77.5°	49.0	50.0	51.1	50.9	50.7	51.1	51.5	52.2	52.8	53.2	53.7
80°	35.6	35.6	35.6	35.9	36.1	36.7	37.4	37.8	38.2	39.1	39.9
82.5°	22.8	23.0	23.2	23.8	24.5	24.9	25.3	26.0	26.6	26.6	26.6
85°	14.2	13.7	13.3	13.7	14.2	14.6	15.0	15.2	15.5	15.9	16.3
87.5°	6.9	6.9	6.9	6.9	6.9	7.1	7.3	7.3	7.3	7.3	7.3
90°	32.9	32.4	31.9	31.4	30.9	30.2	29.2	28.2	27.3	26.3	23.1
92.5°	37.2	37.0	36.7	36.5	36.3	35.3	33.6	31.9	30.2	28.5	26.3
95°	41.6	41.6	41.6	41.6	41.6	40.8	39.1	37.4	35.7	33.9	31.3
97.5°	44.9	44.7	44.4	44.2	43.9	42.8	40.9	38.9	37.0	35.0	47.5
100°	46.0	45.7	45.5	45.3	45.0	43.9	42.0	40.0	38.1	36.1	74.1
102.5°	47.1	46.6	46.1	45.6	45.1	48.9	56.9	65.0	73.0	81.0	123.4
105°	48.2	47.7	47.2	46.7	46.2	67.5	110.6	153.7	196.7	239.8	261.7
107.5°	113.9	145.8	177.6	209.5	241.4	276.1	313.6	351.0	388.5	426.0	422.3
110°	301.1	335.9	370.7	405.5	440.3	461.7	469.8	477.8	485.8	493.9	491.2



TEST NUMBER: P831342

CATALOG NUMBER: S123DIP-S340D1195U830-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	570.5	571.0	571.5	572.0	572.5	571.6	569.4	567.2	565.0	562.9	560.2
115°	643.9	642.9	641.9	641.0	640.0	638.3	635.9	633.4	631.0	628.6	626.4
117.5°	703.0	702.8	702.5	702.3	702.1	701.0	699.0	697.1	695.1	693.2	692.0
120°	764.3	764.3	764.3	764.3	764.3	763.4	761.4	759.5	757.5	755.6	754.9
122.5°	824.6	824.3	824.1	823.8	823.6	822.9	821.7	820.4	819.2	818.0	817.0
125°	880.4	879.9	879.5	879.0	878.5	878.0	877.5	877.0	876.5	876.0	875.1
127.5°	935.2	935.7	936.2	936.6	937.1	937.0	936.3	935.5	934.8	934.1	932.9
130°	987.7	988.2	988.7	989.2	989.7	989.4	988.5	987.5	986.5	985.5	984.6
132.5°	1035.9	1036.7	1037.4	1038.1	1038.8	1038.7	1037.7	1036.8	1035.8	1034.8	1034.1
135°	1085.2	1085.9	1086.7	1087.4	1088.1	1088.1	1087.4	1086.7	1085.9	1085.2	1084.2
137.5°	1132.3	1132.8	1133.3	1133.7	1134.2	1133.9	1132.7	1131.4	1130.2	1129.0	1128.5
140°	1173.9	1174.4	1174.9	1175.4	1175.8	1175.6	1174.6	1173.7	1172.7	1171.7	1171.0
142.5°	1212.2	1213.0	1213.7	1214.4	1215.1	1215.1	1214.4	1213.7	1213.0	1212.2	1211.5
145°	1251.6	1251.6	1251.6	1251.6	1251.6	1251.4	1250.9	1250.4	1249.9	1249.5	1249.0
147.5°	1280.1	1281.3	1282.6	1283.8	1285.0	1285.4	1284.9	1284.4	1283.9	1283.4	1282.9
150°	1313.0	1313.7	1314.4	1315.2	1315.9	1316.0	1315.5	1315.0	1314.6	1314.1	1313.6
152.5°	1339.3	1340.5	1341.7	1342.9	1344.1	1344.2	1343.3	1342.3	1341.3	1340.3	1340.1
155°	1363.3	1364.8	1366.3	1367.7	1369.2	1369.3	1368.1	1366.9	1365.7	1364.4	1364.2
157.5°	1384.1	1386.1	1388.0	1390.0	1391.9	1392.2	1390.7	1389.3	1387.8	1386.3	1386.6
160°	1403.9	1405.6	1407.3	1409.0	1410.7	1410.8	1409.3	1407.9	1406.4	1405.0	1405.2
162.5°	1422.5	1423.9	1425.4	1426.9	1428.3	1428.2	1426.5	1424.8	1423.1	1421.4	1421.6
165°	1436.7	1438.4	1440.1	1441.8	1443.5	1443.4	1441.5	1439.5	1437.6	1435.6	1435.9
167.5°	1447.7	1449.6	1451.6	1453.5	1455.4	1455.4	1453.5	1451.6	1449.6	1447.7	1447.7
170°	1457.5	1459.5	1461.4	1463.4	1465.3	1465.3	1463.4	1461.4	1459.5	1457.5	1457.5
172.5°	1463.0	1465.2	1467.4	1469.6	1471.8	1471.9	1469.9	1468.0	1466.0	1464.1	1463.8
175°	1468.5	1470.4	1472.4	1474.3	1476.3	1476.4	1474.7	1473.0	1471.3	1469.6	1469.3
177.5°	1469.6	1472.0	1474.4	1476.9	1479.3	1479.5	1477.6	1475.6	1473.7	1471.8	1471.5
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P831342

CATALOG NUMBER: S123DIP-S340D1195U830-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	989.8	987.2	977.8	968.4	957.6	946.9	938.9	931.0	919.2	907.4	897.7
5°	1072.7	1060.7	1040.7	1020.7	993.7	966.6	948.4	930.1	905.7	881.2	861.6
7.5°	1138.4	1117.8	1089.9	1062.0	1026.5	991.1	957.6	924.1	886.8	849.4	818.9
10°	1180.3	1166.3	1134.1	1101.9	1054.5	1007.0	960.2	913.4	865.3	817.2	776.8
12.5°	1184.4	1185.6	1156.0	1126.4	1072.7	1019.0	962.1	905.2	844.7	784.1	737.1
15°	1148.5	1170.6	1154.3	1138.0	1083.9	1029.8	959.8	889.8	820.0	750.2	695.9
17.5°	1081.9	1129.4	1131.8	1134.1	1080.0	1025.9	948.4	870.9	791.9	712.8	655.7
20°	991.1	1061.1	1085.2	1109.2	1065.2	1021.2	937.9	854.6	766.1	677.6	617.7
22.5°	898.4	983.4	1027.4	1071.4	1038.8	1006.1	917.5	828.8	735.4	642.0	581.2
25°	792.7	885.5	953.1	1020.7	1000.8	980.8	893.4	806.0	706.6	607.2	545.2
27.5°	700.6	794.9	876.5	958.0	953.8	949.5	862.7	776.0	674.2	572.4	512.5
30°	618.6	706.4	797.7	888.9	899.4	910.0	826.2	742.5	640.5	538.5	480.7
32.5°	546.0	622.7	720.6	818.5	839.1	859.7	784.1	708.6	607.6	506.7	451.1
35°	486.5	556.1	654.0	751.9	777.7	803.5	737.8	672.1	573.7	475.4	422.3
37.5°	433.9	492.1	587.7	683.2	714.8	746.3	687.5	628.7	536.6	444.5	395.7
40°	390.3	437.2	525.0	612.8	649.3	685.8	637.3	588.7	501.4	414.0	369.1
42.5°	353.8	395.5	475.2	554.8	589.8	624.8	583.8	542.8	465.1	387.3	346.3
45°	322.7	356.0	428.4	500.7	534.0	567.3	532.1	496.8	428.4	359.9	321.6
47.5°	293.5	322.1	383.9	445.7	475.4	505.0	477.5	450.0	392.1	334.1	299.5
50°	267.3	290.3	344.4	398.5	424.3	450.0	425.8	401.5	353.8	306.2	276.1
52.5°	244.6	263.2	308.5	353.8	376.0	398.1	377.3	356.4	318.6	280.8	254.6
55°	222.0	237.9	277.2	316.5	331.5	346.5	330.4	314.3	283.9	253.4	231.2
57.5°	201.0	215.1	247.3	279.6	291.2	302.7	288.1	273.5	250.6	227.6	209.1
60°	180.4	192.0	218.8	245.6	252.7	259.8	248.0	236.2	220.1	204.0	187.4
62.5°	161.2	171.8	191.7	211.7	216.4	221.2	212.1	203.1	190.9	178.6	165.8
65°	141.5	149.4	165.8	182.1	185.1	188.1	180.1	172.2	163.0	153.7	144.3
67.5°	123.2	128.8	142.1	155.5	155.7	155.9	149.4	143.0	137.8	132.7	125.2
70°	105.4	110.8	119.6	128.4	128.6	128.8	123.7	118.5	114.7	110.8	105.2
72.5°	87.2	91.0	97.7	104.4	103.9	103.5	100.3	97.1	94.0	91.0	87.0
75°	70.6	73.9	78.4	82.9	81.6	80.3	78.6	76.9	74.3	71.7	69.1
77.5°	55.6	57.5	60.1	62.7	61.8	61.0	59.5	58.0	56.0	54.1	53.0
80°	40.8	41.7	43.4	45.1	44.7	44.2	42.5	40.8	40.4	39.9	38.4
82.5°	27.7	28.8	29.2	29.6	29.4	29.2	27.9	26.6	26.2	25.8	25.6
85°	16.5	16.7	17.0	17.2	16.5	15.9	15.5	15.0	15.0	15.0	14.8
87.5°	7.5	7.7	7.7	7.7	7.5	7.3	6.9	6.4	6.7	6.9	6.9
90°	20.0	16.8	13.6	10.8	8.4	6.0	3.5	1.1	3.5	6.0	8.4
92.5°	24.1	21.9	19.7	19.3	20.8	22.3	23.7	25.2	23.7	22.3	20.8
95°	28.6	25.9	23.2	26.9	36.9	46.8	56.8	66.8	56.8	46.8	36.9
97.5°	59.9	72.3	84.7	94.3	101.1	107.9	114.7	121.6	114.7	107.9	101.1
100°	112.1	150.0	188.0	204.5	199.7	194.8	189.9	185.1	189.9	194.8	199.7
102.5°	165.7	208.1	250.4	270.0	266.8	263.7	260.5	257.3	260.5	263.7	266.8
105°	283.6	305.5	327.4	337.0	334.4	331.7	329.0	326.3	329.0	331.7	334.4
107.5°	418.7	415.0	411.4	408.5	406.3	404.1	401.9	399.7	401.9	404.1	406.3
110°	488.5	485.8	483.2	480.9	478.9	477.0	475.0	473.1	475.0	477.0	478.9



TEST NUMBER: P831342

CATALOG NUMBER: S123DIP-S340D1195U830-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	557.5	554.8	552.2	550.0	548.3	546.6	544.9	543.1	544.9	546.6	548.3
115°	624.2	622.0	619.8	618.0	616.5	615.1	613.6	612.1	613.6	615.1	616.5
117.5°	690.7	689.5	688.3	686.8	685.1	683.4	681.7	680.0	681.7	683.4	685.1
120°	754.1	753.4	752.7	751.2	749.0	746.8	744.6	742.4	744.6	746.8	749.0
122.5°	816.1	815.1	814.1	812.8	811.1	809.4	807.7	806.0	807.7	809.4	811.1
125°	874.1	873.1	872.2	870.7	868.7	866.8	864.9	862.9	864.9	866.8	868.7
127.5°	931.6	930.4	929.2	927.6	925.7	923.7	921.8	919.8	921.8	923.7	925.7
130°	983.6	982.6	981.7	980.2	978.2	976.3	974.4	972.4	974.4	976.3	978.2
132.5°	1033.4	1032.6	1031.9	1030.6	1028.6	1026.7	1024.7	1022.8	1024.7	1026.7	1028.6
135°	1083.3	1082.3	1081.3	1080.1	1078.6	1077.2	1075.7	1074.2	1075.7	1077.2	1078.6
137.5°	1128.0	1127.5	1127.1	1125.8	1123.9	1121.9	1120.0	1118.1	1120.0	1121.9	1123.9
140°	1170.2	1169.5	1168.8	1167.7	1166.2	1164.8	1163.3	1161.9	1163.3	1164.8	1166.2
142.5°	1210.8	1210.0	1209.3	1208.2	1206.8	1205.3	1203.8	1202.4	1203.8	1205.3	1206.8
145°	1248.5	1248.0	1247.5	1246.4	1244.7	1243.0	1241.3	1239.6	1241.3	1243.0	1244.7
147.5°	1282.4	1281.9	1281.5	1280.6	1279.4	1278.2	1277.0	1275.7	1277.0	1278.2	1279.4
150°	1313.1	1312.6	1312.1	1311.5	1310.8	1310.1	1309.3	1308.6	1309.3	1310.1	1310.8
152.5°	1339.9	1339.6	1339.4	1339.1	1338.9	1338.6	1338.4	1338.2	1338.4	1338.6	1338.9
155°	1364.0	1363.7	1363.5	1363.6	1364.1	1364.6	1365.0	1365.5	1365.0	1364.6	1364.1
157.5°	1386.8	1387.1	1387.3	1387.4	1387.4	1387.4	1387.4	1387.4	1387.4	1387.4	1387.4
160°	1405.4	1405.7	1405.9	1406.2	1406.4	1406.7	1406.9	1407.1	1406.9	1406.7	1406.4
162.5°	1421.9	1422.1	1422.4	1422.8	1423.6	1424.3	1425.0	1425.8	1425.0	1424.3	1423.6
165°	1436.1	1436.3	1436.6	1437.1	1437.8	1438.5	1439.3	1440.0	1439.3	1438.5	1437.8
167.5°	1447.7	1447.7	1447.7	1448.1	1449.1	1450.1	1451.1	1452.0	1451.1	1450.1	1449.1
170°	1457.5	1457.5	1457.5	1458.0	1459.0	1460.0	1460.9	1461.9	1460.9	1460.0	1459.0
172.5°	1463.6	1463.4	1463.1	1463.6	1464.8	1466.0	1467.3	1468.5	1467.3	1466.0	1464.8
175°	1469.1	1468.8	1468.6	1469.1	1470.3	1471.5	1472.7	1473.9	1472.7	1471.5	1470.3
177.5°	1471.3	1471.0	1470.8	1471.3	1472.5	1473.7	1474.9	1476.1	1474.9	1473.7	1472.5
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P831342

CATALOG NUMBER: S123DIP-S340D1195U830-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	888.1	879.7	871.3	864.9	858.4	847.5	836.5	833.9	831.4	827.7	824.1
5°	842.1	821.5	800.9	782.4	763.9	749.6	735.2	725.7	716.3	709.4	702.5
7.5°	788.4	757.5	726.6	704.7	682.8	662.0	641.1	634.5	627.8	618.8	609.8
10°	736.5	702.3	668.2	639.6	611.1	590.7	570.3	562.1	554.0	542.6	531.2
12.5°	690.1	652.7	615.4	586.6	557.8	538.1	518.3	506.5	494.7	488.3	481.8
15°	641.6	601.6	561.7	535.1	508.4	490.6	472.8	462.5	452.2	446.0	439.7
17.5°	598.6	559.1	519.6	494.1	468.5	452.2	435.9	426.8	417.8	413.1	408.4
20°	557.8	519.2	480.5	455.6	430.7	417.4	404.1	398.3	392.5	388.6	384.8
22.5°	520.5	482.5	444.5	423.2	401.9	391.2	380.5	376.4	372.3	369.1	365.9
25°	483.1	449.2	415.3	397.2	379.2	370.4	361.6	357.5	353.4	350.2	347.0
27.5°	452.6	420.2	387.8	372.3	356.9	350.0	343.1	339.9	336.7	333.7	330.7
30°	423.0	394.0	365.0	351.7	338.4	332.2	325.9	322.7	319.5	316.7	313.9
32.5°	395.5	370.6	345.7	333.4	321.2	316.1	310.9	307.0	303.2	301.0	298.9
35°	369.3	347.0	324.6	314.6	304.5	299.3	294.2	290.9	287.7	286.0	284.3
37.5°	347.0	327.0	307.0	297.4	287.7	282.8	277.8	275.0	272.3	271.6	271.0
40°	324.2	307.0	289.9	280.4	271.0	266.7	262.4	260.7	258.9	258.5	258.1
42.5°	305.3	288.6	271.8	263.2	254.6	251.0	247.3	246.5	245.6	246.3	246.9
45°	283.4	269.5	255.5	247.6	239.6	236.6	233.6	233.0	232.3	233.6	234.9
47.5°	265.0	252.1	239.2	231.7	224.2	222.0	219.9	219.7	219.4	221.2	222.9
50°	246.1	233.6	221.2	215.1	209.1	207.2	205.3	205.9	206.6	209.3	212.1
52.5°	228.5	216.9	205.3	199.7	194.1	192.8	191.5	193.0	194.5	197.5	200.5
55°	209.1	198.6	188.1	183.8	179.5	178.2	176.9	179.9	182.9	185.7	188.5
57.5°	190.7	181.4	172.2	168.3	164.5	164.3	164.0	166.8	169.6	172.6	175.6
60°	170.9	163.2	155.5	152.4	149.4	149.9	150.3	153.5	156.7	159.1	161.5
62.5°	152.9	146.4	140.0	137.2	134.4	135.5	136.6	139.8	143.0	145.8	148.6
65°	134.8	129.5	124.1	122.2	120.2	121.7	123.2	126.0	128.8	130.8	132.7
67.5°	117.7	113.2	108.6	107.1	105.6	107.1	108.6	111.4	114.2	116.2	118.1
70°	99.6	96.0	92.3	91.3	90.2	91.9	93.6	96.0	98.3	100.3	102.2
72.5°	82.9	80.1	77.3	77.1	76.9	78.4	79.9	82.2	84.6	85.9	87.2
75°	66.6	65.1	63.6	63.3	63.1	64.6	66.1	67.4	68.7	69.8	70.9
77.5°	52.0	50.7	49.4	49.6	49.8	50.9	52.0	53.2	54.5	55.2	55.8
80°	36.9	36.5	36.1	36.5	36.9	37.8	38.6	39.5	40.4	40.8	41.2
82.5°	25.3	24.9	24.5	25.1	25.8	26.4	27.1	27.7	28.3	28.6	28.8
85°	14.6	15.2	15.9	15.9	15.9	16.1	16.3	16.5	16.7	16.5	16.3
87.5°	6.9	7.1	7.3	7.3	7.3	7.5	7.7	7.7	7.7	7.5	7.3
90°	10.8	13.6	16.8	20.0	23.1	26.3	27.3	28.2	29.2	30.2	30.9
92.5°	19.3	19.7	21.9	24.1	26.3	28.5	30.2	31.9	33.6	35.3	36.3
95°	26.9	23.2	25.9	28.6	31.3	33.9	35.7	37.4	39.1	40.8	41.6
97.5°	94.3	84.7	72.3	59.9	47.5	35.0	37.0	38.9	40.9	42.8	43.9
100°	204.5	188.0	150.0	112.1	74.1	36.1	38.1	40.0	42.0	43.9	45.0
102.5°	270.0	250.4	208.1	165.7	123.4	81.0	73.0	65.0	56.9	48.9	45.1
105°	337.0	327.4	305.5	283.6	261.7	239.8	196.7	153.7	110.6	67.5	46.2
107.5°	408.5	411.4	415.0	418.7	422.3	426.0	388.5	351.0	313.6	276.1	241.4
110°	480.9	483.2	485.8	488.5	491.2	493.9	485.8	477.8	469.8	461.7	440.3



TEST NUMBER: P831342

CATALOG NUMBER: S123DIP-S340D1195U830-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	550.0	552.2	554.8	557.5	560.2	562.9	565.0	567.2	569.4	571.6	572.5
115°	618.0	619.8	622.0	624.2	626.4	628.6	631.0	633.4	635.9	638.3	640.0
117.5°	686.8	688.3	689.5	690.7	692.0	693.2	695.1	697.1	699.0	701.0	702.1
120°	751.2	752.7	753.4	754.1	754.9	755.6	757.5	759.5	761.4	763.4	764.3
122.5°	812.8	814.1	815.1	816.1	817.0	818.0	819.2	820.4	821.7	822.9	823.6
125°	870.7	872.2	873.1	874.1	875.1	876.0	876.5	877.0	877.5	878.0	878.5
127.5°	927.6	929.2	930.4	931.6	932.9	934.1	934.8	935.5	936.3	937.0	937.1
130°	980.2	981.7	982.6	983.6	984.6	985.5	986.5	987.5	988.5	989.4	989.7
132.5°	1030.6	1031.9	1032.6	1033.4	1034.1	1034.8	1035.8	1036.8	1037.7	1038.7	1038.8
135°	1080.1	1081.3	1082.3	1083.3	1084.2	1085.2	1085.9	1086.7	1087.4	1088.1	1088.1
137.5°	1125.8	1127.1	1127.5	1128.0	1128.5	1129.0	1130.2	1131.4	1132.7	1133.9	1134.2
140°	1167.7	1168.8	1169.5	1170.2	1171.0	1171.7	1172.7	1173.7	1174.6	1175.6	1175.8
142.5°	1208.2	1209.3	1210.0	1210.8	1211.5	1212.2	1213.0	1213.7	1214.4	1215.1	1215.1
145°	1246.4	1247.5	1248.0	1248.5	1249.0	1249.5	1249.9	1250.4	1250.9	1251.4	1251.6
147.5°	1280.6	1281.5	1281.9	1282.4	1282.9	1283.4	1283.9	1284.4	1284.9	1285.4	1285.0
150°	1311.5	1312.1	1312.6	1313.1	1313.6	1314.1	1314.6	1315.0	1315.5	1316.0	1315.9
152.5°	1339.1	1339.4	1339.6	1339.9	1340.1	1340.3	1341.3	1342.3	1343.3	1344.2	1344.1
155°	1363.6	1363.5	1363.7	1364.0	1364.2	1364.4	1365.7	1366.9	1368.1	1369.3	1369.2
157.5°	1387.4	1387.3	1387.1	1386.8	1386.6	1386.3	1387.8	1389.3	1390.7	1392.2	1391.9
160°	1406.2	1405.9	1405.7	1405.4	1405.2	1405.0	1406.4	1407.9	1409.3	1410.8	1410.7
162.5°	1422.8	1422.4	1422.1	1421.9	1421.6	1421.4	1423.1	1424.8	1426.5	1428.2	1428.3
165°	1437.1	1436.6	1436.3	1436.1	1435.9	1435.6	1437.6	1439.5	1441.5	1443.4	1443.5
167.5°	1448.1	1447.7	1447.7	1447.7	1447.7	1447.7	1449.6	1451.6	1453.5	1455.4	1455.4
170°	1458.0	1457.5	1457.5	1457.5	1457.5	1457.5	1459.5	1461.4	1463.4	1465.3	1465.3
172.5°	1463.6	1463.1	1463.4	1463.6	1463.8	1464.1	1466.0	1468.0	1469.9	1471.9	1471.8
175°	1469.1	1468.6	1468.8	1469.1	1469.3	1469.6	1471.3	1473.0	1474.7	1476.4	1476.3
177.5°	1471.3	1470.8	1471.0	1471.3	1471.5	1471.8	1473.7	1475.6	1477.6	1479.5	1479.3
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P831342

CATALOG NUMBER: S123DIP-S340D1195U830-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	925.4	925.4	925.4	925.4
2.5°	822.6	821.1	815.0	809.0
5°	697.4	692.2	690.5	688.8
7.5°	609.4	608.9	599.9	590.9
10°	531.8	532.5	524.3	516.2
12.5°	476.4	471.1	470.4	469.8
15°	434.8	429.9	429.0	428.1
17.5°	405.4	402.4	401.5	400.7
20°	383.0	381.3	379.8	378.3
22.5°	363.7	361.6	360.3	359.0
25°	345.0	343.1	342.7	342.3
27.5°	328.3	325.9	325.9	325.9
30°	312.4	310.9	310.3	309.6
32.5°	297.6	296.3	296.3	296.3
35°	283.6	283.0	282.1	281.3
37.5°	271.0	271.0	270.5	270.1
40°	258.7	259.4	259.4	259.4
42.5°	247.6	248.2	248.2	248.2
45°	236.0	237.0	237.5	237.9
47.5°	224.6	226.3	226.7	227.2
50°	213.4	214.7	214.9	215.1
52.5°	202.0	203.5	204.6	205.7
55°	190.0	191.5	192.2	192.8
57.5°	177.1	178.6	178.9	179.1
60°	163.0	164.5	164.9	165.3
62.5°	149.4	150.3	150.7	151.2
65°	134.0	135.3	136.1	137.0
67.5°	119.2	120.2	120.2	120.2
70°	102.6	103.1	103.7	104.4
72.5°	87.4	87.6	87.6	87.6
75°	71.3	71.7	71.9	72.1
77.5°	56.0	56.3	56.3	56.3
80°	41.0	40.8	40.8	40.8
82.5°	28.1	27.5	27.5	27.5
85°	16.1	15.9	16.1	16.3
87.5°	7.3	7.3	7.3	7.3
90°	31.4	31.9	32.4	32.9
92.5°	36.5	36.7	37.0	37.2
95°	41.6	41.6	41.6	41.6
97.5°	44.2	44.4	44.7	44.9
100°	45.3	45.5	45.7	46.0
102.5°	45.6	46.1	46.6	47.1
105°	46.7	47.2	47.7	48.2
107.5°	209.5	177.6	145.8	113.9
110°	405.5	370.7	335.9	301.1



TEST NUMBER: P831342

CATALOG NUMBER: S123DIP-S340D1195U830-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	572.0	571.5	571.0	570.5
115°	641.0	641.9	642.9	643.9
117.5°	702.3	702.5	702.8	703.0
120°	764.3	764.3	764.3	764.3
122.5°	823.8	824.1	824.3	824.6
125°	879.0	879.5	879.9	880.4
127.5°	936.6	936.2	935.7	935.2
130°	989.2	988.7	988.2	987.7
132.5°	1038.1	1037.4	1036.7	1035.9
135°	1087.4	1086.7	1085.9	1085.2
137.5°	1133.7	1133.3	1132.8	1132.3
140°	1175.4	1174.9	1174.4	1173.9
142.5°	1214.4	1213.7	1213.0	1212.2
145°	1251.6	1251.6	1251.6	1251.6
147.5°	1283.8	1282.6	1281.3	1280.1
150°	1315.2	1314.4	1313.7	1313.0
152.5°	1342.9	1341.7	1340.5	1339.3
155°	1367.7	1366.3	1364.8	1363.3
157.5°	1390.0	1388.0	1386.1	1384.1
160°	1409.0	1407.3	1405.6	1403.9
162.5°	1426.9	1425.4	1423.9	1422.5
165°	1441.8	1440.1	1438.4	1436.7
167.5°	1453.5	1451.6	1449.6	1447.7
170°	1463.4	1461.4	1459.5	1457.5
172.5°	1469.6	1467.4	1465.2	1463.0
175°	1474.3	1472.4	1470.4	1468.5
177.5°	1476.9	1474.4	1472.0	1469.6
180°	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P831342

CATALOG NUMBER: S123DIP-S340D1195U830-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.56	9.22	9.72	10.36	11.95	10.80	11.46	11.95	12.59	14.19
	3H	10.20	10.79	11.36	11.93	13.54	12.21	12.80	13.37	13.94	15.55
	4H	10.76	11.32	11.93	12.47	14.08	12.65	13.21	13.82	14.36	15.97
	6H	11.12	11.64	12.30	12.79	14.41	12.92	13.43	14.09	14.58	16.20
	8H	11.22	11.70	12.39	12.87	14.48	12.97	13.46	14.15	14.62	16.24
	12H	11.25	11.72	12.43	12.87	14.51	12.99	13.45	14.17	14.61	16.24
4H	2H	9.12	9.67	10.29	10.82	12.43	10.94	11.50	12.12	12.64	14.26
	3H	10.93	11.39	12.11	12.56	14.19	12.54	13.01	13.72	14.18	15.80
	4H	11.62	12.05	12.80	13.20	14.85	13.12	13.55	14.30	14.70	16.35
	6H	12.08	12.45	13.27	13.63	15.26	13.51	13.88	14.70	15.06	16.69
	8H	12.21	12.56	13.40	13.73	15.38	13.62	13.96	14.80	15.13	16.78
	12H	12.27	12.58	13.47	13.76	15.42	13.65	13.96	14.85	15.15	16.80
8H	4H	11.87	12.21	13.05	13.38	15.03	13.21	13.55	14.39	14.72	16.37
	6H	12.45	12.73	13.65	13.95	15.59	13.70	13.99	14.91	15.20	16.84
	8H	12.66	12.90	13.86	14.09	15.76	13.88	14.13	15.09	15.32	16.98
	12H	12.77	12.99	13.98	14.18	15.87	13.97	14.19	15.19	15.38	17.08
12H	4H	11.86	12.17	13.06	13.35	15.00	13.17	13.48	14.37	14.67	16.32
	6H	12.50	12.74	13.71	13.94	15.60	13.72	13.96	14.92	15.15	16.82
	8H	12.72	12.94	13.94	14.13	15.83	13.91	14.12	15.12	15.31	17.01