

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831589

Luminaire Tested: S123DIP-S775D1025U835-4F0-1E-UDD-G1

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P831589  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S775D1025U835-4F0-1E-UDD-G1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7070.3 lumens  
Efficiency: N/A  
Efficacy: 136.5 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 51.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P831589

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-G1

### Luminous Intensity Polar Plot





TEST NUMBER: P831589

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-G1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20										
RC	80					70					50					30					10					0					
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0				
RCR																															
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50													
1	98	94	90	87	91	87	84	81	74	72	70	62	60	59	51	49	49	43													
2	90	83	77	72	83	77	72	67	65	62	58	55	52	50	45	43	42	37													
3	83	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36	32													
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32	28													
5	70	59	51	45	64	55	48	43	47	42	38	40	36	33	33	31	28	25													
6	65	53	45	40	60	49	43	37	43	37	33	37	32	29	31	28	25	22													
7	60	48	40	35	55	45	38	33	39	34	30	34	29	26	28	25	23	20													
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	26	23	21	18													
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	24	21	19	17													
10	49	37	30	26	45	35	29	24	31	26	22	27	23	20	23	20	17	16													

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	23750	23750	23750	23750	23750
5°	30035	28348	23961	19310	17744
10°	30326	31243	23802	15393	13450
15°	22841	29008	23640	13035	11375
20°	15914	23473	23338	11400	10332
25°	12136	18051	22823	10488	9691
30°	10499	14342	22002	9843	9175
35°	9741	12107	21055	9377	8812
40°	9222	10862	19724	8934	8689
45°	8914	10053	18033	8587	8634
50°	8761	9413	16031	8272	8589
55°	8435	8944	14063	7974	8627
60°	8133	8441	12122	7692	8486
65°	7641	7967	10458	7394	8318
70°	7056	7361	8894	6895	7830
75°	6388	6600	7623	6409	7153
80°	5269	5777	6031	5585	6031
85°	4174	4681	4421	4742	4804

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 20588 cd/sqm



TEST NUMBER: P831589

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-G1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	208.6	3.0
10°-20°	518.9	7.3
20°-30°	614.4	8.7
30°-40°	617.8	8.7
40°-50°	566.8	8.0
50°-60°	467.8	6.6
60°-70°	330.9	4.7
70°-80°	176.7	2.5
80°-90°	47.5	0.7
90°-100°	81.8	1.2
100°-110°	247.6	3.5
110°-120°	421.5	6.0
120°-130°	554.5	7.8
130°-140°	623.3	8.8
140°-150°	612.7	8.7
150°-160°	515.9	7.3
160°-170°	343.4	4.9
170°-180°	120.3	1.7
0°-30°	1341.9	19.0
0°-40°	1959.7	27.7
0°-60°	2994.4	42.4
0°-90°	3549.4	50.2
90°-120°	750.9	10.6
90°-150°	2541.3	35.9
90°-180°	3521.0	49.8
0°-180°	7070.3	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2206	2206	2206	2206	2206	
5°	2780	2624	2218	1787	1642	265
15°	2050	2603	2121	1170	1021	566
25°	1022	1520	1922	883	816	482
35°	741	921	1602	714	671	466
45°	586	660	1185	564	567	454
55°	450	477	749	425	460	402
65°	300	313	411	290	327	298
75°	154	159	183	154	172	161
85°	34	38	36	38	39	38
90°	30	24	1	24	30	16
95°	78	74	59	74	78	78
105°	238	236	225	236	238	252
115°	425	425	424	425	425	421
125°	614	622	621	622	614	549
135°	805	810	806	810	805	619
145°	977	982	977	982	977	610
155°	1117	1120	1119	1120	1117	515
165°	1215	1216	1219	1216	1215	343
175°	1263	1264	1268	1264	1263	120
180°	1271	1271	1271	1271	1271	



TEST NUMBER: P831589

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4
2.5°	2486.9	2484.3	2481.8	2469.0	2456.2	2450.0	2443.9	2425.5	2407.0	2386.5	2366.1
5°	2779.7	2786.9	2794.0	2785.8	2777.7	2752.6	2727.5	2694.2	2660.9	2623.6	2586.2
7.5°	2914.8	2918.9	2923.0	2917.9	2912.8	2906.1	2899.5	2869.8	2840.1	2801.7	2763.3
10°	2774.6	2783.8	2793.0	2813.0	2832.9	2855.5	2878.0	2873.9	2869.8	2858.5	2847.3
12.5°	2466.4	2477.7	2488.9	2528.9	2568.8	2620.0	2671.2	2715.2	2759.2	2789.9	2820.7
15°	2049.7	2080.9	2112.2	2148.5	2184.9	2260.1	2335.4	2428.0	2520.7	2603.1	2685.5
17.5°	1688.3	1700.1	1711.8	1750.7	1789.7	1884.4	1979.1	2086.1	2193.0	2329.7	2466.4
20°	1389.3	1400.1	1410.8	1462.0	1513.2	1587.4	1661.7	1782.0	1902.3	2049.2	2196.1
22.5°	1167.2	1184.1	1201.0	1229.6	1258.3	1329.4	1400.6	1507.6	1614.6	1776.9	1939.1
25°	1021.8	1034.1	1046.4	1063.8	1081.2	1138.0	1194.8	1282.9	1370.9	1519.9	1668.8
27.5°	922.5	927.6	932.7	950.1	967.5	1004.4	1041.2	1117.0	1192.8	1319.2	1445.6
30°	844.7	848.2	851.8	867.2	882.5	907.6	932.7	987.5	1042.3	1153.9	1265.5
32.5°	790.4	793.0	795.5	807.3	819.1	837.0	854.9	894.8	934.8	1026.9	1119.0
35°	741.3	742.8	744.3	753.0	761.7	775.0	788.3	818.6	848.8	921.4	994.1
37.5°	698.3	700.3	702.3	707.5	712.6	724.4	736.1	760.2	784.3	840.1	895.9
40°	656.3	659.9	663.4	667.0	670.6	680.3	690.1	708.5	726.9	773.0	819.1
42.5°	620.4	624.0	627.6	629.1	630.7	636.3	641.9	658.8	675.7	710.0	744.3
45°	585.6	587.2	588.7	590.2	591.8	596.4	601.0	615.8	630.7	660.4	690.1
47.5°	553.9	553.9	553.9	554.9	555.9	560.0	564.1	574.9	585.6	608.7	631.7
50°	523.2	523.2	523.2	521.6	520.1	522.7	525.2	533.4	541.6	562.1	582.6
52.5°	486.3	486.3	486.3	486.8	487.3	487.3	487.3	494.5	501.7	520.1	538.5
55°	449.5	451.5	453.6	452.0	450.5	451.5	452.5	457.1	461.7	476.6	491.4
57.5°	412.6	413.6	414.7	414.1	413.6	414.1	414.7	418.7	422.8	434.1	445.4
60°	377.8	377.8	377.8	376.8	375.7	376.8	377.8	379.8	381.9	392.1	402.4
62.5°	338.9	339.4	339.9	340.4	340.9	339.9	338.9	341.4	344.0	351.7	359.4
65°	300.0	300.5	301.0	302.5	304.1	303.1	302.0	304.6	307.1	312.8	318.4
67.5°	265.2	264.1	263.1	263.6	264.1	265.7	267.2	267.7	268.2	274.4	280.5
70°	224.2	225.2	226.3	225.8	225.2	225.8	226.3	227.8	229.3	233.9	238.6
72.5°	187.4	187.9	188.4	188.4	188.4	189.4	190.4	192.0	193.5	196.1	198.6
75°	153.6	153.6	153.6	154.6	155.6	156.1	156.6	156.6	156.6	158.7	160.7
77.5°	116.7	119.3	121.8	121.3	120.8	121.8	122.9	124.4	125.9	127.0	128.0
80°	85.0	85.0	85.0	85.5	86.0	87.5	89.1	90.1	91.1	93.2	95.2
82.5°	54.3	54.8	55.3	56.8	58.4	59.4	60.4	61.9	63.5	63.5	63.5
85°	33.8	32.8	31.7	32.8	33.8	34.8	35.8	36.3	36.9	37.9	38.9
87.5°	16.4	16.4	16.4	16.4	16.4	16.9	17.4	17.4	17.4	17.4	17.4
90°	29.9	29.5	29.1	28.6	28.2	27.5	26.6	25.7	24.8	24.0	21.1
92.5°	42.9	43.4	43.8	44.3	44.7	44.6	43.9	43.3	42.6	41.9	40.6
95°	77.9	77.9	77.9	77.9	77.9	77.4	76.5	75.6	74.8	73.9	72.1
97.5°	111.8	112.0	112.2	112.5	112.7	112.2	111.1	110.0	108.9	107.8	106.5
100°	151.7	151.3	150.8	150.4	150.0	149.4	148.7	148.1	147.4	146.7	145.6
102.5°	192.7	192.9	193.1	193.3	193.5	193.3	192.7	192.0	191.3	190.7	189.1
105°	237.6	237.1	236.7	236.2	235.8	235.6	235.6	235.6	235.6	235.6	233.6
107.5°	283.5	283.7	283.9	284.2	284.4	284.2	283.5	282.8	282.2	281.5	280.6
110°	330.4	330.9	331.3	331.7	332.2	332.0	331.1	330.2	329.3	328.4	328.0



TEST NUMBER: P831589

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	380.3	380.3	380.3	380.3	380.3	379.8	378.7	377.5	376.4	375.3	375.3
115°	425.2	425.5	425.7	425.9	426.1	426.1	425.9	425.7	425.5	425.2	425.7
117.5°	471.2	471.8	472.5	473.2	473.8	474.1	474.1	474.1	474.1	474.1	474.6
120°	520.1	520.5	521.0	521.4	521.8	522.2	522.4	522.6	522.8	523.1	524.2
122.5°	567.0	567.6	568.3	569.0	569.6	570.3	571.0	571.6	572.3	573.0	573.4
125°	613.9	614.8	615.7	616.6	617.4	618.3	619.2	620.1	621.0	621.9	622.3
127.5°	660.8	661.7	662.6	663.5	664.4	665.5	666.8	668.1	669.5	670.8	671.2
130°	706.7	708.3	709.8	711.4	712.9	714.2	715.0	715.9	716.8	717.7	718.4
132.5°	754.6	755.8	756.9	758.0	759.1	760.2	761.3	762.4	763.5	764.6	765.1
135°	804.6	805.0	805.4	805.9	806.3	807.0	807.9	808.8	809.7	810.5	810.8
137.5°	848.5	849.1	849.8	850.5	851.1	852.0	853.1	854.2	855.4	856.5	855.8
140°	891.4	893.0	894.5	896.1	897.6	898.5	898.7	898.9	899.2	899.4	899.2
142.5°	935.3	936.4	937.5	938.6	939.8	940.4	940.6	940.9	941.1	941.3	940.9
145°	977.2	978.1	979.0	979.9	980.8	981.3	981.6	981.8	982.0	982.2	981.6
147.5°	1015.2	1016.5	1017.8	1019.2	1020.5	1021.2	1021.2	1021.2	1021.2	1021.2	1020.5
150°	1051.1	1052.4	1053.8	1055.1	1056.4	1057.1	1057.1	1057.1	1057.1	1057.1	1056.7
152.5°	1086.1	1087.2	1088.3	1089.4	1090.5	1090.8	1090.4	1089.9	1089.5	1089.0	1088.8
155°	1117.0	1118.5	1120.1	1121.7	1123.2	1123.5	1122.7	1121.8	1120.9	1120.0	1119.8
157.5°	1145.9	1147.3	1148.6	1149.9	1151.3	1151.5	1150.6	1149.7	1148.8	1147.9	1147.7
160°	1173.9	1174.8	1175.7	1176.6	1177.4	1177.3	1176.2	1175.1	1174.0	1172.9	1172.9
162.5°	1194.9	1196.4	1198.0	1199.5	1201.1	1201.3	1200.2	1199.1	1198.0	1196.9	1196.6
165°	1214.8	1216.4	1217.9	1219.5	1221.0	1221.1	1219.8	1218.5	1217.1	1215.8	1215.8
167.5°	1232.8	1234.1	1235.4	1236.8	1238.1	1238.1	1236.8	1235.4	1234.1	1232.8	1232.6
170°	1245.8	1247.3	1248.9	1250.4	1252.0	1252.0	1250.4	1248.9	1247.3	1245.8	1245.8
172.5°	1255.7	1257.3	1258.9	1260.4	1262.0	1262.1	1260.7	1259.4	1258.1	1256.7	1256.7
175°	1262.7	1264.3	1265.8	1267.4	1268.9	1269.1	1267.7	1266.4	1265.1	1263.7	1263.7
177.5°	1266.7	1268.3	1269.8	1271.4	1272.9	1273.0	1271.7	1270.4	1269.1	1267.7	1267.7
180°	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7



TEST NUMBER: P831589

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4
2.5°	2359.9	2353.8	2331.3	2308.7	2283.1	2257.5	2238.6	2219.7	2191.5	2163.4	2140.3
5°	2557.5	2528.9	2481.3	2433.6	2369.1	2304.6	2261.1	2217.6	2159.3	2100.9	2054.3
7.5°	2714.2	2665.0	2598.5	2531.9	2447.5	2363.0	2283.1	2203.3	2114.2	2025.1	1952.4
10°	2814.0	2780.7	2703.9	2627.1	2514.0	2400.9	2289.3	2177.7	2063.0	1948.3	1852.1
12.5°	2823.7	2826.8	2756.1	2685.5	2557.5	2429.5	2293.9	2158.2	2013.9	1869.5	1757.4
15°	2738.2	2791.0	2752.1	2713.1	2584.1	2455.1	2288.3	2121.4	1955.0	1788.6	1659.1
17.5°	2579.5	2692.7	2698.3	2703.9	2574.9	2445.9	2261.1	2076.3	1887.9	1699.6	1563.4
20°	2363.0	2529.9	2587.2	2644.6	2539.6	2434.7	2236.0	2037.4	1826.5	1615.6	1472.8
22.5°	2141.9	2344.6	2449.5	2554.5	2476.6	2398.8	2187.4	1976.0	1753.3	1530.6	1385.8
25°	1890.0	2111.1	2272.4	2433.6	2386.0	2338.4	2130.1	1921.7	1684.7	1447.7	1299.8
27.5°	1670.4	1895.1	2089.6	2284.2	2273.9	2263.7	2056.9	1850.1	1607.4	1364.8	1221.9
30°	1474.8	1684.2	1901.8	2119.3	2144.4	2169.5	1969.8	1770.2	1527.0	1283.9	1146.2
32.5°	1301.8	1484.6	1718.0	1951.4	2000.6	2049.7	1869.5	1689.3	1448.7	1208.1	1075.5
35°	1160.0	1325.9	1559.3	1792.7	1854.2	1915.6	1758.9	1602.3	1367.8	1133.4	1006.9
37.5°	1034.6	1173.3	1401.1	1628.9	1704.2	1779.4	1639.2	1498.9	1279.3	1059.7	943.5
40°	930.7	1042.3	1251.6	1461.0	1548.0	1635.1	1519.4	1403.7	1195.3	987.0	880.0
42.5°	843.6	942.9	1132.9	1322.8	1406.2	1489.7	1391.9	1294.1	1108.8	923.5	825.7
45°	769.4	848.8	1021.3	1193.8	1273.1	1352.5	1268.5	1184.6	1021.3	858.0	766.8
47.5°	699.8	767.9	915.3	1062.7	1133.4	1204.0	1138.5	1073.0	934.8	796.5	714.1
50°	637.3	692.1	821.1	950.1	1011.5	1073.0	1015.1	957.3	843.6	730.0	658.3
52.5°	583.1	627.6	735.6	843.6	896.4	949.1	899.4	849.8	759.7	669.6	607.1
55°	529.3	567.2	660.9	754.6	790.4	826.2	787.8	749.4	676.8	604.1	551.3
57.5°	479.2	512.9	589.7	666.5	694.2	721.8	687.0	652.2	597.4	542.6	498.6
60°	430.0	457.7	521.6	585.6	602.5	619.4	591.3	563.1	524.7	486.3	446.9
62.5°	384.4	409.5	457.1	504.7	516.0	527.3	505.8	484.3	455.1	425.9	395.2
65°	337.4	356.3	395.2	434.1	441.3	448.4	429.5	410.6	388.5	366.5	344.0
67.5°	293.8	307.1	338.9	370.6	371.1	371.7	356.3	340.9	328.6	316.4	298.4
70°	251.4	264.1	285.1	306.1	306.6	307.1	294.9	282.6	273.4	264.1	250.8
72.5°	207.8	217.1	232.9	248.8	247.8	246.7	239.1	231.4	224.2	217.1	207.3
75°	168.4	176.1	186.8	197.6	194.5	191.5	187.4	183.3	177.1	171.0	164.8
77.5°	132.6	137.2	143.3	149.5	147.4	145.4	141.8	138.2	133.6	129.0	126.4
80°	97.3	99.3	103.4	107.5	106.5	105.5	101.4	97.3	96.2	95.2	91.6
82.5°	66.0	68.6	69.6	70.6	70.1	69.6	66.5	63.5	62.5	61.4	60.9
85°	39.4	39.9	40.4	41.0	39.4	37.9	36.9	35.8	35.8	35.8	35.3
87.5°	17.9	18.4	18.4	18.4	17.9	17.4	16.4	15.4	15.9	16.4	16.4
90°	18.2	15.3	12.4	9.9	7.7	5.4	3.2	1.0	3.2	5.4	7.7
92.5°	39.3	37.9	36.6	35.3	33.9	32.6	31.3	29.9	31.3	32.6	33.9
95°	70.3	68.5	66.8	65.1	63.6	62.0	60.4	58.9	60.4	62.0	63.6
97.5°	105.1	103.8	102.5	101.3	100.2	99.0	97.9	96.8	97.9	99.0	100.2
100°	144.5	143.4	142.3	141.1	139.7	138.4	137.1	135.8	137.1	138.4	139.7
102.5°	187.6	186.0	184.4	183.3	182.7	182.0	181.3	180.7	181.3	182.0	182.7
105°	231.6	229.6	227.6	226.4	225.9	225.5	225.0	224.6	225.0	225.5	225.9
107.5°	279.7	278.8	277.9	277.4	277.2	276.9	276.7	276.5	276.7	276.9	277.2
110°	327.5	327.1	326.6	326.2	325.7	325.3	324.9	324.4	324.9	325.3	325.7





TEST NUMBER: P831589

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	375.3	375.3	375.3	375.2	375.0	374.8	374.5	374.3	374.5	374.8	375.0
115°	426.1	426.6	427.0	426.9	426.2	425.6	424.9	424.2	424.9	425.6	426.2
117.5°	475.0	475.5	475.9	476.0	475.8	475.6	475.4	475.1	475.4	475.6	475.8
120°	525.3	526.4	527.5	527.4	526.1	524.7	523.4	522.1	523.4	524.7	526.1
122.5°	573.9	574.3	574.7	574.5	573.6	572.7	571.9	571.0	571.9	572.7	573.6
125°	622.8	623.2	623.7	623.5	622.9	622.2	621.6	620.9	621.6	622.2	622.9
127.5°	671.7	672.1	672.6	672.1	670.8	669.5	668.1	666.8	668.1	669.5	670.8
130°	719.0	719.7	720.4	719.8	718.0	716.3	714.5	712.7	714.5	716.3	718.0
132.5°	765.5	766.0	766.4	765.7	764.0	762.2	760.4	758.6	760.4	762.2	764.0
135°	811.0	811.2	811.4	810.9	809.5	808.2	806.9	805.6	806.9	808.2	809.5
137.5°	855.1	854.5	853.8	852.9	851.8	850.7	849.6	848.5	849.6	850.7	851.8
140°	898.9	898.7	898.5	897.8	896.7	895.6	894.5	893.4	894.5	895.6	896.7
142.5°	940.4	940.0	939.5	938.8	937.7	936.5	935.4	934.3	935.4	936.5	937.7
145°	980.9	980.2	979.6	979.0	978.6	978.1	977.7	977.2	977.7	978.1	978.6
147.5°	1019.8	1019.2	1018.5	1017.7	1016.8	1016.0	1015.1	1014.2	1015.1	1016.0	1016.8
150°	1056.2	1055.8	1055.3	1054.9	1054.4	1054.0	1053.6	1053.1	1053.6	1054.0	1054.4
152.5°	1088.6	1088.4	1088.2	1087.7	1087.0	1086.4	1085.7	1085.1	1085.7	1086.4	1087.0
155°	1119.5	1119.3	1119.1	1119.0	1119.0	1119.0	1119.0	1119.0	1119.0	1119.0	1119.0
157.5°	1147.5	1147.3	1147.1	1147.1	1147.3	1147.5	1147.7	1147.9	1147.7	1147.5	1147.3
160°	1172.9	1172.9	1172.9	1173.1	1173.6	1174.0	1174.4	1174.9	1174.4	1174.0	1173.6
162.5°	1196.4	1196.2	1196.0	1196.2	1196.9	1197.5	1198.2	1198.8	1198.2	1197.5	1196.9
165°	1215.8	1215.8	1215.8	1216.2	1216.8	1217.5	1218.1	1218.8	1218.1	1217.5	1216.8
167.5°	1232.3	1232.1	1231.9	1232.2	1233.1	1234.0	1234.9	1235.8	1234.9	1234.0	1233.1
170°	1245.8	1245.8	1245.8	1246.2	1247.1	1248.0	1248.9	1249.8	1248.9	1248.0	1247.1
172.5°	1256.7	1256.7	1256.7	1257.2	1258.1	1259.0	1259.8	1260.7	1259.8	1259.0	1258.1
175°	1263.7	1263.7	1263.7	1264.2	1265.1	1265.9	1266.8	1267.7	1266.8	1265.9	1265.1
177.5°	1267.7	1267.7	1267.7	1268.2	1269.1	1269.9	1270.8	1271.7	1270.8	1269.9	1269.1
180°	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7



TEST NUMBER: P831589

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4
2.5°	2117.3	2097.3	2077.4	2062.0	2046.6	2020.5	1994.4	1988.3	1982.1	1973.4	1964.7
5°	2007.7	1958.6	1909.4	1865.4	1821.4	1787.1	1752.8	1730.3	1707.7	1691.4	1675.0
7.5°	1879.8	1806.0	1732.3	1680.1	1627.9	1578.2	1528.6	1512.7	1496.8	1475.3	1453.8
10°	1755.9	1674.5	1593.1	1525.0	1456.9	1408.3	1359.6	1340.2	1320.7	1293.6	1266.5
12.5°	1645.3	1556.2	1467.1	1398.6	1330.0	1282.9	1235.8	1207.6	1179.5	1164.1	1148.7
15°	1529.6	1434.4	1339.2	1275.7	1212.2	1169.7	1127.2	1102.7	1078.1	1063.2	1048.4
17.5°	1427.2	1333.0	1238.8	1177.9	1117.0	1078.1	1039.2	1017.7	996.2	984.9	973.7
20°	1330.0	1237.8	1145.7	1086.3	1026.9	995.2	963.4	949.6	935.8	926.6	917.4
22.5°	1240.9	1150.3	1059.7	1009.0	958.3	932.7	907.1	897.4	887.7	880.0	872.3
25°	1151.8	1070.9	990.0	947.0	904.0	883.1	862.1	852.3	842.6	834.9	827.3
27.5°	1079.1	1001.8	924.5	887.7	850.8	834.4	818.0	810.4	802.7	795.5	788.3
30°	1008.5	939.4	870.3	838.5	806.8	791.9	777.1	769.4	761.7	755.1	748.4
32.5°	942.9	883.6	824.2	795.0	765.8	753.5	741.3	732.0	722.8	717.7	712.6
35°	880.5	827.3	774.0	750.0	725.9	713.6	701.3	693.6	686.0	681.9	677.8
37.5°	827.3	779.6	732.0	709.0	686.0	674.2	662.4	655.8	649.1	647.6	646.0
40°	773.0	732.0	691.1	668.6	646.0	635.8	625.6	621.5	617.4	616.3	615.3
42.5°	727.9	688.0	648.1	627.6	607.1	598.4	589.7	587.7	585.6	587.2	588.7
45°	675.7	642.5	609.2	590.2	571.3	564.1	557.0	555.4	553.9	557.0	560.0
47.5°	631.7	601.0	570.3	552.4	534.4	529.3	524.2	523.7	523.2	527.3	531.4
50°	586.7	557.0	527.3	512.9	498.6	494.0	489.4	490.9	492.5	499.1	505.8
52.5°	544.7	517.0	489.4	476.1	462.8	459.7	456.6	460.2	463.8	471.0	478.1
55°	498.6	473.5	448.4	438.2	428.0	424.9	421.8	429.0	436.2	442.8	449.5
57.5°	454.6	432.6	410.6	401.3	392.1	391.6	391.1	397.8	404.4	411.6	418.7
60°	407.5	389.1	370.6	363.5	356.3	357.3	358.3	366.0	373.7	379.3	385.0
62.5°	364.5	349.1	333.8	327.1	320.5	323.0	325.6	333.3	340.9	347.6	354.2
65°	321.5	308.7	295.9	291.3	286.7	290.3	293.8	300.5	307.1	311.8	316.4
67.5°	280.5	269.8	259.0	255.4	251.9	255.4	259.0	265.7	272.3	276.9	281.6
70°	237.5	228.8	220.1	217.6	215.0	219.1	223.2	228.8	234.5	239.1	243.7
72.5°	197.6	190.9	184.3	183.8	183.3	186.8	190.4	196.1	201.7	204.8	207.8
75°	158.7	155.1	151.5	151.0	150.5	154.1	157.7	160.7	163.8	166.4	168.9
77.5°	123.9	120.8	117.7	118.3	118.8	121.3	123.9	127.0	130.0	131.6	133.1
80°	88.0	87.0	86.0	87.0	88.0	90.1	92.1	94.2	96.2	97.3	98.3
82.5°	60.4	59.4	58.4	59.9	61.4	63.0	64.5	66.0	67.6	68.1	68.6
85°	34.8	36.3	37.9	37.9	37.9	38.4	38.9	39.4	39.9	39.4	38.9
87.5°	16.4	16.9	17.4	17.4	17.4	17.9	18.4	18.4	18.4	17.9	17.4
90°	9.9	12.4	15.3	18.2	21.1	24.0	24.8	25.7	26.6	27.5	28.2
92.5°	35.3	36.6	37.9	39.3	40.6	41.9	42.6	43.3	43.9	44.6	44.7
95°	65.1	66.8	68.5	70.3	72.1	73.9	74.8	75.6	76.5	77.4	77.9
97.5°	101.3	102.5	103.8	105.1	106.5	107.8	108.9	110.0	111.1	112.2	112.7
100°	141.1	142.3	143.4	144.5	145.6	146.7	147.4	148.1	148.7	149.4	150.0
102.5°	183.3	184.4	186.0	187.6	189.1	190.7	191.3	192.0	192.7	193.3	193.5
105°	226.4	227.6	229.6	231.6	233.6	235.6	235.6	235.6	235.6	235.6	235.8
107.5°	277.4	277.9	278.8	279.7	280.6	281.5	282.2	282.8	283.5	284.2	284.4
110°	326.2	326.6	327.1	327.5	328.0	328.4	329.3	330.2	331.1	332.0	332.2



TEST NUMBER: P831589

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	375.2	375.3	375.3	375.3	375.3	375.3	376.4	377.5	378.7	379.8	380.3
115°	426.9	427.0	426.6	426.1	425.7	425.2	425.5	425.7	425.9	426.1	426.1
117.5°	476.0	475.9	475.5	475.0	474.6	474.1	474.1	474.1	474.1	474.1	473.8
120°	527.4	527.5	526.4	525.3	524.2	523.1	522.8	522.6	522.4	522.2	521.8
122.5°	574.5	574.7	574.3	573.9	573.4	573.0	572.3	571.6	571.0	570.3	569.6
125°	623.5	623.7	623.2	622.8	622.3	621.9	621.0	620.1	619.2	618.3	617.4
127.5°	672.1	672.6	672.1	671.7	671.2	670.8	669.5	668.1	666.8	665.5	664.4
130°	719.8	720.4	719.7	719.0	718.4	717.7	716.8	715.9	715.0	714.2	712.9
132.5°	765.7	766.4	766.0	765.5	765.1	764.6	763.5	762.4	761.3	760.2	759.1
135°	810.9	811.4	811.2	811.0	810.8	810.5	809.7	808.8	807.9	807.0	806.3
137.5°	852.9	853.8	854.5	855.1	855.8	856.5	855.4	854.2	853.1	852.0	851.1
140°	897.8	898.5	898.7	898.9	899.2	899.4	899.2	898.9	898.7	898.5	897.6
142.5°	938.8	939.5	940.0	940.4	940.9	941.3	941.1	940.9	940.6	940.4	939.8
145°	979.0	979.6	980.2	980.9	981.6	982.2	982.0	981.8	981.6	981.3	980.8
147.5°	1017.7	1018.5	1019.2	1019.8	1020.5	1021.2	1021.2	1021.2	1021.2	1021.2	1020.5
150°	1054.9	1055.3	1055.8	1056.2	1056.7	1057.1	1057.1	1057.1	1057.1	1057.1	1056.4
152.5°	1087.7	1088.2	1088.4	1088.6	1088.8	1089.0	1089.5	1089.9	1090.4	1090.8	1090.5
155°	1119.0	1119.1	1119.3	1119.5	1119.8	1120.0	1120.9	1121.8	1122.7	1123.5	1123.2
157.5°	1147.1	1147.1	1147.3	1147.5	1147.7	1147.9	1148.8	1149.7	1150.6	1151.5	1151.3
160°	1173.1	1172.9	1172.9	1172.9	1172.9	1172.9	1174.0	1175.1	1176.2	1177.3	1177.4
162.5°	1196.2	1196.0	1196.2	1196.4	1196.6	1196.9	1198.0	1199.1	1200.2	1201.3	1201.1
165°	1216.2	1215.8	1215.8	1215.8	1215.8	1215.8	1217.1	1218.5	1219.8	1221.1	1221.0
167.5°	1232.2	1231.9	1232.1	1232.3	1232.6	1232.8	1234.1	1235.4	1236.8	1238.1	1238.1
170°	1246.2	1245.8	1245.8	1245.8	1245.8	1245.8	1247.3	1248.9	1250.4	1252.0	1252.0
172.5°	1257.2	1256.7	1256.7	1256.7	1256.7	1256.7	1258.1	1259.4	1260.7	1262.1	1262.0
175°	1264.2	1263.7	1263.7	1263.7	1263.7	1263.7	1265.1	1266.4	1267.7	1269.1	1268.9
177.5°	1268.2	1267.7	1267.7	1267.7	1267.7	1267.7	1269.1	1270.4	1271.7	1273.0	1272.9
180°	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7



TEST NUMBER: P831589

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	2206.4	2206.4	2206.4	2206.4
2.5°	1961.1	1957.6	1943.2	1928.9
5°	1662.7	1650.4	1646.3	1642.2
7.5°	1452.8	1451.8	1430.3	1408.8
10°	1268.0	1269.5	1250.1	1230.6
12.5°	1135.9	1123.1	1121.6	1120.1
15°	1036.6	1024.9	1022.8	1020.8
17.5°	966.5	959.3	957.3	955.2
20°	913.3	909.2	905.6	902.0
22.5°	867.2	862.1	859.0	855.9
25°	822.6	818.0	817.0	816.0
27.5°	782.7	777.1	777.1	777.1
30°	744.8	741.3	739.7	738.2
32.5°	709.5	706.4	706.4	706.4
35°	676.2	674.7	672.7	670.6
37.5°	646.0	646.0	645.0	644.0
40°	616.9	618.4	618.4	618.4
42.5°	590.2	591.8	591.8	591.8
45°	562.6	565.2	566.2	567.2
47.5°	535.5	539.6	540.6	541.6
50°	508.8	511.9	512.4	512.9
52.5°	481.7	485.3	487.9	490.4
55°	453.0	456.6	458.2	459.7
57.5°	422.3	425.9	426.4	426.9
60°	388.5	392.1	393.2	394.2
62.5°	356.3	358.3	359.4	360.4
65°	319.4	322.5	324.6	326.6
67.5°	284.1	286.7	286.7	286.7
70°	244.7	245.7	247.3	248.8
72.5°	208.3	208.9	208.9	208.9
75°	170.0	171.0	171.5	172.0
77.5°	133.6	134.1	134.1	134.1
80°	97.8	97.3	97.3	97.3
82.5°	67.1	65.5	65.5	65.5
85°	38.4	37.9	38.4	38.9
87.5°	17.4	17.4	17.4	17.4
90°	28.6	29.1	29.5	29.9
92.5°	44.3	43.8	43.4	42.9
95°	77.9	77.9	77.9	77.9
97.5°	112.5	112.2	112.0	111.8
100°	150.4	150.8	151.3	151.7
102.5°	193.3	193.1	192.9	192.7
105°	236.2	236.7	237.1	237.6
107.5°	284.2	283.9	283.7	283.5
110°	331.7	331.3	330.9	330.4



TEST NUMBER: P831589

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	380.3	380.3	380.3	380.3
115°	425.9	425.7	425.5	425.2
117.5°	473.2	472.5	471.8	471.2
120°	521.4	521.0	520.5	520.1
122.5°	569.0	568.3	567.6	567.0
125°	616.6	615.7	614.8	613.9
127.5°	663.5	662.6	661.7	660.8
130°	711.4	709.8	708.3	706.7
132.5°	758.0	756.9	755.8	754.6
135°	805.9	805.4	805.0	804.6
137.5°	850.5	849.8	849.1	848.5
140°	896.1	894.5	893.0	891.4
142.5°	938.6	937.5	936.4	935.3
145°	979.9	979.0	978.1	977.2
147.5°	1019.2	1017.8	1016.5	1015.2
150°	1055.1	1053.8	1052.4	1051.1
152.5°	1089.4	1088.3	1087.2	1086.1
155°	1121.7	1120.1	1118.5	1117.0
157.5°	1149.9	1148.6	1147.3	1145.9
160°	1176.6	1175.7	1174.8	1173.9
162.5°	1199.5	1198.0	1196.4	1194.9
165°	1219.5	1217.9	1216.4	1214.8
167.5°	1236.8	1235.4	1234.1	1232.8
170°	1250.4	1248.9	1247.3	1245.8
172.5°	1260.4	1258.9	1257.3	1255.7
175°	1267.4	1265.8	1264.3	1262.7
177.5°	1271.4	1269.8	1268.3	1266.7
180°	1270.7	1270.7	1270.7	1270.7



TEST NUMBER: P831589

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-G1

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.59	15.42	15.55	16.39	17.66	16.83	17.65	17.79	18.63	19.90
	3H	16.24	16.98	17.21	17.96	19.25	18.25	18.99	19.22	19.97	21.27
	4H	16.81	17.51	17.80	18.50	19.80	18.70	19.40	19.69	20.38	21.69
	6H	17.18	17.83	18.18	18.82	20.13	18.97	19.62	19.97	20.61	21.92
	8H	17.28	17.89	18.28	18.90	20.21	19.03	19.65	20.04	20.65	21.97
	12H	17.32	17.90	18.33	18.90	20.24	19.05	19.64	20.06	20.64	21.97
4H	2H	15.16	15.86	16.16	16.85	18.15	16.99	17.69	17.98	18.67	19.98
	3H	16.99	17.57	17.99	18.59	19.90	18.60	19.19	19.61	20.20	21.52
	4H	17.69	18.22	18.70	19.23	20.56	19.19	19.72	20.20	20.73	22.07
	6H	18.16	18.62	19.18	19.65	20.98	19.59	20.05	20.61	21.08	22.41
	8H	18.29	18.72	19.32	19.75	21.10	19.70	20.13	20.72	21.15	22.50
	12H	18.36	18.75	19.40	19.79	21.14	19.74	20.13	20.78	21.17	22.52
8H	4H	17.95	18.38	18.97	19.40	20.75	19.29	19.72	20.31	20.74	22.09
	6H	18.54	18.89	19.58	19.96	21.30	19.79	20.14	20.84	21.21	22.56
	8H	18.74	19.05	19.80	20.11	21.47	19.97	20.28	21.02	21.33	22.70
	12H	18.87	19.14	19.92	20.18	21.60	20.07	20.34	21.13	21.39	22.80
12H	4H	17.95	18.33	18.99	19.37	20.73	19.26	19.65	20.30	20.69	22.04
	6H	18.59	18.90	19.64	19.95	21.32	19.80	20.11	20.86	21.17	22.53
	8H	18.82	19.09	19.88	20.14	21.55	20.00	20.28	21.06	21.32	22.73