

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331991

Luminaire Tested: **S123DIP-S775D1195U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331991
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1195U835-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8034.5 lumens
Efficiency: N/A
Efficacy: 141.2 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331991

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot



59% Up
41% Dn



TEST NUMBER: P331991

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	41	35
2	87	80	74	69	79	73	68	64	60	57	54	49	46	44	37	36	34	29
3	80	71	64	58	73	65	59	54	53	49	45	43	40	37	33	31	30	25
4	73	63	55	49	66	57	51	46	48	43	39	38	35	32	30	28	26	22
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	27	24	22	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	17
7	57	45	37	32	52	42	35	30	35	29	26	28	24	22	22	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11630	11630	11630	11630
5°	13870	11681	10351	11681
10°	17361	11622	9349	11622
15°	21293	11528	8704	11528
20°	25366	11381	8287	11381
25°	26935	11204	8195	11204
30°	23086	11074	8238	11074
35°	16056	10889	8324	10889
40°	12094	10673	8297	10673
45°	10041	10353	8193	10353
50°	8994	9696	8118	9696
55°	8409	8989	8017	8989
60°	7890	8249	7935	8249
65°	7414	7521	7679	7521
70°	6952	6688	7314	6688
75°	6226	5856	6704	5856
80°	5455	4804	5777	4804
85°	4273	3495	3878	3495



TEST NUMBER: P331991

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.4	1.3
10°-20°	341.3	4.2
20°-30°	572.8	7.1
30°-40°	648.6	8.1
40°-50°	581.7	7.2
50°-60°	469.4	5.8
60°-70°	327.1	4.1
70°-80°	171.9	2.1
80°-90°	46.4	0.6
90°-100°	56.9	0.7
100°-110°	271.0	3.4
110°-120°	650.9	8.1
120°-130°	828.8	10.3
130°-140°	885.6	11.0
140°-150°	828.1	10.3
150°-160°	668.0	8.3
160°-170°	431.1	5.4
170°-180°	148.6	1.8
0°-30°	1020.6	12.7
0°-40°	1669.2	20.8
0°-60°	2720.2	33.9
0°-90°	3265.7	40.6
90°-120°	978.7	12.2
90°-150°	3521.2	43.8
90°-180°	4769.0	59.4
0°-180°	8034.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1080	1080	1080	1080	1080	
5°	1284	1081	958	1081	1284	133
15°	1911	1034	781	1034	1911	552
25°	2268	943	690	943	2268	995
35°	1222	829	634	829	1222	794
45°	660	680	538	680	660	522
55°	448	479	427	479	448	402
65°	291	295	302	295	291	290
75°	150	141	161	141	150	160
85°	35	28	31	28	35	42
90°	35	1	35	1	35	18
95°	44	71	44	71	44	37
105°	51	346	51	346	51	117
115°	683	650	683	650	683	631
125°	934	916	934	916	934	834
135°	1151	1140	1151	1140	1151	888
145°	1328	1315	1328	1315	1328	829
155°	1446	1449	1446	1449	1446	667
165°	1524	1528	1524	1528	1524	430
175°	1558	1564	1558	1564	1558	148
180°	1564	1564	1564	1564	1564	



TEST NUMBER: P331991

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1146.7	1145.9	1143.8	1145.5	1142.1	1137.5	1137.1	1132.9	1120.7	1119.9	1116.6
5°	1283.7	1279.5	1279.0	1278.4	1271.1	1261.2	1242.3	1240.7	1215.6	1203.0	1187.9
7.5°	1461.0	1463.2	1455.6	1448.9	1426.5	1411.7	1391.5	1365.6	1334.8	1303.5	1282.6
10°	1588.4	1605.6	1584.2	1569.5	1555.9	1530.2	1500.4	1463.2	1426.1	1382.6	1349.6
12.5°	1724.9	1733.4	1729.1	1715.3	1694.1	1655.1	1602.2	1561.2	1527.0	1454.6	1425.4
15°	1910.8	1942.8	1922.4	1875.2	1876.3	1839.1	1770.0	1694.1	1653.8	1590.4	1504.1
17.5°	2108.9	2112.9	2104.2	2065.0	2038.8	1987.7	1923.9	1851.2	1769.5	1692.8	1601.2
20°	2214.5	2211.3	2193.0	2172.6	2127.6	2087.8	2018.2	1937.0	1832.3	1756.9	1656.9
22.5°	2273.1	2267.9	2259.2	2242.1	2204.6	2161.9	2099.4	2010.7	1911.1	1807.2	1691.7
25°	2267.9	2274.7	2275.7	2271.0	2257.9	2232.3	2183.1	2112.4	2012.9	1879.4	1759.0
27.5°	2062.7	2072.3	2100.3	2125.1	2152.8	2181.1	2177.3	2142.2	2068.6	1953.4	1806.1
30°	1857.4	1836.5	1888.3	1953.8	1998.3	2076.8	2120.8	2123.4	2082.0	1983.1	1839.6
32.5°	1572.6	1595.7	1618.6	1699.1	1796.4	1884.6	1972.1	2042.6	2050.6	1984.8	1859.3
35°	1221.9	1250.7	1292.6	1334.4	1439.2	1529.2	1683.1	1817.1	1923.9	1938.1	1861.1
37.5°	984.6	998.9	1025.4	1067.3	1135.8	1242.6	1361.7	1531.1	1685.8	1800.9	1805.9
40°	860.7	864.9	894.7	926.6	982.1	1070.1	1177.4	1327.1	1512.4	1673.2	1740.2
42.5°	767.7	776.9	789.6	820.2	864.4	930.6	1030.4	1154.1	1324.0	1509.0	1640.1
45°	659.6	670.1	678.0	698.4	729.8	774.3	843.9	957.0	1086.3	1277.4	1453.8
47.5°	588.2	589.1	594.9	610.3	631.7	665.1	714.3	787.0	905.7	1060.6	1241.8
50°	537.1	545.5	547.6	559.6	576.4	601.0	641.8	703.6	801.0	937.1	1103.6
52.5°	501.1	503.6	509.5	518.2	532.8	552.0	587.4	635.8	712.2	828.2	981.3
55°	448.1	448.1	453.9	460.7	469.1	486.3	509.9	545.5	603.6	693.7	820.4
57.5°	399.1	401.7	405.8	407.9	415.0	426.5	446.1	473.2	516.5	585.8	686.5
60°	366.5	371.2	370.7	374.8	381.1	390.0	406.8	428.8	467.5	523.0	607.8
62.5°	338.0	337.7	337.6	342.6	348.9	357.4	368.2	387.3	420.2	469.4	541.6
65°	291.1	290.0	293.7	296.8	298.9	305.2	313.6	330.3	352.3	389.0	445.0
67.5°	249.4	246.4	248.4	249.4	253.0	257.9	265.7	276.1	293.6	323.0	365.2
70°	220.9	218.3	217.8	218.8	222.0	225.6	231.4	241.3	257.6	281.1	312.0
72.5°	191.6	189.8	189.7	192.0	193.5	195.9	200.0	209.1	222.0	239.7	268.5
75°	149.7	149.7	149.7	150.2	151.8	153.9	157.1	161.8	171.7	184.3	203.6
77.5°	112.2	112.1	111.5	111.4	113.7	114.7	115.4	119.8	125.3	133.8	147.9
80°	88.0	85.3	86.4	88.0	89.0	89.5	91.1	92.1	96.9	101.6	111.5
82.5°	65.3	63.1	63.3	65.8	66.0	66.5	68.1	69.5	71.3	75.6	80.9
85°	34.6	34.6	35.1	35.1	35.6	35.1	36.6	37.2	37.2	39.8	42.9
87.5°	19.5	18.6	18.9	19.2	18.7	19.0	19.2	19.4	19.6	19.8	19.6
90°	34.9	34.3	33.8	33.3	32.8	32.0	31.0	29.9	28.9	27.9	24.5
92.5°	38.6	38.3	38.0	37.6	37.3	36.4	34.7	33.0	31.4	29.7	27.2
95°	44.1	44.1	44.1	44.1	44.1	43.2	41.4	39.6	37.8	36.0	33.2
97.5°	47.9	47.6	47.4	47.1	46.8	45.7	43.6	41.5	39.5	37.4	35.0
100°	48.8	48.5	48.3	48.0	47.8	46.6	44.5	42.5	40.4	38.3	35.6
102.5°	49.7	49.3	48.8	48.3	47.9	50.8	57.2	63.6	70.0	76.4	120.4
105°	51.1	50.6	50.1	49.6	49.1	71.6	117.3	163.0	208.7	254.4	277.7
107.5°	160.6	195.0	229.4	263.9	298.3	332.3	365.8	399.3	432.8	466.4	462.7
110°	319.5	356.4	393.3	430.3	467.2	489.9	498.4	506.9	515.5	524.0	521.1



TEST NUMBER: P331991

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	548.1	555.9	563.7	571.5	579.3	583.2	583.0	582.8	582.7	582.5	579.7
115°	683.1	682.1	681.1	680.0	679.0	677.2	674.6	672.0	669.5	666.9	664.6
117.5°	758.9	758.7	758.5	758.3	758.1	756.9	754.9	752.8	750.7	748.7	747.5
120°	810.9	810.9	810.9	810.9	810.9	809.9	807.8	805.8	803.7	801.6	800.9
122.5°	862.1	861.9	861.6	861.4	861.2	860.4	859.0	857.5	856.1	854.6	853.6
125°	934.1	933.6	933.1	932.5	932.0	931.5	931.0	930.5	930.0	929.4	928.4
127.5°	1003.3	1003.9	1004.4	1004.9	1005.4	1005.2	1004.4	1003.6	1002.8	1001.9	1000.7
130°	1048.0	1048.5	1049.0	1049.5	1050.0	1049.8	1048.7	1047.7	1046.7	1045.6	1044.6
132.5°	1088.8	1089.6	1090.3	1091.0	1091.7	1091.6	1090.6	1089.5	1088.5	1087.5	1086.6
135°	1151.4	1152.1	1152.9	1153.7	1154.5	1154.5	1153.7	1152.9	1152.1	1151.4	1150.3
137.5°	1210.1	1210.7	1211.2	1211.7	1212.2	1211.8	1210.6	1209.4	1208.1	1206.9	1206.3
140°	1245.5	1246.0	1246.5	1247.0	1247.5	1247.3	1246.2	1245.2	1244.2	1243.1	1242.4
142.5°	1278.0	1278.7	1279.4	1280.2	1280.9	1280.8	1280.0	1279.2	1278.4	1277.5	1276.8
145°	1327.9	1327.9	1327.9	1327.9	1327.9	1327.7	1327.2	1326.7	1326.1	1325.6	1325.1
147.5°	1365.1	1366.3	1367.5	1368.7	1369.9	1370.2	1369.7	1369.2	1368.7	1368.1	1367.6
150°	1393.0	1393.8	1394.6	1395.3	1396.1	1396.2	1395.7	1395.2	1394.7	1394.2	1393.7
152.5°	1415.3	1416.5	1417.7	1418.9	1420.1	1420.2	1419.3	1418.3	1417.4	1416.5	1416.2
155°	1446.5	1448.0	1449.6	1451.1	1452.6	1452.8	1451.5	1450.2	1448.9	1447.6	1447.4
157.5°	1472.7	1474.7	1476.7	1478.8	1480.8	1481.0	1479.4	1477.9	1476.4	1474.8	1475.1
160°	1489.4	1491.2	1493.1	1494.9	1496.7	1496.8	1495.2	1493.7	1492.2	1490.6	1490.9
162.5°	1505.2	1506.8	1508.4	1510.0	1511.6	1511.6	1509.8	1508.1	1506.3	1504.5	1504.8
165°	1524.3	1526.1	1527.9	1529.7	1531.5	1531.4	1529.3	1527.3	1525.2	1523.1	1523.4
167.5°	1538.0	1540.1	1542.1	1544.2	1546.3	1546.3	1544.2	1542.1	1540.1	1538.0	1538.0
170°	1546.4	1548.4	1550.5	1552.6	1554.6	1554.6	1552.6	1550.5	1548.4	1546.4	1546.4
172.5°	1551.0	1553.3	1555.6	1557.8	1560.1	1560.2	1558.1	1556.1	1554.0	1551.9	1551.7
175°	1558.0	1560.1	1562.1	1564.2	1566.2	1566.4	1564.6	1562.8	1561.0	1559.1	1558.9
177.5°	1560.1	1562.1	1564.2	1566.3	1568.3	1568.5	1566.9	1565.2	1563.6	1561.9	1561.7
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P331991

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1114.0	1110.7	1107.3	1101.5	1096.5	1089.3	1087.2	1084.7	1077.2	1070.5	1065.5
5°	1182.1	1169.5	1151.2	1134.5	1120.9	1102.5	1092.1	1081.1	1065.4	1051.2	1039.7
7.5°	1253.3	1228.6	1200.1	1169.3	1140.6	1113.0	1090.7	1070.8	1048.8	1028.0	1011.8
10°	1309.8	1274.2	1234.5	1191.5	1154.9	1119.3	1089.4	1063.3	1035.0	1010.4	990.0
12.5°	1374.3	1321.6	1266.7	1214.6	1171.2	1121.8	1085.7	1052.4	1020.3	990.7	967.8
15°	1450.7	1383.7	1318.7	1247.0	1181.1	1119.3	1076.4	1034.5	997.3	966.9	937.6
17.5°	1520.2	1444.3	1358.7	1271.5	1191.9	1118.7	1058.6	1011.2	964.7	927.6	898.4
20°	1559.6	1473.2	1376.3	1285.8	1197.8	1116.1	1050.2	993.6	943.4	904.1	871.1
22.5°	1593.5	1492.4	1392.2	1295.4	1197.4	1109.4	1034.7	976.5	922.0	883.6	848.5
25°	1628.7	1507.7	1407.2	1293.6	1184.2	1093.1	1009.3	943.4	888.9	843.9	807.8
27.5°	1658.8	1506.7	1387.4	1265.2	1163.5	1072.2	982.7	912.0	854.2	805.3	768.6
30°	1678.9	1508.8	1366.9	1246.0	1143.4	1049.1	962.2	891.0	830.3	780.6	746.0
32.5°	1691.5	1507.5	1348.1	1219.2	1111.5	1028.2	940.0	866.3	803.9	755.0	721.7
35°	1698.8	1498.3	1315.6	1163.8	1060.1	979.0	905.2	828.7	763.3	717.7	680.1
37.5°	1684.2	1478.9	1277.9	1110.4	996.9	917.0	854.9	789.8	727.2	677.0	644.6
40°	1661.1	1466.4	1248.6	1072.7	953.3	876.4	823.5	759.6	697.8	650.2	619.8
42.5°	1617.1	1440.8	1216.3	1030.8	908.1	831.1	782.5	729.1	670.6	625.9	595.6
45°	1509.8	1385.2	1168.0	968.0	841.3	761.7	718.8	680.1	627.2	583.7	557.5
47.5°	1360.9	1301.6	1098.0	901.7	771.6	695.0	650.4	619.2	580.6	545.5	520.4
50°	1257.5	1232.9	1050.7	856.5	725.1	650.2	607.3	579.0	551.3	516.2	493.2
52.5°	1138.1	1153.3	995.4	809.6	677.7	604.1	563.7	541.3	516.1	487.3	467.2
55°	970.1	1025.0	899.9	730.8	607.3	537.1	498.9	479.0	464.4	442.9	425.6
57.5°	812.7	882.7	796.7	649.7	538.1	477.6	440.9	419.2	409.8	398.6	385.0
60°	719.3	788.4	723.0	595.2	491.6	434.0	401.5	383.2	373.8	365.9	354.4
62.5°	636.0	705.9	650.9	540.0	445.9	392.5	364.3	346.4	339.0	334.9	325.1
65°	521.4	581.6	545.0	453.9	380.6	333.5	307.8	295.3	288.5	286.9	280.6
67.5°	424.4	470.2	443.5	376.5	318.8	278.1	256.3	245.6	240.4	239.9	235.2
70°	360.7	403.6	383.2	322.5	272.8	240.8	222.0	212.5	209.4	208.9	206.3
72.5°	311.3	341.2	325.0	274.3	235.9	206.9	193.1	183.2	179.7	180.4	178.6
75°	230.3	252.9	243.4	208.4	177.5	158.6	147.1	140.8	137.7	139.3	137.2
77.5°	165.7	180.0	171.5	147.2	128.2	114.5	106.1	102.2	99.4	99.3	98.3
80°	125.1	133.5	128.8	114.1	98.4	86.9	80.1	77.5	75.9	75.4	74.9
82.5°	89.1	96.2	90.7	80.6	69.9	63.0	59.2	55.7	54.6	54.9	54.3
85°	45.0	47.6	45.5	39.3	35.1	31.9	29.8	28.3	27.2	27.7	26.7
87.5°	19.7	19.5	17.6	15.3	13.9	12.2	11.6	10.3	10.0	10.5	10.6
90°	21.2	17.8	14.5	11.5	8.9	6.3	3.7	1.2	3.7	6.3	8.9
92.5°	24.7	22.2	19.6	18.7	19.4	20.2	20.9	21.6	20.9	20.2	19.4
95°	30.3	27.5	24.7	28.5	39.1	49.7	60.3	70.9	60.3	49.7	39.1
97.5°	74.6	93.2	111.8	123.4	128.2	132.9	137.7	142.4	137.7	132.9	128.2
100°	118.9	159.2	199.4	217.0	211.8	206.7	201.5	196.3	201.5	206.7	211.8
102.5°	164.4	208.4	252.4	272.6	268.8	265.1	261.4	257.7	261.4	265.1	268.8
105°	300.9	324.1	347.4	357.6	354.7	351.9	349.1	346.2	349.1	351.9	354.7
107.5°	459.0	455.4	451.7	448.7	446.4	444.2	441.9	439.6	441.9	444.2	446.4
110°	518.3	515.5	512.6	510.2	508.1	506.0	504.0	501.9	504.0	506.0	508.1



TEST NUMBER: P331991

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	576.9	574.0	571.2	568.8	567.0	565.1	563.2	561.4	563.2	565.1	567.0
115°	662.2	659.9	657.6	655.6	654.1	652.5	651.0	649.5	651.0	652.5	654.1
117.5°	746.3	745.1	743.9	742.4	740.5	738.5	736.6	734.7	736.6	738.5	740.5
120°	800.1	799.3	798.6	797.0	794.7	792.4	790.0	787.7	790.0	792.4	794.7
122.5°	852.7	851.7	850.7	849.3	847.3	845.4	843.5	841.6	843.5	845.4	847.3
125°	927.4	926.3	925.3	923.8	921.7	919.6	917.6	915.5	917.6	919.6	921.7
127.5°	999.5	998.2	997.0	995.3	993.3	991.2	989.1	987.1	989.1	991.2	993.3
130°	1043.6	1042.5	1041.5	1039.9	1037.9	1035.8	1033.8	1031.7	1033.8	1035.8	1037.9
132.5°	1085.8	1085.0	1084.1	1082.7	1080.6	1078.6	1076.5	1074.4	1076.5	1078.6	1080.6
135°	1149.3	1148.3	1147.2	1145.9	1144.4	1142.8	1141.3	1139.7	1141.3	1142.8	1144.4
137.5°	1205.8	1205.2	1204.6	1203.4	1201.4	1199.4	1197.5	1195.5	1197.5	1199.4	1201.4
140°	1241.6	1240.8	1240.0	1238.9	1237.3	1235.8	1234.2	1232.7	1234.2	1235.8	1237.3
142.5°	1276.0	1275.2	1274.4	1273.3	1271.7	1270.2	1268.6	1267.1	1268.6	1270.2	1271.7
145°	1324.6	1324.1	1323.6	1322.4	1320.6	1318.8	1317.0	1315.2	1317.0	1318.8	1320.6
147.5°	1367.1	1366.6	1366.1	1365.2	1364.0	1362.9	1361.7	1360.5	1361.7	1362.9	1364.0
150°	1393.1	1392.6	1392.1	1391.5	1390.7	1389.9	1389.1	1388.4	1389.1	1389.9	1390.7
152.5°	1415.9	1415.5	1415.2	1414.9	1414.5	1414.2	1413.8	1413.5	1413.8	1414.2	1414.5
155°	1447.1	1446.8	1446.6	1446.7	1447.2	1447.7	1448.3	1448.8	1448.3	1447.7	1447.2
157.5°	1475.3	1475.6	1475.8	1476.0	1476.0	1476.1	1476.1	1476.2	1476.1	1476.1	1476.0
160°	1491.1	1491.4	1491.6	1491.9	1492.2	1492.4	1492.7	1492.9	1492.7	1492.4	1492.2
162.5°	1505.1	1505.3	1505.6	1506.0	1506.7	1507.4	1508.1	1508.7	1508.1	1507.4	1506.7
165°	1523.6	1523.9	1524.2	1524.7	1525.5	1526.2	1527.0	1527.8	1527.0	1526.2	1525.5
167.5°	1538.0	1538.0	1538.0	1538.5	1539.6	1540.6	1541.6	1542.7	1541.6	1540.6	1539.6
170°	1546.4	1546.4	1546.4	1546.9	1547.9	1549.0	1550.0	1551.0	1550.0	1549.0	1547.9
172.5°	1551.5	1551.3	1551.1	1551.6	1552.9	1554.1	1555.4	1556.6	1555.4	1554.1	1552.9
175°	1558.6	1558.4	1558.1	1558.6	1559.9	1561.2	1562.5	1563.8	1562.5	1561.2	1559.9
177.5°	1561.5	1561.3	1561.1	1561.5	1562.6	1563.6	1564.6	1565.7	1564.6	1563.6	1562.6
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P331991

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1062.5	1059.6	1055.4	1049.1	1044.1	1036.1	1036.1	1037.4	1037.4	1037.0	1036.1
5°	1030.3	1022.4	1013.0	1002.0	990.5	979.0	976.9	972.7	969.6	967.5	964.8
7.5°	996.3	982.3	968.6	953.2	939.2	927.6	919.5	912.8	908.5	903.9	900.6
10°	973.2	955.9	939.7	923.5	905.7	891.6	882.7	876.4	871.7	867.5	865.4
12.5°	946.0	926.2	908.3	892.9	873.4	858.9	850.4	847.5	841.9	833.1	828.5
15°	906.2	887.9	866.4	842.9	833.4	815.6	805.7	801.0	797.8	791.0	788.9
17.5°	872.2	848.2	824.1	806.5	789.0	774.6	769.0	763.2	759.0	753.4	751.8
20°	845.0	823.5	801.5	782.7	764.3	748.6	743.9	739.7	735.5	732.9	730.8
22.5°	817.3	795.9	777.6	760.0	740.5	730.2	725.1	720.5	717.5	715.8	713.7
25°	778.5	759.6	739.2	723.5	707.8	701.0	697.8	695.2	693.1	690.5	690.0
27.5°	743.7	723.2	706.6	692.0	680.7	675.0	672.0	670.7	671.2	672.1	672.7
30°	717.7	698.9	685.3	672.7	662.3	657.0	656.5	656.5	658.6	659.1	660.2
32.5°	693.9	678.4	664.8	652.6	644.7	641.1	643.1	643.1	644.8	646.1	648.0
35°	659.1	645.5	635.0	624.6	617.8	619.3	620.4	621.4	624.0	627.2	629.3
37.5°	625.9	614.1	603.2	595.0	591.9	594.7	597.2	599.4	602.5	604.9	607.0
40°	602.0	593.1	582.7	575.3	576.4	578.0	580.1	582.7	585.3	586.9	589.0
42.5°	579.8	570.5	562.6	556.5	558.0	560.0	561.2	562.6	565.6	568.4	569.7
45°	546.0	538.7	531.4	527.7	528.8	529.8	530.8	532.4	535.0	537.1	537.7
47.5°	508.0	502.9	498.0	494.4	496.1	495.7	497.0	500.4	501.2	502.5	505.4
50°	483.7	479.0	473.3	472.2	472.2	472.2	472.7	476.9	476.9	479.0	481.1
52.5°	456.9	453.9	450.2	448.3	447.5	447.5	449.7	451.8	452.6	455.6	457.7
55°	417.2	414.1	411.0	409.4	408.3	409.4	413.6	414.6	417.2	418.8	420.4
57.5°	375.9	373.5	371.0	370.1	369.9	371.3	373.6	376.7	377.4	382.2	384.6
60°	348.7	345.0	342.9	342.9	341.9	346.6	345.5	350.8	351.8	354.9	358.6
62.5°	320.6	315.7	314.8	314.8	316.3	317.7	319.1	321.4	324.2	328.1	331.0
65°	275.4	272.8	276.4	275.9	274.8	278.0	278.0	280.6	283.7	287.4	293.2
67.5°	232.5	231.2	231.5	231.5	233.1	234.9	236.3	238.6	242.4	246.3	250.0
70°	203.6	205.2	202.6	204.7	206.3	206.8	207.8	211.0	215.2	217.8	222.0
72.5°	175.6	175.5	175.8	176.6	178.2	179.1	180.2	183.8	188.4	190.6	193.9
75°	135.1	134.5	136.1	136.1	138.7	139.8	140.8	142.4	146.6	149.7	152.3
77.5°	98.6	99.3	98.9	100.7	100.0	100.2	103.4	105.0	105.4	111.6	113.0
80°	74.3	75.4	75.9	76.4	77.0	75.9	79.6	81.1	81.1	84.8	87.4
82.5°	53.4	54.0	55.4	55.9	56.0	57.1	57.4	58.5	59.8	61.4	64.8
85°	26.7	28.3	28.8	28.3	28.8	27.7	29.3	29.8	30.4	30.4	30.4
87.5°	10.7	11.7	11.9	13.0	13.3	14.4	14.6	13.9	14.2	15.6	14.1
90°	11.5	14.5	17.8	21.2	24.5	27.9	28.9	29.9	31.0	32.0	32.8
92.5°	18.7	19.6	22.2	24.7	27.2	29.7	31.4	33.0	34.7	36.4	37.3
95°	28.5	24.7	27.5	30.3	33.2	36.0	37.8	39.6	41.4	43.2	44.1
97.5°	123.4	111.8	93.2	74.6	56.0	37.4	39.5	41.5	43.6	45.7	46.8
100°	217.0	199.4	159.2	118.9	78.6	38.3	40.4	42.5	44.5	46.6	47.8
102.5°	272.6	252.4	208.4	164.4	120.4	76.4	70.0	63.6	57.2	50.8	47.9
105°	357.6	347.4	324.1	300.9	277.7	254.4	208.7	163.0	117.3	71.6	49.1
107.5°	448.7	451.7	455.4	459.0	462.7	466.4	432.8	399.3	365.8	332.3	298.3
110°	510.2	512.6	515.5	518.3	521.1	524.0	515.5	506.9	498.4	489.9	467.2



TEST NUMBER: P331991

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	568.8	571.2	574.0	576.9	579.7	582.5	582.7	582.8	583.0	583.2	579.3
115°	655.6	657.6	659.9	662.2	664.6	666.9	669.5	672.0	674.6	677.2	679.0
117.5°	742.4	743.9	745.1	746.3	747.5	748.7	750.7	752.8	754.9	756.9	758.1
120°	797.0	798.6	799.3	800.1	800.9	801.6	803.7	805.8	807.8	809.9	810.9
122.5°	849.3	850.7	851.7	852.7	853.6	854.6	856.1	857.5	859.0	860.4	861.2
125°	923.8	925.3	926.3	927.4	928.4	929.4	930.0	930.5	931.0	931.5	932.0
127.5°	995.3	997.0	998.2	999.5	1000.7	1001.9	1002.8	1003.6	1004.4	1005.2	1005.4
130°	1039.9	1041.5	1042.5	1043.6	1044.6	1045.6	1046.7	1047.7	1048.7	1049.8	1050.0
132.5°	1082.7	1084.1	1085.0	1085.8	1086.6	1087.5	1088.5	1089.5	1090.6	1091.6	1091.7
135°	1145.9	1147.2	1148.3	1149.3	1150.3	1151.4	1152.1	1152.9	1153.7	1154.5	1154.5
137.5°	1203.4	1204.6	1205.2	1205.8	1206.3	1206.9	1208.1	1209.4	1210.6	1211.8	1212.2
140°	1238.9	1240.0	1240.8	1241.6	1242.4	1243.1	1244.2	1245.2	1246.2	1247.3	1247.5
142.5°	1273.3	1274.4	1275.2	1276.0	1276.8	1277.5	1278.4	1279.2	1280.0	1280.8	1280.9
145°	1322.4	1323.6	1324.1	1324.6	1325.1	1325.6	1326.1	1326.7	1327.2	1327.7	1327.9
147.5°	1365.2	1366.1	1366.6	1367.1	1367.6	1368.1	1368.7	1369.2	1369.7	1370.2	1369.9
150°	1391.5	1392.1	1392.6	1393.1	1393.7	1394.2	1394.7	1395.2	1395.7	1396.2	1396.1
152.5°	1414.9	1415.2	1415.5	1415.9	1416.2	1416.5	1417.4	1418.3	1419.3	1420.2	1420.1
155°	1446.7	1446.6	1446.8	1447.1	1447.4	1447.6	1448.9	1450.2	1451.5	1452.8	1452.6
157.5°	1476.0	1475.8	1475.6	1475.3	1475.1	1474.8	1476.4	1477.9	1479.4	1481.0	1480.8
160°	1491.9	1491.6	1491.4	1491.1	1490.9	1490.6	1492.2	1493.7	1495.2	1496.8	1496.7
162.5°	1506.0	1505.6	1505.3	1505.1	1504.8	1504.5	1506.3	1508.1	1509.8	1511.6	1511.6
165°	1524.7	1524.2	1523.9	1523.6	1523.4	1523.1	1525.2	1527.3	1529.3	1531.4	1531.5
167.5°	1538.5	1538.0	1538.0	1538.0	1538.0	1538.0	1540.1	1542.1	1544.2	1546.3	1546.3
170°	1546.9	1546.4	1546.4	1546.4	1546.4	1546.4	1548.4	1550.5	1552.6	1554.6	1554.6
172.5°	1551.6	1551.1	1551.3	1551.5	1551.7	1551.9	1554.0	1556.1	1558.1	1560.2	1560.1
175°	1558.6	1558.1	1558.4	1558.6	1558.9	1559.1	1561.0	1562.8	1564.6	1566.4	1566.2
177.5°	1561.5	1561.1	1561.3	1561.5	1561.7	1561.9	1563.6	1565.2	1566.9	1568.5	1568.3
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P331991

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1033.2	1032.8	1035.7	1033.6	1035.7	1032.8	1033.2	1036.1	1037.0	1037.4	1037.4
5°	961.7	963.3	958.0	958.0	958.0	963.3	961.7	964.8	967.5	969.6	972.7
7.5°	898.0	895.7	895.9	893.1	895.9	895.7	898.0	900.6	903.9	908.5	912.8
10°	859.1	856.0	854.9	855.4	854.9	856.0	859.1	865.4	867.5	871.7	876.4
12.5°	826.8	826.2	819.3	819.4	819.3	826.2	826.8	828.5	833.1	841.9	847.5
15°	788.9	779.0	777.9	781.1	777.9	779.0	788.9	788.9	791.0	797.8	801.0
17.5°	750.9	745.7	746.0	744.4	746.0	745.7	750.9	751.8	753.4	759.0	763.2
20°	730.8	727.7	727.2	723.5	727.2	727.7	730.8	730.8	732.9	735.5	739.7
22.5°	712.4	711.4	711.7	707.6	711.7	711.4	712.4	713.7	715.8	717.5	720.5
25°	689.5	692.1	690.0	690.0	690.0	692.1	689.5	690.0	690.5	693.1	695.2
27.5°	674.0	673.9	672.8	672.8	672.8	673.9	674.0	672.7	672.1	671.2	670.7
30°	662.3	661.7	662.8	662.8	662.8	661.7	662.3	660.2	659.1	658.6	656.5
32.5°	650.5	651.3	651.5	651.9	651.5	651.3	650.5	648.0	646.1	644.8	643.1
35°	632.4	632.9	634.5	633.5	634.5	632.9	632.4	629.3	627.2	624.0	621.4
37.5°	607.9	610.3	609.8	610.6	609.8	610.3	607.9	607.0	604.9	602.5	599.4
40°	589.5	591.1	590.5	590.5	590.5	591.1	589.5	589.0	586.9	585.3	582.7
42.5°	570.6	571.8	570.4	569.6	570.4	571.8	570.6	569.7	568.4	565.6	562.6
45°	539.7	538.7	540.3	538.2	540.3	538.7	539.7	537.7	537.1	535.0	532.4
47.5°	505.2	506.2	506.7	508.2	506.7	506.2	505.2	505.4	502.5	501.2	500.4
50°	482.2	485.3	485.3	484.8	485.3	485.3	482.2	481.1	479.0	476.9	476.9
52.5°	459.5	461.0	463.1	463.0	463.1	461.0	459.5	457.7	455.6	452.6	451.8
55°	424.6	425.6	426.7	427.2	426.7	425.6	424.6	420.4	418.8	417.2	414.6
57.5°	388.3	387.9	390.4	391.2	390.4	387.9	388.3	384.6	382.2	377.4	376.7
60°	362.8	362.8	367.0	368.6	367.0	362.8	362.8	358.6	354.9	351.8	350.8
62.5°	335.6	337.3	341.4	339.2	341.4	337.3	335.6	331.0	328.1	324.2	321.4
65°	295.8	300.0	299.5	301.5	299.5	300.0	295.8	293.2	287.4	283.7	280.6
67.5°	254.2	256.8	260.6	260.9	260.6	256.8	254.2	250.0	246.3	242.4	238.6
70°	226.2	228.8	230.9	232.4	230.9	228.8	226.2	222.0	217.8	215.2	211.0
72.5°	198.9	200.3	205.3	203.1	205.3	200.3	198.9	193.9	190.6	188.4	183.8
75°	156.0	159.7	162.8	161.2	162.8	159.7	156.0	152.3	149.7	146.6	142.4
77.5°	115.4	119.0	120.5	119.2	120.5	119.0	115.4	113.0	111.6	105.4	105.0
80°	91.1	90.6	93.7	93.2	93.7	90.6	91.1	87.4	84.8	81.1	81.1
82.5°	66.8	66.3	67.7	68.1	67.7	66.3	66.8	64.8	61.4	59.8	58.5
85°	32.5	34.0	31.9	31.4	31.9	34.0	32.5	30.4	30.4	30.4	29.8
87.5°	14.2	14.3	14.0	13.7	14.0	14.3	14.2	14.1	15.6	14.2	13.9
90°	33.3	33.8	34.3	34.9	34.3	33.8	33.3	32.8	32.0	31.0	29.9
92.5°	37.6	38.0	38.3	38.6	38.3	38.0	37.6	37.3	36.4	34.7	33.0
95°	44.1	44.1	44.1	44.1	44.1	44.1	44.1	44.1	43.2	41.4	39.6
97.5°	47.1	47.4	47.6	47.9	47.6	47.4	47.1	46.8	45.7	43.6	41.5
100°	48.0	48.3	48.5	48.8	48.5	48.3	48.0	47.8	46.6	44.5	42.5
102.5°	48.3	48.8	49.3	49.7	49.3	48.8	48.3	47.9	50.8	57.2	63.6
105°	49.6	50.1	50.6	51.1	50.6	50.1	49.6	49.1	71.6	117.3	163.0
107.5°	263.9	229.4	195.0	160.6	195.0	229.4	263.9	298.3	332.3	365.8	399.3
110°	430.3	393.3	356.4	319.5	356.4	393.3	430.3	467.2	489.9	498.4	506.9



TEST NUMBER: P331991

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	571.5	563.7	555.9	548.1	555.9	563.7	571.5	579.3	583.2	583.0	582.8
115°	680.0	681.1	682.1	683.1	682.1	681.1	680.0	679.0	677.2	674.6	672.0
117.5°	758.3	758.5	758.7	758.9	758.7	758.5	758.3	758.1	756.9	754.9	752.8
120°	810.9	810.9	810.9	810.9	810.9	810.9	810.9	810.9	809.9	807.8	805.8
122.5°	861.4	861.6	861.9	862.1	861.9	861.6	861.4	861.2	860.4	859.0	857.5
125°	932.5	933.1	933.6	934.1	933.6	933.1	932.5	932.0	931.5	931.0	930.5
127.5°	1004.9	1004.4	1003.9	1003.3	1003.9	1004.4	1004.9	1005.4	1005.2	1004.4	1003.6
130°	1049.5	1049.0	1048.5	1048.0	1048.5	1049.0	1049.5	1050.0	1049.8	1048.7	1047.7
132.5°	1091.0	1090.3	1089.6	1088.8	1089.6	1090.3	1091.0	1091.7	1091.6	1090.6	1089.5
135°	1153.7	1152.9	1152.1	1151.4	1152.1	1152.9	1153.7	1154.5	1154.5	1153.7	1152.9
137.5°	1211.7	1211.2	1210.7	1210.1	1210.7	1211.2	1211.7	1212.2	1211.8	1210.6	1209.4
140°	1247.0	1246.5	1246.0	1245.5	1246.0	1246.5	1247.0	1247.5	1247.3	1246.2	1245.2
142.5°	1280.2	1279.4	1278.7	1278.0	1278.7	1279.4	1280.2	1280.9	1280.8	1280.0	1279.2
145°	1327.9	1327.9	1327.9	1327.9	1327.9	1327.9	1327.9	1327.9	1327.7	1327.2	1326.7
147.5°	1368.7	1367.5	1366.3	1365.1	1366.3	1367.5	1368.7	1369.9	1370.2	1369.7	1369.2
150°	1395.3	1394.6	1393.8	1393.0	1393.8	1394.6	1395.3	1396.1	1396.2	1395.7	1395.2
152.5°	1418.9	1417.7	1416.5	1415.3	1416.5	1417.7	1418.9	1420.1	1420.2	1419.3	1418.3
155°	1451.1	1449.6	1448.0	1446.5	1448.0	1449.6	1451.1	1452.6	1452.8	1451.5	1450.2
157.5°	1478.8	1476.7	1474.7	1472.7	1474.7	1476.7	1478.8	1480.8	1481.0	1479.4	1477.9
160°	1494.9	1493.1	1491.2	1489.4	1491.2	1493.1	1494.9	1496.7	1496.8	1495.2	1493.7
162.5°	1510.0	1508.4	1506.8	1505.2	1506.8	1508.4	1510.0	1511.6	1511.6	1509.8	1508.1
165°	1529.7	1527.9	1526.1	1524.3	1526.1	1527.9	1529.7	1531.5	1531.4	1529.3	1527.3
167.5°	1544.2	1542.1	1540.1	1538.0	1540.1	1542.1	1544.2	1546.3	1546.3	1544.2	1542.1
170°	1552.6	1550.5	1548.4	1546.4	1548.4	1550.5	1552.6	1554.6	1554.6	1552.6	1550.5
172.5°	1557.8	1555.6	1553.3	1551.0	1553.3	1555.6	1557.8	1560.1	1560.2	1558.1	1556.1
175°	1564.2	1562.1	1560.1	1558.0	1560.1	1562.1	1564.2	1566.2	1566.4	1564.6	1562.8
177.5°	1566.3	1564.2	1562.1	1560.1	1562.1	1564.2	1566.3	1568.3	1568.5	1566.9	1565.2
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P331991

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1036.1	1036.1	1044.1	1049.1	1055.4	1059.6	1062.5	1065.5	1070.5	1077.2	1084.7
5°	976.9	979.0	990.5	1002.0	1013.0	1022.4	1030.3	1039.7	1051.2	1065.4	1081.1
7.5°	919.5	927.6	939.2	953.2	968.6	982.3	996.3	1011.8	1028.0	1048.8	1070.8
10°	882.7	891.6	905.7	923.5	939.7	955.9	973.2	990.0	1010.4	1035.0	1063.3
12.5°	850.4	858.9	873.4	892.9	908.3	926.2	946.0	967.8	990.7	1020.3	1052.4
15°	805.7	815.6	833.4	842.9	866.4	887.9	906.2	937.6	966.9	997.3	1034.5
17.5°	769.0	774.6	789.0	806.5	824.1	848.2	872.2	898.4	927.6	964.7	1011.2
20°	743.9	748.6	764.3	782.7	801.5	823.5	845.0	871.1	904.1	943.4	993.6
22.5°	725.1	730.2	740.5	760.0	777.6	795.9	817.3	848.5	883.6	922.0	976.5
25°	697.8	701.0	707.8	723.5	739.2	759.6	778.5	807.8	843.9	888.9	943.4
27.5°	672.0	675.0	680.7	692.0	706.6	723.2	743.7	768.6	805.3	854.2	912.0
30°	656.5	657.0	662.3	672.7	685.3	698.9	717.7	746.0	780.6	830.3	891.0
32.5°	643.1	641.1	644.7	652.6	664.8	678.4	693.9	721.7	755.0	803.9	866.3
35°	620.4	619.3	617.8	624.6	635.0	645.5	659.1	680.1	717.7	763.3	828.7
37.5°	597.2	594.7	591.9	595.0	603.2	614.1	625.9	644.6	677.0	727.2	789.8
40°	580.1	578.0	576.4	575.3	582.7	593.1	602.0	619.8	650.2	697.8	759.6
42.5°	561.2	560.0	558.0	556.5	562.6	570.5	579.8	595.6	625.9	670.6	729.1
45°	530.8	529.8	528.8	527.7	531.4	538.7	546.0	557.5	583.7	627.2	680.1
47.5°	497.0	495.7	496.1	494.4	498.0	502.9	508.0	520.4	545.5	580.6	619.2
50°	472.7	472.2	472.2	472.2	473.3	479.0	483.7	493.2	516.2	551.3	579.0
52.5°	449.7	447.5	447.5	448.3	450.2	453.9	456.9	467.2	487.3	516.1	541.3
55°	413.6	409.4	408.3	409.4	411.0	414.1	417.2	425.6	442.9	464.4	479.0
57.5°	373.6	371.3	369.9	370.1	371.0	373.5	375.9	385.0	398.6	409.8	419.2
60°	345.5	346.6	341.9	342.9	342.9	345.0	348.7	354.4	365.9	373.8	383.2
62.5°	319.1	317.7	316.3	314.8	314.8	315.7	320.6	325.1	334.9	339.0	346.4
65°	278.0	278.0	274.8	275.9	276.4	272.8	275.4	280.6	286.9	288.5	295.3
67.5°	236.3	234.9	233.1	231.5	231.5	231.2	232.5	235.2	239.9	240.4	245.6
70°	207.8	206.8	206.3	204.7	202.6	205.2	203.6	206.3	208.9	209.4	212.5
72.5°	180.2	179.1	178.2	176.6	175.8	175.5	175.6	178.6	180.4	179.7	183.2
75°	140.8	139.8	138.7	136.1	136.1	134.5	135.1	137.2	139.3	137.7	140.8
77.5°	103.4	100.2	100.0	100.7	98.9	99.3	98.6	98.3	99.3	99.4	102.2
80°	79.6	75.9	77.0	76.4	75.9	75.4	74.3	74.9	75.4	75.9	77.5
82.5°	57.4	57.1	56.0	55.9	55.4	54.0	53.4	54.3	54.9	54.6	55.7
85°	29.3	27.7	28.8	28.3	28.8	28.3	26.7	26.7	27.7	27.2	28.3
87.5°	14.6	14.4	13.3	13.0	11.9	11.7	10.7	10.6	10.5	10.0	10.3
90°	28.9	27.9	24.5	21.2	17.8	14.5	11.5	8.9	6.3	3.7	1.2
92.5°	31.4	29.7	27.2	24.7	22.2	19.6	18.7	19.4	20.2	20.9	21.6
95°	37.8	36.0	33.2	30.3	27.5	24.7	28.5	39.1	49.7	60.3	70.9
97.5°	39.5	37.4	56.0	74.6	93.2	111.8	123.4	128.2	132.9	137.7	142.4
100°	40.4	38.3	78.6	118.9	159.2	199.4	217.0	211.8	206.7	201.5	196.3
102.5°	70.0	76.4	120.4	164.4	208.4	252.4	272.6	268.8	265.1	261.4	257.7
105°	208.7	254.4	277.7	300.9	324.1	347.4	357.6	354.7	351.9	349.1	346.2
107.5°	432.8	466.4	462.7	459.0	455.4	451.7	448.7	446.4	444.2	441.9	439.6
110°	515.5	524.0	521.1	518.3	515.5	512.6	510.2	508.1	506.0	504.0	501.9



TEST NUMBER: P331991

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	582.7	582.5	579.7	576.9	574.0	571.2	568.8	567.0	565.1	563.2	561.4
115°	669.5	666.9	664.6	662.2	659.9	657.6	655.6	654.1	652.5	651.0	649.5
117.5°	750.7	748.7	747.5	746.3	745.1	743.9	742.4	740.5	738.5	736.6	734.7
120°	803.7	801.6	800.9	800.1	799.3	798.6	797.0	794.7	792.4	790.0	787.7
122.5°	856.1	854.6	853.6	852.7	851.7	850.7	849.3	847.3	845.4	843.5	841.6
125°	930.0	929.4	928.4	927.4	926.3	925.3	923.8	921.7	919.6	917.6	915.5
127.5°	1002.8	1001.9	1000.7	999.5	998.2	997.0	995.3	993.3	991.2	989.1	987.1
130°	1046.7	1045.6	1044.6	1043.6	1042.5	1041.5	1039.9	1037.9	1035.8	1033.8	1031.7
132.5°	1088.5	1087.5	1086.6	1085.8	1085.0	1084.1	1082.7	1080.6	1078.6	1076.5	1074.4
135°	1152.1	1151.4	1150.3	1149.3	1148.3	1147.2	1145.9	1144.4	1142.8	1141.3	1139.7
137.5°	1208.1	1206.9	1206.3	1205.8	1205.2	1204.6	1203.4	1201.4	1199.4	1197.5	1195.5
140°	1244.2	1243.1	1242.4	1241.6	1240.8	1240.0	1238.9	1237.3	1235.8	1234.2	1232.7
142.5°	1278.4	1277.5	1276.8	1276.0	1275.2	1274.4	1273.3	1271.7	1270.2	1268.6	1267.1
145°	1326.1	1325.6	1325.1	1324.6	1324.1	1323.6	1322.4	1320.6	1318.8	1317.0	1315.2
147.5°	1368.7	1368.1	1367.6	1367.1	1366.6	1366.1	1365.2	1364.0	1362.9	1361.7	1360.5
150°	1394.7	1394.2	1393.7	1393.1	1392.6	1392.1	1391.5	1390.7	1389.9	1389.1	1388.4
152.5°	1417.4	1416.5	1416.2	1415.9	1415.5	1415.2	1414.9	1414.5	1414.2	1413.8	1413.5
155°	1448.9	1447.6	1447.4	1447.1	1446.8	1446.6	1446.7	1447.2	1447.7	1448.3	1448.8
157.5°	1476.4	1474.8	1475.1	1475.3	1475.6	1475.8	1476.0	1476.0	1476.1	1476.1	1476.2
160°	1492.2	1490.6	1490.9	1491.1	1491.4	1491.6	1491.9	1492.2	1492.4	1492.7	1492.9
162.5°	1506.3	1504.5	1504.8	1505.1	1505.3	1505.6	1506.0	1506.7	1507.4	1508.1	1508.7
165°	1525.2	1523.1	1523.4	1523.6	1523.9	1524.2	1524.7	1525.5	1526.2	1527.0	1527.8
167.5°	1540.1	1538.0	1538.0	1538.0	1538.0	1538.0	1538.5	1539.6	1540.6	1541.6	1542.7
170°	1548.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.9	1547.9	1549.0	1550.0	1551.0
172.5°	1554.0	1551.9	1551.7	1551.5	1551.3	1551.1	1551.6	1552.9	1554.1	1555.4	1556.6
175°	1561.0	1559.1	1558.9	1558.6	1558.4	1558.1	1558.6	1559.9	1561.2	1562.5	1563.8
177.5°	1563.6	1561.9	1561.7	1561.5	1561.3	1561.1	1561.5	1562.6	1563.6	1564.6	1565.7
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P331991

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1087.2	1089.3	1096.5	1101.5	1107.3	1110.7	1114.0	1116.6	1119.9	1120.7	1132.9
5°	1092.1	1102.5	1120.9	1134.5	1151.2	1169.5	1182.1	1187.9	1203.0	1215.6	1240.7
7.5°	1090.7	1113.0	1140.6	1169.3	1200.1	1228.6	1253.3	1282.6	1303.5	1334.8	1365.6
10°	1089.4	1119.3	1154.9	1191.5	1234.5	1274.2	1309.8	1349.6	1382.6	1426.1	1463.2
12.5°	1085.7	1121.8	1171.2	1214.6	1266.7	1321.6	1374.3	1425.4	1454.6	1527.0	1561.2
15°	1076.4	1119.3	1181.1	1247.0	1318.7	1383.7	1450.7	1504.1	1590.4	1653.8	1694.1
17.5°	1058.6	1118.7	1191.9	1271.5	1358.7	1444.3	1520.2	1601.2	1692.8	1769.5	1851.2
20°	1050.2	1116.1	1197.8	1285.8	1376.3	1473.2	1559.6	1656.9	1756.9	1832.3	1937.0
22.5°	1034.7	1109.4	1197.4	1295.4	1392.2	1492.4	1593.5	1691.7	1807.2	1911.1	2010.7
25°	1009.3	1093.1	1184.2	1293.6	1407.2	1507.7	1628.7	1759.0	1879.4	2012.9	2112.4
27.5°	982.7	1072.2	1163.5	1265.2	1387.4	1506.7	1658.8	1806.1	1953.4	2068.6	2142.2
30°	962.2	1049.1	1143.4	1246.0	1366.9	1508.8	1678.9	1839.6	1983.1	2082.0	2123.4
32.5°	940.0	1028.2	1111.5	1219.2	1348.1	1507.5	1691.5	1859.3	1984.8	2050.6	2042.6
35°	905.2	979.0	1060.1	1163.8	1315.6	1498.3	1698.8	1861.1	1938.1	1923.9	1817.1
37.5°	854.9	917.0	996.9	1110.4	1277.9	1478.9	1684.2	1805.9	1800.9	1685.8	1531.1
40°	823.5	876.4	953.3	1072.7	1248.6	1466.4	1661.1	1740.2	1673.2	1512.4	1327.1
42.5°	782.5	831.1	908.1	1030.8	1216.3	1440.8	1617.1	1640.1	1509.0	1324.0	1154.1
45°	718.8	761.7	841.3	968.0	1168.0	1385.2	1509.8	1453.8	1277.4	1086.3	957.0
47.5°	650.4	695.0	771.6	901.7	1098.0	1301.6	1360.9	1241.8	1060.6	905.7	787.0
50°	607.3	650.2	725.1	856.5	1050.7	1232.9	1257.5	1103.6	937.1	801.0	703.6
52.5°	563.7	604.1	677.7	809.6	995.4	1153.3	1138.1	981.3	828.2	712.2	635.8
55°	498.9	537.1	607.3	730.8	899.9	1025.0	970.1	820.4	693.7	603.6	545.5
57.5°	440.9	477.6	538.1	649.7	796.7	882.7	812.7	686.5	585.8	516.5	473.2
60°	401.5	434.0	491.6	595.2	723.0	788.4	719.3	607.8	523.0	467.5	428.8
62.5°	364.3	392.5	445.9	540.0	650.9	705.9	636.0	541.6	469.4	420.2	387.3
65°	307.8	333.5	380.6	453.9	545.0	581.6	521.4	445.0	389.0	352.3	330.3
67.5°	256.3	278.1	318.8	376.5	443.5	470.2	424.4	365.2	323.0	293.6	276.1
70°	222.0	240.8	272.8	322.5	383.2	403.6	360.7	312.0	281.1	257.6	241.3
72.5°	193.1	206.9	235.9	274.3	325.0	341.2	311.3	268.5	239.7	222.0	209.1
75°	147.1	158.6	177.5	208.4	243.4	252.9	230.3	203.6	184.3	171.7	161.8
77.5°	106.1	114.5	128.2	147.2	171.5	180.0	165.7	147.9	133.8	125.3	119.8
80°	80.1	86.9	98.4	114.1	128.8	133.5	125.1	111.5	101.6	96.9	92.1
82.5°	59.2	63.0	69.9	80.6	90.7	96.2	89.1	80.9	75.6	71.3	69.5
85°	29.8	31.9	35.1	39.3	45.5	47.6	45.0	42.9	39.8	37.2	37.2
87.5°	11.6	12.2	13.9	15.3	17.6	19.5	19.7	19.6	19.8	19.6	19.4
90°	3.7	6.3	8.9	11.5	14.5	17.8	21.2	24.5	27.9	28.9	29.9
92.5°	20.9	20.2	19.4	18.7	19.6	22.2	24.7	27.2	29.7	31.4	33.0
95°	60.3	49.7	39.1	28.5	24.7	27.5	30.3	33.2	36.0	37.8	39.6
97.5°	137.7	132.9	128.2	123.4	111.8	93.2	74.6	56.0	37.4	39.5	41.5
100°	201.5	206.7	211.8	217.0	199.4	159.2	118.9	78.6	38.3	40.4	42.5
102.5°	261.4	265.1	268.8	272.6	252.4	208.4	164.4	120.4	76.4	70.0	63.6
105°	349.1	351.9	354.7	357.6	347.4	324.1	300.9	277.7	254.4	208.7	163.0
107.5°	441.9	444.2	446.4	448.7	451.7	455.4	459.0	462.7	466.4	432.8	399.3
110°	504.0	506.0	508.1	510.2	512.6	515.5	518.3	521.1	524.0	515.5	506.9



TEST NUMBER: P331991

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	563.2	565.1	567.0	568.8	571.2	574.0	576.9	579.7	582.5	582.7	582.8
115°	651.0	652.5	654.1	655.6	657.6	659.9	662.2	664.6	666.9	669.5	672.0
117.5°	736.6	738.5	740.5	742.4	743.9	745.1	746.3	747.5	748.7	750.7	752.8
120°	790.0	792.4	794.7	797.0	798.6	799.3	800.1	800.9	801.6	803.7	805.8
122.5°	843.5	845.4	847.3	849.3	850.7	851.7	852.7	853.6	854.6	856.1	857.5
125°	917.6	919.6	921.7	923.8	925.3	926.3	927.4	928.4	929.4	930.0	930.5
127.5°	989.1	991.2	993.3	995.3	997.0	998.2	999.5	1000.7	1001.9	1002.8	1003.6
130°	1033.8	1035.8	1037.9	1039.9	1041.5	1042.5	1043.6	1044.6	1045.6	1046.7	1047.7
132.5°	1076.5	1078.6	1080.6	1082.7	1084.1	1085.0	1085.8	1086.6	1087.5	1088.5	1089.5
135°	1141.3	1142.8	1144.4	1145.9	1147.2	1148.3	1149.3	1150.3	1151.4	1152.1	1152.9
137.5°	1197.5	1199.4	1201.4	1203.4	1204.6	1205.2	1205.8	1206.3	1206.9	1208.1	1209.4
140°	1234.2	1235.8	1237.3	1238.9	1240.0	1240.8	1241.6	1242.4	1243.1	1244.2	1245.2
142.5°	1268.6	1270.2	1271.7	1273.3	1274.4	1275.2	1276.0	1276.8	1277.5	1278.4	1279.2
145°	1317.0	1318.8	1320.6	1322.4	1323.6	1324.1	1324.6	1325.1	1325.6	1326.1	1326.7
147.5°	1361.7	1362.9	1364.0	1365.2	1366.1	1366.6	1367.1	1367.6	1368.1	1368.7	1369.2
150°	1389.1	1389.9	1390.7	1391.5	1392.1	1392.6	1393.1	1393.7	1394.2	1394.7	1395.2
152.5°	1413.8	1414.2	1414.5	1414.9	1415.2	1415.5	1415.9	1416.2	1416.5	1417.4	1418.3
155°	1448.3	1447.7	1447.2	1446.7	1446.6	1446.8	1447.1	1447.4	1447.6	1448.9	1450.2
157.5°	1476.1	1476.1	1476.0	1476.0	1475.8	1475.6	1475.3	1475.1	1474.8	1476.4	1477.9
160°	1492.7	1492.4	1492.2	1491.9	1491.6	1491.4	1491.1	1490.9	1490.6	1492.2	1493.7
162.5°	1508.1	1507.4	1506.7	1506.0	1505.6	1505.3	1505.1	1504.8	1504.5	1506.3	1508.1
165°	1527.0	1526.2	1525.5	1524.7	1524.2	1523.9	1523.6	1523.4	1523.1	1525.2	1527.3
167.5°	1541.6	1540.6	1539.6	1538.5	1538.0	1538.0	1538.0	1538.0	1538.0	1540.1	1542.1
170°	1550.0	1549.0	1547.9	1546.9	1546.4	1546.4	1546.4	1546.4	1546.4	1548.4	1550.5
172.5°	1555.4	1554.1	1552.9	1551.6	1551.1	1551.3	1551.5	1551.7	1551.9	1554.0	1556.1
175°	1562.5	1561.2	1559.9	1558.6	1558.1	1558.4	1558.6	1558.9	1559.1	1561.0	1562.8
177.5°	1564.6	1563.6	1562.6	1561.5	1561.1	1561.3	1561.5	1561.7	1561.9	1563.6	1565.2
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P331991

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1137.1	1137.5	1142.1	1145.5	1143.8	1145.9	1146.7
5°	1242.3	1261.2	1271.1	1278.4	1279.0	1279.5	1283.7
7.5°	1391.5	1411.7	1426.5	1448.9	1455.6	1463.2	1461.0
10°	1500.4	1530.2	1555.9	1569.5	1584.2	1605.6	1588.4
12.5°	1602.2	1655.1	1694.1	1715.3	1729.1	1733.4	1724.9
15°	1770.0	1839.1	1876.3	1875.2	1922.4	1942.8	1910.8
17.5°	1923.9	1987.7	2038.8	2065.0	2104.2	2112.9	2108.9
20°	2018.2	2087.8	2127.6	2172.6	2193.0	2211.3	2214.5
22.5°	2099.4	2161.9	2204.6	2242.1	2259.2	2267.9	2273.1
25°	2183.1	2232.3	2257.9	2271.0	2275.7	2274.7	2267.9
27.5°	2177.3	2181.1	2152.8	2125.1	2100.3	2072.3	2062.7
30°	2120.8	2076.8	1998.3	1953.8	1888.3	1836.5	1857.4
32.5°	1972.1	1884.6	1796.4	1699.1	1618.6	1595.7	1572.6
35°	1683.1	1529.2	1439.2	1334.4	1292.6	1250.7	1221.9
37.5°	1361.7	1242.6	1135.8	1067.3	1025.4	998.9	984.6
40°	1177.4	1070.1	982.1	926.6	894.7	864.9	860.7
42.5°	1030.4	930.6	864.4	820.2	789.6	776.9	767.7
45°	843.9	774.3	729.8	698.4	678.0	670.1	659.6
47.5°	714.3	665.1	631.7	610.3	594.9	589.1	588.2
50°	641.8	601.0	576.4	559.6	547.6	545.5	537.1
52.5°	587.4	552.0	532.8	518.2	509.5	503.6	501.1
55°	509.9	486.3	469.1	460.7	453.9	448.1	448.1
57.5°	446.1	426.5	415.0	407.9	405.8	401.7	399.1
60°	406.8	390.0	381.1	374.8	370.7	371.2	366.5
62.5°	368.2	357.4	348.9	342.6	337.6	337.7	338.0
65°	313.6	305.2	298.9	296.8	293.7	290.0	291.1
67.5°	265.7	257.9	253.0	249.4	248.4	246.4	249.4
70°	231.4	225.6	222.0	218.8	217.8	218.3	220.9
72.5°	200.0	195.9	193.5	192.0	189.7	189.8	191.6
75°	157.1	153.9	151.8	150.2	149.7	149.7	149.7
77.5°	115.4	114.7	113.7	111.4	111.5	112.1	112.2
80°	91.1	89.5	89.0	88.0	86.4	85.3	88.0
82.5°	68.1	66.5	66.0	65.8	63.3	63.1	65.3
85°	36.6	35.1	35.6	35.1	35.1	34.6	34.6
87.5°	19.2	19.0	18.7	19.2	18.9	18.6	19.5
90°	31.0	32.0	32.8	33.3	33.8	34.3	34.9
92.5°	34.7	36.4	37.3	37.6	38.0	38.3	38.6
95°	41.4	43.2	44.1	44.1	44.1	44.1	44.1
97.5°	43.6	45.7	46.8	47.1	47.4	47.6	47.9
100°	44.5	46.6	47.8	48.0	48.3	48.5	48.8
102.5°	57.2	50.8	47.9	48.3	48.8	49.3	49.7
105°	117.3	71.6	49.1	49.6	50.1	50.6	51.1
107.5°	365.8	332.3	298.3	263.9	229.4	195.0	160.6
110°	498.4	489.9	467.2	430.3	393.3	356.4	319.5



TEST NUMBER: P331991

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	583.0	583.2	579.3	571.5	563.7	555.9	548.1
115°	674.6	677.2	679.0	680.0	681.1	682.1	683.1
117.5°	754.9	756.9	758.1	758.3	758.5	758.7	758.9
120°	807.8	809.9	810.9	810.9	810.9	810.9	810.9
122.5°	859.0	860.4	861.2	861.4	861.6	861.9	862.1
125°	931.0	931.5	932.0	932.5	933.1	933.6	934.1
127.5°	1004.4	1005.2	1005.4	1004.9	1004.4	1003.9	1003.3
130°	1048.7	1049.8	1050.0	1049.5	1049.0	1048.5	1048.0
132.5°	1090.6	1091.6	1091.7	1091.0	1090.3	1089.6	1088.8
135°	1153.7	1154.5	1154.5	1153.7	1152.9	1152.1	1151.4
137.5°	1210.6	1211.8	1212.2	1211.7	1211.2	1210.7	1210.1
140°	1246.2	1247.3	1247.5	1247.0	1246.5	1246.0	1245.5
142.5°	1280.0	1280.8	1280.9	1280.2	1279.4	1278.7	1278.0
145°	1327.2	1327.7	1327.9	1327.9	1327.9	1327.9	1327.9
147.5°	1369.7	1370.2	1369.9	1368.7	1367.5	1366.3	1365.1
150°	1395.7	1396.2	1396.1	1395.3	1394.6	1393.8	1393.0
152.5°	1419.3	1420.2	1420.1	1418.9	1417.7	1416.5	1415.3
155°	1451.5	1452.8	1452.6	1451.1	1449.6	1448.0	1446.5
157.5°	1479.4	1481.0	1480.8	1478.8	1476.7	1474.7	1472.7
160°	1495.2	1496.8	1496.7	1494.9	1493.1	1491.2	1489.4
162.5°	1509.8	1511.6	1511.6	1510.0	1508.4	1506.8	1505.2
165°	1529.3	1531.4	1531.5	1529.7	1527.9	1526.1	1524.3
167.5°	1544.2	1546.3	1546.3	1544.2	1542.1	1540.1	1538.0
170°	1552.6	1554.6	1554.6	1552.6	1550.5	1548.4	1546.4
172.5°	1558.1	1560.2	1560.1	1557.8	1555.6	1553.3	1551.0
175°	1564.6	1566.4	1566.2	1564.2	1562.1	1560.1	1558.0
177.5°	1566.9	1568.5	1568.3	1566.3	1564.2	1562.1	1560.1
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8

(END OF REPORT)