

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331944-830

Luminaire Tested: **S123DIP-S560D1025U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331944-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S560D1025U830-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5506.9 lumens  
Efficiency: N/A  
Efficacy: 123.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 44.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331944-830

CATALOG NUMBER: S123DIP-S560D1025U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331944-830

CATALOG NUMBER: S123DIP-S560D1025U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	95	91	87	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33
2	87	80	73	68	79	73	67	63	59	56	53	47	45	43	36	35	33	28
3	79	70	63	57	72	64	58	53	52	48	44	42	39	36	32	30	28	24
4	72	62	54	48	66	56	50	44	46	41	37	37	34	31	29	26	24	20
5	66	55	47	41	60	50	43	38	42	36	32	33	30	27	26	23	21	18
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	21	18	15
7	56	44	36	31	51	41	34	29	34	29	25	27	23	20	21	19	16	14
8	52	40	33	27	47	37	30	25	31	26	22	25	21	18	20	17	15	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	34	26	22	41	31	25	20	26	21	17	21	17	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9038	9038	9038
5°	9081	8956	9018
10°	9021	8878	8933
15°	8914	8778	8795
20°	8791	8635	8643
25°	8626	8464	8445
30°	8444	8274	8211
35°	8253	8073	7970
40°	8056	7852	7731
45°	7837	7649	7462
50°	7618	7400	7194
55°	7330	7141	6923
60°	7042	6837	6622
65°	6788	6510	6306
70°	6408	6134	5860
75°	5856	5644	5407
80°	5281	5058	5015
85°	4631	4458	4286



TEST NUMBER: P331944-830

CATALOG NUMBER: S123DIP-S560D1025U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	79.1	1.4
10°-20°	223.3	4.1
20°-30°	329.9	6.0
30°-40°	385.4	7.0
40°-50°	387.4	7.0
50°-60°	340.3	6.2
60°-70°	253.5	4.6
70°-80°	144.5	2.6
80°-90°	45.0	0.8
90°-100°	78.0	1.4
100°-110°	233.5	4.2
110°-120°	397.2	7.2
120°-130°	522.5	9.5
130°-140°	587.2	10.7
140°-150°	577.2	10.5
150°-160°	486.0	8.8
160°-170°	323.5	5.9
170°-180°	113.3	2.1
0°-30°	632.3	11.5
0°-40°	1017.7	18.5
0°-60°	1745.5	31.7
0°-90°	2188.5	39.7
90°-120°	708.8	12.9
90°-150°	2395.7	43.5
90°-180°	3318.0	60.3
0°-180°	5506.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	840	840	840	840	840	
5°	840	837	829	836	835	80
15°	800	797	788	793	789	225
25°	726	722	713	713	711	334
35°	628	624	614	610	606	393
45°	515	512	502	494	490	397
55°	391	389	380	373	369	350
65°	266	263	256	250	248	263
75°	141	138	136	132	130	151
85°	38	36	36	35	35	41
90°	1	10	23	26	28	5
95°	56	62	70	73	73	62
105°	212	214	222	222	224	227
115°	400	402	401	402	401	395
125°	585	588	586	582	579	522
135°	759	765	764	760	758	585
145°	921	923	926	925	921	575
155°	1055	1055	1056	1059	1053	485
165°	1149	1146	1146	1151	1145	324
175°	1195	1191	1191	1196	1190	113
180°	1198	1198	1198	1198	1198	



TEST NUMBER: P331944-830

CATALOG NUMBER: S123DIP-S560D1025U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	842.5	842.1	841.6	841.0	840.6	839.5	838.1	836.7	835.4	834.0	835.2
5°	840.4	839.6	838.8	838.0	837.2	835.9	834.2	832.4	830.7	828.9	830.5
7.5°	832.2	831.4	830.6	829.8	829.0	827.6	825.9	824.0	822.2	820.4	821.8
10°	825.3	824.4	823.7	822.8	822.1	820.6	818.5	816.4	814.4	812.3	813.7
12.5°	816.1	815.3	814.6	814.0	813.3	812.0	810.0	808.0	806.2	804.2	805.2
15°	799.9	799.4	798.7	798.1	797.4	796.1	794.0	791.9	789.8	787.7	789.0
17.5°	781.4	780.5	779.7	778.8	778.0	776.6	774.5	772.4	770.3	768.2	769.1
20°	767.5	766.6	765.5	764.6	763.6	762.1	760.1	758.0	755.8	753.8	754.4
22.5°	751.9	750.9	750.0	749.0	748.0	746.5	744.4	742.3	740.3	738.2	738.7
25°	726.3	725.4	724.4	723.5	722.5	721.0	718.9	716.8	714.7	712.7	712.8
27.5°	699.1	698.1	697.2	696.3	695.3	693.7	691.4	689.3	687.0	684.8	684.9
30°	679.4	678.6	677.8	677.0	676.2	674.7	672.4	670.1	668.0	665.7	665.7
32.5°	659.8	658.7	657.6	656.6	655.5	654.1	652.4	650.6	648.9	647.2	646.3
35°	628.1	627.2	626.2	625.3	624.3	622.7	620.7	618.6	616.5	614.4	613.5
37.5°	595.8	594.6	593.3	592.1	590.9	589.3	587.1	585.0	582.9	580.8	579.7
40°	573.3	572.3	571.4	570.4	569.4	567.8	565.5	563.4	561.1	558.8	557.5
42.5°	550.7	549.7	548.6	547.4	546.4	544.7	542.4	540.3	538.0	535.7	534.4
45°	514.8	514.2	513.5	512.8	512.2	510.9	508.8	506.7	504.6	502.5	500.6
47.5°	479.1	478.2	477.3	476.4	475.4	473.9	472.0	470.0	468.1	466.1	464.2
50°	454.9	454.0	453.3	452.4	451.7	450.3	448.1	446.0	443.9	441.9	440.1
52.5°	429.4	428.9	428.4	427.8	427.3	425.8	423.7	421.5	419.2	417.1	415.6
55°	390.6	390.4	390.3	390.1	389.9	388.8	386.7	384.7	382.6	380.5	378.7
57.5°	353.6	353.1	352.5	352.0	351.5	350.3	348.6	347.0	345.3	343.7	342.1
60°	327.1	326.9	326.8	326.6	326.4	325.4	323.5	321.5	319.6	317.6	316.2
62.5°	303.4	302.9	302.6	302.2	301.7	300.6	298.6	296.7	294.7	292.8	291.4
65°	266.5	265.6	264.9	264.0	263.3	262.0	260.4	258.8	257.2	255.6	254.3
67.5°	227.2	226.6	225.8	225.2	224.4	223.5	222.3	221.0	219.8	218.7	217.5
70°	203.6	202.6	201.7	200.8	199.7	198.8	197.8	196.9	195.9	194.9	193.8
72.5°	178.8	178.0	177.4	176.6	176.0	175.0	174.0	172.9	171.7	170.7	169.7
75°	140.8	140.2	139.5	138.8	138.3	137.7	137.1	136.7	136.2	135.7	135.0
77.5°	107.2	106.8	106.4	106.1	105.8	105.3	104.7	104.2	103.5	102.9	102.5
80°	85.2	84.7	84.3	83.8	83.2	82.8	82.6	82.2	81.9	81.6	81.4
82.5°	63.8	63.7	63.6	63.5	63.4	63.3	63.3	63.2	63.2	63.2	62.8
85°	37.5	37.2	36.9	36.6	36.3	36.1	36.1	36.1	36.1	36.1	35.8
87.5°	15.2	15.3	15.3	15.3	15.4	15.6	16.0	16.4	16.8	17.2	17.2
90°	0.9	3.0	5.1	7.3	9.3	11.7	14.4	17.2	19.9	22.6	23.4
92.5°	22.8	24.2	25.6	27.1	28.5	30.0	31.5	33.0	34.6	36.1	36.8
95°	55.5	56.9	58.4	59.9	61.4	63.0	64.6	66.3	68.0	69.7	70.5
97.5°	98.6	99.7	100.8	101.9	102.9	104.1	105.3	106.5	107.7	109.0	109.9
100°	128.0	129.2	130.4	131.7	133.0	134.1	135.2	136.2	137.2	138.3	138.9
102.5°	161.8	162.6	163.3	164.1	164.9	165.9	167.3	168.6	170.0	171.4	172.0
105°	211.7	212.1	212.5	212.9	213.4	214.5	216.4	218.3	220.2	222.1	222.1
107.5°	269.7	269.9	270.1	270.4	270.7	271.2	271.9	272.7	273.4	274.2	274.8
110°	305.8	306.2	306.6	307.0	307.5	307.8	308.3	308.7	309.2	309.5	310.4



TEST NUMBER: P331944-830

CATALOG NUMBER: S123DIP-S560D1025U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	343.4	343.7	343.9	344.1	344.4	344.6	344.7	344.8	344.9	344.9	345.9
115°	399.8	400.5	401.1	401.7	402.4	402.5	402.1	401.6	401.2	400.8	401.1
117.5°	456.7	457.1	457.5	458.0	458.4	458.3	457.8	457.2	456.7	456.1	456.1
120°	492.1	493.3	494.6	495.9	497.1	497.2	496.2	495.1	494.1	493.0	492.8
122.5°	529.0	529.9	530.7	531.7	532.6	532.8	532.3	531.7	531.2	530.7	530.1
125°	585.2	585.9	586.4	587.1	587.7	587.9	587.4	587.0	586.5	586.2	585.3
127.5°	637.2	638.5	639.8	641.1	642.5	642.9	642.4	642.1	641.6	641.1	639.9
130°	671.8	673.4	675.1	676.7	678.4	679.0	678.3	677.7	677.1	676.5	675.6
132.5°	706.4	708.0	709.7	711.4	713.1	713.7	713.2	712.8	712.3	711.8	710.9
135°	759.3	760.5	761.8	763.0	764.3	764.8	764.6	764.4	764.2	763.9	763.2
137.5°	808.2	809.3	810.3	811.3	812.4	813.1	813.7	814.3	814.8	815.3	814.5
140°	842.1	843.1	844.1	845.2	846.2	846.9	847.1	847.3	847.5	847.7	847.5
142.5°	872.9	873.9	875.1	876.1	877.1	877.8	878.2	878.5	878.9	879.3	879.1
145°	921.1	921.5	921.9	922.4	922.7	923.3	923.9	924.5	925.2	925.8	925.6
147.5°	963.3	964.0	964.8	965.5	966.3	967.0	967.5	968.1	968.7	969.3	969.3
150°	992.6	993.1	993.4	993.8	994.3	994.7	995.1	995.5	996.0	996.4	996.4
152.5°	1016.7	1017.3	1017.9	1018.4	1019.0	1019.5	1019.7	1019.9	1020.2	1020.5	1020.8
155°	1054.7	1054.7	1054.7	1054.7	1054.7	1054.8	1055.0	1055.2	1055.5	1055.6	1056.5
157.5°	1087.0	1086.8	1086.6	1086.3	1086.1	1086.0	1086.2	1086.4	1086.6	1086.7	1087.6
160°	1107.4	1106.9	1106.5	1106.2	1105.7	1105.5	1105.5	1105.5	1105.5	1105.5	1106.5
162.5°	1125.5	1124.8	1124.3	1123.7	1123.1	1122.9	1123.0	1123.2	1123.4	1123.6	1124.6
165°	1148.8	1148.1	1147.5	1146.9	1146.3	1145.9	1145.9	1145.9	1145.9	1145.9	1147.2
167.5°	1167.4	1166.6	1165.7	1164.9	1164.0	1163.8	1163.9	1164.0	1164.2	1164.4	1165.7
170°	1178.0	1177.1	1176.3	1175.4	1174.6	1174.2	1174.2	1174.2	1174.2	1174.2	1175.6
172.5°	1186.2	1185.4	1184.6	1183.7	1182.9	1182.4	1182.4	1182.4	1182.4	1182.4	1183.7
175°	1194.9	1194.0	1193.2	1192.4	1191.6	1191.1	1191.1	1191.1	1191.1	1191.1	1192.4
177.5°	1198.4	1197.8	1197.1	1196.5	1195.8	1195.4	1195.4	1195.4	1195.4	1195.4	1196.5
180°	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7



TEST NUMBER: P331944-830

CATALOG NUMBER: S123DIP-S560D1025U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	836.5	837.7	839.1	839.6	839.5	839.3	839.2	839.1
5°	832.1	833.7	835.3	835.9	835.6	835.3	835.0	834.6
7.5°	823.2	824.6	826.1	826.7	826.5	826.3	826.1	826.0
10°	815.1	816.6	818.0	818.6	818.3	817.9	817.7	817.3
12.5°	806.3	807.4	808.4	808.8	808.6	808.4	808.2	808.0
15°	790.3	791.5	792.9	793.0	792.0	791.1	790.1	789.2
17.5°	770.1	770.9	771.8	772.0	771.8	771.4	771.0	770.6
20°	755.1	755.7	756.3	756.4	755.9	755.4	755.0	754.5
22.5°	739.2	739.7	740.3	740.2	739.6	739.0	738.4	737.7
25°	712.9	713.1	713.2	713.1	712.7	712.2	711.6	711.1
27.5°	685.0	685.1	685.2	685.0	684.4	683.8	683.2	682.6
30°	665.7	665.7	665.7	665.2	664.0	662.9	661.8	660.6
32.5°	645.5	644.5	643.6	642.8	642.2	641.7	641.0	640.5
35°	612.5	611.5	610.6	609.7	608.9	608.1	607.3	606.5
37.5°	578.4	577.3	576.2	575.3	574.9	574.3	573.8	573.3
40°	556.3	555.0	553.7	552.7	552.0	551.5	550.8	550.2
42.5°	533.2	531.9	530.6	529.6	529.0	528.4	527.7	527.1
45°	498.7	496.7	494.8	493.4	492.7	491.8	491.1	490.2
47.5°	462.3	460.4	458.5	457.2	456.6	455.8	455.2	454.4
50°	438.4	436.6	434.8	433.5	432.4	431.5	430.6	429.6
52.5°	414.1	412.6	411.0	409.7	408.8	407.8	406.9	406.0
55°	376.9	375.2	373.4	372.1	371.4	370.5	369.8	368.9
57.5°	340.5	338.9	337.4	336.1	335.2	334.3	333.4	332.4
60°	314.8	313.4	311.9	310.8	310.0	309.2	308.4	307.6
62.5°	289.9	288.5	287.1	286.1	285.5	285.0	284.5	283.9
65°	253.0	251.8	250.4	249.6	249.1	248.6	248.2	247.6
67.5°	216.4	215.3	214.1	213.2	212.5	211.9	211.2	210.6
70°	192.7	191.6	190.5	189.5	188.7	187.8	187.1	186.2
72.5°	168.7	167.7	166.7	166.0	165.6	165.1	164.8	164.3
75°	134.1	133.4	132.5	131.9	131.4	130.9	130.4	130.0
77.5°	101.9	101.3	100.8	100.5	100.5	100.5	100.5	100.5
80°	81.2	81.1	81.0	80.9	80.9	80.9	80.9	80.9
82.5°	62.5	62.2	61.9	61.7	61.6	61.5	61.4	61.3
85°	35.4	35.2	34.8	34.7	34.7	34.7	34.7	34.7
87.5°	17.3	17.3	17.3	17.4	17.5	17.6	17.7	17.8
90°	24.2	25.1	25.9	26.6	27.0	27.4	27.8	28.2
92.5°	37.5	38.2	38.8	39.0	38.7	38.5	38.3	38.0
95°	71.3	72.1	73.0	73.4	73.4	73.4	73.4	73.4
97.5°	110.8	111.9	112.8	113.2	113.2	113.1	113.0	112.9
100°	139.6	140.2	140.8	141.4	141.8	142.1	142.6	143.0
102.5°	172.7	173.3	173.9	174.2	174.1	174.0	174.0	173.9
105°	222.1	222.1	222.1	222.3	222.6	223.1	223.5	223.9
107.5°	275.5	276.2	276.8	277.0	276.8	276.5	276.3	276.1
110°	311.2	312.1	312.9	313.1	312.6	312.3	311.9	311.4





TEST NUMBER: P331944-830

CATALOG NUMBER: S123DIP-S560D1025U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	346.9	347.9	348.9	349.4	349.3	349.2	349.1	349.0
115°	401.2	401.4	401.6	401.6	401.4	401.2	401.1	400.8
117.5°	456.0	456.0	456.0	455.6	455.1	454.5	453.9	453.3
120°	492.6	492.4	492.2	491.8	491.4	491.1	490.6	490.2
122.5°	529.5	529.0	528.5	527.9	527.4	526.7	526.1	525.6
125°	584.5	583.6	582.8	581.9	581.2	580.3	579.5	578.6
127.5°	638.8	637.6	636.4	635.4	634.4	633.4	632.4	631.5
130°	674.8	673.9	673.2	671.9	670.5	669.0	667.6	666.1
132.5°	709.8	708.9	707.8	706.8	705.7	704.6	703.4	702.3
135°	762.3	761.5	760.6	760.0	759.6	759.1	758.7	758.4
137.5°	813.6	812.8	811.8	811.0	810.2	809.4	808.6	807.9
140°	847.3	847.1	846.9	846.0	844.6	843.1	841.7	840.2
142.5°	878.9	878.7	878.4	877.8	876.7	875.5	874.4	873.3
145°	925.4	925.2	924.9	924.4	923.6	922.7	921.9	921.1
147.5°	969.3	969.3	969.3	968.7	967.4	966.1	964.9	963.7
150°	996.4	996.4	996.4	995.7	994.5	993.3	991.9	990.7
152.5°	1021.2	1021.4	1021.8	1021.4	1020.3	1019.3	1018.1	1017.1
155°	1057.3	1058.2	1058.9	1058.7	1057.2	1055.7	1054.2	1052.8
157.5°	1088.4	1089.3	1090.2	1090.1	1088.9	1087.7	1086.6	1085.3
160°	1107.6	1108.6	1109.7	1109.7	1109.0	1108.1	1107.3	1106.5
162.5°	1125.7	1126.7	1127.8	1127.6	1126.2	1124.9	1123.6	1122.3
165°	1148.5	1149.7	1150.9	1150.8	1149.4	1147.9	1146.5	1145.0
167.5°	1167.0	1168.3	1169.6	1169.6	1168.3	1167.0	1165.7	1164.4
170°	1177.1	1178.6	1180.1	1180.1	1178.6	1177.1	1175.6	1174.2
172.5°	1185.1	1186.4	1187.6	1187.6	1186.1	1184.7	1183.2	1181.7
175°	1193.6	1194.9	1196.2	1196.0	1194.6	1193.1	1191.7	1190.1
177.5°	1197.5	1198.4	1199.5	1199.4	1198.3	1197.0	1195.9	1194.7
180°	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7

(END OF REPORT)