

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331953-830

Luminaire Tested: **S123DIP-S560D1195U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331953-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D1195U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6051.6 lumens
Efficiency: N/A
Efficacy: 122.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331953-830

CATALOG NUMBER: S123DIP-S560D1195U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331953-830

CATALOG NUMBER: S123DIP-S560D1195U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76		59	59	59		43	43	43	36
1	95	90	87	83	86	82	79	76	66	64	62		52	50	49		38	37	37	30
2	86	79	73	68	78	72	66	62	58	54	51		45	43	41		34	32	31	25
3	79	69	62	56	71	63	57	52	51	47	43		40	37	34		30	28	26	21
4	72	61	53	48	65	56	49	44	45	40	36		36	32	29		27	24	22	18
5	66	54	46	41	59	50	43	37	40	35	31		32	28	25		24	21	20	16
6	61	49	41	35	55	44	37	32	36	31	27		29	25	22		22	19	17	14
7	56	44	36	31	50	40	33	28	33	28	24		26	22	20		20	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21		24	20	17		18	16	14	11
9	48	36	29	24	44	33	27	22	27	22	19		22	18	16		17	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17		20	17	14		16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9038	9038	9038
5°	9081	8956	9018
10°	9021	8878	8933
15°	8914	8778	8795
20°	8791	8635	8643
25°	8626	8464	8445
30°	8444	8274	8211
35°	8253	8073	7970
40°	8056	7852	7731
45°	7837	7649	7462
50°	7618	7400	7194
55°	7330	7141	6923
60°	7042	6837	6622
65°	6788	6510	6306
70°	6408	6134	5860
75°	5856	5644	5407
80°	5281	5058	5015
85°	4631	4458	4286



TEST NUMBER: P331953-830

CATALOG NUMBER: S123DIP-S560D1195U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	1.3
10°-20°	223.3	3.7
20°-30°	329.9	5.5
30°-40°	385.4	6.4
40°-50°	387.4	6.4
50°-60°	340.3	5.6
60°-70°	253.5	4.2
70°-80°	144.5	2.4
80°-90°	45.6	0.8
90°-100°	90.8	1.5
100°-110°	271.8	4.5
110°-120°	462.3	7.6
120°-130°	608.1	10.0
130°-140°	683.5	11.3
140°-150°	671.9	11.1
150°-160°	565.6	9.3
160°-170°	376.5	6.2
170°-180°	131.8	2.2
0°-30°	632.3	10.4
0°-40°	1017.7	16.8
0°-60°	1745.5	28.8
0°-90°	2189.1	36.2
90°-120°	825.0	13.6
90°-150°	2788.5	46.1
90°-180°	3863.0	63.8
0°-180°	6051.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	840	840	840	840	840	
5°	840	837	829	836	835	80
15°	800	797	788	793	789	225
25°	726	722	713	713	711	334
35°	628	624	614	610	606	393
45°	515	512	502	494	490	397
55°	391	389	380	373	369	350
65°	266	263	256	250	248	263
75°	141	138	136	132	130	151
85°	38	36	36	35	35	41
90°	1	12	26	31	33	6
95°	65	72	81	85	85	73
105°	246	249	258	259	261	264
115°	465	468	467	468	467	460
125°	681	684	682	678	674	607
135°	884	890	889	885	883	681
145°	1072	1074	1078	1076	1072	669
155°	1228	1228	1229	1232	1225	565
165°	1337	1334	1334	1340	1333	377
175°	1391	1387	1386	1392	1385	132
180°	1394	1394	1394	1394	1394	



TEST NUMBER: P331953-830

CATALOG NUMBER: S123DIP-S560D1195U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	842.5	842.1	841.6	841.0	840.6	839.5	838.1	836.7	835.4	834.0	835.2
5°	840.4	839.6	838.8	838.0	837.2	835.9	834.2	832.4	830.7	828.9	830.5
7.5°	832.2	831.4	830.6	829.8	829.0	827.6	825.9	824.0	822.2	820.4	821.8
10°	825.3	824.4	823.7	822.8	822.1	820.6	818.5	816.4	814.4	812.3	813.7
12.5°	816.1	815.3	814.6	814.0	813.3	812.0	810.0	808.0	806.2	804.2	805.2
15°	799.9	799.4	798.7	798.1	797.4	796.1	794.0	791.9	789.8	787.7	789.0
17.5°	781.4	780.5	779.7	778.8	778.0	776.6	774.5	772.4	770.3	768.2	769.1
20°	767.5	766.6	765.5	764.6	763.6	762.1	760.1	758.0	755.8	753.8	754.4
22.5°	751.9	750.9	750.0	749.0	748.0	746.5	744.4	742.3	740.3	738.2	738.7
25°	726.3	725.4	724.4	723.5	722.5	721.0	718.9	716.8	714.7	712.7	712.8
27.5°	699.1	698.1	697.2	696.3	695.3	693.7	691.4	689.3	687.0	684.8	684.9
30°	679.4	678.6	677.8	677.0	676.2	674.7	672.4	670.1	668.0	665.7	665.7
32.5°	659.8	658.7	657.6	656.6	655.5	654.1	652.4	650.6	648.9	647.2	646.3
35°	628.1	627.2	626.2	625.3	624.3	622.7	620.7	618.6	616.5	614.4	613.5
37.5°	595.8	594.6	593.3	592.1	590.9	589.3	587.1	585.0	582.9	580.8	579.7
40°	573.3	572.3	571.4	570.4	569.4	567.8	565.5	563.4	561.1	558.8	557.5
42.5°	550.7	549.7	548.6	547.4	546.4	544.7	542.4	540.3	538.0	535.7	534.4
45°	514.8	514.2	513.5	512.8	512.2	510.9	508.8	506.7	504.6	502.5	500.6
47.5°	479.1	478.2	477.3	476.4	475.4	473.9	472.0	470.0	468.1	466.1	464.2
50°	454.9	454.0	453.3	452.4	451.7	450.3	448.1	446.0	443.9	441.9	440.1
52.5°	429.4	428.9	428.4	427.8	427.3	425.8	423.7	421.5	419.2	417.1	415.6
55°	390.6	390.4	390.3	390.1	389.9	388.8	386.7	384.7	382.6	380.5	378.7
57.5°	353.6	353.1	352.5	352.0	351.5	350.3	348.6	347.0	345.3	343.7	342.1
60°	327.1	326.9	326.8	326.6	326.4	325.4	323.5	321.5	319.6	317.6	316.2
62.5°	303.4	302.9	302.6	302.2	301.7	300.6	298.6	296.7	294.7	292.8	291.4
65°	266.5	265.6	264.9	264.0	263.3	262.0	260.4	258.8	257.2	255.6	254.3
67.5°	227.2	226.6	225.8	225.2	224.4	223.5	222.3	221.0	219.8	218.7	217.5
70°	203.6	202.6	201.7	200.8	199.7	198.8	197.8	196.9	195.9	194.9	193.8
72.5°	178.8	178.0	177.4	176.6	176.0	175.0	174.0	172.9	171.7	170.7	169.7
75°	140.8	140.2	139.5	138.8	138.3	137.7	137.1	136.7	136.2	135.7	135.0
77.5°	107.2	106.8	106.4	106.1	105.8	105.3	104.7	104.2	103.5	102.9	102.5
80°	85.2	84.7	84.3	83.8	83.2	82.8	82.6	82.2	81.9	81.6	81.4
82.5°	63.8	63.7	63.6	63.5	63.4	63.3	63.3	63.2	63.2	63.2	62.8
85°	37.5	37.2	36.9	36.6	36.3	36.1	36.1	36.1	36.1	36.1	35.8
87.5°	15.3	15.4	15.5	15.6	15.6	15.9	16.5	17.0	17.4	18.0	18.0
90°	1.1	3.5	5.9	8.4	10.8	13.7	16.8	20.0	23.1	26.3	27.2
92.5°	26.5	28.2	29.8	31.5	33.1	34.9	36.7	38.5	40.2	42.0	42.8
95°	64.7	66.4	68.1	69.7	71.4	73.2	75.2	77.1	79.1	81.1	82.0
97.5°	114.8	116.0	117.3	118.6	119.8	121.2	122.6	124.0	125.4	126.8	127.9
100°	148.9	150.4	151.8	153.4	154.8	156.1	157.3	158.5	159.8	161.0	161.7
102.5°	188.3	189.3	190.1	191.0	191.9	193.1	194.7	196.3	197.9	199.5	200.3
105°	246.4	246.9	247.4	247.9	248.4	249.7	251.8	254.1	256.3	258.4	258.4
107.5°	313.9	314.1	314.4	314.7	315.0	315.7	316.5	317.4	318.2	319.1	319.9
110°	355.9	356.4	356.8	357.4	357.9	358.4	358.8	359.3	359.8	360.3	361.3



TEST NUMBER: P331953-830

CATALOG NUMBER: S123DIP-S560D1195U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	399.7	400.0	400.3	400.6	400.9	401.1	401.1	401.2	401.3	401.4	402.7
115°	465.4	466.2	466.8	467.6	468.3	468.4	468.0	467.5	467.0	466.6	466.7
117.5°	531.6	532.1	532.5	533.0	533.5	533.5	532.8	532.2	531.6	530.9	530.8
120°	572.8	574.2	575.7	577.1	578.6	578.7	577.5	576.3	575.0	573.8	573.6
122.5°	615.7	616.7	617.8	618.9	620.0	620.2	619.5	618.9	618.3	617.6	617.0
125°	681.2	681.9	682.6	683.3	684.1	684.2	683.7	683.2	682.8	682.3	681.3
127.5°	741.6	743.2	744.7	746.3	747.8	748.4	747.8	747.2	746.8	746.2	744.9
130°	781.9	783.8	785.8	787.8	789.7	790.3	789.6	788.8	788.2	787.4	786.5
132.5°	822.2	824.2	826.1	828.0	830.0	830.8	830.2	829.6	829.1	828.6	827.4
135°	883.7	885.2	886.6	888.2	889.6	890.2	889.9	889.8	889.5	889.2	888.3
137.5°	940.8	941.9	943.1	944.3	945.6	946.5	947.2	947.7	948.4	949.0	948.0
140°	980.1	981.4	982.6	983.8	985.0	985.7	986.0	986.2	986.5	986.7	986.5
142.5°	1016.1	1017.3	1018.5	1019.7	1021.0	1021.7	1022.2	1022.7	1023.0	1023.5	1023.2
145°	1072.1	1072.6	1073.1	1073.6	1074.0	1074.7	1075.4	1076.1	1076.9	1077.6	1077.3
147.5°	1121.2	1122.1	1122.9	1123.8	1124.7	1125.5	1126.1	1126.8	1127.5	1128.2	1128.2
150°	1155.4	1155.8	1156.3	1156.8	1157.3	1157.8	1158.3	1158.8	1159.2	1159.7	1159.7
152.5°	1183.4	1184.1	1184.8	1185.4	1186.1	1186.6	1186.8	1187.2	1187.5	1187.8	1188.2
155°	1227.7	1227.7	1227.7	1227.7	1227.7	1227.8	1228.0	1228.2	1228.5	1228.7	1229.7
157.5°	1265.3	1265.0	1264.7	1264.4	1264.1	1264.0	1264.3	1264.5	1264.7	1264.9	1265.9
160°	1288.9	1288.5	1288.0	1287.5	1287.0	1286.8	1286.8	1286.8	1286.8	1286.8	1288.0
162.5°	1309.9	1309.3	1308.6	1308.0	1307.3	1307.0	1307.2	1307.4	1307.6	1307.8	1309.0
165°	1337.2	1336.4	1335.7	1334.9	1334.3	1333.9	1333.9	1333.9	1333.9	1333.9	1335.3
167.5°	1358.9	1357.8	1356.9	1355.9	1354.9	1354.5	1354.7	1354.9	1355.1	1355.3	1356.8
170°	1371.1	1370.1	1369.1	1368.2	1367.2	1366.7	1366.7	1366.7	1366.7	1366.7	1368.4
172.5°	1380.7	1379.8	1378.8	1377.8	1376.9	1376.4	1376.4	1376.4	1376.4	1376.4	1377.9
175°	1390.8	1389.9	1388.8	1387.9	1387.0	1386.4	1386.4	1386.4	1386.4	1386.4	1387.9
177.5°	1395.0	1394.2	1393.5	1392.6	1391.9	1391.5	1391.5	1391.5	1391.5	1391.5	1392.6
180°	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1



TEST NUMBER: P331953-830

CATALOG NUMBER: S123DIP-S560D1195U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	836.5	837.7	839.1	839.6	839.5	839.3	839.2	839.1
5°	832.1	833.7	835.3	835.9	835.6	835.3	835.0	834.6
7.5°	823.2	824.6	826.1	826.7	826.5	826.3	826.1	826.0
10°	815.1	816.6	818.0	818.6	818.3	817.9	817.7	817.3
12.5°	806.3	807.4	808.4	808.8	808.6	808.4	808.2	808.0
15°	790.3	791.5	792.9	793.0	792.0	791.1	790.1	789.2
17.5°	770.1	770.9	771.8	772.0	771.8	771.4	771.0	770.6
20°	755.1	755.7	756.3	756.4	755.9	755.4	755.0	754.5
22.5°	739.2	739.7	740.3	740.2	739.6	739.0	738.4	737.7
25°	712.9	713.1	713.2	713.1	712.7	712.2	711.6	711.1
27.5°	685.0	685.1	685.2	685.0	684.4	683.8	683.2	682.6
30°	665.7	665.7	665.7	665.2	664.0	662.9	661.8	660.6
32.5°	645.5	644.5	643.6	642.8	642.2	641.7	641.0	640.5
35°	612.5	611.5	610.6	609.7	608.9	608.1	607.3	606.5
37.5°	578.4	577.3	576.2	575.3	574.9	574.3	573.8	573.3
40°	556.3	555.0	553.7	552.7	552.0	551.5	550.8	550.2
42.5°	533.2	531.9	530.6	529.6	529.0	528.4	527.7	527.1
45°	498.7	496.7	494.8	493.4	492.7	491.8	491.1	490.2
47.5°	462.3	460.4	458.5	457.2	456.6	455.8	455.2	454.4
50°	438.4	436.6	434.8	433.5	432.4	431.5	430.6	429.6
52.5°	414.1	412.6	411.0	409.7	408.8	407.8	406.9	406.0
55°	376.9	375.2	373.4	372.1	371.4	370.5	369.8	368.9
57.5°	340.5	338.9	337.4	336.1	335.2	334.3	333.4	332.4
60°	314.8	313.4	311.9	310.8	310.0	309.2	308.4	307.6
62.5°	289.9	288.5	287.1	286.1	285.5	285.0	284.5	283.9
65°	253.0	251.8	250.4	249.6	249.1	248.6	248.2	247.6
67.5°	216.4	215.3	214.1	213.2	212.5	211.9	211.2	210.6
70°	192.7	191.6	190.5	189.5	188.7	187.8	187.1	186.2
72.5°	168.7	167.7	166.7	166.0	165.6	165.1	164.8	164.3
75°	134.1	133.4	132.5	131.9	131.4	130.9	130.4	130.0
77.5°	101.9	101.3	100.8	100.5	100.5	100.5	100.5	100.5
80°	81.2	81.1	81.0	80.9	80.9	80.9	80.9	80.9
82.5°	62.5	62.2	61.9	61.7	61.6	61.5	61.4	61.3
85°	35.4	35.2	34.8	34.7	34.7	34.7	34.7	34.7
87.5°	18.1	18.2	18.2	18.3	18.4	18.5	18.6	18.7
90°	28.3	29.2	30.2	30.9	31.4	31.9	32.3	32.9
92.5°	43.6	44.4	45.1	45.4	45.1	44.9	44.5	44.2
95°	82.9	84.0	84.9	85.4	85.4	85.4	85.4	85.4
97.5°	129.0	130.2	131.3	131.8	131.7	131.6	131.5	131.4
100°	162.4	163.2	163.9	164.5	165.0	165.5	166.0	166.5
102.5°	201.0	201.7	202.5	202.7	202.6	202.6	202.5	202.4
105°	258.4	258.4	258.4	258.7	259.2	259.7	260.1	260.6
107.5°	320.7	321.5	322.3	322.4	322.2	321.9	321.6	321.3
110°	362.2	363.3	364.2	364.4	363.9	363.4	363.0	362.5



TEST NUMBER: P331953-830

CATALOG NUMBER: S123DIP-S560D1195U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	403.8	405.0	406.1	406.7	406.6	406.5	406.4	406.3
115°	467.0	467.2	467.5	467.5	467.2	467.0	466.7	466.6
117.5°	530.8	530.7	530.7	530.4	529.7	529.0	528.3	527.6
120°	573.3	573.2	572.9	572.5	572.0	571.6	571.1	570.5
122.5°	616.4	615.8	615.1	614.4	613.8	613.1	612.4	611.7
125°	680.3	679.4	678.3	677.4	676.5	675.4	674.5	673.5
127.5°	743.5	742.2	740.7	739.5	738.4	737.3	736.1	735.1
130°	785.4	784.5	783.5	782.1	780.4	778.7	777.0	775.3
132.5°	826.2	825.1	823.9	822.7	821.3	820.0	818.7	817.4
135°	887.3	886.3	885.3	884.6	884.1	883.6	883.2	882.7
137.5°	947.0	945.9	944.9	944.0	943.0	942.2	941.2	940.3
140°	986.2	986.0	985.7	984.8	983.1	981.4	979.7	978.0
142.5°	1023.0	1022.8	1022.6	1021.7	1020.4	1019.1	1017.9	1016.5
145°	1077.1	1076.9	1076.7	1076.0	1075.1	1074.0	1073.1	1072.1
147.5°	1128.2	1128.2	1128.2	1127.5	1126.0	1124.5	1123.0	1121.6
150°	1159.7	1159.7	1159.7	1159.0	1157.5	1156.1	1154.6	1153.2
152.5°	1188.5	1188.9	1189.3	1188.9	1187.6	1186.4	1185.1	1183.8
155°	1230.7	1231.6	1232.7	1232.3	1230.6	1228.9	1227.2	1225.4
157.5°	1266.9	1267.9	1268.9	1268.8	1267.4	1266.0	1264.7	1263.3
160°	1289.2	1290.4	1291.7	1291.8	1290.8	1289.8	1288.8	1287.9
162.5°	1310.2	1311.5	1312.7	1312.5	1310.9	1309.4	1307.8	1306.3
165°	1336.8	1338.2	1339.7	1339.5	1337.8	1336.1	1334.5	1332.8
167.5°	1358.3	1359.8	1361.3	1361.3	1359.8	1358.3	1356.8	1355.3
170°	1370.1	1371.9	1373.6	1373.6	1371.9	1370.1	1368.4	1366.7
172.5°	1379.4	1380.9	1382.4	1382.3	1380.5	1378.8	1377.1	1375.5
175°	1389.3	1390.8	1392.2	1392.1	1390.4	1388.7	1387.0	1385.3
177.5°	1393.8	1395.0	1396.1	1396.0	1394.7	1393.3	1391.9	1390.6
180°	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1

(END OF REPORT)