

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331964

Luminaire Tested: **S123DIP-S775D585U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331964
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D585U835-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5604.6 lumens
Efficiency: N/A
Efficacy: 139.1 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331964

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331964

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58
1	100	96	92	88	93	89	86	83	78	75	73	67	65	63	57	56	54	50
2	91	84	78	73	85	79	73	69	68	64	61	59	56	53	50	48	46	42
3	83	74	67	61	78	69	63	58	61	56	52	52	49	46	45	42	40	36
4	76	66	58	52	71	62	55	49	54	48	44	47	43	39	40	37	34	31
5	70	59	51	45	65	55	48	42	48	43	38	42	38	34	36	33	30	27
6	65	53	45	39	60	50	42	37	44	38	33	38	34	30	33	29	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	27	24	21
8	56	43	36	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19
9	52	40	32	27	48	37	31	26	33	28	24	29	25	21	26	22	19	17
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11630	11630	11630	11630
5°	13870	11681	10351	11681
10°	17361	11622	9349	11622
15°	21293	11528	8704	11528
20°	25366	11381	8287	11381
25°	26935	11204	8195	11204
30°	23086	11074	8238	11074
35°	16056	10889	8324	10889
40°	12094	10673	8297	10673
45°	10041	10353	8193	10353
50°	8994	9696	8118	9696
55°	8409	8989	8017	8989
60°	7890	8249	7935	8249
65°	7414	7521	7679	7521
70°	6952	6688	7314	6688
75°	6226	5856	6704	5856
80°	5455	4804	5777	4804
85°	4273	3495	3878	3495



TEST NUMBER: P331964

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.4	1.9
10°-20°	341.3	6.1
20°-30°	572.8	10.2
30°-40°	648.6	11.6
40°-50°	581.7	10.4
50°-60°	469.4	8.4
60°-70°	327.1	5.8
70°-80°	171.9	3.1
80°-90°	44.2	0.8
90°-100°	27.9	0.5
100°-110°	133.0	2.4
110°-120°	319.5	5.7
120°-130°	406.9	7.3
130°-140°	434.7	7.8
140°-150°	406.5	7.3
150°-160°	327.9	5.9
160°-170°	211.6	3.8
170°-180°	72.9	1.3
0°-30°	1020.6	18.2
0°-40°	1669.2	29.8
0°-60°	2720.2	48.5
0°-90°	3263.4	58.2
90°-120°	480.5	8.6
90°-150°	1728.6	30.8
90°-180°	2341.0	41.8
0°-180°	5604.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1080	1080	1080	1080	1080	
5°	1284	1081	958	1081	1284	133
15°	1911	1034	781	1034	1911	552
25°	2268	943	690	943	2268	995
35°	1222	829	634	829	1222	794
45°	660	680	538	680	660	522
55°	448	479	427	479	448	402
65°	291	295	302	295	291	290
75°	150	141	161	141	150	160
85°	35	28	31	28	35	41
90°	17	1	17	1	17	9
95°	22	35	22	35	22	18
105°	25	170	25	170	25	57
115°	335	319	335	319	335	310
125°	459	449	459	449	459	410
135°	565	560	565	560	565	436
145°	652	646	652	646	652	407
155°	710	711	710	711	710	327
165°	748	750	748	750	748	211
175°	765	768	765	768	765	73
180°	768	768	768	768	768	



TEST NUMBER: P331964

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1146.7	1145.9	1143.8	1145.5	1142.1	1137.5	1137.1	1132.9	1120.7	1119.9	1116.6
5°	1283.7	1279.5	1279.0	1278.4	1271.1	1261.2	1242.3	1240.7	1215.6	1203.0	1187.9
7.5°	1461.0	1463.2	1455.6	1448.9	1426.5	1411.7	1391.5	1365.6	1334.8	1303.5	1282.6
10°	1588.4	1605.6	1584.2	1569.5	1555.9	1530.2	1500.4	1463.2	1426.1	1382.6	1349.6
12.5°	1724.9	1733.4	1729.1	1715.3	1694.1	1655.1	1602.2	1561.2	1527.0	1454.6	1425.4
15°	1910.8	1942.8	1922.4	1875.2	1876.3	1839.1	1770.0	1694.1	1653.8	1590.4	1504.1
17.5°	2108.9	2112.9	2104.2	2065.0	2038.8	1987.7	1923.9	1851.2	1769.5	1692.8	1601.2
20°	2214.5	2211.3	2193.0	2172.6	2127.6	2087.8	2018.2	1937.0	1832.3	1756.9	1656.9
22.5°	2273.1	2267.9	2259.2	2242.1	2204.6	2161.9	2099.4	2010.7	1911.1	1807.2	1691.7
25°	2267.9	2274.7	2275.7	2271.0	2257.9	2232.3	2183.1	2112.4	2012.9	1879.4	1759.0
27.5°	2062.7	2072.3	2100.3	2125.1	2152.8	2181.1	2177.3	2142.2	2068.6	1953.4	1806.1
30°	1857.4	1836.5	1888.3	1953.8	1998.3	2076.8	2120.8	2123.4	2082.0	1983.1	1839.6
32.5°	1572.6	1595.7	1618.6	1699.1	1796.4	1884.6	1972.1	2042.6	2050.6	1984.8	1859.3
35°	1221.9	1250.7	1292.6	1334.4	1439.2	1529.2	1683.1	1817.1	1923.9	1938.1	1861.1
37.5°	984.6	998.9	1025.4	1067.3	1135.8	1242.6	1361.7	1531.1	1685.8	1800.9	1805.9
40°	860.7	864.9	894.7	926.6	982.1	1070.1	1177.4	1327.1	1512.4	1673.2	1740.2
42.5°	767.7	776.9	789.6	820.2	864.4	930.6	1030.4	1154.1	1324.0	1509.0	1640.1
45°	659.6	670.1	678.0	698.4	729.8	774.3	843.9	957.0	1086.3	1277.4	1453.8
47.5°	588.2	589.1	594.9	610.3	631.7	665.1	714.3	787.0	905.7	1060.6	1241.8
50°	537.1	545.5	547.6	559.6	576.4	601.0	641.8	703.6	801.0	937.1	1103.6
52.5°	501.1	503.6	509.5	518.2	532.8	552.0	587.4	635.8	712.2	828.2	981.3
55°	448.1	448.1	453.9	460.7	469.1	486.3	509.9	545.5	603.6	693.7	820.4
57.5°	399.1	401.7	405.8	407.9	415.0	426.5	446.1	473.2	516.5	585.8	686.5
60°	366.5	371.2	370.7	374.8	381.1	390.0	406.8	428.8	467.5	523.0	607.8
62.5°	338.0	337.7	337.6	342.6	348.9	357.4	368.2	387.3	420.2	469.4	541.6
65°	291.1	290.0	293.7	296.8	298.9	305.2	313.6	330.3	352.3	389.0	445.0
67.5°	249.4	246.4	248.4	249.4	253.0	257.9	265.7	276.1	293.6	323.0	365.2
70°	220.9	218.3	217.8	218.8	222.0	225.6	231.4	241.3	257.6	281.1	312.0
72.5°	191.6	189.8	189.7	192.0	193.5	195.9	200.0	209.1	222.0	239.7	268.5
75°	149.7	149.7	149.7	150.2	151.8	153.9	157.1	161.8	171.7	184.3	203.6
77.5°	112.2	112.1	111.5	111.4	113.7	114.7	115.4	119.8	125.3	133.8	147.9
80°	88.0	85.3	86.4	88.0	89.0	89.5	91.1	92.1	96.9	101.6	111.5
82.5°	65.3	63.1	63.3	65.8	66.0	66.5	68.1	69.5	71.3	75.6	80.9
85°	34.6	34.6	35.1	35.1	35.6	35.1	36.6	37.2	37.2	39.8	42.9
87.5°	16.0	15.1	15.5	15.8	15.4	15.7	16.0	16.3	16.7	17.0	17.1
90°	17.1	16.9	16.6	16.4	16.1	15.7	15.2	14.7	14.2	13.7	12.0
92.5°	18.9	18.8	18.6	18.5	18.3	17.8	17.0	16.2	15.4	14.6	13.4
95°	21.7	21.7	21.7	21.7	21.7	21.2	20.3	19.5	18.6	17.7	16.3
97.5°	23.5	23.4	23.2	23.1	23.0	22.4	21.4	20.4	19.4	18.4	27.5
100°	24.0	23.8	23.7	23.6	23.4	22.9	21.9	20.8	19.8	18.8	38.6
102.5°	24.4	24.2	24.0	23.7	23.5	25.0	28.1	31.2	34.4	37.5	59.1
105°	25.1	24.8	24.6	24.3	24.1	35.2	57.6	80.0	102.5	124.9	136.3
107.5°	78.8	95.7	112.6	129.5	146.5	163.1	179.6	196.0	212.5	228.9	227.1
110°	156.8	175.0	193.1	211.2	229.3	240.5	244.7	248.9	253.0	257.2	255.8



TEST NUMBER: P331964

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	269.1	272.9	276.7	280.6	284.4	286.3	286.2	286.1	286.1	286.0	284.6
115°	335.4	334.9	334.4	333.8	333.3	332.5	331.2	329.9	328.7	327.4	326.2
117.5°	372.6	372.5	372.4	372.3	372.2	371.6	370.6	369.6	368.6	367.5	367.0
120°	398.1	398.1	398.1	398.1	398.1	397.6	396.6	395.6	394.6	393.5	393.2
122.5°	423.2	423.1	423.0	422.9	422.8	422.4	421.7	421.0	420.3	419.6	419.1
125°	458.6	458.3	458.1	457.8	457.6	457.3	457.0	456.8	456.5	456.3	455.8
127.5°	492.6	492.8	493.1	493.3	493.6	493.5	493.1	492.7	492.3	491.9	491.3
130°	514.5	514.7	515.0	515.2	515.5	515.3	514.8	514.3	513.8	513.3	512.8
132.5°	534.5	534.9	535.2	535.6	536.0	535.9	535.4	534.9	534.4	533.9	533.4
135°	565.2	565.6	566.0	566.4	566.7	566.7	566.4	566.0	565.6	565.2	564.7
137.5°	594.1	594.3	594.6	594.8	595.1	594.9	594.3	593.7	593.1	592.5	592.2
140°	611.4	611.7	611.9	612.2	612.4	612.3	611.8	611.3	610.8	610.3	609.9
142.5°	627.4	627.7	628.1	628.5	628.8	628.8	628.4	628.0	627.6	627.2	626.8
145°	651.9	651.9	651.9	651.9	651.9	651.8	651.5	651.3	651.0	650.8	650.5
147.5°	670.2	670.8	671.3	671.9	672.5	672.7	672.4	672.2	671.9	671.7	671.4
150°	683.9	684.2	684.6	685.0	685.4	685.4	685.2	684.9	684.7	684.4	684.2
152.5°	694.8	695.4	696.0	696.6	697.1	697.2	696.7	696.3	695.8	695.4	695.2
155°	710.1	710.9	711.6	712.4	713.1	713.2	712.6	711.9	711.3	710.7	710.5
157.5°	723.0	724.0	725.0	725.9	726.9	727.1	726.3	725.5	724.8	724.0	724.1
160°	731.2	732.1	733.0	733.9	734.7	734.8	734.0	733.3	732.5	731.8	731.9
162.5°	739.0	739.7	740.5	741.3	742.1	742.1	741.2	740.3	739.5	738.6	738.7
165°	748.3	749.2	750.1	751.0	751.9	751.8	750.8	749.8	748.8	747.7	747.9
167.5°	755.0	756.1	757.1	758.1	759.1	759.1	758.1	757.1	756.1	755.0	755.0
170°	759.1	760.2	761.2	762.2	763.2	763.2	762.2	761.2	760.2	759.1	759.1
172.5°	761.4	762.5	763.7	764.8	765.9	765.9	764.9	763.9	762.9	761.9	761.8
175°	764.8	765.9	766.9	767.9	768.9	769.0	768.1	767.2	766.3	765.4	765.3
177.5°	765.9	766.9	767.9	768.9	769.9	770.0	769.2	768.4	767.6	766.8	766.7
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P331964

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1114.0	1110.7	1107.3	1101.5	1096.5	1089.3	1087.2	1084.7	1077.2	1070.5	1065.5
5°	1182.1	1169.5	1151.2	1134.5	1120.9	1102.5	1092.1	1081.1	1065.4	1051.2	1039.7
7.5°	1253.3	1228.6	1200.1	1169.3	1140.6	1113.0	1090.7	1070.8	1048.8	1028.0	1011.8
10°	1309.8	1274.2	1234.5	1191.5	1154.9	1119.3	1089.4	1063.3	1035.0	1010.4	990.0
12.5°	1374.3	1321.6	1266.7	1214.6	1171.2	1121.8	1085.7	1052.4	1020.3	990.7	967.8
15°	1450.7	1383.7	1318.7	1247.0	1181.1	1119.3	1076.4	1034.5	997.3	966.9	937.6
17.5°	1520.2	1444.3	1358.7	1271.5	1191.9	1118.7	1058.6	1011.2	964.7	927.6	898.4
20°	1559.6	1473.2	1376.3	1285.8	1197.8	1116.1	1050.2	993.6	943.4	904.1	871.1
22.5°	1593.5	1492.4	1392.2	1295.4	1197.4	1109.4	1034.7	976.5	922.0	883.6	848.5
25°	1628.7	1507.7	1407.2	1293.6	1184.2	1093.1	1009.3	943.4	888.9	843.9	807.8
27.5°	1658.8	1506.7	1387.4	1265.2	1163.5	1072.2	982.7	912.0	854.2	805.3	768.6
30°	1678.9	1508.8	1366.9	1246.0	1143.4	1049.1	962.2	891.0	830.3	780.6	746.0
32.5°	1691.5	1507.5	1348.1	1219.2	1111.5	1028.2	940.0	866.3	803.9	755.0	721.7
35°	1698.8	1498.3	1315.6	1163.8	1060.1	979.0	905.2	828.7	763.3	717.7	680.1
37.5°	1684.2	1478.9	1277.9	1110.4	996.9	917.0	854.9	789.8	727.2	677.0	644.6
40°	1661.1	1466.4	1248.6	1072.7	953.3	876.4	823.5	759.6	697.8	650.2	619.8
42.5°	1617.1	1440.8	1216.3	1030.8	908.1	831.1	782.5	729.1	670.6	625.9	595.6
45°	1509.8	1385.2	1168.0	968.0	841.3	761.7	718.8	680.1	627.2	583.7	557.5
47.5°	1360.9	1301.6	1098.0	901.7	771.6	695.0	650.4	619.2	580.6	545.5	520.4
50°	1257.5	1232.9	1050.7	856.5	725.1	650.2	607.3	579.0	551.3	516.2	493.2
52.5°	1138.1	1153.3	995.4	809.6	677.7	604.1	563.7	541.3	516.1	487.3	467.2
55°	970.1	1025.0	899.9	730.8	607.3	537.1	498.9	479.0	464.4	442.9	425.6
57.5°	812.7	882.7	796.7	649.7	538.1	477.6	440.9	419.2	409.8	398.6	385.0
60°	719.3	788.4	723.0	595.2	491.6	434.0	401.5	383.2	373.8	365.9	354.4
62.5°	636.0	705.9	650.9	540.0	445.9	392.5	364.3	346.4	339.0	334.9	325.1
65°	521.4	581.6	545.0	453.9	380.6	333.5	307.8	295.3	288.5	286.9	280.6
67.5°	424.4	470.2	443.5	376.5	318.8	278.1	256.3	245.6	240.4	239.9	235.2
70°	360.7	403.6	383.2	322.5	272.8	240.8	222.0	212.5	209.4	208.9	206.3
72.5°	311.3	341.2	325.0	274.3	235.9	206.9	193.1	183.2	179.7	180.4	178.6
75°	230.3	252.9	243.4	208.4	177.5	158.6	147.1	140.8	137.7	139.3	137.2
77.5°	165.7	180.0	171.5	147.2	128.2	114.5	106.1	102.2	99.4	99.3	98.3
80°	125.1	133.5	128.8	114.1	98.4	86.9	80.1	77.5	75.9	75.4	74.9
82.5°	89.1	96.2	90.7	80.6	69.9	63.0	59.2	55.7	54.6	54.9	54.3
85°	45.0	47.6	45.5	39.3	35.1	31.9	29.8	28.3	27.2	27.7	26.7
87.5°	17.6	17.7	16.1	14.1	13.0	11.5	11.3	10.2	9.6	9.8	9.7
90°	10.4	8.7	7.1	5.6	4.4	3.1	1.8	0.6	1.8	3.1	4.4
92.5°	12.1	10.9	9.6	9.2	9.5	9.9	10.3	10.6	10.3	9.9	9.5
95°	14.9	13.5	12.1	14.0	19.2	24.4	29.6	34.8	29.6	24.4	19.2
97.5°	36.6	45.7	54.9	60.6	62.9	65.3	67.6	69.9	67.6	65.3	62.9
100°	58.4	78.1	97.9	106.5	104.0	101.5	98.9	96.4	98.9	101.5	104.0
102.5°	80.7	102.3	123.9	133.8	132.0	130.2	128.3	126.5	128.3	130.2	132.0
105°	147.7	159.1	170.5	175.5	174.1	172.8	171.4	170.0	171.4	172.8	174.1
107.5°	225.3	223.5	221.7	220.3	219.2	218.1	216.9	215.8	216.9	218.1	219.2
110°	254.4	253.0	251.7	250.4	249.4	248.4	247.4	246.4	247.4	248.4	249.4



TEST NUMBER: P331964

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	283.2	281.8	280.4	279.2	278.3	277.4	276.5	275.6	276.5	277.4	278.3
115°	325.1	324.0	322.8	321.9	321.1	320.3	319.6	318.8	319.6	320.3	321.1
117.5°	366.4	365.8	365.2	364.4	363.5	362.6	361.6	360.7	361.6	362.6	363.5
120°	392.8	392.4	392.0	391.3	390.1	389.0	387.8	386.7	387.8	389.0	390.1
122.5°	418.6	418.1	417.6	416.9	416.0	415.0	414.1	413.2	414.1	415.0	416.0
125°	455.3	454.8	454.3	453.5	452.5	451.5	450.5	449.4	450.5	451.5	452.5
127.5°	490.7	490.0	489.4	488.6	487.6	486.6	485.6	484.6	485.6	486.6	487.6
130°	512.3	511.8	511.3	510.5	509.5	508.5	507.5	506.5	507.5	508.5	509.5
132.5°	533.0	532.6	532.2	531.5	530.5	529.5	528.5	527.5	528.5	529.5	530.5
135°	564.2	563.7	563.2	562.6	561.8	561.0	560.3	559.5	560.3	561.0	561.8
137.5°	591.9	591.6	591.4	590.7	589.8	588.8	587.9	586.9	587.9	588.8	589.8
140°	609.5	609.1	608.8	608.2	607.4	606.7	605.9	605.1	605.9	606.7	607.4
142.5°	626.4	626.0	625.6	625.1	624.3	623.6	622.8	622.0	622.8	623.6	624.3
145°	650.3	650.0	649.8	649.2	648.3	647.4	646.5	645.6	646.5	647.4	648.3
147.5°	671.1	670.9	670.6	670.2	669.6	669.1	668.5	667.9	668.5	669.1	669.6
150°	683.9	683.7	683.4	683.1	682.7	682.3	682.0	681.6	682.0	682.3	682.7
152.5°	695.1	694.9	694.8	694.6	694.4	694.2	694.1	693.9	694.1	694.2	694.4
155°	710.4	710.3	710.2	710.2	710.5	710.7	711.0	711.2	711.0	710.7	710.5
157.5°	724.3	724.4	724.5	724.6	724.6	724.6	724.7	724.7	724.7	724.6	724.6
160°	732.0	732.1	732.3	732.4	732.5	732.7	732.8	732.9	732.8	732.7	732.5
162.5°	738.9	739.0	739.1	739.3	739.7	740.0	740.3	740.7	740.3	740.0	739.7
165°	748.0	748.1	748.2	748.5	748.9	749.3	749.6	750.0	749.6	749.3	748.9
167.5°	755.0	755.0	755.0	755.3	755.8	756.3	756.8	757.3	756.8	756.3	755.8
170°	759.1	759.1	759.1	759.4	759.9	760.4	760.9	761.4	760.9	760.4	759.9
172.5°	761.7	761.6	761.5	761.7	762.3	762.9	763.6	764.2	763.6	762.9	762.3
175°	765.2	765.0	764.9	765.2	765.8	766.4	767.1	767.7	767.1	766.4	765.8
177.5°	766.6	766.5	766.4	766.6	767.1	767.6	768.1	768.6	768.1	767.6	767.1
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P331964

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1062.5	1059.6	1055.4	1049.1	1044.1	1036.1	1036.1	1037.4	1037.4	1037.0	1036.1
5°	1030.3	1022.4	1013.0	1002.0	990.5	979.0	976.9	972.7	969.6	967.5	964.8
7.5°	996.3	982.3	968.6	953.2	939.2	927.6	919.5	912.8	908.5	903.9	900.6
10°	973.2	955.9	939.7	923.5	905.7	891.6	882.7	876.4	871.7	867.5	865.4
12.5°	946.0	926.2	908.3	892.9	873.4	858.9	850.4	847.5	841.9	833.1	828.5
15°	906.2	887.9	866.4	842.9	833.4	815.6	805.7	801.0	797.8	791.0	788.9
17.5°	872.2	848.2	824.1	806.5	789.0	774.6	769.0	763.2	759.0	753.4	751.8
20°	845.0	823.5	801.5	782.7	764.3	748.6	743.9	739.7	735.5	732.9	730.8
22.5°	817.3	795.9	777.6	760.0	740.5	730.2	725.1	720.5	717.5	715.8	713.7
25°	778.5	759.6	739.2	723.5	707.8	701.0	697.8	695.2	693.1	690.5	690.0
27.5°	743.7	723.2	706.6	692.0	680.7	675.0	672.0	670.7	671.2	672.1	672.7
30°	717.7	698.9	685.3	672.7	662.3	657.0	656.5	656.5	658.6	659.1	660.2
32.5°	693.9	678.4	664.8	652.6	644.7	641.1	643.1	643.1	644.8	646.1	648.0
35°	659.1	645.5	635.0	624.6	617.8	619.3	620.4	621.4	624.0	627.2	629.3
37.5°	625.9	614.1	603.2	595.0	591.9	594.7	597.2	599.4	602.5	604.9	607.0
40°	602.0	593.1	582.7	575.3	576.4	578.0	580.1	582.7	585.3	586.9	589.0
42.5°	579.8	570.5	562.6	556.5	558.0	560.0	561.2	562.6	565.6	568.4	569.7
45°	546.0	538.7	531.4	527.7	528.8	529.8	530.8	532.4	535.0	537.1	537.7
47.5°	508.0	502.9	498.0	494.4	496.1	495.7	497.0	500.4	501.2	502.5	505.4
50°	483.7	479.0	473.3	472.2	472.2	472.2	472.7	476.9	476.9	479.0	481.1
52.5°	456.9	453.9	450.2	448.3	447.5	447.5	449.7	451.8	452.6	455.6	457.7
55°	417.2	414.1	411.0	409.4	408.3	409.4	413.6	414.6	417.2	418.8	420.4
57.5°	375.9	373.5	371.0	370.1	369.9	371.3	373.6	376.7	377.4	382.2	384.6
60°	348.7	345.0	342.9	342.9	341.9	346.6	345.5	350.8	351.8	354.9	358.6
62.5°	320.6	315.7	314.8	314.8	316.3	317.7	319.1	321.4	324.2	328.1	331.0
65°	275.4	272.8	276.4	275.9	274.8	278.0	278.0	280.6	283.7	287.4	293.2
67.5°	232.5	231.2	231.5	231.5	233.1	234.9	236.3	238.6	242.4	246.3	250.0
70°	203.6	205.2	202.6	204.7	206.3	206.8	207.8	211.0	215.2	217.8	222.0
72.5°	175.6	175.5	175.8	176.6	178.2	179.1	180.2	183.8	188.4	190.6	193.9
75°	135.1	134.5	136.1	136.1	138.7	139.8	140.8	142.4	146.6	149.7	152.3
77.5°	98.6	99.3	98.9	100.7	100.0	100.2	103.4	105.0	105.4	111.6	113.0
80°	74.3	75.4	75.9	76.4	77.0	75.9	79.6	81.1	81.1	84.8	87.4
82.5°	53.4	54.0	55.4	55.9	56.0	57.1	57.4	58.5	59.8	61.4	64.8
85°	26.7	28.3	28.8	28.3	28.8	27.7	29.3	29.8	30.4	30.4	30.4
87.5°	9.5	10.2	10.1	10.9	10.8	11.5	11.6	10.9	11.0	12.4	10.8
90°	5.6	7.1	8.7	10.4	12.0	13.7	14.2	14.7	15.2	15.7	16.1
92.5°	9.2	9.6	10.9	12.1	13.4	14.6	15.4	16.2	17.0	17.8	18.3
95°	14.0	12.1	13.5	14.9	16.3	17.7	18.6	19.5	20.3	21.2	21.7
97.5°	60.6	54.9	45.7	36.6	27.5	18.4	19.4	20.4	21.4	22.4	23.0
100°	106.5	97.9	78.1	58.4	38.6	18.8	19.8	20.8	21.9	22.9	23.4
102.5°	133.8	123.9	102.3	80.7	59.1	37.5	34.4	31.2	28.1	25.0	23.5
105°	175.5	170.5	159.1	147.7	136.3	124.9	102.5	80.0	57.6	35.2	24.1
107.5°	220.3	221.7	223.5	225.3	227.1	228.9	212.5	196.0	179.6	163.1	146.5
110°	250.4	251.7	253.0	254.4	255.8	257.2	253.0	248.9	244.7	240.5	229.3



TEST NUMBER: P331964

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	279.2	280.4	281.8	283.2	284.6	286.0	286.1	286.1	286.2	286.3	284.4
115°	321.9	322.8	324.0	325.1	326.2	327.4	328.7	329.9	331.2	332.5	333.3
117.5°	364.4	365.2	365.8	366.4	367.0	367.5	368.6	369.6	370.6	371.6	372.2
120°	391.3	392.0	392.4	392.8	393.2	393.5	394.6	395.6	396.6	397.6	398.1
122.5°	416.9	417.6	418.1	418.6	419.1	419.6	420.3	421.0	421.7	422.4	422.8
125°	453.5	454.3	454.8	455.3	455.8	456.3	456.5	456.8	457.0	457.3	457.6
127.5°	488.6	489.4	490.0	490.7	491.3	491.9	492.3	492.7	493.1	493.5	493.6
130°	510.5	511.3	511.8	512.3	512.8	513.3	513.8	514.3	514.8	515.3	515.5
132.5°	531.5	532.2	532.6	533.0	533.4	533.9	534.4	534.9	535.4	535.9	536.0
135°	562.6	563.2	563.7	564.2	564.7	565.2	565.6	566.0	566.4	566.7	566.7
137.5°	590.7	591.4	591.6	591.9	592.2	592.5	593.1	593.7	594.3	594.9	595.1
140°	608.2	608.8	609.1	609.5	609.9	610.3	610.8	611.3	611.8	612.3	612.4
142.5°	625.1	625.6	626.0	626.4	626.8	627.2	627.6	628.0	628.4	628.8	628.8
145°	649.2	649.8	650.0	650.3	650.5	650.8	651.0	651.3	651.5	651.8	651.9
147.5°	670.2	670.6	670.9	671.1	671.4	671.7	671.9	672.2	672.4	672.7	672.5
150°	683.1	683.4	683.7	683.9	684.2	684.4	684.7	684.9	685.2	685.4	685.4
152.5°	694.6	694.8	694.9	695.1	695.2	695.4	695.8	696.3	696.7	697.2	697.1
155°	710.2	710.2	710.3	710.4	710.5	710.7	711.3	711.9	712.6	713.2	713.1
157.5°	724.6	724.5	724.4	724.3	724.1	724.0	724.8	725.5	726.3	727.1	726.9
160°	732.4	732.3	732.1	732.0	731.9	731.8	732.5	733.3	734.0	734.8	734.7
162.5°	739.3	739.1	739.0	738.9	738.7	738.6	739.5	740.3	741.2	742.1	742.1
165°	748.5	748.2	748.1	748.0	747.9	747.7	748.8	749.8	750.8	751.8	751.9
167.5°	755.3	755.0	755.0	755.0	755.0	755.0	756.1	757.1	758.1	759.1	759.1
170°	759.4	759.1	759.1	759.1	759.1	759.1	760.2	761.2	762.2	763.2	763.2
172.5°	761.7	761.5	761.6	761.7	761.8	761.9	762.9	763.9	764.9	765.9	765.9
175°	765.2	764.9	765.0	765.2	765.3	765.4	766.3	767.2	768.1	769.0	768.9
177.5°	766.6	766.4	766.5	766.6	766.7	766.8	767.6	768.4	769.2	770.0	769.9
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P331964

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1033.2	1032.8	1035.7	1033.6	1035.7	1032.8	1033.2	1036.1	1037.0	1037.4	1037.4
5°	961.7	963.3	958.0	958.0	958.0	963.3	961.7	964.8	967.5	969.6	972.7
7.5°	898.0	895.7	895.9	893.1	895.9	895.7	898.0	900.6	903.9	908.5	912.8
10°	859.1	856.0	854.9	855.4	854.9	856.0	859.1	865.4	867.5	871.7	876.4
12.5°	826.8	826.2	819.3	819.4	819.3	826.2	826.8	828.5	833.1	841.9	847.5
15°	788.9	779.0	777.9	781.1	777.9	779.0	788.9	788.9	791.0	797.8	801.0
17.5°	750.9	745.7	746.0	744.4	746.0	745.7	750.9	751.8	753.4	759.0	763.2
20°	730.8	727.7	727.2	723.5	727.2	727.7	730.8	730.8	732.9	735.5	739.7
22.5°	712.4	711.4	711.7	707.6	711.7	711.4	712.4	713.7	715.8	717.5	720.5
25°	689.5	692.1	690.0	690.0	690.0	692.1	689.5	690.0	690.5	693.1	695.2
27.5°	674.0	673.9	672.8	672.8	672.8	673.9	674.0	672.7	672.1	671.2	670.7
30°	662.3	661.7	662.8	662.8	662.8	661.7	662.3	660.2	659.1	658.6	656.5
32.5°	650.5	651.3	651.5	651.9	651.5	651.3	650.5	648.0	646.1	644.8	643.1
35°	632.4	632.9	634.5	633.5	634.5	632.9	632.4	629.3	627.2	624.0	621.4
37.5°	607.9	610.3	609.8	610.6	609.8	610.3	607.9	607.0	604.9	602.5	599.4
40°	589.5	591.1	590.5	590.5	590.5	591.1	589.5	589.0	586.9	585.3	582.7
42.5°	570.6	571.8	570.4	569.6	570.4	571.8	570.6	569.7	568.4	565.6	562.6
45°	539.7	538.7	540.3	538.2	540.3	538.7	539.7	537.7	537.1	535.0	532.4
47.5°	505.2	506.2	506.7	508.2	506.7	506.2	505.2	505.4	502.5	501.2	500.4
50°	482.2	485.3	485.3	484.8	485.3	485.3	482.2	481.1	479.0	476.9	476.9
52.5°	459.5	461.0	463.1	463.0	463.1	461.0	459.5	457.7	455.6	452.6	451.8
55°	424.6	425.6	426.7	427.2	426.7	425.6	424.6	420.4	418.8	417.2	414.6
57.5°	388.3	387.9	390.4	391.2	390.4	387.9	388.3	384.6	382.2	377.4	376.7
60°	362.8	362.8	367.0	368.6	367.0	362.8	362.8	358.6	354.9	351.8	350.8
62.5°	335.6	337.3	341.4	339.2	341.4	337.3	335.6	331.0	328.1	324.2	321.4
65°	295.8	300.0	299.5	301.5	299.5	300.0	295.8	293.2	287.4	283.7	280.6
67.5°	254.2	256.8	260.6	260.9	260.6	256.8	254.2	250.0	246.3	242.4	238.6
70°	226.2	228.8	230.9	232.4	230.9	228.8	226.2	222.0	217.8	215.2	211.0
72.5°	198.9	200.3	205.3	203.1	205.3	200.3	198.9	193.9	190.6	188.4	183.8
75°	156.0	159.7	162.8	161.2	162.8	159.7	156.0	152.3	149.7	146.6	142.4
77.5°	115.4	119.0	120.5	119.2	120.5	119.0	115.4	113.0	111.6	105.4	105.0
80°	91.1	90.6	93.7	93.2	93.7	90.6	91.1	87.4	84.8	81.1	81.1
82.5°	66.8	66.3	67.7	68.1	67.7	66.3	66.8	64.8	61.4	59.8	58.5
85°	32.5	34.0	31.9	31.4	31.9	34.0	32.5	30.4	30.4	30.4	29.8
87.5°	10.8	10.9	10.5	10.1	10.5	10.9	10.8	10.8	12.4	11.0	10.9
90°	16.4	16.6	16.9	17.1	16.9	16.6	16.4	16.1	15.7	15.2	14.7
92.5°	18.5	18.6	18.8	18.9	18.8	18.6	18.5	18.3	17.8	17.0	16.2
95°	21.7	21.7	21.7	21.7	21.7	21.7	21.7	21.7	21.2	20.3	19.5
97.5°	23.1	23.2	23.4	23.5	23.4	23.2	23.1	23.0	22.4	21.4	20.4
100°	23.6	23.7	23.8	24.0	23.8	23.7	23.6	23.4	22.9	21.9	20.8
102.5°	23.7	24.0	24.2	24.4	24.2	24.0	23.7	23.5	25.0	28.1	31.2
105°	24.3	24.6	24.8	25.1	24.8	24.6	24.3	24.1	35.2	57.6	80.0
107.5°	129.5	112.6	95.7	78.8	95.7	112.6	129.5	146.5	163.1	179.6	196.0
110°	211.2	193.1	175.0	156.8	175.0	193.1	211.2	229.3	240.5	244.7	248.9



TEST NUMBER: P331964

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	280.6	276.7	272.9	269.1	272.9	276.7	280.6	284.4	286.3	286.2	286.1
115°	333.8	334.4	334.9	335.4	334.9	334.4	333.8	333.3	332.5	331.2	329.9
117.5°	372.3	372.4	372.5	372.6	372.5	372.4	372.3	372.2	371.6	370.6	369.6
120°	398.1	398.1	398.1	398.1	398.1	398.1	398.1	398.1	397.6	396.6	395.6
122.5°	422.9	423.0	423.1	423.2	423.1	423.0	422.9	422.8	422.4	421.7	421.0
125°	457.8	458.1	458.3	458.6	458.3	458.1	457.8	457.6	457.3	457.0	456.8
127.5°	493.3	493.1	492.8	492.6	492.8	493.1	493.3	493.6	493.5	493.1	492.7
130°	515.2	515.0	514.7	514.5	514.7	515.0	515.2	515.5	515.3	514.8	514.3
132.5°	535.6	535.2	534.9	534.5	534.9	535.2	535.6	536.0	535.9	535.4	534.9
135°	566.4	566.0	565.6	565.2	565.6	566.0	566.4	566.7	566.7	566.4	566.0
137.5°	594.8	594.6	594.3	594.1	594.3	594.6	594.8	595.1	594.9	594.3	593.7
140°	612.2	611.9	611.7	611.4	611.7	611.9	612.2	612.4	612.3	611.8	611.3
142.5°	628.5	628.1	627.7	627.4	627.7	628.1	628.5	628.8	628.8	628.4	628.0
145°	651.9	651.9	651.9	651.9	651.9	651.9	651.9	651.9	651.8	651.5	651.3
147.5°	671.9	671.3	670.8	670.2	670.8	671.3	671.9	672.5	672.7	672.4	672.2
150°	685.0	684.6	684.2	683.9	684.2	684.6	685.0	685.4	685.4	685.2	684.9
152.5°	696.6	696.0	695.4	694.8	695.4	696.0	696.6	697.1	697.2	696.7	696.3
155°	712.4	711.6	710.9	710.1	710.9	711.6	712.4	713.1	713.2	712.6	711.9
157.5°	725.9	725.0	724.0	723.0	724.0	725.0	725.9	726.9	727.1	726.3	725.5
160°	733.9	733.0	732.1	731.2	732.1	733.0	733.9	734.7	734.8	734.0	733.3
162.5°	741.3	740.5	739.7	739.0	739.7	740.5	741.3	742.1	742.1	741.2	740.3
165°	751.0	750.1	749.2	748.3	749.2	750.1	751.0	751.9	751.8	750.8	749.8
167.5°	758.1	757.1	756.1	755.0	756.1	757.1	758.1	759.1	759.1	758.1	757.1
170°	762.2	761.2	760.2	759.1	760.2	761.2	762.2	763.2	763.2	762.2	761.2
172.5°	764.8	763.7	762.5	761.4	762.5	763.7	764.8	765.9	765.9	764.9	763.9
175°	767.9	766.9	765.9	764.8	765.9	766.9	767.9	768.9	769.0	768.1	767.2
177.5°	768.9	767.9	766.9	765.9	766.9	767.9	768.9	769.9	770.0	769.2	768.4
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P331964

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1036.1	1036.1	1044.1	1049.1	1055.4	1059.6	1062.5	1065.5	1070.5	1077.2	1084.7
5°	976.9	979.0	990.5	1002.0	1013.0	1022.4	1030.3	1039.7	1051.2	1065.4	1081.1
7.5°	919.5	927.6	939.2	953.2	968.6	982.3	996.3	1011.8	1028.0	1048.8	1070.8
10°	882.7	891.6	905.7	923.5	939.7	955.9	973.2	990.0	1010.4	1035.0	1063.3
12.5°	850.4	858.9	873.4	892.9	908.3	926.2	946.0	967.8	990.7	1020.3	1052.4
15°	805.7	815.6	833.4	842.9	866.4	887.9	906.2	937.6	966.9	997.3	1034.5
17.5°	769.0	774.6	789.0	806.5	824.1	848.2	872.2	898.4	927.6	964.7	1011.2
20°	743.9	748.6	764.3	782.7	801.5	823.5	845.0	871.1	904.1	943.4	993.6
22.5°	725.1	730.2	740.5	760.0	777.6	795.9	817.3	848.5	883.6	922.0	976.5
25°	697.8	701.0	707.8	723.5	739.2	759.6	778.5	807.8	843.9	888.9	943.4
27.5°	672.0	675.0	680.7	692.0	706.6	723.2	743.7	768.6	805.3	854.2	912.0
30°	656.5	657.0	662.3	672.7	685.3	698.9	717.7	746.0	780.6	830.3	891.0
32.5°	643.1	641.1	644.7	652.6	664.8	678.4	693.9	721.7	755.0	803.9	866.3
35°	620.4	619.3	617.8	624.6	635.0	645.5	659.1	680.1	717.7	763.3	828.7
37.5°	597.2	594.7	591.9	595.0	603.2	614.1	625.9	644.6	677.0	727.2	789.8
40°	580.1	578.0	576.4	575.3	582.7	593.1	602.0	619.8	650.2	697.8	759.6
42.5°	561.2	560.0	558.0	556.5	562.6	570.5	579.8	595.6	625.9	670.6	729.1
45°	530.8	529.8	528.8	527.7	531.4	538.7	546.0	557.5	583.7	627.2	680.1
47.5°	497.0	495.7	496.1	494.4	498.0	502.9	508.0	520.4	545.5	580.6	619.2
50°	472.7	472.2	472.2	472.2	473.3	479.0	483.7	493.2	516.2	551.3	579.0
52.5°	449.7	447.5	447.5	448.3	450.2	453.9	456.9	467.2	487.3	516.1	541.3
55°	413.6	409.4	408.3	409.4	411.0	414.1	417.2	425.6	442.9	464.4	479.0
57.5°	373.6	371.3	369.9	370.1	371.0	373.5	375.9	385.0	398.6	409.8	419.2
60°	345.5	346.6	341.9	342.9	342.9	345.0	348.7	354.4	365.9	373.8	383.2
62.5°	319.1	317.7	316.3	314.8	314.8	315.7	320.6	325.1	334.9	339.0	346.4
65°	278.0	278.0	274.8	275.9	276.4	272.8	275.4	280.6	286.9	288.5	295.3
67.5°	236.3	234.9	233.1	231.5	231.5	231.2	232.5	235.2	239.9	240.4	245.6
70°	207.8	206.8	206.3	204.7	202.6	205.2	203.6	206.3	208.9	209.4	212.5
72.5°	180.2	179.1	178.2	176.6	175.8	175.5	175.6	178.6	180.4	179.7	183.2
75°	140.8	139.8	138.7	136.1	136.1	134.5	135.1	137.2	139.3	137.7	140.8
77.5°	103.4	100.2	100.0	100.7	98.9	99.3	98.6	98.3	99.3	99.4	102.2
80°	79.6	75.9	77.0	76.4	75.9	75.4	74.3	74.9	75.4	75.9	77.5
82.5°	57.4	57.1	56.0	55.9	55.4	54.0	53.4	54.3	54.9	54.6	55.7
85°	29.3	27.7	28.8	28.3	28.8	28.3	26.7	26.7	27.7	27.2	28.3
87.5°	11.6	11.5	10.8	10.9	10.1	10.2	9.5	9.7	9.8	9.6	10.2
90°	14.2	13.7	12.0	10.4	8.7	7.1	5.6	4.4	3.1	1.8	0.6
92.5°	15.4	14.6	13.4	12.1	10.9	9.6	9.2	9.5	9.9	10.3	10.6
95°	18.6	17.7	16.3	14.9	13.5	12.1	14.0	19.2	24.4	29.6	34.8
97.5°	19.4	18.4	27.5	36.6	45.7	54.9	60.6	62.9	65.3	67.6	69.9
100°	19.8	18.8	38.6	58.4	78.1	97.9	106.5	104.0	101.5	98.9	96.4
102.5°	34.4	37.5	59.1	80.7	102.3	123.9	133.8	132.0	130.2	128.3	126.5
105°	102.5	124.9	136.3	147.7	159.1	170.5	175.5	174.1	172.8	171.4	170.0
107.5°	212.5	228.9	227.1	225.3	223.5	221.7	220.3	219.2	218.1	216.9	215.8
110°	253.0	257.2	255.8	254.4	253.0	251.7	250.4	249.4	248.4	247.4	246.4



TEST NUMBER: P331964

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	286.1	286.0	284.6	283.2	281.8	280.4	279.2	278.3	277.4	276.5	275.6
115°	328.7	327.4	326.2	325.1	324.0	322.8	321.9	321.1	320.3	319.6	318.8
117.5°	368.6	367.5	367.0	366.4	365.8	365.2	364.4	363.5	362.6	361.6	360.7
120°	394.6	393.5	393.2	392.8	392.4	392.0	391.3	390.1	389.0	387.8	386.7
122.5°	420.3	419.6	419.1	418.6	418.1	417.6	416.9	416.0	415.0	414.1	413.2
125°	456.5	456.3	455.8	455.3	454.8	454.3	453.5	452.5	451.5	450.5	449.4
127.5°	492.3	491.9	491.3	490.7	490.0	489.4	488.6	487.6	486.6	485.6	484.6
130°	513.8	513.3	512.8	512.3	511.8	511.3	510.5	509.5	508.5	507.5	506.5
132.5°	534.4	533.9	533.4	533.0	532.6	532.2	531.5	530.5	529.5	528.5	527.5
135°	565.6	565.2	564.7	564.2	563.7	563.2	562.6	561.8	561.0	560.3	559.5
137.5°	593.1	592.5	592.2	591.9	591.6	591.4	590.7	589.8	588.8	587.9	586.9
140°	610.8	610.3	609.9	609.5	609.1	608.8	608.2	607.4	606.7	605.9	605.1
142.5°	627.6	627.2	626.8	626.4	626.0	625.6	625.1	624.3	623.6	622.8	622.0
145°	651.0	650.8	650.5	650.3	650.0	649.8	649.2	648.3	647.4	646.5	645.6
147.5°	671.9	671.7	671.4	671.1	670.9	670.6	670.2	669.6	669.1	668.5	667.9
150°	684.7	684.4	684.2	683.9	683.7	683.4	683.1	682.7	682.3	682.0	681.6
152.5°	695.8	695.4	695.2	695.1	694.9	694.8	694.6	694.4	694.2	694.1	693.9
155°	711.3	710.7	710.5	710.4	710.3	710.2	710.2	710.5	710.7	711.0	711.2
157.5°	724.8	724.0	724.1	724.3	724.4	724.5	724.6	724.6	724.6	724.7	724.7
160°	732.5	731.8	731.9	732.0	732.1	732.3	732.4	732.5	732.7	732.8	732.9
162.5°	739.5	738.6	738.7	738.9	739.0	739.1	739.3	739.7	740.0	740.3	740.7
165°	748.8	747.7	747.9	748.0	748.1	748.2	748.5	748.9	749.3	749.6	750.0
167.5°	756.1	755.0	755.0	755.0	755.0	755.0	755.3	755.8	756.3	756.8	757.3
170°	760.2	759.1	759.1	759.1	759.1	759.1	759.4	759.9	760.4	760.9	761.4
172.5°	762.9	761.9	761.8	761.7	761.6	761.5	761.7	762.3	762.9	763.6	764.2
175°	766.3	765.4	765.3	765.2	765.0	764.9	765.2	765.8	766.4	767.1	767.7
177.5°	767.6	766.8	766.7	766.6	766.5	766.4	766.6	767.1	767.6	768.1	768.6
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P331964

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1087.2	1089.3	1096.5	1101.5	1107.3	1110.7	1114.0	1116.6	1119.9	1120.7	1132.9
5°	1092.1	1102.5	1120.9	1134.5	1151.2	1169.5	1182.1	1187.9	1203.0	1215.6	1240.7
7.5°	1090.7	1113.0	1140.6	1169.3	1200.1	1228.6	1253.3	1282.6	1303.5	1334.8	1365.6
10°	1089.4	1119.3	1154.9	1191.5	1234.5	1274.2	1309.8	1349.6	1382.6	1426.1	1463.2
12.5°	1085.7	1121.8	1171.2	1214.6	1266.7	1321.6	1374.3	1425.4	1454.6	1527.0	1561.2
15°	1076.4	1119.3	1181.1	1247.0	1318.7	1383.7	1450.7	1504.1	1590.4	1653.8	1694.1
17.5°	1058.6	1118.7	1191.9	1271.5	1358.7	1444.3	1520.2	1601.2	1692.8	1769.5	1851.2
20°	1050.2	1116.1	1197.8	1285.8	1376.3	1473.2	1559.6	1656.9	1756.9	1832.3	1937.0
22.5°	1034.7	1109.4	1197.4	1295.4	1392.2	1492.4	1593.5	1691.7	1807.2	1911.1	2010.7
25°	1009.3	1093.1	1184.2	1293.6	1407.2	1507.7	1628.7	1759.0	1879.4	2012.9	2112.4
27.5°	982.7	1072.2	1163.5	1265.2	1387.4	1506.7	1658.8	1806.1	1953.4	2068.6	2142.2
30°	962.2	1049.1	1143.4	1246.0	1366.9	1508.8	1678.9	1839.6	1983.1	2082.0	2123.4
32.5°	940.0	1028.2	1111.5	1219.2	1348.1	1507.5	1691.5	1859.3	1984.8	2050.6	2042.6
35°	905.2	979.0	1060.1	1163.8	1315.6	1498.3	1698.8	1861.1	1938.1	1923.9	1817.1
37.5°	854.9	917.0	996.9	1110.4	1277.9	1478.9	1684.2	1805.9	1800.9	1685.8	1531.1
40°	823.5	876.4	953.3	1072.7	1248.6	1466.4	1661.1	1740.2	1673.2	1512.4	1327.1
42.5°	782.5	831.1	908.1	1030.8	1216.3	1440.8	1617.1	1640.1	1509.0	1324.0	1154.1
45°	718.8	761.7	841.3	968.0	1168.0	1385.2	1509.8	1453.8	1277.4	1086.3	957.0
47.5°	650.4	695.0	771.6	901.7	1098.0	1301.6	1360.9	1241.8	1060.6	905.7	787.0
50°	607.3	650.2	725.1	856.5	1050.7	1232.9	1257.5	1103.6	937.1	801.0	703.6
52.5°	563.7	604.1	677.7	809.6	995.4	1153.3	1138.1	981.3	828.2	712.2	635.8
55°	498.9	537.1	607.3	730.8	899.9	1025.0	970.1	820.4	693.7	603.6	545.5
57.5°	440.9	477.6	538.1	649.7	796.7	882.7	812.7	686.5	585.8	516.5	473.2
60°	401.5	434.0	491.6	595.2	723.0	788.4	719.3	607.8	523.0	467.5	428.8
62.5°	364.3	392.5	445.9	540.0	650.9	705.9	636.0	541.6	469.4	420.2	387.3
65°	307.8	333.5	380.6	453.9	545.0	581.6	521.4	445.0	389.0	352.3	330.3
67.5°	256.3	278.1	318.8	376.5	443.5	470.2	424.4	365.2	323.0	293.6	276.1
70°	222.0	240.8	272.8	322.5	383.2	403.6	360.7	312.0	281.1	257.6	241.3
72.5°	193.1	206.9	235.9	274.3	325.0	341.2	311.3	268.5	239.7	222.0	209.1
75°	147.1	158.6	177.5	208.4	243.4	252.9	230.3	203.6	184.3	171.7	161.8
77.5°	106.1	114.5	128.2	147.2	171.5	180.0	165.7	147.9	133.8	125.3	119.8
80°	80.1	86.9	98.4	114.1	128.8	133.5	125.1	111.5	101.6	96.9	92.1
82.5°	59.2	63.0	69.9	80.6	90.7	96.2	89.1	80.9	75.6	71.3	69.5
85°	29.8	31.9	35.1	39.3	45.5	47.6	45.0	42.9	39.8	37.2	37.2
87.5°	11.3	11.5	13.0	14.1	16.1	17.7	17.6	17.1	17.0	16.7	16.3
90°	1.8	3.1	4.4	5.6	7.1	8.7	10.4	12.0	13.7	14.2	14.7
92.5°	10.3	9.9	9.5	9.2	9.6	10.9	12.1	13.4	14.6	15.4	16.2
95°	29.6	24.4	19.2	14.0	12.1	13.5	14.9	16.3	17.7	18.6	19.5
97.5°	67.6	65.3	62.9	60.6	54.9	45.7	36.6	27.5	18.4	19.4	20.4
100°	98.9	101.5	104.0	106.5	97.9	78.1	58.4	38.6	18.8	19.8	20.8
102.5°	128.3	130.2	132.0	133.8	123.9	102.3	80.7	59.1	37.5	34.4	31.2
105°	171.4	172.8	174.1	175.5	170.5	159.1	147.7	136.3	124.9	102.5	80.0
107.5°	216.9	218.1	219.2	220.3	221.7	223.5	225.3	227.1	228.9	212.5	196.0
110°	247.4	248.4	249.4	250.4	251.7	253.0	254.4	255.8	257.2	253.0	248.9



TEST NUMBER: P331964

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	276.5	277.4	278.3	279.2	280.4	281.8	283.2	284.6	286.0	286.1	286.1
115°	319.6	320.3	321.1	321.9	322.8	324.0	325.1	326.2	327.4	328.7	329.9
117.5°	361.6	362.6	363.5	364.4	365.2	365.8	366.4	367.0	367.5	368.6	369.6
120°	387.8	389.0	390.1	391.3	392.0	392.4	392.8	393.2	393.5	394.6	395.6
122.5°	414.1	415.0	416.0	416.9	417.6	418.1	418.6	419.1	419.6	420.3	421.0
125°	450.5	451.5	452.5	453.5	454.3	454.8	455.3	455.8	456.3	456.5	456.8
127.5°	485.6	486.6	487.6	488.6	489.4	490.0	490.7	491.3	491.9	492.3	492.7
130°	507.5	508.5	509.5	510.5	511.3	511.8	512.3	512.8	513.3	513.8	514.3
132.5°	528.5	529.5	530.5	531.5	532.2	532.6	533.0	533.4	533.9	534.4	534.9
135°	560.3	561.0	561.8	562.6	563.2	563.7	564.2	564.7	565.2	565.6	566.0
137.5°	587.9	588.8	589.8	590.7	591.4	591.6	591.9	592.2	592.5	593.1	593.7
140°	605.9	606.7	607.4	608.2	608.8	609.1	609.5	609.9	610.3	610.8	611.3
142.5°	622.8	623.6	624.3	625.1	625.6	626.0	626.4	626.8	627.2	627.6	628.0
145°	646.5	647.4	648.3	649.2	649.8	650.0	650.3	650.5	650.8	651.0	651.3
147.5°	668.5	669.1	669.6	670.2	670.6	670.9	671.1	671.4	671.7	671.9	672.2
150°	682.0	682.3	682.7	683.1	683.4	683.7	683.9	684.2	684.4	684.7	684.9
152.5°	694.1	694.2	694.4	694.6	694.8	694.9	695.1	695.2	695.4	695.8	696.3
155°	711.0	710.7	710.5	710.2	710.2	710.3	710.4	710.5	710.7	711.3	711.9
157.5°	724.7	724.6	724.6	724.6	724.5	724.4	724.3	724.1	724.0	724.8	725.5
160°	732.8	732.7	732.5	732.4	732.3	732.1	732.0	731.9	731.8	732.5	733.3
162.5°	740.3	740.0	739.7	739.3	739.1	739.0	738.9	738.7	738.6	739.5	740.3
165°	749.6	749.3	748.9	748.5	748.2	748.1	748.0	747.9	747.7	748.8	749.8
167.5°	756.8	756.3	755.8	755.3	755.0	755.0	755.0	755.0	755.0	756.1	757.1
170°	760.9	760.4	759.9	759.4	759.1	759.1	759.1	759.1	759.1	760.2	761.2
172.5°	763.6	762.9	762.3	761.7	761.5	761.6	761.7	761.8	761.9	762.9	763.9
175°	767.1	766.4	765.8	765.2	764.9	765.0	765.2	765.3	765.4	766.3	767.2
177.5°	768.1	767.6	767.1	766.6	766.4	766.5	766.6	766.7	766.8	767.6	768.4
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P331964

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1137.1	1137.5	1142.1	1145.5	1143.8	1145.9	1146.7
5°	1242.3	1261.2	1271.1	1278.4	1279.0	1279.5	1283.7
7.5°	1391.5	1411.7	1426.5	1448.9	1455.6	1463.2	1461.0
10°	1500.4	1530.2	1555.9	1569.5	1584.2	1605.6	1588.4
12.5°	1602.2	1655.1	1694.1	1715.3	1729.1	1733.4	1724.9
15°	1770.0	1839.1	1876.3	1875.2	1922.4	1942.8	1910.8
17.5°	1923.9	1987.7	2038.8	2065.0	2104.2	2112.9	2108.9
20°	2018.2	2087.8	2127.6	2172.6	2193.0	2211.3	2214.5
22.5°	2099.4	2161.9	2204.6	2242.1	2259.2	2267.9	2273.1
25°	2183.1	2232.3	2257.9	2271.0	2275.7	2274.7	2267.9
27.5°	2177.3	2181.1	2152.8	2125.1	2100.3	2072.3	2062.7
30°	2120.8	2076.8	1998.3	1953.8	1888.3	1836.5	1857.4
32.5°	1972.1	1884.6	1796.4	1699.1	1618.6	1595.7	1572.6
35°	1683.1	1529.2	1439.2	1334.4	1292.6	1250.7	1221.9
37.5°	1361.7	1242.6	1135.8	1067.3	1025.4	998.9	984.6
40°	1177.4	1070.1	982.1	926.6	894.7	864.9	860.7
42.5°	1030.4	930.6	864.4	820.2	789.6	776.9	767.7
45°	843.9	774.3	729.8	698.4	678.0	670.1	659.6
47.5°	714.3	665.1	631.7	610.3	594.9	589.1	588.2
50°	641.8	601.0	576.4	559.6	547.6	545.5	537.1
52.5°	587.4	552.0	532.8	518.2	509.5	503.6	501.1
55°	509.9	486.3	469.1	460.7	453.9	448.1	448.1
57.5°	446.1	426.5	415.0	407.9	405.8	401.7	399.1
60°	406.8	390.0	381.1	374.8	370.7	371.2	366.5
62.5°	368.2	357.4	348.9	342.6	337.6	337.7	338.0
65°	313.6	305.2	298.9	296.8	293.7	290.0	291.1
67.5°	265.7	257.9	253.0	249.4	248.4	246.4	249.4
70°	231.4	225.6	222.0	218.8	217.8	218.3	220.9
72.5°	200.0	195.9	193.5	192.0	189.7	189.8	191.6
75°	157.1	153.9	151.8	150.2	149.7	149.7	149.7
77.5°	115.4	114.7	113.7	111.4	111.5	112.1	112.2
80°	91.1	89.5	89.0	88.0	86.4	85.3	88.0
82.5°	68.1	66.5	66.0	65.8	63.3	63.1	65.3
85°	36.6	35.1	35.6	35.1	35.1	34.6	34.6
87.5°	16.0	15.7	15.4	15.8	15.5	15.1	16.0
90°	15.2	15.7	16.1	16.4	16.6	16.9	17.1
92.5°	17.0	17.8	18.3	18.5	18.6	18.8	18.9
95°	20.3	21.2	21.7	21.7	21.7	21.7	21.7
97.5°	21.4	22.4	23.0	23.1	23.2	23.4	23.5
100°	21.9	22.9	23.4	23.6	23.7	23.8	24.0
102.5°	28.1	25.0	23.5	23.7	24.0	24.2	24.4
105°	57.6	35.2	24.1	24.3	24.6	24.8	25.1
107.5°	179.6	163.1	146.5	129.5	112.6	95.7	78.8
110°	244.7	240.5	229.3	211.2	193.1	175.0	156.8



TEST NUMBER: P331964

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	286.2	286.3	284.4	280.6	276.7	272.9	269.1
115°	331.2	332.5	333.3	333.8	334.4	334.9	335.4
117.5°	370.6	371.6	372.2	372.3	372.4	372.5	372.6
120°	396.6	397.6	398.1	398.1	398.1	398.1	398.1
122.5°	421.7	422.4	422.8	422.9	423.0	423.1	423.2
125°	457.0	457.3	457.6	457.8	458.1	458.3	458.6
127.5°	493.1	493.5	493.6	493.3	493.1	492.8	492.6
130°	514.8	515.3	515.5	515.2	515.0	514.7	514.5
132.5°	535.4	535.9	536.0	535.6	535.2	534.9	534.5
135°	566.4	566.7	566.7	566.4	566.0	565.6	565.2
137.5°	594.3	594.9	595.1	594.8	594.6	594.3	594.1
140°	611.8	612.3	612.4	612.2	611.9	611.7	611.4
142.5°	628.4	628.8	628.8	628.5	628.1	627.7	627.4
145°	651.5	651.8	651.9	651.9	651.9	651.9	651.9
147.5°	672.4	672.7	672.5	671.9	671.3	670.8	670.2
150°	685.2	685.4	685.4	685.0	684.6	684.2	683.9
152.5°	696.7	697.2	697.1	696.6	696.0	695.4	694.8
155°	712.6	713.2	713.1	712.4	711.6	710.9	710.1
157.5°	726.3	727.1	726.9	725.9	725.0	724.0	723.0
160°	734.0	734.8	734.7	733.9	733.0	732.1	731.2
162.5°	741.2	742.1	742.1	741.3	740.5	739.7	739.0
165°	750.8	751.8	751.9	751.0	750.1	749.2	748.3
167.5°	758.1	759.1	759.1	758.1	757.1	756.1	755.0
170°	762.2	763.2	763.2	762.2	761.2	760.2	759.1
172.5°	764.9	765.9	765.9	764.8	763.7	762.5	761.4
175°	768.1	769.0	768.9	767.9	766.9	765.9	764.8
177.5°	769.2	770.0	769.9	768.9	767.9	766.9	765.9
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7

(END OF REPORT)