

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331917-830

Luminaire Tested: **S123DIP-S560D365U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331917-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D365U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3361.0 lumens
Efficiency: N/A
Efficacy: 122.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331917-830

CATALOG NUMBER: S123DIP-S560D365U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331917-830

CATALOG NUMBER: S123DIP-S560D365U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65
1	101	97	93	89	95	91	87	84	80	78	75	71	69	67	62	60	59	55
2	92	84	78	73	86	80	74	69	70	66	62	62	59	56	54	52	50	46
3	84	74	67	61	79	70	63	58	62	57	52	55	51	47	48	45	42	39
4	77	66	58	51	72	62	55	49	55	49	45	49	44	40	43	39	36	33
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	39	35	32	29
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28	25
7	60	48	39	34	56	45	38	32	41	34	30	36	31	27	32	28	25	22
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9038	9038	9038
5°	9081	8956	9018
10°	9021	8878	8933
15°	8914	8778	8795
20°	8791	8635	8643
25°	8626	8464	8445
30°	8444	8274	8211
35°	8253	8073	7970
40°	8056	7852	7731
45°	7837	7649	7462
50°	7618	7400	7194
55°	7330	7141	6923
60°	7042	6837	6622
65°	6788	6510	6306
70°	6408	6134	5860
75°	5856	5644	5407
80°	5281	5058	5015
85°	4631	4458	4286



TEST NUMBER: P331917-830

CATALOG NUMBER: S123DIP-S560D365U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	2.4
10°-20°	223.3	6.6
20°-30°	329.9	9.8
30°-40°	385.4	11.5
40°-50°	387.4	11.5
50°-60°	340.3	10.1
60°-70°	253.5	7.5
70°-80°	144.5	4.3
80°-90°	42.7	1.3
90°-100°	27.6	0.8
100°-110°	82.7	2.5
110°-120°	140.6	4.2
120°-130°	185.0	5.5
130°-140°	207.9	6.2
140°-150°	204.4	6.1
150°-160°	172.0	5.1
160°-170°	114.5	3.4
170°-180°	40.1	1.2
0°-30°	632.3	18.8
0°-40°	1017.7	30.3
0°-60°	1745.5	51.9
0°-90°	2186.2	65.0
90°-120°	250.9	7.5
90°-150°	848.1	25.2
90°-180°	1175.0	35.0
0°-180°	3361.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	840	840	840	840	840	
5°	840	837	829	836	835	80
15°	800	797	788	793	789	225
25°	726	722	713	713	711	334
35°	628	624	614	610	606	393
45°	515	512	502	494	490	397
55°	391	389	380	373	369	350
65°	266	263	256	250	248	263
75°	141	138	136	132	130	151
85°	38	36	36	35	35	41
90°	0	4	8	9	10	3
95°	20	22	25	26	26	22
105°	75	76	79	79	79	80
115°	142	142	142	142	142	140
125°	207	208	208	206	205	185
135°	269	271	270	269	268	207
145°	326	327	328	327	326	204
155°	373	373	374	375	373	172
165°	407	406	406	408	405	115
175°	423	422	422	423	421	40
180°	424	424	424	424	424	



TEST NUMBER: P331917-830

CATALOG NUMBER: S123DIP-S560D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	842.5	842.1	841.6	841.0	840.6	839.5	838.1	836.7	835.4	834.0	835.2
5°	840.4	839.6	838.8	838.0	837.2	835.9	834.2	832.4	830.7	828.9	830.5
7.5°	832.2	831.4	830.6	829.8	829.0	827.6	825.9	824.0	822.2	820.4	821.8
10°	825.3	824.4	823.7	822.8	822.1	820.6	818.5	816.4	814.4	812.3	813.7
12.5°	816.1	815.3	814.6	814.0	813.3	812.0	810.0	808.0	806.2	804.2	805.2
15°	799.9	799.4	798.7	798.1	797.4	796.1	794.0	791.9	789.8	787.7	789.0
17.5°	781.4	780.5	779.7	778.8	778.0	776.6	774.5	772.4	770.3	768.2	769.1
20°	767.5	766.6	765.5	764.6	763.6	762.1	760.1	758.0	755.8	753.8	754.4
22.5°	751.9	750.9	750.0	749.0	748.0	746.5	744.4	742.3	740.3	738.2	738.7
25°	726.3	725.4	724.4	723.5	722.5	721.0	718.9	716.8	714.7	712.7	712.8
27.5°	699.1	698.1	697.2	696.3	695.3	693.7	691.4	689.3	687.0	684.8	684.9
30°	679.4	678.6	677.8	677.0	676.2	674.7	672.4	670.1	668.0	665.7	665.7
32.5°	659.8	658.7	657.6	656.6	655.5	654.1	652.4	650.6	648.9	647.2	646.3
35°	628.1	627.2	626.2	625.3	624.3	622.7	620.7	618.6	616.5	614.4	613.5
37.5°	595.8	594.6	593.3	592.1	590.9	589.3	587.1	585.0	582.9	580.8	579.7
40°	573.3	572.3	571.4	570.4	569.4	567.8	565.5	563.4	561.1	558.8	557.5
42.5°	550.7	549.7	548.6	547.4	546.4	544.7	542.4	540.3	538.0	535.7	534.4
45°	514.8	514.2	513.5	512.8	512.2	510.9	508.8	506.7	504.6	502.5	500.6
47.5°	479.1	478.2	477.3	476.4	475.4	473.9	472.0	470.0	468.1	466.1	464.2
50°	454.9	454.0	453.3	452.4	451.7	450.3	448.1	446.0	443.9	441.9	440.1
52.5°	429.4	428.9	428.4	427.8	427.3	425.8	423.7	421.5	419.2	417.1	415.6
55°	390.6	390.4	390.3	390.1	389.9	388.8	386.7	384.7	382.6	380.5	378.7
57.5°	353.6	353.1	352.5	352.0	351.5	350.3	348.6	347.0	345.3	343.7	342.1
60°	327.1	326.9	326.8	326.6	326.4	325.4	323.5	321.5	319.6	317.6	316.2
62.5°	303.4	302.9	302.6	302.2	301.7	300.6	298.6	296.7	294.7	292.8	291.4
65°	266.5	265.6	264.9	264.0	263.3	262.0	260.4	258.8	257.2	255.6	254.3
67.5°	227.2	226.6	225.8	225.2	224.4	223.5	222.3	221.0	219.8	218.7	217.5
70°	203.6	202.6	201.7	200.8	199.7	198.8	197.8	196.9	195.9	194.9	193.8
72.5°	178.8	178.0	177.4	176.6	176.0	175.0	174.0	172.9	171.7	170.7	169.7
75°	140.8	140.2	139.5	138.8	138.3	137.7	137.1	136.7	136.2	135.7	135.0
77.5°	107.2	106.8	106.4	106.1	105.8	105.3	104.7	104.2	103.5	102.9	102.5
80°	85.2	84.7	84.3	83.8	83.2	82.8	82.6	82.2	81.9	81.6	81.4
82.5°	63.8	63.7	63.6	63.5	63.4	63.3	63.3	63.2	63.2	63.2	62.8
85°	37.5	37.2	36.9	36.6	36.3	36.1	36.1	36.1	36.1	36.1	35.8
87.5°	15.1	14.9	14.6	14.3	14.1	14.0	14.1	14.1	14.2	14.3	14.2
90°	0.4	1.0	1.8	2.5	3.3	4.1	5.1	6.0	7.1	8.0	8.3
92.5°	8.1	8.6	9.0	9.6	10.1	10.6	11.1	11.7	12.3	12.8	13.0
95°	19.7	20.2	20.6	21.2	21.7	22.2	22.9	23.5	24.0	24.7	25.0
97.5°	34.9	35.3	35.7	36.1	36.5	36.9	37.3	37.7	38.2	38.5	38.9
100°	45.3	45.7	46.2	46.7	47.0	47.5	47.9	48.3	48.6	48.9	49.2
102.5°	57.3	57.6	57.8	58.1	58.3	58.7	59.2	59.8	60.2	60.7	60.9
105°	74.9	75.1	75.2	75.4	75.5	76.0	76.6	77.3	77.9	78.6	78.6
107.5°	95.5	95.6	95.7	95.8	95.9	96.0	96.2	96.5	96.8	97.1	97.3
110°	108.3	108.4	108.6	108.7	108.9	109.0	109.1	109.3	109.4	109.6	109.9



TEST NUMBER: P331917-830

CATALOG NUMBER: S123DIP-S560D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	121.6	121.7	121.8	121.9	122.0	122.0	122.1	122.1	122.1	122.2	122.4
115°	141.6	141.8	142.0	142.2	142.4	142.5	142.3	142.2	142.0	141.9	141.9
117.5°	161.6	161.8	162.0	162.1	162.3	162.2	162.0	161.8	161.6	161.5	161.5
120°	174.2	174.7	175.1	175.5	176.0	176.0	175.7	175.3	174.9	174.6	174.5
122.5°	187.3	187.6	187.9	188.2	188.6	188.6	188.4	188.2	188.0	187.8	187.7
125°	207.2	207.4	207.6	207.8	208.1	208.1	207.9	207.8	207.6	207.5	207.2
127.5°	225.6	226.0	226.5	227.0	227.4	227.6	227.4	227.2	227.2	227.0	226.6
130°	237.8	238.4	239.0	239.6	240.2	240.3	240.2	240.0	239.7	239.5	239.2
132.5°	250.1	250.7	251.3	251.8	252.4	252.7	252.5	252.3	252.1	252.0	251.7
135°	268.8	269.3	269.7	270.1	270.6	270.8	270.7	270.6	270.5	270.5	270.1
137.5°	286.2	286.5	286.8	287.2	287.6	287.9	288.0	288.2	288.4	288.6	288.3
140°	298.1	298.5	298.9	299.3	299.6	299.8	299.9	299.9	300.0	300.1	300.0
142.5°	309.1	309.4	309.8	310.2	310.5	310.8	310.9	311.0	311.1	311.3	311.2
145°	326.1	326.2	326.4	326.5	326.7	326.9	327.1	327.3	327.5	327.7	327.7
147.5°	341.0	341.3	341.6	341.9	342.0	342.3	342.5	342.7	342.9	343.2	343.2
150°	351.4	351.6	351.7	351.9	352.0	352.1	352.3	352.4	352.6	352.7	352.7
152.5°	360.0	360.1	360.3	360.5	360.8	360.9	361.0	361.1	361.2	361.3	361.4
155°	373.4	373.4	373.4	373.4	373.4	373.4	373.5	373.5	373.6	373.7	374.0
157.5°	384.8	384.7	384.7	384.6	384.5	384.5	384.6	384.6	384.7	384.7	385.0
160°	392.0	391.9	391.7	391.6	391.4	391.3	391.3	391.3	391.3	391.3	391.7
162.5°	398.4	398.2	398.0	397.8	397.6	397.6	397.6	397.7	397.8	397.8	398.1
165°	406.7	406.5	406.2	406.0	405.8	405.7	405.7	405.7	405.7	405.7	406.1
167.5°	413.3	413.0	412.7	412.4	412.1	412.0	412.1	412.1	412.2	412.3	412.6
170°	417.0	416.7	416.4	416.1	415.8	415.7	415.7	415.7	415.7	415.7	416.2
172.5°	420.0	419.6	419.3	419.1	418.8	418.6	418.6	418.6	418.6	418.6	419.1
175°	423.0	422.7	422.4	422.2	421.9	421.7	421.7	421.7	421.7	421.7	422.2
177.5°	424.2	424.0	423.8	423.6	423.3	423.2	423.2	423.2	423.2	423.2	423.6
180°	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0



TEST NUMBER: P331917-830

CATALOG NUMBER: S123DIP-S560D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	836.5	837.7	839.1	839.6	839.5	839.3	839.2	839.1
5°	832.1	833.7	835.3	835.9	835.6	835.3	835.0	834.6
7.5°	823.2	824.6	826.1	826.7	826.5	826.3	826.1	826.0
10°	815.1	816.6	818.0	818.6	818.3	817.9	817.7	817.3
12.5°	806.3	807.4	808.4	808.8	808.6	808.4	808.2	808.0
15°	790.3	791.5	792.9	793.0	792.0	791.1	790.1	789.2
17.5°	770.1	770.9	771.8	772.0	771.8	771.4	771.0	770.6
20°	755.1	755.7	756.3	756.4	755.9	755.4	755.0	754.5
22.5°	739.2	739.7	740.3	740.2	739.6	739.0	738.4	737.7
25°	712.9	713.1	713.2	713.1	712.7	712.2	711.6	711.1
27.5°	685.0	685.1	685.2	685.0	684.4	683.8	683.2	682.6
30°	665.7	665.7	665.7	665.2	664.0	662.9	661.8	660.6
32.5°	645.5	644.5	643.6	642.8	642.2	641.7	641.0	640.5
35°	612.5	611.5	610.6	609.7	608.9	608.1	607.3	606.5
37.5°	578.4	577.3	576.2	575.3	574.9	574.3	573.8	573.3
40°	556.3	555.0	553.7	552.7	552.0	551.5	550.8	550.2
42.5°	533.2	531.9	530.6	529.6	529.0	528.4	527.7	527.1
45°	498.7	496.7	494.8	493.4	492.7	491.8	491.1	490.2
47.5°	462.3	460.4	458.5	457.2	456.6	455.8	455.2	454.4
50°	438.4	436.6	434.8	433.5	432.4	431.5	430.6	429.6
52.5°	414.1	412.6	411.0	409.7	408.8	407.8	406.9	406.0
55°	376.9	375.2	373.4	372.1	371.4	370.5	369.8	368.9
57.5°	340.5	338.9	337.4	336.1	335.2	334.3	333.4	332.4
60°	314.8	313.4	311.9	310.8	310.0	309.2	308.4	307.6
62.5°	289.9	288.5	287.1	286.1	285.5	285.0	284.5	283.9
65°	253.0	251.8	250.4	249.6	249.1	248.6	248.2	247.6
67.5°	216.4	215.3	214.1	213.2	212.5	211.9	211.2	210.6
70°	192.7	191.6	190.5	189.5	188.7	187.8	187.1	186.2
72.5°	168.7	167.7	166.7	166.0	165.6	165.1	164.8	164.3
75°	134.1	133.4	132.5	131.9	131.4	130.9	130.4	130.0
77.5°	101.9	101.3	100.8	100.5	100.5	100.5	100.5	100.5
80°	81.2	81.1	81.0	80.9	80.9	80.9	80.9	80.9
82.5°	62.5	62.2	61.9	61.7	61.6	61.5	61.4	61.3
85°	35.4	35.2	34.8	34.7	34.7	34.7	34.7	34.7
87.5°	14.1	14.1	14.0	14.0	14.0	14.0	14.1	14.1
90°	8.6	8.9	9.1	9.4	9.5	9.7	9.8	10.0
92.5°	13.3	13.5	13.8	13.9	13.8	13.7	13.6	13.5
95°	25.3	25.5	25.8	26.0	26.0	26.0	26.0	26.0
97.5°	39.2	39.6	40.0	40.1	40.1	40.1	40.0	40.0
100°	49.4	49.7	49.9	50.0	50.1	50.3	50.5	50.6
102.5°	61.2	61.4	61.5	61.6	61.6	61.6	61.5	61.5
105°	78.6	78.6	78.6	78.7	78.8	79.0	79.2	79.3
107.5°	97.6	97.7	98.0	98.1	98.0	97.9	97.8	97.7
110°	110.2	110.5	110.7	110.8	110.7	110.6	110.4	110.3



TEST NUMBER: P331917-830

CATALOG NUMBER: S123DIP-S560D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	122.8	123.2	123.6	123.7	123.7	123.7	123.6	123.6
115°	142.0	142.1	142.2	142.2	142.1	142.0	141.9	141.9
117.5°	161.5	161.5	161.5	161.3	161.1	160.9	160.7	160.5
120°	174.4	174.3	174.3	174.1	174.0	173.8	173.7	173.5
122.5°	187.5	187.3	187.1	186.9	186.7	186.4	186.2	186.1
125°	206.9	206.6	206.3	206.0	205.8	205.5	205.1	204.8
127.5°	226.1	225.7	225.3	224.9	224.6	224.2	223.9	223.6
130°	238.9	238.6	238.3	237.9	237.4	236.9	236.4	235.8
132.5°	251.3	250.9	250.6	250.2	249.8	249.4	249.0	248.6
135°	269.8	269.6	269.3	269.1	268.9	268.7	268.6	268.4
137.5°	288.0	287.8	287.4	287.1	286.8	286.5	286.3	286.0
140°	299.9	299.9	299.8	299.5	299.0	298.5	297.9	297.5
142.5°	311.1	311.0	311.0	310.8	310.4	310.0	309.5	309.2
145°	327.6	327.5	327.4	327.3	327.0	326.7	326.4	326.1
147.5°	343.2	343.2	343.2	342.9	342.5	342.0	341.6	341.1
150°	352.7	352.7	352.7	352.5	352.0	351.7	351.2	350.7
152.5°	361.5	361.7	361.7	361.6	361.2	360.8	360.4	360.1
155°	374.3	374.6	374.9	374.8	374.3	373.7	373.2	372.7
157.5°	385.3	385.7	386.0	385.9	385.5	385.1	384.7	384.3
160°	392.1	392.5	392.9	392.9	392.6	392.3	392.0	391.7
162.5°	398.5	398.9	399.3	399.2	398.7	398.2	397.8	397.3
165°	406.6	407.0	407.5	407.5	406.9	406.4	405.9	405.4
167.5°	413.1	413.6	414.1	414.1	413.6	413.1	412.6	412.3
170°	416.7	417.3	417.7	417.7	417.3	416.7	416.2	415.7
172.5°	419.5	420.0	420.5	420.5	419.9	419.4	418.9	418.4
175°	422.5	423.0	423.5	423.4	422.9	422.4	421.9	421.3
177.5°	424.0	424.2	424.6	424.6	424.2	423.8	423.4	422.9
180°	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0

(END OF REPORT)