

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331970

Luminaire Tested: **S123DIP-S775D585U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331970
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D585U835-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5512.0 lumens
Efficiency: N/A
Efficacy: 136.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331970

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331970

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	88	88	88	75	75	75	63	63	63	58
1	99	95	91	87	92	89	85	82	77	74	72	66	64	62	56	54	53	48
2	90	83	77	71	84	77	72	67	67	63	59	58	55	52	49	47	45	40
3	83	73	65	59	77	68	62	56	59	54	50	51	47	44	43	40	38	34
4	76	65	56	50	70	60	53	48	53	47	43	45	41	38	39	35	33	29
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	28	25
6	64	52	43	37	59	48	41	36	42	37	32	37	32	29	32	28	25	22
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	22	20
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18	16
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13108	13108	13108
5°	13169	12988	13078
10°	13081	12875	12955
15°	12929	12730	12754
20°	12749	12521	12534
25°	12511	12275	12250
30°	12246	11999	11908
35°	11971	11709	11557
40°	11682	11387	11212
45°	11365	11094	10823
50°	11047	10731	10433
55°	10631	10355	10042
60°	10211	9918	9604
65°	9841	9442	9146
70°	9294	8897	8500
75°	8492	8189	7839
80°	7662	7333	7271
85°	6719	6472	6212



TEST NUMBER: P331970

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.7	2.1
10°-20°	323.9	5.9
20°-30°	478.4	8.7
30°-40°	558.9	10.1
40°-50°	561.9	10.2
50°-60°	493.6	9.0
60°-70°	367.7	6.7
70°-80°	209.5	3.8
80°-90°	62.3	1.1
90°-100°	27.9	0.5
100°-110°	133.0	2.4
110°-120°	319.5	5.8
120°-130°	406.9	7.4
130°-140°	434.7	7.9
140°-150°	406.5	7.4
150°-160°	327.9	5.9
160°-170°	211.6	3.8
170°-180°	72.9	1.3
0°-30°	917.1	16.6
0°-40°	1475.9	26.8
0°-60°	2531.4	45.9
0°-90°	3170.9	57.5
90°-120°	480.5	8.7
90°-150°	1728.6	31.4
90°-180°	2341.0	42.5
0°-180°	5512.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1218	1218	1218	1218	1218	
5°	1219	1213	1202	1212	1210	115
15°	1160	1155	1142	1150	1144	327
25°	1053	1047	1034	1034	1031	485
35°	911	904	891	885	880	570
45°	747	742	729	717	711	576
55°	566	565	552	541	535	507
65°	386	381	371	363	359	381
75°	204	200	197	192	188	218
85°	54	52	52	50	50	60
90°	1	6	14	16	17	5
95°	35	13	18	21	22	43
105°	170	173	125	30	25	180
115°	319	322	327	333	335	315
125°	449	454	456	457	459	401
135°	560	563	565	567	565	431
145°	646	650	651	652	652	404
155°	711	710	711	713	710	328
165°	750	748	748	752	748	212
175°	768	765	765	769	765	73
180°	768	768	768	768	768	



TEST NUMBER: P331970

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8
2.5°	1221.9	1221.2	1220.5	1219.7	1219.0	1217.6	1215.5	1213.5	1211.4	1209.4	1211.2
5°	1218.8	1217.6	1216.5	1215.3	1214.1	1212.3	1209.7	1207.2	1204.6	1202.0	1204.4
7.5°	1206.9	1205.7	1204.5	1203.4	1202.2	1200.3	1197.6	1195.0	1192.3	1189.7	1191.8
10°	1196.8	1195.6	1194.5	1193.3	1192.2	1190.1	1187.0	1184.0	1181.0	1178.0	1180.1
12.5°	1183.4	1182.4	1181.5	1180.5	1179.5	1177.6	1174.8	1171.9	1169.1	1166.2	1167.8
15°	1160.2	1159.2	1158.3	1157.4	1156.4	1154.5	1151.4	1148.4	1145.4	1142.4	1144.2
17.5°	1133.1	1131.9	1130.7	1129.5	1128.3	1126.2	1123.2	1120.1	1117.1	1114.1	1115.4
20°	1113.0	1111.6	1110.3	1108.9	1107.5	1105.2	1102.2	1099.2	1096.2	1093.1	1094.1
22.5°	1090.4	1089.0	1087.6	1086.2	1084.8	1082.6	1079.6	1076.6	1073.6	1070.5	1071.3
25°	1053.4	1052.0	1050.6	1049.2	1047.8	1045.6	1042.5	1039.5	1036.5	1033.5	1033.7
27.5°	1013.8	1012.4	1011.1	1009.7	1008.4	1006.1	1002.8	999.6	996.3	993.0	993.2
30°	985.3	984.1	983.0	981.8	980.6	978.4	975.2	971.9	968.7	965.4	965.4
32.5°	956.8	955.3	953.7	952.2	950.7	948.7	946.1	943.6	941.1	938.6	937.3
35°	911.0	909.6	908.2	906.8	905.4	903.2	900.1	897.1	894.1	891.1	889.7
37.5°	864.0	862.3	860.5	858.7	857.0	854.6	851.5	848.4	845.3	842.3	840.6
40°	831.4	830.0	828.6	827.2	825.8	823.5	820.2	817.0	813.7	810.4	808.6
42.5°	798.7	797.1	795.5	794.0	792.4	790.0	786.7	783.4	780.2	776.9	775.1
45°	746.6	745.6	744.7	743.8	742.8	740.9	737.8	734.8	731.8	728.8	726.0
47.5°	694.8	693.5	692.1	690.8	689.4	687.3	684.5	681.7	678.8	676.0	673.2
50°	659.7	658.5	657.3	656.2	655.0	652.9	649.9	646.9	643.8	640.8	638.3
52.5°	622.8	622.0	621.2	620.4	619.6	617.6	614.4	611.2	608.0	604.8	602.6
55°	566.5	566.2	566.0	565.8	565.5	563.9	560.9	557.9	554.8	551.8	549.3
57.5°	512.9	512.1	511.3	510.5	509.7	508.1	505.7	503.2	500.8	498.4	496.1
60°	474.3	474.1	473.9	473.6	473.4	471.9	469.1	466.3	463.5	460.7	458.6
62.5°	440.0	439.4	438.8	438.2	437.6	435.9	433.1	430.3	427.5	424.7	422.6
65°	386.4	385.2	384.0	382.9	381.7	380.0	377.6	375.3	373.0	370.7	368.8
67.5°	329.6	328.6	327.6	326.5	325.5	324.1	322.4	320.6	318.8	317.1	315.4
70°	295.3	293.9	292.5	291.1	289.7	288.3	286.9	285.5	284.1	282.7	281.1
72.5°	259.3	258.2	257.2	256.2	255.2	253.9	252.3	250.7	249.1	247.5	246.1
75°	204.2	203.2	202.3	201.4	200.5	199.6	198.9	198.2	197.5	196.9	195.7
77.5°	155.4	154.9	154.4	153.9	153.3	152.7	151.8	151.0	150.2	149.3	148.5
80°	123.6	122.9	122.2	121.5	120.8	120.2	119.7	119.3	118.8	118.3	118.1
82.5°	92.6	92.4	92.3	92.1	92.0	91.9	91.8	91.7	91.6	91.5	91.1
85°	54.4	54.0	53.5	53.1	52.6	52.4	52.4	52.4	52.4	52.4	51.9
87.5°	21.9	21.6	21.3	21.0	20.7	20.6	20.7	20.9	21.0	21.2	21.1
90°	0.6	1.8	3.1	4.4	5.6	7.1	8.7	10.4	12.0	13.7	14.2
92.5°	10.6	10.3	9.9	9.5	9.2	9.6	10.9	12.1	13.4	14.6	15.4
95°	34.8	29.6	24.4	19.2	14.0	12.1	13.5	14.9	16.3	17.7	18.6
97.5°	69.9	67.6	65.3	62.9	60.6	54.9	45.7	36.6	27.5	18.4	19.4
100°	96.4	98.9	101.5	104.0	106.5	97.9	78.1	58.4	38.6	18.8	19.8
102.5°	126.5	128.3	130.2	132.0	133.8	123.9	102.3	80.7	59.1	37.5	34.4
105°	170.0	171.4	172.8	174.1	175.5	170.5	159.1	147.7	136.3	124.9	102.5
107.5°	215.8	216.9	218.1	219.2	220.3	221.7	223.5	225.3	227.1	228.9	212.5
110°	246.4	247.4	248.4	249.4	250.4	251.7	253.0	254.4	255.8	257.2	253.0



TEST NUMBER: P331970

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	275.6	276.5	277.4	278.3	279.2	280.4	281.8	283.2	284.6	286.0	286.1
115°	318.8	319.6	320.3	321.1	321.9	322.8	324.0	325.1	326.2	327.4	328.7
117.5°	360.7	361.6	362.6	363.5	364.4	365.2	365.8	366.4	367.0	367.5	368.6
120°	386.7	387.8	389.0	390.1	391.3	392.0	392.4	392.8	393.2	393.5	394.6
122.5°	413.2	414.1	415.0	416.0	416.9	417.6	418.1	418.6	419.1	419.6	420.3
125°	449.4	450.5	451.5	452.5	453.5	454.3	454.8	455.3	455.8	456.3	456.5
127.5°	484.6	485.6	486.6	487.6	488.6	489.4	490.0	490.7	491.3	491.9	492.3
130°	506.5	507.5	508.5	509.5	510.5	511.3	511.8	512.3	512.8	513.3	513.8
132.5°	527.5	528.5	529.5	530.5	531.5	532.2	532.6	533.0	533.4	533.9	534.4
135°	559.5	560.3	561.0	561.8	562.6	563.2	563.7	564.2	564.7	565.2	565.6
137.5°	586.9	587.9	588.8	589.8	590.7	591.4	591.6	591.9	592.2	592.5	593.1
140°	605.1	605.9	606.7	607.4	608.2	608.8	609.1	609.5	609.9	610.3	610.8
142.5°	622.0	622.8	623.6	624.3	625.1	625.6	626.0	626.4	626.8	627.2	627.6
145°	645.6	646.5	647.4	648.3	649.2	649.8	650.0	650.3	650.5	650.8	651.0
147.5°	667.9	668.5	669.1	669.6	670.2	670.6	670.9	671.1	671.4	671.7	671.9
150°	681.6	682.0	682.3	682.7	683.1	683.4	683.7	683.9	684.2	684.4	684.7
152.5°	693.9	694.1	694.2	694.4	694.6	694.8	694.9	695.1	695.2	695.4	695.8
155°	711.2	711.0	710.7	710.5	710.2	710.2	710.3	710.4	710.5	710.7	711.3
157.5°	724.7	724.7	724.6	724.6	724.6	724.5	724.4	724.3	724.1	724.0	724.8
160°	732.9	732.8	732.7	732.5	732.4	732.3	732.1	732.0	731.9	731.8	732.5
162.5°	740.7	740.3	740.0	739.7	739.3	739.1	739.0	738.9	738.7	738.6	739.5
165°	750.0	749.6	749.3	748.9	748.5	748.2	748.1	748.0	747.9	747.7	748.8
167.5°	757.3	756.8	756.3	755.8	755.3	755.0	755.0	755.0	755.0	755.0	756.1
170°	761.4	760.9	760.4	759.9	759.4	759.1	759.1	759.1	759.1	759.1	760.2
172.5°	764.2	763.6	762.9	762.3	761.7	761.5	761.6	761.7	761.8	761.9	762.9
175°	767.7	767.1	766.4	765.8	765.2	764.9	765.0	765.2	765.3	765.4	766.3
177.5°	768.6	768.1	767.6	767.1	766.6	766.4	766.5	766.6	766.7	766.8	767.6
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P331970

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8
2.5°	1213.1	1215.0	1216.8	1217.7	1217.5	1217.3	1217.1	1216.9
5°	1206.7	1209.0	1211.4	1212.3	1211.8	1211.4	1210.9	1210.4
7.5°	1193.9	1196.0	1198.1	1199.0	1198.7	1198.4	1198.1	1197.9
10°	1182.2	1184.2	1186.3	1187.2	1186.7	1186.2	1185.8	1185.3
12.5°	1169.3	1170.8	1172.4	1173.0	1172.7	1172.4	1172.2	1171.9
15°	1146.1	1147.9	1149.8	1150.0	1148.6	1147.2	1145.9	1144.5
17.5°	1116.7	1118.0	1119.3	1119.7	1119.2	1118.7	1118.2	1117.7
20°	1095.0	1095.9	1096.9	1097.0	1096.3	1095.6	1094.9	1094.2
22.5°	1072.0	1072.8	1073.5	1073.4	1072.6	1071.7	1070.8	1069.9
25°	1033.9	1034.2	1034.4	1034.2	1033.5	1032.8	1032.1	1031.4
27.5°	993.4	993.6	993.8	993.4	992.6	991.7	990.8	989.9
30°	965.4	965.4	965.4	964.6	963.0	961.3	959.7	958.1
32.5°	936.0	934.7	933.4	932.3	931.4	930.5	929.6	928.8
35°	888.3	886.9	885.5	884.2	883.0	881.9	880.7	879.5
37.5°	838.9	837.2	835.6	834.4	833.6	832.9	832.1	831.4
40°	806.7	804.9	803.0	801.6	800.7	799.7	798.8	797.9
42.5°	773.2	771.3	769.5	768.1	767.2	766.2	765.3	764.4
45°	723.2	720.4	717.6	715.6	714.5	713.3	712.1	711.0
47.5°	670.5	667.8	665.0	663.1	662.1	661.1	660.1	659.0
50°	635.7	633.1	630.6	628.6	627.2	625.8	624.4	623.0
52.5°	600.4	598.2	596.0	594.3	592.9	591.5	590.1	588.7
55°	546.7	544.1	541.6	539.7	538.5	537.4	536.2	535.1
57.5°	493.8	491.6	489.3	487.5	486.1	484.8	483.4	482.1
60°	456.5	454.4	452.3	450.7	449.5	448.4	447.2	446.1
62.5°	420.5	418.4	416.3	414.9	414.1	413.3	412.5	411.7
65°	366.9	365.1	363.2	361.9	361.2	360.5	359.8	359.1
67.5°	313.8	312.2	310.5	309.2	308.3	307.3	306.3	305.3
70°	279.5	277.8	276.2	274.8	273.6	272.5	271.3	270.1
72.5°	244.6	243.2	241.8	240.7	240.1	239.5	238.9	238.3
75°	194.5	193.4	192.2	191.3	190.6	189.9	189.2	188.5
77.5°	147.7	146.9	146.1	145.8	145.8	145.8	145.8	145.8
80°	117.9	117.6	117.4	117.3	117.3	117.3	117.3	117.3
82.5°	90.7	90.3	89.8	89.5	89.4	89.2	89.0	88.8
85°	51.4	51.0	50.5	50.3	50.3	50.3	50.3	50.3
87.5°	21.0	20.9	20.8	20.8	20.9	20.9	21.0	21.0
90°	14.7	15.2	15.7	16.1	16.4	16.6	16.9	17.1
92.5°	16.2	17.0	17.8	18.3	18.5	18.6	18.8	18.9
95°	19.5	20.3	21.2	21.7	21.7	21.7	21.7	21.7
97.5°	20.4	21.4	22.4	23.0	23.1	23.2	23.4	23.5
100°	20.8	21.9	22.9	23.4	23.6	23.7	23.8	24.0
102.5°	31.2	28.1	25.0	23.5	23.7	24.0	24.2	24.4
105°	80.0	57.6	35.2	24.1	24.3	24.6	24.8	25.1
107.5°	196.0	179.6	163.1	146.5	129.5	112.6	95.7	78.8
110°	248.9	244.7	240.5	229.3	211.2	193.1	175.0	156.8



TEST NUMBER: P331970

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	286.1	286.2	286.3	284.4	280.6	276.7	272.9	269.1
115°	329.9	331.2	332.5	333.3	333.8	334.4	334.9	335.4
117.5°	369.6	370.6	371.6	372.2	372.3	372.4	372.5	372.6
120°	395.6	396.6	397.6	398.1	398.1	398.1	398.1	398.1
122.5°	421.0	421.7	422.4	422.8	422.9	423.0	423.1	423.2
125°	456.8	457.0	457.3	457.6	457.8	458.1	458.3	458.6
127.5°	492.7	493.1	493.5	493.6	493.3	493.1	492.8	492.6
130°	514.3	514.8	515.3	515.5	515.2	515.0	514.7	514.5
132.5°	534.9	535.4	535.9	536.0	535.6	535.2	534.9	534.5
135°	566.0	566.4	566.7	566.7	566.4	566.0	565.6	565.2
137.5°	593.7	594.3	594.9	595.1	594.8	594.6	594.3	594.1
140°	611.3	611.8	612.3	612.4	612.2	611.9	611.7	611.4
142.5°	628.0	628.4	628.8	628.8	628.5	628.1	627.7	627.4
145°	651.3	651.5	651.8	651.9	651.9	651.9	651.9	651.9
147.5°	672.2	672.4	672.7	672.5	671.9	671.3	670.8	670.2
150°	684.9	685.2	685.4	685.4	685.0	684.6	684.2	683.9
152.5°	696.3	696.7	697.2	697.1	696.6	696.0	695.4	694.8
155°	711.9	712.6	713.2	713.1	712.4	711.6	710.9	710.1
157.5°	725.5	726.3	727.1	726.9	725.9	725.0	724.0	723.0
160°	733.3	734.0	734.8	734.7	733.9	733.0	732.1	731.2
162.5°	740.3	741.2	742.1	742.1	741.3	740.5	739.7	739.0
165°	749.8	750.8	751.8	751.9	751.0	750.1	749.2	748.3
167.5°	757.1	758.1	759.1	759.1	758.1	757.1	756.1	755.0
170°	761.2	762.2	763.2	763.2	762.2	761.2	760.2	759.1
172.5°	763.9	764.9	765.9	765.9	764.8	763.7	762.5	761.4
175°	767.2	768.1	769.0	768.9	767.9	766.9	765.9	764.8
177.5°	768.4	769.2	770.0	769.9	768.9	767.9	766.9	765.9
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7

(END OF REPORT)