

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331918-830

Luminaire Tested: **S123DIP-S560D365U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331918-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D365U830-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3424.1 lumens
Efficiency: N/A
Efficacy: 124.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331918-830

CATALOG NUMBER: S123DIP-S560D365U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331918-830

CATALOG NUMBER: S123DIP-S560D365U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69	64
1	101	96	92	89	94	91	87	84	80	77	75	70	68	66	61	59	58	54
2	92	84	78	72	86	79	74	69	70	66	62	61	58	55	53	51	49	45
3	84	74	66	60	78	70	63	58	62	56	52	54	50	47	47	44	41	38
4	77	65	57	51	72	62	54	49	55	49	44	48	44	40	42	39	36	33
5	70	58	50	44	66	55	48	42	49	43	38	43	39	35	38	34	31	28
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	35	31	27	25
7	60	47	39	34	56	45	38	32	40	34	30	36	31	27	32	28	24	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20
9	52	39	32	27	49	38	30	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9038	9038	9038
5°	9081	8956	9018
10°	9021	8878	8933
15°	8914	8778	8795
20°	8791	8635	8643
25°	8626	8464	8445
30°	8444	8274	8211
35°	8253	8073	7970
40°	8056	7852	7731
45°	7837	7649	7462
50°	7618	7400	7194
55°	7330	7141	6923
60°	7042	6837	6622
65°	6788	6510	6306
70°	6408	6134	5860
75°	5856	5644	5407
80°	5281	5058	5015
85°	4631	4458	4286



TEST NUMBER: P331918-830

CATALOG NUMBER: S123DIP-S560D365U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	2.3
10°-20°	223.3	6.5
20°-30°	329.9	9.6
30°-40°	385.4	11.3
40°-50°	387.4	11.3
50°-60°	340.3	9.9
60°-70°	253.5	7.4
70°-80°	144.5	4.2
80°-90°	42.7	1.2
90°-100°	91.6	2.7
100°-110°	259.3	7.6
110°-120°	255.1	7.4
120°-130°	203.5	5.9
130°-140°	160.4	4.7
140°-150°	119.7	3.5
150°-160°	83.4	2.4
160°-170°	49.0	1.4
170°-180°	16.0	0.5
0°-30°	632.3	18.5
0°-40°	1017.7	29.7
0°-60°	1745.5	51.0
0°-90°	2186.2	63.8
90°-120°	605.9	17.7
90°-150°	1089.5	31.8
90°-180°	1238.0	36.2
0°-180°	3424.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	840	840	840	840	840	
5°	840	837	829	836	835	80
15°	800	797	788	793	789	225
25°	726	722	713	713	711	334
35°	628	624	614	610	606	393
45°	515	512	502	494	490	397
55°	391	389	380	373	369	350
65°	266	263	256	250	248	263
75°	141	138	136	132	130	151
85°	38	36	36	35	35	41
90°	1	4	8	9	10	3
95°	11	37	198	58	39	12
105°	39	57	268	468	424	41
115°	68	85	205	449	515	68
125°	95	112	191	346	406	84
135°	111	133	188	285	329	86
145°	127	145	186	234	258	80
155°	144	156	180	205	214	66
165°	158	162	173	183	186	44
175°	164	164	166	168	168	16
180°	165	165	165	165	165	



TEST NUMBER: P331918-830

CATALOG NUMBER: S123DIP-S560D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	842.5	842.1	841.6	841.0	840.6	839.5	838.1	836.7	835.4	834.0	835.2
5°	840.4	839.6	838.8	838.0	837.2	835.9	834.2	832.4	830.7	828.9	830.5
7.5°	832.2	831.4	830.6	829.8	829.0	827.6	825.9	824.0	822.2	820.4	821.8
10°	825.3	824.4	823.7	822.8	822.1	820.6	818.5	816.4	814.4	812.3	813.7
12.5°	816.1	815.3	814.6	814.0	813.3	812.0	810.0	808.0	806.2	804.2	805.2
15°	799.9	799.4	798.7	798.1	797.4	796.1	794.0	791.9	789.8	787.7	789.0
17.5°	781.4	780.5	779.7	778.8	778.0	776.6	774.5	772.4	770.3	768.2	769.1
20°	767.5	766.6	765.5	764.6	763.6	762.1	760.1	758.0	755.8	753.8	754.4
22.5°	751.9	750.9	750.0	749.0	748.0	746.5	744.4	742.3	740.3	738.2	738.7
25°	726.3	725.4	724.4	723.5	722.5	721.0	718.9	716.8	714.7	712.7	712.8
27.5°	699.1	698.1	697.2	696.3	695.3	693.7	691.4	689.3	687.0	684.8	684.9
30°	679.4	678.6	677.8	677.0	676.2	674.7	672.4	670.1	668.0	665.7	665.7
32.5°	659.8	658.7	657.6	656.6	655.5	654.1	652.4	650.6	648.9	647.2	646.3
35°	628.1	627.2	626.2	625.3	624.3	622.7	620.7	618.6	616.5	614.4	613.5
37.5°	595.8	594.6	593.3	592.1	590.9	589.3	587.1	585.0	582.9	580.8	579.7
40°	573.3	572.3	571.4	570.4	569.4	567.8	565.5	563.4	561.1	558.8	557.5
42.5°	550.7	549.7	548.6	547.4	546.4	544.7	542.4	540.3	538.0	535.7	534.4
45°	514.8	514.2	513.5	512.8	512.2	510.9	508.8	506.7	504.6	502.5	500.6
47.5°	479.1	478.2	477.3	476.4	475.4	473.9	472.0	470.0	468.1	466.1	464.2
50°	454.9	454.0	453.3	452.4	451.7	450.3	448.1	446.0	443.9	441.9	440.1
52.5°	429.4	428.9	428.4	427.8	427.3	425.8	423.7	421.5	419.2	417.1	415.6
55°	390.6	390.4	390.3	390.1	389.9	388.8	386.7	384.7	382.6	380.5	378.7
57.5°	353.6	353.1	352.5	352.0	351.5	350.3	348.6	347.0	345.3	343.7	342.1
60°	327.1	326.9	326.8	326.6	326.4	325.4	323.5	321.5	319.6	317.6	316.2
62.5°	303.4	302.9	302.6	302.2	301.7	300.6	298.6	296.7	294.7	292.8	291.4
65°	266.5	265.6	264.9	264.0	263.3	262.0	260.4	258.8	257.2	255.6	254.3
67.5°	227.2	226.6	225.8	225.2	224.4	223.5	222.3	221.0	219.8	218.7	217.5
70°	203.6	202.6	201.7	200.8	199.7	198.8	197.8	196.9	195.9	194.9	193.8
72.5°	178.8	178.0	177.4	176.6	176.0	175.0	174.0	172.9	171.7	170.7	169.7
75°	140.8	140.2	139.5	138.8	138.3	137.7	137.1	136.7	136.2	135.7	135.0
77.5°	107.2	106.8	106.4	106.1	105.8	105.3	104.7	104.2	103.5	102.9	102.5
80°	85.2	84.7	84.3	83.8	83.2	82.8	82.6	82.2	81.9	81.6	81.4
82.5°	63.8	63.7	63.6	63.5	63.4	63.3	63.3	63.2	63.2	63.2	62.8
85°	37.5	37.2	36.9	36.6	36.3	36.1	36.1	36.1	36.1	36.1	35.8
87.5°	15.2	14.9	14.6	14.4	14.2	14.0	14.1	14.2	14.3	14.3	14.1
90°	0.7	1.3	2.0	3.0	3.7	4.3	5.4	6.3	7.4	8.3	8.0
92.5°	4.1	6.1	9.0	11.5	14.3	19.2	28.0	42.3	56.4	51.2	38.6
95°	11.3	12.3	16.0	21.7	30.3	43.3	71.6	121.2	175.9	197.6	160.2
97.5°	19.3	19.6	22.5	27.4	36.0	50.0	77.1	133.0	224.1	306.1	327.4
100°	24.7	25.0	27.3	32.0	40.0	53.0	76.3	125.5	213.2	315.5	381.1
102.5°	30.3	30.8	32.9	37.3	44.5	56.5	77.4	119.1	197.2	298.1	383.7
105°	38.6	39.7	41.7	45.6	51.9	62.3	80.3	114.6	177.6	267.8	363.4
107.5°	47.6	48.5	50.5	54.4	60.3	69.9	85.8	114.2	165.0	241.0	327.8
110°	53.9	55.0	56.6	60.3	66.0	75.3	90.3	115.6	160.2	225.8	305.5



TEST NUMBER: P331918-830

CATALOG NUMBER: S123DIP-S560D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	59.9	60.8	62.5	66.2	71.8	80.9	94.8	118.3	157.5	215.7	286.0
115°	68.2	69.7	71.6	74.9	80.6	89.6	102.3	122.5	156.6	204.8	262.5
117.5°	76.7	78.2	79.9	83.0	89.4	97.6	110.2	128.3	157.1	198.4	248.3
120°	82.6	83.6	85.3	88.6	94.9	103.2	115.3	132.5	158.3	195.5	240.8
122.5°	87.7	88.7	90.3	94.0	100.0	108.9	120.6	136.6	160.0	193.7	234.7
125°	94.9	95.6	97.6	101.2	107.5	116.6	128.3	142.9	162.9	191.1	226.9
127.5°	100.5	101.4	104.0	107.6	114.6	123.7	134.9	148.1	166.1	190.0	219.9
130°	104.0	104.9	107.9	111.9	118.9	127.9	138.9	151.6	168.2	189.2	216.1
132.5°	106.6	107.8	111.1	115.9	122.9	131.7	142.3	154.8	169.8	188.9	212.7
135°	111.2	112.5	116.2	121.2	128.3	137.2	147.5	158.9	172.2	188.5	208.2
137.5°	115.6	117.1	120.6	125.9	132.9	141.2	151.2	161.9	173.8	187.8	204.2
140°	118.6	120.3	123.6	128.9	135.5	143.9	153.5	163.5	174.8	187.6	201.8
142.5°	121.8	123.2	126.8	131.6	138.3	146.0	155.4	165.1	175.7	187.0	199.7
145°	126.9	127.9	130.9	135.9	141.6	149.2	157.9	166.8	176.2	186.2	196.8
147.5°	132.1	132.7	135.6	140.0	145.4	151.9	159.9	168.0	176.2	184.9	194.1
150°	135.5	135.9	138.6	142.9	147.5	153.5	161.2	168.2	176.2	183.9	192.2
152.5°	139.0	139.1	141.8	145.5	149.7	155.4	162.0	168.7	175.4	182.6	190.0
155°	144.2	144.2	146.2	149.6	153.3	157.9	163.5	168.9	174.6	180.2	186.8
157.5°	148.4	148.6	150.2	153.2	156.3	159.9	164.4	169.2	173.4	178.1	183.2
160°	151.6	151.6	152.9	155.5	157.9	161.2	165.2	169.2	172.9	176.5	180.9
162.5°	153.9	153.9	155.0	157.1	159.2	162.0	165.5	168.9	171.8	174.9	178.4
165°	157.5	157.2	157.9	159.6	160.9	163.2	165.9	168.2	170.2	172.6	175.2
167.5°	160.2	159.9	160.2	161.5	162.4	163.9	165.8	167.7	168.6	170.1	172.1
170°	161.8	161.2	161.6	162.5	163.2	163.9	165.5	166.8	167.6	168.5	170.2
172.5°	163.0	162.5	162.6	163.3	163.7	164.1	165.5	166.6	166.7	167.2	168.3
175°	164.2	163.9	163.5	164.2	164.2	164.6	165.2	165.9	165.5	165.5	166.2
177.5°	164.9	164.6	164.3	164.6	164.6	164.6	164.9	165.3	164.9	164.6	164.9
180°	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6



TEST NUMBER: P331918-830

CATALOG NUMBER: S123DIP-S560D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	836.5	837.7	839.1	839.6	839.5	839.3	839.2	839.1
5°	832.1	833.7	835.3	835.9	835.6	835.3	835.0	834.6
7.5°	823.2	824.6	826.1	826.7	826.5	826.3	826.1	826.0
10°	815.1	816.6	818.0	818.6	818.3	817.9	817.7	817.3
12.5°	806.3	807.4	808.4	808.8	808.6	808.4	808.2	808.0
15°	790.3	791.5	792.9	793.0	792.0	791.1	790.1	789.2
17.5°	770.1	770.9	771.8	772.0	771.8	771.4	771.0	770.6
20°	755.1	755.7	756.3	756.4	755.9	755.4	755.0	754.5
22.5°	739.2	739.7	740.3	740.2	739.6	739.0	738.4	737.7
25°	712.9	713.1	713.2	713.1	712.7	712.2	711.6	711.1
27.5°	685.0	685.1	685.2	685.0	684.4	683.8	683.2	682.6
30°	665.7	665.7	665.7	665.2	664.0	662.9	661.8	660.6
32.5°	645.5	644.5	643.6	642.8	642.2	641.7	641.0	640.5
35°	612.5	611.5	610.6	609.7	608.9	608.1	607.3	606.5
37.5°	578.4	577.3	576.2	575.3	574.9	574.3	573.8	573.3
40°	556.3	555.0	553.7	552.7	552.0	551.5	550.8	550.2
42.5°	533.2	531.9	530.6	529.6	529.0	528.4	527.7	527.1
45°	498.7	496.7	494.8	493.4	492.7	491.8	491.1	490.2
47.5°	462.3	460.4	458.5	457.2	456.6	455.8	455.2	454.4
50°	438.4	436.6	434.8	433.5	432.4	431.5	430.6	429.6
52.5°	414.1	412.6	411.0	409.7	408.8	407.8	406.9	406.0
55°	376.9	375.2	373.4	372.1	371.4	370.5	369.8	368.9
57.5°	340.5	338.9	337.4	336.1	335.2	334.3	333.4	332.4
60°	314.8	313.4	311.9	310.8	310.0	309.2	308.4	307.6
62.5°	289.9	288.5	287.1	286.1	285.5	285.0	284.5	283.9
65°	253.0	251.8	250.4	249.6	249.1	248.6	248.2	247.6
67.5°	216.4	215.3	214.1	213.2	212.5	211.9	211.2	210.6
70°	192.7	191.6	190.5	189.5	188.7	187.8	187.1	186.2
72.5°	168.7	167.7	166.7	166.0	165.6	165.1	164.8	164.3
75°	134.1	133.4	132.5	131.9	131.4	130.9	130.4	130.0
77.5°	101.9	101.3	100.8	100.5	100.5	100.5	100.5	100.5
80°	81.2	81.1	81.0	80.9	80.9	80.9	80.9	80.9
82.5°	62.5	62.2	61.9	61.7	61.6	61.5	61.4	61.3
85°	35.4	35.2	34.8	34.7	34.7	34.7	34.7	34.7
87.5°	14.1	14.0	13.9	14.0	13.9	14.0	14.1	14.0
90°	8.3	8.7	9.0	9.6	9.3	9.6	10.0	9.6
92.5°	28.1	22.2	19.6	17.9	17.3	16.3	16.7	16.0
95°	119.9	81.2	63.6	51.7	45.3	42.3	40.0	38.6
97.5°	298.9	239.4	196.4	156.7	132.1	117.1	108.0	105.2
100°	392.7	365.7	326.8	279.5	245.8	221.5	208.5	208.9
102.5°	423.9	423.0	400.3	370.3	344.1	324.9	314.1	306.3
105°	433.0	466.3	472.6	464.0	448.7	436.0	425.4	423.7
107.5°	406.7	460.8	490.0	501.9	502.2	497.9	494.3	491.3
110°	381.7	443.0	484.9	508.3	517.6	520.3	519.6	519.0



TEST NUMBER: P331918-830

CATALOG NUMBER: S123DIP-S560D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	356.9	419.5	466.6	496.5	513.6	521.9	524.4	524.5
115°	324.0	382.0	431.0	467.3	492.3	506.9	513.6	515.3
117.5°	300.3	350.3	394.3	431.1	457.2	474.0	483.5	485.8
120°	287.8	332.7	372.7	406.3	432.6	451.3	459.3	461.3
122.5°	278.0	318.6	355.6	386.9	410.3	427.1	435.8	438.4
125°	264.8	301.1	333.1	359.8	381.1	395.7	404.1	406.3
127.5°	253.4	285.7	314.5	338.8	357.8	370.3	377.9	379.9
130°	246.1	276.2	303.1	325.7	343.4	355.4	362.4	365.0
132.5°	239.5	267.0	292.2	313.8	330.4	342.3	348.6	350.4
135°	230.5	254.1	275.8	294.7	311.1	321.1	327.1	329.4
137.5°	222.3	241.7	260.3	276.8	290.5	300.7	305.7	307.3
140°	217.5	234.5	250.4	264.8	277.5	286.8	292.1	291.8
142.5°	213.0	227.5	241.4	253.8	264.7	273.0	277.7	277.4
145°	207.5	218.5	229.1	238.8	247.1	254.1	256.8	257.5
147.5°	203.0	211.8	220.4	227.2	233.6	238.3	240.8	241.1
150°	199.8	207.5	214.5	220.8	225.8	229.5	231.5	231.5
152.5°	196.9	203.5	209.7	215.0	218.9	222.3	223.5	223.5
155°	192.6	197.8	202.8	206.8	209.8	212.5	213.2	213.5
157.5°	187.8	192.3	196.1	199.3	201.9	203.9	204.4	204.3
160°	185.2	188.9	192.2	194.5	196.8	198.9	198.9	198.5
162.5°	182.0	185.1	188.2	190.3	191.8	193.5	193.5	193.2
165°	177.9	179.8	182.2	183.9	185.2	186.5	186.2	186.2
167.5°	174.3	175.8	177.1	178.3	178.9	179.8	179.6	179.6
170°	171.8	172.9	174.2	174.8	175.2	175.9	175.5	175.5
172.5°	169.8	170.5	171.5	171.9	172.0	172.7	172.1	171.8
175°	166.8	167.2	167.9	167.9	167.9	168.2	167.9	167.6
177.5°	165.0	165.3	165.6	165.6	165.3	165.6	165.0	165.0
180°	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6

(END OF REPORT)