

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331974

Luminaire Tested: **S123DIP-S775D805U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331974
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D805U835-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6021.8 lumens
Efficiency: N/A
Efficacy: 131.2 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331974

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331974

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51	46
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	47	45	44	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37	33
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	38	35	32	29
5	70	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	42	36	42	37	32	37	32	29	31	28	25	22
7	59	47	39	34	55	44	37	32	39	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	26	23	20	18
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	21	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11630	11630	11630	11630
5°	13870	11681	10351	11681
10°	17361	11622	9349	11622
15°	21293	11528	8704	11528
20°	25366	11381	8287	11381
25°	26935	11204	8195	11204
30°	23086	11074	8238	11074
35°	16056	10889	8324	10889
40°	12094	10673	8297	10673
45°	10041	10353	8193	10353
50°	8994	9696	8118	9696
55°	8409	8989	8017	8989
60°	7890	8249	7935	8249
65°	7414	7521	7679	7521
70°	6952	6688	7314	6688
75°	6226	5856	6704	5856
80°	5455	4804	5777	4804
85°	4273	3495	3878	3495



TEST NUMBER: P331974

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.4	1.8
10°-20°	341.3	5.7
20°-30°	572.8	9.5
30°-40°	648.6	10.8
40°-50°	581.7	9.7
50°-60°	469.4	7.8
60°-70°	327.1	5.4
70°-80°	171.9	2.9
80°-90°	45.0	0.7
90°-100°	64.8	1.1
100°-110°	194.1	3.2
110°-120°	330.1	5.5
120°-130°	434.2	7.2
130°-140°	488.0	8.1
140°-150°	479.7	8.0
150°-160°	403.8	6.7
160°-170°	268.8	4.5
170°-180°	94.1	1.6
0°-30°	1020.6	16.9
0°-40°	1669.2	27.7
0°-60°	2720.2	45.2
0°-90°	3264.2	54.2
90°-120°	589.0	9.8
90°-150°	1990.8	33.1
90°-180°	2758.0	45.8
0°-180°	6021.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1080	1080	1080	1080	1080	
5°	1284	1081	958	1081	1284	133
15°	1911	1034	781	1034	1911	552
25°	2268	943	690	943	2268	995
35°	1222	829	634	829	1222	794
45°	660	680	538	680	660	522
55°	448	479	427	479	448	402
65°	291	295	302	295	291	290
75°	150	141	161	141	150	160
85°	35	28	31	28	35	41
90°	24	1	24	1	24	13
95°	61	46	61	46	61	63
105°	186	176	186	176	186	197
115°	333	332	333	332	333	330
125°	481	486	481	486	481	430
135°	630	631	630	631	630	484
145°	765	765	765	765	765	478
155°	875	876	875	876	875	403
165°	952	955	952	955	952	268
175°	989	993	989	993	989	94
180°	995	995	995	995	995	



TEST NUMBER: P331974

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1146.7	1145.9	1143.8	1145.5	1142.1	1137.5	1137.1	1132.9	1120.7	1119.9	1116.6
5°	1283.7	1279.5	1279.0	1278.4	1271.1	1261.2	1242.3	1240.7	1215.6	1203.0	1187.9
7.5°	1461.0	1463.2	1455.6	1448.9	1426.5	1411.7	1391.5	1365.6	1334.8	1303.5	1282.6
10°	1588.4	1605.6	1584.2	1569.5	1555.9	1530.2	1500.4	1463.2	1426.1	1382.6	1349.6
12.5°	1724.9	1733.4	1729.1	1715.3	1694.1	1655.1	1602.2	1561.2	1527.0	1454.6	1425.4
15°	1910.8	1942.8	1922.4	1875.2	1876.3	1839.1	1770.0	1694.1	1653.8	1590.4	1504.1
17.5°	2108.9	2112.9	2104.2	2065.0	2038.8	1987.7	1923.9	1851.2	1769.5	1692.8	1601.2
20°	2214.5	2211.3	2193.0	2172.6	2127.6	2087.8	2018.2	1937.0	1832.3	1756.9	1656.9
22.5°	2273.1	2267.9	2259.2	2242.1	2204.6	2161.9	2099.4	2010.7	1911.1	1807.2	1691.7
25°	2267.9	2274.7	2275.7	2271.0	2257.9	2232.3	2183.1	2112.4	2012.9	1879.4	1759.0
27.5°	2062.7	2072.3	2100.3	2125.1	2152.8	2181.1	2177.3	2142.2	2068.6	1953.4	1806.1
30°	1857.4	1836.5	1888.3	1953.8	1998.3	2076.8	2120.8	2123.4	2082.0	1983.1	1839.6
32.5°	1572.6	1595.7	1618.6	1699.1	1796.4	1884.6	1972.1	2042.6	2050.6	1984.8	1859.3
35°	1221.9	1250.7	1292.6	1334.4	1439.2	1529.2	1683.1	1817.1	1923.9	1938.1	1861.1
37.5°	984.6	998.9	1025.4	1067.3	1135.8	1242.6	1361.7	1531.1	1685.8	1800.9	1805.9
40°	860.7	864.9	894.7	926.6	982.1	1070.1	1177.4	1327.1	1512.4	1673.2	1740.2
42.5°	767.7	776.9	789.6	820.2	864.4	930.6	1030.4	1154.1	1324.0	1509.0	1640.1
45°	659.6	670.1	678.0	698.4	729.8	774.3	843.9	957.0	1086.3	1277.4	1453.8
47.5°	588.2	589.1	594.9	610.3	631.7	665.1	714.3	787.0	905.7	1060.6	1241.8
50°	537.1	545.5	547.6	559.6	576.4	601.0	641.8	703.6	801.0	937.1	1103.6
52.5°	501.1	503.6	509.5	518.2	532.8	552.0	587.4	635.8	712.2	828.2	981.3
55°	448.1	448.1	453.9	460.7	469.1	486.3	509.9	545.5	603.6	693.7	820.4
57.5°	399.1	401.7	405.8	407.9	415.0	426.5	446.1	473.2	516.5	585.8	686.5
60°	366.5	371.2	370.7	374.8	381.1	390.0	406.8	428.8	467.5	523.0	607.8
62.5°	338.0	337.7	337.6	342.6	348.9	357.4	368.2	387.3	420.2	469.4	541.6
65°	291.1	290.0	293.7	296.8	298.9	305.2	313.6	330.3	352.3	389.0	445.0
67.5°	249.4	246.4	248.4	249.4	253.0	257.9	265.7	276.1	293.6	323.0	365.2
70°	220.9	218.3	217.8	218.8	222.0	225.6	231.4	241.3	257.6	281.1	312.0
72.5°	191.6	189.8	189.7	192.0	193.5	195.9	200.0	209.1	222.0	239.7	268.5
75°	149.7	149.7	149.7	150.2	151.8	153.9	157.1	161.8	171.7	184.3	203.6
77.5°	112.2	112.1	111.5	111.4	113.7	114.7	115.4	119.8	125.3	133.8	147.9
80°	88.0	85.3	86.4	88.0	89.0	89.5	91.1	92.1	96.9	101.6	111.5
82.5°	65.3	63.1	63.3	65.8	66.0	66.5	68.1	69.5	71.3	75.6	80.9
85°	34.6	34.6	35.1	35.1	35.6	35.1	36.6	37.2	37.2	39.8	42.9
87.5°	17.3	16.3	16.7	17.0	16.6	16.9	17.2	17.4	17.7	18.0	18.0
90°	23.5	23.1	22.8	22.4	22.1	21.5	20.8	20.2	19.5	18.8	16.5
92.5°	31.6	31.8	32.0	32.2	32.4	32.2	31.7	31.1	30.6	30.0	28.7
95°	61.0	61.0	61.0	61.0	61.0	60.6	59.9	59.2	58.6	57.9	56.5
97.5°	93.8	93.9	94.0	94.0	94.1	93.7	92.9	92.1	91.3	90.5	89.5
100°	118.8	118.5	118.1	117.8	117.5	117.0	116.5	116.0	115.5	114.9	114.1
102.5°	144.5	144.6	144.6	144.7	144.8	144.5	144.0	143.5	143.0	142.5	141.3
105°	186.1	185.7	185.4	185.0	184.7	184.5	184.5	184.5	184.5	184.5	183.0
107.5°	229.4	229.6	229.8	230.0	230.2	230.1	229.5	228.9	228.4	227.8	227.2
110°	258.8	259.1	259.5	259.8	260.2	260.0	259.3	258.6	257.9	257.2	256.9



TEST NUMBER: P331974

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	290.1	290.1	290.2	290.3	290.3	290.0	289.1	288.3	287.5	286.6	286.6
115°	333.1	333.2	333.4	333.6	333.8	333.8	333.6	333.4	333.2	333.1	333.4
117.5°	376.7	377.2	377.7	378.2	378.6	378.9	378.9	379.0	379.0	379.0	379.5
120°	407.3	407.7	408.0	408.4	408.7	409.0	409.2	409.3	409.5	409.7	410.6
122.5°	436.7	437.2	437.7	438.2	438.7	439.2	439.6	440.1	440.5	441.0	441.4
125°	480.8	481.5	482.2	482.9	483.6	484.3	485.0	485.7	486.4	487.1	487.4
127.5°	524.8	525.6	526.4	527.2	528.0	528.9	529.8	530.8	531.8	532.7	533.1
130°	553.5	554.8	556.0	557.2	558.4	559.4	560.1	560.8	561.4	562.1	562.7
132.5°	583.6	584.5	585.4	586.4	587.3	588.2	589.0	589.9	590.7	591.5	591.9
135°	630.2	630.5	630.9	631.2	631.6	632.1	632.8	633.5	634.2	634.9	635.0
137.5°	671.3	672.0	672.6	673.3	673.9	674.6	675.4	676.1	676.8	677.5	677.1
140°	698.2	699.4	700.6	701.8	703.1	703.7	703.9	704.1	704.3	704.4	704.3
142.5°	725.7	726.6	727.6	728.5	729.5	730.0	730.2	730.4	730.5	730.7	730.4
145°	765.4	766.1	766.8	767.5	768.2	768.6	768.8	769.0	769.2	769.3	768.8
147.5°	800.8	801.8	802.8	803.9	804.9	805.5	805.5	805.5	805.5	805.5	805.0
150°	823.3	824.3	825.4	826.4	827.5	828.0	828.0	828.0	828.0	828.0	827.6
152.5°	845.2	846.1	847.0	847.9	848.8	849.1	848.8	848.5	848.3	848.0	847.8
155°	874.9	876.1	877.3	878.5	879.7	880.0	879.3	878.6	877.9	877.2	877.1
157.5°	901.9	902.9	903.9	904.9	905.8	905.9	905.2	904.5	903.8	903.0	902.9
160°	919.4	920.1	920.8	921.5	922.2	922.1	921.3	920.4	919.5	918.7	918.7
162.5°	932.6	933.7	934.8	935.9	937.0	937.2	936.3	935.4	934.5	933.7	933.5
165°	951.5	952.7	953.9	955.2	956.4	956.5	955.4	954.4	953.3	952.3	952.3
167.5°	967.6	968.7	969.8	970.8	971.9	971.9	970.8	969.8	968.7	967.6	967.5
170°	975.7	977.0	978.2	979.4	980.6	980.6	979.4	978.2	977.0	975.7	975.7
172.5°	982.0	983.2	984.4	985.6	986.9	986.9	985.9	984.8	983.7	982.6	982.6
175°	989.0	990.2	991.5	992.7	993.9	994.0	992.9	991.9	990.9	989.8	989.8
177.5°	992.8	993.8	994.7	995.7	996.7	996.7	995.9	995.1	994.2	993.4	993.4
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3



TEST NUMBER: P331974

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1114.0	1110.7	1107.3	1101.5	1096.5	1089.3	1087.2	1084.7	1077.2	1070.5	1065.5
5°	1182.1	1169.5	1151.2	1134.5	1120.9	1102.5	1092.1	1081.1	1065.4	1051.2	1039.7
7.5°	1253.3	1228.6	1200.1	1169.3	1140.6	1113.0	1090.7	1070.8	1048.8	1028.0	1011.8
10°	1309.8	1274.2	1234.5	1191.5	1154.9	1119.3	1089.4	1063.3	1035.0	1010.4	990.0
12.5°	1374.3	1321.6	1266.7	1214.6	1171.2	1121.8	1085.7	1052.4	1020.3	990.7	967.8
15°	1450.7	1383.7	1318.7	1247.0	1181.1	1119.3	1076.4	1034.5	997.3	966.9	937.6
17.5°	1520.2	1444.3	1358.7	1271.5	1191.9	1118.7	1058.6	1011.2	964.7	927.6	898.4
20°	1559.6	1473.2	1376.3	1285.8	1197.8	1116.1	1050.2	993.6	943.4	904.1	871.1
22.5°	1593.5	1492.4	1392.2	1295.4	1197.4	1109.4	1034.7	976.5	922.0	883.6	848.5
25°	1628.7	1507.7	1407.2	1293.6	1184.2	1093.1	1009.3	943.4	888.9	843.9	807.8
27.5°	1658.8	1506.7	1387.4	1265.2	1163.5	1072.2	982.7	912.0	854.2	805.3	768.6
30°	1678.9	1508.8	1366.9	1246.0	1143.4	1049.1	962.2	891.0	830.3	780.6	746.0
32.5°	1691.5	1507.5	1348.1	1219.2	1111.5	1028.2	940.0	866.3	803.9	755.0	721.7
35°	1698.8	1498.3	1315.6	1163.8	1060.1	979.0	905.2	828.7	763.3	717.7	680.1
37.5°	1684.2	1478.9	1277.9	1110.4	996.9	917.0	854.9	789.8	727.2	677.0	644.6
40°	1661.1	1466.4	1248.6	1072.7	953.3	876.4	823.5	759.6	697.8	650.2	619.8
42.5°	1617.1	1440.8	1216.3	1030.8	908.1	831.1	782.5	729.1	670.6	625.9	595.6
45°	1509.8	1385.2	1168.0	968.0	841.3	761.7	718.8	680.1	627.2	583.7	557.5
47.5°	1360.9	1301.6	1098.0	901.7	771.6	695.0	650.4	619.2	580.6	545.5	520.4
50°	1257.5	1232.9	1050.7	856.5	725.1	650.2	607.3	579.0	551.3	516.2	493.2
52.5°	1138.1	1153.3	995.4	809.6	677.7	604.1	563.7	541.3	516.1	487.3	467.2
55°	970.1	1025.0	899.9	730.8	607.3	537.1	498.9	479.0	464.4	442.9	425.6
57.5°	812.7	882.7	796.7	649.7	538.1	477.6	440.9	419.2	409.8	398.6	385.0
60°	719.3	788.4	723.0	595.2	491.6	434.0	401.5	383.2	373.8	365.9	354.4
62.5°	636.0	705.9	650.9	540.0	445.9	392.5	364.3	346.4	339.0	334.9	325.1
65°	521.4	581.6	545.0	453.9	380.6	333.5	307.8	295.3	288.5	286.9	280.6
67.5°	424.4	470.2	443.5	376.5	318.8	278.1	256.3	245.6	240.4	239.9	235.2
70°	360.7	403.6	383.2	322.5	272.8	240.8	222.0	212.5	209.4	208.9	206.3
72.5°	311.3	341.2	325.0	274.3	235.9	206.9	193.1	183.2	179.7	180.4	178.6
75°	230.3	252.9	243.4	208.4	177.5	158.6	147.1	140.8	137.7	139.3	137.2
77.5°	165.7	180.0	171.5	147.2	128.2	114.5	106.1	102.2	99.4	99.3	98.3
80°	125.1	133.5	128.8	114.1	98.4	86.9	80.1	77.5	75.9	75.4	74.9
82.5°	89.1	96.2	90.7	80.6	69.9	63.0	59.2	55.7	54.6	54.9	54.3
85°	45.0	47.6	45.5	39.3	35.1	31.9	29.8	28.3	27.2	27.7	26.7
87.5°	18.3	18.3	16.6	14.5	13.3	11.7	11.4	10.2	9.7	10.1	10.0
90°	14.2	12.0	9.7	7.7	6.0	4.3	2.5	0.8	2.5	4.3	6.0
92.5°	27.5	26.2	24.9	23.6	22.5	21.3	20.1	18.9	20.1	21.3	22.5
95°	55.1	53.7	52.3	51.0	49.8	48.6	47.3	46.1	47.3	48.6	49.8
97.5°	88.5	87.5	86.5	85.6	84.6	83.7	82.8	81.9	82.8	83.7	84.6
100°	113.2	112.3	111.5	110.5	109.5	108.4	107.4	106.3	107.4	108.4	109.5
102.5°	140.2	139.0	137.9	137.0	136.4	135.7	135.1	134.5	135.1	135.7	136.4
105°	181.4	179.8	178.3	177.3	177.0	176.6	176.3	175.9	176.3	176.6	177.0
107.5°	226.6	226.0	225.3	224.9	224.7	224.5	224.3	224.1	224.3	224.5	224.7
110°	256.5	256.2	255.8	255.5	255.1	254.8	254.4	254.1	254.4	254.8	255.1



TEST NUMBER: P331974

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	286.5	286.4	286.3	286.2	286.0	285.8	285.6	285.4	285.6	285.8	286.0
115°	333.8	334.1	334.5	334.4	333.8	333.3	332.8	332.3	332.8	333.3	333.8
117.5°	379.9	380.4	380.8	380.9	380.5	380.2	379.9	379.5	379.9	380.2	380.5
120°	411.4	412.3	413.2	413.1	412.0	411.0	409.9	408.9	409.9	411.0	412.0
122.5°	441.9	442.3	442.8	442.6	441.8	441.1	440.3	439.6	440.3	441.1	441.8
125°	487.8	488.1	488.5	488.4	487.9	487.3	486.8	486.3	486.8	487.3	487.9
127.5°	533.5	533.9	534.3	533.9	532.8	531.7	530.6	529.5	530.6	531.7	532.8
130°	563.2	563.7	564.2	563.8	562.4	561.0	559.6	558.2	559.6	561.0	562.4
132.5°	592.3	592.7	593.1	592.6	591.2	589.8	588.4	587.0	588.4	589.8	591.2
135°	635.2	635.4	635.6	635.1	634.1	633.0	632.0	630.9	632.0	633.0	634.1
137.5°	676.6	676.2	675.7	675.1	674.2	673.3	672.5	671.6	672.5	673.3	674.2
140°	704.1	703.9	703.7	703.2	702.4	701.5	700.6	699.7	700.6	701.5	702.4
142.5°	730.1	729.8	729.5	728.9	728.0	727.1	726.3	725.4	726.3	727.1	728.0
145°	768.3	767.8	767.2	766.8	766.5	766.1	765.8	765.4	765.8	766.1	766.5
147.5°	804.5	804.0	803.5	803.0	802.3	801.7	801.1	800.5	801.1	801.7	802.3
150°	827.3	826.9	826.6	826.2	825.9	825.5	825.2	824.8	825.2	825.5	825.9
152.5°	847.6	847.4	847.2	846.8	846.3	845.8	845.3	844.9	845.3	845.8	846.3
155°	876.9	876.7	876.5	876.4	876.4	876.4	876.4	876.4	876.4	876.4	876.4
157.5°	902.8	902.6	902.5	902.5	902.7	902.9	903.1	903.3	903.1	902.9	902.7
160°	918.7	918.7	918.7	918.8	919.2	919.5	919.9	920.2	919.9	919.5	919.2
162.5°	933.4	933.3	933.1	933.3	933.8	934.3	934.8	935.2	934.8	934.3	933.8
165°	952.3	952.3	952.3	952.5	953.1	953.6	954.1	954.6	954.1	953.6	953.1
167.5°	967.3	967.2	967.1	967.3	968.0	968.7	969.4	970.1	969.4	968.7	968.0
170°	975.7	975.7	975.7	976.1	976.8	977.5	978.2	978.9	978.2	977.5	976.8
172.5°	982.6	982.6	982.6	983.0	983.7	984.4	985.1	985.7	985.1	984.4	983.7
175°	989.8	989.8	989.8	990.2	990.9	991.6	992.2	992.9	992.2	991.6	990.9
177.5°	993.4	993.4	993.4	993.7	994.2	994.8	995.4	995.9	995.4	994.8	994.2
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3



TEST NUMBER: P331974

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1062.5	1059.6	1055.4	1049.1	1044.1	1036.1	1036.1	1037.4	1037.4	1037.0	1036.1
5°	1030.3	1022.4	1013.0	1002.0	990.5	979.0	976.9	972.7	969.6	967.5	964.8
7.5°	996.3	982.3	968.6	953.2	939.2	927.6	919.5	912.8	908.5	903.9	900.6
10°	973.2	955.9	939.7	923.5	905.7	891.6	882.7	876.4	871.7	867.5	865.4
12.5°	946.0	926.2	908.3	892.9	873.4	858.9	850.4	847.5	841.9	833.1	828.5
15°	906.2	887.9	866.4	842.9	833.4	815.6	805.7	801.0	797.8	791.0	788.9
17.5°	872.2	848.2	824.1	806.5	789.0	774.6	769.0	763.2	759.0	753.4	751.8
20°	845.0	823.5	801.5	782.7	764.3	748.6	743.9	739.7	735.5	732.9	730.8
22.5°	817.3	795.9	777.6	760.0	740.5	730.2	725.1	720.5	717.5	715.8	713.7
25°	778.5	759.6	739.2	723.5	707.8	701.0	697.8	695.2	693.1	690.5	690.0
27.5°	743.7	723.2	706.6	692.0	680.7	675.0	672.0	670.7	671.2	672.1	672.7
30°	717.7	698.9	685.3	672.7	662.3	657.0	656.5	656.5	658.6	659.1	660.2
32.5°	693.9	678.4	664.8	652.6	644.7	641.1	643.1	643.1	644.8	646.1	648.0
35°	659.1	645.5	635.0	624.6	617.8	619.3	620.4	621.4	624.0	627.2	629.3
37.5°	625.9	614.1	603.2	595.0	591.9	594.7	597.2	599.4	602.5	604.9	607.0
40°	602.0	593.1	582.7	575.3	576.4	578.0	580.1	582.7	585.3	586.9	589.0
42.5°	579.8	570.5	562.6	556.5	558.0	560.0	561.2	562.6	565.6	568.4	569.7
45°	546.0	538.7	531.4	527.7	528.8	529.8	530.8	532.4	535.0	537.1	537.7
47.5°	508.0	502.9	498.0	494.4	496.1	495.7	497.0	500.4	501.2	502.5	505.4
50°	483.7	479.0	473.3	472.2	472.2	472.2	472.7	476.9	476.9	479.0	481.1
52.5°	456.9	453.9	450.2	448.3	447.5	447.5	449.7	451.8	452.6	455.6	457.7
55°	417.2	414.1	411.0	409.4	408.3	409.4	413.6	414.6	417.2	418.8	420.4
57.5°	375.9	373.5	371.0	370.1	369.9	371.3	373.6	376.7	377.4	382.2	384.6
60°	348.7	345.0	342.9	342.9	341.9	346.6	345.5	350.8	351.8	354.9	358.6
62.5°	320.6	315.7	314.8	314.8	316.3	317.7	319.1	321.4	324.2	328.1	331.0
65°	275.4	272.8	276.4	275.9	274.8	278.0	278.0	280.6	283.7	287.4	293.2
67.5°	232.5	231.2	231.5	231.5	233.1	234.9	236.3	238.6	242.4	246.3	250.0
70°	203.6	205.2	202.6	204.7	206.3	206.8	207.8	211.0	215.2	217.8	222.0
72.5°	175.6	175.5	175.8	176.6	178.2	179.1	180.2	183.8	188.4	190.6	193.9
75°	135.1	134.5	136.1	136.1	138.7	139.8	140.8	142.4	146.6	149.7	152.3
77.5°	98.6	99.3	98.9	100.7	100.0	100.2	103.4	105.0	105.4	111.6	113.0
80°	74.3	75.4	75.9	76.4	77.0	75.9	79.6	81.1	81.1	84.8	87.4
82.5°	53.4	54.0	55.4	55.9	56.0	57.1	57.4	58.5	59.8	61.4	64.8
85°	26.7	28.3	28.8	28.3	28.8	27.7	29.3	29.8	30.4	30.4	30.4
87.5°	9.9	10.7	10.8	11.6	11.7	12.5	12.7	12.0	12.1	13.5	12.0
90°	7.7	9.7	12.0	14.2	16.5	18.8	19.5	20.2	20.8	21.5	22.1
92.5°	23.6	24.9	26.2	27.5	28.7	30.0	30.6	31.1	31.7	32.2	32.4
95°	51.0	52.3	53.7	55.1	56.5	57.9	58.6	59.2	59.9	60.6	61.0
97.5°	85.6	86.5	87.5	88.5	89.5	90.5	91.3	92.1	92.9	93.7	94.1
100°	110.5	111.5	112.3	113.2	114.1	114.9	115.5	116.0	116.5	117.0	117.5
102.5°	137.0	137.9	139.0	140.2	141.3	142.5	143.0	143.5	144.0	144.5	144.8
105°	177.3	178.3	179.8	181.4	183.0	184.5	184.5	184.5	184.5	184.5	184.7
107.5°	224.9	225.3	226.0	226.6	227.2	227.8	228.4	228.9	229.5	230.1	230.2
110°	255.5	255.8	256.2	256.5	256.9	257.2	257.9	258.6	259.3	260.0	260.2



TEST NUMBER: P331974

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	286.2	286.3	286.4	286.5	286.6	286.6	287.5	288.3	289.1	290.0	290.3
115°	334.4	334.5	334.1	333.8	333.4	333.1	333.2	333.4	333.6	333.8	333.8
117.5°	380.9	380.8	380.4	379.9	379.5	379.0	379.0	379.0	378.9	378.9	378.6
120°	413.1	413.2	412.3	411.4	410.6	409.7	409.5	409.3	409.2	409.0	408.7
122.5°	442.6	442.8	442.3	441.9	441.4	441.0	440.5	440.1	439.6	439.2	438.7
125°	488.4	488.5	488.1	487.8	487.4	487.1	486.4	485.7	485.0	484.3	483.6
127.5°	533.9	534.3	533.9	533.5	533.1	532.7	531.8	530.8	529.8	528.9	528.0
130°	563.8	564.2	563.7	563.2	562.7	562.1	561.4	560.8	560.1	559.4	558.4
132.5°	592.6	593.1	592.7	592.3	591.9	591.5	590.7	589.9	589.0	588.2	587.3
135°	635.1	635.6	635.4	635.2	635.0	634.9	634.2	633.5	632.8	632.1	631.6
137.5°	675.1	675.7	676.2	676.6	677.1	677.5	676.8	676.1	675.4	674.6	673.9
140°	703.2	703.7	703.9	704.1	704.3	704.4	704.3	704.1	703.9	703.7	703.1
142.5°	728.9	729.5	729.8	730.1	730.4	730.7	730.5	730.4	730.2	730.0	729.5
145°	766.8	767.2	767.8	768.3	768.8	769.3	769.2	769.0	768.8	768.6	768.2
147.5°	803.0	803.5	804.0	804.5	805.0	805.5	805.5	805.5	805.5	805.5	804.9
150°	826.2	826.6	826.9	827.3	827.6	828.0	828.0	828.0	828.0	828.0	827.5
152.5°	846.8	847.2	847.4	847.6	847.8	848.0	848.3	848.5	848.8	849.1	848.8
155°	876.4	876.5	876.7	876.9	877.1	877.2	877.9	878.6	879.3	880.0	879.7
157.5°	902.5	902.5	902.6	902.8	902.9	903.0	903.8	904.5	905.2	905.9	905.8
160°	918.8	918.7	918.7	918.7	918.7	918.7	919.5	920.4	921.3	922.1	922.2
162.5°	933.3	933.1	933.3	933.4	933.5	933.7	934.5	935.4	936.3	937.2	937.0
165°	952.5	952.3	952.3	952.3	952.3	952.3	953.3	954.4	955.4	956.5	956.4
167.5°	967.3	967.1	967.2	967.3	967.5	967.6	968.7	969.8	970.8	971.9	971.9
170°	976.1	975.7	975.7	975.7	975.7	975.7	977.0	978.2	979.4	980.6	980.6
172.5°	983.0	982.6	982.6	982.6	982.6	982.6	983.7	984.8	985.9	986.9	986.9
175°	990.2	989.8	989.8	989.8	989.8	989.8	990.9	991.9	992.9	994.0	993.9
177.5°	993.7	993.4	993.4	993.4	993.4	993.4	994.2	995.1	995.9	996.7	996.7
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3



TEST NUMBER: P331974

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1033.2	1032.8	1035.7	1033.6	1035.7	1032.8	1033.2	1036.1	1037.0	1037.4	1037.4
5°	961.7	963.3	958.0	958.0	958.0	963.3	961.7	964.8	967.5	969.6	972.7
7.5°	898.0	895.7	895.9	893.1	895.9	895.7	898.0	900.6	903.9	908.5	912.8
10°	859.1	856.0	854.9	855.4	854.9	856.0	859.1	865.4	867.5	871.7	876.4
12.5°	826.8	826.2	819.3	819.4	819.3	826.2	826.8	828.5	833.1	841.9	847.5
15°	788.9	779.0	777.9	781.1	777.9	779.0	788.9	788.9	791.0	797.8	801.0
17.5°	750.9	745.7	746.0	744.4	746.0	745.7	750.9	751.8	753.4	759.0	763.2
20°	730.8	727.7	727.2	723.5	727.2	727.7	730.8	730.8	732.9	735.5	739.7
22.5°	712.4	711.4	711.7	707.6	711.7	711.4	712.4	713.7	715.8	717.5	720.5
25°	689.5	692.1	690.0	690.0	690.0	692.1	689.5	690.0	690.5	693.1	695.2
27.5°	674.0	673.9	672.8	672.8	672.8	673.9	674.0	672.7	672.1	671.2	670.7
30°	662.3	661.7	662.8	662.8	662.8	661.7	662.3	660.2	659.1	658.6	656.5
32.5°	650.5	651.3	651.5	651.9	651.5	651.3	650.5	648.0	646.1	644.8	643.1
35°	632.4	632.9	634.5	633.5	634.5	632.9	632.4	629.3	627.2	624.0	621.4
37.5°	607.9	610.3	609.8	610.6	609.8	610.3	607.9	607.0	604.9	602.5	599.4
40°	589.5	591.1	590.5	590.5	590.5	591.1	589.5	589.0	586.9	585.3	582.7
42.5°	570.6	571.8	570.4	569.6	570.4	571.8	570.6	569.7	568.4	565.6	562.6
45°	539.7	538.7	540.3	538.2	540.3	538.7	539.7	537.7	537.1	535.0	532.4
47.5°	505.2	506.2	506.7	508.2	506.7	506.2	505.2	505.4	502.5	501.2	500.4
50°	482.2	485.3	485.3	484.8	485.3	485.3	482.2	481.1	479.0	476.9	476.9
52.5°	459.5	461.0	463.1	463.0	463.1	461.0	459.5	457.7	455.6	452.6	451.8
55°	424.6	425.6	426.7	427.2	426.7	425.6	424.6	420.4	418.8	417.2	414.6
57.5°	388.3	387.9	390.4	391.2	390.4	387.9	388.3	384.6	382.2	377.4	376.7
60°	362.8	362.8	367.0	368.6	367.0	362.8	362.8	358.6	354.9	351.8	350.8
62.5°	335.6	337.3	341.4	339.2	341.4	337.3	335.6	331.0	328.1	324.2	321.4
65°	295.8	300.0	299.5	301.5	299.5	300.0	295.8	293.2	287.4	283.7	280.6
67.5°	254.2	256.8	260.6	260.9	260.6	256.8	254.2	250.0	246.3	242.4	238.6
70°	226.2	228.8	230.9	232.4	230.9	228.8	226.2	222.0	217.8	215.2	211.0
72.5°	198.9	200.3	205.3	203.1	205.3	200.3	198.9	193.9	190.6	188.4	183.8
75°	156.0	159.7	162.8	161.2	162.8	159.7	156.0	152.3	149.7	146.6	142.4
77.5°	115.4	119.0	120.5	119.2	120.5	119.0	115.4	113.0	111.6	105.4	105.0
80°	91.1	90.6	93.7	93.2	93.7	90.6	91.1	87.4	84.8	81.1	81.1
82.5°	66.8	66.3	67.7	68.1	67.7	66.3	66.8	64.8	61.4	59.8	58.5
85°	32.5	34.0	31.9	31.4	31.9	34.0	32.5	30.4	30.4	30.4	29.8
87.5°	12.0	12.1	11.7	11.4	11.7	12.1	12.0	12.0	13.5	12.1	12.0
90°	22.4	22.8	23.1	23.5	23.1	22.8	22.4	22.1	21.5	20.8	20.2
92.5°	32.2	32.0	31.8	31.6	31.8	32.0	32.2	32.4	32.2	31.7	31.1
95°	61.0	61.0	61.0	61.0	61.0	61.0	61.0	61.0	60.6	59.9	59.2
97.5°	94.0	94.0	93.9	93.8	93.9	94.0	94.0	94.1	93.7	92.9	92.1
100°	117.8	118.1	118.5	118.8	118.5	118.1	117.8	117.5	117.0	116.5	116.0
102.5°	144.7	144.6	144.6	144.5	144.6	144.6	144.7	144.8	144.5	144.0	143.5
105°	185.0	185.4	185.7	186.1	185.7	185.4	185.0	184.7	184.5	184.5	184.5
107.5°	230.0	229.8	229.6	229.4	229.6	229.8	230.0	230.2	230.1	229.5	228.9
110°	259.8	259.5	259.1	258.8	259.1	259.5	259.8	260.2	260.0	259.3	258.6



TEST NUMBER: P331974

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	290.3	290.2	290.1	290.1	290.1	290.2	290.3	290.3	290.0	289.1	288.3
115°	333.6	333.4	333.2	333.1	333.2	333.4	333.6	333.8	333.8	333.6	333.4
117.5°	378.2	377.7	377.2	376.7	377.2	377.7	378.2	378.6	378.9	378.9	379.0
120°	408.4	408.0	407.7	407.3	407.7	408.0	408.4	408.7	409.0	409.2	409.3
122.5°	438.2	437.7	437.2	436.7	437.2	437.7	438.2	438.7	439.2	439.6	440.1
125°	482.9	482.2	481.5	480.8	481.5	482.2	482.9	483.6	484.3	485.0	485.7
127.5°	527.2	526.4	525.6	524.8	525.6	526.4	527.2	528.0	528.9	529.8	530.8
130°	557.2	556.0	554.8	553.5	554.8	556.0	557.2	558.4	559.4	560.1	560.8
132.5°	586.4	585.4	584.5	583.6	584.5	585.4	586.4	587.3	588.2	589.0	589.9
135°	631.2	630.9	630.5	630.2	630.5	630.9	631.2	631.6	632.1	632.8	633.5
137.5°	673.3	672.6	672.0	671.3	672.0	672.6	673.3	673.9	674.6	675.4	676.1
140°	701.8	700.6	699.4	698.2	699.4	700.6	701.8	703.1	703.7	703.9	704.1
142.5°	728.5	727.6	726.6	725.7	726.6	727.6	728.5	729.5	730.0	730.2	730.4
145°	767.5	766.8	766.1	765.4	766.1	766.8	767.5	768.2	768.6	768.8	769.0
147.5°	803.9	802.8	801.8	800.8	801.8	802.8	803.9	804.9	805.5	805.5	805.5
150°	826.4	825.4	824.3	823.3	824.3	825.4	826.4	827.5	828.0	828.0	828.0
152.5°	847.9	847.0	846.1	845.2	846.1	847.0	847.9	848.8	849.1	848.8	848.5
155°	878.5	877.3	876.1	874.9	876.1	877.3	878.5	879.7	880.0	879.3	878.6
157.5°	904.9	903.9	902.9	901.9	902.9	903.9	904.9	905.8	905.9	905.2	904.5
160°	921.5	920.8	920.1	919.4	920.1	920.8	921.5	922.2	922.1	921.3	920.4
162.5°	935.9	934.8	933.7	932.6	933.7	934.8	935.9	937.0	937.2	936.3	935.4
165°	955.2	953.9	952.7	951.5	952.7	953.9	955.2	956.4	956.5	955.4	954.4
167.5°	970.8	969.8	968.7	967.6	968.7	969.8	970.8	971.9	971.9	970.8	969.8
170°	979.4	978.2	977.0	975.7	977.0	978.2	979.4	980.6	980.6	979.4	978.2
172.5°	985.6	984.4	983.2	982.0	983.2	984.4	985.6	986.9	986.9	985.9	984.8
175°	992.7	991.5	990.2	989.0	990.2	991.5	992.7	993.9	994.0	992.9	991.9
177.5°	995.7	994.7	993.8	992.8	993.8	994.7	995.7	996.7	996.7	995.9	995.1
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3



TEST NUMBER: P331974

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1036.1	1036.1	1044.1	1049.1	1055.4	1059.6	1062.5	1065.5	1070.5	1077.2	1084.7
5°	976.9	979.0	990.5	1002.0	1013.0	1022.4	1030.3	1039.7	1051.2	1065.4	1081.1
7.5°	919.5	927.6	939.2	953.2	968.6	982.3	996.3	1011.8	1028.0	1048.8	1070.8
10°	882.7	891.6	905.7	923.5	939.7	955.9	973.2	990.0	1010.4	1035.0	1063.3
12.5°	850.4	858.9	873.4	892.9	908.3	926.2	946.0	967.8	990.7	1020.3	1052.4
15°	805.7	815.6	833.4	842.9	866.4	887.9	906.2	937.6	966.9	997.3	1034.5
17.5°	769.0	774.6	789.0	806.5	824.1	848.2	872.2	898.4	927.6	964.7	1011.2
20°	743.9	748.6	764.3	782.7	801.5	823.5	845.0	871.1	904.1	943.4	993.6
22.5°	725.1	730.2	740.5	760.0	777.6	795.9	817.3	848.5	883.6	922.0	976.5
25°	697.8	701.0	707.8	723.5	739.2	759.6	778.5	807.8	843.9	888.9	943.4
27.5°	672.0	675.0	680.7	692.0	706.6	723.2	743.7	768.6	805.3	854.2	912.0
30°	656.5	657.0	662.3	672.7	685.3	698.9	717.7	746.0	780.6	830.3	891.0
32.5°	643.1	641.1	644.7	652.6	664.8	678.4	693.9	721.7	755.0	803.9	866.3
35°	620.4	619.3	617.8	624.6	635.0	645.5	659.1	680.1	717.7	763.3	828.7
37.5°	597.2	594.7	591.9	595.0	603.2	614.1	625.9	644.6	677.0	727.2	789.8
40°	580.1	578.0	576.4	575.3	582.7	593.1	602.0	619.8	650.2	697.8	759.6
42.5°	561.2	560.0	558.0	556.5	562.6	570.5	579.8	595.6	625.9	670.6	729.1
45°	530.8	529.8	528.8	527.7	531.4	538.7	546.0	557.5	583.7	627.2	680.1
47.5°	497.0	495.7	496.1	494.4	498.0	502.9	508.0	520.4	545.5	580.6	619.2
50°	472.7	472.2	472.2	472.2	473.3	479.0	483.7	493.2	516.2	551.3	579.0
52.5°	449.7	447.5	447.5	448.3	450.2	453.9	456.9	467.2	487.3	516.1	541.3
55°	413.6	409.4	408.3	409.4	411.0	414.1	417.2	425.6	442.9	464.4	479.0
57.5°	373.6	371.3	369.9	370.1	371.0	373.5	375.9	385.0	398.6	409.8	419.2
60°	345.5	346.6	341.9	342.9	342.9	345.0	348.7	354.4	365.9	373.8	383.2
62.5°	319.1	317.7	316.3	314.8	314.8	315.7	320.6	325.1	334.9	339.0	346.4
65°	278.0	278.0	274.8	275.9	276.4	272.8	275.4	280.6	286.9	288.5	295.3
67.5°	236.3	234.9	233.1	231.5	231.5	231.2	232.5	235.2	239.9	240.4	245.6
70°	207.8	206.8	206.3	204.7	202.6	205.2	203.6	206.3	208.9	209.4	212.5
72.5°	180.2	179.1	178.2	176.6	175.8	175.5	175.6	178.6	180.4	179.7	183.2
75°	140.8	139.8	138.7	136.1	136.1	134.5	135.1	137.2	139.3	137.7	140.8
77.5°	103.4	100.2	100.0	100.7	98.9	99.3	98.6	98.3	99.3	99.4	102.2
80°	79.6	75.9	77.0	76.4	75.9	75.4	74.3	74.9	75.4	75.9	77.5
82.5°	57.4	57.1	56.0	55.9	55.4	54.0	53.4	54.3	54.9	54.6	55.7
85°	29.3	27.7	28.8	28.3	28.8	28.3	26.7	26.7	27.7	27.2	28.3
87.5°	12.7	12.5	11.7	11.6	10.8	10.7	9.9	10.0	10.1	9.7	10.2
90°	19.5	18.8	16.5	14.2	12.0	9.7	7.7	6.0	4.3	2.5	0.8
92.5°	30.6	30.0	28.7	27.5	26.2	24.9	23.6	22.5	21.3	20.1	18.9
95°	58.6	57.9	56.5	55.1	53.7	52.3	51.0	49.8	48.6	47.3	46.1
97.5°	91.3	90.5	89.5	88.5	87.5	86.5	85.6	84.6	83.7	82.8	81.9
100°	115.5	114.9	114.1	113.2	112.3	111.5	110.5	109.5	108.4	107.4	106.3
102.5°	143.0	142.5	141.3	140.2	139.0	137.9	137.0	136.4	135.7	135.1	134.5
105°	184.5	184.5	183.0	181.4	179.8	178.3	177.3	177.0	176.6	176.3	175.9
107.5°	228.4	227.8	227.2	226.6	226.0	225.3	224.9	224.7	224.5	224.3	224.1
110°	257.9	257.2	256.9	256.5	256.2	255.8	255.5	255.1	254.8	254.4	254.1



TEST NUMBER: P331974

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	287.5	286.6	286.6	286.5	286.4	286.3	286.2	286.0	285.8	285.6	285.4
115°	333.2	333.1	333.4	333.8	334.1	334.5	334.4	333.8	333.3	332.8	332.3
117.5°	379.0	379.0	379.5	379.9	380.4	380.8	380.9	380.5	380.2	379.9	379.5
120°	409.5	409.7	410.6	411.4	412.3	413.2	413.1	412.0	411.0	409.9	408.9
122.5°	440.5	441.0	441.4	441.9	442.3	442.8	442.6	441.8	441.1	440.3	439.6
125°	486.4	487.1	487.4	487.8	488.1	488.5	488.4	487.9	487.3	486.8	486.3
127.5°	531.8	532.7	533.1	533.5	533.9	534.3	533.9	532.8	531.7	530.6	529.5
130°	561.4	562.1	562.7	563.2	563.7	564.2	563.8	562.4	561.0	559.6	558.2
132.5°	590.7	591.5	591.9	592.3	592.7	593.1	592.6	591.2	589.8	588.4	587.0
135°	634.2	634.9	635.0	635.2	635.4	635.6	635.1	634.1	633.0	632.0	630.9
137.5°	676.8	677.5	677.1	676.6	676.2	675.7	675.1	674.2	673.3	672.5	671.6
140°	704.3	704.4	704.3	704.1	703.9	703.7	703.2	702.4	701.5	700.6	699.7
142.5°	730.5	730.7	730.4	730.1	729.8	729.5	728.9	728.0	727.1	726.3	725.4
145°	769.2	769.3	768.8	768.3	767.8	767.2	766.8	766.5	766.1	765.8	765.4
147.5°	805.5	805.5	805.0	804.5	804.0	803.5	803.0	802.3	801.7	801.1	800.5
150°	828.0	828.0	827.6	827.3	826.9	826.6	826.2	825.9	825.5	825.2	824.8
152.5°	848.3	848.0	847.8	847.6	847.4	847.2	846.8	846.3	845.8	845.3	844.9
155°	877.9	877.2	877.1	876.9	876.7	876.5	876.4	876.4	876.4	876.4	876.4
157.5°	903.8	903.0	902.9	902.8	902.6	902.5	902.5	902.7	902.9	903.1	903.3
160°	919.5	918.7	918.7	918.7	918.7	918.7	918.8	919.2	919.5	919.9	920.2
162.5°	934.5	933.7	933.5	933.4	933.3	933.1	933.3	933.8	934.3	934.8	935.2
165°	953.3	952.3	952.3	952.3	952.3	952.3	952.5	953.1	953.6	954.1	954.6
167.5°	968.7	967.6	967.5	967.3	967.2	967.1	967.3	968.0	968.7	969.4	970.1
170°	977.0	975.7	975.7	975.7	975.7	975.7	976.1	976.8	977.5	978.2	978.9
172.5°	983.7	982.6	982.6	982.6	982.6	982.6	983.0	983.7	984.4	985.1	985.7
175°	990.9	989.8	989.8	989.8	989.8	989.8	990.2	990.9	991.6	992.2	992.9
177.5°	994.2	993.4	993.4	993.4	993.4	993.4	993.7	994.2	994.8	995.4	995.9
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3



TEST NUMBER: P331974

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1087.2	1089.3	1096.5	1101.5	1107.3	1110.7	1114.0	1116.6	1119.9	1120.7	1132.9
5°	1092.1	1102.5	1120.9	1134.5	1151.2	1169.5	1182.1	1187.9	1203.0	1215.6	1240.7
7.5°	1090.7	1113.0	1140.6	1169.3	1200.1	1228.6	1253.3	1282.6	1303.5	1334.8	1365.6
10°	1089.4	1119.3	1154.9	1191.5	1234.5	1274.2	1309.8	1349.6	1382.6	1426.1	1463.2
12.5°	1085.7	1121.8	1171.2	1214.6	1266.7	1321.6	1374.3	1425.4	1454.6	1527.0	1561.2
15°	1076.4	1119.3	1181.1	1247.0	1318.7	1383.7	1450.7	1504.1	1590.4	1653.8	1694.1
17.5°	1058.6	1118.7	1191.9	1271.5	1358.7	1444.3	1520.2	1601.2	1692.8	1769.5	1851.2
20°	1050.2	1116.1	1197.8	1285.8	1376.3	1473.2	1559.6	1656.9	1756.9	1832.3	1937.0
22.5°	1034.7	1109.4	1197.4	1295.4	1392.2	1492.4	1593.5	1691.7	1807.2	1911.1	2010.7
25°	1009.3	1093.1	1184.2	1293.6	1407.2	1507.7	1628.7	1759.0	1879.4	2012.9	2112.4
27.5°	982.7	1072.2	1163.5	1265.2	1387.4	1506.7	1658.8	1806.1	1953.4	2068.6	2142.2
30°	962.2	1049.1	1143.4	1246.0	1366.9	1508.8	1678.9	1839.6	1983.1	2082.0	2123.4
32.5°	940.0	1028.2	1111.5	1219.2	1348.1	1507.5	1691.5	1859.3	1984.8	2050.6	2042.6
35°	905.2	979.0	1060.1	1163.8	1315.6	1498.3	1698.8	1861.1	1938.1	1923.9	1817.1
37.5°	854.9	917.0	996.9	1110.4	1277.9	1478.9	1684.2	1805.9	1800.9	1685.8	1531.1
40°	823.5	876.4	953.3	1072.7	1248.6	1466.4	1661.1	1740.2	1673.2	1512.4	1327.1
42.5°	782.5	831.1	908.1	1030.8	1216.3	1440.8	1617.1	1640.1	1509.0	1324.0	1154.1
45°	718.8	761.7	841.3	968.0	1168.0	1385.2	1509.8	1453.8	1277.4	1086.3	957.0
47.5°	650.4	695.0	771.6	901.7	1098.0	1301.6	1360.9	1241.8	1060.6	905.7	787.0
50°	607.3	650.2	725.1	856.5	1050.7	1232.9	1257.5	1103.6	937.1	801.0	703.6
52.5°	563.7	604.1	677.7	809.6	995.4	1153.3	1138.1	981.3	828.2	712.2	635.8
55°	498.9	537.1	607.3	730.8	899.9	1025.0	970.1	820.4	693.7	603.6	545.5
57.5°	440.9	477.6	538.1	649.7	796.7	882.7	812.7	686.5	585.8	516.5	473.2
60°	401.5	434.0	491.6	595.2	723.0	788.4	719.3	607.8	523.0	467.5	428.8
62.5°	364.3	392.5	445.9	540.0	650.9	705.9	636.0	541.6	469.4	420.2	387.3
65°	307.8	333.5	380.6	453.9	545.0	581.6	521.4	445.0	389.0	352.3	330.3
67.5°	256.3	278.1	318.8	376.5	443.5	470.2	424.4	365.2	323.0	293.6	276.1
70°	222.0	240.8	272.8	322.5	383.2	403.6	360.7	312.0	281.1	257.6	241.3
72.5°	193.1	206.9	235.9	274.3	325.0	341.2	311.3	268.5	239.7	222.0	209.1
75°	147.1	158.6	177.5	208.4	243.4	252.9	230.3	203.6	184.3	171.7	161.8
77.5°	106.1	114.5	128.2	147.2	171.5	180.0	165.7	147.9	133.8	125.3	119.8
80°	80.1	86.9	98.4	114.1	128.8	133.5	125.1	111.5	101.6	96.9	92.1
82.5°	59.2	63.0	69.9	80.6	90.7	96.2	89.1	80.9	75.6	71.3	69.5
85°	29.8	31.9	35.1	39.3	45.5	47.6	45.0	42.9	39.8	37.2	37.2
87.5°	11.4	11.7	13.3	14.5	16.6	18.3	18.3	18.0	18.0	17.7	17.4
90°	2.5	4.3	6.0	7.7	9.7	12.0	14.2	16.5	18.8	19.5	20.2
92.5°	20.1	21.3	22.5	23.6	24.9	26.2	27.5	28.7	30.0	30.6	31.1
95°	47.3	48.6	49.8	51.0	52.3	53.7	55.1	56.5	57.9	58.6	59.2
97.5°	82.8	83.7	84.6	85.6	86.5	87.5	88.5	89.5	90.5	91.3	92.1
100°	107.4	108.4	109.5	110.5	111.5	112.3	113.2	114.1	114.9	115.5	116.0
102.5°	135.1	135.7	136.4	137.0	137.9	139.0	140.2	141.3	142.5	143.0	143.5
105°	176.3	176.6	177.0	177.3	178.3	179.8	181.4	183.0	184.5	184.5	184.5
107.5°	224.3	224.5	224.7	224.9	225.3	226.0	226.6	227.2	227.8	228.4	228.9
110°	254.4	254.8	255.1	255.5	255.8	256.2	256.5	256.9	257.2	257.9	258.6



TEST NUMBER: P331974

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	285.6	285.8	286.0	286.2	286.3	286.4	286.5	286.6	286.6	287.5	288.3
115°	332.8	333.3	333.8	334.4	334.5	334.1	333.8	333.4	333.1	333.2	333.4
117.5°	379.9	380.2	380.5	380.9	380.8	380.4	379.9	379.5	379.0	379.0	379.0
120°	409.9	411.0	412.0	413.1	413.2	412.3	411.4	410.6	409.7	409.5	409.3
122.5°	440.3	441.1	441.8	442.6	442.8	442.3	441.9	441.4	441.0	440.5	440.1
125°	486.8	487.3	487.9	488.4	488.5	488.1	487.8	487.4	487.1	486.4	485.7
127.5°	530.6	531.7	532.8	533.9	534.3	533.9	533.5	533.1	532.7	531.8	530.8
130°	559.6	561.0	562.4	563.8	564.2	563.7	563.2	562.7	562.1	561.4	560.8
132.5°	588.4	589.8	591.2	592.6	593.1	592.7	592.3	591.9	591.5	590.7	589.9
135°	632.0	633.0	634.1	635.1	635.6	635.4	635.2	635.0	634.9	634.2	633.5
137.5°	672.5	673.3	674.2	675.1	675.7	676.2	676.6	677.1	677.5	676.8	676.1
140°	700.6	701.5	702.4	703.2	703.7	703.9	704.1	704.3	704.4	704.3	704.1
142.5°	726.3	727.1	728.0	728.9	729.5	729.8	730.1	730.4	730.7	730.5	730.4
145°	765.8	766.1	766.5	766.8	767.2	767.8	768.3	768.8	769.3	769.2	769.0
147.5°	801.1	801.7	802.3	803.0	803.5	804.0	804.5	805.0	805.5	805.5	805.5
150°	825.2	825.5	825.9	826.2	826.6	826.9	827.3	827.6	828.0	828.0	828.0
152.5°	845.3	845.8	846.3	846.8	847.2	847.4	847.6	847.8	848.0	848.3	848.5
155°	876.4	876.4	876.4	876.4	876.5	876.7	876.9	877.1	877.2	877.9	878.6
157.5°	903.1	902.9	902.7	902.5	902.5	902.6	902.8	902.9	903.0	903.8	904.5
160°	919.9	919.5	919.2	918.8	918.7	918.7	918.7	918.7	918.7	919.5	920.4
162.5°	934.8	934.3	933.8	933.3	933.1	933.3	933.4	933.5	933.7	934.5	935.4
165°	954.1	953.6	953.1	952.5	952.3	952.3	952.3	952.3	952.3	953.3	954.4
167.5°	969.4	968.7	968.0	967.3	967.1	967.2	967.3	967.5	967.6	968.7	969.8
170°	978.2	977.5	976.8	976.1	975.7	975.7	975.7	975.7	975.7	977.0	978.2
172.5°	985.1	984.4	983.7	983.0	982.6	982.6	982.6	982.6	982.6	983.7	984.8
175°	992.2	991.6	990.9	990.2	989.8	989.8	989.8	989.8	989.8	990.9	991.9
177.5°	995.4	994.8	994.2	993.7	993.4	993.4	993.4	993.4	993.4	994.2	995.1
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3



TEST NUMBER: P331974

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1137.1	1137.5	1142.1	1145.5	1143.8	1145.9	1146.7
5°	1242.3	1261.2	1271.1	1278.4	1279.0	1279.5	1283.7
7.5°	1391.5	1411.7	1426.5	1448.9	1455.6	1463.2	1461.0
10°	1500.4	1530.2	1555.9	1569.5	1584.2	1605.6	1588.4
12.5°	1602.2	1655.1	1694.1	1715.3	1729.1	1733.4	1724.9
15°	1770.0	1839.1	1876.3	1875.2	1922.4	1942.8	1910.8
17.5°	1923.9	1987.7	2038.8	2065.0	2104.2	2112.9	2108.9
20°	2018.2	2087.8	2127.6	2172.6	2193.0	2211.3	2214.5
22.5°	2099.4	2161.9	2204.6	2242.1	2259.2	2267.9	2273.1
25°	2183.1	2232.3	2257.9	2271.0	2275.7	2274.7	2267.9
27.5°	2177.3	2181.1	2152.8	2125.1	2100.3	2072.3	2062.7
30°	2120.8	2076.8	1998.3	1953.8	1888.3	1836.5	1857.4
32.5°	1972.1	1884.6	1796.4	1699.1	1618.6	1595.7	1572.6
35°	1683.1	1529.2	1439.2	1334.4	1292.6	1250.7	1221.9
37.5°	1361.7	1242.6	1135.8	1067.3	1025.4	998.9	984.6
40°	1177.4	1070.1	982.1	926.6	894.7	864.9	860.7
42.5°	1030.4	930.6	864.4	820.2	789.6	776.9	767.7
45°	843.9	774.3	729.8	698.4	678.0	670.1	659.6
47.5°	714.3	665.1	631.7	610.3	594.9	589.1	588.2
50°	641.8	601.0	576.4	559.6	547.6	545.5	537.1
52.5°	587.4	552.0	532.8	518.2	509.5	503.6	501.1
55°	509.9	486.3	469.1	460.7	453.9	448.1	448.1
57.5°	446.1	426.5	415.0	407.9	405.8	401.7	399.1
60°	406.8	390.0	381.1	374.8	370.7	371.2	366.5
62.5°	368.2	357.4	348.9	342.6	337.6	337.7	338.0
65°	313.6	305.2	298.9	296.8	293.7	290.0	291.1
67.5°	265.7	257.9	253.0	249.4	248.4	246.4	249.4
70°	231.4	225.6	222.0	218.8	217.8	218.3	220.9
72.5°	200.0	195.9	193.5	192.0	189.7	189.8	191.6
75°	157.1	153.9	151.8	150.2	149.7	149.7	149.7
77.5°	115.4	114.7	113.7	111.4	111.5	112.1	112.2
80°	91.1	89.5	89.0	88.0	86.4	85.3	88.0
82.5°	68.1	66.5	66.0	65.8	63.3	63.1	65.3
85°	36.6	35.1	35.6	35.1	35.1	34.6	34.6
87.5°	17.2	16.9	16.6	17.0	16.7	16.3	17.3
90°	20.8	21.5	22.1	22.4	22.8	23.1	23.5
92.5°	31.7	32.2	32.4	32.2	32.0	31.8	31.6
95°	59.9	60.6	61.0	61.0	61.0	61.0	61.0
97.5°	92.9	93.7	94.1	94.0	94.0	93.9	93.8
100°	116.5	117.0	117.5	117.8	118.1	118.5	118.8
102.5°	144.0	144.5	144.8	144.7	144.6	144.6	144.5
105°	184.5	184.5	184.7	185.0	185.4	185.7	186.1
107.5°	229.5	230.1	230.2	230.0	229.8	229.6	229.4
110°	259.3	260.0	260.2	259.8	259.5	259.1	258.8



TEST NUMBER: P331974

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	289.1	290.0	290.3	290.3	290.2	290.1	290.1
115°	333.6	333.8	333.8	333.6	333.4	333.2	333.1
117.5°	378.9	378.9	378.6	378.2	377.7	377.2	376.7
120°	409.2	409.0	408.7	408.4	408.0	407.7	407.3
122.5°	439.6	439.2	438.7	438.2	437.7	437.2	436.7
125°	485.0	484.3	483.6	482.9	482.2	481.5	480.8
127.5°	529.8	528.9	528.0	527.2	526.4	525.6	524.8
130°	560.1	559.4	558.4	557.2	556.0	554.8	553.5
132.5°	589.0	588.2	587.3	586.4	585.4	584.5	583.6
135°	632.8	632.1	631.6	631.2	630.9	630.5	630.2
137.5°	675.4	674.6	673.9	673.3	672.6	672.0	671.3
140°	703.9	703.7	703.1	701.8	700.6	699.4	698.2
142.5°	730.2	730.0	729.5	728.5	727.6	726.6	725.7
145°	768.8	768.6	768.2	767.5	766.8	766.1	765.4
147.5°	805.5	805.5	804.9	803.9	802.8	801.8	800.8
150°	828.0	828.0	827.5	826.4	825.4	824.3	823.3
152.5°	848.8	849.1	848.8	847.9	847.0	846.1	845.2
155°	879.3	880.0	879.7	878.5	877.3	876.1	874.9
157.5°	905.2	905.9	905.8	904.9	903.9	902.9	901.9
160°	921.3	922.1	922.2	921.5	920.8	920.1	919.4
162.5°	936.3	937.2	937.0	935.9	934.8	933.7	932.6
165°	955.4	956.5	956.4	955.2	953.9	952.7	951.5
167.5°	970.8	971.9	971.9	970.8	969.8	968.7	967.6
170°	979.4	980.6	980.6	979.4	978.2	977.0	975.7
172.5°	985.9	986.9	986.9	985.6	984.4	983.2	982.0
175°	992.9	994.0	993.9	992.7	991.5	990.2	989.0
177.5°	995.9	996.7	996.7	995.7	994.7	993.8	992.8
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3

(END OF REPORT)