

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331934-830

Luminaire Tested: **S123DIP-S560D805U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331934-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S560D805U830-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 805 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5212.4 lumens  
Efficiency: N/A  
Efficacy: 135.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331934-830

CATALOG NUMBER: S123DIP-S560D805U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331934-830

CATALOG NUMBER: S123DIP-S560D805U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	105	105	105	105	96	96	96	96	79	79	79		63	63	63		49	49	49	42
1	96	92	88	84	87	84	80	77	69	67	65		55	54	52		43	42	41	35
2	87	80	74	69	79	73	68	64	60	57	53		49	46	44		38	36	34	29
3	80	70	63	57	72	64	58	53	53	49	45		43	40	37		33	31	29	25
4	73	62	54	48	66	57	50	45	47	42	38		38	35	32		30	27	25	21
5	67	55	47	41	61	51	44	38	42	37	33		34	30	27		27	24	22	19
6	61	49	41	36	56	46	38	33	38	33	29		31	27	24		24	22	19	16
7	57	45	37	31	52	41	34	29	34	29	25		28	24	21		22	19	17	14
8	53	40	33	28	48	37	31	26	31	26	22		26	22	19		20	18	15	13
9	49	37	29	24	45	34	27	23	29	24	20		24	20	17		19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18		22	18	15		17	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9038	9038	9038
5°	9081	8956	9018
10°	9021	8878	8933
15°	8914	8778	8795
20°	8791	8635	8643
25°	8626	8464	8445
30°	8444	8274	8211
35°	8253	8073	7970
40°	8056	7852	7731
45°	7837	7649	7462
50°	7618	7400	7194
55°	7330	7141	6923
60°	7042	6837	6622
65°	6788	6510	6306
70°	6408	6134	5860
75°	5856	5644	5407
80°	5281	5058	5015
85°	4631	4458	4286



TEST NUMBER: P331934-830

CATALOG NUMBER: S123DIP-S560D805U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	79.1	1.5
10°-20°	223.3	4.3
20°-30°	329.9	6.3
30°-40°	385.4	7.4
40°-50°	387.4	7.4
50°-60°	340.3	6.5
60°-70°	253.5	4.9
70°-80°	144.5	2.8
80°-90°	44.2	0.8
90°-100°	36.1	0.7
100°-110°	171.9	3.3
110°-120°	412.8	7.9
120°-130°	525.7	10.1
130°-140°	561.7	10.8
140°-150°	525.2	10.1
150°-160°	423.7	8.1
160°-170°	273.4	5.2
170°-180°	94.2	1.8
0°-30°	632.3	12.1
0°-40°	1017.7	19.5
0°-60°	1745.5	33.5
0°-90°	2187.7	42.0
90°-120°	620.7	11.9
90°-150°	2233.3	42.8
90°-180°	3025.0	58.0
0°-180°	5212.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	840	840	840	840	840	
5°	840	837	829	836	835	80
15°	800	797	788	793	789	225
25°	726	722	713	713	711	334
35°	628	624	614	610	606	393
45°	515	512	502	494	490	397
55°	391	389	380	373	369	350
65°	266	263	256	250	248	263
75°	141	138	136	132	130	151
85°	38	36	36	35	35	41
90°	1	8	18	21	22	4
95°	45	17	23	28	28	56
105°	220	224	161	38	32	233
115°	412	416	423	430	433	406
125°	581	586	590	591	592	518
135°	723	727	730	732	730	556
145°	834	839	841	842	842	522
155°	919	918	918	921	917	423
165°	969	967	966	971	967	274
175°	992	988	989	993	988	94
180°	992	992	992	992	992	



TEST NUMBER: P331934-830

CATALOG NUMBER: S123DIP-S560D805U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	842.5	842.1	841.6	841.0	840.6	839.5	838.1	836.7	835.4	834.0	835.2
5°	840.4	839.6	838.8	838.0	837.2	835.9	834.2	832.4	830.7	828.9	830.5
7.5°	832.2	831.4	830.6	829.8	829.0	827.6	825.9	824.0	822.2	820.4	821.8
10°	825.3	824.4	823.7	822.8	822.1	820.6	818.5	816.4	814.4	812.3	813.7
12.5°	816.1	815.3	814.6	814.0	813.3	812.0	810.0	808.0	806.2	804.2	805.2
15°	799.9	799.4	798.7	798.1	797.4	796.1	794.0	791.9	789.8	787.7	789.0
17.5°	781.4	780.5	779.7	778.8	778.0	776.6	774.5	772.4	770.3	768.2	769.1
20°	767.5	766.6	765.5	764.6	763.6	762.1	760.1	758.0	755.8	753.8	754.4
22.5°	751.9	750.9	750.0	749.0	748.0	746.5	744.4	742.3	740.3	738.2	738.7
25°	726.3	725.4	724.4	723.5	722.5	721.0	718.9	716.8	714.7	712.7	712.8
27.5°	699.1	698.1	697.2	696.3	695.3	693.7	691.4	689.3	687.0	684.8	684.9
30°	679.4	678.6	677.8	677.0	676.2	674.7	672.4	670.1	668.0	665.7	665.7
32.5°	659.8	658.7	657.6	656.6	655.5	654.1	652.4	650.6	648.9	647.2	646.3
35°	628.1	627.2	626.2	625.3	624.3	622.7	620.7	618.6	616.5	614.4	613.5
37.5°	595.8	594.6	593.3	592.1	590.9	589.3	587.1	585.0	582.9	580.8	579.7
40°	573.3	572.3	571.4	570.4	569.4	567.8	565.5	563.4	561.1	558.8	557.5
42.5°	550.7	549.7	548.6	547.4	546.4	544.7	542.4	540.3	538.0	535.7	534.4
45°	514.8	514.2	513.5	512.8	512.2	510.9	508.8	506.7	504.6	502.5	500.6
47.5°	479.1	478.2	477.3	476.4	475.4	473.9	472.0	470.0	468.1	466.1	464.2
50°	454.9	454.0	453.3	452.4	451.7	450.3	448.1	446.0	443.9	441.9	440.1
52.5°	429.4	428.9	428.4	427.8	427.3	425.8	423.7	421.5	419.2	417.1	415.6
55°	390.6	390.4	390.3	390.1	389.9	388.8	386.7	384.7	382.6	380.5	378.7
57.5°	353.6	353.1	352.5	352.0	351.5	350.3	348.6	347.0	345.3	343.7	342.1
60°	327.1	326.9	326.8	326.6	326.4	325.4	323.5	321.5	319.6	317.6	316.2
62.5°	303.4	302.9	302.6	302.2	301.7	300.6	298.6	296.7	294.7	292.8	291.4
65°	266.5	265.6	264.9	264.0	263.3	262.0	260.4	258.8	257.2	255.6	254.3
67.5°	227.2	226.6	225.8	225.2	224.4	223.5	222.3	221.0	219.8	218.7	217.5
70°	203.6	202.6	201.7	200.8	199.7	198.8	197.8	196.9	195.9	194.9	193.8
72.5°	178.8	178.0	177.4	176.6	176.0	175.0	174.0	172.9	171.7	170.7	169.7
75°	140.8	140.2	139.5	138.8	138.3	137.7	137.1	136.7	136.2	135.7	135.0
77.5°	107.2	106.8	106.4	106.1	105.8	105.3	104.7	104.2	103.5	102.9	102.5
80°	85.2	84.7	84.3	83.8	83.2	82.8	82.6	82.2	81.9	81.6	81.4
82.5°	63.8	63.7	63.6	63.5	63.4	63.3	63.3	63.2	63.2	63.2	62.8
85°	37.5	37.2	36.9	36.6	36.3	36.1	36.1	36.1	36.1	36.1	35.8
87.5°	15.2	15.1	15.1	15.0	14.9	15.1	15.4	15.6	15.9	16.2	16.2
90°	0.8	2.4	4.1	5.7	7.3	9.1	11.3	13.4	15.6	17.7	18.4
92.5°	13.7	13.3	12.8	12.3	11.9	12.4	14.0	15.6	17.2	18.9	19.9
95°	45.0	38.3	31.5	24.8	18.1	15.6	17.4	19.2	21.0	22.8	24.0
97.5°	90.3	87.4	84.4	81.3	78.3	70.9	59.1	47.3	35.5	23.8	25.1
100°	124.5	127.8	131.1	134.3	137.6	126.5	100.9	75.4	49.9	24.3	25.6
102.5°	163.4	165.8	168.1	170.5	172.9	160.1	132.2	104.2	76.3	48.4	44.4
105°	219.6	221.4	223.2	225.0	226.8	220.4	205.6	190.9	176.1	161.4	132.4
107.5°	278.8	280.3	281.7	283.1	284.6	286.4	288.8	291.2	293.4	295.8	274.6
110°	318.3	319.6	320.9	322.3	323.6	325.1	327.0	328.8	330.5	332.3	327.0



TEST NUMBER: P331934-830

CATALOG NUMBER: S123DIP-S560D805U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	356.1	357.2	358.4	359.6	360.8	362.2	364.1	365.9	367.7	369.5	369.6
115°	411.9	412.9	413.9	414.9	415.8	417.1	418.6	420.0	421.5	423.0	424.6
117.5°	466.0	467.2	468.4	469.7	470.8	471.8	472.6	473.3	474.1	474.9	476.2
120°	499.6	501.1	502.6	504.0	505.5	506.5	507.0	507.5	507.9	508.4	509.7
122.5°	533.8	535.0	536.2	537.4	538.7	539.5	540.2	540.8	541.4	542.1	543.0
125°	580.7	581.9	583.2	584.6	585.9	586.9	587.6	588.1	588.8	589.5	589.8
127.5°	626.0	627.4	628.7	630.0	631.3	632.4	633.1	634.0	634.7	635.5	636.0
130°	654.3	655.6	657.0	658.3	659.6	660.5	661.2	661.9	662.5	663.2	663.8
132.5°	681.5	682.8	684.1	685.4	686.7	687.6	688.2	688.6	689.2	689.8	690.4
135°	722.8	723.9	724.8	725.9	726.8	727.6	728.3	729.0	729.6	730.3	730.8
137.5°	758.3	759.5	760.7	762.0	763.2	764.0	764.4	764.8	765.1	765.4	766.3
140°	781.8	782.8	783.8	784.8	785.8	786.5	787.0	787.5	788.0	788.4	789.1
142.5°	803.6	804.6	805.6	806.6	807.6	808.3	808.8	809.3	809.7	810.3	810.8
145°	834.2	835.3	836.4	837.5	838.8	839.4	839.8	840.1	840.5	840.7	841.1
147.5°	862.9	863.7	864.4	865.2	865.9	866.5	866.8	867.0	867.4	867.7	868.1
150°	880.5	881.1	881.6	882.0	882.5	883.0	883.3	883.6	883.9	884.3	884.6
152.5°	896.5	896.7	896.9	897.2	897.4	897.6	897.8	898.0	898.2	898.4	899.0
155°	918.9	918.6	918.2	917.9	917.6	917.5	917.7	917.8	917.9	918.1	919.0
157.5°	936.2	936.2	936.2	936.1	936.1	936.0	935.9	935.8	935.6	935.4	936.4
160°	946.9	946.7	946.6	946.4	946.2	946.0	945.9	945.7	945.6	945.4	946.4
162.5°	956.9	956.5	956.0	955.6	955.2	954.9	954.7	954.6	954.4	954.2	955.4
165°	969.0	968.5	968.0	967.5	967.0	966.7	966.6	966.4	966.2	966.0	967.3
167.5°	978.5	977.8	977.1	976.5	975.8	975.4	975.4	975.4	975.4	975.4	976.8
170°	983.7	983.1	982.4	981.8	981.1	980.8	980.8	980.8	980.8	980.8	982.1
172.5°	987.2	986.5	985.7	984.9	984.1	983.8	983.9	984.0	984.2	984.3	985.6
175°	991.8	991.0	990.2	989.4	988.5	988.3	988.4	988.5	988.7	988.9	990.0
177.5°	993.0	992.4	991.7	991.1	990.4	990.1	990.2	990.4	990.5	990.6	991.7
180°	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8



TEST NUMBER: P331934-830

CATALOG NUMBER: S123DIP-S560D805U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	836.5	837.7	839.1	839.6	839.5	839.3	839.2	839.1
5°	832.1	833.7	835.3	835.9	835.6	835.3	835.0	834.6
7.5°	823.2	824.6	826.1	826.7	826.5	826.3	826.1	826.0
10°	815.1	816.6	818.0	818.6	818.3	817.9	817.7	817.3
12.5°	806.3	807.4	808.4	808.8	808.6	808.4	808.2	808.0
15°	790.3	791.5	792.9	793.0	792.0	791.1	790.1	789.2
17.5°	770.1	770.9	771.8	772.0	771.8	771.4	771.0	770.6
20°	755.1	755.7	756.3	756.4	755.9	755.4	755.0	754.5
22.5°	739.2	739.7	740.3	740.2	739.6	739.0	738.4	737.7
25°	712.9	713.1	713.2	713.1	712.7	712.2	711.6	711.1
27.5°	685.0	685.1	685.2	685.0	684.4	683.8	683.2	682.6
30°	665.7	665.7	665.7	665.2	664.0	662.9	661.8	660.6
32.5°	645.5	644.5	643.6	642.8	642.2	641.7	641.0	640.5
35°	612.5	611.5	610.6	609.7	608.9	608.1	607.3	606.5
37.5°	578.4	577.3	576.2	575.3	574.9	574.3	573.8	573.3
40°	556.3	555.0	553.7	552.7	552.0	551.5	550.8	550.2
42.5°	533.2	531.9	530.6	529.6	529.0	528.4	527.7	527.1
45°	498.7	496.7	494.8	493.4	492.7	491.8	491.1	490.2
47.5°	462.3	460.4	458.5	457.2	456.6	455.8	455.2	454.4
50°	438.4	436.6	434.8	433.5	432.4	431.5	430.6	429.6
52.5°	414.1	412.6	411.0	409.7	408.8	407.8	406.9	406.0
55°	376.9	375.2	373.4	372.1	371.4	370.5	369.8	368.9
57.5°	340.5	338.9	337.4	336.1	335.2	334.3	333.4	332.4
60°	314.8	313.4	311.9	310.8	310.0	309.2	308.4	307.6
62.5°	289.9	288.5	287.1	286.1	285.5	285.0	284.5	283.9
65°	253.0	251.8	250.4	249.6	249.1	248.6	248.2	247.6
67.5°	216.4	215.3	214.1	213.2	212.5	211.9	211.2	210.6
70°	192.7	191.6	190.5	189.5	188.7	187.8	187.1	186.2
72.5°	168.7	167.7	166.7	166.0	165.6	165.1	164.8	164.3
75°	134.1	133.4	132.5	131.9	131.4	130.9	130.4	130.0
77.5°	101.9	101.3	100.8	100.5	100.5	100.5	100.5	100.5
80°	81.2	81.1	81.0	80.9	80.9	80.9	80.9	80.9
82.5°	62.5	62.2	61.9	61.7	61.6	61.5	61.4	61.3
85°	35.4	35.2	34.8	34.7	34.7	34.7	34.7	34.7
87.5°	16.2	16.2	16.2	16.3	16.4	16.4	16.5	16.6
90°	19.0	19.6	20.3	20.8	21.1	21.5	21.8	22.1
92.5°	20.9	22.0	23.1	23.7	23.8	24.0	24.2	24.5
95°	25.2	26.3	27.4	28.0	28.0	28.0	28.0	28.0
97.5°	26.4	27.6	28.9	29.7	29.9	30.1	30.2	30.3
100°	27.0	28.3	29.6	30.3	30.4	30.6	30.8	30.9
102.5°	40.3	36.3	32.2	30.3	30.6	30.9	31.2	31.6
105°	103.4	74.5	45.4	31.1	31.5	31.8	32.1	32.4
107.5°	253.3	232.1	210.8	189.2	167.4	145.5	123.7	101.8
110°	321.5	316.1	310.8	296.3	272.9	249.5	226.0	202.6





TEST NUMBER: P331934-830

CATALOG NUMBER: S123DIP-S560D805U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	369.7	369.8	369.9	367.4	362.5	357.5	352.6	347.7
115°	426.2	427.9	429.5	430.6	431.3	432.0	432.6	433.3
117.5°	477.5	478.8	480.0	480.8	481.0	481.1	481.2	481.4
120°	511.0	512.4	513.7	514.3	514.3	514.3	514.3	514.3
122.5°	543.8	544.8	545.7	546.2	546.4	546.5	546.7	546.8
125°	590.1	590.5	590.8	591.2	591.4	591.8	592.1	592.5
127.5°	636.5	637.1	637.5	637.6	637.3	637.1	636.7	636.4
130°	664.5	665.2	665.8	666.0	665.6	665.3	665.0	664.7
132.5°	691.0	691.6	692.3	692.4	692.0	691.5	691.1	690.6
135°	731.2	731.7	732.2	732.2	731.7	731.2	730.8	730.3
137.5°	767.0	767.8	768.6	768.8	768.5	768.2	767.9	767.5
140°	789.8	790.4	791.1	791.3	790.9	790.6	790.2	789.9
142.5°	811.3	811.8	812.4	812.4	811.9	811.4	811.1	810.6
145°	841.4	841.8	842.1	842.3	842.3	842.3	842.3	842.3
147.5°	868.4	868.7	869.0	868.8	868.1	867.3	866.6	865.8
150°	884.9	885.2	885.5	885.5	885.0	884.5	884.0	883.5
152.5°	899.6	900.1	900.8	900.7	899.9	899.2	898.4	897.7
155°	919.8	920.6	921.4	921.3	920.4	919.4	918.4	917.4
157.5°	937.4	938.3	939.3	939.1	937.9	936.6	935.4	934.1
160°	947.3	948.4	949.3	949.2	948.1	947.0	945.8	944.7
162.5°	956.5	957.6	958.7	958.8	957.7	956.7	955.7	954.7
165°	968.7	970.0	971.3	971.4	970.3	969.0	967.9	966.8
167.5°	978.1	979.4	980.7	980.7	979.4	978.1	976.8	975.4
170°	983.4	984.7	986.0	986.0	984.7	983.4	982.1	980.8
172.5°	986.9	988.3	989.6	989.5	988.1	986.7	985.1	983.7
175°	991.2	992.3	993.4	993.3	992.1	990.8	989.5	988.2
177.5°	992.8	993.8	994.9	994.8	993.4	992.1	990.8	989.5
180°	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8

(END OF REPORT)