

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332353

Luminaire Tested: **S123RDIP-S1000D1025U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332353
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D1025U835-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7504.8 lumens
Efficiency: N/A
Efficacy: 124.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332353

CATALOG NUMBER: S123RDIP-S1000D1025U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332353

CATALOG NUMBER: S123RDIP-S1000D1025U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	87	91	87	84	81	74	71	69	62	60	59	51	49	48	43
2	90	82	77	71	83	76	71	67	65	61	58	55	52	49	45	43	41	37
3	82	73	66	60	76	68	61	56	58	53	49	49	45	42	40	38	36	31
4	75	65	57	51	69	60	53	48	51	46	42	43	40	36	36	33	31	27
5	69	58	50	44	64	54	47	41	46	41	36	39	35	32	33	30	27	24
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	30	26	24	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	24	21	19
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19	17
9	51	39	32	27	47	37	30	25	32	26	23	27	23	20	23	20	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18064	18064	18064
5°	18133	17882	17986
10°	18030	17658	17598
15°	17836	17245	17063
20°	17570	16728	16339
25°	17296	16149	15631
30°	16933	15479	14633
35°	16561	14808	13717
40°	16218	14018	12584
45°	15767	13239	11561
50°	15270	12353	10416
55°	14763	11340	9348
60°	14299	10256	8174
65°	13692	9082	7002
70°	12935	7626	5655
75°	11832	6001	5319
80°	10544	5312	4891
85°	8904	4705	4372



TEST NUMBER: P332353

CATALOG NUMBER: S123RDIP-S1000D1025U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.6	2.1
10°-20°	438.5	5.8
20°-30°	631.4	8.4
30°-40°	711.2	9.5
40°-50°	680.4	9.1
50°-60°	557.2	7.4
60°-70°	375.9	5.0
70°-80°	189.1	2.5
80°-90°	53.8	0.7
90°-100°	274.4	3.7
100°-110°	777.0	10.4
110°-120°	764.4	10.2
120°-130°	609.7	8.1
130°-140°	480.7	6.4
140°-150°	358.8	4.8
150°-160°	250.1	3.3
160°-170°	146.9	2.0
170°-180°	47.8	0.6
0°-30°	1227.4	16.4
0°-40°	1938.6	25.8
0°-60°	3176.1	42.3
0°-90°	3794.9	50.6
90°-120°	1815.8	24.2
90°-150°	3265.1	43.5
90°-180°	3710.0	49.4
0°-180°	7504.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1678	1678	1678	1678	1678	
5°	1678	1671	1655	1666	1665	159
15°	1601	1584	1548	1541	1531	451
25°	1456	1421	1360	1332	1316	669
35°	1260	1209	1127	1070	1044	788
45°	1036	972	870	795	760	799
55°	787	717	604	528	498	705
65°	538	461	357	293	275	532
75°	284	219	144	131	128	303
85°	72	44	38	36	35	81
90°	2	12	25	28	29	6
95°	34	110	592	173	116	37
105°	116	171	802	1403	1270	123
115°	205	255	614	1346	1544	203
125°	284	336	573	1038	1218	252
135°	333	398	565	855	987	258
145°	380	436	558	701	772	238
155°	432	466	540	614	640	199
165°	472	486	517	548	558	133
175°	492	493	496	503	502	47
180°	493	493	493	493	493	



TEST NUMBER: P332353

CATALOG NUMBER: S123RDIP-S1000D1025U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2
2.5°	1683.6	1682.6	1681.7	1680.7	1679.7	1677.8	1674.9	1672.0	1669.1	1666.2	1668.8
5°	1678.2	1676.6	1675.1	1673.6	1672.1	1669.5	1665.9	1662.3	1658.7	1655.0	1657.7
7.5°	1662.6	1661.0	1659.4	1657.7	1656.1	1652.9	1648.2	1643.5	1638.8	1634.1	1635.6
10°	1649.6	1647.5	1645.3	1643.2	1641.1	1637.3	1631.9	1626.4	1621.0	1615.6	1615.9
12.5°	1631.1	1628.7	1626.4	1624.0	1621.6	1617.1	1610.5	1603.8	1597.2	1590.5	1590.3
15°	1600.6	1597.3	1593.9	1590.6	1587.3	1581.4	1572.9	1564.4	1556.0	1547.5	1546.0
17.5°	1562.2	1558.3	1554.5	1550.6	1546.7	1539.4	1528.6	1517.9	1507.1	1496.3	1493.1
20°	1533.9	1529.1	1524.2	1519.4	1514.5	1506.4	1494.9	1483.4	1471.9	1460.4	1456.5
22.5°	1502.3	1496.8	1491.2	1485.6	1480.1	1471.2	1458.9	1446.7	1434.5	1422.3	1417.4
25°	1456.3	1448.8	1441.2	1433.6	1426.1	1415.3	1401.4	1387.5	1373.6	1359.7	1353.3
27.5°	1400.5	1392.2	1383.8	1375.5	1367.1	1355.2	1339.7	1324.2	1308.7	1293.3	1284.4
30°	1362.4	1353.3	1344.3	1335.2	1326.1	1313.1	1296.2	1279.2	1262.3	1245.4	1235.1
32.5°	1324.3	1314.0	1303.7	1293.4	1283.2	1269.1	1251.2	1233.3	1215.3	1197.4	1186.2
35°	1260.3	1249.4	1238.5	1227.7	1216.8	1201.9	1183.2	1164.4	1145.7	1126.9	1113.9
37.5°	1195.5	1183.4	1171.3	1159.2	1147.1	1131.1	1111.1	1091.0	1071.0	1051.0	1036.2
40°	1154.2	1140.9	1127.5	1114.2	1100.9	1083.5	1062.1	1040.6	1019.1	997.6	981.9
42.5°	1107.3	1094.0	1080.7	1067.4	1054.1	1036.4	1014.2	992.0	969.8	947.6	930.4
45°	1035.8	1022.1	1008.5	994.9	981.3	962.9	939.6	916.3	893.0	869.7	852.5
47.5°	964.2	949.2	934.3	919.3	904.4	885.3	862.0	838.7	815.4	792.1	773.4
50°	911.9	897.7	883.5	869.3	855.0	835.7	811.2	786.7	762.2	737.7	718.9
52.5°	865.1	849.7	834.2	818.8	803.4	783.5	759.3	735.0	710.8	686.5	667.0
55°	786.7	771.9	757.0	742.2	727.4	707.1	681.4	655.7	630.0	604.3	586.8
57.5°	714.3	698.1	682.0	665.8	649.7	628.7	602.8	577.0	551.2	525.4	508.8
60°	664.2	647.6	630.9	614.3	597.6	576.8	551.7	526.6	501.5	476.4	460.0
62.5°	614.1	597.5	580.8	564.2	547.6	526.7	501.6	476.5	451.4	426.3	410.9
65°	537.6	521.0	504.3	487.7	471.1	451.0	427.4	403.8	380.2	356.6	341.8
67.5°	461.1	444.3	427.5	410.7	393.9	374.1	351.5	328.9	306.3	283.6	272.6
70°	411.0	394.7	378.4	362.0	345.7	327.0	305.8	284.6	263.4	242.3	231.7
72.5°	360.9	344.9	328.8	312.7	296.6	278.9	259.7	240.5	221.2	202.0	193.3
75°	284.5	269.9	255.4	240.9	226.4	210.8	194.2	177.5	160.9	144.3	141.2
77.5°	214.8	201.6	188.5	175.4	162.3	150.3	139.6	128.9	118.2	107.5	105.9
80°	170.1	157.7	145.3	132.9	120.5	111.2	104.8	98.4	92.1	85.7	84.8
82.5°	127.7	117.0	106.3	95.5	84.8	78.0	75.0	72.1	69.1	66.1	65.2
85°	72.1	65.5	58.8	52.2	45.5	41.7	40.8	39.9	39.0	38.1	37.5
87.5°	26.5	24.3	22.0	19.9	17.7	16.8	17.3	17.9	18.5	19.1	18.7
90°	2.0	4.0	6.0	9.0	11.0	13.0	16.0	19.0	22.0	25.0	24.0
92.5°	12.4	18.4	26.8	34.5	42.9	57.7	83.8	126.8	168.9	153.5	115.8
95°	33.9	36.9	47.9	64.9	90.8	129.8	214.6	363.3	527.0	591.9	480.1
97.5°	57.9	58.9	67.5	82.2	107.8	149.9	231.0	398.7	671.6	917.3	981.4
100°	73.9	74.9	81.9	95.8	119.8	158.7	228.6	376.3	638.8	945.3	1141.9
102.5°	90.6	92.4	98.6	111.8	133.4	169.1	231.8	357.1	590.9	893.4	1149.9
105°	115.8	118.8	124.8	136.8	155.7	186.7	240.6	343.4	532.0	802.5	1089.0
107.5°	142.5	145.5	151.3	163.1	180.9	209.6	256.9	342.4	494.5	722.3	982.4
110°	161.7	164.7	169.7	180.7	197.6	225.6	270.5	346.4	480.1	676.8	915.3



TEST NUMBER: P332353

CATALOG NUMBER: S123RDIP-S1000D1025U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	179.3	182.3	187.3	198.2	215.2	242.4	284.1	354.4	472.1	646.4	857.0
115°	204.6	208.6	214.6	224.6	241.6	268.5	306.4	367.3	469.1	613.9	786.6
117.5°	230.0	234.6	239.6	248.7	267.7	292.7	330.2	384.5	470.9	594.7	744.0
120°	247.5	250.5	255.5	265.5	284.5	309.4	345.4	397.3	474.1	585.9	721.7
122.5°	262.7	265.7	270.7	281.5	299.7	326.2	361.3	409.3	479.7	580.3	703.3
125°	284.5	286.5	292.5	303.4	322.4	349.4	384.3	428.2	488.1	573.0	679.8
127.5°	301.1	304.0	311.4	322.6	343.6	370.5	404.3	443.8	497.7	569.4	659.0
130°	311.4	314.4	323.4	335.4	356.3	383.3	416.2	454.2	504.1	567.0	647.8
132.5°	319.4	323.2	333.0	347.4	368.3	394.5	426.6	463.8	508.9	566.2	637.4
135°	333.4	337.4	348.4	363.3	384.3	411.2	442.2	476.1	516.1	565.0	623.9
137.5°	346.6	350.8	361.5	377.5	398.3	423.2	453.0	485.3	520.8	562.8	612.1
140°	355.4	360.3	370.3	386.3	406.3	431.2	460.2	490.1	524.0	562.0	604.9
142.5°	364.9	369.1	379.9	394.3	414.2	437.6	465.8	494.9	526.4	560.4	598.5
145°	380.3	383.3	392.3	407.3	424.2	447.2	473.1	500.1	528.0	558.0	589.9
147.5°	395.9	397.7	406.5	419.4	435.8	455.4	479.1	503.3	528.0	554.2	581.5
150°	406.3	407.3	415.2	428.2	442.2	460.2	483.1	504.1	528.0	551.0	575.9
152.5°	416.6	416.8	424.8	436.2	448.6	465.8	485.5	505.7	525.6	547.0	569.6
155°	432.2	432.2	438.2	448.2	459.2	473.1	490.1	506.1	523.0	540.0	560.0
157.5°	444.6	445.4	450.2	459.0	468.3	479.1	492.7	507.1	519.7	533.8	549.2
160°	454.2	454.2	458.2	466.1	473.1	483.1	495.1	507.1	518.1	529.0	542.0
162.5°	461.4	461.4	464.6	470.9	477.1	485.5	495.9	506.3	514.9	524.2	534.8
165°	472.1	471.1	473.1	478.1	482.1	489.1	497.1	504.1	510.1	517.1	525.0
167.5°	480.3	479.1	480.1	483.9	486.7	491.1	496.9	502.5	505.3	509.9	515.7
170°	485.1	483.1	484.1	487.1	489.1	491.1	496.1	500.1	502.1	505.1	510.1
172.5°	488.3	487.1	487.3	489.5	490.7	491.9	496.1	499.3	499.7	501.1	504.5
175°	492.1	491.1	490.1	492.1	492.1	493.1	495.1	497.1	496.1	496.1	498.1
177.5°	493.9	493.1	492.3	493.1	493.1	493.1	493.9	495.5	493.9	493.1	493.9
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P332353

CATALOG NUMBER: S123RDIP-S1000D1025U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2
2.5°	1671.5	1674.2	1676.8	1677.9	1677.4	1677.0	1676.5	1676.0
5°	1660.5	1663.2	1665.9	1667.0	1666.4	1665.8	1665.2	1664.6
7.5°	1637.1	1638.6	1640.1	1640.4	1639.3	1638.3	1637.3	1636.2
10°	1616.2	1616.5	1616.8	1616.2	1614.6	1613.1	1611.6	1610.1
12.5°	1590.1	1590.0	1589.8	1588.8	1587.1	1585.3	1583.6	1581.8
15°	1544.5	1543.0	1541.5	1539.6	1537.5	1535.4	1533.3	1531.2
17.5°	1489.9	1486.7	1483.5	1480.3	1477.2	1474.0	1470.9	1467.7
20°	1452.5	1448.6	1444.7	1440.9	1437.3	1433.6	1430.0	1426.4
22.5°	1412.5	1407.6	1402.7	1398.5	1395.2	1391.8	1388.4	1385.0
25°	1347.0	1340.6	1334.3	1329.4	1326.1	1322.8	1319.5	1316.1
27.5°	1275.6	1266.8	1257.9	1251.0	1245.9	1240.8	1235.7	1230.7
30°	1224.8	1214.5	1204.2	1196.7	1191.8	1187.0	1182.1	1177.3
32.5°	1174.9	1163.7	1152.4	1144.3	1139.2	1134.1	1129.0	1123.9
35°	1100.9	1087.9	1074.9	1065.7	1060.3	1054.8	1049.4	1043.9
37.5°	1021.5	1006.7	992.0	981.2	974.5	967.8	961.1	954.4
40°	966.2	950.5	934.7	923.4	916.4	909.5	902.5	895.6
42.5°	913.2	896.0	878.8	867.1	860.9	854.7	848.4	842.2
45°	835.2	818.0	800.7	788.5	781.2	774.0	766.7	759.5
47.5°	754.6	735.9	717.1	704.5	698.0	691.6	685.1	678.6
50°	700.2	681.4	662.7	649.8	642.9	635.9	629.0	622.0
52.5°	647.6	628.1	608.6	595.7	589.5	583.3	577.1	570.8
55°	569.2	551.7	534.1	522.3	516.3	510.2	504.2	498.1
57.5°	492.2	475.6	459.1	448.2	443.1	437.9	432.8	427.6
60°	443.7	427.4	411.0	400.3	395.2	390.0	384.9	379.7
62.5°	395.5	380.2	364.8	354.4	349.1	343.7	338.3	332.9
65°	327.0	312.1	297.3	288.2	284.9	281.6	278.3	274.9
67.5°	261.5	250.4	239.4	232.0	228.5	224.9	221.3	217.8
70°	221.1	210.5	199.9	193.0	189.6	186.3	183.0	179.7
72.5°	184.7	176.0	167.4	162.4	161.0	159.6	158.2	156.8
75°	138.2	135.2	132.2	130.4	129.8	129.1	128.5	127.9
77.5°	104.3	102.6	101.0	99.9	99.3	98.7	98.1	97.5
80°	83.9	83.0	82.1	81.4	80.8	80.2	79.5	78.9
82.5°	64.3	63.4	62.5	62.0	61.9	61.8	61.6	61.5
85°	36.9	36.3	35.7	35.4	35.4	35.4	35.4	35.4
87.5°	18.7	18.6	18.6	18.7	18.3	18.3	18.2	17.8
90°	25.0	26.0	27.0	28.9	27.9	28.9	29.9	28.9
92.5°	84.0	66.7	58.9	53.7	51.9	48.9	49.9	48.1
95°	359.3	243.6	190.7	154.7	135.8	126.8	119.8	115.8
97.5°	895.8	717.5	588.7	469.3	395.7	350.8	323.8	315.2
100°	1176.9	1096.0	979.2	837.5	736.7	663.8	624.9	625.9
102.5°	1270.3	1267.7	1199.6	1109.8	1031.3	973.6	941.1	918.1
105°	1297.6	1397.5	1416.4	1390.5	1344.5	1306.6	1274.7	1269.7
107.5°	1219.0	1381.1	1468.5	1504.1	1504.9	1492.1	1481.3	1472.1
110°	1143.9	1327.6	1453.3	1523.2	1551.2	1559.2	1557.2	1555.2



TEST NUMBER: P332353

CATALOG NUMBER: S123RDIP-S1000D1025U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1069.6	1257.3	1398.2	1488.1	1539.2	1563.9	1571.5	1571.9
115°	971.2	1144.9	1291.6	1400.4	1475.3	1519.2	1539.2	1544.2
117.5°	900.0	1049.9	1181.6	1292.0	1370.1	1420.4	1449.2	1455.9
120°	862.4	997.2	1117.0	1217.8	1296.6	1352.5	1376.5	1382.5
122.5°	832.9	954.9	1065.9	1159.5	1229.6	1279.9	1306.2	1313.8
125°	793.6	902.4	998.2	1078.0	1141.9	1185.8	1210.8	1217.8
127.5°	759.2	856.2	942.7	1015.3	1072.2	1109.8	1132.3	1138.7
130°	737.7	827.5	908.3	976.2	1029.1	1065.1	1086.0	1094.0
132.5°	717.7	800.3	875.6	940.3	990.0	1025.9	1044.5	1050.1
135°	690.7	761.6	826.5	883.4	932.3	962.2	980.2	987.2
137.5°	666.2	724.3	780.2	829.5	870.6	901.0	916.1	920.7
140°	651.8	702.7	750.6	793.6	831.5	859.4	875.4	874.4
142.5°	638.2	682.0	723.5	760.8	793.2	817.9	832.3	831.3
145°	621.9	654.8	686.7	715.7	740.6	761.6	769.6	771.6
147.5°	608.5	634.6	660.4	681.0	699.9	714.1	721.7	722.5
150°	598.9	621.9	642.8	661.8	676.8	687.7	693.7	693.7
152.5°	590.1	609.9	628.5	644.2	656.0	666.2	669.8	669.8
155°	576.9	592.9	607.9	619.9	628.9	636.8	638.8	639.8
157.5°	563.0	576.3	587.9	597.3	605.1	611.1	612.7	612.5
160°	555.0	566.0	575.9	582.9	589.9	595.9	595.9	594.9
162.5°	545.4	554.8	564.0	570.2	574.8	579.9	579.9	578.9
165°	533.0	539.0	546.0	551.0	555.0	559.0	558.0	558.0
167.5°	522.2	526.8	530.8	534.4	536.2	539.0	538.0	538.0
170°	515.1	518.1	522.0	524.0	525.0	527.0	526.0	526.0
172.5°	508.7	510.9	514.1	515.3	515.5	517.5	515.7	514.9
175°	500.1	501.1	503.1	503.1	503.1	504.1	503.1	502.1
177.5°	494.7	495.5	496.3	496.3	495.5	496.3	494.7	494.7
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1

(END OF REPORT)