

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332357

Luminaire Tested: **S123RDIP-S1000D1195U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332357  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1000D1195U835-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1195 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8564.3 lumens  
Efficiency: N/A  
Efficacy: 131.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332357

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332357

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44				
1	97	93	89	85	89	85	82	79	71	68	66	58	56	55	45	44	44	38				
2	88	81	75	70	81	75	70	65	62	59	55	51	48	46	40	39	37	32				
3	81	72	64	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28				
4	74	63	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24				
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	29	26	24	21				
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21	18				
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19	16				
8	54	42	34	29	49	39	32	27	33	28	24	27	23	21	22	19	17	15				
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	16	13				
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18064	18064	18064
5°	18133	17882	17986
10°	18030	17658	17598
15°	17836	17245	17063
20°	17570	16728	16339
25°	17296	16149	15631
30°	16933	15479	14633
35°	16561	14808	13717
40°	16218	14018	12584
45°	15767	13239	11561
50°	15270	12353	10416
55°	14763	11340	9348
60°	14299	10256	8174
65°	13692	9082	7002
70°	12935	7626	5655
75°	11832	6001	5319
80°	10544	5312	4891
85°	8904	4705	4372



TEST NUMBER: P332357

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	157.6	1.8
10°-20°	438.5	5.1
20°-30°	631.4	7.4
30°-40°	711.2	8.3
40°-50°	680.4	7.9
50°-60°	557.2	6.5
60°-70°	375.9	4.4
70°-80°	189.1	2.2
80°-90°	54.4	0.6
90°-100°	56.9	0.7
100°-110°	271.0	3.2
110°-120°	650.9	7.6
120°-130°	828.8	9.7
130°-140°	885.6	10.3
140°-150°	828.1	9.7
150°-160°	668.0	7.8
160°-170°	431.1	5.0
170°-180°	148.6	1.7
0°-30°	1227.4	14.3
0°-40°	1938.6	22.6
0°-60°	3176.1	37.1
0°-90°	3795.5	44.3
90°-120°	978.7	11.4
90°-150°	3521.2	41.1
90°-180°	4769.0	55.7
0°-180°	8564.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1678	1678	1678	1678	1678	
5°	1678	1671	1655	1666	1665	159
15°	1601	1584	1548	1541	1531	451
25°	1456	1421	1360	1332	1316	669
35°	1260	1209	1127	1070	1044	788
45°	1036	972	870	795	760	799
55°	787	717	604	528	498	705
65°	538	461	357	293	275	532
75°	284	219	144	131	128	303
85°	72	44	38	36	35	81
90°	1	13	28	32	35	7
95°	71	27	36	44	44	88
105°	346	352	254	60	51	367
115°	650	657	667	678	683	641
125°	916	925	929	932	934	817
135°	1140	1147	1151	1154	1151	877
145°	1315	1323	1326	1328	1328	823
155°	1449	1447	1448	1453	1446	667
165°	1528	1524	1523	1531	1524	431
175°	1564	1558	1559	1566	1558	149
180°	1564	1564	1564	1564	1564	



TEST NUMBER: P332357

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2
2.5°	1683.6	1682.6	1681.7	1680.7	1679.7	1677.8	1674.9	1672.0	1669.1	1666.2	1668.8
5°	1678.2	1676.6	1675.1	1673.6	1672.1	1669.5	1665.9	1662.3	1658.7	1655.0	1657.7
7.5°	1662.6	1661.0	1659.4	1657.7	1656.1	1652.9	1648.2	1643.5	1638.8	1634.1	1635.6
10°	1649.6	1647.5	1645.3	1643.2	1641.1	1637.3	1631.9	1626.4	1621.0	1615.6	1615.9
12.5°	1631.1	1628.7	1626.4	1624.0	1621.6	1617.1	1610.5	1603.8	1597.2	1590.5	1590.3
15°	1600.6	1597.3	1593.9	1590.6	1587.3	1581.4	1572.9	1564.4	1556.0	1547.5	1546.0
17.5°	1562.2	1558.3	1554.5	1550.6	1546.7	1539.4	1528.6	1517.9	1507.1	1496.3	1493.1
20°	1533.9	1529.1	1524.2	1519.4	1514.5	1506.4	1494.9	1483.4	1471.9	1460.4	1456.5
22.5°	1502.3	1496.8	1491.2	1485.6	1480.1	1471.2	1458.9	1446.7	1434.5	1422.3	1417.4
25°	1456.3	1448.8	1441.2	1433.6	1426.1	1415.3	1401.4	1387.5	1373.6	1359.7	1353.3
27.5°	1400.5	1392.2	1383.8	1375.5	1367.1	1355.2	1339.7	1324.2	1308.7	1293.3	1284.4
30°	1362.4	1353.3	1344.3	1335.2	1326.1	1313.1	1296.2	1279.2	1262.3	1245.4	1235.1
32.5°	1324.3	1314.0	1303.7	1293.4	1283.2	1269.1	1251.2	1233.3	1215.3	1197.4	1186.2
35°	1260.3	1249.4	1238.5	1227.7	1216.8	1201.9	1183.2	1164.4	1145.7	1126.9	1113.9
37.5°	1195.5	1183.4	1171.3	1159.2	1147.1	1131.1	1111.1	1091.0	1071.0	1051.0	1036.2
40°	1154.2	1140.9	1127.5	1114.2	1100.9	1083.5	1062.1	1040.6	1019.1	997.6	981.9
42.5°	1107.3	1094.0	1080.7	1067.4	1054.1	1036.4	1014.2	992.0	969.8	947.6	930.4
45°	1035.8	1022.1	1008.5	994.9	981.3	962.9	939.6	916.3	893.0	869.7	852.5
47.5°	964.2	949.2	934.3	919.3	904.4	885.3	862.0	838.7	815.4	792.1	773.4
50°	911.9	897.7	883.5	869.3	855.0	835.7	811.2	786.7	762.2	737.7	718.9
52.5°	865.1	849.7	834.2	818.8	803.4	783.5	759.3	735.0	710.8	686.5	667.0
55°	786.7	771.9	757.0	742.2	727.4	707.1	681.4	655.7	630.0	604.3	586.8
57.5°	714.3	698.1	682.0	665.8	649.7	628.7	602.8	577.0	551.2	525.4	508.8
60°	664.2	647.6	630.9	614.3	597.6	576.8	551.7	526.6	501.5	476.4	460.0
62.5°	614.1	597.5	580.8	564.2	547.6	526.7	501.6	476.5	451.4	426.3	410.9
65°	537.6	521.0	504.3	487.7	471.1	451.0	427.4	403.8	380.2	356.6	341.8
67.5°	461.1	444.3	427.5	410.7	393.9	374.1	351.5	328.9	306.3	283.6	272.6
70°	411.0	394.7	378.4	362.0	345.7	327.0	305.8	284.6	263.4	242.3	231.7
72.5°	360.9	344.9	328.8	312.7	296.6	278.9	259.7	240.5	221.2	202.0	193.3
75°	284.5	269.9	255.4	240.9	226.4	210.8	194.2	177.5	160.9	144.3	141.2
77.5°	214.8	201.6	188.5	175.4	162.3	150.3	139.6	128.9	118.2	107.5	105.9
80°	170.1	157.7	145.3	132.9	120.5	111.2	104.8	98.4	92.1	85.7	84.8
82.5°	127.7	117.0	106.3	95.5	84.8	78.0	75.0	72.1	69.1	66.1	65.2
85°	72.1	65.5	58.8	52.2	45.5	41.7	40.8	39.9	39.0	38.1	37.5
87.5°	26.4	24.2	22.1	19.9	17.8	17.0	17.7	18.4	19.1	19.7	19.7
90°	1.2	3.7	6.3	8.9	11.5	14.5	17.8	21.2	24.5	27.9	28.9
92.5°	21.6	20.9	20.2	19.4	18.7	19.6	22.2	24.7	27.2	29.7	31.4
95°	70.9	60.3	49.7	39.1	28.5	24.7	27.5	30.3	33.2	36.0	37.8
97.5°	142.4	137.7	132.9	128.2	123.4	111.8	93.2	74.6	56.0	37.4	39.5
100°	196.3	201.5	206.7	211.8	217.0	199.4	159.2	118.9	78.6	38.3	40.4
102.5°	257.7	261.4	265.1	268.8	272.6	252.4	208.4	164.4	120.4	76.4	70.0
105°	346.2	349.1	351.9	354.7	357.6	347.4	324.1	300.9	277.7	254.4	208.7
107.5°	439.6	441.9	444.2	446.4	448.7	451.7	455.4	459.0	462.7	466.4	432.8
110°	501.9	504.0	506.0	508.1	510.2	512.6	515.5	518.3	521.1	524.0	515.5



TEST NUMBER: P332357

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	561.4	563.2	565.1	567.0	568.8	571.2	574.0	576.9	579.7	582.5	582.7
115°	649.5	651.0	652.5	654.1	655.6	657.6	659.9	662.2	664.6	666.9	669.5
117.5°	734.7	736.6	738.5	740.5	742.4	743.9	745.1	746.3	747.5	748.7	750.7
120°	787.7	790.0	792.4	794.7	797.0	798.6	799.3	800.1	800.9	801.6	803.7
122.5°	841.6	843.5	845.4	847.3	849.3	850.7	851.7	852.7	853.6	854.6	856.1
125°	915.5	917.6	919.6	921.7	923.8	925.3	926.3	927.4	928.4	929.4	930.0
127.5°	987.1	989.1	991.2	993.3	995.3	997.0	998.2	999.5	1000.7	1001.9	1002.8
130°	1031.7	1033.8	1035.8	1037.9	1039.9	1041.5	1042.5	1043.6	1044.6	1045.6	1046.7
132.5°	1074.4	1076.5	1078.6	1080.6	1082.7	1084.1	1085.0	1085.8	1086.6	1087.5	1088.5
135°	1139.7	1141.3	1142.8	1144.4	1145.9	1147.2	1148.3	1149.3	1150.3	1151.4	1152.1
137.5°	1195.5	1197.5	1199.4	1201.4	1203.4	1204.6	1205.2	1205.8	1206.3	1206.9	1208.1
140°	1232.7	1234.2	1235.8	1237.3	1238.9	1240.0	1240.8	1241.6	1242.4	1243.1	1244.2
142.5°	1267.1	1268.6	1270.2	1271.7	1273.3	1274.4	1275.2	1276.0	1276.8	1277.5	1278.4
145°	1315.2	1317.0	1318.8	1320.6	1322.4	1323.6	1324.1	1324.6	1325.1	1325.6	1326.1
147.5°	1360.5	1361.7	1362.9	1364.0	1365.2	1366.1	1366.6	1367.1	1367.6	1368.1	1368.7
150°	1388.4	1389.1	1389.9	1390.7	1391.5	1392.1	1392.6	1393.1	1393.7	1394.2	1394.7
152.5°	1413.5	1413.8	1414.2	1414.5	1414.9	1415.2	1415.5	1415.9	1416.2	1416.5	1417.4
155°	1448.8	1448.3	1447.7	1447.2	1446.7	1446.6	1446.8	1447.1	1447.4	1447.6	1448.9
157.5°	1476.2	1476.1	1476.1	1476.0	1476.0	1475.8	1475.6	1475.3	1475.1	1474.8	1476.4
160°	1492.9	1492.7	1492.4	1492.2	1491.9	1491.6	1491.4	1491.1	1490.9	1490.6	1492.2
162.5°	1508.7	1508.1	1507.4	1506.7	1506.0	1505.6	1505.3	1505.1	1504.8	1504.5	1506.3
165°	1527.8	1527.0	1526.2	1525.5	1524.7	1524.2	1523.9	1523.6	1523.4	1523.1	1525.2
167.5°	1542.7	1541.6	1540.6	1539.6	1538.5	1538.0	1538.0	1538.0	1538.0	1538.0	1540.1
170°	1551.0	1550.0	1549.0	1547.9	1546.9	1546.4	1546.4	1546.4	1546.4	1546.4	1548.4
172.5°	1556.6	1555.4	1554.1	1552.9	1551.6	1551.1	1551.3	1551.5	1551.7	1551.9	1554.0
175°	1563.8	1562.5	1561.2	1559.9	1558.6	1558.1	1558.4	1558.6	1558.9	1559.1	1561.0
177.5°	1565.7	1564.6	1563.6	1562.6	1561.5	1561.1	1561.3	1561.5	1561.7	1561.9	1563.6
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P332357

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2
2.5°	1671.5	1674.2	1676.8	1677.9	1677.4	1677.0	1676.5	1676.0
5°	1660.5	1663.2	1665.9	1667.0	1666.4	1665.8	1665.2	1664.6
7.5°	1637.1	1638.6	1640.1	1640.4	1639.3	1638.3	1637.3	1636.2
10°	1616.2	1616.5	1616.8	1616.2	1614.6	1613.1	1611.6	1610.1
12.5°	1590.1	1590.0	1589.8	1588.8	1587.1	1585.3	1583.6	1581.8
15°	1544.5	1543.0	1541.5	1539.6	1537.5	1535.4	1533.3	1531.2
17.5°	1489.9	1486.7	1483.5	1480.3	1477.2	1474.0	1470.9	1467.7
20°	1452.5	1448.6	1444.7	1440.9	1437.3	1433.6	1430.0	1426.4
22.5°	1412.5	1407.6	1402.7	1398.5	1395.2	1391.8	1388.4	1385.0
25°	1347.0	1340.6	1334.3	1329.4	1326.1	1322.8	1319.5	1316.1
27.5°	1275.6	1266.8	1257.9	1251.0	1245.9	1240.8	1235.7	1230.7
30°	1224.8	1214.5	1204.2	1196.7	1191.8	1187.0	1182.1	1177.3
32.5°	1174.9	1163.7	1152.4	1144.3	1139.2	1134.1	1129.0	1123.9
35°	1100.9	1087.9	1074.9	1065.7	1060.3	1054.8	1049.4	1043.9
37.5°	1021.5	1006.7	992.0	981.2	974.5	967.8	961.1	954.4
40°	966.2	950.5	934.7	923.4	916.4	909.5	902.5	895.6
42.5°	913.2	896.0	878.8	867.1	860.9	854.7	848.4	842.2
45°	835.2	818.0	800.7	788.5	781.2	774.0	766.7	759.5
47.5°	754.6	735.9	717.1	704.5	698.0	691.6	685.1	678.6
50°	700.2	681.4	662.7	649.8	642.9	635.9	629.0	622.0
52.5°	647.6	628.1	608.6	595.7	589.5	583.3	577.1	570.8
55°	569.2	551.7	534.1	522.3	516.3	510.2	504.2	498.1
57.5°	492.2	475.6	459.1	448.2	443.1	437.9	432.8	427.6
60°	443.7	427.4	411.0	400.3	395.2	390.0	384.9	379.7
62.5°	395.5	380.2	364.8	354.4	349.1	343.7	338.3	332.9
65°	327.0	312.1	297.3	288.2	284.9	281.6	278.3	274.9
67.5°	261.5	250.4	239.4	232.0	228.5	224.9	221.3	217.8
70°	221.1	210.5	199.9	193.0	189.6	186.3	183.0	179.7
72.5°	184.7	176.0	167.4	162.4	161.0	159.6	158.2	156.8
75°	138.2	135.2	132.2	130.4	129.8	129.1	128.5	127.9
77.5°	104.3	102.6	101.0	99.9	99.3	98.7	98.1	97.5
80°	83.9	83.0	82.1	81.4	80.8	80.2	79.5	78.9
82.5°	64.3	63.4	62.5	62.0	61.9	61.8	61.6	61.5
85°	36.9	36.3	35.7	35.4	35.4	35.4	35.4	35.4
87.5°	19.7	19.6	19.6	19.5	19.4	19.2	19.1	18.9
90°	29.9	31.0	32.0	32.8	33.3	33.8	34.3	34.9
92.5°	33.0	34.7	36.4	37.3	37.6	38.0	38.3	38.6
95°	39.6	41.4	43.2	44.1	44.1	44.1	44.1	44.1
97.5°	41.5	43.6	45.7	46.8	47.1	47.4	47.6	47.9
100°	42.5	44.5	46.6	47.8	48.0	48.3	48.5	48.8
102.5°	63.6	57.2	50.8	47.9	48.3	48.8	49.3	49.7
105°	163.0	117.3	71.6	49.1	49.6	50.1	50.6	51.1
107.5°	399.3	365.8	332.3	298.3	263.9	229.4	195.0	160.6
110°	506.9	498.4	489.9	467.2	430.3	393.3	356.4	319.5





TEST NUMBER: P332357

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	582.8	583.0	583.2	579.3	571.5	563.7	555.9	548.1
115°	672.0	674.6	677.2	679.0	680.0	681.1	682.1	683.1
117.5°	752.8	754.9	756.9	758.1	758.3	758.5	758.7	758.9
120°	805.8	807.8	809.9	810.9	810.9	810.9	810.9	810.9
122.5°	857.5	859.0	860.4	861.2	861.4	861.6	861.9	862.1
125°	930.5	931.0	931.5	932.0	932.5	933.1	933.6	934.1
127.5°	1003.6	1004.4	1005.2	1005.4	1004.9	1004.4	1003.9	1003.3
130°	1047.7	1048.7	1049.8	1050.0	1049.5	1049.0	1048.5	1048.0
132.5°	1089.5	1090.6	1091.6	1091.7	1091.0	1090.3	1089.6	1088.8
135°	1152.9	1153.7	1154.5	1154.5	1153.7	1152.9	1152.1	1151.4
137.5°	1209.4	1210.6	1211.8	1212.2	1211.7	1211.2	1210.7	1210.1
140°	1245.2	1246.2	1247.3	1247.5	1247.0	1246.5	1246.0	1245.5
142.5°	1279.2	1280.0	1280.8	1280.9	1280.2	1279.4	1278.7	1278.0
145°	1326.7	1327.2	1327.7	1327.9	1327.9	1327.9	1327.9	1327.9
147.5°	1369.2	1369.7	1370.2	1369.9	1368.7	1367.5	1366.3	1365.1
150°	1395.2	1395.7	1396.2	1396.1	1395.3	1394.6	1393.8	1393.0
152.5°	1418.3	1419.3	1420.2	1420.1	1418.9	1417.7	1416.5	1415.3
155°	1450.2	1451.5	1452.8	1452.6	1451.1	1449.6	1448.0	1446.5
157.5°	1477.9	1479.4	1481.0	1480.8	1478.8	1476.7	1474.7	1472.7
160°	1493.7	1495.2	1496.8	1496.7	1494.9	1493.1	1491.2	1489.4
162.5°	1508.1	1509.8	1511.6	1511.6	1510.0	1508.4	1506.8	1505.2
165°	1527.3	1529.3	1531.4	1531.5	1529.7	1527.9	1526.1	1524.3
167.5°	1542.1	1544.2	1546.3	1546.3	1544.2	1542.1	1540.1	1538.0
170°	1550.5	1552.6	1554.6	1554.6	1552.6	1550.5	1548.4	1546.4
172.5°	1556.1	1558.1	1560.2	1560.1	1557.8	1555.6	1553.3	1551.0
175°	1562.8	1564.6	1566.4	1566.2	1564.2	1562.1	1560.1	1558.0
177.5°	1565.2	1566.9	1568.5	1568.3	1566.3	1564.2	1562.1	1560.1
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8

(END OF REPORT)