

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331997-830

Luminaire Tested: **S123DIP-S775D1195U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331997-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1195U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7485.6 lumens
Efficiency: N/A
Efficacy: 131.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331997-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331997-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40				
1	95	91	87	84	87	83	80	77	68	66	64	54	53	51	41	40	39	34				
2	87	80	74	68	79	73	67	63	60	56	53	47	45	43	36	35	33	28				
3	79	70	63	57	72	64	58	53	52	48	44	42	39	36	32	30	28	24				
4	72	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	20				
5	66	55	47	41	60	50	43	38	42	36	32	33	30	27	26	23	21	18				
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	21	19	15				
7	56	44	37	31	51	41	34	29	34	29	25	27	23	21	21	19	16	14				
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	12				
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13	11				
10	45	34	26	22	41	31	25	20	26	21	18	21	17	15	17	14	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12355	12355	12355
5°	12413	12241	12327
10°	12329	12136	12211
15°	12186	11999	12021
20°	12016	11802	11813
25°	11792	11569	11545
30°	11543	11309	11225
35°	11284	11037	10893
40°	11011	10732	10568
45°	10712	10456	10201
50°	10412	10114	9833
55°	10021	9760	9466
60°	9623	9347	9052
65°	9276	8899	8621
70°	8759	8387	8013
75°	8006	7719	7390
80°	7221	6912	6856
85°	6336	6101	5854



TEST NUMBER: P331997-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.1	1.4
10°-20°	305.3	4.1
20°-30°	451.0	6.0
30°-40°	526.8	7.0
40°-50°	529.6	7.1
50°-60°	465.2	6.2
60°-70°	346.6	4.6
70°-80°	197.5	2.6
80°-90°	60.8	0.8
90°-100°	53.6	0.7
100°-110°	255.4	3.4
110°-120°	613.5	8.2
120°-130°	781.2	10.4
130°-140°	834.7	11.2
140°-150°	780.5	10.4
150°-160°	629.6	8.4
160°-170°	406.3	5.4
170°-180°	140.0	1.9
0°-30°	864.4	11.5
0°-40°	1391.1	18.6
0°-60°	2385.9	31.9
0°-90°	2990.8	40.0
90°-120°	922.4	12.3
90°-150°	3318.8	44.3
90°-180°	4495.0	60.0
0°-180°	7485.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1148	1148	1148	1148	1148	
5°	1149	1143	1133	1142	1141	109
15°	1094	1089	1077	1084	1079	308
25°	993	987	974	975	972	457
35°	859	852	840	834	829	537
45°	704	699	687	675	670	543
55°	534	532	520	510	504	478
65°	364	359	349	342	338	359
75°	192	189	186	181	178	206
85°	51	50	49	48	47	56
90°	1	12	26	31	33	6
95°	67	25	34	41	42	83
105°	326	332	240	57	48	346
115°	612	619	629	639	644	604
125°	863	871	876	878	880	770
135°	1074	1081	1085	1088	1085	827
145°	1240	1247	1249	1252	1252	776
155°	1366	1364	1364	1369	1363	629
165°	1440	1437	1436	1443	1437	407
175°	1474	1469	1470	1476	1468	140
180°	1474	1474	1474	1474	1474	



TEST NUMBER: P331997-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8
2.5°	1151.7	1151.0	1150.4	1149.6	1149.0	1147.6	1145.7	1143.8	1141.8	1139.9	1141.6
5°	1148.8	1147.6	1146.6	1145.5	1144.3	1142.6	1140.2	1137.8	1135.4	1132.9	1135.2
7.5°	1137.6	1136.4	1135.3	1134.3	1133.1	1131.3	1128.8	1126.3	1123.8	1121.3	1123.3
10°	1128.0	1126.9	1125.9	1124.7	1123.7	1121.7	1118.8	1116.0	1113.1	1110.3	1112.3
12.5°	1115.4	1114.5	1113.6	1112.7	1111.7	1109.9	1107.3	1104.6	1101.9	1099.2	1100.7
15°	1093.5	1092.6	1091.7	1090.9	1090.0	1088.2	1085.2	1082.4	1079.6	1076.8	1078.5
17.5°	1068.0	1066.9	1065.7	1064.6	1063.5	1061.5	1058.7	1055.7	1052.9	1050.1	1051.3
20°	1049.0	1047.7	1046.5	1045.2	1043.9	1041.7	1038.9	1036.0	1033.2	1030.3	1031.2
22.5°	1027.7	1026.4	1025.1	1023.8	1022.5	1020.4	1017.6	1014.7	1011.9	1009.0	1009.7
25°	992.9	991.6	990.2	988.9	987.6	985.5	982.6	979.8	976.9	974.1	974.3
27.5°	955.5	954.2	953.0	951.7	950.5	948.3	945.2	942.2	939.1	935.9	936.1
30°	928.7	927.6	926.5	925.4	924.3	922.2	919.2	916.1	913.0	909.9	909.9
32.5°	901.8	900.4	898.9	897.5	896.1	894.2	891.7	889.4	887.0	884.7	883.4
35°	858.7	857.3	856.0	854.7	853.4	851.3	848.4	845.6	842.7	839.9	838.6
37.5°	814.4	812.8	811.1	809.4	807.8	805.5	802.6	799.7	796.7	793.9	792.3
40°	783.6	782.3	781.0	779.7	778.4	776.2	773.1	770.1	766.9	763.8	762.1
42.5°	752.8	751.3	749.8	748.4	746.9	744.6	741.5	738.4	735.4	732.3	730.6
45°	703.7	702.8	701.9	701.1	700.1	698.3	695.4	692.6	689.8	686.9	684.3
47.5°	654.9	653.7	652.3	651.1	649.8	647.8	645.2	642.5	639.8	637.2	634.5
50°	621.8	620.7	619.5	618.5	617.4	615.4	612.6	609.7	606.8	604.0	601.6
52.5°	587.0	586.3	585.5	584.8	584.0	582.1	579.1	576.1	573.1	570.0	568.0
55°	534.0	533.7	533.5	533.3	533.0	531.5	528.7	525.8	522.9	520.1	517.7
57.5°	483.4	482.7	481.9	481.2	480.4	478.9	476.6	474.3	472.0	469.8	467.6
60°	447.0	446.9	446.7	446.4	446.2	444.8	442.1	439.5	436.9	434.2	432.3
62.5°	414.7	414.2	413.6	413.0	412.5	410.9	408.2	405.6	402.9	400.3	398.3
65°	364.2	363.1	361.9	360.9	359.8	358.2	355.9	353.7	351.6	349.4	347.6
67.5°	310.7	309.7	308.8	307.7	306.8	305.5	303.9	302.2	300.5	298.9	297.3
70°	278.3	277.0	275.7	274.4	273.1	271.7	270.4	269.1	267.8	266.5	264.9
72.5°	244.4	243.4	242.4	241.5	240.5	239.3	237.8	236.3	234.8	233.3	232.0
75°	192.5	191.5	190.7	189.8	189.0	188.1	187.5	186.8	186.2	185.6	184.5
77.5°	146.5	146.0	145.5	145.1	144.5	143.9	143.1	142.3	141.6	140.7	140.0
80°	116.5	115.8	115.2	114.5	113.9	113.3	112.8	112.4	112.0	111.5	111.3
82.5°	87.3	87.1	87.0	86.8	86.7	86.6	86.5	86.4	86.3	86.2	85.9
85°	51.3	50.9	50.4	50.0	49.6	49.4	49.4	49.4	49.4	49.4	48.9
87.5°	20.7	20.7	20.6	20.6	20.5	20.8	21.2	21.7	22.1	22.6	22.6
90°	1.1	3.5	5.9	8.4	10.8	13.7	16.8	20.0	23.1	26.3	27.2
92.5°	20.4	19.7	19.0	18.3	17.6	18.5	20.9	23.3	25.6	28.0	29.6
95°	66.8	56.8	46.8	36.9	26.9	23.3	25.9	28.6	31.3	33.9	35.6
97.5°	134.2	129.8	125.3	120.8	116.3	105.4	87.8	70.3	52.8	35.3	37.2
100°	185.0	189.9	194.8	199.6	204.5	187.9	150.1	112.1	74.1	36.1	38.1
102.5°	242.9	246.4	249.9	253.4	256.9	237.9	196.4	155.0	113.5	72.0	66.0
105°	326.3	329.0	331.7	334.3	337.1	327.4	305.5	283.6	261.7	239.8	196.7
107.5°	414.3	416.5	418.7	420.8	422.9	425.7	429.2	432.6	436.1	439.6	407.9
110°	473.1	475.0	476.9	478.9	480.9	483.1	485.9	488.5	491.2	493.9	485.9



TEST NUMBER: P331997-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	529.1	530.8	532.6	534.4	536.1	538.4	541.0	543.8	546.4	549.0	549.2
115°	612.2	613.6	615.0	616.5	617.9	619.8	622.0	624.2	626.4	628.6	631.0
117.5°	692.5	694.3	696.1	698.0	699.7	701.2	702.3	703.4	704.6	705.7	707.6
120°	742.4	744.6	746.9	749.0	751.2	752.7	753.4	754.1	754.9	755.5	757.5
122.5°	793.2	795.0	796.8	798.6	800.5	801.8	802.8	803.7	804.6	805.5	806.9
125°	862.9	864.9	866.8	868.7	870.7	872.1	873.1	874.1	875.1	876.0	876.6
127.5°	930.4	932.3	934.2	936.2	938.1	939.7	940.8	942.1	943.2	944.3	945.2
130°	972.4	974.4	976.3	978.3	980.1	981.7	982.6	983.6	984.6	985.5	986.6
132.5°	1012.7	1014.6	1016.6	1018.5	1020.5	1021.8	1022.7	1023.4	1024.2	1025.0	1026.0
135°	1074.2	1075.7	1077.1	1078.6	1080.1	1081.3	1082.3	1083.3	1084.2	1085.2	1085.9
137.5°	1126.8	1128.7	1130.5	1132.4	1134.3	1135.4	1136.0	1136.5	1137.0	1137.6	1138.7
140°	1161.9	1163.3	1164.8	1166.2	1167.7	1168.8	1169.5	1170.3	1171.0	1171.7	1172.7
142.5°	1194.3	1195.7	1197.2	1198.6	1200.1	1201.2	1201.9	1202.7	1203.4	1204.1	1204.9
145°	1239.6	1241.3	1243.0	1244.7	1246.4	1247.5	1248.0	1248.5	1249.0	1249.4	1249.9
147.5°	1282.3	1283.5	1284.6	1285.6	1286.8	1287.6	1288.1	1288.5	1289.0	1289.5	1290.1
150°	1308.6	1309.3	1310.0	1310.8	1311.5	1312.1	1312.6	1313.1	1313.6	1314.1	1314.6
152.5°	1332.3	1332.6	1332.9	1333.2	1333.6	1333.9	1334.2	1334.5	1334.8	1335.1	1336.0
155°	1365.6	1365.1	1364.5	1364.0	1363.6	1363.5	1363.7	1364.0	1364.2	1364.4	1365.6
157.5°	1391.4	1391.3	1391.3	1391.2	1391.2	1391.0	1390.8	1390.5	1390.3	1390.1	1391.6
160°	1407.1	1406.9	1406.7	1406.5	1406.2	1405.9	1405.7	1405.4	1405.2	1405.0	1406.5
162.5°	1422.0	1421.4	1420.8	1420.1	1419.5	1419.1	1418.8	1418.6	1418.3	1418.1	1419.8
165°	1440.0	1439.3	1438.5	1437.8	1437.1	1436.6	1436.3	1436.1	1435.9	1435.6	1437.6
167.5°	1454.1	1453.0	1452.1	1451.1	1450.1	1449.6	1449.6	1449.6	1449.6	1449.6	1451.6
170°	1461.9	1460.9	1460.0	1459.0	1458.0	1457.5	1457.5	1457.5	1457.5	1457.5	1459.4
172.5°	1467.2	1466.0	1464.8	1463.7	1462.4	1462.0	1462.2	1462.4	1462.5	1462.7	1464.7
175°	1473.9	1472.7	1471.5	1470.3	1469.0	1468.6	1468.9	1469.0	1469.3	1469.5	1471.3
177.5°	1475.7	1474.7	1473.8	1472.8	1471.8	1471.4	1471.6	1471.8	1472.0	1472.2	1473.8
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P331997-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8
2.5°	1143.4	1145.2	1146.9	1147.7	1147.5	1147.4	1147.2	1147.0
5°	1137.4	1139.5	1141.8	1142.6	1142.2	1141.8	1141.3	1140.9
7.5°	1125.3	1127.3	1129.3	1130.1	1129.8	1129.5	1129.3	1129.1
10°	1114.3	1116.2	1118.1	1119.0	1118.5	1118.0	1117.7	1117.2
12.5°	1102.1	1103.5	1105.0	1105.6	1105.3	1105.0	1104.8	1104.6
15°	1080.2	1081.9	1083.7	1083.9	1082.6	1081.3	1080.1	1078.7
17.5°	1052.5	1053.8	1055.0	1055.4	1054.9	1054.4	1054.0	1053.5
20°	1032.1	1032.9	1033.9	1034.0	1033.3	1032.6	1032.0	1031.3
22.5°	1010.4	1011.2	1011.8	1011.7	1011.0	1010.1	1009.3	1008.4
25°	974.5	974.8	975.0	974.8	974.1	973.5	972.8	972.1
27.5°	936.3	936.5	936.7	936.3	935.6	934.7	933.9	933.0
30°	909.9	909.9	909.9	909.2	907.7	906.1	904.6	903.1
32.5°	882.2	881.0	879.8	878.7	877.9	877.0	876.2	875.4
35°	837.3	835.9	834.6	833.4	832.3	831.2	830.1	829.0
37.5°	790.7	789.1	787.6	786.5	785.7	785.0	784.3	783.6
40°	760.3	758.7	756.9	755.5	754.7	753.8	752.9	752.1
42.5°	728.8	727.0	725.3	724.0	723.1	722.2	721.3	720.5
45°	681.6	679.0	676.4	674.5	673.4	672.3	671.2	670.1
47.5°	632.0	629.4	626.8	625.0	624.1	623.1	622.2	621.1
50°	599.2	596.7	594.4	592.5	591.2	589.8	588.5	587.2
52.5°	565.9	563.8	561.8	560.2	558.8	557.5	556.2	554.9
55°	515.3	512.8	510.5	508.7	507.6	506.5	505.4	504.4
57.5°	465.4	463.4	461.2	459.5	458.2	456.9	455.6	454.4
60°	430.3	428.3	426.3	424.8	423.7	422.6	421.5	420.5
62.5°	396.3	394.4	392.4	391.1	390.3	389.6	388.8	388.0
65°	345.8	344.1	342.3	341.1	340.4	339.8	339.1	338.5
67.5°	295.8	294.3	292.7	291.4	290.6	289.6	288.7	287.8
70°	263.4	261.8	260.3	259.0	257.9	256.8	255.7	254.6
72.5°	230.5	229.2	227.9	226.9	226.3	225.7	225.2	224.6
75°	183.3	182.3	181.2	180.3	179.6	179.0	178.3	177.7
77.5°	139.2	138.5	137.7	137.4	137.4	137.4	137.4	137.4
80°	111.1	110.8	110.7	110.6	110.6	110.6	110.6	110.6
82.5°	85.5	85.1	84.6	84.4	84.3	84.1	83.9	83.7
85°	48.4	48.1	47.6	47.4	47.4	47.4	47.4	47.4
87.5°	22.6	22.7	22.7	22.7	22.9	23.0	23.1	23.2
90°	28.2	29.2	30.2	30.9	31.4	31.9	32.3	32.9
92.5°	31.1	32.7	34.3	35.2	35.4	35.8	36.1	36.4
95°	37.3	39.0	40.7	41.6	41.6	41.6	41.6	41.6
97.5°	39.1	41.1	43.1	44.1	44.4	44.7	44.9	45.1
100°	40.1	41.9	43.9	45.1	45.2	45.5	45.7	46.0
102.5°	59.9	53.9	47.9	45.1	45.5	46.0	46.5	46.8
105°	153.6	110.6	67.5	46.3	46.8	47.2	47.7	48.2
107.5°	376.4	344.8	313.2	281.2	248.7	216.2	183.8	151.4
110°	477.8	469.8	461.8	440.4	405.6	370.7	335.9	301.1



TEST NUMBER: P331997-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	549.3	549.5	549.7	546.0	538.7	531.3	524.0	516.6
115°	633.4	635.8	638.3	640.0	640.9	642.0	642.9	643.9
117.5°	709.5	711.5	713.4	714.5	714.7	714.9	715.1	715.3
120°	759.5	761.4	763.4	764.3	764.3	764.3	764.3	764.3
122.5°	808.2	809.6	811.0	811.7	811.9	812.1	812.4	812.6
125°	877.0	877.5	878.0	878.4	878.9	879.5	880.0	880.4
127.5°	945.9	946.7	947.4	947.6	947.2	946.7	946.2	945.7
130°	987.5	988.4	989.5	989.7	989.2	988.7	988.3	987.8
132.5°	1026.9	1027.9	1028.9	1029.0	1028.3	1027.7	1027.0	1026.2
135°	1086.7	1087.4	1088.2	1088.2	1087.4	1086.7	1085.9	1085.2
137.5°	1139.9	1141.0	1142.2	1142.6	1142.1	1141.6	1141.1	1140.6
140°	1173.7	1174.6	1175.6	1175.8	1175.4	1174.9	1174.4	1173.9
142.5°	1205.7	1206.5	1207.2	1207.3	1206.6	1205.9	1205.2	1204.6
145°	1250.5	1250.9	1251.4	1251.6	1251.6	1251.6	1251.6	1251.6
147.5°	1290.5	1291.0	1291.5	1291.2	1290.1	1288.9	1287.8	1286.7
150°	1315.0	1315.5	1316.0	1315.9	1315.1	1314.5	1313.7	1313.0
152.5°	1336.8	1337.8	1338.6	1338.5	1337.4	1336.2	1335.1	1334.0
155°	1366.9	1368.1	1369.3	1369.1	1367.7	1366.3	1364.8	1363.4
157.5°	1393.0	1394.4	1395.9	1395.7	1393.8	1391.9	1390.0	1388.1
160°	1407.9	1409.3	1410.8	1410.7	1409.0	1407.3	1405.5	1403.8
162.5°	1421.4	1423.1	1424.7	1424.7	1423.2	1421.7	1420.2	1418.7
165°	1439.5	1441.4	1443.4	1443.5	1441.8	1440.1	1438.4	1436.7
167.5°	1453.5	1455.5	1457.5	1457.5	1455.5	1453.5	1451.6	1449.6
170°	1461.4	1463.4	1465.3	1465.3	1463.4	1461.4	1459.4	1457.5
172.5°	1466.7	1468.6	1470.6	1470.5	1468.3	1466.2	1464.1	1461.9
175°	1473.0	1474.7	1476.4	1476.2	1474.3	1472.3	1470.5	1468.5
177.5°	1475.3	1476.9	1478.4	1478.2	1476.3	1474.3	1472.3	1470.5
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9

(END OF REPORT)