

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332358

Luminaire Tested: **S123RDIP-S1000D1195U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332358
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D1195U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7893.5 lumens
Efficiency: N/A
Efficacy: 120.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332358

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332358

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48					48			
1	98	93	90	86	90	86	83	80	73	70	68	60	58	57	49	47	47	41					41			
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	40	35					35			
3	82	72	65	59	75	67	61	56	57	52	48	47	44	41	38	36	34	30					30			
4	75	64	56	51	69	59	53	47	51	45	41	42	38	35	35	32	30	26					26			
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23					23			
6	63	51	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20					20			
7	59	47	39	33	54	43	36	31	37	32	28	31	27	24	26	23	21	18					18			
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	18	16					16			
9	51	39	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17	15					15			
10	47	35	28	24	44	33	27	22	29	24	20	25	20	18	21	17	15	13					13			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18064	18064	18064
5°	18133	17882	17986
10°	18030	17658	17598
15°	17836	17245	17063
20°	17570	16728	16339
25°	17296	16149	15631
30°	16933	15479	14633
35°	16561	14808	13717
40°	16218	14018	12584
45°	15767	13239	11561
50°	15270	12353	10416
55°	14763	11340	9348
60°	14299	10256	8174
65°	13692	9082	7002
70°	12935	7626	5655
75°	11832	6001	5319
80°	10544	5312	4891
85°	8904	4705	4372



TEST NUMBER: P332358

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.6	2.0
10°-20°	438.5	5.6
20°-30°	631.4	8.0
30°-40°	711.2	9.0
40°-50°	680.4	8.6
50°-60°	557.2	7.1
60°-70°	375.9	4.8
70°-80°	189.1	2.4
80°-90°	54.4	0.7
90°-100°	96.4	1.2
100°-110°	288.4	3.7
110°-120°	490.5	6.2
120°-130°	645.2	8.2
130°-140°	725.2	9.2
140°-150°	712.8	9.0
150°-160°	600.1	7.6
160°-170°	399.5	5.1
170°-180°	139.9	1.8
0°-30°	1227.4	15.5
0°-40°	1938.6	24.6
0°-60°	3176.1	40.2
0°-90°	3795.5	48.1
90°-120°	875.3	11.1
90°-150°	2958.5	37.5
90°-180°	4098.0	51.9
0°-180°	7893.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1678	1678	1678	1678	1678	
5°	1678	1671	1655	1666	1665	159
15°	1601	1584	1548	1541	1531	451
25°	1456	1421	1360	1332	1316	669
35°	1260	1209	1127	1070	1044	788
45°	1036	972	870	795	760	799
55°	787	717	604	528	498	705
65°	538	461	357	293	275	532
75°	284	219	144	131	128	303
85°	72	44	38	36	35	81
90°	1	13	28	32	35	8
95°	69	77	86	90	91	77
105°	261	264	274	274	276	280
115°	494	497	495	496	495	488
125°	723	726	724	719	715	644
135°	938	944	943	939	936	722
145°	1138	1140	1143	1142	1138	710
155°	1302	1303	1304	1308	1300	599
165°	1419	1415	1415	1421	1414	400
175°	1476	1471	1471	1477	1470	140
180°	1479	1479	1479	1479	1479	



TEST NUMBER: P332358

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2
2.5°	1683.6	1682.6	1681.7	1680.7	1679.7	1677.8	1674.9	1672.0	1669.1	1666.2	1668.8
5°	1678.2	1676.6	1675.1	1673.6	1672.1	1669.5	1665.9	1662.3	1658.7	1655.0	1657.7
7.5°	1662.6	1661.0	1659.4	1657.7	1656.1	1652.9	1648.2	1643.5	1638.8	1634.1	1635.6
10°	1649.6	1647.5	1645.3	1643.2	1641.1	1637.3	1631.9	1626.4	1621.0	1615.6	1615.9
12.5°	1631.1	1628.7	1626.4	1624.0	1621.6	1617.1	1610.5	1603.8	1597.2	1590.5	1590.3
15°	1600.6	1597.3	1593.9	1590.6	1587.3	1581.4	1572.9	1564.4	1556.0	1547.5	1546.0
17.5°	1562.2	1558.3	1554.5	1550.6	1546.7	1539.4	1528.6	1517.9	1507.1	1496.3	1493.1
20°	1533.9	1529.1	1524.2	1519.4	1514.5	1506.4	1494.9	1483.4	1471.9	1460.4	1456.5
22.5°	1502.3	1496.8	1491.2	1485.6	1480.1	1471.2	1458.9	1446.7	1434.5	1422.3	1417.4
25°	1456.3	1448.8	1441.2	1433.6	1426.1	1415.3	1401.4	1387.5	1373.6	1359.7	1353.3
27.5°	1400.5	1392.2	1383.8	1375.5	1367.1	1355.2	1339.7	1324.2	1308.7	1293.3	1284.4
30°	1362.4	1353.3	1344.3	1335.2	1326.1	1313.1	1296.2	1279.2	1262.3	1245.4	1235.1
32.5°	1324.3	1314.0	1303.7	1293.4	1283.2	1269.1	1251.2	1233.3	1215.3	1197.4	1186.2
35°	1260.3	1249.4	1238.5	1227.7	1216.8	1201.9	1183.2	1164.4	1145.7	1126.9	1113.9
37.5°	1195.5	1183.4	1171.3	1159.2	1147.1	1131.1	1111.1	1091.0	1071.0	1051.0	1036.2
40°	1154.2	1140.9	1127.5	1114.2	1100.9	1083.5	1062.1	1040.6	1019.1	997.6	981.9
42.5°	1107.3	1094.0	1080.7	1067.4	1054.1	1036.4	1014.2	992.0	969.8	947.6	930.4
45°	1035.8	1022.1	1008.5	994.9	981.3	962.9	939.6	916.3	893.0	869.7	852.5
47.5°	964.2	949.2	934.3	919.3	904.4	885.3	862.0	838.7	815.4	792.1	773.4
50°	911.9	897.7	883.5	869.3	855.0	835.7	811.2	786.7	762.2	737.7	718.9
52.5°	865.1	849.7	834.2	818.8	803.4	783.5	759.3	735.0	710.8	686.5	667.0
55°	786.7	771.9	757.0	742.2	727.4	707.1	681.4	655.7	630.0	604.3	586.8
57.5°	714.3	698.1	682.0	665.8	649.7	628.7	602.8	577.0	551.2	525.4	508.8
60°	664.2	647.6	630.9	614.3	597.6	576.8	551.7	526.6	501.5	476.4	460.0
62.5°	614.1	597.5	580.8	564.2	547.6	526.7	501.6	476.5	451.4	426.3	410.9
65°	537.6	521.0	504.3	487.7	471.1	451.0	427.4	403.8	380.2	356.6	341.8
67.5°	461.1	444.3	427.5	410.7	393.9	374.1	351.5	328.9	306.3	283.6	272.6
70°	411.0	394.7	378.4	362.0	345.7	327.0	305.8	284.6	263.4	242.3	231.7
72.5°	360.9	344.9	328.8	312.7	296.6	278.9	259.7	240.5	221.2	202.0	193.3
75°	284.5	269.9	255.4	240.9	226.4	210.8	194.2	177.5	160.9	144.3	141.2
77.5°	214.8	201.6	188.5	175.4	162.3	150.3	139.6	128.9	118.2	107.5	105.9
80°	170.1	157.7	145.3	132.9	120.5	111.2	104.8	98.4	92.1	85.7	84.8
82.5°	127.7	117.0	106.3	95.5	84.8	78.0	75.0	72.1	69.1	66.1	65.2
85°	72.1	65.5	58.8	52.2	45.5	41.7	40.8	39.9	39.0	38.1	37.5
87.5°	26.4	24.2	22.1	19.9	17.8	17.0	17.7	18.4	19.1	19.7	19.7
90°	1.2	3.7	6.3	8.9	11.5	14.5	17.8	21.2	24.5	27.9	28.9
92.5°	28.1	29.9	31.6	33.4	35.1	37.0	38.9	40.8	42.7	44.6	45.4
95°	68.6	70.4	72.2	74.0	75.8	77.7	79.8	81.8	83.9	86.0	87.0
97.5°	121.8	123.1	124.5	125.8	127.1	128.6	130.1	131.6	133.0	134.5	135.7
100°	158.0	159.6	161.1	162.7	164.2	165.6	166.9	168.2	169.5	170.8	171.6
102.5°	199.8	200.8	201.7	202.6	203.6	204.9	206.6	208.3	210.0	211.7	212.5
105°	261.4	261.9	262.5	263.0	263.5	264.9	267.2	269.6	271.9	274.2	274.2
107.5°	333.0	333.3	333.6	333.9	334.2	334.9	335.8	336.7	337.6	338.6	339.4
110°	377.6	378.1	378.6	379.2	379.7	380.2	380.7	381.2	381.7	382.3	383.3



TEST NUMBER: P332358

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	424.1	424.4	424.7	425.0	425.3	425.5	425.6	425.7	425.8	425.9	427.2
115°	493.8	494.6	495.3	496.1	496.9	497.0	496.5	496.0	495.5	495.0	495.2
117.5°	564.0	564.5	565.0	565.5	566.0	566.0	565.3	564.6	564.0	563.3	563.2
120°	607.7	609.2	610.8	612.3	613.9	614.0	612.7	611.4	610.1	608.8	608.6
122.5°	653.2	654.3	655.5	656.6	657.8	658.0	657.3	656.6	656.0	655.3	654.6
125°	722.7	723.5	724.2	725.0	725.8	725.9	725.4	724.9	724.4	723.9	722.8
127.5°	786.8	788.5	790.1	791.8	793.4	794.0	793.4	792.8	792.3	791.7	790.3
130°	829.6	831.6	833.7	835.8	837.8	838.5	837.7	836.9	836.2	835.4	834.4
132.5°	872.3	874.4	876.5	878.5	880.6	881.4	880.8	880.2	879.6	879.1	877.8
135°	937.6	939.2	940.7	942.3	943.8	944.5	944.2	944.0	943.7	943.4	942.4
137.5°	998.1	999.3	1000.6	1001.9	1003.2	1004.2	1004.9	1005.5	1006.2	1006.9	1005.8
140°	1039.9	1041.2	1042.5	1043.8	1045.0	1045.8	1046.1	1046.3	1046.6	1046.9	1046.6
142.5°	1078.0	1079.3	1080.6	1081.9	1083.2	1084.0	1084.5	1085.0	1085.4	1085.9	1085.6
145°	1137.5	1138.0	1138.5	1139.0	1139.5	1140.2	1141.0	1141.7	1142.5	1143.3	1143.0
147.5°	1189.5	1190.5	1191.4	1192.3	1193.3	1194.1	1194.8	1195.5	1196.2	1197.0	1197.0
150°	1225.8	1226.3	1226.8	1227.3	1227.9	1228.4	1228.9	1229.4	1229.9	1230.4	1230.4
152.5°	1255.5	1256.3	1257.0	1257.7	1258.4	1258.9	1259.2	1259.6	1259.9	1260.2	1260.6
155°	1302.5	1302.5	1302.5	1302.5	1302.5	1302.6	1302.9	1303.1	1303.4	1303.6	1304.7
157.5°	1342.4	1342.1	1341.8	1341.5	1341.2	1341.1	1341.4	1341.6	1341.8	1342.0	1343.1
160°	1367.5	1367.0	1366.5	1366.0	1365.5	1365.2	1365.2	1365.2	1365.2	1365.2	1366.5
162.5°	1389.8	1389.1	1388.4	1387.7	1387.0	1386.7	1386.9	1387.1	1387.3	1387.5	1388.8
165°	1418.7	1417.9	1417.1	1416.3	1415.6	1415.2	1415.2	1415.2	1415.2	1415.2	1416.7
167.5°	1441.7	1440.6	1439.6	1438.6	1437.5	1437.1	1437.3	1437.5	1437.7	1437.9	1439.5
170°	1454.7	1453.6	1452.6	1451.6	1450.5	1450.0	1450.0	1450.0	1450.0	1450.0	1451.8
172.5°	1464.9	1463.9	1462.8	1461.8	1460.8	1460.3	1460.3	1460.3	1460.3	1460.3	1461.9
175°	1475.6	1474.6	1473.5	1472.5	1471.5	1470.9	1470.9	1470.9	1470.9	1470.9	1472.5
177.5°	1480.0	1479.2	1478.4	1477.5	1476.7	1476.3	1476.3	1476.3	1476.3	1476.3	1477.5
180°	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1



TEST NUMBER: P332358

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2
2.5°	1671.5	1674.2	1676.8	1677.9	1677.4	1677.0	1676.5	1676.0
5°	1660.5	1663.2	1665.9	1667.0	1666.4	1665.8	1665.2	1664.6
7.5°	1637.1	1638.6	1640.1	1640.4	1639.3	1638.3	1637.3	1636.2
10°	1616.2	1616.5	1616.8	1616.2	1614.6	1613.1	1611.6	1610.1
12.5°	1590.1	1590.0	1589.8	1588.8	1587.1	1585.3	1583.6	1581.8
15°	1544.5	1543.0	1541.5	1539.6	1537.5	1535.4	1533.3	1531.2
17.5°	1489.9	1486.7	1483.5	1480.3	1477.2	1474.0	1470.9	1467.7
20°	1452.5	1448.6	1444.7	1440.9	1437.3	1433.6	1430.0	1426.4
22.5°	1412.5	1407.6	1402.7	1398.5	1395.2	1391.8	1388.4	1385.0
25°	1347.0	1340.6	1334.3	1329.4	1326.1	1322.8	1319.5	1316.1
27.5°	1275.6	1266.8	1257.9	1251.0	1245.9	1240.8	1235.7	1230.7
30°	1224.8	1214.5	1204.2	1196.7	1191.8	1187.0	1182.1	1177.3
32.5°	1174.9	1163.7	1152.4	1144.3	1139.2	1134.1	1129.0	1123.9
35°	1100.9	1087.9	1074.9	1065.7	1060.3	1054.8	1049.4	1043.9
37.5°	1021.5	1006.7	992.0	981.2	974.5	967.8	961.1	954.4
40°	966.2	950.5	934.7	923.4	916.4	909.5	902.5	895.6
42.5°	913.2	896.0	878.8	867.1	860.9	854.7	848.4	842.2
45°	835.2	818.0	800.7	788.5	781.2	774.0	766.7	759.5
47.5°	754.6	735.9	717.1	704.5	698.0	691.6	685.1	678.6
50°	700.2	681.4	662.7	649.8	642.9	635.9	629.0	622.0
52.5°	647.6	628.1	608.6	595.7	589.5	583.3	577.1	570.8
55°	569.2	551.7	534.1	522.3	516.3	510.2	504.2	498.1
57.5°	492.2	475.6	459.1	448.2	443.1	437.9	432.8	427.6
60°	443.7	427.4	411.0	400.3	395.2	390.0	384.9	379.7
62.5°	395.5	380.2	364.8	354.4	349.1	343.7	338.3	332.9
65°	327.0	312.1	297.3	288.2	284.9	281.6	278.3	274.9
67.5°	261.5	250.4	239.4	232.0	228.5	224.9	221.3	217.8
70°	221.1	210.5	199.9	193.0	189.6	186.3	183.0	179.7
72.5°	184.7	176.0	167.4	162.4	161.0	159.6	158.2	156.8
75°	138.2	135.2	132.2	130.4	129.8	129.1	128.5	127.9
77.5°	104.3	102.6	101.0	99.9	99.3	98.7	98.1	97.5
80°	83.9	83.0	82.1	81.4	80.8	80.2	79.5	78.9
82.5°	64.3	63.4	62.5	62.0	61.9	61.8	61.6	61.5
85°	36.9	36.3	35.7	35.4	35.4	35.4	35.4	35.4
87.5°	19.7	19.6	19.6	19.5	19.4	19.2	19.1	18.9
90°	30.0	31.0	32.0	32.8	33.3	33.8	34.3	34.9
92.5°	46.3	47.1	47.9	48.2	47.9	47.6	47.2	46.9
95°	88.0	89.1	90.1	90.6	90.6	90.6	90.6	90.6
97.5°	136.9	138.1	139.3	139.8	139.7	139.6	139.5	139.4
100°	172.3	173.1	173.9	174.5	175.1	175.6	176.1	176.6
102.5°	213.2	214.0	214.8	215.1	215.0	214.9	214.8	214.7
105°	274.2	274.2	274.2	274.5	275.0	275.5	276.0	276.5
107.5°	340.2	341.1	341.9	342.1	341.8	341.5	341.2	340.9
110°	384.3	385.4	386.4	386.6	386.1	385.6	385.1	384.6



TEST NUMBER: P332358

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	428.4	429.7	430.9	431.5	431.4	431.3	431.2	431.1
115°	495.5	495.7	496.0	496.0	495.7	495.5	495.2	495.0
117.5°	563.2	563.1	563.1	562.7	562.0	561.2	560.5	559.8
120°	608.3	608.1	607.8	607.4	606.9	606.4	605.9	605.3
122.5°	654.0	653.3	652.6	651.9	651.2	650.5	649.7	649.0
125°	721.8	720.8	719.7	718.7	717.7	716.6	715.6	714.6
127.5°	788.8	787.4	785.9	784.6	783.4	782.2	781.0	779.9
130°	833.3	832.3	831.3	829.8	828.0	826.2	824.4	822.6
132.5°	876.6	875.4	874.1	872.8	871.4	870.0	868.6	867.2
135°	941.4	940.3	939.3	938.5	938.0	937.5	937.0	936.5
137.5°	1004.7	1003.6	1002.5	1001.5	1000.5	999.6	998.6	997.6
140°	1046.3	1046.1	1045.8	1044.8	1043.0	1041.2	1039.4	1037.6
142.5°	1085.4	1085.1	1084.9	1084.0	1082.6	1081.2	1079.9	1078.5
145°	1142.8	1142.5	1142.3	1141.6	1140.6	1139.5	1138.5	1137.5
147.5°	1197.0	1197.0	1197.0	1196.2	1194.6	1193.1	1191.5	1190.0
150°	1230.4	1230.4	1230.4	1229.7	1228.1	1226.6	1225.0	1223.5
152.5°	1261.0	1261.4	1261.8	1261.4	1260.0	1258.7	1257.3	1256.0
155°	1305.7	1306.7	1307.8	1307.4	1305.6	1303.8	1302.0	1300.1
157.5°	1344.1	1345.2	1346.3	1346.1	1344.7	1343.2	1341.8	1340.3
160°	1367.8	1369.1	1370.4	1370.5	1369.5	1368.4	1367.4	1366.4
162.5°	1390.1	1391.4	1392.7	1392.5	1390.8	1389.2	1387.5	1385.9
165°	1418.3	1419.8	1421.4	1421.2	1419.4	1417.6	1415.8	1414.0
167.5°	1441.1	1442.7	1444.3	1444.3	1442.7	1441.1	1439.5	1437.9
170°	1453.6	1455.5	1457.3	1457.3	1455.5	1453.6	1451.8	1450.0
172.5°	1463.5	1465.1	1466.7	1466.6	1464.7	1462.9	1461.1	1459.3
175°	1474.0	1475.6	1477.1	1477.0	1475.2	1473.4	1471.6	1469.8
177.5°	1478.8	1480.0	1481.2	1481.1	1479.7	1478.2	1476.8	1475.4
180°	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1

(END OF REPORT)