

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831795

Luminaire Tested: S123RDIP-S1000D1195U835-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831795
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D1195U835-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9072.7 lumens
Efficiency: N/A
Efficacy: 137.3 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 66.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831795

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P831795

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47				47
1	98	94	90	87	90	87	84	81	73	71	69	60	59	57	49	48	47	41				41
2	90	83	77	72	83	77	72	68	65	61	58	54	51	49	44	42	41	36				36
3	83	74	67	61	76	68	62	58	58	54	50	48	45	43	40	37	36	32				32
4	76	66	58	53	70	61	55	50	52	47	43	44	40	37	36	34	32	28				28
5	70	59	52	46	64	55	48	43	47	42	38	40	36	33	33	30	28	25				25
6	65	53	46	40	60	50	43	38	43	38	34	36	32	29	30	28	25	22				22
7	60	49	41	36	56	45	39	34	39	34	30	33	30	27	28	25	23	20				20
8	56	44	37	32	52	42	35	30	36	31	27	31	27	24	26	23	21	19				19
9	53	41	34	29	49	38	32	28	33	28	25	29	25	22	24	21	19	17				17
10	49	38	31	26	46	35	29	25	31	26	23	27	23	20	23	20	18	16				16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	34929	34929	34929	34929	34929
5°	41474	40151	35149	28414	26379
10°	37576	40783	34974	22766	19530
15°	25872	34968	34604	18607	15450
20°	17999	26922	33909	15690	13580
25°	13715	20518	32898	13944	12514
30°	11939	16404	31635	12949	11593
35°	10962	13838	29843	12107	10751
40°	10002	12357	27500	11282	9983
45°	9033	11301	24972	10500	9216
50°	8199	10428	21990	9736	8266
55°	7416	9575	19125	8989	7092
60°	6646	8708	16613	8163	6702
65°	6133	7725	14301	7335	6337
70°	4982	6678	12478	6637	5149
75°	4371	5311	10568	5506	4537
80°	3961	4494	8660	4618	4289
85°	3619	3940	6570	4187	3940

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 26349 cd/sqm



TEST NUMBER: P831795

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	295.8	3.3
10°-20°	684.4	7.5
20°-30°	785.3	8.7
30°-40°	774.0	8.5
40°-50°	682.6	7.5
50°-60°	525.1	5.8
60°-70°	345.2	3.8
70°-80°	167.7	1.8
80°-90°	45.4	0.5
90°-100°	55.1	0.6
100°-110°	266.5	2.9
110°-120°	653.3	7.2
120°-130°	829.4	9.1
130°-140°	886.0	9.8
140°-150°	828.5	9.1
150°-160°	668.3	7.4
160°-170°	431.3	4.8
170°-180°	148.6	1.6
0°-30°	1765.5	19.5
0°-40°	2539.5	28.0
0°-60°	3747.2	41.3
0°-90°	4305.6	47.5
90°-120°	975.0	10.7
90°-150°	3518.9	38.8
90°-180°	4767.0	52.5
0°-180°	9072.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	3245	3245	3245	3245	3245	
5°	3838	3716	3253	2630	2441	351
15°	2322	3138	3105	1670	1386	655
25°	1155	1728	2770	1174	1054	545
35°	834	1053	2271	921	818	520
45°	593	742	1640	690	605	461
55°	395	510	1019	479	378	354
65°	241	303	562	288	249	236
75°	105	128	254	132	109	113
85°	29	32	53	34	32	31
90°	35	28	1	28	35	17
95°	44	36	71	36	44	37
105°	51	254	346	254	51	107
115°	683	667	650	667	683	643
125°	934	929	916	929	934	835
135°	1151	1151	1140	1151	1151	888
145°	1328	1326	1315	1326	1328	829
155°	1446	1448	1449	1448	1446	667
165°	1524	1523	1528	1523	1524	431
175°	1558	1559	1564	1559	1558	148
180°	1564	1564	1564	1564	1564	



TEST NUMBER: P831795

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0
2.5°	3596.3	3585.0	3573.6	3570.3	3567.0	3556.4	3545.7	3521.8	3497.8	3473.2	3448.6
5°	3838.4	3839.7	3841.1	3837.7	3834.4	3820.4	3806.5	3777.2	3747.9	3716.0	3684.1
7.5°	3763.9	3785.2	3806.5	3810.5	3814.5	3825.1	3835.8	3829.1	3822.4	3810.5	3798.5
10°	3437.9	3436.6	3435.3	3459.2	3483.2	3554.4	3625.5	3662.1	3698.7	3731.3	3763.9
12.5°	2905.8	2907.7	2909.7	2988.2	3066.7	3133.9	3201.1	3294.2	3387.4	3487.8	3588.3
15°	2321.7	2354.3	2386.9	2456.7	2526.6	2627.7	2728.8	2853.9	2978.9	3137.9	3296.9
17.5°	1906.6	1920.5	1934.5	2001.7	2068.9	2164.7	2260.5	2402.2	2543.9	2748.8	2953.6
20°	1571.3	1583.9	1596.6	1645.1	1693.7	1785.5	1877.3	2012.3	2147.4	2350.3	2553.2
22.5°	1311.8	1336.5	1361.1	1393.7	1426.3	1492.8	1559.3	1697.0	1834.7	2019.7	2204.6
25°	1154.8	1166.2	1177.5	1205.4	1233.3	1297.2	1361.1	1452.2	1543.3	1727.6	1911.9
27.5°	1048.4	1051.7	1055.1	1075.7	1096.3	1137.6	1178.8	1263.3	1347.8	1499.4	1651.1
30°	960.6	966.6	972.6	988.5	1004.5	1034.4	1064.4	1124.2	1184.1	1319.8	1455.5
32.5°	892.7	896.1	899.4	912.7	926.0	948.0	969.9	1017.1	1064.4	1168.2	1271.9
35°	834.2	834.9	835.5	845.5	855.5	876.8	898.1	937.3	976.6	1053.1	1129.6
37.5°	767.7	772.3	777.0	784.3	791.6	810.3	828.9	860.8	892.7	955.9	1019.1
40°	711.8	715.8	719.8	728.4	737.1	751.7	766.4	795.6	824.9	879.4	934.0
42.5°	655.9	658.6	661.2	669.9	678.5	696.5	714.5	737.7	761.0	806.3	851.5
45°	593.4	600.0	606.7	616.0	625.3	640.6	655.9	679.9	703.8	742.4	781.0
47.5°	541.5	544.8	548.2	556.1	564.1	582.7	601.4	622.7	643.9	679.9	715.8
50°	489.6	490.9	492.3	499.6	506.9	523.5	540.2	564.8	589.4	622.7	655.9
52.5°	440.4	443.7	447.0	454.4	461.7	473.0	484.3	509.6	534.8	567.4	600.0
55°	395.2	397.1	399.1	404.5	409.8	423.1	436.4	458.3	480.3	510.2	540.2
57.5°	352.6	355.2	357.9	361.9	365.9	377.9	389.8	409.1	428.4	458.3	488.3
60°	308.7	312.0	315.3	320.0	324.6	333.9	343.3	360.6	377.9	404.5	431.1
62.5°	276.7	277.4	278.1	282.1	286.1	292.7	299.4	313.3	327.3	353.9	380.5
65°	240.8	242.8	244.8	246.8	248.8	254.1	259.4	271.4	283.4	303.3	323.3
67.5°	203.6	205.6	207.6	210.9	214.2	218.9	223.5	231.5	239.5	258.1	276.7
70°	158.3	158.3	158.3	163.6	169.0	177.0	184.9	190.9	196.9	212.2	227.5
72.5°	129.1	129.7	130.4	131.1	131.7	136.4	141.0	151.0	161.0	170.3	179.6
75°	105.1	105.8	106.4	107.1	107.8	109.1	110.4	113.8	117.1	127.7	138.4
77.5°	83.8	84.5	85.2	85.8	86.5	87.8	89.1	90.5	91.8	95.8	99.8
80°	63.9	64.5	65.2	65.9	66.5	67.2	67.9	69.2	70.5	72.5	74.5
82.5°	46.6	46.6	46.6	46.6	46.6	47.9	49.2	49.2	49.2	50.6	51.9
85°	29.3	29.3	29.3	29.9	30.6	30.6	30.6	31.3	31.9	31.9	31.9
87.5°	13.3	12.6	12.0	12.6	13.3	13.3	13.3	14.0	14.6	14.6	14.6
90°	34.9	34.3	33.8	33.3	32.8	32.0	31.0	29.9	28.9	27.9	24.5
92.5°	39.5	39.2	39.0	38.7	38.5	37.4	35.6	33.8	32.0	30.2	27.9
95°	44.1	44.1	44.1	44.1	44.1	43.2	41.4	39.6	37.8	36.0	33.2
97.5°	47.6	47.4	47.1	46.9	46.6	45.4	43.4	41.3	39.2	37.2	50.3
100°	48.8	48.5	48.3	48.0	47.8	46.6	44.5	42.5	40.4	38.3	78.6
102.5°	50.0	49.4	48.9	48.4	47.9	51.9	60.4	68.9	77.5	86.0	130.9
105°	51.1	50.6	50.1	49.6	49.1	71.6	117.3	163.0	208.7	254.4	277.7
107.5°	120.8	154.6	188.5	222.3	256.1	292.9	332.7	372.4	412.2	451.9	448.1
110°	319.5	356.4	393.3	430.3	467.2	489.9	498.4	506.9	515.5	524.0	521.1



TEST NUMBER: P831795

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	605.3	605.8	606.3	606.9	607.4	606.5	604.1	601.8	599.5	597.2	594.3
115°	683.1	682.1	681.1	680.0	679.0	677.2	674.6	672.0	669.5	666.9	664.6
117.5°	745.9	745.6	745.4	745.1	744.8	743.7	741.6	739.6	737.5	735.4	734.1
120°	810.9	810.9	810.9	810.9	810.9	809.9	807.8	805.8	803.7	801.6	800.9
122.5°	874.8	874.6	874.3	874.1	873.8	873.0	871.7	870.5	869.2	867.9	866.8
125°	934.1	933.6	933.1	932.5	932.0	931.5	931.0	930.5	930.0	929.4	928.4
127.5°	992.2	992.7	993.2	993.7	994.3	994.1	993.3	992.6	991.8	991.0	989.7
130°	1048.0	1048.5	1049.0	1049.5	1050.0	1049.8	1048.7	1047.7	1046.7	1045.6	1044.6
132.5°	1099.1	1099.8	1100.6	1101.4	1102.2	1102.0	1101.0	1100.0	1098.9	1097.9	1097.1
135°	1151.4	1152.1	1152.9	1153.7	1154.5	1154.5	1153.7	1152.9	1152.1	1151.4	1150.3
137.5°	1201.3	1201.8	1202.3	1202.9	1203.4	1203.0	1201.7	1200.4	1199.1	1197.8	1197.3
140°	1245.5	1246.0	1246.5	1247.0	1247.5	1247.3	1246.2	1245.2	1244.2	1243.1	1242.4
142.5°	1286.1	1286.9	1287.7	1288.4	1289.2	1289.2	1288.4	1287.7	1286.9	1286.1	1285.3
145°	1327.9	1327.9	1327.9	1327.9	1327.9	1327.7	1327.2	1326.7	1326.1	1325.6	1325.1
147.5°	1358.2	1359.4	1360.7	1362.0	1363.3	1363.7	1363.2	1362.7	1362.2	1361.6	1361.1
150°	1393.0	1393.8	1394.6	1395.3	1396.1	1396.2	1395.7	1395.2	1394.7	1394.2	1393.7
152.5°	1420.9	1422.2	1423.5	1424.8	1426.1	1426.2	1425.2	1424.1	1423.1	1422.1	1421.8
155°	1446.5	1448.0	1449.6	1451.1	1452.6	1452.8	1451.5	1450.2	1448.9	1447.6	1447.4
157.5°	1468.5	1470.6	1472.7	1474.7	1476.8	1477.0	1475.5	1473.9	1472.4	1470.9	1471.1
160°	1489.4	1491.2	1493.1	1494.9	1496.7	1496.8	1495.2	1493.7	1492.2	1490.6	1490.9
162.5°	1509.2	1510.7	1512.3	1513.8	1515.4	1515.3	1513.5	1511.6	1509.8	1508.0	1508.3
165°	1524.3	1526.1	1527.9	1529.7	1531.5	1531.4	1529.3	1527.3	1525.2	1523.1	1523.4
167.5°	1535.9	1538.0	1540.0	1542.1	1544.2	1544.2	1542.1	1540.0	1538.0	1535.9	1535.9
170°	1546.4	1548.4	1550.5	1552.6	1554.6	1554.6	1552.6	1550.5	1548.4	1546.4	1546.4
172.5°	1552.2	1554.5	1556.8	1559.1	1561.5	1561.6	1559.5	1557.5	1555.4	1553.3	1553.1
175°	1558.0	1560.1	1562.1	1564.2	1566.2	1566.4	1564.6	1562.8	1561.0	1559.1	1558.9
177.5°	1559.1	1561.7	1564.3	1566.9	1569.5	1569.7	1567.7	1565.6	1563.5	1561.5	1561.2
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P831795

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0
2.5°	3445.3	3441.9	3410.0	3378.1	3346.8	3315.5	3292.3	3269.0	3229.7	3190.5	3165.9
5°	3658.8	3633.5	3583.0	3532.4	3456.6	3380.7	3316.9	3253.0	3171.8	3090.7	3022.8
7.5°	3777.9	3757.3	3696.1	3634.8	3534.4	3433.9	3334.2	3234.4	3114.6	2994.9	2892.4
10°	3781.2	3798.5	3747.9	3697.4	3584.3	3471.2	3335.5	3199.8	3038.8	2877.8	2745.4
12.5°	3662.8	3737.3	3726.7	3716.0	3600.9	3485.8	3320.9	3155.9	2958.3	2760.7	2595.1
15°	3441.3	3585.6	3628.2	3670.8	3575.6	3480.5	3292.9	3105.3	2873.2	2641.0	2450.7
17.5°	3155.9	3358.1	3470.5	3583.0	3513.8	3444.6	3239.0	3033.5	2772.0	2510.6	2303.7
20°	2817.9	3082.7	3259.0	3435.3	3410.0	3384.7	3172.5	2960.3	2678.2	2396.2	2172.0
22.5°	2484.0	2763.4	3006.9	3250.3	3276.3	3302.2	3088.0	2873.8	2565.1	2256.5	2028.3
25°	2195.9	2480.0	2770.0	3060.1	3118.6	3177.2	2973.6	2770.0	2450.1	2130.1	1903.2
27.5°	1921.2	2191.3	2510.6	2829.9	2936.4	3042.8	2856.5	2670.3	2337.0	2003.7	1777.5
30°	1697.0	1938.5	2264.5	2590.4	2738.8	2887.1	2716.2	2545.2	2214.6	1883.9	1662.4
32.5°	1488.1	1704.3	2031.6	2358.9	2531.2	2703.5	2555.8	2408.2	2090.2	1772.2	1553.3
35°	1323.2	1516.7	1822.1	2127.4	2320.3	2513.3	2392.2	2271.1	1960.5	1649.8	1442.9
37.5°	1181.5	1343.8	1630.5	1917.2	2122.1	2327.0	2225.9	2124.8	1832.7	1540.7	1345.1
40°	1064.4	1194.8	1461.5	1728.3	1929.2	2130.1	2043.6	1957.1	1695.7	1434.2	1251.3
42.5°	963.9	1076.4	1315.8	1555.3	1739.6	1923.9	1866.7	1809.4	1572.6	1335.8	1166.2
45°	875.5	969.9	1180.8	1391.7	1561.3	1730.9	1685.7	1640.5	1436.2	1232.0	1076.4
47.5°	797.0	878.1	1066.4	1254.6	1407.0	1559.3	1517.4	1475.5	1306.5	1137.6	995.9
50°	725.1	794.3	951.3	1108.3	1245.3	1382.4	1347.8	1313.2	1173.5	1033.8	911.4
52.5°	657.3	714.5	855.5	996.5	1107.0	1217.4	1190.8	1164.2	1056.4	948.6	837.5
55°	592.7	645.3	764.4	883.4	977.9	1072.4	1045.8	1019.1	935.3	851.5	753.7
57.5°	534.2	580.1	676.5	773.0	848.2	923.3	910.7	898.1	828.2	758.4	677.9
60°	472.3	513.6	596.7	679.9	740.4	800.9	786.3	771.7	721.8	671.9	602.7
62.5°	417.1	453.7	520.2	586.7	636.0	685.2	674.5	663.9	626.0	588.1	530.9
65°	359.2	395.2	449.0	502.9	541.5	580.1	570.8	561.5	532.9	504.2	458.3
67.5°	306.7	336.6	383.2	429.7	455.7	481.6	476.3	471.0	449.0	427.1	391.2
70°	253.5	279.4	318.0	356.6	374.5	392.5	394.5	396.5	376.5	356.6	330.0
72.5°	200.2	220.9	256.8	292.7	306.7	320.6	320.0	319.3	307.3	295.4	271.4
75°	153.7	169.0	196.9	224.8	236.8	248.8	251.5	254.1	242.8	231.5	218.2
77.5°	110.4	121.1	142.4	163.6	177.0	190.3	191.6	192.9	187.6	182.3	169.6
80°	77.8	81.2	94.5	107.8	121.7	135.7	137.7	139.7	134.4	129.1	121.1
82.5°	53.9	55.9	60.5	65.2	76.5	87.8	90.5	93.1	90.5	87.8	79.2
85°	32.6	33.3	35.3	37.3	42.6	47.9	50.6	53.2	51.9	50.6	45.9
87.5°	14.6	14.6	15.3	16.0	17.3	18.6	22.0	25.3	23.3	21.3	19.3
90°	21.2	17.8	14.5	11.5	8.9	6.3	3.7	1.2	3.7	6.3	8.9
92.5°	25.6	23.2	20.9	20.5	22.1	23.6	25.2	26.7	25.2	23.6	22.1
95°	30.3	27.5	24.7	28.5	39.1	49.7	60.3	70.9	60.3	49.7	39.1
97.5°	63.5	76.7	89.8	100.0	107.3	114.5	121.7	129.0	121.7	114.5	107.3
100°	118.9	159.2	199.4	217.0	211.8	206.7	201.5	196.3	201.5	206.7	211.8
102.5°	175.8	220.7	265.7	286.5	283.1	279.7	276.4	273.0	276.4	279.7	283.1
105°	300.9	324.1	347.4	357.6	354.7	351.9	349.1	346.2	349.1	351.9	354.7
107.5°	444.2	440.3	436.5	433.4	431.0	428.7	426.4	424.1	426.4	428.7	431.0
110°	518.3	515.5	512.6	510.2	508.1	506.0	504.0	501.9	504.0	506.0	508.1



TEST NUMBER: P831795

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	591.5	588.7	585.8	583.5	581.7	579.9	578.1	576.3	578.1	579.9	581.7
115°	662.2	659.9	657.6	655.6	654.1	652.5	651.0	649.5	651.0	652.5	654.1
117.5°	732.8	731.6	730.3	728.7	726.9	725.1	723.3	721.5	723.3	725.1	726.9
120°	800.1	799.3	798.6	797.0	794.7	792.4	790.0	787.7	790.0	792.4	794.7
122.5°	865.8	864.8	863.7	862.3	860.5	858.7	856.9	855.1	856.9	858.7	860.5
125°	927.4	926.3	925.3	923.8	921.7	919.6	917.6	915.5	917.6	919.6	921.7
127.5°	988.4	987.2	985.9	984.2	982.1	980.1	978.0	975.9	978.0	980.1	982.1
130°	1043.6	1042.5	1041.5	1039.9	1037.9	1035.8	1033.8	1031.7	1033.8	1035.8	1037.9
132.5°	1096.4	1095.6	1094.8	1093.4	1091.3	1089.3	1087.2	1085.1	1087.2	1089.3	1091.3
135°	1149.3	1148.3	1147.2	1145.9	1144.4	1142.8	1141.3	1139.7	1141.3	1142.8	1144.4
137.5°	1196.8	1196.3	1195.8	1194.5	1192.4	1190.3	1188.3	1186.2	1188.3	1190.3	1192.4
140°	1241.6	1240.8	1240.0	1238.9	1237.3	1235.8	1234.2	1232.7	1234.2	1235.8	1237.3
142.5°	1284.6	1283.8	1283.0	1281.9	1280.3	1278.8	1277.2	1275.7	1277.2	1278.8	1280.3
145°	1324.6	1324.1	1323.6	1322.4	1320.6	1318.8	1317.0	1315.2	1317.0	1318.8	1320.6
147.5°	1360.6	1360.1	1359.6	1358.7	1357.4	1356.1	1354.8	1353.5	1354.8	1356.1	1357.4
150°	1393.1	1392.6	1392.1	1391.5	1390.7	1389.9	1389.1	1388.4	1389.1	1389.9	1390.7
152.5°	1421.5	1421.3	1421.0	1420.8	1420.5	1420.2	1420.0	1419.7	1420.0	1420.2	1420.5
155°	1447.1	1446.8	1446.6	1446.7	1447.2	1447.7	1448.3	1448.8	1448.3	1447.7	1447.2
157.5°	1471.4	1471.6	1471.9	1472.0	1472.0	1472.0	1472.0	1472.0	1472.0	1472.0	1472.0
160°	1491.1	1491.4	1491.6	1491.9	1492.2	1492.4	1492.7	1492.9	1492.7	1492.4	1492.2
162.5°	1508.5	1508.8	1509.1	1509.6	1510.4	1511.1	1511.9	1512.7	1511.9	1511.1	1510.4
165°	1523.6	1523.9	1524.2	1524.7	1525.5	1526.2	1527.0	1527.8	1527.0	1526.2	1525.5
167.5°	1535.9	1535.9	1535.9	1536.4	1537.5	1538.5	1539.5	1540.6	1539.5	1538.5	1537.5
170°	1546.4	1546.4	1546.4	1546.9	1547.9	1549.0	1550.0	1551.0	1550.0	1549.0	1547.9
172.5°	1552.8	1552.6	1552.3	1552.8	1554.1	1555.4	1556.7	1558.0	1556.7	1555.4	1554.1
175°	1558.6	1558.4	1558.1	1558.6	1559.9	1561.2	1562.5	1563.8	1562.5	1561.2	1559.9
177.5°	1561.0	1560.7	1560.4	1561.0	1562.2	1563.5	1564.8	1566.1	1564.8	1563.5	1562.2
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P831795

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0	3245.0
2.5°	3141.2	3103.3	3065.4	3038.1	3010.9	2976.9	2943.0	2941.7	2940.3	2915.1	2889.8
5°	2955.0	2889.1	2823.3	2758.7	2694.2	2629.7	2565.1	2550.5	2535.9	2513.9	2492.0
7.5°	2790.0	2684.9	2579.8	2497.3	2414.8	2350.3	2285.8	2241.8	2197.9	2164.0	2130.1
10°	2613.0	2482.7	2352.3	2252.5	2152.7	2082.9	2013.0	1962.4	1911.9	1887.9	1864.0
12.5°	2429.4	2287.7	2146.1	2048.3	1950.5	1866.7	1782.8	1736.9	1691.0	1657.8	1624.5
15°	2260.5	2108.1	1955.8	1852.0	1748.2	1669.7	1591.2	1545.3	1499.4	1466.2	1432.9
17.5°	2096.8	1943.2	1789.5	1684.4	1579.3	1508.1	1436.9	1392.3	1347.8	1327.1	1306.5
20°	1947.8	1792.8	1637.8	1538.7	1439.6	1369.7	1299.9	1275.9	1252.0	1232.7	1213.4
22.5°	1800.1	1651.1	1502.1	1407.0	1311.8	1261.3	1210.7	1191.4	1172.1	1157.5	1142.9
25°	1676.4	1528.0	1379.7	1296.5	1213.4	1174.1	1134.9	1122.3	1109.6	1095.0	1080.3
27.5°	1551.3	1410.3	1269.3	1202.7	1136.2	1104.3	1072.4	1056.4	1040.4	1028.5	1016.5
30°	1440.9	1310.5	1180.1	1124.9	1069.7	1041.8	1013.8	996.5	979.2	967.9	956.6
32.5°	1334.5	1218.7	1103.0	1055.7	1008.5	981.2	953.9	937.3	920.7	907.4	894.1
35°	1236.0	1135.6	1035.1	991.9	948.6	921.4	894.1	877.4	860.8	847.5	834.2
37.5°	1149.5	1058.4	967.3	926.7	886.1	862.1	838.2	820.9	803.6	789.6	775.7
40°	1068.4	987.9	907.4	868.1	828.9	802.9	777.0	761.7	746.4	733.8	721.1
42.5°	996.5	922.7	848.8	810.3	771.7	747.1	722.4	704.5	686.5	679.2	671.9
45°	920.7	855.5	790.3	753.0	715.8	689.8	663.9	648.6	633.3	626.7	620.0
47.5°	854.2	793.6	733.1	696.5	659.9	636.6	613.3	601.4	589.4	580.1	570.8
50°	789.0	730.4	671.9	636.6	601.4	581.4	561.5	546.8	532.2	525.5	518.9
52.5°	726.4	673.2	620.0	584.1	548.2	528.9	509.6	496.9	484.3	470.3	456.4
55°	655.9	609.4	562.8	530.9	498.9	479.0	459.0	444.4	429.7	415.1	400.5
57.5°	597.4	551.5	505.6	477.0	448.4	429.1	409.8	393.8	377.9	365.9	353.9
60°	533.5	493.6	453.7	425.8	397.8	379.2	360.6	345.3	330.0	324.0	318.0
62.5°	473.6	436.4	399.1	374.5	349.9	332.0	314.0	304.0	294.0	290.0	286.1
65°	412.4	380.5	348.6	326.0	303.3	288.0	272.7	268.1	263.4	260.1	256.8
67.5°	355.2	328.0	300.7	280.7	260.8	250.1	239.5	234.2	228.8	224.8	220.9
70°	303.3	279.4	255.5	238.2	220.9	210.9	200.9	196.2	191.6	184.3	177.0
72.5°	247.5	228.8	210.2	196.9	183.6	175.0	166.3	157.0	147.7	141.0	134.4
75°	204.9	186.3	167.6	155.0	142.4	132.4	122.4	119.1	115.8	113.8	111.8
77.5°	157.0	141.0	125.1	115.1	105.1	100.5	95.8	93.8	91.8	91.1	90.5
80°	113.1	99.8	86.5	81.2	75.8	74.5	73.2	71.8	70.5	69.8	69.2
82.5°	70.5	63.9	57.2	55.9	54.5	53.9	53.2	52.6	51.9	51.2	50.6
85°	41.2	38.6	35.9	35.3	34.6	33.9	33.3	33.3	33.3	33.3	33.3
87.5°	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3	16.6	16.0
90°	11.5	14.5	17.8	21.2	24.5	27.9	28.9	29.9	31.0	32.0	32.8
92.5°	20.5	20.9	23.2	25.6	27.9	30.2	32.0	33.8	35.6	37.4	38.5
95°	28.5	24.7	27.5	30.3	33.2	36.0	37.8	39.6	41.4	43.2	44.1
97.5°	100.0	89.8	76.7	63.5	50.3	37.2	39.2	41.3	43.4	45.4	46.6
100°	217.0	199.4	159.2	118.9	78.6	38.3	40.4	42.5	44.5	46.6	47.8
102.5°	286.5	265.7	220.7	175.8	130.9	86.0	77.5	68.9	60.4	51.9	47.9
105°	357.6	347.4	324.1	300.9	277.7	254.4	208.7	163.0	117.3	71.6	49.1
107.5°	433.4	436.5	440.3	444.2	448.1	451.9	412.2	372.4	332.7	292.9	256.1
110°	510.2	512.6	515.5	518.3	521.1	524.0	515.5	506.9	498.4	489.9	467.2



TEST NUMBER: P831795

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	583.5	585.8	588.7	591.5	594.3	597.2	599.5	601.8	604.1	606.5	607.4
115°	655.6	657.6	659.9	662.2	664.6	666.9	669.5	672.0	674.6	677.2	679.0
117.5°	728.7	730.3	731.6	732.8	734.1	735.4	737.5	739.6	741.6	743.7	744.8
120°	797.0	798.6	799.3	800.1	800.9	801.6	803.7	805.8	807.8	809.9	810.9
122.5°	862.3	863.7	864.8	865.8	866.8	867.9	869.2	870.5	871.7	873.0	873.8
125°	923.8	925.3	926.3	927.4	928.4	929.4	930.0	930.5	931.0	931.5	932.0
127.5°	984.2	985.9	987.2	988.4	989.7	991.0	991.8	992.6	993.3	994.1	994.3
130°	1039.9	1041.5	1042.5	1043.6	1044.6	1045.6	1046.7	1047.7	1048.7	1049.8	1050.0
132.5°	1093.4	1094.8	1095.6	1096.4	1097.1	1097.9	1098.9	1100.0	1101.0	1102.0	1102.2
135°	1145.9	1147.2	1148.3	1149.3	1150.3	1151.4	1152.1	1152.9	1153.7	1154.5	1154.5
137.5°	1194.5	1195.8	1196.3	1196.8	1197.3	1197.8	1199.1	1200.4	1201.7	1203.0	1203.4
140°	1238.9	1240.0	1240.8	1241.6	1242.4	1243.1	1244.2	1245.2	1246.2	1247.3	1247.5
142.5°	1281.9	1283.0	1283.8	1284.6	1285.3	1286.1	1286.9	1287.7	1288.4	1289.2	1289.2
145°	1322.4	1323.6	1324.1	1324.6	1325.1	1325.6	1326.1	1326.7	1327.2	1327.7	1327.9
147.5°	1358.7	1359.6	1360.1	1360.6	1361.1	1361.6	1362.2	1362.7	1363.2	1363.7	1363.3
150°	1391.5	1392.1	1392.6	1393.1	1393.7	1394.2	1394.7	1395.2	1395.7	1396.2	1396.1
152.5°	1420.8	1421.0	1421.3	1421.5	1421.8	1422.1	1423.1	1424.1	1425.2	1426.2	1426.1
155°	1446.7	1446.6	1446.8	1447.1	1447.4	1447.6	1448.9	1450.2	1451.5	1452.8	1452.6
157.5°	1472.0	1471.9	1471.6	1471.4	1471.1	1470.9	1472.4	1473.9	1475.5	1477.0	1476.8
160°	1491.9	1491.6	1491.4	1491.1	1490.9	1490.6	1492.2	1493.7	1495.2	1496.8	1496.7
162.5°	1509.6	1509.1	1508.8	1508.5	1508.3	1508.0	1509.8	1511.6	1513.5	1515.3	1515.4
165°	1524.7	1524.2	1523.9	1523.6	1523.4	1523.1	1525.2	1527.3	1529.3	1531.4	1531.5
167.5°	1536.4	1535.9	1535.9	1535.9	1535.9	1535.9	1538.0	1540.0	1542.1	1544.2	1544.2
170°	1546.9	1546.4	1546.4	1546.4	1546.4	1546.4	1548.4	1550.5	1552.6	1554.6	1554.6
172.5°	1552.8	1552.3	1552.6	1552.8	1553.1	1553.3	1555.4	1557.5	1559.5	1561.6	1561.5
175°	1558.6	1558.1	1558.4	1558.6	1558.9	1559.1	1561.0	1562.8	1564.6	1566.4	1566.2
177.5°	1561.0	1560.4	1560.7	1561.0	1561.2	1561.5	1563.5	1565.6	1567.7	1569.7	1569.5
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P831795

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	3245.0	3245.0	3245.0	3245.0
2.5°	2883.1	2876.5	2873.8	2871.2
5°	2471.4	2450.7	2446.1	2441.4
7.5°	2121.4	2112.8	2084.2	2055.6
10°	1837.4	1810.8	1798.8	1786.8
12.5°	1599.9	1575.3	1571.3	1567.3
15°	1415.6	1398.3	1392.3	1386.4
17.5°	1294.5	1282.6	1275.3	1267.9
20°	1204.7	1196.1	1190.8	1185.5
22.5°	1136.2	1129.6	1125.6	1121.6
25°	1070.4	1060.4	1057.1	1053.7
27.5°	1007.8	999.2	995.9	992.5
30°	949.3	942.0	937.3	932.7
32.5°	885.4	876.8	874.1	871.5
35°	828.9	823.6	820.9	818.2
37.5°	769.0	762.4	758.4	754.4
40°	717.8	714.5	712.5	710.5
42.5°	665.9	659.9	659.2	658.6
45°	614.0	608.0	606.7	605.4
47.5°	565.5	560.1	559.5	558.8
50°	511.6	504.2	498.9	493.6
52.5°	449.7	443.0	438.4	433.7
55°	393.2	385.8	381.8	377.9
57.5°	350.6	347.3	345.3	343.3
60°	316.0	314.0	312.7	311.3
62.5°	284.1	282.1	282.1	282.1
65°	254.8	252.8	250.8	248.8
67.5°	216.9	212.9	212.2	211.5
70°	171.0	165.0	164.3	163.6
72.5°	133.7	133.0	131.7	130.4
75°	110.4	109.1	109.1	109.1
77.5°	89.1	87.8	87.8	87.8
80°	68.5	67.9	68.5	69.2
82.5°	50.6	50.6	49.9	49.2
85°	32.6	31.9	31.9	31.9
87.5°	16.0	16.0	16.0	16.0
90°	33.3	33.8	34.3	34.9
92.5°	38.7	39.0	39.2	39.5
95°	44.1	44.1	44.1	44.1
97.5°	46.9	47.1	47.4	47.6
100°	48.0	48.3	48.5	48.8
102.5°	48.4	48.9	49.4	50.0
105°	49.6	50.1	50.6	51.1
107.5°	222.3	188.5	154.6	120.8
110°	430.3	393.3	356.4	319.5



TEST NUMBER: P831795

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	606.9	606.3	605.8	605.3
115°	680.0	681.1	682.1	683.1
117.5°	745.1	745.4	745.6	745.9
120°	810.9	810.9	810.9	810.9
122.5°	874.1	874.3	874.6	874.8
125°	932.5	933.1	933.6	934.1
127.5°	993.7	993.2	992.7	992.2
130°	1049.5	1049.0	1048.5	1048.0
132.5°	1101.4	1100.6	1099.8	1099.1
135°	1153.7	1152.9	1152.1	1151.4
137.5°	1202.9	1202.3	1201.8	1201.3
140°	1247.0	1246.5	1246.0	1245.5
142.5°	1288.4	1287.7	1286.9	1286.1
145°	1327.9	1327.9	1327.9	1327.9
147.5°	1362.0	1360.7	1359.4	1358.2
150°	1395.3	1394.6	1393.8	1393.0
152.5°	1424.8	1423.5	1422.2	1420.9
155°	1451.1	1449.6	1448.0	1446.5
157.5°	1474.7	1472.7	1470.6	1468.5
160°	1494.9	1493.1	1491.2	1489.4
162.5°	1513.8	1512.3	1510.7	1509.2
165°	1529.7	1527.9	1526.1	1524.3
167.5°	1542.1	1540.0	1538.0	1535.9
170°	1552.6	1550.5	1548.4	1546.4
172.5°	1559.1	1556.8	1554.5	1552.2
175°	1564.2	1562.1	1560.1	1558.0
177.5°	1566.9	1564.3	1561.7	1559.1
180°	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P831795

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.85	13.64	13.84	14.63	15.94	17.51	18.30	18.50	19.29	20.61
	3H	14.06	14.77	15.07	15.77	17.11	19.01	19.71	20.01	20.72	22.05
	4H	14.44	15.11	15.46	16.12	17.46	19.49	20.16	20.51	21.17	22.51
	6H	14.72	15.34	15.75	16.35	17.70	19.80	20.42	20.83	21.43	22.78
	8H	14.81	15.39	15.84	16.42	17.77	19.88	20.46	20.91	21.49	22.84
	12H	14.86	15.41	15.89	16.44	17.81	19.91	20.47	20.95	21.49	22.86
4H	2H	13.56	14.23	14.58	15.24	16.58	17.50	18.17	18.52	19.17	20.52
	3H	14.93	15.48	15.96	16.52	17.87	19.16	19.71	20.18	20.74	22.10
	4H	15.38	15.89	16.42	16.92	18.29	19.76	20.27	20.79	21.29	22.67
	6H	15.75	16.18	16.79	17.23	18.61	20.20	20.63	21.24	21.68	23.05
	8H	15.87	16.28	16.92	17.32	18.71	20.33	20.73	21.37	21.77	23.16
	12H	15.95	16.31	17.01	17.37	18.76	20.39	20.75	21.45	21.81	23.20
8H	4H	15.70	16.10	16.74	17.14	18.53	19.72	20.13	20.77	21.17	22.56
	6H	16.16	16.49	17.23	17.58	18.96	20.22	20.55	21.29	21.64	23.02
	8H	16.35	16.64	17.43	17.71	19.12	20.41	20.70	21.48	21.77	23.17
	12H	16.49	16.75	17.57	17.81	19.26	20.52	20.78	21.60	21.84	23.29
12H	4H	15.70	16.07	16.77	17.13	18.52	19.67	20.04	20.74	21.10	22.49
	6H	16.22	16.51	17.29	17.58	18.98	20.19	20.49	21.27	21.56	22.96
	8H	16.43	16.69	17.51	17.76	19.20	20.39	20.64	21.46	21.71	23.15