

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331999-830

Luminaire Tested: **S123DIP-S775D1195U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331999-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S775D1195U830-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7060.9 lumens  
Efficiency: N/A  
Efficacy: 124.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331999-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331999-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42																				
1	96	92	88	84	88	84	81	78	69	67	65	56	54	53	43	42	41	36																				
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35	30																				
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	34	31	30	25																				
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	28	25	22																				
5	67	55	47	41	61	51	44	38	42	37	33	34	31	27	27	24	22	19																				
6	62	50	42	36	56	46	39	33	38	33	29	31	27	24	25	22	19	16																				
7	57	45	37	31	52	41	34	29	35	29	25	28	24	21	22	19	17	15																				
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	21	18	15	13																				
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12																				
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	18	15	13	11																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12355	12355	12355
5°	12413	12241	12327
10°	12329	12136	12211
15°	12186	11999	12021
20°	12016	11802	11813
25°	11792	11569	11545
30°	11543	11309	11225
35°	11284	11037	10893
40°	11011	10732	10568
45°	10712	10456	10201
50°	10412	10114	9833
55°	10021	9760	9466
60°	9623	9347	9052
65°	9276	8899	8621
70°	8759	8387	8013
75°	8006	7719	7390
80°	7221	6912	6856
85°	6336	6101	5854



TEST NUMBER: P331999-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.1	1.5
10°-20°	305.3	4.3
20°-30°	451.0	6.4
30°-40°	526.8	7.5
40°-50°	529.6	7.5
50°-60°	465.2	6.6
60°-70°	346.6	4.9
70°-80°	197.5	2.8
80°-90°	60.9	0.9
90°-100°	301.1	4.3
100°-110°	852.5	12.1
110°-120°	838.6	11.9
120°-130°	668.9	9.5
130°-140°	527.4	7.5
140°-150°	393.6	5.6
150°-160°	274.4	3.9
160°-170°	161.2	2.3
170°-180°	52.4	0.7
0°-30°	864.4	12.2
0°-40°	1391.1	19.7
0°-60°	2385.9	33.8
0°-90°	2990.8	42.4
90°-120°	1992.1	28.2
90°-150°	3582.0	50.7
90°-180°	4070.0	57.6
0°-180°	7060.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1148	1148	1148	1148	1148	
5°	1149	1143	1133	1142	1141	109
15°	1094	1089	1077	1084	1079	308
25°	993	987	974	975	972	457
35°	859	852	840	834	829	537
45°	704	699	687	675	670	543
55°	534	532	520	510	504	478
65°	364	359	349	342	338	359
75°	192	189	186	181	178	206
85°	51	50	49	48	47	56
90°	2	13	27	31	32	5
95°	37	121	649	190	127	40
105°	127	188	880	1540	1393	135
115°	224	280	673	1477	1694	222
125°	312	368	629	1139	1336	277
135°	366	436	620	938	1083	283
145°	417	478	612	769	846	261
155°	474	511	592	673	702	218
165°	518	533	567	602	612	146
175°	540	540	544	552	551	51
180°	541	541	541	541	541	



TEST NUMBER: P331999-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8
2.5°	1151.7	1151.0	1150.4	1149.6	1149.0	1147.6	1145.7	1143.8	1141.8	1139.9	1141.6
5°	1148.8	1147.6	1146.6	1145.5	1144.3	1142.6	1140.2	1137.8	1135.4	1132.9	1135.2
7.5°	1137.6	1136.4	1135.3	1134.3	1133.1	1131.3	1128.8	1126.3	1123.8	1121.3	1123.3
10°	1128.0	1126.9	1125.9	1124.7	1123.7	1121.7	1118.8	1116.0	1113.1	1110.3	1112.3
12.5°	1115.4	1114.5	1113.6	1112.7	1111.7	1109.9	1107.3	1104.6	1101.9	1099.2	1100.7
15°	1093.5	1092.6	1091.7	1090.9	1090.0	1088.2	1085.2	1082.4	1079.6	1076.8	1078.5
17.5°	1068.0	1066.9	1065.7	1064.6	1063.5	1061.5	1058.7	1055.7	1052.9	1050.1	1051.3
20°	1049.0	1047.7	1046.5	1045.2	1043.9	1041.7	1038.9	1036.0	1033.2	1030.3	1031.2
22.5°	1027.7	1026.4	1025.1	1023.8	1022.5	1020.4	1017.6	1014.7	1011.9	1009.0	1009.7
25°	992.9	991.6	990.2	988.9	987.6	985.5	982.6	979.8	976.9	974.1	974.3
27.5°	955.5	954.2	953.0	951.7	950.5	948.3	945.2	942.2	939.1	935.9	936.1
30°	928.7	927.6	926.5	925.4	924.3	922.2	919.2	916.1	913.0	909.9	909.9
32.5°	901.8	900.4	898.9	897.5	896.1	894.2	891.7	889.4	887.0	884.7	883.4
35°	858.7	857.3	856.0	854.7	853.4	851.3	848.4	845.6	842.7	839.9	838.6
37.5°	814.4	812.8	811.1	809.4	807.8	805.5	802.6	799.7	796.7	793.9	792.3
40°	783.6	782.3	781.0	779.7	778.4	776.2	773.1	770.1	766.9	763.8	762.1
42.5°	752.8	751.3	749.8	748.4	746.9	744.6	741.5	738.4	735.4	732.3	730.6
45°	703.7	702.8	701.9	701.1	700.1	698.3	695.4	692.6	689.8	686.9	684.3
47.5°	654.9	653.7	652.3	651.1	649.8	647.8	645.2	642.5	639.8	637.2	634.5
50°	621.8	620.7	619.5	618.5	617.4	615.4	612.6	609.7	606.8	604.0	601.6
52.5°	587.0	586.3	585.5	584.8	584.0	582.1	579.1	576.1	573.1	570.0	568.0
55°	534.0	533.7	533.5	533.3	533.0	531.5	528.7	525.8	522.9	520.1	517.7
57.5°	483.4	482.7	481.9	481.2	480.4	478.9	476.6	474.3	472.0	469.8	467.6
60°	447.0	446.9	446.7	446.4	446.2	444.8	442.1	439.5	436.9	434.2	432.3
62.5°	414.7	414.2	413.6	413.0	412.5	410.9	408.2	405.6	402.9	400.3	398.3
65°	364.2	363.1	361.9	360.9	359.8	358.2	355.9	353.7	351.6	349.4	347.6
67.5°	310.7	309.7	308.8	307.7	306.8	305.5	303.9	302.2	300.5	298.9	297.3
70°	278.3	277.0	275.7	274.4	273.1	271.7	270.4	269.1	267.8	266.5	264.9
72.5°	244.4	243.4	242.4	241.5	240.5	239.3	237.8	236.3	234.8	233.3	232.0
75°	192.5	191.5	190.7	189.8	189.0	188.1	187.5	186.8	186.2	185.6	184.5
77.5°	146.5	146.0	145.5	145.1	144.5	143.9	143.1	142.3	141.6	140.7	140.0
80°	116.5	115.8	115.2	114.5	113.9	113.3	112.8	112.4	112.0	111.5	111.3
82.5°	87.3	87.1	87.0	86.8	86.7	86.6	86.5	86.4	86.3	86.2	85.9
85°	51.3	50.9	50.4	50.0	49.6	49.4	49.4	49.4	49.4	49.4	48.9
87.5°	20.9	20.9	20.8	20.9	20.8	20.9	21.4	21.9	22.3	22.8	22.4
90°	2.2	4.3	6.6	9.9	12.1	14.2	17.5	20.8	24.1	27.3	26.3
92.5°	13.6	20.2	29.3	37.9	47.1	63.3	92.0	139.1	185.3	168.4	127.1
95°	37.2	40.5	52.6	71.2	99.6	142.3	235.4	398.6	578.2	649.4	526.7
97.5°	63.5	64.6	74.0	90.2	118.3	164.5	253.4	437.3	736.8	1006.4	1076.7
100°	81.1	82.1	89.8	105.1	131.4	174.1	250.8	412.8	700.9	1037.1	1252.8
102.5°	99.4	101.4	108.2	122.6	146.3	185.5	254.3	391.8	648.3	980.1	1261.5
105°	127.1	130.4	136.9	150.1	170.8	204.8	263.9	376.7	583.7	880.4	1194.8
107.5°	156.4	159.7	166.0	178.9	198.4	230.0	281.9	375.6	542.5	792.4	1077.8
110°	177.4	180.7	186.2	198.2	216.8	247.5	296.8	380.0	526.7	742.4	1004.2



TEST NUMBER: P331999-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	196.7	200.0	205.5	217.4	236.1	265.9	311.7	388.8	518.0	709.2	940.3
115°	224.5	228.8	235.4	246.4	265.0	294.5	336.2	403.0	514.7	673.4	862.9
117.5°	252.3	257.3	262.8	272.9	293.7	321.1	362.2	421.8	516.7	652.4	816.2
120°	271.5	274.8	280.3	291.3	312.1	339.5	378.9	435.8	520.2	642.8	791.7
122.5°	288.2	291.5	297.0	308.8	328.8	357.9	396.4	449.0	526.3	636.7	771.6
125°	312.1	314.3	320.8	332.9	353.7	383.2	421.6	469.8	535.5	628.6	745.7
127.5°	330.3	333.6	341.7	353.9	376.9	406.5	443.5	486.9	546.0	624.6	723.0
130°	341.7	345.0	354.8	368.0	391.0	420.5	456.7	498.2	553.0	622.0	710.7
132.5°	350.4	354.6	365.3	381.1	404.1	432.8	468.1	508.8	558.3	621.1	699.4
135°	365.8	370.1	382.2	398.6	421.6	451.2	485.1	522.4	566.2	619.8	684.5
137.5°	380.2	384.8	396.6	414.2	437.0	464.3	496.9	532.4	571.5	617.4	671.5
140°	389.8	395.3	406.2	423.8	445.7	473.1	504.8	537.7	575.0	616.5	663.6
142.5°	400.4	405.0	416.8	432.5	454.5	480.1	511.0	542.9	577.6	614.8	656.6
145°	417.3	420.5	430.4	446.8	465.4	490.6	519.1	548.7	579.3	612.2	647.2
147.5°	434.3	436.3	445.9	460.1	478.2	499.5	525.7	552.1	579.3	608.0	638.0
150°	445.7	446.8	455.5	469.8	485.1	504.8	530.0	553.0	579.3	604.5	631.9
152.5°	457.1	457.3	466.1	478.5	492.1	511.0	532.6	554.8	576.6	600.1	624.9
155°	474.2	474.2	480.8	491.7	503.7	519.1	537.7	555.3	573.8	592.5	614.3
157.5°	487.8	488.6	493.9	503.5	513.8	525.7	540.5	556.3	570.1	585.7	602.5
160°	498.2	498.2	502.7	511.4	519.1	530.0	543.2	556.3	568.4	580.4	594.7
162.5°	506.1	506.1	509.6	516.7	523.5	532.6	544.0	555.4	564.9	575.1	586.7
165°	518.0	516.9	519.1	524.5	529.0	536.6	545.4	553.0	559.6	567.2	576.0
167.5°	527.0	525.7	526.7	530.9	534.0	538.8	545.2	551.3	554.3	559.4	565.7
170°	532.3	530.0	531.1	534.4	536.6	538.8	544.2	548.7	550.8	554.1	559.6
172.5°	535.7	534.4	534.6	537.1	538.4	539.7	544.2	547.8	548.2	549.7	553.5
175°	539.9	538.8	537.7	539.9	539.9	541.0	543.2	545.4	544.2	544.2	546.5
177.5°	541.9	541.0	540.1	541.0	541.0	541.0	541.9	543.6	541.9	541.0	541.9
180°	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0



TEST NUMBER: P331999-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8
2.5°	1143.4	1145.2	1146.9	1147.7	1147.5	1147.4	1147.2	1147.0
5°	1137.4	1139.5	1141.8	1142.6	1142.2	1141.8	1141.3	1140.9
7.5°	1125.3	1127.3	1129.3	1130.1	1129.8	1129.5	1129.3	1129.1
10°	1114.3	1116.2	1118.1	1119.0	1118.5	1118.0	1117.7	1117.2
12.5°	1102.1	1103.5	1105.0	1105.6	1105.3	1105.0	1104.8	1104.6
15°	1080.2	1081.9	1083.7	1083.9	1082.6	1081.3	1080.1	1078.7
17.5°	1052.5	1053.8	1055.0	1055.4	1054.9	1054.4	1054.0	1053.5
20°	1032.1	1032.9	1033.9	1034.0	1033.3	1032.6	1032.0	1031.3
22.5°	1010.4	1011.2	1011.8	1011.7	1011.0	1010.1	1009.3	1008.4
25°	974.5	974.8	975.0	974.8	974.1	973.5	972.8	972.1
27.5°	936.3	936.5	936.7	936.3	935.6	934.7	933.9	933.0
30°	909.9	909.9	909.9	909.2	907.7	906.1	904.6	903.1
32.5°	882.2	881.0	879.8	878.7	877.9	877.0	876.2	875.4
35°	837.3	835.9	834.6	833.4	832.3	831.2	830.1	829.0
37.5°	790.7	789.1	787.6	786.5	785.7	785.0	784.3	783.6
40°	760.3	758.7	756.9	755.5	754.7	753.8	752.9	752.1
42.5°	728.8	727.0	725.3	724.0	723.1	722.2	721.3	720.5
45°	681.6	679.0	676.4	674.5	673.4	672.3	671.2	670.1
47.5°	632.0	629.4	626.8	625.0	624.1	623.1	622.2	621.1
50°	599.2	596.7	594.4	592.5	591.2	589.8	588.5	587.2
52.5°	565.9	563.8	561.8	560.2	558.8	557.5	556.2	554.9
55°	515.3	512.8	510.5	508.7	507.6	506.5	505.4	504.4
57.5°	465.4	463.4	461.2	459.5	458.2	456.9	455.6	454.4
60°	430.3	428.3	426.3	424.8	423.7	422.6	421.5	420.5
62.5°	396.3	394.4	392.4	391.1	390.3	389.6	388.8	388.0
65°	345.8	344.1	342.3	341.1	340.4	339.8	339.1	338.5
67.5°	295.8	294.3	292.7	291.4	290.6	289.6	288.7	287.8
70°	263.4	261.8	260.3	259.0	257.9	256.8	255.7	254.6
72.5°	230.5	229.2	227.9	226.9	226.3	225.7	225.2	224.6
75°	183.3	182.3	181.2	180.3	179.6	179.0	178.3	177.7
77.5°	139.2	138.5	137.7	137.4	137.4	137.4	137.4	137.4
80°	111.1	110.8	110.7	110.6	110.6	110.6	110.6	110.6
82.5°	85.5	85.1	84.6	84.4	84.3	84.1	83.9	83.7
85°	48.4	48.1	47.6	47.4	47.4	47.4	47.4	47.4
87.5°	22.5	22.5	22.6	22.9	22.7	22.9	23.2	22.9
90°	27.3	28.5	29.6	31.8	30.6	31.8	32.9	31.8
92.5°	92.2	73.1	64.6	58.9	56.9	53.6	54.8	52.8
95°	394.3	267.2	209.2	169.8	148.9	139.1	131.4	127.1
97.5°	982.7	787.1	645.9	514.9	434.1	384.8	355.2	345.8
100°	1291.1	1202.4	1074.3	918.8	808.1	728.2	685.5	686.6
102.5°	1393.6	1390.7	1316.1	1217.5	1131.4	1068.2	1032.5	1007.3
105°	1423.6	1533.1	1554.0	1525.5	1475.1	1433.5	1398.5	1393.0
107.5°	1337.3	1515.1	1611.1	1650.1	1651.0	1636.9	1625.1	1615.0
110°	1255.0	1456.5	1594.5	1671.1	1701.8	1710.5	1708.4	1706.2





TEST NUMBER: P331999-830

CATALOG NUMBER: S123DIP-S775D1195U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1173.5	1379.4	1534.0	1632.6	1688.7	1715.8	1724.1	1724.6
115°	1065.5	1256.0	1417.0	1536.4	1618.5	1666.7	1688.7	1694.1
117.5°	987.3	1151.8	1296.4	1417.5	1503.2	1558.3	1589.9	1597.3
120°	946.1	1094.0	1225.4	1336.1	1422.5	1483.8	1510.1	1516.7
122.5°	913.7	1047.5	1169.3	1272.1	1349.0	1404.1	1433.0	1441.3
125°	870.6	990.0	1095.0	1182.7	1252.8	1301.0	1328.3	1336.1
127.5°	832.9	939.3	1034.2	1113.9	1176.4	1217.5	1242.3	1249.2
130°	809.3	907.9	996.6	1071.0	1129.1	1168.5	1191.5	1200.2
132.5°	787.4	878.1	960.6	1031.6	1086.1	1125.5	1145.9	1152.1
135°	757.8	835.6	906.7	969.1	1022.8	1055.6	1075.3	1083.1
137.5°	730.8	794.6	855.9	910.0	955.2	988.4	1005.0	1010.1
140°	715.1	770.9	823.5	870.6	912.2	942.9	960.4	959.3
142.5°	700.2	748.2	793.7	834.7	870.2	897.3	913.0	912.0
145°	682.2	718.4	753.5	785.1	812.6	835.6	844.3	846.5
147.5°	667.6	696.3	724.5	747.1	767.9	783.4	791.7	792.6
150°	657.0	682.2	705.2	726.0	742.4	754.5	761.1	761.1
152.5°	647.4	669.1	689.5	706.8	719.7	730.8	734.8	734.8
155°	632.9	650.4	666.9	680.0	689.9	698.7	700.9	701.9
157.5°	617.6	632.4	645.0	655.3	663.8	670.4	672.1	671.9
160°	608.9	620.9	631.9	639.5	647.2	653.7	653.7	652.7
162.5°	598.3	608.7	618.7	625.5	630.6	636.2	636.2	635.2
165°	584.8	591.4	599.0	604.5	608.9	613.2	612.2	612.2
167.5°	573.0	578.0	582.4	586.4	588.2	591.4	590.2	590.2
170°	565.1	568.4	572.7	575.0	576.0	578.2	577.1	577.1
172.5°	558.1	560.4	564.0	565.2	565.5	567.7	565.7	564.9
175°	548.7	549.7	552.0	552.0	552.0	553.0	552.0	550.8
177.5°	542.7	543.6	544.5	544.5	543.6	544.5	542.7	542.7
180°	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0

(END OF REPORT)