

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331961-830

Luminaire Tested: **S123DIP-S775D365U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331961-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S775D365U830-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4355.0 lumens  
Efficiency: N/A  
Efficacy: 124.4 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331961-830

CATALOG NUMBER: S123DIP-S775D365U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331961-830

CATALOG NUMBER: S123DIP-S775D365U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69				
1	102	97	93	90	96	92	89	85	82	79	77	73	71	69	65	63	62	58				
2	93	85	79	73	87	80	75	70	72	68	64	64	61	58	57	54	52	48				
3	85	75	67	61	80	71	64	58	63	58	54	57	52	49	50	47	44	41				
4	77	66	58	52	73	63	55	50	56	50	46	51	46	42	45	41	38	35				
5	71	59	51	44	67	56	49	43	51	44	39	45	40	36	41	36	33	30				
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	33	29	27				
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	34	29	26	24				
8	57	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23	21				
9	53	40	32	27	50	38	31	26	35	29	24	32	26	23	29	24	21	19				
10	49	37	29	24	47	35	28	24	32	26	22	29	24	21	26	22	19	17				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12355	12355	12355
5°	12413	12241	12327
10°	12329	12136	12211
15°	12186	11999	12021
20°	12016	11802	11813
25°	11792	11569	11545
30°	11543	11309	11225
35°	11284	11037	10893
40°	11011	10732	10568
45°	10712	10456	10201
50°	10412	10114	9833
55°	10021	9760	9466
60°	9623	9347	9052
65°	9276	8899	8621
70°	8759	8387	8013
75°	8006	7719	7390
80°	7221	6912	6856
85°	6336	6101	5854



TEST NUMBER: P331961-830

CATALOG NUMBER: S123DIP-S775D365U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.1	2.5
10°-20°	305.3	7.0
20°-30°	451.0	10.4
30°-40°	526.8	12.1
40°-50°	529.6	12.2
50°-60°	465.2	10.7
60°-70°	346.6	8.0
70°-80°	197.5	4.5
80°-90°	57.9	1.3
90°-100°	16.3	0.4
100°-110°	77.7	1.8
110°-120°	186.6	4.3
120°-130°	237.6	5.5
130°-140°	253.9	5.8
140°-150°	237.4	5.5
150°-160°	191.5	4.4
160°-170°	123.6	2.8
170°-180°	42.6	1.0
0°-30°	864.4	19.8
0°-40°	1391.1	31.9
0°-60°	2385.9	54.8
0°-90°	2987.9	68.6
90°-120°	280.6	6.4
90°-150°	1009.4	23.2
90°-180°	1367.0	31.4
0°-180°	4355.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1148	1148	1148	1148	1148	
5°	1149	1143	1133	1142	1141	109
15°	1094	1089	1077	1084	1079	308
25°	993	987	974	975	972	457
35°	859	852	840	834	829	537
45°	704	699	687	675	670	543
55°	534	532	520	510	504	478
65°	364	359	349	342	338	359
75°	192	189	186	181	178	206
85°	51	50	49	48	47	56
90°	0	4	8	9	10	4
95°	20	8	10	12	13	25
105°	99	101	73	17	15	105
115°	186	188	191	194	196	184
125°	262	265	266	267	268	234
135°	327	329	330	331	330	251
145°	377	379	380	381	381	236
155°	415	415	415	416	415	191
165°	438	437	437	439	437	124
175°	448	447	447	449	447	43
180°	448	448	448	448	448	



TEST NUMBER: P331961-830

CATALOG NUMBER: S123DIP-S775D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8
2.5°	1151.7	1151.0	1150.4	1149.6	1149.0	1147.6	1145.7	1143.8	1141.8	1139.9	1141.6
5°	1148.8	1147.6	1146.6	1145.5	1144.3	1142.6	1140.2	1137.8	1135.4	1132.9	1135.2
7.5°	1137.6	1136.4	1135.3	1134.3	1133.1	1131.3	1128.8	1126.3	1123.8	1121.3	1123.3
10°	1128.0	1126.9	1125.9	1124.7	1123.7	1121.7	1118.8	1116.0	1113.1	1110.3	1112.3
12.5°	1115.4	1114.5	1113.6	1112.7	1111.7	1109.9	1107.3	1104.6	1101.9	1099.2	1100.7
15°	1093.5	1092.6	1091.7	1090.9	1090.0	1088.2	1085.2	1082.4	1079.6	1076.8	1078.5
17.5°	1068.0	1066.9	1065.7	1064.6	1063.5	1061.5	1058.7	1055.7	1052.9	1050.1	1051.3
20°	1049.0	1047.7	1046.5	1045.2	1043.9	1041.7	1038.9	1036.0	1033.2	1030.3	1031.2
22.5°	1027.7	1026.4	1025.1	1023.8	1022.5	1020.4	1017.6	1014.7	1011.9	1009.0	1009.7
25°	992.9	991.6	990.2	988.9	987.6	985.5	982.6	979.8	976.9	974.1	974.3
27.5°	955.5	954.2	953.0	951.7	950.5	948.3	945.2	942.2	939.1	935.9	936.1
30°	928.7	927.6	926.5	925.4	924.3	922.2	919.2	916.1	913.0	909.9	909.9
32.5°	901.8	900.4	898.9	897.5	896.1	894.2	891.7	889.4	887.0	884.7	883.4
35°	858.7	857.3	856.0	854.7	853.4	851.3	848.4	845.6	842.7	839.9	838.6
37.5°	814.4	812.8	811.1	809.4	807.8	805.5	802.6	799.7	796.7	793.9	792.3
40°	783.6	782.3	781.0	779.7	778.4	776.2	773.1	770.1	766.9	763.8	762.1
42.5°	752.8	751.3	749.8	748.4	746.9	744.6	741.5	738.4	735.4	732.3	730.6
45°	703.7	702.8	701.9	701.1	700.1	698.3	695.4	692.6	689.8	686.9	684.3
47.5°	654.9	653.7	652.3	651.1	649.8	647.8	645.2	642.5	639.8	637.2	634.5
50°	621.8	620.7	619.5	618.5	617.4	615.4	612.6	609.7	606.8	604.0	601.6
52.5°	587.0	586.3	585.5	584.8	584.0	582.1	579.1	576.1	573.1	570.0	568.0
55°	534.0	533.7	533.5	533.3	533.0	531.5	528.7	525.8	522.9	520.1	517.7
57.5°	483.4	482.7	481.9	481.2	480.4	478.9	476.6	474.3	472.0	469.8	467.6
60°	447.0	446.9	446.7	446.4	446.2	444.8	442.1	439.5	436.9	434.2	432.3
62.5°	414.7	414.2	413.6	413.0	412.5	410.9	408.2	405.6	402.9	400.3	398.3
65°	364.2	363.1	361.9	360.9	359.8	358.2	355.9	353.7	351.6	349.4	347.6
67.5°	310.7	309.7	308.8	307.7	306.8	305.5	303.9	302.2	300.5	298.9	297.3
70°	278.3	277.0	275.7	274.4	273.1	271.7	270.4	269.1	267.8	266.5	264.9
72.5°	244.4	243.4	242.4	241.5	240.5	239.3	237.8	236.3	234.8	233.3	232.0
75°	192.5	191.5	190.7	189.8	189.0	188.1	187.5	186.8	186.2	185.6	184.5
77.5°	146.5	146.0	145.5	145.1	144.5	143.9	143.1	142.3	141.6	140.7	140.0
80°	116.5	115.8	115.2	114.5	113.9	113.3	112.8	112.4	112.0	111.5	111.3
82.5°	87.3	87.1	87.0	86.8	86.7	86.6	86.5	86.4	86.3	86.2	85.9
85°	51.3	50.9	50.4	50.0	49.6	49.4	49.4	49.4	49.4	49.4	48.9
87.5°	20.5	20.2	19.8	19.4	19.0	18.9	18.9	18.9	18.9	18.9	18.9
90°	0.4	1.0	1.8	2.5	3.3	4.1	5.1	6.0	7.1	8.0	8.3
92.5°	6.2	6.0	5.7	5.6	5.4	5.7	6.3	7.1	7.8	8.5	9.0
95°	20.4	17.2	14.2	11.2	8.2	7.1	7.9	8.7	9.5	10.4	10.8
97.5°	40.8	39.5	38.1	36.8	35.3	32.0	26.7	21.4	16.0	10.7	11.3
100°	56.3	57.8	59.3	60.7	62.2	57.2	45.6	34.1	22.5	11.0	11.6
102.5°	73.9	74.9	76.0	77.1	78.1	72.4	59.8	47.1	34.5	22.0	20.1
105°	99.2	100.1	100.9	101.7	102.5	99.6	92.9	86.2	79.6	73.0	59.9
107.5°	126.0	126.7	127.3	128.0	128.7	129.5	130.5	131.6	132.6	133.7	124.0
110°	143.9	144.5	145.1	145.6	146.3	146.9	147.8	148.5	149.4	150.2	147.8



TEST NUMBER: P331961-830

CATALOG NUMBER: S123DIP-S775D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	160.9	161.5	162.0	162.5	163.1	163.7	164.6	165.4	166.2	167.0	167.0
115°	186.2	186.6	187.1	187.5	187.9	188.5	189.2	189.8	190.5	191.1	191.9
117.5°	210.7	211.2	211.7	212.3	212.8	213.3	213.6	214.0	214.3	214.6	215.2
120°	225.8	226.5	227.2	227.8	228.5	228.9	229.1	229.4	229.6	229.8	230.5
122.5°	241.3	241.9	242.3	242.9	243.5	243.8	244.1	244.4	244.7	245.0	245.4
125°	262.5	263.1	263.6	264.2	264.9	265.2	265.6	265.9	266.2	266.5	266.6
127.5°	283.0	283.6	284.2	284.7	285.3	285.8	286.2	286.5	286.9	287.2	287.5
130°	295.8	296.3	296.9	297.6	298.1	298.6	298.9	299.2	299.4	299.7	300.0
132.5°	308.0	308.6	309.2	309.8	310.4	310.8	311.0	311.3	311.5	311.8	312.1
135°	326.8	327.2	327.6	328.1	328.5	328.9	329.1	329.5	329.8	330.1	330.3
137.5°	342.7	343.3	343.8	344.4	345.0	345.3	345.5	345.6	345.8	346.0	346.4
140°	353.4	353.8	354.3	354.7	355.2	355.5	355.7	355.9	356.2	356.4	356.7
142.5°	363.3	363.7	364.1	364.6	365.0	365.3	365.6	365.8	366.0	366.3	366.5
145°	377.0	377.6	378.1	378.6	379.1	379.5	379.6	379.8	379.8	380.0	380.2
147.5°	390.0	390.4	390.7	391.1	391.3	391.6	391.8	391.9	392.1	392.2	392.4
150°	398.0	398.2	398.4	398.7	398.9	399.1	399.3	399.4	399.5	399.6	399.8
152.5°	405.2	405.3	405.4	405.5	405.6	405.8	405.8	405.9	406.0	406.0	406.3
155°	415.4	415.2	415.0	414.9	414.7	414.7	414.8	414.8	414.9	415.0	415.4
157.5°	423.2	423.2	423.2	423.1	423.1	423.1	423.0	422.9	422.8	422.8	423.2
160°	428.0	427.9	427.8	427.7	427.7	427.6	427.5	427.4	427.4	427.3	427.7
162.5°	432.5	432.3	432.2	432.0	431.8	431.6	431.5	431.5	431.4	431.3	431.8
165°	438.0	437.7	437.5	437.3	437.1	437.0	436.9	436.8	436.7	436.7	437.2
167.5°	442.2	442.0	441.7	441.4	441.0	440.9	440.9	440.9	440.9	440.9	441.5
170°	444.6	444.3	444.0	443.7	443.5	443.3	443.3	443.3	443.3	443.3	443.9
172.5°	446.2	445.9	445.5	445.2	444.8	444.7	444.7	444.8	444.9	444.9	445.5
175°	448.3	447.9	447.5	447.2	446.9	446.7	446.8	446.9	446.9	447.0	447.5
177.5°	448.8	448.6	448.3	448.0	447.6	447.5	447.6	447.6	447.7	447.8	448.3
180°	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3



TEST NUMBER: P331961-830

CATALOG NUMBER: S123DIP-S775D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8
2.5°	1143.4	1145.2	1146.9	1147.7	1147.5	1147.4	1147.2	1147.0
5°	1137.4	1139.5	1141.8	1142.6	1142.2	1141.8	1141.3	1140.9
7.5°	1125.3	1127.3	1129.3	1130.1	1129.8	1129.5	1129.3	1129.1
10°	1114.3	1116.2	1118.1	1119.0	1118.5	1118.0	1117.7	1117.2
12.5°	1102.1	1103.5	1105.0	1105.6	1105.3	1105.0	1104.8	1104.6
15°	1080.2	1081.9	1083.7	1083.9	1082.6	1081.3	1080.1	1078.7
17.5°	1052.5	1053.8	1055.0	1055.4	1054.9	1054.4	1054.0	1053.5
20°	1032.1	1032.9	1033.9	1034.0	1033.3	1032.6	1032.0	1031.3
22.5°	1010.4	1011.2	1011.8	1011.7	1011.0	1010.1	1009.3	1008.4
25°	974.5	974.8	975.0	974.8	974.1	973.5	972.8	972.1
27.5°	936.3	936.5	936.7	936.3	935.6	934.7	933.9	933.0
30°	909.9	909.9	909.9	909.2	907.7	906.1	904.6	903.1
32.5°	882.2	881.0	879.8	878.7	877.9	877.0	876.2	875.4
35°	837.3	835.9	834.6	833.4	832.3	831.2	830.1	829.0
37.5°	790.7	789.1	787.6	786.5	785.7	785.0	784.3	783.6
40°	760.3	758.7	756.9	755.5	754.7	753.8	752.9	752.1
42.5°	728.8	727.0	725.3	724.0	723.1	722.2	721.3	720.5
45°	681.6	679.0	676.4	674.5	673.4	672.3	671.2	670.1
47.5°	632.0	629.4	626.8	625.0	624.1	623.1	622.2	621.1
50°	599.2	596.7	594.4	592.5	591.2	589.8	588.5	587.2
52.5°	565.9	563.8	561.8	560.2	558.8	557.5	556.2	554.9
55°	515.3	512.8	510.5	508.7	507.6	506.5	505.4	504.4
57.5°	465.4	463.4	461.2	459.5	458.2	456.9	455.6	454.4
60°	430.3	428.3	426.3	424.8	423.7	422.6	421.5	420.5
62.5°	396.3	394.4	392.4	391.1	390.3	389.6	388.8	388.0
65°	345.8	344.1	342.3	341.1	340.4	339.8	339.1	338.5
67.5°	295.8	294.3	292.7	291.4	290.6	289.6	288.7	287.8
70°	263.4	261.8	260.3	259.0	257.9	256.8	255.7	254.6
72.5°	230.5	229.2	227.9	226.9	226.3	225.7	225.2	224.6
75°	183.3	182.3	181.2	180.3	179.6	179.0	178.3	177.7
77.5°	139.2	138.5	137.7	137.4	137.4	137.4	137.4	137.4
80°	111.1	110.8	110.7	110.6	110.6	110.6	110.6	110.6
82.5°	85.5	85.1	84.6	84.4	84.3	84.1	83.9	83.7
85°	48.4	48.1	47.6	47.4	47.4	47.4	47.4	47.4
87.5°	18.8	18.7	18.5	18.5	18.5	18.5	18.6	18.6
90°	8.6	8.9	9.1	9.4	9.5	9.7	9.8	10.0
92.5°	9.5	10.0	10.5	10.7	10.7	10.8	10.9	11.0
95°	11.4	11.9	12.4	12.6	12.6	12.6	12.6	12.6
97.5°	11.9	12.5	13.1	13.4	13.5	13.6	13.7	13.8
100°	12.2	12.7	13.4	13.7	13.8	13.9	13.9	13.9
102.5°	18.3	16.4	14.6	13.8	13.9	13.9	14.1	14.2
105°	46.8	33.6	20.5	14.0	14.2	14.3	14.5	14.6
107.5°	114.5	104.9	95.3	85.5	75.7	65.8	55.9	46.0
110°	145.3	142.9	140.4	133.9	123.4	112.7	102.2	91.6





TEST NUMBER: P331961-830

CATALOG NUMBER: S123DIP-S775D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	167.1	167.1	167.2	166.1	163.8	161.6	159.4	157.1
115°	192.7	193.4	194.2	194.6	194.9	195.3	195.6	195.9
117.5°	215.8	216.4	217.0	217.4	217.4	217.4	217.5	217.5
120°	231.0	231.6	232.1	232.5	232.5	232.5	232.5	232.5
122.5°	245.8	246.3	246.7	246.9	246.9	247.0	247.0	247.1
125°	266.7	266.9	267.0	267.2	267.3	267.5	267.7	267.8
127.5°	287.7	287.9	288.2	288.2	288.0	287.9	287.8	287.7
130°	300.4	300.7	301.0	301.0	300.9	300.8	300.6	300.4
132.5°	312.4	312.6	312.9	313.0	312.7	312.5	312.4	312.2
135°	330.5	330.7	330.9	330.9	330.7	330.5	330.3	330.1
137.5°	346.7	347.0	347.4	347.5	347.3	347.2	347.0	346.9
140°	356.9	357.2	357.6	357.6	357.5	357.3	357.2	357.0
142.5°	366.7	366.9	367.2	367.2	367.0	366.7	366.6	366.4
145°	380.3	380.5	380.6	380.7	380.7	380.7	380.7	380.7
147.5°	392.5	392.7	392.9	392.8	392.4	392.0	391.7	391.3
150°	400.0	400.1	400.3	400.2	400.0	399.8	399.5	399.4
152.5°	406.6	406.9	407.2	407.1	406.8	406.4	406.0	405.8
155°	415.8	416.1	416.5	416.4	416.0	415.6	415.1	414.6
157.5°	423.7	424.1	424.6	424.5	424.0	423.4	422.7	422.2
160°	428.2	428.7	429.1	429.0	428.6	428.0	427.5	427.0
162.5°	432.3	432.8	433.3	433.4	432.9	432.4	432.0	431.5
165°	437.8	438.5	439.0	439.0	438.6	438.0	437.5	437.0
167.5°	442.1	442.7	443.3	443.3	442.7	442.1	441.5	440.9
170°	444.5	445.1	445.6	445.6	445.1	444.5	443.9	443.3
172.5°	446.1	446.7	447.2	447.2	446.6	445.9	445.3	444.6
175°	448.0	448.6	449.0	449.0	448.5	447.8	447.2	446.7
177.5°	448.7	449.2	449.7	449.6	449.0	448.5	447.8	447.2
180°	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3

(END OF REPORT)