

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332341

Luminaire Tested: **S123RDIP-S1000D585U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332341
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D585U835-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5913.1 lumens
Efficiency: N/A
Efficacy: 121.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332341

CATALOG NUMBER: S123RDIP-S1000D585U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332341

CATALOG NUMBER: S123RDIP-S1000D585U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	62	60	59	55
2	93	85	79	74	87	80	75	70	71	67	64	63	60	57	55	53	51	47
3	85	75	68	62	79	71	65	59	63	58	54	56	52	49	49	46	43	40
4	78	67	59	53	73	63	56	51	56	51	46	50	46	42	44	41	38	35
5	72	60	52	46	67	57	49	44	51	45	40	45	40	37	40	36	33	30
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	27
7	61	49	41	35	58	47	39	34	42	36	31	37	32	29	33	29	26	24
8	57	45	37	31	54	42	35	30	38	32	28	34	29	26	31	27	24	21
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	28	24	21	19
10	50	38	30	26	47	36	29	25	33	27	23	29	25	21	26	22	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18064	18064	18064
5°	18133	17882	17986
10°	18030	17658	17598
15°	17836	17245	17063
20°	17570	16728	16339
25°	17296	16149	15631
30°	16933	15479	14633
35°	16561	14808	13717
40°	16218	14018	12584
45°	15767	13239	11561
50°	15270	12353	10416
55°	14763	11340	9348
60°	14299	10256	8174
65°	13692	9082	7002
70°	12935	7626	5655
75°	11832	6001	5319
80°	10544	5312	4891
85°	8904	4705	4372



TEST NUMBER: P332341

CATALOG NUMBER: S123RDIP-S1000D585U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.6	2.7
10°-20°	438.5	7.4
20°-30°	631.4	10.7
30°-40°	711.2	12.0
40°-50°	680.4	11.5
50°-60°	557.2	9.4
60°-70°	375.9	6.4
70°-80°	189.1	3.2
80°-90°	52.2	0.9
90°-100°	156.8	2.7
100°-110°	444.0	7.5
110°-120°	436.8	7.4
120°-130°	348.4	5.9
130°-140°	274.7	4.6
140°-150°	205.0	3.5
150°-160°	142.9	2.4
160°-170°	83.9	1.4
170°-180°	27.3	0.5
0°-30°	1227.4	20.8
0°-40°	1938.6	32.8
0°-60°	3176.1	53.7
0°-90°	3793.3	64.2
90°-120°	1037.6	17.5
90°-150°	1865.7	31.6
90°-180°	2120.0	35.9
0°-180°	5913.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1678	1678	1678	1678	1678	
5°	1678	1671	1655	1666	1665	159
15°	1601	1584	1548	1541	1531	451
25°	1456	1421	1360	1332	1316	669
35°	1260	1209	1127	1070	1044	788
45°	1036	972	870	795	760	799
55°	787	717	604	528	498	705
65°	538	461	357	293	275	532
75°	284	219	144	131	128	303
85°	72	44	38	36	35	81
90°	1	7	14	16	16	5
95°	19	63	338	99	66	21
105°	66	98	459	802	726	70
115°	117	146	351	769	882	116
125°	163	192	327	593	696	144
135°	190	227	323	489	564	147
145°	217	249	319	401	441	136
155°	247	266	309	351	366	114
165°	270	278	296	313	319	76
175°	281	282	284	288	287	27
180°	282	282	282	282	282	



TEST NUMBER: P332341

CATALOG NUMBER: S123RDIP-S1000D585U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2
2.5°	1683.6	1682.6	1681.7	1680.7	1679.7	1677.8	1674.9	1672.0	1669.1	1666.2	1668.8
5°	1678.2	1676.6	1675.1	1673.6	1672.1	1669.5	1665.9	1662.3	1658.7	1655.0	1657.7
7.5°	1662.6	1661.0	1659.4	1657.7	1656.1	1652.9	1648.2	1643.5	1638.8	1634.1	1635.6
10°	1649.6	1647.5	1645.3	1643.2	1641.1	1637.3	1631.9	1626.4	1621.0	1615.6	1615.9
12.5°	1631.1	1628.7	1626.4	1624.0	1621.6	1617.1	1610.5	1603.8	1597.2	1590.5	1590.3
15°	1600.6	1597.3	1593.9	1590.6	1587.3	1581.4	1572.9	1564.4	1556.0	1547.5	1546.0
17.5°	1562.2	1558.3	1554.5	1550.6	1546.7	1539.4	1528.6	1517.9	1507.1	1496.3	1493.1
20°	1533.9	1529.1	1524.2	1519.4	1514.5	1506.4	1494.9	1483.4	1471.9	1460.4	1456.5
22.5°	1502.3	1496.8	1491.2	1485.6	1480.1	1471.2	1458.9	1446.7	1434.5	1422.3	1417.4
25°	1456.3	1448.8	1441.2	1433.6	1426.1	1415.3	1401.4	1387.5	1373.6	1359.7	1353.3
27.5°	1400.5	1392.2	1383.8	1375.5	1367.1	1355.2	1339.7	1324.2	1308.7	1293.3	1284.4
30°	1362.4	1353.3	1344.3	1335.2	1326.1	1313.1	1296.2	1279.2	1262.3	1245.4	1235.1
32.5°	1324.3	1314.0	1303.7	1293.4	1283.2	1269.1	1251.2	1233.3	1215.3	1197.4	1186.2
35°	1260.3	1249.4	1238.5	1227.7	1216.8	1201.9	1183.2	1164.4	1145.7	1126.9	1113.9
37.5°	1195.5	1183.4	1171.3	1159.2	1147.1	1131.1	1111.1	1091.0	1071.0	1051.0	1036.2
40°	1154.2	1140.9	1127.5	1114.2	1100.9	1083.5	1062.1	1040.6	1019.1	997.6	981.9
42.5°	1107.3	1094.0	1080.7	1067.4	1054.1	1036.4	1014.2	992.0	969.8	947.6	930.4
45°	1035.8	1022.1	1008.5	994.9	981.3	962.9	939.6	916.3	893.0	869.7	852.5
47.5°	964.2	949.2	934.3	919.3	904.4	885.3	862.0	838.7	815.4	792.1	773.4
50°	911.9	897.7	883.5	869.3	855.0	835.7	811.2	786.7	762.2	737.7	718.9
52.5°	865.1	849.7	834.2	818.8	803.4	783.5	759.3	735.0	710.8	686.5	667.0
55°	786.7	771.9	757.0	742.2	727.4	707.1	681.4	655.7	630.0	604.3	586.8
57.5°	714.3	698.1	682.0	665.8	649.7	628.7	602.8	577.0	551.2	525.4	508.8
60°	664.2	647.6	630.9	614.3	597.6	576.8	551.7	526.6	501.5	476.4	460.0
62.5°	614.1	597.5	580.8	564.2	547.6	526.7	501.6	476.5	451.4	426.3	410.9
65°	537.6	521.0	504.3	487.7	471.1	451.0	427.4	403.8	380.2	356.6	341.8
67.5°	461.1	444.3	427.5	410.7	393.9	374.1	351.5	328.9	306.3	283.6	272.6
70°	411.0	394.7	378.4	362.0	345.7	327.0	305.8	284.6	263.4	242.3	231.7
72.5°	360.9	344.9	328.8	312.7	296.6	278.9	259.7	240.5	221.2	202.0	193.3
75°	284.5	269.9	255.4	240.9	226.4	210.8	194.2	177.5	160.9	144.3	141.2
77.5°	214.8	201.6	188.5	175.4	162.3	150.3	139.6	128.9	118.2	107.5	105.9
80°	170.1	157.7	145.3	132.9	120.5	111.2	104.8	98.4	92.1	85.7	84.8
82.5°	127.7	117.0	106.3	95.5	84.8	78.0	75.0	72.1	69.1	66.1	65.2
85°	72.1	65.5	58.8	52.2	45.5	41.7	40.8	39.9	39.0	38.1	37.5
87.5°	26.4	23.9	21.5	19.2	16.7	15.6	16.0	16.3	16.7	17.0	16.7
90°	1.1	2.3	3.4	5.1	6.3	7.4	9.1	10.8	12.5	14.3	13.7
92.5°	7.1	10.5	15.3	19.7	24.5	33.0	47.9	72.4	96.5	87.7	66.2
95°	19.4	21.1	27.4	37.1	51.9	74.1	122.6	207.6	301.2	338.2	274.3
97.5°	33.1	33.7	38.6	47.0	61.6	85.7	132.0	227.8	383.7	524.2	560.8
100°	42.2	42.8	46.8	54.8	68.4	90.7	130.6	215.0	365.0	540.1	652.5
102.5°	51.8	52.8	56.4	63.9	76.2	96.6	132.4	204.1	337.7	510.5	657.1
105°	66.2	67.9	71.3	78.1	89.0	106.7	137.5	196.2	304.0	458.6	622.3
107.5°	81.4	83.2	86.5	93.2	103.4	119.8	146.8	195.6	282.6	412.7	561.4
110°	92.4	94.1	97.0	103.2	112.9	128.9	154.6	197.9	274.3	386.7	523.0



TEST NUMBER: P332341

CATALOG NUMBER: S123RDIP-S1000D585U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	102.4	104.2	107.0	113.3	123.0	138.5	162.3	202.5	269.8	369.4	489.7
115°	116.9	119.2	122.6	128.3	138.0	153.4	175.1	209.9	268.1	350.8	449.5
117.5°	131.4	134.0	136.9	142.1	153.0	167.2	188.7	219.7	269.1	339.8	425.2
120°	141.5	143.2	146.0	151.7	162.6	176.8	197.3	227.0	270.9	334.8	412.4
122.5°	150.1	151.8	154.7	160.8	171.2	186.4	206.5	233.9	274.1	331.6	401.9
125°	162.6	163.7	167.1	173.4	184.2	199.6	219.6	244.7	278.9	327.4	388.4
127.5°	172.0	173.7	178.0	184.3	196.3	211.7	231.0	253.6	284.4	325.3	376.6
130°	178.0	179.7	184.8	191.6	203.6	219.0	237.8	259.5	288.0	324.0	370.2
132.5°	182.5	184.7	190.3	198.5	210.5	225.4	243.8	265.0	290.8	323.5	364.2
135°	190.5	192.8	199.1	207.6	219.6	235.0	252.7	272.1	294.9	322.8	356.5
137.5°	198.0	200.4	206.6	215.7	227.6	241.8	258.8	277.3	297.6	321.6	349.8
140°	203.1	205.9	211.6	220.7	232.1	246.4	262.9	280.1	299.4	321.1	345.6
142.5°	208.5	210.9	217.1	225.3	236.7	250.1	266.1	282.8	300.8	320.2	342.0
145°	217.3	219.0	224.2	232.7	242.4	255.5	270.4	285.8	301.7	318.8	337.1
147.5°	226.2	227.2	232.3	239.7	249.0	260.2	273.8	287.6	301.7	316.7	332.3
150°	232.1	232.7	237.3	244.7	252.7	262.9	276.1	288.0	301.7	314.8	329.1
152.5°	238.1	238.2	242.8	249.3	256.3	266.1	277.4	289.0	300.4	312.6	325.5
155°	247.0	247.0	250.4	256.1	262.4	270.4	280.1	289.2	298.9	308.6	320.0
157.5°	254.0	254.5	257.2	262.3	267.6	273.8	281.5	289.8	296.9	305.0	313.8
160°	259.5	259.5	261.8	266.4	270.4	276.1	282.9	289.8	296.0	302.3	309.7
162.5°	263.6	263.6	265.5	269.1	272.6	277.4	283.4	289.3	294.2	299.6	305.6
165°	269.8	269.2	270.4	273.2	275.5	279.5	284.0	288.0	291.5	295.5	300.0
167.5°	274.5	273.8	274.3	276.5	278.1	280.6	283.9	287.1	288.7	291.3	294.7
170°	277.2	276.1	276.6	278.3	279.5	280.6	283.5	285.8	286.9	288.6	291.5
172.5°	279.0	278.3	278.5	279.7	280.4	281.1	283.5	285.3	285.5	286.3	288.3
175°	281.2	280.6	280.1	281.2	281.2	281.8	282.9	284.0	283.5	283.5	284.6
177.5°	282.2	281.8	281.3	281.8	281.8	281.8	282.2	283.1	282.2	281.8	282.2
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332341

CATALOG NUMBER: S123RDIP-S1000D585U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2
2.5°	1671.5	1674.2	1676.8	1677.9	1677.4	1677.0	1676.5	1676.0
5°	1660.5	1663.2	1665.9	1667.0	1666.4	1665.8	1665.2	1664.6
7.5°	1637.1	1638.6	1640.1	1640.4	1639.3	1638.3	1637.3	1636.2
10°	1616.2	1616.5	1616.8	1616.2	1614.6	1613.1	1611.6	1610.1
12.5°	1590.1	1590.0	1589.8	1588.8	1587.1	1585.3	1583.6	1581.8
15°	1544.5	1543.0	1541.5	1539.6	1537.5	1535.4	1533.3	1531.2
17.5°	1489.9	1486.7	1483.5	1480.3	1477.2	1474.0	1470.9	1467.7
20°	1452.5	1448.6	1444.7	1440.9	1437.3	1433.6	1430.0	1426.4
22.5°	1412.5	1407.6	1402.7	1398.5	1395.2	1391.8	1388.4	1385.0
25°	1347.0	1340.6	1334.3	1329.4	1326.1	1322.8	1319.5	1316.1
27.5°	1275.6	1266.8	1257.9	1251.0	1245.9	1240.8	1235.7	1230.7
30°	1224.8	1214.5	1204.2	1196.7	1191.8	1187.0	1182.1	1177.3
32.5°	1174.9	1163.7	1152.4	1144.3	1139.2	1134.1	1129.0	1123.9
35°	1100.9	1087.9	1074.9	1065.7	1060.3	1054.8	1049.4	1043.9
37.5°	1021.5	1006.7	992.0	981.2	974.5	967.8	961.1	954.4
40°	966.2	950.5	934.7	923.4	916.4	909.5	902.5	895.6
42.5°	913.2	896.0	878.8	867.1	860.9	854.7	848.4	842.2
45°	835.2	818.0	800.7	788.5	781.2	774.0	766.7	759.5
47.5°	754.6	735.9	717.1	704.5	698.0	691.6	685.1	678.6
50°	700.2	681.4	662.7	649.8	642.9	635.9	629.0	622.0
52.5°	647.6	628.1	608.6	595.7	589.5	583.3	577.1	570.8
55°	569.2	551.7	534.1	522.3	516.3	510.2	504.2	498.1
57.5°	492.2	475.6	459.1	448.2	443.1	437.9	432.8	427.6
60°	443.7	427.4	411.0	400.3	395.2	390.0	384.9	379.7
62.5°	395.5	380.2	364.8	354.4	349.1	343.7	338.3	332.9
65°	327.0	312.1	297.3	288.2	284.9	281.6	278.3	274.9
67.5°	261.5	250.4	239.4	232.0	228.5	224.9	221.3	217.8
70°	221.1	210.5	199.9	193.0	189.6	186.3	183.0	179.7
72.5°	184.7	176.0	167.4	162.4	161.0	159.6	158.2	156.8
75°	138.2	135.2	132.2	130.4	129.8	129.1	128.5	127.9
77.5°	104.3	102.6	101.0	99.9	99.3	98.7	98.1	97.5
80°	83.9	83.0	82.1	81.4	80.8	80.2	79.5	78.9
82.5°	64.3	63.4	62.5	62.0	61.9	61.8	61.6	61.5
85°	36.9	36.3	35.7	35.4	35.4	35.4	35.4	35.4
87.5°	16.5	16.4	16.3	16.3	15.9	15.8	15.6	15.3
90°	14.3	14.8	15.4	16.5	16.0	16.5	17.1	16.5
92.5°	48.0	38.1	33.7	30.7	29.7	27.9	28.5	27.5
95°	205.3	139.2	108.9	88.4	77.6	72.4	68.4	66.2
97.5°	511.9	410.0	336.4	268.2	226.1	200.4	185.0	180.1
100°	672.5	626.3	559.5	478.5	420.9	379.3	357.1	357.6
102.5°	725.9	724.4	685.5	634.1	589.3	556.3	537.7	524.6
105°	741.5	798.5	809.4	794.5	768.3	746.6	728.4	725.5
107.5°	696.5	789.2	839.1	859.4	859.9	852.6	846.4	841.2
110°	653.6	758.6	830.5	870.4	886.4	890.9	889.8	888.6



TEST NUMBER: P332341

CATALOG NUMBER: S123RDIP-S1000D585U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	611.2	718.4	799.0	850.3	879.5	893.7	898.0	898.2
115°	555.0	654.2	738.1	800.2	843.0	868.1	879.5	882.4
117.5°	514.2	599.9	675.2	738.3	782.9	811.6	828.1	831.9
120°	492.8	569.8	638.2	695.9	740.9	772.9	786.5	790.0
122.5°	475.9	545.6	609.0	662.5	702.6	731.3	746.4	750.7
125°	453.4	515.6	570.4	616.0	652.5	677.6	691.9	695.9
127.5°	433.8	489.3	538.7	580.2	612.7	634.1	647.0	650.7
130°	421.5	472.8	519.0	557.8	588.1	608.6	620.6	625.1
132.5°	410.1	457.3	500.3	537.3	565.7	586.2	596.8	600.0
135°	394.7	435.2	472.3	504.8	532.7	549.8	560.1	564.1
137.5°	380.7	413.9	445.8	474.0	497.5	514.8	523.5	526.1
140°	372.5	401.5	428.9	453.4	475.1	491.1	500.2	499.6
142.5°	364.7	389.7	413.4	434.7	453.2	467.4	475.6	475.0
145°	355.3	374.2	392.4	409.0	423.2	435.2	439.8	440.9
147.5°	347.7	362.6	377.4	389.1	399.9	408.0	412.4	412.8
150°	342.2	355.3	367.3	378.2	386.7	393.0	396.4	396.4
152.5°	337.2	348.5	359.1	368.1	374.8	380.7	382.7	382.7
155°	329.7	338.8	347.4	354.2	359.3	363.9	365.0	365.6
157.5°	321.7	329.3	336.0	341.3	345.8	349.2	350.1	350.0
160°	317.1	323.4	329.1	333.1	337.1	340.5	340.5	339.9
162.5°	311.7	317.0	322.3	325.8	328.4	331.4	331.4	330.8
165°	304.6	308.0	312.0	314.8	317.1	319.4	318.8	318.8
167.5°	298.4	301.0	303.3	305.4	306.4	308.0	307.4	307.4
170°	294.3	296.0	298.3	299.4	300.0	301.2	300.6	300.6
172.5°	290.7	291.9	293.7	294.4	294.5	295.7	294.7	294.2
175°	285.8	286.3	287.5	287.5	287.5	288.0	287.5	286.9
177.5°	282.7	283.1	283.6	283.6	283.1	283.6	282.7	282.7
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8

(END OF REPORT)