

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331971-830

Luminaire Tested: **S123DIP-S775D585U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331971-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S775D585U830-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4884.9 lumens  
Efficiency: N/A  
Efficacy: 121.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331971-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331971-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	77	77	77	66	66	66	61
1	100	96	92	88	94	90	86	83	78	76	73	68	66	64	59	57	56	51
2	91	84	77	72	85	78	73	68	69	64	61	60	57	54	52	49	47	43
3	83	73	66	60	78	69	62	57	61	55	51	53	49	45	46	43	40	36
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	37	34	31
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	27
6	64	52	44	38	60	49	42	36	44	37	33	38	33	30	33	29	26	24
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	27	24	21
8	55	43	35	29	52	41	33	28	36	30	26	32	27	23	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	22	19	24	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12355	12355	12355
5°	12413	12241	12327
10°	12329	12136	12211
15°	12186	11999	12021
20°	12016	11802	11813
25°	11792	11569	11545
30°	11543	11309	11225
35°	11284	11037	10893
40°	11011	10732	10568
45°	10712	10456	10201
50°	10412	10114	9833
55°	10021	9760	9466
60°	9623	9347	9052
65°	9276	8899	8621
70°	8759	8387	8013
75°	8006	7719	7390
80°	7221	6912	6856
85°	6336	6101	5854



TEST NUMBER: P331971-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.1	2.2
10°-20°	305.3	6.2
20°-30°	451.0	9.2
30°-40°	526.8	10.8
40°-50°	529.6	10.8
50°-60°	465.2	9.5
60°-70°	346.6	7.1
70°-80°	197.5	4.0
80°-90°	58.7	1.2
90°-100°	44.6	0.9
100°-110°	133.4	2.7
110°-120°	227.0	4.6
120°-130°	298.5	6.1
130°-140°	335.6	6.9
140°-150°	329.8	6.8
150°-160°	277.7	5.7
160°-170°	184.8	3.8
170°-180°	64.7	1.3
0°-30°	864.4	17.7
0°-40°	1391.1	28.5
0°-60°	2385.9	48.8
0°-90°	2988.7	61.2
90°-120°	405.0	8.3
90°-150°	1368.9	28.0
90°-180°	1896.0	38.8
0°-180°	4884.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1148	1148	1148	1148	1148	
5°	1149	1143	1133	1142	1141	109
15°	1094	1089	1077	1084	1079	308
25°	993	987	974	975	972	457
35°	859	852	840	834	829	537
45°	704	699	687	675	670	543
55°	534	532	520	510	504	478
65°	364	359	349	342	338	359
75°	192	189	186	181	178	206
85°	51	50	49	48	47	56
90°	1	6	13	15	16	5
95°	32	36	40	42	42	36
105°	121	122	127	127	128	130
115°	228	230	229	230	229	226
125°	334	336	335	333	331	298
135°	434	437	437	434	433	334
145°	526	527	529	528	526	329
155°	603	603	603	605	602	277
165°	656	655	655	658	654	185
175°	683	681	681	683	680	65
180°	684	684	684	684	684	



TEST NUMBER: P331971-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8
2.5°	1151.7	1151.0	1150.4	1149.6	1149.0	1147.6	1145.7	1143.8	1141.8	1139.9	1141.6
5°	1148.8	1147.6	1146.6	1145.5	1144.3	1142.6	1140.2	1137.8	1135.4	1132.9	1135.2
7.5°	1137.6	1136.4	1135.3	1134.3	1133.1	1131.3	1128.8	1126.3	1123.8	1121.3	1123.3
10°	1128.0	1126.9	1125.9	1124.7	1123.7	1121.7	1118.8	1116.0	1113.1	1110.3	1112.3
12.5°	1115.4	1114.5	1113.6	1112.7	1111.7	1109.9	1107.3	1104.6	1101.9	1099.2	1100.7
15°	1093.5	1092.6	1091.7	1090.9	1090.0	1088.2	1085.2	1082.4	1079.6	1076.8	1078.5
17.5°	1068.0	1066.9	1065.7	1064.6	1063.5	1061.5	1058.7	1055.7	1052.9	1050.1	1051.3
20°	1049.0	1047.7	1046.5	1045.2	1043.9	1041.7	1038.9	1036.0	1033.2	1030.3	1031.2
22.5°	1027.7	1026.4	1025.1	1023.8	1022.5	1020.4	1017.6	1014.7	1011.9	1009.0	1009.7
25°	992.9	991.6	990.2	988.9	987.6	985.5	982.6	979.8	976.9	974.1	974.3
27.5°	955.5	954.2	953.0	951.7	950.5	948.3	945.2	942.2	939.1	935.9	936.1
30°	928.7	927.6	926.5	925.4	924.3	922.2	919.2	916.1	913.0	909.9	909.9
32.5°	901.8	900.4	898.9	897.5	896.1	894.2	891.7	889.4	887.0	884.7	883.4
35°	858.7	857.3	856.0	854.7	853.4	851.3	848.4	845.6	842.7	839.9	838.6
37.5°	814.4	812.8	811.1	809.4	807.8	805.5	802.6	799.7	796.7	793.9	792.3
40°	783.6	782.3	781.0	779.7	778.4	776.2	773.1	770.1	766.9	763.8	762.1
42.5°	752.8	751.3	749.8	748.4	746.9	744.6	741.5	738.4	735.4	732.3	730.6
45°	703.7	702.8	701.9	701.1	700.1	698.3	695.4	692.6	689.8	686.9	684.3
47.5°	654.9	653.7	652.3	651.1	649.8	647.8	645.2	642.5	639.8	637.2	634.5
50°	621.8	620.7	619.5	618.5	617.4	615.4	612.6	609.7	606.8	604.0	601.6
52.5°	587.0	586.3	585.5	584.8	584.0	582.1	579.1	576.1	573.1	570.0	568.0
55°	534.0	533.7	533.5	533.3	533.0	531.5	528.7	525.8	522.9	520.1	517.7
57.5°	483.4	482.7	481.9	481.2	480.4	478.9	476.6	474.3	472.0	469.8	467.6
60°	447.0	446.9	446.7	446.4	446.2	444.8	442.1	439.5	436.9	434.2	432.3
62.5°	414.7	414.2	413.6	413.0	412.5	410.9	408.2	405.6	402.9	400.3	398.3
65°	364.2	363.1	361.9	360.9	359.8	358.2	355.9	353.7	351.6	349.4	347.6
67.5°	310.7	309.7	308.8	307.7	306.8	305.5	303.9	302.2	300.5	298.9	297.3
70°	278.3	277.0	275.7	274.4	273.1	271.7	270.4	269.1	267.8	266.5	264.9
72.5°	244.4	243.4	242.4	241.5	240.5	239.3	237.8	236.3	234.8	233.3	232.0
75°	192.5	191.5	190.7	189.8	189.0	188.1	187.5	186.8	186.2	185.6	184.5
77.5°	146.5	146.0	145.5	145.1	144.5	143.9	143.1	142.3	141.6	140.7	140.0
80°	116.5	115.8	115.2	114.5	113.9	113.3	112.8	112.4	112.0	111.5	111.3
82.5°	87.3	87.1	87.0	86.8	86.7	86.6	86.5	86.4	86.3	86.2	85.9
85°	51.3	50.9	50.4	50.0	49.6	49.4	49.4	49.4	49.4	49.4	48.9
87.5°	20.6	20.4	20.1	19.8	19.5	19.4	19.5	19.7	19.8	20.0	19.9
90°	0.6	1.7	2.9	4.1	5.3	6.7	8.2	9.8	11.3	12.9	13.4
92.5°	13.0	13.9	14.6	15.5	16.3	17.2	18.0	18.9	19.8	20.6	21.0
95°	31.8	32.5	33.4	34.2	35.1	36.0	36.9	37.9	38.8	39.8	40.2
97.5°	56.4	56.9	57.6	58.2	58.8	59.5	60.1	60.9	61.5	62.3	62.8
100°	73.1	73.8	74.6	75.3	76.0	76.6	77.2	77.9	78.4	79.0	79.4
102.5°	92.5	92.9	93.3	93.8	94.2	94.8	95.6	96.4	97.2	97.9	98.3
105°	120.9	121.2	121.4	121.7	122.0	122.5	123.7	124.7	125.8	126.9	126.9
107.5°	154.1	154.2	154.4	154.5	154.7	155.0	155.3	155.8	156.3	156.7	157.0
110°	174.7	174.9	175.2	175.4	175.7	175.9	176.2	176.4	176.6	176.9	177.4



TEST NUMBER: P331971-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	196.2	196.3	196.5	196.6	196.8	196.9	197.0	197.0	197.1	197.1	197.7
115°	228.5	228.8	229.2	229.6	229.9	230.0	229.7	229.5	229.2	229.0	229.1
117.5°	261.0	261.2	261.5	261.6	261.9	261.8	261.6	261.3	261.0	260.6	260.6
120°	281.2	281.9	282.6	283.3	284.1	284.1	283.5	283.0	282.3	281.7	281.6
122.5°	302.3	302.7	303.3	303.8	304.3	304.4	304.2	303.9	303.5	303.2	302.9
125°	334.4	334.8	335.1	335.5	335.8	335.9	335.6	335.5	335.2	335.0	334.4
127.5°	364.1	364.9	365.6	366.4	367.1	367.4	367.1	366.8	366.6	366.4	365.7
130°	383.9	384.8	385.8	386.7	387.7	388.0	387.7	387.3	386.9	386.5	386.1
132.5°	403.6	404.6	405.6	406.5	407.5	407.8	407.6	407.3	407.0	406.8	406.1
135°	433.9	434.6	435.3	436.0	436.7	437.1	436.9	436.8	436.7	436.6	436.1
137.5°	461.8	462.4	463.0	463.6	464.2	464.7	465.0	465.2	465.6	465.9	465.4
140°	481.2	481.7	482.4	483.0	483.5	483.9	484.0	484.2	484.3	484.4	484.3
142.5°	498.8	499.4	500.0	500.6	501.1	501.6	501.8	502.0	502.3	502.5	502.4
145°	526.3	526.6	526.8	527.1	527.3	527.5	527.9	528.3	528.7	529.0	528.9
147.5°	550.4	550.8	551.3	551.7	552.1	552.5	552.9	553.2	553.6	553.8	553.8
150°	567.2	567.4	567.7	567.9	568.2	568.4	568.6	568.8	569.1	569.3	569.3
152.5°	581.0	581.3	581.6	581.9	582.3	582.5	582.7	582.8	583.0	583.1	583.2
155°	602.7	602.7	602.7	602.7	602.7	602.8	602.9	602.9	603.1	603.2	603.7
157.5°	621.1	621.0	620.9	620.8	620.6	620.6	620.7	620.8	620.9	620.9	621.4
160°	632.7	632.5	632.3	632.1	631.8	631.7	631.7	631.7	631.7	631.7	632.3
162.5°	643.1	642.7	642.4	642.1	641.8	641.7	641.8	641.9	642.0	642.1	642.6
165°	656.4	656.1	655.7	655.3	655.0	654.8	654.8	654.8	654.8	654.8	655.5
167.5°	667.0	666.6	666.1	665.6	665.2	665.0	665.1	665.2	665.2	665.3	666.1
170°	673.1	672.6	672.1	671.7	671.2	670.9	670.9	670.9	670.9	670.9	671.8
172.5°	677.8	677.3	676.8	676.4	675.9	675.7	675.7	675.7	675.7	675.7	676.5
175°	682.8	682.3	681.8	681.4	680.9	680.6	680.6	680.6	680.6	680.6	681.4
177.5°	684.9	684.5	684.1	683.6	683.2	683.1	683.1	683.1	683.1	683.1	683.6
180°	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4



TEST NUMBER: P331971-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8
2.5°	1143.4	1145.2	1146.9	1147.7	1147.5	1147.4	1147.2	1147.0
5°	1137.4	1139.5	1141.8	1142.6	1142.2	1141.8	1141.3	1140.9
7.5°	1125.3	1127.3	1129.3	1130.1	1129.8	1129.5	1129.3	1129.1
10°	1114.3	1116.2	1118.1	1119.0	1118.5	1118.0	1117.7	1117.2
12.5°	1102.1	1103.5	1105.0	1105.6	1105.3	1105.0	1104.8	1104.6
15°	1080.2	1081.9	1083.7	1083.9	1082.6	1081.3	1080.1	1078.7
17.5°	1052.5	1053.8	1055.0	1055.4	1054.9	1054.4	1054.0	1053.5
20°	1032.1	1032.9	1033.9	1034.0	1033.3	1032.6	1032.0	1031.3
22.5°	1010.4	1011.2	1011.8	1011.7	1011.0	1010.1	1009.3	1008.4
25°	974.5	974.8	975.0	974.8	974.1	973.5	972.8	972.1
27.5°	936.3	936.5	936.7	936.3	935.6	934.7	933.9	933.0
30°	909.9	909.9	909.9	909.2	907.7	906.1	904.6	903.1
32.5°	882.2	881.0	879.8	878.7	877.9	877.0	876.2	875.4
35°	837.3	835.9	834.6	833.4	832.3	831.2	830.1	829.0
37.5°	790.7	789.1	787.6	786.5	785.7	785.0	784.3	783.6
40°	760.3	758.7	756.9	755.5	754.7	753.8	752.9	752.1
42.5°	728.8	727.0	725.3	724.0	723.1	722.2	721.3	720.5
45°	681.6	679.0	676.4	674.5	673.4	672.3	671.2	670.1
47.5°	632.0	629.4	626.8	625.0	624.1	623.1	622.2	621.1
50°	599.2	596.7	594.4	592.5	591.2	589.8	588.5	587.2
52.5°	565.9	563.8	561.8	560.2	558.8	557.5	556.2	554.9
55°	515.3	512.8	510.5	508.7	507.6	506.5	505.4	504.4
57.5°	465.4	463.4	461.2	459.5	458.2	456.9	455.6	454.4
60°	430.3	428.3	426.3	424.8	423.7	422.6	421.5	420.5
62.5°	396.3	394.4	392.4	391.1	390.3	389.6	388.8	388.0
65°	345.8	344.1	342.3	341.1	340.4	339.8	339.1	338.5
67.5°	295.8	294.3	292.7	291.4	290.6	289.6	288.7	287.8
70°	263.4	261.8	260.3	259.0	257.9	256.8	255.7	254.6
72.5°	230.5	229.2	227.9	226.9	226.3	225.7	225.2	224.6
75°	183.3	182.3	181.2	180.3	179.6	179.0	178.3	177.7
77.5°	139.2	138.5	137.7	137.4	137.4	137.4	137.4	137.4
80°	111.1	110.8	110.7	110.6	110.6	110.6	110.6	110.6
82.5°	85.5	85.1	84.6	84.4	84.3	84.1	83.9	83.7
85°	48.4	48.1	47.6	47.4	47.4	47.4	47.4	47.4
87.5°	19.8	19.7	19.6	19.6	19.7	19.7	19.8	19.8
90°	13.9	14.3	14.8	15.2	15.5	15.6	15.9	16.1
92.5°	21.4	21.8	22.1	22.3	22.1	22.0	21.9	21.7
95°	40.7	41.2	41.7	41.9	41.9	41.9	41.9	41.9
97.5°	63.3	63.9	64.5	64.7	64.7	64.6	64.6	64.5
100°	79.7	80.1	80.5	80.8	81.0	81.2	81.4	81.7
102.5°	98.7	99.1	99.3	99.5	99.5	99.4	99.4	99.3
105°	126.9	126.9	126.9	127.0	127.2	127.4	127.7	128.0
107.5°	157.4	157.8	158.2	158.3	158.2	158.1	157.9	157.8
110°	177.9	178.3	178.8	178.9	178.7	178.4	178.2	178.0





TEST NUMBER: P331971-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	198.2	198.8	199.3	199.6	199.6	199.5	199.5	199.4
115°	229.2	229.4	229.5	229.5	229.4	229.2	229.1	229.0
117.5°	260.6	260.5	260.5	260.3	260.0	259.7	259.4	259.0
120°	281.4	281.3	281.3	281.1	280.8	280.6	280.3	280.1
122.5°	302.6	302.3	302.0	301.6	301.3	301.0	300.7	300.3
125°	333.9	333.5	333.0	332.5	332.1	331.6	331.1	330.6
127.5°	365.0	364.3	363.6	363.1	362.5	361.9	361.4	360.8
130°	385.6	385.1	384.7	384.0	383.1	382.3	381.4	380.6
132.5°	405.6	405.0	404.4	403.9	403.2	402.6	401.9	401.2
135°	435.5	435.1	434.6	434.2	434.0	433.8	433.6	433.3
137.5°	464.9	464.4	463.9	463.4	463.0	462.5	462.0	461.6
140°	484.2	484.0	483.9	483.4	482.6	481.7	480.9	480.1
142.5°	502.2	502.1	502.0	501.6	501.0	500.3	499.6	499.0
145°	528.8	528.7	528.6	528.2	527.7	527.3	526.8	526.3
147.5°	553.8	553.8	553.8	553.5	552.8	552.0	551.4	550.6
150°	569.3	569.3	569.3	569.0	568.3	567.5	566.8	566.1
152.5°	583.5	583.7	583.9	583.6	583.1	582.4	581.8	581.2
155°	604.2	604.6	605.1	604.9	604.1	603.2	602.5	601.6
157.5°	622.0	622.5	622.9	622.8	622.2	621.5	620.9	620.2
160°	632.9	633.5	634.0	634.1	633.7	633.2	632.7	632.3
162.5°	643.2	643.9	644.4	644.3	643.6	642.8	642.1	641.3
165°	656.3	657.0	657.7	657.6	656.8	655.9	655.2	654.3
167.5°	666.8	667.6	668.4	668.4	667.6	666.8	666.1	665.3
170°	672.6	673.4	674.3	674.3	673.4	672.6	671.8	670.9
172.5°	677.1	677.9	678.6	678.6	677.8	676.9	676.1	675.2
175°	682.0	682.8	683.5	683.4	682.6	681.7	680.9	680.0
177.5°	684.3	684.9	685.4	685.3	684.7	684.0	683.3	682.7
180°	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4

(END OF REPORT)