

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332344

Luminaire Tested: **S123RDIP-S1000D805U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332344
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D805U835-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6866.9 lumens
Efficiency: N/A
Efficacy: 126.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332344

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332344

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58
1	100	96	92	89	93	90	87	84	78	76	73	67	65	64	57	56	55	50
2	92	85	79	74	85	79	74	70	69	65	62	60	57	54	51	49	47	43
3	84	75	68	62	78	70	64	59	61	57	53	53	50	47	46	43	41	37
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	41	38	36	32
5	71	60	52	46	66	56	49	44	50	44	40	43	39	36	37	34	32	29
6	66	54	46	40	61	51	44	39	45	39	35	39	35	32	34	31	28	25
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	31	28	25	23
8	57	45	37	32	53	42	35	31	38	32	28	33	29	25	29	25	23	20
9	53	41	34	29	49	39	32	27	35	29	25	31	26	23	27	23	21	19
10	50	38	31	26	46	36	29	25	32	27	23	28	24	21	25	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17111	17111	17111	17111
5°	20398	17184	15132	17184
10°	25468	17086	13671	17086
15°	29895	16912	12467	16912
20°	33364	16651	11443	16651
25°	32831	16376	10815	16376
30°	23599	16122	10167	16122
35°	15757	15792	9747	15792
40°	11609	15396	9313	15396
45°	9738	14700	8888	14700
50°	8592	13788	8296	13788
55°	7535	12746	7484	12746
60°	6710	11750	6857	11750
65°	5894	10677	6378	10677
70°	4626	9725	5825	9725
75°	4076	8492	5319	8492
80°	3546	7215	5232	7215
85°	2853	5805	5545	5805



TEST NUMBER: P332344

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.3	2.3
10°-20°	488.4	7.1
20°-30°	767.3	11.2
30°-40°	800.5	11.7
40°-50°	685.1	10.0
50°-60°	522.2	7.6
60°-70°	334.7	4.9
70°-80°	161.0	2.3
80°-90°	45.6	0.7
90°-100°	214.9	3.1
100°-110°	608.6	8.9
110°-120°	598.7	8.7
120°-130°	477.5	7.0
130°-140°	376.5	5.5
140°-150°	281.0	4.1
150°-160°	195.9	2.9
160°-170°	115.1	1.7
170°-180°	37.4	0.5
0°-30°	1412.0	20.6
0°-40°	2212.6	32.2
0°-60°	3419.8	49.8
0°-90°	3961.1	57.7
90°-120°	1422.2	20.7
90°-150°	2557.3	37.2
90°-180°	2906.0	42.3
0°-180°	6866.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1590	1590	1590	1590	1590	
5°	1888	1590	1400	1590	1888	195
15°	2683	1518	1119	1518	2683	761
25°	2764	1379	911	1379	2764	1188
35°	1199	1202	742	1202	1199	786
45°	640	966	584	966	640	503
55°	402	679	399	679	402	363
65°	231	419	250	419	231	228
75°	98	204	128	204	98	105
85°	23	47	45	47	23	27
90°	23	2	23	2	23	13
95°	91	27	91	27	91	163
105°	994	91	994	91	994	981
115°	1210	160	1210	160	1210	1175
125°	954	223	954	223	954	864
135°	773	261	773	261	773	600
145°	604	298	604	298	604	384
155°	501	338	501	338	501	234
165°	437	370	437	370	437	125
175°	393	385	393	385	393	38
180°	386	386	386	386	386	



TEST NUMBER: P332344

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1693.2	1695.3	1688.3	1687.2	1679.0	1676.8	1676.8	1665.4	1658.3	1649.1	1643.6
5°	1887.8	1898.7	1893.2	1881.0	1860.6	1855.8	1842.9	1822.5	1799.3	1770.7	1757.1
7.5°	2130.9	2145.7	2140.0	2121.1	2099.7	2082.4	2046.0	2012.1	1964.6	1922.9	1887.3
10°	2330.1	2314.5	2302.2	2283.9	2264.1	2232.1	2194.0	2141.6	2081.1	2033.4	1980.4
12.5°	2479.3	2476.7	2461.2	2442.3	2414.4	2384.0	2337.2	2273.4	2203.0	2134.2	2073.4
15°	2682.7	2686.7	2676.5	2656.8	2617.3	2563.6	2492.8	2466.3	2365.5	2290.7	2215.8
17.5°	2823.4	2822.6	2821.2	2793.9	2753.6	2715.3	2649.7	2579.9	2488.7	2383.2	2282.4
20°	2912.7	2905.9	2907.2	2876.6	2846.7	2802.4	2738.5	2637.1	2562.2	2440.4	2336.3
22.5°	2910.5	2909.1	2914.3	2903.8	2882.1	2848.2	2797.8	2712.2	2616.6	2493.7	2376.6
25°	2764.3	2758.9	2790.9	2799.7	2834.4	2840.5	2825.6	2778.6	2688.1	2561.5	2416.6
27.5°	2313.5	2310.5	2369.9	2444.2	2538.4	2611.6	2682.4	2716.6	2688.1	2597.5	2452.2
30°	1898.7	1962.7	1992.6	2100.1	2219.9	2362.8	2488.0	2607.1	2636.4	2596.9	2477.8
32.5°	1576.4	1632.2	1657.2	1749.5	1861.1	2028.5	2216.4	2385.0	2504.1	2534.3	2462.6
35°	1199.1	1199.8	1256.9	1297.8	1401.2	1573.4	1755.8	1981.7	2206.3	2376.4	2394.1
37.5°	956.8	960.2	994.8	1035.5	1113.1	1204.1	1364.7	1552.6	1812.0	2073.2	2226.3
40°	826.2	832.3	858.2	898.3	954.1	1022.8	1148.1	1325.0	1541.4	1832.0	2069.5
42.5°	742.3	752.3	765.6	796.5	831.1	895.4	996.7	1133.4	1330.2	1605.0	1879.0
45°	639.7	645.1	655.4	669.6	700.9	745.9	813.9	905.8	1069.1	1290.3	1564.5
47.5°	564.3	561.4	572.2	583.8	604.6	635.2	680.8	755.8	872.3	1049.8	1282.4
50°	513.1	512.4	519.9	528.8	548.5	571.0	608.4	664.9	757.4	904.4	1117.4
52.5°	465.2	467.8	473.1	484.1	498.4	516.5	550.1	590.8	670.3	797.2	974.8
55°	401.5	403.6	411.0	417.2	427.4	445.7	466.8	500.9	555.3	643.8	790.1
57.5°	347.6	346.7	353.9	355.4	366.9	381.9	398.2	424.7	464.1	529.9	628.4
60°	311.7	309.6	315.8	320.5	326.7	338.9	352.5	378.4	409.7	458.0	542.4
62.5°	279.0	278.1	282.6	287.3	292.4	303.5	315.0	334.8	359.6	400.3	467.3
65°	231.4	233.4	235.5	237.5	240.2	247.0	257.9	271.5	288.5	317.1	365.4
67.5°	181.8	183.9	184.6	188.8	194.6	198.9	205.5	217.6	229.5	253.6	281.1
70°	147.0	146.3	147.0	149.0	156.5	164.0	172.9	181.7	189.2	206.2	229.3
72.5°	126.3	125.1	126.9	127.3	130.9	133.0	138.6	146.9	156.5	168.1	184.7
75°	98.0	98.0	98.0	98.0	100.7	102.1	104.1	106.2	109.6	115.0	127.3
77.5°	72.4	72.5	73.5	74.2	74.7	75.5	76.8	78.8	80.0	82.9	88.2
80°	57.2	57.8	57.2	57.8	57.8	59.2	59.9	61.9	62.6	66.0	68.1
82.5°	43.0	42.6	43.0	43.7	43.7	45.1	45.2	46.7	46.8	48.6	50.6
85°	23.1	21.8	23.1	22.5	23.8	22.5	23.1	24.5	24.5	25.2	27.9
87.5°	10.0	11.2	10.0	10.4	10.5	10.8	10.6	10.4	11.4	11.0	11.1
90°	22.7	23.5	22.7	21.9	22.7	21.1	20.3	19.5	18.8	19.5	17.2
92.5°	37.7	39.1	38.3	40.7	42.1	46.1	52.2	65.8	90.7	120.2	132.3
95°	90.7	93.8	99.3	106.3	121.2	149.3	190.8	281.5	376.1	463.6	412.8
97.5°	246.9	253.6	274.7	309.9	367.6	461.1	562.0	701.6	768.7	718.5	526.0
100°	490.2	489.4	519.9	577.0	655.9	767.0	858.4	921.8	894.4	740.4	500.4
102.5°	719.1	737.1	762.6	807.8	869.2	939.6	992.9	994.9	900.7	699.7	462.8
105°	994.5	998.4	1023.4	1053.1	1089.1	1109.4	1094.5	1016.4	853.0	628.6	416.7
107.5°	1153.0	1160.2	1168.7	1178.7	1178.0	1150.2	1081.7	954.8	769.5	565.7	387.3
110°	1218.1	1219.6	1221.2	1214.9	1193.1	1138.3	1039.8	896.0	716.9	530.1	376.1



TEST NUMBER: P332344

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1231.2	1230.9	1225.0	1205.6	1165.5	1095.2	984.8	837.8	671.3	506.3	369.8
115°	1209.5	1205.6	1189.9	1155.5	1096.9	1011.7	896.7	760.7	616.1	480.8	367.5
117.5°	1140.4	1135.0	1112.5	1073.1	1012.0	925.5	822.3	704.9	582.8	465.8	368.9
120°	1082.8	1078.1	1059.4	1015.6	953.8	874.9	781.0	675.5	565.3	458.9	371.4
122.5°	1029.0	1023.1	1002.4	963.0	908.2	834.8	747.9	652.4	550.9	454.6	375.7
125°	953.8	948.3	928.8	894.4	844.4	781.8	706.8	621.5	532.4	448.8	382.3
127.5°	891.9	886.9	869.2	839.8	795.3	738.4	670.6	594.7	516.2	446.0	389.8
130°	856.9	850.6	834.2	806.1	764.6	711.5	648.1	577.8	507.4	444.1	394.8
132.5°	822.5	818.1	803.6	775.4	736.5	685.8	626.9	562.1	499.3	443.4	398.6
135°	773.2	767.7	753.7	730.2	691.9	647.3	596.5	541.0	488.6	442.5	404.2
137.5°	721.2	717.6	705.7	681.9	649.7	611.1	567.3	521.8	479.4	440.8	408.0
140°	684.9	685.7	673.1	651.3	621.5	587.9	550.4	510.5	473.8	440.2	410.5
142.5°	651.1	651.9	640.6	621.2	595.9	566.7	534.1	499.9	468.8	438.9	412.3
145°	604.3	602.8	596.5	580.1	560.6	537.9	512.9	487.1	462.1	437.0	413.6
147.5°	565.9	565.3	559.3	548.2	533.4	517.3	497.1	476.6	455.5	434.1	413.6
150°	543.4	543.4	538.7	530.1	518.3	503.5	487.1	469.1	451.1	431.6	413.6
152.5°	524.6	524.6	521.8	513.8	504.6	492.2	477.7	462.2	446.1	428.4	411.7
155°	501.1	500.4	498.8	492.5	485.5	476.1	464.4	451.9	438.6	423.0	409.7
157.5°	479.7	479.9	478.6	473.9	467.8	460.5	451.4	440.9	430.2	418.1	407.0
160°	466.0	466.7	466.7	462.1	456.6	451.1	443.3	434.7	424.5	414.4	405.8
162.5°	453.5	454.2	454.2	450.2	446.6	441.7	434.5	427.2	418.9	410.6	403.3
165°	437.0	437.0	437.8	434.7	431.6	427.7	422.2	417.5	411.2	405.0	399.5
167.5°	421.4	421.4	422.2	420.0	418.6	415.8	412.6	409.0	403.9	399.4	395.8
170°	412.0	412.0	412.8	411.2	410.5	408.9	405.8	403.4	399.5	395.6	393.3
172.5°	403.3	403.9	405.3	403.7	403.6	402.6	400.1	398.4	395.1	392.5	391.4
175°	393.3	394.0	394.8	394.0	394.0	394.0	392.5	391.7	390.1	388.6	388.6
177.5°	387.5	387.5	388.7	388.1	388.7	388.7	388.1	387.5	386.8	386.2	386.8
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332344

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1641.4	1639.8	1632.2	1623.5	1612.0	1604.4	1598.4	1595.2	1585.4	1573.4	1565.2
5°	1742.8	1722.4	1700.7	1674.1	1649.6	1624.4	1608.8	1590.4	1567.9	1542.8	1525.1
7.5°	1851.5	1811.4	1768.3	1723.8	1679.8	1640.4	1605.5	1575.7	1539.9	1503.8	1478.5
10°	1934.8	1876.2	1815.7	1753.7	1697.2	1644.2	1603.3	1563.2	1520.3	1478.8	1447.5
12.5°	2010.4	1933.4	1863.6	1787.5	1715.2	1651.8	1593.0	1545.8	1494.2	1449.9	1414.3
15°	2106.2	2027.3	1942.9	1827.2	1731.3	1651.0	1579.5	1517.6	1455.0	1400.5	1365.8
17.5°	2195.8	2077.0	1963.6	1867.1	1742.4	1642.1	1554.9	1480.8	1412.1	1354.4	1311.7
20°	2232.8	2117.8	1994.6	1871.5	1749.0	1636.7	1535.3	1453.6	1382.2	1316.8	1277.4
22.5°	2255.1	2124.9	1995.2	1862.8	1732.6	1616.0	1515.7	1425.9	1348.4	1286.3	1237.6
25°	2281.1	2126.0	1983.1	1852.4	1719.7	1593.1	1474.0	1378.8	1295.1	1229.0	1177.3
27.5°	2298.3	2115.8	1946.9	1801.6	1667.0	1541.0	1431.8	1330.8	1245.9	1176.1	1120.6
30°	2301.6	2107.6	1919.1	1761.9	1625.1	1509.4	1393.7	1297.1	1207.3	1133.1	1081.4
32.5°	2305.9	2087.5	1881.5	1714.5	1574.5	1459.9	1355.1	1262.8	1170.8	1097.7	1044.9
35°	2288.0	2076.3	1824.5	1632.6	1492.4	1381.5	1286.9	1201.8	1111.3	1040.5	986.8
37.5°	2210.6	2032.1	1765.4	1540.3	1393.7	1291.0	1213.9	1139.8	1056.7	980.4	929.7
40°	2132.8	1988.5	1719.7	1484.2	1331.1	1225.6	1156.2	1095.7	1015.4	943.9	889.5
42.5°	2016.8	1929.2	1676.2	1425.4	1260.3	1158.7	1100.1	1043.4	972.9	900.3	849.2
45°	1804.1	1815.7	1587.0	1331.8	1162.3	1060.3	1005.1	965.7	903.1	843.2	790.8
47.5°	1537.3	1645.5	1482.3	1232.0	1059.0	963.2	915.0	880.6	838.4	779.6	731.8
50°	1363.1	1517.6	1398.5	1165.1	994.3	899.0	851.3	823.4	786.7	740.4	694.8
52.5°	1202.5	1368.4	1297.2	1090.5	924.0	836.9	790.4	767.4	738.2	694.7	653.4
55°	980.6	1148.7	1132.4	977.9	818.7	740.4	705.0	679.2	659.4	626.8	594.1
57.5°	793.2	952.6	961.0	852.7	725.9	648.5	618.1	598.6	585.7	561.0	530.8
60°	675.1	821.4	850.0	768.3	659.4	591.4	561.4	545.8	535.6	515.8	492.7
62.5°	577.1	701.6	734.0	675.2	595.7	532.0	508.6	493.5	486.6	469.6	449.2
65°	441.7	545.1	576.4	543.7	502.2	451.2	432.1	419.2	413.1	403.6	388.6
67.5°	332.1	407.5	441.8	418.8	403.8	371.6	359.5	352.5	347.1	340.5	328.0
70°	266.8	322.6	358.0	351.8	339.6	322.6	313.7	309.0	303.5	298.1	287.2
72.5°	214.5	252.9	286.1	289.2	279.2	275.8	268.0	266.0	262.7	256.2	250.2
75°	142.2	168.8	191.9	200.8	204.8	208.2	204.8	204.2	203.5	198.0	194.6
77.5°	93.2	107.5	122.1	137.2	143.6	148.2	149.3	151.8	150.0	147.1	145.5
80°	71.5	74.9	85.1	98.0	108.2	112.3	115.0	116.4	115.7	115.0	112.3
82.5°	51.9	54.7	59.5	68.6	77.2	84.0	85.6	85.3	86.8	87.2	85.1
85°	27.9	28.6	29.9	31.3	36.1	43.6	45.6	47.0	48.3	48.3	44.2
87.5°	11.7	10.7	11.3	11.0	12.3	12.4	15.3	17.7	18.6	16.7	17.2
90°	14.9	12.5	10.2	8.6	7.0	4.7	3.1	1.6	3.1	4.7	7.0
92.5°	99.3	65.7	45.2	33.6	27.1	21.0	14.4	9.7	14.4	21.0	27.1
95°	284.6	168.1	101.6	71.1	50.8	37.5	28.9	26.6	28.9	37.5	50.8
97.5°	312.3	180.9	117.4	84.4	64.4	52.9	46.1	45.3	46.1	52.9	64.4
100°	294.7	179.0	124.3	93.8	75.1	64.1	58.6	57.9	58.6	64.1	75.1
102.5°	279.7	181.5	132.4	104.5	87.6	77.2	72.4	71.0	72.4	77.2	87.6
105°	268.9	188.4	146.2	122.0	107.1	97.7	93.0	90.7	93.0	97.7	107.1
107.5°	268.2	201.2	164.2	141.7	127.7	118.5	114.0	111.6	114.0	118.5	127.7
110°	271.3	211.9	176.7	154.8	141.5	132.9	129.0	126.7	129.0	132.9	141.5



TEST NUMBER: P332344

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	277.5	222.5	189.8	168.6	155.3	146.7	142.8	140.4	142.8	146.7	155.3
115°	287.7	240.0	210.3	189.2	175.9	168.1	163.4	160.3	163.4	168.1	175.9
117.5°	301.2	258.6	229.2	209.7	194.8	187.6	183.7	180.1	183.7	187.6	194.8
120°	311.2	270.5	242.4	222.8	208.0	200.1	196.2	193.9	196.2	200.1	208.0
122.5°	320.5	283.0	255.5	234.7	220.5	212.0	208.1	205.8	208.1	212.0	220.5
125°	335.4	301.0	273.6	252.5	237.7	229.1	224.4	222.8	224.4	229.1	237.7
127.5°	347.6	316.6	290.2	269.1	252.7	243.9	238.1	235.8	238.1	243.9	252.7
130°	355.7	326.0	300.2	279.1	262.7	253.3	246.3	243.9	246.3	253.3	262.7
132.5°	363.2	334.1	309.0	288.5	272.1	260.8	253.2	250.2	253.2	260.8	272.1
135°	372.9	346.3	322.1	301.0	284.6	272.9	264.3	261.1	264.3	272.9	284.6
137.5°	380.1	354.8	331.5	311.9	295.7	283.2	274.7	271.4	274.7	283.2	295.7
140°	383.9	360.4	337.7	318.2	302.6	290.1	282.2	278.3	282.2	290.1	302.6
142.5°	387.6	364.8	342.7	324.5	308.8	297.6	289.1	285.8	289.1	297.6	308.8
145°	391.7	370.6	350.3	332.3	319.0	307.3	300.2	297.9	300.2	307.3	319.0
147.5°	394.2	375.3	356.7	341.3	328.5	318.4	311.5	310.1	311.5	318.4	328.5
150°	394.8	378.4	360.4	346.3	335.4	325.2	319.0	318.2	319.0	325.2	335.4
152.5°	396.1	380.3	364.8	351.3	341.7	332.7	326.5	326.3	326.5	332.7	341.7
155°	396.4	383.9	370.6	359.6	351.0	343.2	338.5	338.5	338.5	343.2	351.0
157.5°	397.2	385.9	375.3	366.8	359.5	352.6	348.8	348.2	348.8	352.6	359.5
160°	397.2	387.8	378.4	370.6	365.1	358.9	355.7	355.7	355.7	358.9	365.1
162.5°	396.5	388.4	380.3	373.7	368.9	363.9	361.4	361.4	361.4	363.9	368.9
165°	394.8	389.3	383.1	377.6	374.5	370.6	369.0	369.8	369.0	370.6	374.5
167.5°	393.6	389.2	384.7	381.2	379.0	376.1	375.3	376.2	375.3	376.1	379.0
170°	391.7	388.6	384.7	383.1	381.5	379.2	378.4	380.0	378.4	379.2	381.5
172.5°	391.1	388.6	385.3	384.3	383.4	381.7	381.5	382.5	381.5	381.7	383.4
175°	389.3	387.8	386.2	385.4	385.4	383.9	384.7	385.4	384.7	383.9	385.4
177.5°	388.1	386.8	386.2	386.2	386.2	385.6	386.2	386.8	386.2	385.6	386.2
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332344

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1562.5	1555.4	1550.5	1539.6	1532.6	1524.9	1517.3	1522.2	1521.7	1521.1	1521.1
5°	1510.1	1494.4	1480.2	1461.8	1450.2	1435.9	1425.0	1423.7	1426.4	1416.9	1411.4
7.5°	1458.1	1436.7	1416.5	1396.2	1374.7	1357.5	1346.8	1341.7	1334.8	1328.9	1322.8
10°	1421.6	1396.5	1376.7	1351.5	1328.4	1308.0	1295.1	1286.2	1281.4	1276.7	1267.8
12.5°	1384.1	1359.4	1334.3	1305.8	1283.8	1260.1	1250.4	1240.5	1231.4	1226.0	1213.9
15°	1329.1	1297.1	1270.6	1240.6	1216.1	1193.0	1179.4	1159.6	1156.9	1150.1	1137.9
17.5°	1274.0	1239.2	1202.6	1180.5	1152.8	1128.7	1108.0	1101.4	1081.9	1074.6	1063.9
20°	1230.4	1198.4	1170.5	1141.3	1101.1	1078.6	1062.3	1053.5	1037.8	1028.3	1021.5
22.5°	1192.8	1160.3	1128.1	1093.9	1060.8	1035.6	1023.7	1009.9	1001.3	988.0	980.6
25°	1139.2	1103.8	1065.0	1028.3	1004.5	985.4	966.4	954.1	941.9	935.7	922.1
27.5°	1076.9	1039.9	1003.6	975.7	946.5	927.7	910.4	899.5	884.8	874.5	867.0
30°	1042.6	999.0	967.7	942.5	905.1	887.4	874.5	860.9	850.0	839.1	831.6
32.5°	1002.8	963.1	933.4	902.3	873.5	854.2	837.5	825.5	816.2	805.9	798.4
35°	940.5	907.2	876.5	845.2	824.1	804.4	784.7	774.4	765.6	756.1	749.3
37.5°	884.1	853.0	823.9	794.2	768.0	752.0	736.1	728.3	716.3	709.9	703.0
40°	849.3	818.7	787.4	758.8	731.6	719.3	705.0	693.5	682.6	677.8	670.3
42.5°	811.2	780.6	754.2	723.4	701.1	684.5	671.3	658.6	650.5	643.5	639.3
45°	754.7	727.5	701.6	671.0	649.9	635.6	620.6	609.1	601.6	596.8	589.3
47.5°	699.9	672.6	646.4	619.7	599.3	582.9	568.0	559.9	550.0	544.2	539.1
50°	660.1	635.6	607.7	583.2	562.8	546.5	534.2	524.0	515.2	507.7	504.3
52.5°	623.6	597.5	573.4	550.6	529.0	510.5	499.4	488.6	482.0	473.4	469.4
55°	563.5	538.3	517.9	495.4	474.3	458.7	445.1	435.5	428.7	419.2	413.8
57.5°	507.0	484.4	460.0	440.6	418.8	405.6	394.3	381.4	373.1	365.6	360.3
60°	468.9	443.0	421.9	403.6	384.5	367.5	357.3	347.1	338.2	330.7	326.0
62.5°	429.1	406.6	386.5	366.5	349.1	334.3	322.4	313.9	306.1	301.3	296.6
65°	368.2	350.5	330.1	313.7	297.4	286.5	277.0	269.5	264.0	260.6	256.6
67.5°	312.1	294.9	277.1	261.1	250.2	241.9	235.6	229.2	226.5	222.1	219.4
70°	275.6	257.9	242.3	230.0	219.1	213.0	208.9	204.2	201.4	196.0	193.3
72.5°	235.9	223.1	211.8	201.7	193.0	187.4	182.2	176.4	172.0	166.0	163.3
75°	185.8	174.2	165.4	158.6	153.1	145.6	138.1	132.0	130.0	127.9	127.3
77.5°	137.6	130.3	123.9	118.1	111.3	105.9	104.3	102.9	102.5	101.4	101.4
80°	108.2	101.4	96.6	89.8	85.7	85.7	85.7	84.4	85.1	85.1	85.1
82.5°	80.4	74.2	71.6	69.1	68.3	68.9	68.9	69.1	68.7	69.8	69.3
85°	41.5	42.2	43.6	42.9	43.6	43.6	44.9	44.2	44.9	43.6	44.9
87.5°	17.0	18.9	19.9	20.9	22.0	21.9	22.3	22.4	23.1	23.3	23.6
90°	8.6	10.2	12.5	14.9	17.2	19.5	18.8	19.5	20.3	21.1	22.7
92.5°	33.6	45.2	65.7	99.3	132.3	120.2	90.7	65.8	52.2	46.1	42.1
95°	71.1	101.6	168.1	284.6	412.8	463.6	376.1	281.5	190.8	149.3	121.2
97.5°	84.4	117.4	180.9	312.3	526.0	718.5	768.7	701.6	562.0	461.1	367.6
100°	93.8	124.3	179.0	294.7	500.4	740.4	894.4	921.8	858.4	767.0	655.9
102.5°	104.5	132.4	181.5	279.7	462.8	699.7	900.7	994.9	992.9	939.6	869.2
105°	122.0	146.2	188.4	268.9	416.7	628.6	853.0	1016.4	1094.5	1109.4	1089.1
107.5°	141.7	164.2	201.2	268.2	387.3	565.7	769.5	954.8	1081.7	1150.2	1178.0
110°	154.8	176.7	211.9	271.3	376.1	530.1	716.9	896.0	1039.8	1138.3	1193.1



TEST NUMBER: P332344

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	168.6	189.8	222.5	277.5	369.8	506.3	671.3	837.8	984.8	1095.2	1165.5
115°	189.2	210.3	240.0	287.7	367.5	480.8	616.1	760.7	896.7	1011.7	1096.9
117.5°	209.7	229.2	258.6	301.2	368.9	465.8	582.8	704.9	822.3	925.5	1012.0
120°	222.8	242.4	270.5	311.2	371.4	458.9	565.3	675.5	781.0	874.9	953.8
122.5°	234.7	255.5	283.0	320.5	375.7	454.6	550.9	652.4	747.9	834.8	908.2
125°	252.5	273.6	301.0	335.4	382.3	448.8	532.4	621.5	706.8	781.8	844.4
127.5°	269.1	290.2	316.6	347.6	389.8	446.0	516.2	594.7	670.6	738.4	795.3
130°	279.1	300.2	326.0	355.7	394.8	444.1	507.4	577.8	648.1	711.5	764.6
132.5°	288.5	309.0	334.1	363.2	398.6	443.4	499.3	562.1	626.9	685.8	736.5
135°	301.0	322.1	346.3	372.9	404.2	442.5	488.6	541.0	596.5	647.3	691.9
137.5°	311.9	331.5	354.8	380.1	408.0	440.8	479.4	521.8	567.3	611.1	649.7
140°	318.2	337.7	360.4	383.9	410.5	440.2	473.8	510.5	550.4	587.9	621.5
142.5°	324.5	342.7	364.8	387.6	412.3	438.9	468.8	499.9	534.1	566.7	595.9
145°	332.3	350.3	370.6	391.7	413.6	437.0	462.1	487.1	512.9	537.9	560.6
147.5°	341.3	356.7	375.3	394.2	413.6	434.1	455.5	476.6	497.1	517.3	533.4
150°	346.3	360.4	378.4	394.8	413.6	431.6	451.1	469.1	487.1	503.5	518.3
152.5°	351.3	364.8	380.3	396.1	411.7	428.4	446.1	462.2	477.7	492.2	504.6
155°	359.6	370.6	383.9	396.4	409.7	423.0	438.6	451.9	464.4	476.1	485.5
157.5°	366.8	375.3	385.9	397.2	407.0	418.1	430.2	440.9	451.4	460.5	467.8
160°	370.6	378.4	387.8	397.2	405.8	414.4	424.5	434.7	443.3	451.1	456.6
162.5°	373.7	380.3	388.4	396.5	403.3	410.6	418.9	427.2	434.5	441.7	446.6
165°	377.6	383.1	389.3	394.8	399.5	405.0	411.2	417.5	422.2	427.7	431.6
167.5°	381.2	384.7	389.2	393.6	395.8	399.4	403.9	409.0	412.6	415.8	418.6
170°	383.1	384.7	388.6	391.7	393.3	395.6	399.5	403.4	405.8	408.9	410.5
172.5°	384.3	385.3	388.6	391.1	391.4	392.5	395.1	398.4	400.1	402.6	403.6
175°	385.4	386.2	387.8	389.3	388.6	388.6	390.1	391.7	392.5	394.0	394.0
177.5°	386.2	386.2	386.8	388.1	386.8	386.2	386.8	387.5	388.1	388.7	388.7
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332344

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1514.6	1514.0	1514.6	1512.4	1514.6	1514.0	1514.6	1521.1	1521.1	1521.7	1522.2
5°	1409.4	1408.7	1406.7	1400.5	1406.7	1408.7	1409.4	1411.4	1416.9	1426.4	1423.7
7.5°	1317.5	1316.6	1310.6	1310.7	1310.6	1316.6	1317.5	1322.8	1328.9	1334.8	1341.7
10°	1263.1	1263.7	1255.6	1250.8	1255.6	1263.7	1263.1	1267.8	1276.7	1281.4	1286.2
12.5°	1210.3	1207.1	1200.6	1195.3	1200.6	1207.1	1210.3	1213.9	1226.0	1231.4	1240.5
15°	1140.6	1133.8	1117.4	1118.8	1117.4	1133.8	1140.6	1137.9	1150.1	1156.9	1159.6
17.5°	1058.5	1053.5	1053.2	1043.7	1053.2	1053.5	1058.5	1063.9	1074.6	1081.9	1101.4
20°	1010.6	1007.2	1008.5	999.0	1008.5	1007.2	1010.6	1021.5	1028.3	1037.8	1053.5
22.5°	973.0	969.6	963.9	960.9	963.9	969.6	973.0	980.6	988.0	1001.3	1009.9
25°	918.0	912.6	907.2	910.6	907.2	912.6	918.0	922.1	935.7	941.9	954.1
27.5°	863.1	859.0	853.5	852.8	853.5	859.0	863.1	867.0	874.5	884.8	899.5
30°	828.2	824.1	821.4	818.0	821.4	824.1	828.2	831.6	839.1	850.0	860.9
32.5°	792.8	792.0	787.1	786.4	787.1	792.0	792.8	798.4	805.9	816.2	825.5
35°	746.5	742.5	741.1	741.8	741.1	742.5	746.5	749.3	756.1	765.6	774.4
37.5°	702.6	697.1	694.7	692.2	694.7	697.1	702.6	703.0	709.9	716.3	728.3
40°	671.0	665.6	664.2	662.8	664.2	665.6	671.0	670.3	677.8	682.6	693.5
42.5°	635.6	633.4	632.6	630.2	632.6	633.4	635.6	639.3	643.5	650.5	658.6
45°	587.3	586.6	582.5	583.9	582.5	586.6	587.3	589.3	596.8	601.6	609.1
47.5°	536.4	533.4	530.5	532.4	530.5	533.4	536.4	539.1	544.2	550.0	559.9
50°	501.6	500.2	494.1	495.4	494.1	500.2	501.6	504.3	507.7	515.2	524.0
52.5°	466.7	461.5	459.2	458.4	459.2	461.5	466.7	469.4	473.4	482.0	488.6
55°	409.0	402.9	400.2	398.8	400.2	402.9	409.0	413.8	419.2	428.7	435.5
57.5°	352.4	350.7	348.6	350.1	348.6	350.7	352.4	360.3	365.6	373.1	381.4
60°	319.2	319.2	319.2	318.5	319.2	319.2	319.2	326.0	330.7	338.2	347.1
62.5°	293.6	291.9	291.4	292.4	291.4	291.9	293.6	296.6	301.3	306.1	313.9
65°	254.5	253.8	251.1	250.4	251.1	253.8	254.5	256.6	260.6	264.0	269.5
67.5°	217.6	215.2	214.4	213.4	214.4	215.2	217.6	219.4	222.1	226.5	229.2
70°	189.9	188.5	184.4	185.1	184.4	188.5	189.9	193.3	196.0	201.4	204.2
72.5°	159.9	158.6	157.7	156.8	157.7	158.6	159.9	163.3	166.0	172.0	176.4
75°	126.6	125.9	125.2	127.9	125.2	125.9	126.6	127.3	127.9	130.0	132.0
77.5°	101.4	101.4	101.8	100.7	101.8	101.4	101.4	101.4	101.4	102.5	102.9
80°	85.1	85.1	84.4	84.4	84.4	85.1	85.1	85.1	85.1	85.1	84.4
82.5°	68.2	68.7	69.1	68.1	69.1	68.7	68.2	69.3	69.8	68.7	69.1
85°	44.9	44.2	45.6	44.9	45.6	44.2	44.9	44.9	43.6	44.9	44.2
87.5°	24.5	23.6	23.7	24.1	23.7	23.6	24.5	23.6	23.3	23.1	22.4
90°	21.9	22.7	23.5	22.7	23.5	22.7	21.9	22.7	21.1	20.3	19.5
92.5°	40.7	38.3	39.1	37.7	39.1	38.3	40.7	42.1	46.1	52.2	65.8
95°	106.3	99.3	93.8	90.7	93.8	99.3	106.3	121.2	149.3	190.8	281.5
97.5°	309.9	274.7	253.6	246.9	253.6	274.7	309.9	367.6	461.1	562.0	701.6
100°	577.0	519.9	489.4	490.2	489.4	519.9	577.0	655.9	767.0	858.4	921.8
102.5°	807.8	762.6	737.1	719.1	737.1	762.6	807.8	869.2	939.6	992.9	994.9
105°	1053.1	1023.4	998.4	994.5	998.4	1023.4	1053.1	1089.1	1109.4	1094.5	1016.4
107.5°	1178.7	1168.7	1160.2	1153.0	1160.2	1168.7	1178.7	1178.0	1150.2	1081.7	954.8
110°	1214.9	1221.2	1219.6	1218.1	1219.6	1221.2	1214.9	1193.1	1138.3	1039.8	896.0



TEST NUMBER: P332344

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1205.6	1225.0	1230.9	1231.2	1230.9	1225.0	1205.6	1165.5	1095.2	984.8	837.8
115°	1155.5	1189.9	1205.6	1209.5	1205.6	1189.9	1155.5	1096.9	1011.7	896.7	760.7
117.5°	1073.1	1112.5	1135.0	1140.4	1135.0	1112.5	1073.1	1012.0	925.5	822.3	704.9
120°	1015.6	1059.4	1078.1	1082.8	1078.1	1059.4	1015.6	953.8	874.9	781.0	675.5
122.5°	963.0	1002.4	1023.1	1029.0	1023.1	1002.4	963.0	908.2	834.8	747.9	652.4
125°	894.4	928.8	948.3	953.8	948.3	928.8	894.4	844.4	781.8	706.8	621.5
127.5°	839.8	869.2	886.9	891.9	886.9	869.2	839.8	795.3	738.4	670.6	594.7
130°	806.1	834.2	850.6	856.9	850.6	834.2	806.1	764.6	711.5	648.1	577.8
132.5°	775.4	803.6	818.1	822.5	818.1	803.6	775.4	736.5	685.8	626.9	562.1
135°	730.2	753.7	767.7	773.2	767.7	753.7	730.2	691.9	647.3	596.5	541.0
137.5°	681.9	705.7	717.6	721.2	717.6	705.7	681.9	649.7	611.1	567.3	521.8
140°	651.3	673.1	685.7	684.9	685.7	673.1	651.3	621.5	587.9	550.4	510.5
142.5°	621.2	640.6	651.9	651.1	651.9	640.6	621.2	595.9	566.7	534.1	499.9
145°	580.1	596.5	602.8	604.3	602.8	596.5	580.1	560.6	537.9	512.9	487.1
147.5°	548.2	559.3	565.3	565.9	565.3	559.3	548.2	533.4	517.3	497.1	476.6
150°	530.1	538.7	543.4	543.4	543.4	538.7	530.1	518.3	503.5	487.1	469.1
152.5°	513.8	521.8	524.6	524.6	524.6	521.8	513.8	504.6	492.2	477.7	462.2
155°	492.5	498.8	500.4	501.1	500.4	498.8	492.5	485.5	476.1	464.4	451.9
157.5°	473.9	478.6	479.9	479.7	479.9	478.6	473.9	467.8	460.5	451.4	440.9
160°	462.1	466.7	466.7	466.0	466.7	466.7	462.1	456.6	451.1	443.3	434.7
162.5°	450.2	454.2	454.2	453.5	454.2	454.2	450.2	446.6	441.7	434.5	427.2
165°	434.7	437.8	437.0	437.0	437.0	437.8	434.7	431.6	427.7	422.2	417.5
167.5°	420.0	422.2	421.4	421.4	421.4	422.2	420.0	418.6	415.8	412.6	409.0
170°	411.2	412.8	412.0	412.0	412.0	412.8	411.2	410.5	408.9	405.8	403.4
172.5°	403.7	405.3	403.9	403.3	403.9	405.3	403.7	403.6	402.6	400.1	398.4
175°	394.0	394.8	394.0	393.3	394.0	394.8	394.0	394.0	394.0	392.5	391.7
177.5°	388.1	388.7	387.5	387.5	387.5	388.7	388.1	388.7	388.7	388.1	387.5
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332344

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1517.3	1524.9	1532.6	1539.6	1550.5	1555.4	1562.5	1565.2	1573.4	1585.4	1595.2
5°	1425.0	1435.9	1450.2	1461.8	1480.2	1494.4	1510.1	1525.1	1542.8	1567.9	1590.4
7.5°	1346.8	1357.5	1374.7	1396.2	1416.5	1436.7	1458.1	1478.5	1503.8	1539.9	1575.7
10°	1295.1	1308.0	1328.4	1351.5	1376.7	1396.5	1421.6	1447.5	1478.8	1520.3	1563.2
12.5°	1250.4	1260.1	1283.8	1305.8	1334.3	1359.4	1384.1	1414.3	1449.9	1494.2	1545.8
15°	1179.4	1193.0	1216.1	1240.6	1270.6	1297.1	1329.1	1365.8	1400.5	1455.0	1517.6
17.5°	1108.0	1128.7	1152.8	1180.5	1202.6	1239.2	1274.0	1311.7	1354.4	1412.1	1480.8
20°	1062.3	1078.6	1101.1	1141.3	1170.5	1198.4	1230.4	1277.4	1316.8	1382.2	1453.6
22.5°	1023.7	1035.6	1060.8	1093.9	1128.1	1160.3	1192.8	1237.6	1286.3	1348.4	1425.9
25°	966.4	985.4	1004.5	1028.3	1065.0	1103.8	1139.2	1177.3	1229.0	1295.1	1378.8
27.5°	910.4	927.7	946.5	975.7	1003.6	1039.9	1076.9	1120.6	1176.1	1245.9	1330.8
30°	874.5	887.4	905.1	942.5	967.7	999.0	1042.6	1081.4	1133.1	1207.3	1297.1
32.5°	837.5	854.2	873.5	902.3	933.4	963.1	1002.8	1044.9	1097.7	1170.8	1262.8
35°	784.7	804.4	824.1	845.2	876.5	907.2	940.5	986.8	1040.5	1111.3	1201.8
37.5°	736.1	752.0	768.0	794.2	823.9	853.0	884.1	929.7	980.4	1056.7	1139.8
40°	705.0	719.3	731.6	758.8	787.4	818.7	849.3	889.5	943.9	1015.4	1095.7
42.5°	671.3	684.5	701.1	723.4	754.2	780.6	811.2	849.2	900.3	972.9	1043.4
45°	620.6	635.6	649.9	671.0	701.6	727.5	754.7	790.8	843.2	903.1	965.7
47.5°	568.0	582.9	599.3	619.7	646.4	672.6	699.9	731.8	779.6	838.4	880.6
50°	534.2	546.5	562.8	583.2	607.7	635.6	660.1	694.8	740.4	786.7	823.4
52.5°	499.4	510.5	529.0	550.6	573.4	597.5	623.6	653.4	694.7	738.2	767.4
55°	445.1	458.7	474.3	495.4	517.9	538.3	563.5	594.1	626.8	659.4	679.2
57.5°	394.3	405.6	418.8	440.6	460.0	484.4	507.0	530.8	561.0	585.7	598.6
60°	357.3	367.5	384.5	403.6	421.9	443.0	468.9	492.7	515.8	535.6	545.8
62.5°	322.4	334.3	349.1	366.5	386.5	406.6	429.1	449.2	469.6	486.6	493.5
65°	277.0	286.5	297.4	313.7	330.1	350.5	368.2	388.6	403.6	413.1	419.2
67.5°	235.6	241.9	250.2	261.1	277.1	294.9	312.1	328.0	340.5	347.1	352.5
70°	208.9	213.0	219.1	230.0	242.3	257.9	275.6	287.2	298.1	303.5	309.0
72.5°	182.2	187.4	193.0	201.7	211.8	223.1	235.9	250.2	256.2	262.7	266.0
75°	138.1	145.6	153.1	158.6	165.4	174.2	185.8	194.6	198.0	203.5	204.2
77.5°	104.3	105.9	111.3	118.1	123.9	130.3	137.6	145.5	147.1	150.0	151.8
80°	85.7	85.7	85.7	89.8	96.6	101.4	108.2	112.3	115.0	115.7	116.4
82.5°	68.9	68.9	68.3	69.1	71.6	74.2	80.4	85.1	87.2	86.8	85.3
85°	44.9	43.6	43.6	42.9	43.6	42.2	41.5	44.2	48.3	48.3	47.0
87.5°	22.3	21.9	22.0	20.9	19.9	18.9	17.0	17.2	16.7	18.6	17.7
90°	18.8	19.5	17.2	14.9	12.5	10.2	8.6	7.0	4.7	3.1	1.6
92.5°	90.7	120.2	132.3	99.3	65.7	45.2	33.6	27.1	21.0	14.4	9.7
95°	376.1	463.6	412.8	284.6	168.1	101.6	71.1	50.8	37.5	28.9	26.6
97.5°	768.7	718.5	526.0	312.3	180.9	117.4	84.4	64.4	52.9	46.1	45.3
100°	894.4	740.4	500.4	294.7	179.0	124.3	93.8	75.1	64.1	58.6	57.9
102.5°	900.7	699.7	462.8	279.7	181.5	132.4	104.5	87.6	77.2	72.4	71.0
105°	853.0	628.6	416.7	268.9	188.4	146.2	122.0	107.1	97.7	93.0	90.7
107.5°	769.5	565.7	387.3	268.2	201.2	164.2	141.7	127.7	118.5	114.0	111.6
110°	716.9	530.1	376.1	271.3	211.9	176.7	154.8	141.5	132.9	129.0	126.7



TEST NUMBER: P332344

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	671.3	506.3	369.8	277.5	222.5	189.8	168.6	155.3	146.7	142.8	140.4
115°	616.1	480.8	367.5	287.7	240.0	210.3	189.2	175.9	168.1	163.4	160.3
117.5°	582.8	465.8	368.9	301.2	258.6	229.2	209.7	194.8	187.6	183.7	180.1
120°	565.3	458.9	371.4	311.2	270.5	242.4	222.8	208.0	200.1	196.2	193.9
122.5°	550.9	454.6	375.7	320.5	283.0	255.5	234.7	220.5	212.0	208.1	205.8
125°	532.4	448.8	382.3	335.4	301.0	273.6	252.5	237.7	229.1	224.4	222.8
127.5°	516.2	446.0	389.8	347.6	316.6	290.2	269.1	252.7	243.9	238.1	235.8
130°	507.4	444.1	394.8	355.7	326.0	300.2	279.1	262.7	253.3	246.3	243.9
132.5°	499.3	443.4	398.6	363.2	334.1	309.0	288.5	272.1	260.8	253.2	250.2
135°	488.6	442.5	404.2	372.9	346.3	322.1	301.0	284.6	272.9	264.3	261.1
137.5°	479.4	440.8	408.0	380.1	354.8	331.5	311.9	295.7	283.2	274.7	271.4
140°	473.8	440.2	410.5	383.9	360.4	337.7	318.2	302.6	290.1	282.2	278.3
142.5°	468.8	438.9	412.3	387.6	364.8	342.7	324.5	308.8	297.6	289.1	285.8
145°	462.1	437.0	413.6	391.7	370.6	350.3	332.3	319.0	307.3	300.2	297.9
147.5°	455.5	434.1	413.6	394.2	375.3	356.7	341.3	328.5	318.4	311.5	310.1
150°	451.1	431.6	413.6	394.8	378.4	360.4	346.3	335.4	325.2	319.0	318.2
152.5°	446.1	428.4	411.7	396.1	380.3	364.8	351.3	341.7	332.7	326.5	326.3
155°	438.6	423.0	409.7	396.4	383.9	370.6	359.6	351.0	343.2	338.5	338.5
157.5°	430.2	418.1	407.0	397.2	385.9	375.3	366.8	359.5	352.6	348.8	348.2
160°	424.5	414.4	405.8	397.2	387.8	378.4	370.6	365.1	358.9	355.7	355.7
162.5°	418.9	410.6	403.3	396.5	388.4	380.3	373.7	368.9	363.9	361.4	361.4
165°	411.2	405.0	399.5	394.8	389.3	383.1	377.6	374.5	370.6	369.0	369.8
167.5°	403.9	399.4	395.8	393.6	389.2	384.7	381.2	379.0	376.1	375.3	376.2
170°	399.5	395.6	393.3	391.7	388.6	384.7	383.1	381.5	379.2	378.4	380.0
172.5°	395.1	392.5	391.4	391.1	388.6	385.3	384.3	383.4	381.7	381.5	382.5
175°	390.1	388.6	388.6	389.3	387.8	386.2	385.4	385.4	383.9	384.7	385.4
177.5°	386.8	386.2	386.8	388.1	386.8	386.2	386.2	386.2	385.6	386.2	386.8
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332344

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1598.4	1604.4	1612.0	1623.5	1632.2	1639.8	1641.4	1643.6	1649.1	1658.3	1665.4
5°	1608.8	1624.4	1649.6	1674.1	1700.7	1722.4	1742.8	1757.1	1770.7	1799.3	1822.5
7.5°	1605.5	1640.4	1679.8	1723.8	1768.3	1811.4	1851.5	1887.3	1922.9	1964.6	2012.1
10°	1603.3	1644.2	1697.2	1753.7	1815.7	1876.2	1934.8	1980.4	2033.4	2081.1	2141.6
12.5°	1593.0	1651.8	1715.2	1787.5	1863.6	1933.4	2010.4	2073.4	2134.2	2203.0	2273.4
15°	1579.5	1651.0	1731.3	1827.2	1942.9	2027.3	2106.2	2215.8	2290.7	2365.5	2466.3
17.5°	1554.9	1642.1	1742.4	1867.1	1963.6	2077.0	2195.8	2282.4	2383.2	2488.7	2579.9
20°	1535.3	1636.7	1749.0	1871.5	1994.6	2117.8	2232.8	2336.3	2440.4	2562.2	2637.1
22.5°	1515.7	1616.0	1732.6	1862.8	1995.2	2124.9	2255.1	2376.6	2493.7	2616.6	2712.2
25°	1474.0	1593.1	1719.7	1852.4	1983.1	2126.0	2281.1	2416.6	2561.5	2688.1	2778.6
27.5°	1431.8	1541.0	1667.0	1801.6	1946.9	2115.8	2298.3	2452.2	2597.5	2688.1	2716.6
30°	1393.7	1509.4	1625.1	1761.9	1919.1	2107.6	2301.6	2477.8	2596.9	2636.4	2607.1
32.5°	1355.1	1459.9	1574.5	1714.5	1881.5	2087.5	2305.9	2462.6	2534.3	2504.1	2385.0
35°	1286.9	1381.5	1492.4	1632.6	1824.5	2076.3	2288.0	2394.1	2376.4	2206.3	1981.7
37.5°	1213.9	1291.0	1393.7	1540.3	1765.4	2032.1	2210.6	2226.3	2073.2	1812.0	1552.6
40°	1156.2	1225.6	1331.1	1484.2	1719.7	1988.5	2132.8	2069.5	1832.0	1541.4	1325.0
42.5°	1100.1	1158.7	1260.3	1425.4	1676.2	1929.2	2016.8	1879.0	1605.0	1330.2	1133.4
45°	1005.1	1060.3	1162.3	1331.8	1587.0	1815.7	1804.1	1564.5	1290.3	1069.1	905.8
47.5°	915.0	963.2	1059.0	1232.0	1482.3	1645.5	1537.3	1282.4	1049.8	872.3	755.8
50°	851.3	899.0	994.3	1165.1	1398.5	1517.6	1363.1	1117.4	904.4	757.4	664.9
52.5°	790.4	836.9	924.0	1090.5	1297.2	1368.4	1202.5	974.8	797.2	670.3	590.8
55°	705.0	740.4	818.7	977.9	1132.4	1148.7	980.6	790.1	643.8	555.3	500.9
57.5°	618.1	648.5	725.9	852.7	961.0	952.6	793.2	628.4	529.9	464.1	424.7
60°	561.4	591.4	659.4	768.3	850.0	821.4	675.1	542.4	458.0	409.7	378.4
62.5°	508.6	532.0	595.7	675.2	734.0	701.6	577.1	467.3	400.3	359.6	334.8
65°	432.1	451.2	502.2	543.7	576.4	545.1	441.7	365.4	317.1	288.5	271.5
67.5°	359.5	371.6	403.8	418.8	441.8	407.5	332.1	281.1	253.6	229.5	217.6
70°	313.7	322.6	339.6	351.8	358.0	322.6	266.8	229.3	206.2	189.2	181.7
72.5°	268.0	275.8	279.2	289.2	286.1	252.9	214.5	184.7	168.1	156.5	146.9
75°	204.8	208.2	204.8	200.8	191.9	168.8	142.2	127.3	115.0	109.6	106.2
77.5°	149.3	148.2	143.6	137.2	122.1	107.5	93.2	88.2	82.9	80.0	78.8
80°	115.0	112.3	108.2	98.0	85.1	74.9	71.5	68.1	66.0	62.6	61.9
82.5°	85.6	84.0	77.2	68.6	59.5	54.7	51.9	50.6	48.6	46.8	46.7
85°	45.6	43.6	36.1	31.3	29.9	28.6	27.9	27.9	25.2	24.5	24.5
87.5°	15.3	12.4	12.3	11.0	11.3	10.7	11.7	11.1	11.0	11.4	10.4
90°	3.1	4.7	7.0	8.6	10.2	12.5	14.9	17.2	19.5	18.8	19.5
92.5°	14.4	21.0	27.1	33.6	45.2	65.7	99.3	132.3	120.2	90.7	65.8
95°	28.9	37.5	50.8	71.1	101.6	168.1	284.6	412.8	463.6	376.1	281.5
97.5°	46.1	52.9	64.4	84.4	117.4	180.9	312.3	526.0	718.5	768.7	701.6
100°	58.6	64.1	75.1	93.8	124.3	179.0	294.7	500.4	740.4	894.4	921.8
102.5°	72.4	77.2	87.6	104.5	132.4	181.5	279.7	462.8	699.7	900.7	994.9
105°	93.0	97.7	107.1	122.0	146.2	188.4	268.9	416.7	628.6	853.0	1016.4
107.5°	114.0	118.5	127.7	141.7	164.2	201.2	268.2	387.3	565.7	769.5	954.8
110°	129.0	132.9	141.5	154.8	176.7	211.9	271.3	376.1	530.1	716.9	896.0



TEST NUMBER: P332344

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	142.8	146.7	155.3	168.6	189.8	222.5	277.5	369.8	506.3	671.3	837.8
115°	163.4	168.1	175.9	189.2	210.3	240.0	287.7	367.5	480.8	616.1	760.7
117.5°	183.7	187.6	194.8	209.7	229.2	258.6	301.2	368.9	465.8	582.8	704.9
120°	196.2	200.1	208.0	222.8	242.4	270.5	311.2	371.4	458.9	565.3	675.5
122.5°	208.1	212.0	220.5	234.7	255.5	283.0	320.5	375.7	454.6	550.9	652.4
125°	224.4	229.1	237.7	252.5	273.6	301.0	335.4	382.3	448.8	532.4	621.5
127.5°	238.1	243.9	252.7	269.1	290.2	316.6	347.6	389.8	446.0	516.2	594.7
130°	246.3	253.3	262.7	279.1	300.2	326.0	355.7	394.8	444.1	507.4	577.8
132.5°	253.2	260.8	272.1	288.5	309.0	334.1	363.2	398.6	443.4	499.3	562.1
135°	264.3	272.9	284.6	301.0	322.1	346.3	372.9	404.2	442.5	488.6	541.0
137.5°	274.7	283.2	295.7	311.9	331.5	354.8	380.1	408.0	440.8	479.4	521.8
140°	282.2	290.1	302.6	318.2	337.7	360.4	383.9	410.5	440.2	473.8	510.5
142.5°	289.1	297.6	308.8	324.5	342.7	364.8	387.6	412.3	438.9	468.8	499.9
145°	300.2	307.3	319.0	332.3	350.3	370.6	391.7	413.6	437.0	462.1	487.1
147.5°	311.5	318.4	328.5	341.3	356.7	375.3	394.2	413.6	434.1	455.5	476.6
150°	319.0	325.2	335.4	346.3	360.4	378.4	394.8	413.6	431.6	451.1	469.1
152.5°	326.5	332.7	341.7	351.3	364.8	380.3	396.1	411.7	428.4	446.1	462.2
155°	338.5	343.2	351.0	359.6	370.6	383.9	396.4	409.7	423.0	438.6	451.9
157.5°	348.8	352.6	359.5	366.8	375.3	385.9	397.2	407.0	418.1	430.2	440.9
160°	355.7	358.9	365.1	370.6	378.4	387.8	397.2	405.8	414.4	424.5	434.7
162.5°	361.4	363.9	368.9	373.7	380.3	388.4	396.5	403.3	410.6	418.9	427.2
165°	369.0	370.6	374.5	377.6	383.1	389.3	394.8	399.5	405.0	411.2	417.5
167.5°	375.3	376.1	379.0	381.2	384.7	389.2	393.6	395.8	399.4	403.9	409.0
170°	378.4	379.2	381.5	383.1	384.7	388.6	391.7	393.3	395.6	399.5	403.4
172.5°	381.5	381.7	383.4	384.3	385.3	388.6	391.1	391.4	392.5	395.1	398.4
175°	384.7	383.9	385.4	385.4	386.2	387.8	389.3	388.6	388.6	390.1	391.7
177.5°	386.2	385.6	386.2	386.2	386.2	386.8	388.1	386.8	386.2	386.8	387.5
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332344

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1676.8	1676.8	1679.0	1687.2	1688.3	1695.3	1693.2
5°	1842.9	1855.8	1860.6	1881.0	1893.2	1898.7	1887.8
7.5°	2046.0	2082.4	2099.7	2121.1	2140.0	2145.7	2130.9
10°	2194.0	2232.1	2264.1	2283.9	2302.2	2314.5	2330.1
12.5°	2337.2	2384.0	2414.4	2442.3	2461.2	2476.7	2479.3
15°	2492.8	2563.6	2617.3	2656.8	2676.5	2686.7	2682.7
17.5°	2649.7	2715.3	2753.6	2793.9	2821.2	2822.6	2823.4
20°	2738.5	2802.4	2846.7	2876.6	2907.2	2905.9	2912.7
22.5°	2797.8	2848.2	2882.1	2903.8	2914.3	2909.1	2910.5
25°	2825.6	2840.5	2834.4	2799.7	2790.9	2758.9	2764.3
27.5°	2682.4	2611.6	2538.4	2444.2	2369.9	2310.5	2313.5
30°	2488.0	2362.8	2219.9	2100.1	1992.6	1962.7	1898.7
32.5°	2216.4	2028.5	1861.1	1749.5	1657.2	1632.2	1576.4
35°	1755.8	1573.4	1401.2	1297.8	1256.9	1199.8	1199.1
37.5°	1364.7	1204.1	1113.1	1035.5	994.8	960.2	956.8
40°	1148.1	1022.8	954.1	898.3	858.2	832.3	826.2
42.5°	996.7	895.4	831.1	796.5	765.6	752.3	742.3
45°	813.9	745.9	700.9	669.6	655.4	645.1	639.7
47.5°	680.8	635.2	604.6	583.8	572.2	561.4	564.3
50°	608.4	571.0	548.5	528.8	519.9	512.4	513.1
52.5°	550.1	516.5	498.4	484.1	473.1	467.8	465.2
55°	466.8	445.7	427.4	417.2	411.0	403.6	401.5
57.5°	398.2	381.9	366.9	355.4	353.9	346.7	347.6
60°	352.5	338.9	326.7	320.5	315.8	309.6	311.7
62.5°	315.0	303.5	292.4	287.3	282.6	278.1	279.0
65°	257.9	247.0	240.2	237.5	235.5	233.4	231.4
67.5°	205.5	198.9	194.6	188.8	184.6	183.9	181.8
70°	172.9	164.0	156.5	149.0	147.0	146.3	147.0
72.5°	138.6	133.0	130.9	127.3	126.9	125.1	126.3
75°	104.1	102.1	100.7	98.0	98.0	98.0	98.0
77.5°	76.8	75.5	74.7	74.2	73.5	72.5	72.4
80°	59.9	59.2	57.8	57.8	57.2	57.8	57.2
82.5°	45.2	45.1	43.7	43.7	43.0	42.6	43.0
85°	23.1	22.5	23.8	22.5	23.1	21.8	23.1
87.5°	10.6	10.8	10.5	10.4	10.0	11.2	10.0
90°	20.3	21.1	22.7	21.9	22.7	23.5	22.7
92.5°	52.2	46.1	42.1	40.7	38.3	39.1	37.7
95°	190.8	149.3	121.2	106.3	99.3	93.8	90.7
97.5°	562.0	461.1	367.6	309.9	274.7	253.6	246.9
100°	858.4	767.0	655.9	577.0	519.9	489.4	490.2
102.5°	992.9	939.6	869.2	807.8	762.6	737.1	719.1
105°	1094.5	1109.4	1089.1	1053.1	1023.4	998.4	994.5
107.5°	1081.7	1150.2	1178.0	1178.7	1168.7	1160.2	1153.0
110°	1039.8	1138.3	1193.1	1214.9	1221.2	1219.6	1218.1



TEST NUMBER: P332344

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	984.8	1095.2	1165.5	1205.6	1225.0	1230.9	1231.2
115°	896.7	1011.7	1096.9	1155.5	1189.9	1205.6	1209.5
117.5°	822.3	925.5	1012.0	1073.1	1112.5	1135.0	1140.4
120°	781.0	874.9	953.8	1015.6	1059.4	1078.1	1082.8
122.5°	747.9	834.8	908.2	963.0	1002.4	1023.1	1029.0
125°	706.8	781.8	844.4	894.4	928.8	948.3	953.8
127.5°	670.6	738.4	795.3	839.8	869.2	886.9	891.9
130°	648.1	711.5	764.6	806.1	834.2	850.6	856.9
132.5°	626.9	685.8	736.5	775.4	803.6	818.1	822.5
135°	596.5	647.3	691.9	730.2	753.7	767.7	773.2
137.5°	567.3	611.1	649.7	681.9	705.7	717.6	721.2
140°	550.4	587.9	621.5	651.3	673.1	685.7	684.9
142.5°	534.1	566.7	595.9	621.2	640.6	651.9	651.1
145°	512.9	537.9	560.6	580.1	596.5	602.8	604.3
147.5°	497.1	517.3	533.4	548.2	559.3	565.3	565.9
150°	487.1	503.5	518.3	530.1	538.7	543.4	543.4
152.5°	477.7	492.2	504.6	513.8	521.8	524.6	524.6
155°	464.4	476.1	485.5	492.5	498.8	500.4	501.1
157.5°	451.4	460.5	467.8	473.9	478.6	479.9	479.7
160°	443.3	451.1	456.6	462.1	466.7	466.7	466.0
162.5°	434.5	441.7	446.6	450.2	454.2	454.2	453.5
165°	422.2	427.7	431.6	434.7	437.8	437.0	437.0
167.5°	412.6	415.8	418.6	420.0	422.2	421.4	421.4
170°	405.8	408.9	410.5	411.2	412.8	412.0	412.0
172.5°	400.1	402.6	403.6	403.7	405.3	403.9	403.3
175°	392.5	394.0	394.0	394.0	394.8	394.0	393.3
177.5°	388.1	388.7	388.7	388.1	388.7	387.5	387.5
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2

(END OF REPORT)