

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831693

Luminaire Tested: S123DIP-S775D805U830-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831693
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D805U830-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6368.5 lumens
Efficiency: N/A
Efficacy: 137.0 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 46.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831693

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P831693

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	53				
1	99	95	91	88	91	88	85	82	75	73	71	63	62	60	52	51	50	45				
2	91	83	78	73	84	78	72	68	66	63	59	56	54	51	47	45	43	39				
3	83	74	67	61	77	69	63	58	59	55	51	50	47	44	42	40	38	34				
4	76	66	58	52	71	61	55	50	53	48	44	45	42	38	38	35	33	30				
5	70	59	51	46	65	55	48	43	48	43	38	41	37	34	35	32	29	26				
6	65	53	46	40	60	50	43	38	44	38	34	38	33	30	32	29	26	23				
7	60	49	41	35	56	46	39	34	40	34	30	34	30	27	29	26	24	21				
8	56	44	37	32	52	42	35	30	37	31	27	32	28	24	27	24	22	19				
9	53	41	33	29	49	38	32	27	34	28	25	29	25	22	25	22	20	18				
10	49	38	31	26	46	35	29	25	31	26	23	27	23	20	24	21	18	16				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	22385	22385	22385	22385	22385
5°	28309	26719	22585	18200	16725
10°	28584	29449	22435	14508	12678
15°	21528	27341	22282	12286	10721
20°	15000	22125	21998	10745	9739
25°	11438	17013	21512	9885	9134
30°	9895	13518	20738	9277	8648
35°	9181	11412	19845	8838	8306
40°	8692	10238	18590	8421	8190
45°	8403	9474	16996	8094	8138
50°	8257	8872	15110	7797	8097
55°	7949	8430	13257	7516	8131
60°	7666	7957	11427	7251	7998
65°	7200	7508	9857	6968	7840
70°	6650	6939	8381	6499	7380
75°	6022	6222	7182	6039	6742
80°	4965	5442	5684	5263	5684
85°	3927	4409	4174	4471	4533

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 19406 cd/sqm

TEST NUMBER: P831693

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.6	3.1
10°-20°	489.1	7.7
20°-30°	579.1	9.1
30°-40°	582.3	9.1
40°-50°	534.2	8.4
50°-60°	440.9	6.9
60°-70°	311.9	4.9
70°-80°	166.5	2.6
80°-90°	44.2	0.7
90°-100°	35.0	0.5
100°-110°	169.0	2.7
110°-120°	414.4	6.5
120°-130°	526.0	8.3
130°-140°	562.0	8.8
140°-150°	525.5	8.3
150°-160°	423.9	6.7
160°-170°	273.5	4.3
170°-180°	94.3	1.5
0°-30°	1264.8	19.9
0°-40°	1847.1	29.0
0°-60°	2822.3	44.3
0°-90°	3345.0	52.5
90°-120°	618.4	9.7
90°-150°	2231.9	35.0
90°-180°	3024.0	47.5
0°-180°	6368.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2080	2080	2080	2080	2080	
5°	2620	2473	2090	1684	1548	250
15°	1932	2454	2000	1102	962	534
25°	963	1432	1811	832	769	455
35°	699	868	1510	673	632	439
45°	552	622	1116	532	535	427
55°	424	449	706	400	433	379
65°	283	295	387	274	308	281
75°	145	150	173	145	162	152
85°	32	36	34	36	37	36
90°	22	18	1	18	22	12
95°	28	23	45	23	28	23
105°	32	161	220	161	32	68
115°	433	423	412	423	433	408
125°	592	590	581	590	592	529
135°	730	730	723	730	730	563
145°	842	841	834	841	842	526
155°	917	918	919	918	917	423
165°	967	966	969	966	967	273
175°	988	989	992	989	988	94
180°	992	992	992	992	992	



TEST NUMBER: P831693

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2079.6	2079.6	2079.6	2079.6	2079.6	2079.6	2079.6	2079.6	2079.6	2079.6	2079.6
2.5°	2344.0	2341.6	2339.2	2327.1	2315.0	2309.3	2303.5	2286.1	2268.7	2249.4	2230.1
5°	2620.0	2626.7	2633.5	2625.8	2618.1	2594.4	2570.8	2539.4	2508.0	2472.8	2437.6
7.5°	2747.4	2751.2	2755.1	2750.3	2745.4	2739.2	2732.9	2704.9	2676.9	2640.7	2604.5
10°	2615.2	2623.8	2632.5	2651.3	2670.2	2691.4	2712.6	2708.8	2704.9	2694.3	2683.7
12.5°	2324.7	2335.3	2345.9	2383.6	2421.2	2469.4	2517.7	2559.2	2600.7	2629.6	2658.6
15°	1931.9	1961.4	1990.8	2025.1	2059.3	2130.2	2201.2	2288.5	2375.8	2453.5	2531.2
17.5°	1591.3	1602.4	1613.5	1650.2	1686.8	1776.1	1865.4	1966.2	2067.0	2195.9	2324.7
20°	1309.5	1319.6	1329.8	1378.0	1426.3	1496.2	1566.2	1679.6	1793.0	1931.5	2069.9
22.5°	1100.1	1116.0	1131.9	1159.0	1186.0	1253.1	1320.1	1421.0	1521.8	1674.8	1827.7
25°	963.1	974.7	986.2	1002.6	1019.0	1072.6	1126.2	1209.1	1292.1	1432.5	1573.0
27.5°	869.5	874.3	879.1	895.5	911.9	946.7	981.4	1052.8	1124.2	1243.4	1362.6
30°	796.1	799.5	802.9	817.4	831.8	855.5	879.1	930.7	982.4	1087.6	1192.7
32.5°	745.0	747.4	749.8	760.9	772.0	788.9	805.8	843.4	881.0	967.9	1054.7
35°	698.7	700.1	701.6	709.8	718.0	730.5	743.1	771.5	800.0	868.5	937.0
37.5°	658.1	660.1	662.0	666.8	671.6	682.7	693.8	716.5	739.2	791.8	844.4
40°	618.6	621.9	625.3	628.7	632.1	641.2	650.4	667.8	685.2	728.6	772.0
42.5°	584.8	588.2	591.5	593.0	594.4	599.7	605.1	621.0	636.9	669.2	701.6
45°	552.0	553.4	554.9	556.3	557.8	562.1	566.5	580.4	594.4	622.4	650.4
47.5°	522.1	522.1	522.1	523.0	524.0	527.9	531.7	541.8	552.0	573.7	595.4
50°	493.1	493.1	493.1	491.7	490.2	492.6	495.0	502.8	510.5	529.8	549.1
52.5°	458.4	458.4	458.4	458.9	459.3	459.3	459.3	466.1	472.9	490.2	507.6
55°	423.6	425.6	427.5	426.0	424.6	425.6	426.5	430.9	435.2	449.2	463.2
57.5°	388.9	389.9	390.8	390.3	389.9	390.3	390.8	394.7	398.5	409.2	419.8
60°	356.1	356.1	356.1	355.1	354.2	355.1	356.1	358.0	359.9	369.6	379.2
62.5°	319.4	319.9	320.4	320.9	321.3	320.4	319.4	321.8	324.2	331.5	338.7
65°	282.7	283.2	283.7	285.2	286.6	285.6	284.7	287.1	289.5	294.8	300.1
67.5°	249.9	249.0	248.0	248.5	249.0	250.4	251.9	252.3	252.8	258.6	264.4
70°	211.3	212.3	213.3	212.8	212.3	212.8	213.3	214.7	216.2	220.5	224.8
72.5°	176.6	177.1	177.6	177.6	177.6	178.5	179.5	180.9	182.4	184.8	187.2
75°	144.8	144.8	144.8	145.7	146.7	147.2	147.6	147.6	147.6	149.6	151.5
77.5°	110.0	112.4	114.8	114.4	113.9	114.8	115.8	117.2	118.7	119.7	120.6
80°	80.1	80.1	80.1	80.6	81.1	82.5	84.0	84.9	85.9	87.8	89.7
82.5°	51.1	51.6	52.1	53.6	55.0	56.0	56.9	58.4	59.8	59.8	59.8
85°	31.8	30.9	29.9	30.9	31.8	32.8	33.8	34.3	34.7	35.7	36.7
87.5°	15.4	15.4	15.4	15.4	15.4	15.9	16.4	16.4	16.4	16.4	16.4
90°	22.1	21.8	21.5	21.1	20.8	20.3	19.6	19.0	18.3	17.7	15.6
92.5°	25.1	24.9	24.7	24.6	24.4	23.7	22.6	21.5	20.3	19.2	17.7
95°	28.0	28.0	28.0	28.0	28.0	27.4	26.3	25.1	24.0	22.8	21.0
97.5°	30.2	30.0	29.9	29.7	29.6	28.8	27.5	26.2	24.9	23.6	31.9
100°	30.9	30.8	30.6	30.5	30.3	29.6	28.2	26.9	25.6	24.3	49.9
102.5°	31.7	31.4	31.0	30.7	30.4	32.9	38.3	43.7	49.1	54.5	83.0
105°	32.4	32.1	31.8	31.4	31.1	45.4	74.4	103.4	132.4	161.4	176.1
107.5°	76.6	98.1	119.5	141.0	162.4	185.8	211.0	236.2	261.4	286.6	284.2
110°	202.6	226.1	249.5	272.9	296.3	310.7	316.1	321.5	326.9	332.3	330.5



TEST NUMBER: P831693

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	383.9	384.2	384.6	384.9	385.2	384.6	383.2	381.7	380.2	378.8	377.0
115°	433.3	432.6	432.0	431.3	430.7	429.5	427.9	426.2	424.6	423.0	421.5
117.5°	473.1	472.9	472.7	472.6	472.4	471.7	470.4	469.1	467.8	466.4	465.6
120°	514.3	514.3	514.3	514.3	514.3	513.7	512.4	511.1	509.8	508.4	508.0
122.5°	554.9	554.7	554.5	554.4	554.2	553.7	552.9	552.1	551.3	550.4	549.8
125°	592.4	592.1	591.8	591.5	591.1	590.8	590.5	590.2	589.8	589.5	588.8
127.5°	629.3	629.6	629.9	630.3	630.6	630.5	630.0	629.5	629.0	628.6	627.7
130°	664.7	665.0	665.3	665.6	666.0	665.8	665.2	664.5	663.8	663.2	662.5
132.5°	697.1	697.6	698.1	698.6	699.0	699.0	698.3	697.7	697.0	696.3	695.9
135°	730.2	730.7	731.2	731.7	732.2	732.2	731.7	731.2	730.7	730.2	729.6
137.5°	761.9	762.3	762.6	762.9	763.2	763.0	762.2	761.4	760.5	759.7	759.4
140°	789.9	790.3	790.6	790.9	791.2	791.1	790.4	789.8	789.1	788.5	788.0
142.5°	815.7	816.2	816.7	817.2	817.7	817.7	817.2	816.7	816.2	815.7	815.2
145°	842.2	842.2	842.2	842.2	842.2	842.1	841.8	841.4	841.1	840.8	840.4
147.5°	861.4	862.2	863.0	863.9	864.7	864.9	864.6	864.3	863.9	863.6	863.3
150°	883.5	884.0	884.5	885.0	885.5	885.6	885.2	884.9	884.6	884.2	883.9
152.5°	901.2	902.0	902.8	903.7	904.5	904.6	903.9	903.2	902.6	901.9	901.8
155°	917.4	918.4	919.4	920.4	921.3	921.4	920.6	919.8	919.0	918.1	918.0
157.5°	931.4	932.7	934.0	935.3	936.6	936.8	935.8	934.8	933.9	932.9	933.0
160°	944.7	945.8	947.0	948.1	949.3	949.3	948.4	947.4	946.4	945.4	945.6
162.5°	957.2	958.2	959.2	960.1	961.1	961.0	959.9	958.8	957.6	956.5	956.6
165°	966.8	967.9	969.1	970.2	971.4	971.3	970.0	968.7	967.4	966.0	966.2
167.5°	974.1	975.5	976.8	978.1	979.4	979.4	978.1	976.8	975.5	974.1	974.1
170°	980.8	982.1	983.4	984.7	986.0	986.0	984.7	983.4	982.1	980.8	980.8
172.5°	984.5	985.9	987.4	988.9	990.4	990.4	989.1	987.8	986.5	985.2	985.0
175°	988.1	989.5	990.8	992.1	993.4	993.5	992.3	991.2	990.0	988.9	988.7
177.5°	988.9	990.5	992.2	993.8	995.4	995.6	994.3	993.0	991.7	990.4	990.2
180°	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8



TEST NUMBER: P831693

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2079.6	2079.6	2079.6	2079.6	2079.6	2079.6	2079.6	2079.6	2079.6	2079.6	2079.6
2.5°	2224.3	2218.5	2197.3	2176.1	2152.0	2127.8	2110.0	2092.1	2065.6	2039.1	2017.3
5°	2410.6	2383.6	2338.7	2293.8	2233.0	2172.2	2131.2	2090.2	2035.2	1980.2	1936.3
7.5°	2558.2	2511.9	2449.2	2386.5	2306.8	2227.2	2152.0	2076.7	1992.7	1908.8	1840.3
10°	2652.3	2620.9	2548.6	2476.2	2369.6	2262.9	2157.7	2052.6	1944.5	1836.4	1745.7
12.5°	2661.5	2664.4	2597.8	2531.2	2410.6	2290.0	2162.1	2034.2	1898.2	1762.1	1656.4
15°	2580.9	2630.6	2593.9	2557.3	2435.7	2314.1	2156.8	1999.5	1842.7	1685.9	1563.8
17.5°	2431.3	2538.0	2543.3	2548.6	2427.0	2305.4	2131.2	1957.0	1779.5	1601.9	1473.6
20°	2227.2	2384.5	2438.6	2492.6	2393.7	2294.8	2107.6	1920.4	1721.6	1522.8	1388.2
22.5°	2018.8	2209.9	2308.8	2407.7	2334.3	2261.0	2061.7	1862.5	1652.6	1442.7	1306.1
25°	1781.4	1989.8	2141.8	2293.8	2248.9	2204.1	2007.7	1811.3	1587.9	1364.5	1225.1
27.5°	1574.4	1786.2	1969.6	2152.9	2143.3	2133.6	1938.7	1743.8	1515.1	1286.3	1151.7
30°	1390.1	1587.4	1792.5	1997.6	2021.2	2044.8	1856.7	1668.5	1439.3	1210.1	1080.3
32.5°	1227.0	1399.3	1619.3	1839.3	1885.6	1931.9	1762.1	1592.3	1365.5	1138.7	1013.7
35°	1093.3	1249.7	1469.7	1689.7	1747.6	1805.5	1657.9	1510.2	1289.2	1068.3	949.1
37.5°	975.1	1105.9	1320.6	1535.3	1606.2	1677.2	1545.0	1412.8	1205.8	998.8	889.3
40°	877.2	982.4	1179.7	1377.1	1459.1	1541.1	1432.1	1323.0	1126.6	930.3	829.4
42.5°	795.2	888.8	1067.8	1246.8	1325.4	1404.1	1311.9	1219.8	1045.1	870.4	778.3
45°	725.2	800.0	962.6	1125.2	1200.0	1274.8	1195.6	1116.5	962.6	808.7	722.8
47.5°	659.6	723.8	862.7	1001.7	1068.3	1134.8	1073.1	1011.3	881.0	750.8	673.1
50°	600.7	652.3	773.9	895.5	953.4	1011.3	956.8	902.3	795.2	688.0	620.5
52.5°	549.6	591.5	693.4	795.2	844.9	894.6	847.8	801.0	716.0	631.1	572.2
55°	498.9	534.6	622.9	711.2	745.0	778.8	742.6	706.4	637.9	569.4	519.7
57.5°	451.6	483.5	555.8	628.2	654.3	680.3	647.5	614.7	563.1	511.5	470.0
60°	405.3	431.4	491.7	552.0	567.9	583.8	557.3	530.8	494.6	458.4	421.2
62.5°	362.4	386.0	430.9	475.7	486.4	497.0	476.7	456.4	428.9	401.4	372.5
65°	318.0	335.8	372.5	409.2	415.9	422.7	404.8	387.0	366.2	345.5	324.2
67.5°	277.0	289.5	319.4	349.3	349.8	350.3	335.8	321.3	309.8	298.2	281.3
70°	236.9	249.0	268.8	288.5	289.0	289.5	277.9	266.3	257.7	249.0	236.4
72.5°	195.9	204.6	219.5	234.5	233.5	232.6	225.3	218.1	211.3	204.6	195.4
75°	158.7	166.0	176.1	186.2	183.4	180.5	176.6	172.7	166.9	161.2	155.4
77.5°	125.0	129.3	135.1	140.9	139.0	137.0	133.7	130.3	125.9	121.6	119.2
80°	91.7	93.6	97.5	101.3	100.4	99.4	95.5	91.7	90.7	89.7	86.4
82.5°	62.2	64.7	65.6	66.6	66.1	65.6	62.7	59.8	58.9	57.9	57.4
85°	37.2	37.6	38.1	38.6	37.2	35.7	34.7	33.8	33.8	33.8	33.3
87.5°	16.9	17.4	17.4	17.4	16.9	16.4	15.4	14.5	15.0	15.4	15.4
90°	13.4	11.3	9.2	7.3	5.6	4.0	2.4	0.7	2.4	4.0	5.6
92.5°	16.2	14.7	13.3	13.0	14.0	15.0	16.0	16.9	16.0	15.0	14.0
95°	19.2	17.4	15.6	18.1	24.8	31.5	38.2	44.9	38.2	31.5	24.8
97.5°	40.3	48.6	57.0	63.5	68.0	72.6	77.2	81.8	77.2	72.6	68.0
100°	75.4	101.0	126.5	137.6	134.4	131.1	127.8	124.5	127.8	131.1	134.4
102.5°	111.5	140.0	168.5	181.7	179.6	177.4	175.3	173.2	175.3	177.4	179.6
105°	190.9	205.6	220.3	226.8	225.0	223.2	221.4	219.6	221.4	223.2	225.0
107.5°	281.7	279.3	276.8	274.9	273.4	271.9	270.4	269.0	270.4	271.9	273.4
110°	328.7	326.9	325.1	323.6	322.3	320.9	319.6	318.3	319.6	320.9	322.3



TEST NUMBER: P831693

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	375.2	373.3	371.5	370.1	368.9	367.8	366.6	365.5	366.6	367.8	368.9
115°	420.0	418.5	417.1	415.8	414.9	413.9	412.9	411.9	412.9	413.9	414.9
117.5°	464.8	464.0	463.2	462.2	461.0	459.9	458.7	457.6	458.7	459.9	461.0
120°	507.5	507.0	506.5	505.5	504.0	502.5	501.1	499.6	501.1	502.5	504.0
122.5°	549.1	548.5	547.8	546.9	545.8	544.6	543.5	542.3	543.5	544.6	545.8
125°	588.2	587.5	586.9	585.9	584.6	583.3	582.0	580.7	582.0	583.3	584.6
127.5°	626.9	626.1	625.3	624.2	622.9	621.6	620.3	619.0	620.3	621.6	622.9
130°	661.9	661.2	660.6	659.6	658.3	657.0	655.7	654.3	655.7	657.0	658.3
132.5°	695.4	694.9	694.4	693.5	692.2	690.9	689.6	688.2	689.6	690.9	692.2
135°	728.9	728.3	727.6	726.8	725.8	724.8	723.9	722.9	723.9	724.8	725.8
137.5°	759.1	758.7	758.4	757.6	756.3	755.0	753.7	752.3	753.7	755.0	756.3
140°	787.5	787.0	786.5	785.8	784.8	783.8	782.8	781.8	782.8	783.8	784.8
142.5°	814.7	814.2	813.8	813.0	812.0	811.1	810.1	809.1	810.1	811.1	812.0
145°	840.1	839.8	839.5	838.7	837.6	836.4	835.3	834.1	835.3	836.4	837.6
147.5°	863.0	862.6	862.3	861.7	860.9	860.1	859.3	858.5	859.3	860.1	860.9
150°	883.6	883.3	882.9	882.5	882.0	881.5	881.1	880.6	881.1	881.5	882.0
152.5°	901.6	901.4	901.3	901.1	901.0	900.8	900.6	900.5	900.6	900.8	901.0
155°	917.8	917.7	917.5	917.6	917.9	918.2	918.6	918.9	918.6	918.2	917.9
157.5°	933.2	933.4	933.5	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6
160°	945.7	945.9	946.1	946.2	946.4	946.6	946.7	946.9	946.7	946.6	946.4
162.5°	956.8	957.0	957.1	957.4	957.9	958.4	958.9	959.4	958.9	958.4	957.9
165°	966.4	966.5	966.7	967.0	967.5	968.0	968.5	969.0	968.5	968.0	967.5
167.5°	974.1	974.1	974.1	974.5	975.1	975.8	976.4	977.1	976.4	975.8	975.1
170°	980.8	980.8	980.8	981.1	981.8	982.4	983.1	983.7	983.1	982.4	981.8
172.5°	984.9	984.7	984.5	984.9	985.7	986.5	987.3	988.1	987.3	986.5	985.7
175°	988.6	988.4	988.2	988.6	989.4	990.2	991.0	991.8	991.0	990.2	989.4
177.5°	990.0	989.9	989.7	990.0	990.9	991.7	992.5	993.3	992.5	991.7	990.9
180°	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8



TEST NUMBER: P831693

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2079.6	2079.6	2079.6	2079.6	2079.6	2079.6	2079.6	2079.6	2079.6	2079.6	2079.6
2.5°	1995.6	1976.8	1958.0	1943.5	1929.0	1904.4	1879.8	1874.0	1868.2	1860.0	1851.8
5°	1892.4	1846.1	1799.7	1758.2	1716.7	1684.4	1652.1	1630.9	1609.6	1594.2	1578.7
7.5°	1771.7	1702.3	1632.8	1583.6	1534.4	1487.6	1440.7	1425.8	1410.8	1390.6	1370.3
10°	1655.0	1578.3	1501.5	1437.4	1373.2	1327.4	1281.5	1263.2	1244.9	1219.3	1193.7
12.5°	1550.8	1466.8	1382.8	1318.2	1253.5	1209.1	1164.8	1138.2	1111.7	1097.2	1082.7
15°	1441.7	1352.0	1262.2	1202.4	1142.6	1102.5	1062.5	1039.3	1016.1	1002.2	988.2
17.5°	1345.2	1256.4	1167.7	1110.2	1052.8	1016.1	979.5	959.2	938.9	928.3	917.7
20°	1253.5	1166.7	1079.8	1023.9	967.9	938.0	908.1	895.0	882.0	873.3	864.6
22.5°	1169.6	1084.2	998.8	951.0	903.2	879.1	855.0	845.8	836.7	829.4	822.2
25°	1085.6	1009.4	933.2	892.6	852.1	832.3	812.5	803.4	794.2	787.0	779.7
27.5°	1017.1	944.3	871.4	836.7	801.9	786.5	771.0	763.8	756.6	749.8	743.1
30°	950.5	885.4	820.3	790.3	760.4	746.4	732.4	725.2	718.0	711.7	705.4
32.5°	888.8	832.8	776.8	749.3	721.8	710.2	698.7	690.0	681.3	676.5	671.6
35°	829.9	779.7	729.5	706.9	684.2	672.6	661.0	653.8	646.6	642.7	638.8
37.5°	779.7	734.8	690.0	668.3	646.6	635.5	624.4	618.1	611.8	610.4	608.9
40°	728.6	690.0	651.4	630.1	608.9	599.3	589.6	585.8	581.9	580.9	580.0
42.5°	686.1	648.5	610.8	591.5	572.2	564.0	555.8	553.9	552.0	553.4	554.9
45°	636.9	605.5	574.2	556.3	538.5	531.7	525.0	523.5	522.1	525.0	527.9
47.5°	595.4	566.5	537.5	520.6	503.7	498.9	494.1	493.6	493.1	497.0	500.8
50°	552.9	525.0	497.0	483.5	470.0	465.6	461.3	462.7	464.2	470.4	476.7
52.5°	513.4	487.3	461.3	448.7	436.2	433.3	430.4	433.8	437.1	443.9	450.7
55°	470.0	446.3	422.7	413.0	403.4	400.5	397.6	404.3	411.1	417.4	423.6
57.5°	428.5	407.7	387.0	378.3	369.6	369.1	368.6	374.9	381.2	387.9	394.7
60°	384.1	366.7	349.3	342.6	335.8	336.8	337.8	345.0	352.2	357.5	362.8
62.5°	343.5	329.1	314.6	308.3	302.0	304.5	306.9	314.1	321.3	327.6	333.9
65°	303.0	290.9	278.9	274.5	270.2	273.6	277.0	283.2	289.5	293.8	298.2
67.5°	264.4	254.3	244.1	240.8	237.4	240.8	244.1	250.4	256.7	261.0	265.4
70°	223.9	215.7	207.5	205.1	202.7	206.5	210.4	215.7	221.0	225.3	229.7
72.5°	186.2	180.0	173.7	173.2	172.7	176.1	179.5	184.8	190.1	193.0	195.9
75°	149.6	146.2	142.8	142.3	141.9	145.2	148.6	151.5	154.4	156.8	159.2
77.5°	116.8	113.9	111.0	111.5	111.9	114.4	116.8	119.7	122.6	124.0	125.5
80°	83.0	82.0	81.1	82.0	83.0	84.9	86.9	88.8	90.7	91.7	92.6
82.5°	56.9	56.0	55.0	56.5	57.9	59.3	60.8	62.2	63.7	64.2	64.7
85°	32.8	34.3	35.7	35.7	35.7	36.2	36.7	37.2	37.6	37.2	36.7
87.5°	15.4	15.9	16.4	16.4	16.4	16.9	17.4	17.4	17.4	16.9	16.4
90°	7.3	9.2	11.3	13.4	15.6	17.7	18.3	19.0	19.6	20.3	20.8
92.5°	13.0	13.3	14.7	16.2	17.7	19.2	20.3	21.5	22.6	23.7	24.4
95°	18.1	15.6	17.4	19.2	21.0	22.8	24.0	25.1	26.3	27.4	28.0
97.5°	63.5	57.0	48.6	40.3	31.9	23.6	24.9	26.2	27.5	28.8	29.6
100°	137.6	126.5	101.0	75.4	49.9	24.3	25.6	26.9	28.2	29.6	30.3
102.5°	181.7	168.5	140.0	111.5	83.0	54.5	49.1	43.7	38.3	32.9	30.4
105°	226.8	220.3	205.6	190.9	176.1	161.4	132.4	103.4	74.4	45.4	31.1
107.5°	274.9	276.8	279.3	281.7	284.2	286.6	261.4	236.2	211.0	185.8	162.4
110°	323.6	325.1	326.9	328.7	330.5	332.3	326.9	321.5	316.1	310.7	296.3



TEST NUMBER: P831693

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	370.1	371.5	373.3	375.2	377.0	378.8	380.2	381.7	383.2	384.6	385.2
115°	415.8	417.1	418.5	420.0	421.5	423.0	424.6	426.2	427.9	429.5	430.7
117.5°	462.2	463.2	464.0	464.8	465.6	466.4	467.8	469.1	470.4	471.7	472.4
120°	505.5	506.5	507.0	507.5	508.0	508.4	509.8	511.1	512.4	513.7	514.3
122.5°	546.9	547.8	548.5	549.1	549.8	550.4	551.3	552.1	552.9	553.7	554.2
125°	585.9	586.9	587.5	588.2	588.8	589.5	589.8	590.2	590.5	590.8	591.1
127.5°	624.2	625.3	626.1	626.9	627.7	628.6	629.0	629.5	630.0	630.5	630.6
130°	659.6	660.6	661.2	661.9	662.5	663.2	663.8	664.5	665.2	665.8	666.0
132.5°	693.5	694.4	694.9	695.4	695.9	696.3	697.0	697.7	698.3	699.0	699.0
135°	726.8	727.6	728.3	728.9	729.6	730.2	730.7	731.2	731.7	732.2	732.2
137.5°	757.6	758.4	758.7	759.1	759.4	759.7	760.5	761.4	762.2	763.0	763.2
140°	785.8	786.5	787.0	787.5	788.0	788.5	789.1	789.8	790.4	791.1	791.2
142.5°	813.0	813.8	814.2	814.7	815.2	815.7	816.2	816.7	817.2	817.7	817.7
145°	838.7	839.5	839.8	840.1	840.4	840.8	841.1	841.4	841.8	842.1	842.2
147.5°	861.7	862.3	862.6	863.0	863.3	863.6	863.9	864.3	864.6	864.9	864.7
150°	882.5	882.9	883.3	883.6	883.9	884.2	884.6	884.9	885.2	885.6	885.5
152.5°	901.1	901.3	901.4	901.6	901.8	901.9	902.6	903.2	903.9	904.6	904.5
155°	917.6	917.5	917.7	917.8	918.0	918.1	919.0	919.8	920.6	921.4	921.3
157.5°	933.6	933.5	933.4	933.2	933.0	932.9	933.9	934.8	935.8	936.8	936.6
160°	946.2	946.1	945.9	945.7	945.6	945.4	946.4	947.4	948.4	949.3	949.3
162.5°	957.4	957.1	957.0	956.8	956.6	956.5	957.6	958.8	959.9	961.0	961.1
165°	967.0	966.7	966.5	966.4	966.2	966.0	967.4	968.7	970.0	971.3	971.4
167.5°	974.5	974.1	974.1	974.1	974.1	974.1	975.5	976.8	978.1	979.4	979.4
170°	981.1	980.8	980.8	980.8	980.8	980.8	982.1	983.4	984.7	986.0	986.0
172.5°	984.9	984.5	984.7	984.9	985.0	985.2	986.5	987.8	989.1	990.4	990.4
175°	988.6	988.2	988.4	988.6	988.7	988.9	990.0	991.2	992.3	993.5	993.4
177.5°	990.0	989.7	989.9	990.0	990.2	990.4	991.7	993.0	994.3	995.6	995.4
180°	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8



TEST NUMBER: P831693

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2079.6	2079.6	2079.6	2079.6
2.5°	1848.5	1845.1	1831.6	1818.1
5°	1567.2	1555.6	1551.7	1547.9
7.5°	1369.3	1368.4	1348.1	1327.8
10°	1195.2	1196.6	1178.3	1159.9
12.5°	1070.7	1058.6	1057.2	1055.7
15°	977.1	966.0	964.0	962.1
17.5°	911.0	904.2	902.3	900.3
20°	860.8	856.9	853.5	850.2
22.5°	817.4	812.5	809.6	806.7
25°	775.4	771.0	770.1	769.1
27.5°	737.7	732.4	732.4	732.4
30°	702.0	698.7	697.2	695.8
32.5°	668.7	665.9	665.9	665.9
35°	637.4	635.9	634.0	632.1
37.5°	608.9	608.9	608.0	607.0
40°	581.4	582.9	582.9	582.9
42.5°	556.3	557.8	557.8	557.8
45°	530.3	532.7	533.6	534.6
47.5°	504.7	508.6	509.5	510.5
50°	479.6	482.5	483.0	483.5
52.5°	454.0	457.4	459.8	462.2
55°	427.0	430.4	431.8	433.3
57.5°	398.1	401.4	401.9	402.4
60°	366.2	369.6	370.6	371.5
62.5°	335.8	337.8	338.7	339.7
65°	301.1	304.0	305.9	307.8
67.5°	267.8	270.2	270.2	270.2
70°	230.6	231.6	233.0	234.5
72.5°	196.4	196.9	196.9	196.9
75°	160.2	161.2	161.6	162.1
77.5°	125.9	126.4	126.4	126.4
80°	92.2	91.7	91.7	91.7
82.5°	63.2	61.8	61.8	61.8
85°	36.2	35.7	36.2	36.7
87.5°	16.4	16.4	16.4	16.4
90°	21.1	21.5	21.8	22.1
92.5°	24.6	24.7	24.9	25.1
95°	28.0	28.0	28.0	28.0
97.5°	29.7	29.9	30.0	30.2
100°	30.5	30.6	30.8	30.9
102.5°	30.7	31.0	31.4	31.7
105°	31.4	31.8	32.1	32.4
107.5°	141.0	119.5	98.1	76.6
110°	272.9	249.5	226.1	202.6



TEST NUMBER: P831693

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	384.9	384.6	384.2	383.9
115°	431.3	432.0	432.6	433.3
117.5°	472.6	472.7	472.9	473.1
120°	514.3	514.3	514.3	514.3
122.5°	554.4	554.5	554.7	554.9
125°	591.5	591.8	592.1	592.4
127.5°	630.3	629.9	629.6	629.3
130°	665.6	665.3	665.0	664.7
132.5°	698.6	698.1	697.6	697.1
135°	731.7	731.2	730.7	730.2
137.5°	762.9	762.6	762.3	761.9
140°	790.9	790.6	790.3	789.9
142.5°	817.2	816.7	816.2	815.7
145°	842.2	842.2	842.2	842.2
147.5°	863.9	863.0	862.2	861.4
150°	885.0	884.5	884.0	883.5
152.5°	903.7	902.8	902.0	901.2
155°	920.4	919.4	918.4	917.4
157.5°	935.3	934.0	932.7	931.4
160°	948.1	947.0	945.8	944.7
162.5°	960.1	959.2	958.2	957.2
165°	970.2	969.1	967.9	966.8
167.5°	978.1	976.8	975.5	974.1
170°	984.7	983.4	982.1	980.8
172.5°	988.9	987.4	985.9	984.5
175°	992.1	990.8	989.5	988.1
177.5°	993.8	992.2	990.5	988.9
180°	991.8	991.8	991.8	991.8



TEST NUMBER: P831693

CATALOG NUMBER: S123DIP-S775D805U830-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.60	15.45	15.54	16.40	17.64	16.84	17.68	17.78	18.64	19.88
	3H	16.25	17.00	17.20	17.97	19.23	18.26	19.02	19.22	19.98	21.24
	4H	16.82	17.54	17.79	18.51	19.78	18.71	19.43	19.68	20.39	21.66
	6H	17.19	17.85	18.17	18.83	20.11	18.99	19.64	19.96	20.62	21.90
	8H	17.29	17.92	18.28	18.91	20.19	19.05	19.67	20.03	20.66	21.94
	12H	17.33	17.93	18.32	18.91	20.22	19.07	19.66	20.06	20.65	21.95
4H	2H	15.17	15.89	16.15	16.86	18.13	17.00	17.72	17.97	18.68	19.95
	3H	17.00	17.60	17.98	18.59	19.88	18.62	19.21	19.60	20.21	21.49
	4H	17.70	18.24	18.69	19.23	20.54	19.20	19.74	20.19	20.74	22.04
	6H	18.17	18.64	19.18	19.66	20.96	19.60	20.07	20.61	21.09	22.39
	8H	18.31	18.75	19.31	19.75	21.07	19.72	20.15	20.72	21.16	22.48
	12H	18.38	18.77	19.40	19.79	21.12	19.76	20.15	20.78	21.18	22.50
8H	4H	17.96	18.40	18.97	19.41	20.73	19.30	19.74	20.31	20.75	22.07
	6H	18.55	18.91	19.58	19.96	21.28	19.81	20.17	20.84	21.22	22.53
	8H	18.76	19.08	19.80	20.11	21.45	19.99	20.30	21.02	21.34	22.68
	12H	18.88	19.16	19.92	20.19	21.57	20.09	20.37	21.13	21.40	22.78
12H	4H	17.96	18.36	18.99	19.38	20.71	19.28	19.67	20.30	20.70	22.02
	6H	18.60	18.92	19.64	19.96	21.29	19.82	20.14	20.86	21.17	22.51
	8H	18.84	19.12	19.88	20.15	21.53	20.02	20.30	21.06	21.33	22.71