

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332355-830

Luminaire Tested: **S123RDIP-S1000D1195U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332355-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1000D1195U830-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7597.4 lumens  
Efficiency: N/A  
Efficacy: 116.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332355-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332355-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49
1	98	94	90	87	90	87	84	81	73	71	69	61	60	58	50	49	48	43
2	90	83	77	72	83	77	72	67	65	61	58	54	52	49	45	43	41	37
3	82	73	66	61	76	68	62	57	58	53	50	49	45	43	40	38	36	32
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	36	33	31	28
5	70	58	51	45	64	54	47	42	47	41	37	39	35	32	33	30	28	24
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	24	22
7	59	48	40	34	55	44	38	33	38	33	29	33	29	25	27	24	22	19
8	55	43	36	31	51	40	34	29	35	30	26	30	26	23	25	22	20	17
9	52	40	32	27	48	37	30	26	32	27	23	28	24	21	23	20	18	16
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	16129	16129	16129	16129
5°	19225	16197	14263	16197
10°	24004	16104	12885	16104
15°	28178	15940	11751	15940
20°	31447	15694	10786	15694
25°	30945	15435	10194	15435
30°	22243	15196	9583	15196
35°	14851	14884	9188	14884
40°	10942	14511	8778	14511
45°	9178	13855	8378	13855
50°	8098	12996	7819	12996
55°	7101	12014	7054	12014
60°	6325	11074	6463	11074
65°	5555	10063	6011	10063
70°	4362	9165	5492	9165
75°	3843	8006	5016	8006
80°	3341	6800	4934	6800
85°	2692	5471	5224	5471



TEST NUMBER: P332355-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	147.4	1.9
10°-20°	460.3	6.1
20°-30°	723.2	9.5
30°-40°	754.5	9.9
40°-50°	645.7	8.5
50°-60°	492.2	6.5
60°-70°	315.5	4.2
70°-80°	151.8	2.0
80°-90°	44.3	0.6
90°-100°	90.8	1.2
100°-110°	271.8	3.6
110°-120°	462.3	6.1
120°-130°	608.1	8.0
130°-140°	683.5	9.0
140°-150°	671.9	8.8
150°-160°	565.6	7.4
160°-170°	376.5	5.0
170°-180°	131.8	1.7
0°-30°	1330.9	17.5
0°-40°	2085.5	27.4
0°-60°	3223.3	42.4
0°-90°	3734.9	49.2
90°-120°	825.0	10.9
90°-150°	2788.5	36.7
90°-180°	3863.0	50.8
0°-180°	7597.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1498	1498	1498	1498	1498	
5°	1779	1499	1320	1499	1779	184
15°	2529	1430	1054	1430	2529	717
25°	2606	1300	858	1300	2606	1120
35°	1130	1133	699	1133	1130	741
45°	603	910	550	910	603	474
55°	378	640	376	640	378	342
65°	218	395	236	395	218	215
75°	92	192	121	192	92	99
85°	22	44	42	44	22	26
90°	33	1	33	1	33	17
95°	85	65	85	65	85	88
105°	261	246	261	246	261	277
115°	467	465	467	465	467	462
125°	674	681	674	681	674	602
135°	883	884	883	884	883	679
145°	1072	1072	1072	1072	1072	669
155°	1225	1228	1225	1228	1225	564
165°	1333	1337	1333	1337	1333	376
175°	1385	1391	1385	1391	1385	132
180°	1394	1394	1394	1394	1394	



TEST NUMBER: P332355-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4
2.5°	1595.9	1597.9	1591.3	1590.3	1582.5	1580.5	1580.5	1569.7	1563.0	1554.3	1549.2
5°	1779.3	1789.6	1784.4	1772.9	1753.7	1749.2	1737.0	1717.8	1695.9	1669.0	1656.1
7.5°	2008.5	2022.4	2017.0	1999.2	1979.1	1962.8	1928.4	1896.5	1851.7	1812.4	1778.9
10°	2196.2	2181.5	2169.9	2152.7	2134.0	2103.8	2067.9	2018.5	1961.5	1916.6	1866.6
12.5°	2336.8	2334.4	2319.8	2302.0	2275.7	2247.0	2202.9	2142.8	2076.4	2011.6	1954.3
15°	2528.6	2532.3	2522.7	2504.1	2466.9	2416.3	2349.6	2324.6	2229.6	2159.1	2088.5
17.5°	2661.2	2660.4	2659.1	2633.4	2595.4	2559.3	2497.5	2431.7	2345.7	2246.3	2151.3
20°	2745.3	2738.9	2740.2	2711.3	2683.1	2641.4	2581.2	2485.6	2415.0	2300.2	2202.1
22.5°	2743.3	2742.0	2746.9	2737.0	2716.5	2684.5	2637.0	2556.4	2466.3	2350.4	2240.0
25°	2605.5	2600.4	2630.5	2638.8	2671.5	2677.3	2663.2	2618.9	2533.6	2414.3	2277.7
27.5°	2180.6	2177.7	2233.7	2303.8	2392.6	2461.5	2528.3	2560.5	2533.6	2448.3	2311.3
30°	1789.6	1849.9	1878.1	1979.4	2092.4	2227.0	2345.0	2457.3	2484.9	2447.7	2335.4
32.5°	1485.8	1538.4	1562.0	1649.0	1754.2	1911.9	2089.1	2248.0	2360.2	2388.7	2321.1
35°	1130.2	1130.9	1184.7	1223.2	1320.7	1483.0	1654.9	1867.8	2079.5	2239.9	2256.5
37.5°	901.8	905.0	937.6	976.0	1049.1	1134.9	1286.3	1463.4	1707.9	1954.1	2098.4
40°	778.7	784.5	808.9	846.7	899.3	964.0	1082.1	1248.9	1452.8	1726.7	1950.6
42.5°	699.6	709.1	721.6	750.7	783.3	844.0	939.4	1068.3	1253.8	1512.8	1771.0
45°	602.9	608.0	617.7	631.1	660.6	703.0	767.1	853.8	1007.7	1216.2	1474.6
47.5°	531.9	529.1	539.3	550.3	569.9	598.7	641.7	712.4	822.2	989.5	1208.7
50°	483.6	483.0	490.0	498.4	517.0	538.2	573.4	626.7	713.9	852.4	1053.2
52.5°	438.5	440.9	445.9	456.3	469.8	486.8	518.5	556.9	631.8	751.4	918.8
55°	378.4	380.4	387.4	393.2	402.8	420.1	440.0	472.1	523.4	606.8	744.7
57.5°	327.6	326.8	333.6	335.0	345.8	360.0	375.3	400.3	437.4	499.5	592.3
60°	293.8	291.8	297.7	302.1	307.9	319.4	332.2	356.7	386.2	431.7	511.2
62.5°	263.0	262.1	266.4	270.8	275.6	286.1	296.9	315.6	338.9	377.3	440.5
65°	218.1	220.0	222.0	223.9	226.4	232.8	243.1	255.9	271.9	298.9	344.4
67.5°	171.4	173.3	174.0	178.0	183.4	187.5	193.7	205.1	216.3	239.0	264.9
70°	138.6	137.9	138.6	140.4	147.5	154.6	163.0	171.3	178.3	194.4	216.1
72.5°	119.0	117.9	119.6	120.0	123.4	125.4	130.6	138.5	147.5	158.4	174.1
75°	92.4	92.4	92.4	92.4	94.9	96.2	98.1	100.1	103.3	108.4	120.0
77.5°	68.2	68.3	69.3	69.9	70.4	71.2	72.4	74.3	75.4	78.1	83.1
80°	53.9	54.5	53.9	54.5	54.5	55.8	56.5	58.3	59.0	62.2	64.2
82.5°	40.5	40.2	40.5	41.2	41.2	42.5	42.6	44.0	44.1	45.8	47.7
85°	21.8	20.5	21.8	21.2	22.4	21.2	21.8	23.1	23.1	23.8	26.3
87.5°	11.7	12.6	11.5	12.0	11.8	12.2	12.0	11.8	12.6	12.0	11.8
90°	32.9	32.3	31.9	31.4	30.9	30.2	29.2	28.3	27.2	26.3	23.1
92.5°	44.2	44.5	44.9	45.1	45.4	45.1	44.4	43.6	42.8	42.0	40.2
95°	85.4	85.4	85.4	85.4	85.4	84.9	84.0	82.9	82.0	81.1	79.1
97.5°	131.4	131.5	131.6	131.7	131.8	131.3	130.2	129.0	127.9	126.8	125.4
100°	166.5	166.0	165.5	165.0	164.5	163.9	163.2	162.4	161.7	161.0	159.8
102.5°	202.4	202.5	202.6	202.6	202.7	202.5	201.7	201.0	200.3	199.5	197.9
105°	260.6	260.1	259.7	259.2	258.7	258.4	258.4	258.4	258.4	258.4	256.3
107.5°	321.3	321.6	321.9	322.2	322.4	322.3	321.5	320.7	319.9	319.1	318.2
110°	362.5	363.0	363.4	363.9	364.4	364.2	363.3	362.2	361.3	360.3	359.8



TEST NUMBER: P332355-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	406.3	406.4	406.5	406.6	406.7	406.1	405.0	403.8	402.7	401.4	401.3
115°	466.6	466.7	467.0	467.2	467.5	467.5	467.2	467.0	466.7	466.6	467.0
117.5°	527.6	528.3	529.0	529.7	530.4	530.7	530.7	530.8	530.8	530.9	531.6
120°	570.5	571.1	571.6	572.0	572.5	572.9	573.2	573.3	573.6	573.8	575.0
122.5°	611.7	612.4	613.1	613.8	614.4	615.1	615.8	616.4	617.0	617.6	618.3
125°	673.5	674.5	675.4	676.5	677.4	678.3	679.4	680.3	681.3	682.3	682.8
127.5°	735.1	736.1	737.3	738.4	739.5	740.7	742.2	743.5	744.9	746.2	746.8
130°	775.3	777.0	778.7	780.4	782.1	783.5	784.5	785.4	786.5	787.4	788.2
132.5°	817.4	818.7	820.0	821.3	822.7	823.9	825.1	826.2	827.4	828.6	829.1
135°	882.7	883.2	883.6	884.1	884.6	885.3	886.3	887.3	888.3	889.2	889.5
137.5°	940.3	941.2	942.2	943.0	944.0	944.9	945.9	947.0	948.0	949.0	948.4
140°	978.0	979.7	981.4	983.1	984.8	985.7	986.0	986.2	986.5	986.7	986.5
142.5°	1016.5	1017.9	1019.1	1020.4	1021.7	1022.6	1022.8	1023.0	1023.2	1023.5	1023.0
145°	1072.1	1073.1	1074.0	1075.1	1076.0	1076.7	1076.9	1077.1	1077.3	1077.6	1076.9
147.5°	1121.6	1123.0	1124.5	1126.0	1127.5	1128.2	1128.2	1128.2	1128.2	1128.2	1127.5
150°	1153.2	1154.6	1156.1	1157.5	1159.0	1159.7	1159.7	1159.7	1159.7	1159.7	1159.2
152.5°	1183.8	1185.1	1186.4	1187.6	1188.9	1189.3	1188.9	1188.5	1188.2	1187.8	1187.5
155°	1225.4	1227.2	1228.9	1230.6	1232.3	1232.7	1231.6	1230.7	1229.7	1228.7	1228.5
157.5°	1263.3	1264.7	1266.0	1267.4	1268.8	1268.9	1267.9	1266.9	1265.9	1264.9	1264.7
160°	1287.9	1288.8	1289.8	1290.8	1291.8	1291.7	1290.4	1289.2	1288.0	1286.8	1286.8
162.5°	1306.3	1307.8	1309.4	1310.9	1312.5	1312.7	1311.5	1310.2	1309.0	1307.8	1307.6
165°	1332.8	1334.5	1336.1	1337.8	1339.5	1339.7	1338.2	1336.8	1335.3	1333.9	1333.9
167.5°	1355.3	1356.8	1358.3	1359.8	1361.3	1361.3	1359.8	1358.3	1356.8	1355.3	1355.1
170°	1366.7	1368.4	1370.1	1371.9	1373.6	1373.6	1371.9	1370.1	1368.4	1366.7	1366.7
172.5°	1375.5	1377.1	1378.8	1380.5	1382.3	1382.4	1380.9	1379.4	1377.9	1376.4	1376.4
175°	1385.3	1387.0	1388.7	1390.4	1392.1	1392.2	1390.8	1389.3	1387.9	1386.4	1386.4
177.5°	1390.6	1391.9	1393.3	1394.7	1396.0	1396.1	1395.0	1393.8	1392.6	1391.5	1391.5
180°	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1



TEST NUMBER: P332355-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4
2.5°	1547.1	1545.6	1538.4	1530.2	1519.4	1512.2	1506.6	1503.5	1494.3	1483.0	1475.3
5°	1642.7	1623.4	1603.0	1577.9	1554.8	1531.1	1516.4	1499.0	1477.8	1454.2	1437.5
7.5°	1745.1	1707.3	1666.7	1624.8	1583.3	1546.1	1513.3	1485.2	1451.4	1417.4	1393.5
10°	1823.6	1768.4	1711.4	1652.9	1599.7	1549.7	1511.2	1473.4	1432.9	1393.8	1364.3
12.5°	1894.9	1822.3	1756.5	1684.8	1616.6	1556.9	1501.5	1457.0	1408.3	1366.6	1333.0
15°	1985.2	1910.8	1831.3	1722.2	1631.8	1556.1	1488.7	1430.4	1371.4	1320.0	1287.3
17.5°	2069.6	1957.7	1850.8	1759.8	1642.3	1547.7	1465.6	1395.7	1331.0	1276.6	1236.3
20°	2104.5	1996.1	1880.0	1764.0	1648.5	1542.7	1447.1	1370.1	1302.8	1241.1	1204.0
22.5°	2125.5	2002.8	1880.6	1755.8	1633.0	1523.1	1428.6	1344.0	1270.9	1212.4	1166.5
25°	2150.0	2003.8	1869.2	1746.0	1620.9	1501.6	1389.3	1299.6	1220.7	1158.4	1109.7
27.5°	2166.2	1994.2	1835.0	1698.1	1571.2	1452.5	1349.5	1254.3	1174.3	1108.5	1056.2
30°	2169.4	1986.5	1808.8	1660.7	1531.7	1422.7	1313.6	1222.6	1137.9	1068.0	1019.3
32.5°	2173.4	1967.6	1773.4	1616.0	1484.0	1376.0	1277.2	1190.2	1103.5	1034.6	984.9
35°	2156.5	1957.0	1719.7	1538.8	1406.7	1302.1	1213.0	1132.7	1047.4	980.7	930.1
37.5°	2083.6	1915.3	1664.0	1451.8	1313.6	1216.8	1144.2	1074.3	996.0	924.1	876.3
40°	2010.3	1874.2	1620.9	1398.9	1254.6	1155.2	1089.8	1032.7	957.1	889.7	838.4
42.5°	1900.9	1818.4	1579.9	1343.5	1187.9	1092.1	1036.9	983.4	917.0	848.6	800.4
45°	1700.4	1711.4	1495.8	1255.3	1095.5	999.4	947.3	910.2	851.2	794.8	745.4
47.5°	1449.0	1551.0	1397.1	1161.2	998.2	907.9	862.4	830.0	790.2	734.8	689.8
50°	1284.8	1430.4	1318.1	1098.2	937.2	847.3	802.4	776.1	741.5	697.9	654.9
52.5°	1133.4	1289.8	1222.7	1027.8	870.9	788.8	745.0	723.3	695.8	654.8	615.9
55°	924.3	1082.7	1067.3	921.7	771.7	697.9	664.5	640.2	621.5	590.8	560.0
57.5°	747.6	897.9	905.8	803.7	684.2	611.2	582.6	564.2	552.0	528.8	500.3
60°	636.3	774.2	801.2	724.2	621.5	557.4	529.1	514.4	504.8	486.2	464.4
62.5°	543.9	661.3	691.8	636.4	561.5	501.4	479.4	465.1	458.6	442.6	423.4
65°	416.3	513.8	543.3	512.5	473.3	425.3	407.3	395.1	389.4	380.4	366.3
67.5°	313.0	384.1	416.4	394.7	380.6	350.2	338.8	332.2	327.2	320.9	309.2
70°	251.5	304.1	337.4	331.6	320.1	304.1	295.7	291.2	286.1	281.0	270.7
72.5°	202.2	238.4	269.7	272.6	263.2	260.0	252.6	250.7	247.6	241.5	235.8
75°	134.0	159.1	180.9	189.3	193.0	196.2	193.0	192.5	191.8	186.6	183.4
77.5°	87.8	101.3	115.1	129.3	135.3	139.7	140.7	143.1	141.4	138.6	137.1
80°	67.4	70.6	80.2	92.4	102.0	105.8	108.4	109.7	109.1	108.4	105.8
82.5°	48.9	51.6	56.1	64.7	72.8	79.2	80.7	80.4	81.8	82.2	80.2
85°	26.3	27.0	28.2	29.5	34.0	41.1	43.0	44.3	45.5	45.5	41.7
87.5°	12.2	11.0	11.4	10.9	12.0	12.0	14.5	16.7	17.6	16.1	16.6
90°	20.0	16.8	13.7	10.8	8.4	5.9	3.5	1.1	3.5	5.9	8.4
92.5°	38.5	36.7	34.9	33.1	31.5	29.8	28.2	26.5	28.2	29.8	31.5
95°	77.1	75.2	73.2	71.4	69.7	68.1	66.4	64.7	66.4	68.1	69.7
97.5°	124.0	122.6	121.2	119.8	118.6	117.3	116.0	114.8	116.0	117.3	118.6
100°	158.5	157.3	156.1	154.8	153.4	151.8	150.4	148.9	150.4	151.8	153.4
102.5°	196.3	194.7	193.1	191.9	191.0	190.1	189.3	188.3	189.3	190.1	191.0
105°	254.1	251.8	249.7	248.4	247.9	247.4	246.9	246.4	246.9	247.4	247.9
107.5°	317.4	316.5	315.7	315.0	314.7	314.4	314.1	313.9	314.1	314.4	314.7
110°	359.3	358.8	358.4	357.9	357.4	356.8	356.4	355.9	356.4	356.8	357.4





TEST NUMBER: P332355-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	401.2	401.1	401.1	400.9	400.6	400.3	400.0	399.7	400.0	400.3	400.6
115°	467.5	468.0	468.4	468.3	467.6	466.8	466.2	465.4	466.2	466.8	467.6
117.5°	532.2	532.8	533.5	533.5	533.0	532.5	532.1	531.6	532.1	532.5	533.0
120°	576.3	577.5	578.7	578.6	577.1	575.7	574.2	572.8	574.2	575.7	577.1
122.5°	618.9	619.5	620.2	620.0	618.9	617.8	616.7	615.7	616.7	617.8	618.9
125°	683.2	683.7	684.2	684.1	683.3	682.6	681.9	681.2	681.9	682.6	683.3
127.5°	747.2	747.8	748.4	747.8	746.3	744.7	743.2	741.6	743.2	744.7	746.3
130°	788.8	789.6	790.3	789.7	787.8	785.8	783.8	781.9	783.8	785.8	787.8
132.5°	829.6	830.2	830.8	830.0	828.0	826.1	824.2	822.2	824.2	826.1	828.0
135°	889.8	889.9	890.2	889.6	888.2	886.6	885.2	883.7	885.2	886.6	888.2
137.5°	947.7	947.2	946.5	945.6	944.3	943.1	941.9	940.8	941.9	943.1	944.3
140°	986.2	986.0	985.7	985.0	983.8	982.6	981.4	980.1	981.4	982.6	983.8
142.5°	1022.7	1022.2	1021.7	1021.0	1019.7	1018.5	1017.3	1016.1	1017.3	1018.5	1019.7
145°	1076.1	1075.4	1074.7	1074.0	1073.6	1073.1	1072.6	1072.1	1072.6	1073.1	1073.6
147.5°	1126.8	1126.1	1125.5	1124.7	1123.8	1122.9	1122.1	1121.2	1122.1	1122.9	1123.8
150°	1158.8	1158.3	1157.8	1157.3	1156.8	1156.3	1155.8	1155.4	1155.8	1156.3	1156.8
152.5°	1187.2	1186.8	1186.6	1186.1	1185.4	1184.8	1184.1	1183.4	1184.1	1184.8	1185.4
155°	1228.2	1228.0	1227.8	1227.7	1227.7	1227.7	1227.7	1227.7	1227.7	1227.7	1227.7
157.5°	1264.5	1264.3	1264.0	1264.1	1264.4	1264.7	1265.0	1265.3	1265.0	1264.7	1264.4
160°	1286.8	1286.8	1286.8	1287.0	1287.5	1288.0	1288.5	1288.9	1288.5	1288.0	1287.5
162.5°	1307.4	1307.2	1307.0	1307.3	1308.0	1308.6	1309.3	1309.9	1309.3	1308.6	1308.0
165°	1333.9	1333.9	1333.9	1334.3	1334.9	1335.7	1336.4	1337.2	1336.4	1335.7	1334.9
167.5°	1354.9	1354.7	1354.5	1354.9	1355.9	1356.9	1357.8	1358.9	1357.8	1356.9	1355.9
170°	1366.7	1366.7	1366.7	1367.2	1368.2	1369.1	1370.1	1371.1	1370.1	1369.1	1368.2
172.5°	1376.4	1376.4	1376.4	1376.9	1377.8	1378.8	1379.8	1380.7	1379.8	1378.8	1377.8
175°	1386.4	1386.4	1386.4	1387.0	1387.9	1388.8	1389.9	1390.8	1389.9	1388.8	1387.9
177.5°	1391.5	1391.5	1391.5	1391.9	1392.6	1393.5	1394.2	1395.0	1394.2	1393.5	1392.6
180°	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1



TEST NUMBER: P332355-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4
2.5°	1472.7	1466.0	1461.4	1451.1	1444.5	1437.3	1430.1	1434.7	1434.3	1433.7	1433.7
5°	1423.3	1408.5	1395.2	1377.8	1366.9	1353.4	1343.1	1341.9	1344.4	1335.5	1330.3
7.5°	1374.3	1354.2	1335.1	1316.0	1295.7	1279.5	1269.4	1264.6	1258.1	1252.5	1246.8
10°	1339.9	1316.3	1297.6	1273.8	1252.1	1232.8	1220.7	1212.3	1207.8	1203.3	1195.0
12.5°	1304.6	1281.3	1257.6	1230.8	1210.0	1187.7	1178.6	1169.2	1160.6	1155.6	1144.2
15°	1252.7	1222.6	1197.6	1169.3	1146.2	1124.5	1111.6	1093.0	1090.4	1084.0	1072.5
17.5°	1200.8	1168.0	1133.5	1112.7	1086.6	1063.8	1044.3	1038.1	1019.7	1012.9	1002.8
20°	1159.7	1129.5	1103.2	1075.7	1037.8	1016.6	1001.3	993.0	978.2	969.2	962.8
22.5°	1124.3	1093.6	1063.3	1031.0	999.8	976.1	964.9	951.9	943.8	931.2	924.3
25°	1073.7	1040.4	1003.8	969.2	946.8	928.8	910.9	899.3	887.8	881.9	869.1
27.5°	1015.0	980.1	945.9	919.6	892.1	874.4	858.1	847.8	834.0	824.3	817.2
30°	982.7	941.6	912.1	888.3	853.1	836.4	824.3	811.4	801.2	790.9	783.8
32.5°	945.2	907.8	879.8	850.5	823.3	805.1	789.4	778.1	769.3	759.6	752.5
35°	886.5	855.1	826.1	796.6	776.7	758.2	739.6	729.9	721.6	712.7	706.2
37.5°	833.3	804.0	776.6	748.6	723.9	708.8	693.8	686.5	675.1	669.1	662.6
40°	800.5	771.7	742.2	715.2	689.6	678.0	664.5	653.7	643.4	638.9	631.8
42.5°	764.6	735.7	710.9	681.8	660.8	645.2	632.7	620.8	613.1	606.5	602.6
45°	711.3	685.7	661.3	632.4	612.6	599.1	584.9	574.1	567.0	562.5	555.4
47.5°	659.7	634.0	609.3	584.1	564.9	549.4	535.4	527.7	518.4	512.9	508.1
50°	622.2	599.1	572.8	549.7	530.5	515.1	503.5	493.9	485.6	478.5	475.3
52.5°	587.8	563.2	540.5	519.0	498.6	481.2	470.7	460.5	454.3	446.2	442.4
55°	531.1	507.4	488.1	466.9	447.0	432.3	419.5	410.5	404.1	395.1	390.0
57.5°	477.9	456.6	433.6	415.3	394.7	382.3	371.6	359.5	351.7	344.6	339.6
60°	442.0	417.5	397.7	380.4	362.4	346.4	336.8	327.2	318.8	311.7	307.3
62.5°	404.4	383.2	364.3	345.4	329.0	315.1	303.9	295.9	288.5	284.0	279.6
65°	347.0	330.4	311.1	295.7	280.3	270.0	261.1	254.0	248.8	245.6	241.9
67.5°	294.2	278.0	261.2	246.1	235.8	228.0	222.1	216.0	213.5	209.3	206.8
70°	259.8	243.1	228.4	216.8	206.5	200.8	196.9	192.5	189.8	184.7	182.2
72.5°	222.3	210.3	199.6	190.1	181.9	176.6	171.7	166.3	162.1	156.5	153.9
75°	175.1	164.2	155.9	149.5	144.3	137.2	130.2	124.4	122.5	120.6	120.0
77.5°	129.7	122.8	116.8	111.3	104.9	99.8	98.3	97.0	96.6	95.6	95.6
80°	102.0	95.6	91.0	84.6	80.8	80.8	80.8	79.6	80.2	80.2	80.2
82.5°	75.8	69.9	67.5	65.1	64.4	64.9	64.9	65.1	64.8	65.8	65.3
85°	39.1	39.8	41.1	40.4	41.1	41.1	42.3	41.7	42.3	41.1	42.3
87.5°	16.5	18.7	19.8	20.9	22.1	22.1	22.9	23.1	23.8	24.0	24.1
90°	10.8	13.7	16.8	20.0	23.1	26.3	27.2	28.3	29.2	30.2	30.9
92.5°	33.1	34.9	36.7	38.5	40.2	42.0	42.8	43.6	44.4	45.1	45.4
95°	71.4	73.2	75.2	77.1	79.1	81.1	82.0	82.9	84.0	84.9	85.4
97.5°	119.8	121.2	122.6	124.0	125.4	126.8	127.9	129.0	130.2	131.3	131.8
100°	154.8	156.1	157.3	158.5	159.8	161.0	161.7	162.4	163.2	163.9	164.5
102.5°	191.9	193.1	194.7	196.3	197.9	199.5	200.3	201.0	201.7	202.5	202.7
105°	248.4	249.7	251.8	254.1	256.3	258.4	258.4	258.4	258.4	258.4	258.7
107.5°	315.0	315.7	316.5	317.4	318.2	319.1	319.9	320.7	321.5	322.3	322.4
110°	357.9	358.4	358.8	359.3	359.8	360.3	361.3	362.2	363.3	364.2	364.4



TEST NUMBER: P332355-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	400.9	401.1	401.1	401.2	401.3	401.4	402.7	403.8	405.0	406.1	406.7
115°	468.3	468.4	468.0	467.5	467.0	466.6	466.7	467.0	467.2	467.5	467.5
117.5°	533.5	533.5	532.8	532.2	531.6	530.9	530.8	530.8	530.7	530.7	530.4
120°	578.6	578.7	577.5	576.3	575.0	573.8	573.6	573.3	573.2	572.9	572.5
122.5°	620.0	620.2	619.5	618.9	618.3	617.6	617.0	616.4	615.8	615.1	614.4
125°	684.1	684.2	683.7	683.2	682.8	682.3	681.3	680.3	679.4	678.3	677.4
127.5°	747.8	748.4	747.8	747.2	746.8	746.2	744.9	743.5	742.2	740.7	739.5
130°	789.7	790.3	789.6	788.8	788.2	787.4	786.5	785.4	784.5	783.5	782.1
132.5°	830.0	830.8	830.2	829.6	829.1	828.6	827.4	826.2	825.1	823.9	822.7
135°	889.6	890.2	889.9	889.8	889.5	889.2	888.3	887.3	886.3	885.3	884.6
137.5°	945.6	946.5	947.2	947.7	948.4	949.0	948.0	947.0	945.9	944.9	944.0
140°	985.0	985.7	986.0	986.2	986.5	986.7	986.5	986.2	986.0	985.7	984.8
142.5°	1021.0	1021.7	1022.2	1022.7	1023.0	1023.5	1023.2	1023.0	1022.8	1022.6	1021.7
145°	1074.0	1074.7	1075.4	1076.1	1076.9	1077.6	1077.3	1077.1	1076.9	1076.7	1076.0
147.5°	1124.7	1125.5	1126.1	1126.8	1127.5	1128.2	1128.2	1128.2	1128.2	1128.2	1127.5
150°	1157.3	1157.8	1158.3	1158.8	1159.2	1159.7	1159.7	1159.7	1159.7	1159.7	1159.0
152.5°	1186.1	1186.6	1186.8	1187.2	1187.5	1187.8	1188.2	1188.5	1188.9	1189.3	1188.9
155°	1227.7	1227.8	1228.0	1228.2	1228.5	1228.7	1229.7	1230.7	1231.6	1232.7	1232.3
157.5°	1264.1	1264.0	1264.3	1264.5	1264.7	1264.9	1265.9	1266.9	1267.9	1268.9	1268.8
160°	1287.0	1286.8	1286.8	1286.8	1286.8	1286.8	1288.0	1289.2	1290.4	1291.7	1291.8
162.5°	1307.3	1307.0	1307.2	1307.4	1307.6	1307.8	1309.0	1310.2	1311.5	1312.7	1312.5
165°	1334.3	1333.9	1333.9	1333.9	1333.9	1333.9	1335.3	1336.8	1338.2	1339.7	1339.5
167.5°	1354.9	1354.5	1354.7	1354.9	1355.1	1355.3	1356.8	1358.3	1359.8	1361.3	1361.3
170°	1367.2	1366.7	1366.7	1366.7	1366.7	1366.7	1368.4	1370.1	1371.9	1373.6	1373.6
172.5°	1376.9	1376.4	1376.4	1376.4	1376.4	1376.4	1377.9	1379.4	1380.9	1382.4	1382.3
175°	1387.0	1386.4	1386.4	1386.4	1386.4	1386.4	1387.9	1389.3	1390.8	1392.2	1392.1
177.5°	1391.9	1391.5	1391.5	1391.5	1391.5	1391.5	1392.6	1393.8	1395.0	1396.1	1396.0
180°	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1



TEST NUMBER: P332355-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4
2.5°	1427.6	1427.0	1427.6	1425.5	1427.6	1427.0	1427.6	1433.7	1433.7	1434.3	1434.7
5°	1328.4	1327.8	1325.9	1320.0	1325.9	1327.8	1328.4	1330.3	1335.5	1344.4	1341.9
7.5°	1241.8	1241.0	1235.3	1235.4	1235.3	1241.0	1241.8	1246.8	1252.5	1258.1	1264.6
10°	1190.5	1191.1	1183.5	1178.9	1183.5	1191.1	1190.5	1195.0	1203.3	1207.8	1212.3
12.5°	1140.8	1137.7	1131.6	1126.6	1131.6	1137.7	1140.8	1144.2	1155.6	1160.6	1169.2
15°	1075.1	1068.7	1053.2	1054.5	1053.2	1068.7	1075.1	1072.5	1084.0	1090.4	1093.0
17.5°	997.7	993.0	992.7	983.7	992.7	993.0	997.7	1002.8	1012.9	1019.7	1038.1
20°	952.5	949.3	950.6	941.6	950.6	949.3	952.5	962.8	969.2	978.2	993.0
22.5°	917.1	913.9	908.5	905.7	908.5	913.9	917.1	924.3	931.2	943.8	951.9
25°	865.3	860.2	855.1	858.3	855.1	860.2	865.3	869.1	881.9	887.8	899.3
27.5°	813.5	809.6	804.5	803.8	804.5	809.6	813.5	817.2	824.3	834.0	847.8
30°	780.6	776.7	774.2	771.0	774.2	776.7	780.6	783.8	790.9	801.2	811.4
32.5°	747.2	746.5	741.9	741.2	741.9	746.5	747.2	752.5	759.6	769.3	778.1
35°	703.6	699.8	698.5	699.2	698.5	699.8	703.6	706.2	712.7	721.6	729.9
37.5°	662.2	657.0	654.8	652.4	654.8	657.0	662.2	662.6	669.1	675.1	686.5
40°	632.4	627.4	626.0	624.7	626.0	627.4	632.4	631.8	638.9	643.4	653.7
42.5°	599.1	597.0	596.3	594.0	596.3	597.0	599.1	602.6	606.5	613.1	620.8
45°	553.6	552.9	549.0	550.4	549.0	552.9	553.6	555.4	562.5	567.0	574.1
47.5°	505.6	502.8	500.0	501.8	500.0	502.8	505.6	508.1	512.9	518.4	527.7
50°	472.8	471.5	465.7	466.9	465.7	471.5	472.8	475.3	478.5	485.6	493.9
52.5°	439.9	435.0	432.8	432.1	432.8	435.0	439.9	442.4	446.2	454.3	460.5
55°	385.5	379.8	377.2	375.9	377.2	379.8	385.5	390.0	395.1	404.1	410.5
57.5°	332.2	330.5	328.6	330.0	328.6	330.5	332.2	339.6	344.6	351.7	359.5
60°	300.9	300.9	300.9	300.2	300.9	300.9	300.9	307.3	311.7	318.8	327.2
62.5°	276.7	275.1	274.7	275.6	274.7	275.1	276.7	279.6	284.0	288.5	295.9
65°	239.9	239.2	236.7	236.0	236.7	239.2	239.9	241.9	245.6	248.8	254.0
67.5°	205.1	202.8	202.1	201.1	202.1	202.8	205.1	206.8	209.3	213.5	216.0
70°	179.0	177.7	173.8	174.5	173.8	177.7	179.0	182.2	184.7	189.8	192.5
72.5°	150.7	149.5	148.6	147.8	148.6	149.5	150.7	153.9	156.5	162.1	166.3
75°	119.3	118.7	118.0	120.6	118.0	118.7	119.3	120.0	120.6	122.5	124.4
77.5°	95.6	95.6	96.0	94.9	96.0	95.6	95.6	95.6	95.6	96.6	97.0
80°	80.2	80.2	79.6	79.6	79.6	80.2	80.2	80.2	80.2	80.2	79.6
82.5°	64.3	64.8	65.1	64.2	65.1	64.8	64.3	65.3	65.8	64.8	65.1
85°	42.3	41.7	43.0	42.3	43.0	41.7	42.3	42.3	41.1	42.3	41.7
87.5°	25.3	24.3	24.4	25.1	24.4	24.3	25.3	24.1	24.0	23.8	23.1
90°	31.4	31.9	32.3	32.9	32.3	31.9	31.4	30.9	30.2	29.2	28.3
92.5°	45.1	44.9	44.5	44.2	44.5	44.9	45.1	45.4	45.1	44.4	43.6
95°	85.4	85.4	85.4	85.4	85.4	85.4	85.4	85.4	84.9	84.0	82.9
97.5°	131.7	131.6	131.5	131.4	131.5	131.6	131.7	131.8	131.3	130.2	129.0
100°	165.0	165.5	166.0	166.5	166.0	165.5	165.0	164.5	163.9	163.2	162.4
102.5°	202.6	202.6	202.5	202.4	202.5	202.6	202.6	202.7	202.5	201.7	201.0
105°	259.2	259.7	260.1	260.6	260.1	259.7	259.2	258.7	258.4	258.4	258.4
107.5°	322.2	321.9	321.6	321.3	321.6	321.9	322.2	322.4	322.3	321.5	320.7
110°	363.9	363.4	363.0	362.5	363.0	363.4	363.9	364.4	364.2	363.3	362.2



TEST NUMBER: P332355-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	406.6	406.5	406.4	406.3	406.4	406.5	406.6	406.7	406.1	405.0	403.8
115°	467.2	467.0	466.7	466.6	466.7	467.0	467.2	467.5	467.5	467.2	467.0
117.5°	529.7	529.0	528.3	527.6	528.3	529.0	529.7	530.4	530.7	530.7	530.8
120°	572.0	571.6	571.1	570.5	571.1	571.6	572.0	572.5	572.9	573.2	573.3
122.5°	613.8	613.1	612.4	611.7	612.4	613.1	613.8	614.4	615.1	615.8	616.4
125°	676.5	675.4	674.5	673.5	674.5	675.4	676.5	677.4	678.3	679.4	680.3
127.5°	738.4	737.3	736.1	735.1	736.1	737.3	738.4	739.5	740.7	742.2	743.5
130°	780.4	778.7	777.0	775.3	777.0	778.7	780.4	782.1	783.5	784.5	785.4
132.5°	821.3	820.0	818.7	817.4	818.7	820.0	821.3	822.7	823.9	825.1	826.2
135°	884.1	883.6	883.2	882.7	883.2	883.6	884.1	884.6	885.3	886.3	887.3
137.5°	943.0	942.2	941.2	940.3	941.2	942.2	943.0	944.0	944.9	945.9	947.0
140°	983.1	981.4	979.7	978.0	979.7	981.4	983.1	984.8	985.7	986.0	986.2
142.5°	1020.4	1019.1	1017.9	1016.5	1017.9	1019.1	1020.4	1021.7	1022.6	1022.8	1023.0
145°	1075.1	1074.0	1073.1	1072.1	1073.1	1074.0	1075.1	1076.0	1076.7	1076.9	1077.1
147.5°	1126.0	1124.5	1123.0	1121.6	1123.0	1124.5	1126.0	1127.5	1128.2	1128.2	1128.2
150°	1157.5	1156.1	1154.6	1153.2	1154.6	1156.1	1157.5	1159.0	1159.7	1159.7	1159.7
152.5°	1187.6	1186.4	1185.1	1183.8	1185.1	1186.4	1187.6	1188.9	1189.3	1188.9	1188.5
155°	1230.6	1228.9	1227.2	1225.4	1227.2	1228.9	1230.6	1232.3	1232.7	1231.6	1230.7
157.5°	1267.4	1266.0	1264.7	1263.3	1264.7	1266.0	1267.4	1268.8	1268.9	1267.9	1266.9
160°	1290.8	1289.8	1288.8	1287.9	1288.8	1289.8	1290.8	1291.8	1291.7	1290.4	1289.2
162.5°	1310.9	1309.4	1307.8	1306.3	1307.8	1309.4	1310.9	1312.5	1312.7	1311.5	1310.2
165°	1337.8	1336.1	1334.5	1332.8	1334.5	1336.1	1337.8	1339.5	1339.7	1338.2	1336.8
167.5°	1359.8	1358.3	1356.8	1355.3	1356.8	1358.3	1359.8	1361.3	1361.3	1359.8	1358.3
170°	1371.9	1370.1	1368.4	1366.7	1368.4	1370.1	1371.9	1373.6	1373.6	1371.9	1370.1
172.5°	1380.5	1378.8	1377.1	1375.5	1377.1	1378.8	1380.5	1382.3	1382.4	1380.9	1379.4
175°	1390.4	1388.7	1387.0	1385.3	1387.0	1388.7	1390.4	1392.1	1392.2	1390.8	1389.3
177.5°	1394.7	1393.3	1391.9	1390.6	1391.9	1393.3	1394.7	1396.0	1396.1	1395.0	1393.8
180°	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1



TEST NUMBER: P332355-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4
2.5°	1430.1	1437.3	1444.5	1451.1	1461.4	1466.0	1472.7	1475.3	1483.0	1494.3	1503.5
5°	1343.1	1353.4	1366.9	1377.8	1395.2	1408.5	1423.3	1437.5	1454.2	1477.8	1499.0
7.5°	1269.4	1279.5	1295.7	1316.0	1335.1	1354.2	1374.3	1393.5	1417.4	1451.4	1485.2
10°	1220.7	1232.8	1252.1	1273.8	1297.6	1316.3	1339.9	1364.3	1393.8	1432.9	1473.4
12.5°	1178.6	1187.7	1210.0	1230.8	1257.6	1281.3	1304.6	1333.0	1366.6	1408.3	1457.0
15°	1111.6	1124.5	1146.2	1169.3	1197.6	1222.6	1252.7	1287.3	1320.0	1371.4	1430.4
17.5°	1044.3	1063.8	1086.6	1112.7	1133.5	1168.0	1200.8	1236.3	1276.6	1331.0	1395.7
20°	1001.3	1016.6	1037.8	1075.7	1103.2	1129.5	1159.7	1204.0	1241.1	1302.8	1370.1
22.5°	964.9	976.1	999.8	1031.0	1063.3	1093.6	1124.3	1166.5	1212.4	1270.9	1344.0
25°	910.9	928.8	946.8	969.2	1003.8	1040.4	1073.7	1109.7	1158.4	1220.7	1299.6
27.5°	858.1	874.4	892.1	919.6	945.9	980.1	1015.0	1056.2	1108.5	1174.3	1254.3
30°	824.3	836.4	853.1	888.3	912.1	941.6	982.7	1019.3	1068.0	1137.9	1222.6
32.5°	789.4	805.1	823.3	850.5	879.8	907.8	945.2	984.9	1034.6	1103.5	1190.2
35°	739.6	758.2	776.7	796.6	826.1	855.1	886.5	930.1	980.7	1047.4	1132.7
37.5°	693.8	708.8	723.9	748.6	776.6	804.0	833.3	876.3	924.1	996.0	1074.3
40°	664.5	678.0	689.6	715.2	742.2	771.7	800.5	838.4	889.7	957.1	1032.7
42.5°	632.7	645.2	660.8	681.8	710.9	735.7	764.6	800.4	848.6	917.0	983.4
45°	584.9	599.1	612.6	632.4	661.3	685.7	711.3	745.4	794.8	851.2	910.2
47.5°	535.4	549.4	564.9	584.1	609.3	634.0	659.7	689.8	734.8	790.2	830.0
50°	503.5	515.1	530.5	549.7	572.8	599.1	622.2	654.9	697.9	741.5	776.1
52.5°	470.7	481.2	498.6	519.0	540.5	563.2	587.8	615.9	654.8	695.8	723.3
55°	419.5	432.3	447.0	466.9	488.1	507.4	531.1	560.0	590.8	621.5	640.2
57.5°	371.6	382.3	394.7	415.3	433.6	456.6	477.9	500.3	528.8	552.0	564.2
60°	336.8	346.4	362.4	380.4	397.7	417.5	442.0	464.4	486.2	504.8	514.4
62.5°	303.9	315.1	329.0	345.4	364.3	383.2	404.4	423.4	442.6	458.6	465.1
65°	261.1	270.0	280.3	295.7	311.1	330.4	347.0	366.3	380.4	389.4	395.1
67.5°	222.1	228.0	235.8	246.1	261.2	278.0	294.2	309.2	320.9	327.2	332.2
70°	196.9	200.8	206.5	216.8	228.4	243.1	259.8	270.7	281.0	286.1	291.2
72.5°	171.7	176.6	181.9	190.1	199.6	210.3	222.3	235.8	241.5	247.6	250.7
75°	130.2	137.2	144.3	149.5	155.9	164.2	175.1	183.4	186.6	191.8	192.5
77.5°	98.3	99.8	104.9	111.3	116.8	122.8	129.7	137.1	138.6	141.4	143.1
80°	80.8	80.8	80.8	84.6	91.0	95.6	102.0	105.8	108.4	109.1	109.7
82.5°	64.9	64.9	64.4	65.1	67.5	69.9	75.8	80.2	82.2	81.8	80.4
85°	42.3	41.1	41.1	40.4	41.1	39.8	39.1	41.7	45.5	45.5	44.3
87.5°	22.9	22.1	22.1	20.9	19.8	18.7	16.5	16.6	16.1	17.6	16.7
90°	27.2	26.3	23.1	20.0	16.8	13.7	10.8	8.4	5.9	3.5	1.1
92.5°	42.8	42.0	40.2	38.5	36.7	34.9	33.1	31.5	29.8	28.2	26.5
95°	82.0	81.1	79.1	77.1	75.2	73.2	71.4	69.7	68.1	66.4	64.7
97.5°	127.9	126.8	125.4	124.0	122.6	121.2	119.8	118.6	117.3	116.0	114.8
100°	161.7	161.0	159.8	158.5	157.3	156.1	154.8	153.4	151.8	150.4	148.9
102.5°	200.3	199.5	197.9	196.3	194.7	193.1	191.9	191.0	190.1	189.3	188.3
105°	258.4	258.4	256.3	254.1	251.8	249.7	248.4	247.9	247.4	246.9	246.4
107.5°	319.9	319.1	318.2	317.4	316.5	315.7	315.0	314.7	314.4	314.1	313.9
110°	361.3	360.3	359.8	359.3	358.8	358.4	357.9	357.4	356.8	356.4	355.9



TEST NUMBER: P332355-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	402.7	401.4	401.3	401.2	401.1	401.1	400.9	400.6	400.3	400.0	399.7
115°	466.7	466.6	467.0	467.5	468.0	468.4	468.3	467.6	466.8	466.2	465.4
117.5°	530.8	530.9	531.6	532.2	532.8	533.5	533.5	533.0	532.5	532.1	531.6
120°	573.6	573.8	575.0	576.3	577.5	578.7	578.6	577.1	575.7	574.2	572.8
122.5°	617.0	617.6	618.3	618.9	619.5	620.2	620.0	618.9	617.8	616.7	615.7
125°	681.3	682.3	682.8	683.2	683.7	684.2	684.1	683.3	682.6	681.9	681.2
127.5°	744.9	746.2	746.8	747.2	747.8	748.4	747.8	746.3	744.7	743.2	741.6
130°	786.5	787.4	788.2	788.8	789.6	790.3	789.7	787.8	785.8	783.8	781.9
132.5°	827.4	828.6	829.1	829.6	830.2	830.8	830.0	828.0	826.1	824.2	822.2
135°	888.3	889.2	889.5	889.8	889.9	890.2	889.6	888.2	886.6	885.2	883.7
137.5°	948.0	949.0	948.4	947.7	947.2	946.5	945.6	944.3	943.1	941.9	940.8
140°	986.5	986.7	986.5	986.2	986.0	985.7	985.0	983.8	982.6	981.4	980.1
142.5°	1023.2	1023.5	1023.0	1022.7	1022.2	1021.7	1021.0	1019.7	1018.5	1017.3	1016.1
145°	1077.3	1077.6	1076.9	1076.1	1075.4	1074.7	1074.0	1073.6	1073.1	1072.6	1072.1
147.5°	1128.2	1128.2	1127.5	1126.8	1126.1	1125.5	1124.7	1123.8	1122.9	1122.1	1121.2
150°	1159.7	1159.7	1159.2	1158.8	1158.3	1157.8	1157.3	1156.8	1156.3	1155.8	1155.4
152.5°	1188.2	1187.8	1187.5	1187.2	1186.8	1186.6	1186.1	1185.4	1184.8	1184.1	1183.4
155°	1229.7	1228.7	1228.5	1228.2	1228.0	1227.8	1227.7	1227.7	1227.7	1227.7	1227.7
157.5°	1265.9	1264.9	1264.7	1264.5	1264.3	1264.0	1264.1	1264.4	1264.7	1265.0	1265.3
160°	1288.0	1286.8	1286.8	1286.8	1286.8	1286.8	1287.0	1287.5	1288.0	1288.5	1288.9
162.5°	1309.0	1307.8	1307.6	1307.4	1307.2	1307.0	1307.3	1308.0	1308.6	1309.3	1309.9
165°	1335.3	1333.9	1333.9	1333.9	1333.9	1333.9	1334.3	1334.9	1335.7	1336.4	1337.2
167.5°	1356.8	1355.3	1355.1	1354.9	1354.7	1354.5	1354.9	1355.9	1356.9	1357.8	1358.9
170°	1368.4	1366.7	1366.7	1366.7	1366.7	1366.7	1367.2	1368.2	1369.1	1370.1	1371.1
172.5°	1377.9	1376.4	1376.4	1376.4	1376.4	1376.4	1376.9	1377.8	1378.8	1379.8	1380.7
175°	1387.9	1386.4	1386.4	1386.4	1386.4	1386.4	1387.0	1387.9	1388.8	1389.9	1390.8
177.5°	1392.6	1391.5	1391.5	1391.5	1391.5	1391.5	1391.9	1392.6	1393.5	1394.2	1395.0
180°	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1



TEST NUMBER: P332355-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4
2.5°	1506.6	1512.2	1519.4	1530.2	1538.4	1545.6	1547.1	1549.2	1554.3	1563.0	1569.7
5°	1516.4	1531.1	1554.8	1577.9	1603.0	1623.4	1642.7	1656.1	1669.0	1695.9	1717.8
7.5°	1513.3	1546.1	1583.3	1624.8	1666.7	1707.3	1745.1	1778.9	1812.4	1851.7	1896.5
10°	1511.2	1549.7	1599.7	1652.9	1711.4	1768.4	1823.6	1866.6	1916.6	1961.5	2018.5
12.5°	1501.5	1556.9	1616.6	1684.8	1756.5	1822.3	1894.9	1954.3	2011.6	2076.4	2142.8
15°	1488.7	1556.1	1631.8	1722.2	1831.3	1910.8	1985.2	2088.5	2159.1	2229.6	2324.6
17.5°	1465.6	1547.7	1642.3	1759.8	1850.8	1957.7	2069.6	2151.3	2246.3	2345.7	2431.7
20°	1447.1	1542.7	1648.5	1764.0	1880.0	1996.1	2104.5	2202.1	2300.2	2415.0	2485.6
22.5°	1428.6	1523.1	1633.0	1755.8	1880.6	2002.8	2125.5	2240.0	2350.4	2466.3	2556.4
25°	1389.3	1501.6	1620.9	1746.0	1869.2	2003.8	2150.0	2277.7	2414.3	2533.6	2618.9
27.5°	1349.5	1452.5	1571.2	1698.1	1835.0	1994.2	2166.2	2311.3	2448.3	2533.6	2560.5
30°	1313.6	1422.7	1531.7	1660.7	1808.8	1986.5	2169.4	2335.4	2447.7	2484.9	2457.3
32.5°	1277.2	1376.0	1484.0	1616.0	1773.4	1967.6	2173.4	2321.1	2388.7	2360.2	2248.0
35°	1213.0	1302.1	1406.7	1538.8	1719.7	1957.0	2156.5	2256.5	2239.9	2079.5	1867.8
37.5°	1144.2	1216.8	1313.6	1451.8	1664.0	1915.3	2083.6	2098.4	1954.1	1707.9	1463.4
40°	1089.8	1155.2	1254.6	1398.9	1620.9	1874.2	2010.3	1950.6	1726.7	1452.8	1248.9
42.5°	1036.9	1092.1	1187.9	1343.5	1579.9	1818.4	1900.9	1771.0	1512.8	1253.8	1068.3
45°	947.3	999.4	1095.5	1255.3	1495.8	1711.4	1700.4	1474.6	1216.2	1007.7	853.8
47.5°	862.4	907.9	998.2	1161.2	1397.1	1551.0	1449.0	1208.7	989.5	822.2	712.4
50°	802.4	847.3	937.2	1098.2	1318.1	1430.4	1284.8	1053.2	852.4	713.9	626.7
52.5°	745.0	788.8	870.9	1027.8	1222.7	1289.8	1133.4	918.8	751.4	631.8	556.9
55°	664.5	697.9	771.7	921.7	1067.3	1082.7	924.3	744.7	606.8	523.4	472.1
57.5°	582.6	611.2	684.2	803.7	905.8	897.9	747.6	592.3	499.5	437.4	400.3
60°	529.1	557.4	621.5	724.2	801.2	774.2	636.3	511.2	431.7	386.2	356.7
62.5°	479.4	501.4	561.5	636.4	691.8	661.3	543.9	440.5	377.3	338.9	315.6
65°	407.3	425.3	473.3	512.5	543.3	513.8	416.3	344.4	298.9	271.9	255.9
67.5°	338.8	350.2	380.6	394.7	416.4	384.1	313.0	264.9	239.0	216.3	205.1
70°	295.7	304.1	320.1	331.6	337.4	304.1	251.5	216.1	194.4	178.3	171.3
72.5°	252.6	260.0	263.2	272.6	269.7	238.4	202.2	174.1	158.4	147.5	138.5
75°	193.0	196.2	193.0	189.3	180.9	159.1	134.0	120.0	108.4	103.3	100.1
77.5°	140.7	139.7	135.3	129.3	115.1	101.3	87.8	83.1	78.1	75.4	74.3
80°	108.4	105.8	102.0	92.4	80.2	70.6	67.4	64.2	62.2	59.0	58.3
82.5°	80.7	79.2	72.8	64.7	56.1	51.6	48.9	47.7	45.8	44.1	44.0
85°	43.0	41.1	34.0	29.5	28.2	27.0	26.3	26.3	23.8	23.1	23.1
87.5°	14.5	12.0	12.0	10.9	11.4	11.0	12.2	11.8	12.0	12.6	11.8
90°	3.5	5.9	8.4	10.8	13.7	16.8	20.0	23.1	26.3	27.2	28.3
92.5°	28.2	29.8	31.5	33.1	34.9	36.7	38.5	40.2	42.0	42.8	43.6
95°	66.4	68.1	69.7	71.4	73.2	75.2	77.1	79.1	81.1	82.0	82.9
97.5°	116.0	117.3	118.6	119.8	121.2	122.6	124.0	125.4	126.8	127.9	129.0
100°	150.4	151.8	153.4	154.8	156.1	157.3	158.5	159.8	161.0	161.7	162.4
102.5°	189.3	190.1	191.0	191.9	193.1	194.7	196.3	197.9	199.5	200.3	201.0
105°	246.9	247.4	247.9	248.4	249.7	251.8	254.1	256.3	258.4	258.4	258.4
107.5°	314.1	314.4	314.7	315.0	315.7	316.5	317.4	318.2	319.1	319.9	320.7
110°	356.4	356.8	357.4	357.9	358.4	358.8	359.3	359.8	360.3	361.3	362.2





TEST NUMBER: P332355-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	400.0	400.3	400.6	400.9	401.1	401.1	401.2	401.3	401.4	402.7	403.8
115°	466.2	466.8	467.6	468.3	468.4	468.0	467.5	467.0	466.6	466.7	467.0
117.5°	532.1	532.5	533.0	533.5	533.5	532.8	532.2	531.6	530.9	530.8	530.8
120°	574.2	575.7	577.1	578.6	578.7	577.5	576.3	575.0	573.8	573.6	573.3
122.5°	616.7	617.8	618.9	620.0	620.2	619.5	618.9	618.3	617.6	617.0	616.4
125°	681.9	682.6	683.3	684.1	684.2	683.7	683.2	682.8	682.3	681.3	680.3
127.5°	743.2	744.7	746.3	747.8	748.4	747.8	747.2	746.8	746.2	744.9	743.5
130°	783.8	785.8	787.8	789.7	790.3	789.6	788.8	788.2	787.4	786.5	785.4
132.5°	824.2	826.1	828.0	830.0	830.8	830.2	829.6	829.1	828.6	827.4	826.2
135°	885.2	886.6	888.2	889.6	890.2	889.9	889.8	889.5	889.2	888.3	887.3
137.5°	941.9	943.1	944.3	945.6	946.5	947.2	947.7	948.4	949.0	948.0	947.0
140°	981.4	982.6	983.8	985.0	985.7	986.0	986.2	986.5	986.7	986.5	986.2
142.5°	1017.3	1018.5	1019.7	1021.0	1021.7	1022.2	1022.7	1023.0	1023.5	1023.2	1023.0
145°	1072.6	1073.1	1073.6	1074.0	1074.7	1075.4	1076.1	1076.9	1077.6	1077.3	1077.1
147.5°	1122.1	1122.9	1123.8	1124.7	1125.5	1126.1	1126.8	1127.5	1128.2	1128.2	1128.2
150°	1155.8	1156.3	1156.8	1157.3	1157.8	1158.3	1158.8	1159.2	1159.7	1159.7	1159.7
152.5°	1184.1	1184.8	1185.4	1186.1	1186.6	1186.8	1187.2	1187.5	1187.8	1188.2	1188.5
155°	1227.7	1227.7	1227.7	1227.7	1227.8	1228.0	1228.2	1228.5	1228.7	1229.7	1230.7
157.5°	1265.0	1264.7	1264.4	1264.1	1264.0	1264.3	1264.5	1264.7	1264.9	1265.9	1266.9
160°	1288.5	1288.0	1287.5	1287.0	1286.8	1286.8	1286.8	1286.8	1286.8	1288.0	1289.2
162.5°	1309.3	1308.6	1308.0	1307.3	1307.0	1307.2	1307.4	1307.6	1307.8	1309.0	1310.2
165°	1336.4	1335.7	1334.9	1334.3	1333.9	1333.9	1333.9	1333.9	1333.9	1335.3	1336.8
167.5°	1357.8	1356.9	1355.9	1354.9	1354.5	1354.7	1354.9	1355.1	1355.3	1356.8	1358.3
170°	1370.1	1369.1	1368.2	1367.2	1366.7	1366.7	1366.7	1366.7	1366.7	1368.4	1370.1
172.5°	1379.8	1378.8	1377.8	1376.9	1376.4	1376.4	1376.4	1376.4	1376.4	1377.9	1379.4
175°	1389.9	1388.8	1387.9	1387.0	1386.4	1386.4	1386.4	1386.4	1386.4	1387.9	1389.3
177.5°	1394.2	1393.5	1392.6	1391.9	1391.5	1391.5	1391.5	1391.5	1391.5	1392.6	1393.8
180°	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1



TEST NUMBER: P332355-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4
2.5°	1580.5	1580.5	1582.5	1590.3	1591.3	1597.9	1595.9
5°	1737.0	1749.2	1753.7	1772.9	1784.4	1789.6	1779.3
7.5°	1928.4	1962.8	1979.1	1999.2	2017.0	2022.4	2008.5
10°	2067.9	2103.8	2134.0	2152.7	2169.9	2181.5	2196.2
12.5°	2202.9	2247.0	2275.7	2302.0	2319.8	2334.4	2336.8
15°	2349.6	2416.3	2466.9	2504.1	2522.7	2532.3	2528.6
17.5°	2497.5	2559.3	2595.4	2633.4	2659.1	2660.4	2661.2
20°	2581.2	2641.4	2683.1	2711.3	2740.2	2738.9	2745.3
22.5°	2637.0	2684.5	2716.5	2737.0	2746.9	2742.0	2743.3
25°	2663.2	2677.3	2671.5	2638.8	2630.5	2600.4	2605.5
27.5°	2528.3	2461.5	2392.6	2303.8	2233.7	2177.7	2180.6
30°	2345.0	2227.0	2092.4	1979.4	1878.1	1849.9	1789.6
32.5°	2089.1	1911.9	1754.2	1649.0	1562.0	1538.4	1485.8
35°	1654.9	1483.0	1320.7	1223.2	1184.7	1130.9	1130.2
37.5°	1286.3	1134.9	1049.1	976.0	937.6	905.0	901.8
40°	1082.1	964.0	899.3	846.7	808.9	784.5	778.7
42.5°	939.4	844.0	783.3	750.7	721.6	709.1	699.6
45°	767.1	703.0	660.6	631.1	617.7	608.0	602.9
47.5°	641.7	598.7	569.9	550.3	539.3	529.1	531.9
50°	573.4	538.2	517.0	498.4	490.0	483.0	483.6
52.5°	518.5	486.8	469.8	456.3	445.9	440.9	438.5
55°	440.0	420.1	402.8	393.2	387.4	380.4	378.4
57.5°	375.3	360.0	345.8	335.0	333.6	326.8	327.6
60°	332.2	319.4	307.9	302.1	297.7	291.8	293.8
62.5°	296.9	286.1	275.6	270.8	266.4	262.1	263.0
65°	243.1	232.8	226.4	223.9	222.0	220.0	218.1
67.5°	193.7	187.5	183.4	178.0	174.0	173.3	171.4
70°	163.0	154.6	147.5	140.4	138.6	137.9	138.6
72.5°	130.6	125.4	123.4	120.0	119.6	117.9	119.0
75°	98.1	96.2	94.9	92.4	92.4	92.4	92.4
77.5°	72.4	71.2	70.4	69.9	69.3	68.3	68.2
80°	56.5	55.8	54.5	54.5	53.9	54.5	53.9
82.5°	42.6	42.5	41.2	41.2	40.5	40.2	40.5
85°	21.8	21.2	22.4	21.2	21.8	20.5	21.8
87.5°	12.0	12.2	11.8	12.0	11.5	12.6	11.7
90°	29.2	30.2	30.9	31.4	31.9	32.3	32.9
92.5°	44.4	45.1	45.4	45.1	44.9	44.5	44.2
95°	84.0	84.9	85.4	85.4	85.4	85.4	85.4
97.5°	130.2	131.3	131.8	131.7	131.6	131.5	131.4
100°	163.2	163.9	164.5	165.0	165.5	166.0	166.5
102.5°	201.7	202.5	202.7	202.6	202.6	202.5	202.4
105°	258.4	258.4	258.7	259.2	259.7	260.1	260.6
107.5°	321.5	322.3	322.4	322.2	321.9	321.6	321.3
110°	363.3	364.2	364.4	363.9	363.4	363.0	362.5



TEST NUMBER: P332355-830

CATALOG NUMBER: S123RDIP-S1000D1195U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	405.0	406.1	406.7	406.6	406.5	406.4	406.3
115°	467.2	467.5	467.5	467.2	467.0	466.7	466.6
117.5°	530.7	530.7	530.4	529.7	529.0	528.3	527.6
120°	573.2	572.9	572.5	572.0	571.6	571.1	570.5
122.5°	615.8	615.1	614.4	613.8	613.1	612.4	611.7
125°	679.4	678.3	677.4	676.5	675.4	674.5	673.5
127.5°	742.2	740.7	739.5	738.4	737.3	736.1	735.1
130°	784.5	783.5	782.1	780.4	778.7	777.0	775.3
132.5°	825.1	823.9	822.7	821.3	820.0	818.7	817.4
135°	886.3	885.3	884.6	884.1	883.6	883.2	882.7
137.5°	945.9	944.9	944.0	943.0	942.2	941.2	940.3
140°	986.0	985.7	984.8	983.1	981.4	979.7	978.0
142.5°	1022.8	1022.6	1021.7	1020.4	1019.1	1017.9	1016.5
145°	1076.9	1076.7	1076.0	1075.1	1074.0	1073.1	1072.1
147.5°	1128.2	1128.2	1127.5	1126.0	1124.5	1123.0	1121.6
150°	1159.7	1159.7	1159.0	1157.5	1156.1	1154.6	1153.2
152.5°	1188.9	1189.3	1188.9	1187.6	1186.4	1185.1	1183.8
155°	1231.6	1232.7	1232.3	1230.6	1228.9	1227.2	1225.4
157.5°	1267.9	1268.9	1268.8	1267.4	1266.0	1264.7	1263.3
160°	1290.4	1291.7	1291.8	1290.8	1289.8	1288.8	1287.9
162.5°	1311.5	1312.7	1312.5	1310.9	1309.4	1307.8	1306.3
165°	1338.2	1339.7	1339.5	1337.8	1336.1	1334.5	1332.8
167.5°	1359.8	1361.3	1361.3	1359.8	1358.3	1356.8	1355.3
170°	1371.9	1373.6	1373.6	1371.9	1370.1	1368.4	1366.7
172.5°	1380.9	1382.4	1382.3	1380.5	1378.8	1377.1	1375.5
175°	1390.8	1392.2	1392.1	1390.4	1388.7	1387.0	1385.3
177.5°	1395.0	1396.1	1396.0	1394.7	1393.3	1391.9	1390.6
180°	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1

(END OF REPORT)