

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332383

Luminaire Tested: **S123RDIP-S1165D1025U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332383
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D1025U835-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8092.1 lumens
Efficiency: N/A
Efficacy: 121.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332383

CATALOG NUMBER: S123RDIP-S1165D1025U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332383

CATALOG NUMBER: S123RDIP-S1165D1025U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	54	52	51	46
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	39
3	83	73	66	61	77	68	62	57	59	54	50	50	47	44	42	40	38	34
4	76	65	57	51	70	61	54	49	53	47	43	45	41	38	38	35	33	29
5	70	58	50	44	65	55	47	42	47	42	37	41	36	33	34	31	29	26
6	64	52	44	39	60	49	42	37	43	37	33	37	32	29	31	28	25	23
7	60	47	40	34	55	45	37	32	39	33	29	34	29	26	29	25	23	20
8	55	43	35	30	51	41	34	29	36	30	26	31	26	23	26	23	20	18
9	52	40	32	27	48	37	30	26	33	27	23	28	24	21	24	21	19	16
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20863	20863	20863
5°	20942	20653	20772
10°	20824	20394	20325
15°	20600	19917	19706
20°	20292	19321	18871
25°	19975	18650	18053
30°	19557	17877	16900
35°	19127	17102	15843
40°	18730	16190	14533
45°	18209	15289	13352
50°	17637	14267	12030
55°	17051	13097	10796
60°	16514	11845	9442
65°	15814	10488	8087
70°	14940	8806	6530
75°	13662	6929	6147
80°	12180	6137	5653
85°	10288	5434	5051



TEST NUMBER: P332383

CATALOG NUMBER: S123RDIP-S1165D1025U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.0	2.2
10°-20°	506.4	6.3
20°-30°	729.2	9.0
30°-40°	821.3	10.1
40°-50°	785.8	9.7
50°-60°	643.5	8.0
60°-70°	434.1	5.4
70°-80°	218.4	2.7
80°-90°	61.6	0.8
90°-100°	274.4	3.4
100°-110°	777.0	9.6
110°-120°	764.4	9.4
120°-130°	609.7	7.5
130°-140°	480.7	5.9
140°-150°	358.8	4.4
150°-160°	250.1	3.1
160°-170°	146.9	1.8
170°-180°	47.8	0.6
0°-30°	1417.6	17.5
0°-40°	2238.9	27.7
0°-60°	3668.1	45.3
0°-90°	4382.3	54.2
90°-120°	1815.8	22.4
90°-150°	3265.1	40.3
90°-180°	3710.0	45.8
0°-180°	8092.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1938	1938	1938	1938	1938	
5°	1938	1930	1911	1925	1922	184
15°	1849	1830	1787	1779	1768	521
25°	1682	1641	1570	1538	1520	773
35°	1456	1397	1302	1236	1206	911
45°	1196	1123	1004	918	877	923
55°	909	828	698	610	575	814
65°	621	532	412	338	318	614
75°	328	252	167	152	148	350
85°	83	50	44	41	41	94
90°	2	12	25	28	29	6
95°	34	110	592	173	116	37
105°	116	171	802	1403	1270	123
115°	205	255	614	1346	1544	203
125°	284	336	573	1038	1218	252
135°	333	398	565	855	987	258
145°	380	436	558	701	772	238
155°	432	466	540	614	640	199
165°	472	486	517	548	558	133
175°	492	493	496	503	502	47
180°	493	493	493	493	493	



TEST NUMBER: P332383

CATALOG NUMBER: S123RDIP-S1165D1025U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2
2.5°	1944.5	1943.3	1942.2	1941.1	1940.0	1937.7	1934.4	1931.0	1927.7	1924.3	1927.4
5°	1938.2	1936.4	1934.7	1932.9	1931.2	1928.2	1924.0	1919.8	1915.6	1911.4	1914.6
7.5°	1920.2	1918.4	1916.5	1914.6	1912.7	1909.0	1903.6	1898.1	1892.7	1887.2	1889.0
10°	1905.2	1902.7	1900.3	1897.8	1895.4	1891.0	1884.7	1878.4	1872.1	1865.9	1866.2
12.5°	1883.8	1881.1	1878.3	1875.6	1872.9	1867.7	1860.0	1852.3	1844.6	1836.9	1836.7
15°	1848.6	1844.7	1840.9	1837.0	1833.2	1826.4	1816.6	1806.8	1797.0	1787.3	1785.5
17.5°	1804.2	1799.8	1795.3	1790.8	1786.4	1777.9	1765.5	1753.0	1740.6	1728.2	1724.5
20°	1771.5	1766.0	1760.4	1754.8	1749.2	1739.8	1726.5	1713.2	1699.9	1686.7	1682.1
22.5°	1735.1	1728.6	1722.2	1715.8	1709.4	1699.1	1685.0	1670.9	1656.8	1642.6	1637.0
25°	1681.9	1673.2	1664.5	1655.7	1647.0	1634.6	1618.5	1602.5	1586.4	1570.3	1563.0
27.5°	1617.5	1607.9	1598.2	1588.6	1578.9	1565.2	1547.3	1529.4	1511.5	1493.6	1483.4
30°	1573.5	1563.0	1552.5	1542.0	1531.6	1516.5	1497.0	1477.4	1457.9	1438.3	1426.4
32.5°	1529.5	1517.6	1505.7	1493.8	1482.0	1465.7	1445.0	1424.3	1403.6	1383.0	1370.0
35°	1455.6	1443.0	1430.4	1417.9	1405.3	1388.2	1366.5	1344.9	1323.2	1301.5	1286.5
37.5°	1380.8	1366.8	1352.8	1338.8	1324.9	1306.3	1283.2	1260.1	1237.0	1213.8	1196.8
40°	1333.0	1317.6	1302.2	1286.9	1271.5	1251.4	1226.6	1201.8	1177.0	1152.2	1134.0
42.5°	1278.9	1263.5	1248.2	1232.8	1217.4	1196.9	1171.3	1145.6	1120.0	1094.4	1074.5
45°	1196.2	1180.5	1164.8	1149.1	1133.3	1112.0	1085.1	1058.2	1031.3	1004.4	984.5
47.5°	1113.5	1096.3	1079.0	1061.8	1044.5	1022.4	995.5	968.6	941.7	914.9	893.2
50°	1053.2	1036.8	1020.3	1003.9	987.5	965.2	936.9	908.6	880.3	852.0	830.3
52.5°	999.1	981.3	963.5	945.7	927.8	904.9	876.9	848.9	820.9	792.9	770.4
55°	908.6	891.4	874.3	857.2	840.1	816.7	787.0	757.3	727.6	697.9	677.7
57.5°	824.9	806.3	787.6	769.0	750.3	726.1	696.3	666.4	636.6	606.8	587.6
60°	767.1	747.9	728.7	709.5	690.2	666.1	637.1	608.2	579.2	550.2	531.3
62.5°	709.2	690.0	670.8	651.6	632.4	608.3	579.3	550.3	521.3	492.3	474.6
65°	620.9	601.7	582.5	563.3	544.1	520.8	493.6	466.3	439.1	411.8	394.7
67.5°	532.6	513.1	493.7	474.3	454.9	432.1	406.0	379.8	353.7	327.6	314.8
70°	474.7	455.9	437.0	418.1	399.3	377.6	353.2	328.7	304.3	279.8	267.6
72.5°	416.9	398.3	379.7	361.1	342.5	322.1	299.9	277.7	255.5	233.3	223.3
75°	328.5	311.8	295.0	278.2	261.5	243.5	224.3	205.0	185.8	166.6	163.1
77.5°	248.0	232.9	217.7	202.6	187.4	173.6	161.3	148.9	136.5	124.2	122.3
80°	196.5	182.2	167.8	153.5	139.2	128.4	121.0	113.7	106.4	99.0	98.0
82.5°	147.4	135.1	122.7	110.3	98.0	90.1	86.7	83.2	79.8	76.4	75.3
85°	83.3	75.6	67.9	60.3	52.6	48.2	47.2	46.1	45.1	44.0	43.3
87.5°	30.6	27.9	25.2	22.8	20.1	18.9	19.5	20.1	20.7	21.3	20.9
90°	2.0	4.0	6.0	9.0	11.0	13.0	16.0	19.0	22.0	25.0	24.0
92.5°	12.4	18.4	26.8	34.5	42.9	57.7	83.8	126.8	168.9	153.5	115.8
95°	33.9	36.9	47.9	64.9	90.8	129.8	214.6	363.3	527.0	591.9	480.1
97.5°	57.9	58.9	67.5	82.2	107.8	149.9	231.0	398.7	671.6	917.3	981.4
100°	73.9	74.9	81.9	95.8	119.8	158.7	228.6	376.3	638.8	945.3	1141.9
102.5°	90.6	92.4	98.6	111.8	133.4	169.1	231.8	357.1	590.9	893.4	1149.9
105°	115.8	118.8	124.8	136.8	155.7	186.7	240.6	343.4	532.0	802.5	1089.0
107.5°	142.5	145.5	151.3	163.1	180.9	209.6	256.9	342.4	494.5	722.3	982.4
110°	161.7	164.7	169.7	180.7	197.6	225.6	270.5	346.4	480.1	676.8	915.3



TEST NUMBER: P332383

CATALOG NUMBER: S123RDIP-S1165D1025U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	179.3	182.3	187.3	198.2	215.2	242.4	284.1	354.4	472.1	646.4	857.0
115°	204.6	208.6	214.6	224.6	241.6	268.5	306.4	367.3	469.1	613.9	786.6
117.5°	230.0	234.6	239.6	248.7	267.7	292.7	330.2	384.5	470.9	594.7	744.0
120°	247.5	250.5	255.5	265.5	284.5	309.4	345.4	397.3	474.1	585.9	721.7
122.5°	262.7	265.7	270.7	281.5	299.7	326.2	361.3	409.3	479.7	580.3	703.3
125°	284.5	286.5	292.5	303.4	322.4	349.4	384.3	428.2	488.1	573.0	679.8
127.5°	301.1	304.0	311.4	322.6	343.6	370.5	404.3	443.8	497.7	569.4	659.0
130°	311.4	314.4	323.4	335.4	356.3	383.3	416.2	454.2	504.1	567.0	647.8
132.5°	319.4	323.2	333.0	347.4	368.3	394.5	426.6	463.8	508.9	566.2	637.4
135°	333.4	337.4	348.4	363.3	384.3	411.2	442.2	476.1	516.1	565.0	623.9
137.5°	346.6	350.8	361.5	377.5	398.3	423.2	453.0	485.3	520.8	562.8	612.1
140°	355.4	360.3	370.3	386.3	406.3	431.2	460.2	490.1	524.0	562.0	604.9
142.5°	364.9	369.1	379.9	394.3	414.2	437.6	465.8	494.9	526.4	560.4	598.5
145°	380.3	383.3	392.3	407.3	424.2	447.2	473.1	500.1	528.0	558.0	589.9
147.5°	395.9	397.7	406.5	419.4	435.8	455.4	479.1	503.3	528.0	554.2	581.5
150°	406.3	407.3	415.2	428.2	442.2	460.2	483.1	504.1	528.0	551.0	575.9
152.5°	416.6	416.8	424.8	436.2	448.6	465.8	485.5	505.7	525.6	547.0	569.6
155°	432.2	432.2	438.2	448.2	459.2	473.1	490.1	506.1	523.0	540.0	560.0
157.5°	444.6	445.4	450.2	459.0	468.3	479.1	492.7	507.1	519.7	533.8	549.2
160°	454.2	454.2	458.2	466.1	473.1	483.1	495.1	507.1	518.1	529.0	542.0
162.5°	461.4	461.4	464.6	470.9	477.1	485.5	495.9	506.3	514.9	524.2	534.8
165°	472.1	471.1	473.1	478.1	482.1	489.1	497.1	504.1	510.1	517.1	525.0
167.5°	480.3	479.1	480.1	483.9	486.7	491.1	496.9	502.5	505.3	509.9	515.7
170°	485.1	483.1	484.1	487.1	489.1	491.1	496.1	500.1	502.1	505.1	510.1
172.5°	488.3	487.1	487.3	489.5	490.7	491.9	496.1	499.3	499.7	501.1	504.5
175°	492.1	491.1	490.1	492.1	492.1	493.1	495.1	497.1	496.1	496.1	498.1
177.5°	493.9	493.1	492.3	493.1	493.1	493.1	493.9	495.5	493.9	493.1	493.9
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P332383

CATALOG NUMBER: S123RDIP-S1165D1025U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2
2.5°	1930.5	1933.6	1936.6	1937.9	1937.3	1936.8	1936.2	1935.6
5°	1917.7	1920.9	1924.0	1925.2	1924.5	1923.8	1923.1	1922.4
7.5°	1890.7	1892.5	1894.2	1894.5	1893.3	1892.1	1890.9	1889.7
10°	1866.6	1866.9	1867.3	1866.6	1864.8	1863.1	1861.3	1859.6
12.5°	1836.5	1836.3	1836.1	1835.0	1833.0	1830.9	1828.9	1826.9
15°	1783.8	1782.0	1780.3	1778.2	1775.7	1773.3	1770.8	1768.4
17.5°	1720.8	1717.0	1713.3	1709.7	1706.0	1702.4	1698.8	1695.1
20°	1677.6	1673.0	1668.5	1664.1	1659.9	1655.7	1651.6	1647.4
22.5°	1631.3	1625.7	1620.0	1615.2	1611.3	1607.4	1603.5	1599.6
25°	1555.7	1548.3	1541.0	1535.4	1531.6	1527.7	1523.9	1520.0
27.5°	1473.2	1463.0	1452.8	1444.8	1438.9	1433.1	1427.2	1421.3
30°	1414.5	1402.7	1390.8	1382.1	1376.5	1370.9	1365.3	1359.7
32.5°	1357.0	1344.0	1331.0	1321.6	1315.7	1309.8	1304.0	1298.1
35°	1271.5	1256.5	1241.5	1230.8	1224.5	1218.2	1211.9	1205.7
37.5°	1179.7	1162.7	1145.6	1133.2	1125.5	1117.7	1110.0	1102.2
40°	1115.9	1097.7	1079.6	1066.5	1058.4	1050.4	1042.4	1034.3
42.5°	1054.7	1034.8	1015.0	1001.5	994.3	987.1	979.9	972.7
45°	964.6	944.7	924.8	910.7	902.3	893.9	885.5	877.1
47.5°	871.5	849.9	828.2	813.7	806.2	798.7	791.2	783.8
50°	808.7	787.0	765.3	750.5	742.5	734.4	726.4	718.4
52.5°	747.9	725.4	702.9	688.0	680.8	673.7	666.5	659.3
55°	657.4	637.1	616.9	603.3	596.3	589.3	582.3	575.3
57.5°	568.5	549.3	530.2	517.6	511.7	505.8	499.8	493.9
60°	512.4	493.6	474.7	462.3	456.4	450.4	444.5	438.6
62.5°	456.8	439.1	421.3	409.4	403.1	396.9	390.7	384.5
65°	377.6	360.5	343.4	332.9	329.1	325.2	321.4	317.5
67.5°	302.0	289.2	276.4	268.0	263.9	259.7	255.6	251.5
70°	255.3	243.1	230.9	222.9	219.0	215.2	211.3	207.5
72.5°	213.3	203.3	193.3	187.5	185.9	184.3	182.7	181.1
75°	159.6	156.1	152.6	150.6	149.9	149.2	148.5	147.8
77.5°	120.4	118.5	116.6	115.3	114.6	113.9	113.2	112.5
80°	96.9	95.9	94.8	94.0	93.3	92.6	91.9	91.2
82.5°	74.3	73.3	72.2	71.6	71.5	71.3	71.2	71.1
85°	42.6	41.9	41.2	40.9	40.9	40.9	40.9	40.9
87.5°	20.8	20.7	20.6	20.7	20.3	20.2	20.1	19.6
90°	25.0	26.0	27.0	28.9	27.9	28.9	29.9	28.9
92.5°	84.0	66.7	58.9	53.7	51.9	48.9	49.9	48.1
95°	359.3	243.6	190.7	154.7	135.8	126.8	119.8	115.8
97.5°	895.8	717.5	588.7	469.3	395.7	350.8	323.8	315.2
100°	1176.9	1096.0	979.2	837.5	736.7	663.8	624.9	625.9
102.5°	1270.3	1267.7	1199.6	1109.8	1031.3	973.6	941.1	918.1
105°	1297.6	1397.5	1416.4	1390.5	1344.5	1306.6	1274.7	1269.7
107.5°	1219.0	1381.1	1468.5	1504.1	1504.9	1492.1	1481.3	1472.1
110°	1143.9	1327.6	1453.3	1523.2	1551.2	1559.2	1557.2	1555.2



TEST NUMBER: P332383

CATALOG NUMBER: S123RDIP-S1165D1025U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1069.6	1257.3	1398.2	1488.1	1539.2	1563.9	1571.5	1571.9
115°	971.2	1144.9	1291.6	1400.4	1475.3	1519.2	1539.2	1544.2
117.5°	900.0	1049.9	1181.6	1292.0	1370.1	1420.4	1449.2	1455.9
120°	862.4	997.2	1117.0	1217.8	1296.6	1352.5	1376.5	1382.5
122.5°	832.9	954.9	1065.9	1159.5	1229.6	1279.9	1306.2	1313.8
125°	793.6	902.4	998.2	1078.0	1141.9	1185.8	1210.8	1217.8
127.5°	759.2	856.2	942.7	1015.3	1072.2	1109.8	1132.3	1138.7
130°	737.7	827.5	908.3	976.2	1029.1	1065.1	1086.0	1094.0
132.5°	717.7	800.3	875.6	940.3	990.0	1025.9	1044.5	1050.1
135°	690.7	761.6	826.5	883.4	932.3	962.2	980.2	987.2
137.5°	666.2	724.3	780.2	829.5	870.6	901.0	916.1	920.7
140°	651.8	702.7	750.6	793.6	831.5	859.4	875.4	874.4
142.5°	638.2	682.0	723.5	760.8	793.2	817.9	832.3	831.3
145°	621.9	654.8	686.7	715.7	740.6	761.6	769.6	771.6
147.5°	608.5	634.6	660.4	681.0	699.9	714.1	721.7	722.5
150°	598.9	621.9	642.8	661.8	676.8	687.7	693.7	693.7
152.5°	590.1	609.9	628.5	644.2	656.0	666.2	669.8	669.8
155°	576.9	592.9	607.9	619.9	628.9	636.8	638.8	639.8
157.5°	563.0	576.3	587.9	597.3	605.1	611.1	612.7	612.5
160°	555.0	566.0	575.9	582.9	589.9	595.9	595.9	594.9
162.5°	545.4	554.8	564.0	570.2	574.8	579.9	579.9	578.9
165°	533.0	539.0	546.0	551.0	555.0	559.0	558.0	558.0
167.5°	522.2	526.8	530.8	534.4	536.2	539.0	538.0	538.0
170°	515.1	518.1	522.0	524.0	525.0	527.0	526.0	526.0
172.5°	508.7	510.9	514.1	515.3	515.5	517.5	515.7	514.9
175°	500.1	501.1	503.1	503.1	503.1	504.1	503.1	502.1
177.5°	494.7	495.5	496.3	496.3	495.5	496.3	494.7	494.7
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1

(END OF REPORT)