

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332335-830

Luminaire Tested: **S123RDIP-S1000D365U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332335-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1000D365U830-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4812.5 lumens  
Efficiency: N/A  
Efficacy: 110.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332335-830

CATALOG NUMBER: S123RDIP-S1000D365U830-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332335-830

CATALOG NUMBER: S123RDIP-S1000D365U830-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78
1	104	99	96	92	98	95	91	88	86	83	81	78	76	74	70	69	67
2	95	87	81	76	90	83	78	73	76	71	68	69	65	62	62	60	57
3	87	77	70	64	82	74	67	62	67	62	58	61	57	53	56	52	49
4	80	69	61	55	76	66	59	53	60	54	50	55	50	46	50	46	43
5	74	62	53	47	70	59	52	46	54	48	43	50	44	40	45	41	38
6	68	56	47	41	64	53	46	40	49	43	38	45	40	36	41	37	33
7	63	51	42	37	60	49	41	36	45	38	34	41	36	32	38	33	30
8	59	46	38	33	56	44	37	32	41	35	30	38	32	29	35	30	27
9	55	42	35	30	52	41	34	29	38	32	27	35	30	26	32	28	24
10	51	39	32	27	49	38	31	26	35	29	25	32	27	24	30	26	22

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17026	17026	17026
5°	17091	16855	16953
10°	16994	16644	16587
15°	16811	16254	16082
20°	16561	15767	15400
25°	16302	15221	14733
30°	15960	14589	13793
35°	15609	13958	12929
40°	15286	13212	11861
45°	14862	12478	10898
50°	14393	11643	9818
55°	13915	10689	8811
60°	13476	9666	7705
65°	12905	8560	6599
70°	12192	7188	5331
75°	11154	5656	5016
80°	9937	5009	4612
85°	8398	4434	4125



TEST NUMBER: P332335-830

CATALOG NUMBER: S123RDIP-S1000D365U830-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.5	3.1
10°-20°	413.3	8.6
20°-30°	595.1	12.4
30°-40°	670.3	13.9
40°-50°	641.3	13.3
50°-60°	525.1	10.9
60°-70°	354.3	7.4
70°-80°	178.2	3.7
80°-90°	48.4	1.0
90°-100°	91.6	1.9
100°-110°	259.3	5.4
110°-120°	255.1	5.3
120°-130°	203.5	4.2
130°-140°	160.4	3.3
140°-150°	119.7	2.5
150°-160°	83.4	1.7
160°-170°	49.0	1.0
170°-180°	16.0	0.3
0°-30°	1156.9	24.0
0°-40°	1827.2	38.0
0°-60°	2993.6	62.2
0°-90°	3574.6	74.3
90°-120°	605.9	12.6
90°-150°	1089.5	22.6
90°-180°	1238.0	25.7
0°-180°	4812.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1582	1582	1582	1582	1582	
5°	1582	1575	1560	1571	1569	150
15°	1509	1493	1459	1452	1443	425
25°	1373	1339	1282	1255	1240	631
35°	1188	1140	1062	1009	984	743
45°	976	916	820	749	716	753
55°	742	676	570	498	470	665
65°	507	435	336	276	259	501
75°	268	206	136	124	121	286
85°	68	41	36	34	33	76
90°	1	4	8	9	10	4
95°	11	37	198	58	39	12
105°	39	57	268	468	424	41
115°	68	85	205	449	515	68
125°	95	112	191	346	406	84
135°	111	133	188	285	329	86
145°	127	145	186	234	258	80
155°	144	156	180	205	214	66
165°	158	162	173	183	186	44
175°	164	164	166	168	168	16
180°	165	165	165	165	165	



TEST NUMBER: P332335-830

CATALOG NUMBER: S123RDIP-S1000D365U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8
2.5°	1586.9	1585.9	1585.1	1584.1	1583.2	1581.4	1578.7	1575.9	1573.2	1570.5	1572.9
5°	1581.8	1580.3	1578.9	1577.4	1576.0	1573.6	1570.2	1566.8	1563.4	1559.9	1562.5
7.5°	1567.1	1565.6	1564.1	1562.5	1560.9	1557.9	1553.5	1549.1	1544.6	1540.2	1541.6
10°	1554.8	1552.8	1550.8	1548.8	1546.8	1543.2	1538.1	1533.0	1527.9	1522.8	1523.1
12.5°	1537.4	1535.1	1533.0	1530.7	1528.4	1524.2	1518.0	1511.6	1505.4	1499.1	1498.9
15°	1508.6	1505.5	1502.3	1499.2	1496.1	1490.5	1482.5	1474.5	1466.6	1458.6	1457.2
17.5°	1472.4	1468.8	1465.2	1461.5	1457.8	1451.0	1440.8	1430.7	1420.5	1410.3	1407.3
20°	1445.8	1441.2	1436.6	1432.1	1427.5	1419.8	1409.0	1398.2	1387.3	1376.5	1372.8
22.5°	1416.0	1410.8	1405.5	1400.2	1395.1	1386.7	1375.1	1363.6	1352.1	1340.6	1336.0
25°	1372.6	1365.6	1358.4	1351.2	1344.2	1334.0	1320.9	1307.8	1294.7	1281.6	1275.5
27.5°	1320.0	1312.2	1304.3	1296.5	1288.5	1277.3	1262.7	1248.1	1233.5	1219.0	1210.6
30°	1284.1	1275.5	1267.1	1258.5	1249.9	1237.7	1221.7	1205.7	1189.8	1173.8	1164.1
32.5°	1248.2	1238.5	1228.8	1219.1	1209.5	1196.2	1179.3	1162.4	1145.5	1128.6	1118.0
35°	1187.9	1177.6	1167.3	1157.2	1146.9	1132.8	1115.2	1097.5	1079.9	1062.2	1049.9
37.5°	1126.8	1115.4	1104.0	1092.6	1081.2	1066.1	1047.3	1028.3	1009.5	990.6	976.7
40°	1087.9	1075.3	1062.7	1050.2	1037.6	1021.2	1001.1	980.8	960.5	940.3	925.5
42.5°	1043.7	1031.1	1018.6	1006.1	993.5	976.9	955.9	935.0	914.1	893.2	876.9
45°	976.3	963.4	950.6	937.7	924.9	907.6	885.6	863.7	841.7	819.7	803.5
47.5°	908.8	894.7	880.6	866.5	852.4	834.4	812.5	790.5	768.5	746.6	729.0
50°	859.5	846.1	832.7	819.4	805.9	787.7	764.6	741.5	718.4	695.3	677.6
52.5°	815.4	800.9	786.3	771.8	757.2	738.5	715.7	692.8	670.0	647.1	628.7
55°	741.5	727.5	713.5	699.6	685.6	666.5	642.2	618.0	593.8	569.6	553.1
57.5°	673.3	658.0	642.8	627.5	612.4	592.6	568.2	543.8	519.5	495.2	479.6
60°	626.0	610.4	594.7	579.0	563.3	543.7	520.0	496.3	472.7	449.0	433.6
62.5°	578.8	563.2	547.4	531.8	516.1	496.4	472.8	449.1	425.5	401.8	387.3
65°	506.7	491.1	475.3	459.7	444.0	425.1	402.8	380.6	358.4	336.1	322.2
67.5°	434.6	418.8	402.9	387.1	371.3	352.6	331.3	310.0	288.7	267.3	256.9
70°	387.4	372.0	356.7	341.2	325.8	308.2	288.2	268.2	248.3	228.4	218.4
72.5°	340.2	325.1	309.9	294.7	279.6	262.9	244.8	226.7	208.5	190.4	182.2
75°	268.2	254.4	240.7	227.1	213.4	198.7	183.0	167.3	151.7	136.0	133.1
77.5°	202.5	190.0	177.7	165.3	153.0	141.7	131.6	121.5	111.4	101.3	99.8
80°	160.3	148.6	137.0	125.3	113.6	104.8	98.8	92.7	86.8	80.8	79.9
82.5°	120.4	110.3	100.2	90.0	79.9	73.5	70.7	68.0	65.1	62.3	61.5
85°	68.0	61.7	55.4	49.2	42.9	39.3	38.5	37.6	36.8	35.9	35.3
87.5°	24.8	22.4	20.0	17.7	15.4	14.2	14.4	14.6	14.8	15.0	14.7
90°	0.7	1.3	2.0	3.0	3.7	4.3	5.4	6.3	7.4	8.3	8.0
92.5°	4.1	6.1	9.0	11.5	14.3	19.2	28.0	42.3	56.4	51.2	38.6
95°	11.3	12.3	16.0	21.7	30.3	43.3	71.6	121.2	175.9	197.6	160.2
97.5°	19.3	19.6	22.5	27.4	36.0	50.0	77.1	133.0	224.1	306.1	327.4
100°	24.7	25.0	27.3	32.0	40.0	53.0	76.3	125.5	213.2	315.5	381.1
102.5°	30.3	30.8	32.9	37.3	44.5	56.5	77.4	119.1	197.2	298.1	383.7
105°	38.6	39.7	41.7	45.6	51.9	62.3	80.3	114.6	177.6	267.8	363.4
107.5°	47.6	48.5	50.5	54.4	60.3	69.9	85.8	114.2	165.0	241.0	327.8
110°	53.9	55.0	56.6	60.3	66.0	75.3	90.3	115.6	160.2	225.8	305.5



TEST NUMBER: P332335-830

CATALOG NUMBER: S123RDIP-S1000D365U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	59.9	60.8	62.5	66.2	71.8	80.9	94.8	118.3	157.5	215.7	286.0
115°	68.2	69.7	71.6	74.9	80.6	89.6	102.3	122.5	156.6	204.8	262.5
117.5°	76.7	78.2	79.9	83.0	89.4	97.6	110.2	128.3	157.1	198.4	248.3
120°	82.6	83.6	85.3	88.6	94.9	103.2	115.3	132.5	158.3	195.5	240.8
122.5°	87.7	88.7	90.3	94.0	100.0	108.9	120.6	136.6	160.0	193.7	234.7
125°	94.9	95.6	97.6	101.2	107.5	116.6	128.3	142.9	162.9	191.1	226.9
127.5°	100.5	101.4	104.0	107.6	114.6	123.7	134.9	148.1	166.1	190.0	219.9
130°	104.0	104.9	107.9	111.9	118.9	127.9	138.9	151.6	168.2	189.2	216.1
132.5°	106.6	107.8	111.1	115.9	122.9	131.7	142.3	154.8	169.8	188.9	212.7
135°	111.2	112.5	116.2	121.2	128.3	137.2	147.5	158.9	172.2	188.5	208.2
137.5°	115.6	117.1	120.6	125.9	132.9	141.2	151.2	161.9	173.8	187.8	204.2
140°	118.6	120.3	123.6	128.9	135.5	143.9	153.5	163.5	174.8	187.6	201.8
142.5°	121.8	123.2	126.8	131.6	138.3	146.0	155.4	165.1	175.7	187.0	199.7
145°	126.9	127.9	130.9	135.9	141.6	149.2	157.9	166.8	176.2	186.2	196.8
147.5°	132.1	132.7	135.6	140.0	145.4	151.9	159.9	168.0	176.2	184.9	194.1
150°	135.5	135.9	138.6	142.9	147.5	153.5	161.2	168.2	176.2	183.9	192.2
152.5°	139.0	139.1	141.8	145.5	149.7	155.4	162.0	168.7	175.4	182.6	190.0
155°	144.2	144.2	146.2	149.6	153.3	157.9	163.5	168.9	174.6	180.2	186.8
157.5°	148.4	148.6	150.2	153.2	156.3	159.9	164.4	169.2	173.4	178.1	183.2
160°	151.6	151.6	152.9	155.5	157.9	161.2	165.2	169.2	172.9	176.5	180.9
162.5°	153.9	153.9	155.0	157.1	159.2	162.0	165.5	168.9	171.8	174.9	178.4
165°	157.5	157.2	157.9	159.6	160.9	163.2	165.9	168.2	170.2	172.6	175.2
167.5°	160.2	159.9	160.2	161.5	162.4	163.9	165.8	167.7	168.6	170.1	172.1
170°	161.8	161.2	161.6	162.5	163.2	163.9	165.5	166.8	167.6	168.5	170.2
172.5°	163.0	162.5	162.6	163.3	163.7	164.1	165.5	166.6	166.7	167.2	168.3
175°	164.2	163.9	163.5	164.2	164.2	164.6	165.2	165.9	165.5	165.5	166.2
177.5°	164.9	164.6	164.3	164.6	164.6	164.6	164.9	165.3	164.9	164.6	164.9
180°	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6



TEST NUMBER: P332335-830

CATALOG NUMBER: S123RDIP-S1000D365U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8
2.5°	1575.5	1578.0	1580.5	1581.5	1581.0	1580.6	1580.2	1579.7
5°	1565.1	1567.6	1570.2	1571.2	1570.7	1570.1	1569.5	1569.0
7.5°	1543.0	1544.5	1545.9	1546.1	1545.1	1544.2	1543.2	1542.2
10°	1523.3	1523.6	1523.9	1523.3	1521.8	1520.4	1519.0	1517.6
12.5°	1498.7	1498.6	1498.5	1497.5	1495.9	1494.2	1492.6	1490.9
15°	1455.8	1454.3	1452.9	1451.1	1449.2	1447.2	1445.2	1443.2
17.5°	1404.3	1401.3	1398.3	1395.2	1392.3	1389.3	1386.4	1383.4
20°	1369.0	1365.4	1361.7	1358.1	1354.7	1351.2	1347.8	1344.4
22.5°	1331.3	1326.7	1322.1	1318.1	1315.0	1311.8	1308.6	1305.4
25°	1269.6	1263.6	1257.6	1253.0	1249.9	1246.8	1243.7	1240.5
27.5°	1202.3	1194.0	1185.6	1179.1	1174.3	1169.5	1164.7	1160.0
30°	1154.4	1144.7	1135.0	1127.9	1123.3	1118.8	1114.2	1109.7
32.5°	1107.4	1096.8	1086.2	1078.6	1073.7	1068.9	1064.1	1059.3
35°	1037.6	1025.4	1013.1	1004.5	999.4	994.2	989.1	983.9
37.5°	962.8	948.9	935.0	924.8	918.5	912.2	905.9	899.6
40°	910.7	895.9	881.0	870.3	863.7	857.2	850.6	844.1
42.5°	860.7	844.5	828.3	817.3	811.4	805.6	799.7	793.8
45°	787.2	771.0	754.7	743.2	736.3	729.5	722.6	715.9
47.5°	711.2	693.6	675.9	664.0	657.9	651.9	645.7	639.6
50°	660.0	642.2	624.6	612.5	606.0	599.4	592.9	586.3
52.5°	610.4	592.0	573.6	561.5	555.6	549.8	543.9	538.0
55°	536.5	520.0	503.4	492.3	486.6	480.9	475.2	469.5
57.5°	463.9	448.3	432.7	422.4	417.6	412.7	407.9	403.0
60°	418.2	402.8	387.4	377.3	372.5	367.6	362.8	357.9
62.5°	372.8	358.4	343.8	334.0	329.0	324.0	318.9	313.8
65°	308.2	294.2	280.2	271.6	268.5	265.4	262.3	259.1
67.5°	246.5	236.0	225.6	218.7	215.4	212.0	208.6	205.3
70°	208.4	198.4	188.4	181.9	178.7	175.6	172.5	169.4
72.5°	174.1	165.9	157.8	153.1	151.7	150.4	149.1	147.8
75°	130.3	127.4	124.6	122.9	122.3	121.7	121.1	120.6
77.5°	98.3	96.7	95.2	94.2	93.6	93.0	92.5	91.9
80°	79.1	78.2	77.4	76.7	76.2	75.6	74.9	74.4
82.5°	60.6	59.8	58.9	58.4	58.3	58.2	58.1	58.0
85°	34.8	34.2	33.6	33.4	33.4	33.4	33.4	33.4
87.5°	14.5	14.4	14.2	14.1	13.9	13.7	13.5	13.2
90°	8.3	8.7	9.0	9.6	9.3	9.6	10.0	9.6
92.5°	28.1	22.2	19.6	17.9	17.3	16.3	16.7	16.0
95°	119.9	81.2	63.6	51.7	45.3	42.3	40.0	38.6
97.5°	298.9	239.4	196.4	156.7	132.1	117.1	108.0	105.2
100°	392.7	365.7	326.8	279.5	245.8	221.5	208.5	208.9
102.5°	423.9	423.0	400.3	370.3	344.1	324.9	314.1	306.3
105°	433.0	466.3	472.6	464.0	448.7	436.0	425.4	423.7
107.5°	406.7	460.8	490.0	501.9	502.2	497.9	494.3	491.3
110°	381.7	443.0	484.9	508.3	517.6	520.3	519.6	519.0





TEST NUMBER: P332335-830

CATALOG NUMBER: S123RDIP-S1000D365U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	356.9	419.5	466.6	496.5	513.6	521.9	524.4	524.5
115°	324.0	382.0	431.0	467.3	492.3	506.9	513.6	515.3
117.5°	300.3	350.3	394.3	431.1	457.2	474.0	483.5	485.8
120°	287.8	332.7	372.7	406.3	432.6	451.3	459.3	461.3
122.5°	278.0	318.6	355.6	386.9	410.3	427.1	435.8	438.4
125°	264.8	301.1	333.1	359.8	381.1	395.7	404.1	406.3
127.5°	253.4	285.7	314.5	338.8	357.8	370.3	377.9	379.9
130°	246.1	276.2	303.1	325.7	343.4	355.4	362.4	365.0
132.5°	239.5	267.0	292.2	313.8	330.4	342.3	348.6	350.4
135°	230.5	254.1	275.8	294.7	311.1	321.1	327.1	329.4
137.5°	222.3	241.7	260.3	276.8	290.5	300.7	305.7	307.3
140°	217.5	234.5	250.4	264.8	277.5	286.8	292.1	291.8
142.5°	213.0	227.5	241.4	253.8	264.7	273.0	277.7	277.4
145°	207.5	218.5	229.1	238.8	247.1	254.1	256.8	257.5
147.5°	203.0	211.8	220.4	227.2	233.6	238.3	240.8	241.1
150°	199.8	207.5	214.5	220.8	225.8	229.5	231.5	231.5
152.5°	196.9	203.5	209.7	215.0	218.9	222.3	223.5	223.5
155°	192.6	197.8	202.8	206.8	209.8	212.5	213.2	213.5
157.5°	187.8	192.3	196.1	199.3	201.9	203.9	204.4	204.3
160°	185.2	188.9	192.2	194.5	196.8	198.9	198.9	198.5
162.5°	182.0	185.1	188.2	190.3	191.8	193.5	193.5	193.2
165°	177.9	179.8	182.2	183.9	185.2	186.5	186.2	186.2
167.5°	174.3	175.8	177.1	178.3	178.9	179.8	179.6	179.6
170°	171.8	172.9	174.2	174.8	175.2	175.9	175.5	175.5
172.5°	169.8	170.5	171.5	171.9	172.0	172.7	172.1	171.8
175°	166.8	167.2	167.9	167.9	167.9	168.2	167.9	167.6
177.5°	165.0	165.3	165.6	165.6	165.3	165.6	165.0	165.0
180°	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6

(END OF REPORT)