

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332385

Luminaire Tested: **S123RDIP-S1165D1195U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332385
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D1195U835-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8673.8 lumens
Efficiency: N/A
Efficacy: 121.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332385

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332385

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	47	45	44	39
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	42	40	38	34
4	76	66	58	52	71	62	55	50	53	48	44	45	42	38	38	35	33	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26
6	65	53	45	40	60	50	43	38	43	38	34	37	33	30	32	29	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	27	29	26	23	21
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	24	21	19
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	22	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19763	19763	19763	19763
5°	23558	19847	17477	19847
10°	29415	19733	15789	19733
15°	34526	19531	14399	19531
20°	38533	19230	13216	19230
25°	37917	18912	12490	18912
30°	27256	18620	11742	18620
35°	18198	18239	11257	18239
40°	13408	17781	10756	17781
45°	11246	16978	10266	16978
50°	9923	15925	9582	15925
55°	8702	14720	8644	14720
60°	7750	13569	7918	13569
65°	6805	12332	7366	12332
70°	5344	11229	6729	11229
75°	4708	9807	6147	9807
80°	4091	8331	6044	8331
85°	3298	6694	6410	6694



TEST NUMBER: P332385

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.6	2.1
10°-20°	564.1	6.5
20°-30°	886.2	10.2
30°-40°	924.6	10.7
40°-50°	791.2	9.1
50°-60°	603.1	7.0
60°-70°	386.5	4.5
70°-80°	186.0	2.1
80°-90°	53.6	0.6
90°-100°	96.4	1.1
100°-110°	288.4	3.3
110°-120°	490.5	5.7
120°-130°	645.2	7.4
130°-140°	725.2	8.4
140°-150°	712.8	8.2
150°-160°	600.1	6.9
160°-170°	399.5	4.6
170°-180°	139.9	1.6
0°-30°	1630.8	18.8
0°-40°	2555.4	29.5
0°-60°	3949.7	45.5
0°-90°	4575.8	52.8
90°-120°	875.3	10.1
90°-150°	2958.5	34.1
90°-180°	4098.0	47.2
0°-180°	8673.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1836	1836	1836	1836	1836	
5°	2180	1837	1618	1837	2180	225
15°	3098	1753	1292	1753	3098	879
25°	3193	1592	1052	1592	3193	1372
35°	1385	1388	857	1388	1385	908
45°	739	1115	674	1115	739	581
55°	464	784	461	784	464	419
65°	267	484	289	484	267	263
75°	113	236	148	236	113	121
85°	27	54	52	54	27	32
90°	35	1	35	1	35	18
95°	91	69	91	69	91	93
105°	276	261	276	261	276	293
115°	495	494	495	494	495	490
125°	715	723	715	723	715	639
135°	936	938	936	938	936	720
145°	1138	1138	1138	1138	1138	710
155°	1300	1302	1300	1302	1300	599
165°	1414	1419	1414	1419	1414	399
175°	1470	1476	1470	1476	1470	140
180°	1479	1479	1479	1479	1479	



TEST NUMBER: P332385

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1955.5	1958.0	1949.8	1948.6	1939.1	1936.6	1936.6	1923.4	1915.2	1904.6	1898.3
5°	2180.3	2192.9	2186.6	2172.4	2148.8	2143.3	2128.4	2104.8	2078.1	2045.1	2029.4
7.5°	2461.0	2478.2	2471.6	2449.7	2425.0	2405.1	2362.9	2323.8	2268.9	2220.8	2179.6
10°	2691.2	2673.1	2658.9	2637.7	2614.9	2578.0	2534.0	2473.4	2403.5	2348.5	2287.2
12.5°	2863.4	2860.5	2842.5	2820.7	2788.5	2753.4	2699.3	2625.6	2544.3	2464.8	2394.7
15°	3098.3	3103.0	3091.2	3068.4	3022.8	2960.7	2879.0	2848.4	2732.0	2645.6	2559.1
17.5°	3260.8	3259.9	3258.3	3226.7	3180.2	3136.0	3060.2	2979.6	2874.3	2752.5	2636.0
20°	3363.9	3356.1	3357.7	3322.3	3287.7	3236.6	3162.7	3045.6	2959.2	2818.5	2698.2
22.5°	3361.4	3359.9	3365.8	3353.7	3328.6	3289.4	3231.3	3132.4	3022.1	2880.1	2744.8
25°	3192.6	3186.3	3223.3	3233.5	3273.6	3280.6	3263.3	3209.1	3104.6	2958.4	2791.0
27.5°	2672.0	2668.5	2737.1	2822.9	2931.7	3016.2	3098.0	3137.4	3104.6	2999.9	2832.2
30°	2192.9	2266.7	2301.3	2425.5	2563.8	2728.9	2873.5	3011.0	3044.8	2999.3	2861.7
32.5°	1820.6	1885.1	1914.0	2020.6	2149.5	2342.8	2559.7	2754.5	2892.1	2926.9	2844.1
35°	1384.9	1385.7	1451.7	1498.8	1618.3	1817.2	2027.8	2288.7	2548.1	2744.6	2765.0
37.5°	1105.1	1109.0	1148.9	1195.9	1285.5	1390.7	1576.2	1793.1	2092.7	2394.4	2571.2
40°	954.2	961.2	991.1	1037.5	1101.9	1181.3	1325.9	1530.3	1780.2	2115.8	2390.1
42.5°	857.3	868.8	884.2	919.9	959.8	1034.2	1151.1	1309.0	1536.3	1853.6	2170.1
45°	738.8	745.1	756.9	773.4	809.5	861.4	940.0	1046.1	1234.8	1490.2	1806.9
47.5°	651.7	648.4	660.8	674.2	698.3	733.6	786.3	872.9	1007.5	1212.4	1481.1
50°	592.6	591.8	600.5	610.7	633.5	659.4	702.7	767.9	874.8	1044.6	1290.6
52.5°	537.3	540.3	546.4	559.1	575.6	596.6	635.4	682.4	774.2	920.7	1125.8
55°	463.7	466.1	474.7	481.8	493.6	514.8	539.2	578.5	641.4	743.5	912.5
57.5°	401.5	400.4	408.7	410.4	423.8	441.1	459.9	490.4	536.0	612.0	725.8
60°	360.0	357.6	364.7	370.2	377.3	391.4	407.1	437.0	473.2	529.0	626.4
62.5°	322.2	321.1	326.3	331.8	337.7	350.5	363.7	386.7	415.3	462.3	539.6
65°	267.2	269.6	271.9	274.3	277.4	285.3	297.9	313.6	333.3	366.3	422.1
67.5°	210.0	212.4	213.2	218.0	224.8	229.7	237.4	251.4	265.0	292.9	324.6
70°	169.8	169.0	169.8	172.1	180.8	189.4	199.6	209.9	218.5	238.1	264.9
72.5°	145.9	144.5	146.5	147.0	151.2	153.6	160.0	169.6	180.8	194.1	213.3
75°	113.2	113.2	113.2	113.2	116.3	117.9	120.3	122.6	126.5	132.8	147.0
77.5°	83.6	83.8	84.9	85.7	86.3	87.2	88.7	91.0	92.4	95.7	101.9
80°	66.0	66.8	66.0	66.8	66.8	68.4	69.2	71.5	72.3	76.2	78.6
82.5°	49.7	49.2	49.7	50.5	50.5	52.0	52.2	53.9	54.1	56.1	58.5
85°	26.7	25.2	26.7	25.9	27.5	25.9	26.7	28.3	28.3	29.1	32.2
87.5°	13.3	14.4	13.1	13.6	13.5	13.9	13.7	13.5	14.6	13.8	13.7
90°	34.9	34.3	33.8	33.3	32.8	32.0	31.0	30.0	28.9	27.9	24.5
92.5°	46.9	47.2	47.6	47.9	48.2	47.9	47.1	46.3	45.4	44.6	42.7
95°	90.6	90.6	90.6	90.6	90.6	90.1	89.1	88.0	87.0	86.0	83.9
97.5°	139.4	139.5	139.6	139.7	139.8	139.3	138.1	136.9	135.7	134.5	133.0
100°	176.6	176.1	175.6	175.1	174.5	173.9	173.1	172.3	171.6	170.8	169.5
102.5°	214.7	214.8	214.9	215.0	215.1	214.8	214.0	213.2	212.5	211.7	210.0
105°	276.5	276.0	275.5	275.0	274.5	274.2	274.2	274.2	274.2	274.2	271.9
107.5°	340.9	341.2	341.5	341.8	342.1	341.9	341.1	340.2	339.4	338.6	337.6
110°	384.6	385.1	385.6	386.1	386.6	386.4	385.4	384.3	383.3	382.3	381.7



TEST NUMBER: P332385

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	431.1	431.2	431.3	431.4	431.5	430.9	429.7	428.4	427.2	425.9	425.8
115°	495.0	495.2	495.5	495.7	496.0	496.0	495.7	495.5	495.2	495.0	495.5
117.5°	559.8	560.5	561.2	562.0	562.7	563.1	563.1	563.2	563.2	563.3	564.0
120°	605.3	605.9	606.4	606.9	607.4	607.8	608.1	608.3	608.6	608.8	610.1
122.5°	649.0	649.7	650.5	651.2	651.9	652.6	653.3	654.0	654.6	655.3	656.0
125°	714.6	715.6	716.6	717.7	718.7	719.7	720.8	721.8	722.8	723.9	724.4
127.5°	779.9	781.0	782.2	783.4	784.6	785.9	787.4	788.8	790.3	791.7	792.3
130°	822.6	824.4	826.2	828.0	829.8	831.3	832.3	833.3	834.4	835.4	836.2
132.5°	867.2	868.6	870.0	871.4	872.8	874.1	875.4	876.6	877.8	879.1	879.6
135°	936.5	937.0	937.5	938.0	938.5	939.3	940.3	941.4	942.4	943.4	943.7
137.5°	997.6	998.6	999.6	1000.5	1001.5	1002.5	1003.6	1004.7	1005.8	1006.9	1006.2
140°	1037.6	1039.4	1041.2	1043.0	1044.8	1045.8	1046.1	1046.3	1046.6	1046.9	1046.6
142.5°	1078.5	1079.9	1081.2	1082.6	1084.0	1084.9	1085.1	1085.4	1085.6	1085.9	1085.4
145°	1137.5	1138.5	1139.5	1140.6	1141.6	1142.3	1142.5	1142.8	1143.0	1143.3	1142.5
147.5°	1190.0	1191.5	1193.1	1194.6	1196.2	1197.0	1197.0	1197.0	1197.0	1197.0	1196.2
150°	1223.5	1225.0	1226.6	1228.1	1229.7	1230.4	1230.4	1230.4	1230.4	1230.4	1229.9
152.5°	1256.0	1257.3	1258.7	1260.0	1261.4	1261.8	1261.4	1261.0	1260.6	1260.2	1259.9
155°	1300.1	1302.0	1303.8	1305.6	1307.4	1307.8	1306.7	1305.7	1304.7	1303.6	1303.4
157.5°	1340.3	1341.8	1343.2	1344.7	1346.1	1346.3	1345.2	1344.1	1343.1	1342.0	1341.8
160°	1366.4	1367.4	1368.4	1369.5	1370.5	1370.4	1369.1	1367.8	1366.5	1365.2	1365.2
162.5°	1385.9	1387.5	1389.2	1390.8	1392.5	1392.7	1391.4	1390.1	1388.8	1387.5	1387.3
165°	1414.0	1415.8	1417.6	1419.4	1421.2	1421.4	1419.8	1418.3	1416.7	1415.2	1415.2
167.5°	1437.9	1439.5	1441.1	1442.7	1444.3	1444.3	1442.7	1441.1	1439.5	1437.9	1437.7
170°	1450.0	1451.8	1453.6	1455.5	1457.3	1457.3	1455.5	1453.6	1451.8	1450.0	1450.0
172.5°	1459.3	1461.1	1462.9	1464.7	1466.6	1466.7	1465.1	1463.5	1461.9	1460.3	1460.3
175°	1469.8	1471.6	1473.4	1475.2	1477.0	1477.1	1475.6	1474.0	1472.5	1470.9	1470.9
177.5°	1475.4	1476.8	1478.2	1479.7	1481.1	1481.2	1480.0	1478.8	1477.5	1476.3	1476.3
180°	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1



TEST NUMBER: P332385

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1895.8	1893.9	1885.1	1875.0	1861.8	1853.0	1846.1	1842.3	1831.0	1817.2	1807.7
5°	2012.9	1989.3	1964.1	1933.5	1905.2	1876.1	1858.0	1836.8	1810.9	1781.8	1761.4
7.5°	2138.3	2092.1	2042.3	1990.9	1940.1	1894.5	1854.3	1819.8	1778.5	1736.8	1707.6
10°	2234.5	2166.9	2097.0	2025.4	1960.2	1898.9	1851.7	1805.4	1755.9	1707.9	1671.8
12.5°	2321.9	2232.9	2152.3	2064.4	1981.0	1907.7	1839.8	1785.2	1725.7	1674.6	1633.4
15°	2432.6	2341.4	2243.9	2110.3	1999.5	1906.8	1824.2	1752.7	1680.4	1617.5	1577.4
17.5°	2536.0	2398.8	2267.8	2156.4	2012.4	1896.5	1795.8	1710.3	1630.9	1564.2	1514.9
20°	2578.8	2445.9	2303.7	2161.4	2019.9	1890.3	1773.1	1678.8	1596.3	1520.8	1475.3
22.5°	2604.5	2454.1	2304.3	2151.4	2001.1	1866.4	1750.5	1646.8	1557.3	1485.6	1429.4
25°	2634.6	2455.4	2290.3	2139.4	1986.1	1840.0	1702.4	1592.4	1495.7	1419.5	1359.7
27.5°	2654.4	2443.6	2248.5	2080.8	1925.3	1779.7	1653.7	1537.0	1439.0	1358.3	1294.2
30°	2658.1	2434.1	2216.4	2034.9	1876.9	1743.3	1609.7	1498.1	1394.3	1308.6	1248.9
32.5°	2663.2	2410.9	2173.0	1980.2	1818.4	1686.1	1565.0	1458.4	1352.2	1267.8	1206.8
35°	2642.4	2398.0	2107.2	1885.5	1723.6	1595.5	1486.3	1388.0	1283.5	1201.7	1139.7
37.5°	2553.1	2346.9	2039.0	1779.0	1609.7	1491.0	1402.0	1316.3	1220.5	1132.3	1073.8
40°	2463.2	2296.6	1986.1	1714.2	1537.4	1415.5	1335.4	1265.4	1172.7	1090.1	1027.3
42.5°	2329.3	2228.1	1935.8	1646.3	1455.6	1338.2	1270.6	1205.0	1123.6	1039.8	980.7
45°	2083.6	2097.0	1832.9	1538.1	1342.4	1224.5	1160.9	1115.3	1043.0	973.8	913.3
47.5°	1775.5	1900.5	1712.0	1422.9	1223.1	1112.5	1056.8	1017.0	968.3	900.4	845.2
50°	1574.3	1752.7	1615.2	1345.6	1148.3	1038.3	983.2	951.0	908.6	855.1	802.5
52.5°	1388.8	1580.4	1498.2	1259.4	1067.2	966.6	912.8	886.3	852.6	802.3	754.7
55°	1132.6	1326.7	1307.9	1129.4	945.5	855.1	814.3	784.4	761.6	723.9	686.2
57.5°	916.1	1100.2	1109.9	984.8	838.3	749.0	713.8	691.3	676.4	648.0	613.1
60°	779.7	948.7	981.7	887.4	761.6	683.0	648.4	630.3	618.6	595.8	569.0
62.5°	666.5	810.3	847.7	779.8	688.0	614.5	587.4	570.0	562.0	542.3	518.7
65°	510.1	629.6	665.7	628.0	580.0	521.1	499.1	484.2	477.1	466.1	448.8
67.5°	383.6	470.6	510.3	483.7	466.4	429.1	415.1	407.1	400.8	393.3	378.8
70°	308.1	372.5	413.4	406.3	392.2	372.5	362.3	356.8	350.5	344.3	331.7
72.5°	247.7	292.1	330.4	334.0	322.4	318.5	309.5	307.2	303.4	295.8	288.9
75°	164.3	194.9	221.6	231.9	236.6	240.5	236.6	235.8	235.0	228.7	224.8
77.5°	107.7	124.2	141.0	158.5	165.8	171.2	172.4	175.3	173.2	169.9	168.0
80°	82.5	86.5	98.2	113.2	125.0	129.7	132.8	134.4	133.6	132.8	129.7
82.5°	59.9	63.2	68.7	79.2	89.1	97.0	98.9	98.6	100.3	100.8	98.2
85°	32.2	33.0	34.6	36.2	41.7	50.3	52.7	54.2	55.8	55.8	51.1
87.5°	14.3	13.0	13.6	13.0	14.4	14.5	17.7	20.4	21.5	19.5	20.0
90°	21.2	17.8	14.5	11.5	8.9	6.3	3.7	1.2	3.7	6.3	8.9
92.5°	40.8	38.9	37.0	35.1	33.4	31.6	29.9	28.1	29.9	31.6	33.4
95°	81.8	79.8	77.7	75.8	74.0	72.2	70.4	68.6	70.4	72.2	74.0
97.5°	131.6	130.1	128.6	127.1	125.8	124.5	123.1	121.8	123.1	124.5	125.8
100°	168.2	166.9	165.6	164.2	162.7	161.1	159.6	158.0	159.6	161.1	162.7
102.5°	208.3	206.6	204.9	203.6	202.6	201.7	200.8	199.8	200.8	201.7	202.6
105°	269.6	267.2	264.9	263.5	263.0	262.5	261.9	261.4	261.9	262.5	263.0
107.5°	336.7	335.8	334.9	334.2	333.9	333.6	333.3	333.0	333.3	333.6	333.9
110°	381.2	380.7	380.2	379.7	379.2	378.6	378.1	377.6	378.1	378.6	379.2



TEST NUMBER: P332385

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	425.7	425.6	425.5	425.3	425.0	424.7	424.4	424.1	424.4	424.7	425.0
115°	496.0	496.5	497.0	496.9	496.1	495.3	494.6	493.8	494.6	495.3	496.1
117.5°	564.6	565.3	566.0	566.0	565.5	565.0	564.5	564.0	564.5	565.0	565.5
120°	611.4	612.7	614.0	613.9	612.3	610.8	609.2	607.7	609.2	610.8	612.3
122.5°	656.6	657.3	658.0	657.8	656.6	655.5	654.3	653.2	654.3	655.5	656.6
125°	724.9	725.4	725.9	725.8	725.0	724.2	723.5	722.7	723.5	724.2	725.0
127.5°	792.8	793.4	794.0	793.4	791.8	790.1	788.5	786.8	788.5	790.1	791.8
130°	836.9	837.7	838.5	837.8	835.8	833.7	831.6	829.6	831.6	833.7	835.8
132.5°	880.2	880.8	881.4	880.6	878.5	876.5	874.4	872.3	874.4	876.5	878.5
135°	944.0	944.2	944.5	943.8	942.3	940.7	939.2	937.6	939.2	940.7	942.3
137.5°	1005.5	1004.9	1004.2	1003.2	1001.9	1000.6	999.3	998.1	999.3	1000.6	1001.9
140°	1046.3	1046.1	1045.8	1045.0	1043.8	1042.5	1041.2	1039.9	1041.2	1042.5	1043.8
142.5°	1085.0	1084.5	1084.0	1083.2	1081.9	1080.6	1079.3	1078.0	1079.3	1080.6	1081.9
145°	1141.7	1141.0	1140.2	1139.5	1139.0	1138.5	1138.0	1137.5	1138.0	1138.5	1139.0
147.5°	1195.5	1194.8	1194.1	1193.3	1192.3	1191.4	1190.5	1189.5	1190.5	1191.4	1192.3
150°	1229.4	1228.9	1228.4	1227.9	1227.3	1226.8	1226.3	1225.8	1226.3	1226.8	1227.3
152.5°	1259.6	1259.2	1258.9	1258.4	1257.7	1257.0	1256.3	1255.5	1256.3	1257.0	1257.7
155°	1303.1	1302.9	1302.6	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5
157.5°	1341.6	1341.4	1341.1	1341.2	1341.5	1341.8	1342.1	1342.4	1342.1	1341.8	1341.5
160°	1365.2	1365.2	1365.2	1365.5	1366.0	1366.5	1367.0	1367.5	1367.0	1366.5	1366.0
162.5°	1387.1	1386.9	1386.7	1387.0	1387.7	1388.4	1389.1	1389.8	1389.1	1388.4	1387.7
165°	1415.2	1415.2	1415.2	1415.6	1416.3	1417.1	1417.9	1418.7	1417.9	1417.1	1416.3
167.5°	1437.5	1437.3	1437.1	1437.5	1438.6	1439.6	1440.6	1441.7	1440.6	1439.6	1438.6
170°	1450.0	1450.0	1450.0	1450.5	1451.6	1452.6	1453.6	1454.7	1453.6	1452.6	1451.6
172.5°	1460.3	1460.3	1460.3	1460.8	1461.8	1462.8	1463.9	1464.9	1463.9	1462.8	1461.8
175°	1470.9	1470.9	1470.9	1471.5	1472.5	1473.5	1474.6	1475.6	1474.6	1473.5	1472.5
177.5°	1476.3	1476.3	1476.3	1476.7	1477.5	1478.4	1479.2	1480.0	1479.2	1478.4	1477.5
180°	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1



TEST NUMBER: P332385

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1804.6	1796.4	1790.8	1778.2	1770.0	1761.2	1752.4	1758.1	1757.4	1756.8	1756.8
5°	1744.1	1726.0	1709.5	1688.3	1674.9	1658.4	1645.8	1644.2	1647.4	1636.4	1630.1
7.5°	1684.0	1659.3	1635.9	1612.5	1587.7	1567.9	1555.4	1549.6	1541.6	1534.8	1527.8
10°	1641.9	1612.8	1590.0	1560.9	1534.2	1510.6	1495.7	1485.5	1480.0	1474.5	1464.3
12.5°	1598.5	1570.1	1541.0	1508.1	1482.7	1455.3	1444.1	1432.7	1422.1	1416.0	1402.0
15°	1535.0	1498.1	1467.4	1432.8	1404.5	1377.8	1362.1	1339.3	1336.1	1328.3	1314.1
17.5°	1471.3	1431.2	1389.0	1363.3	1331.4	1303.6	1279.7	1272.0	1249.5	1241.0	1228.8
20°	1421.0	1384.1	1351.9	1318.1	1271.7	1245.8	1226.9	1216.7	1198.6	1187.6	1179.7
22.5°	1377.6	1340.1	1302.8	1263.4	1225.2	1196.1	1182.3	1166.4	1156.5	1141.1	1132.6
25°	1315.7	1274.8	1230.0	1187.6	1160.1	1138.1	1116.1	1101.9	1087.8	1080.7	1065.0
27.5°	1243.7	1201.0	1159.1	1126.9	1093.1	1071.4	1051.5	1038.9	1021.9	1010.0	1001.3
30°	1204.1	1153.8	1117.6	1088.6	1045.3	1024.9	1010.0	994.3	981.7	969.1	960.5
32.5°	1158.2	1112.3	1078.0	1042.0	1008.9	986.5	967.2	953.4	942.7	930.7	922.1
35°	1086.2	1047.7	1012.3	976.2	951.8	929.0	906.2	894.4	884.2	873.2	865.4
37.5°	1021.1	985.1	951.5	917.2	887.0	868.5	850.1	841.1	827.3	819.9	811.9
40°	980.9	945.5	909.4	876.4	844.9	830.8	814.3	800.9	788.3	782.8	774.2
42.5°	936.9	901.5	871.0	835.5	809.7	790.5	775.3	760.7	751.2	743.2	738.3
45°	871.6	840.2	810.3	775.0	750.6	734.1	716.8	703.4	694.8	689.3	680.6
47.5°	808.3	776.9	746.5	715.7	692.1	673.3	656.0	646.7	635.2	628.5	622.6
50°	762.4	734.1	701.9	673.6	650.0	631.1	617.0	605.2	595.0	586.3	582.4
52.5°	720.3	690.1	662.3	635.8	611.0	589.6	576.7	564.3	556.6	546.7	542.2
55°	650.8	621.7	598.1	572.2	547.8	529.7	514.0	503.0	495.2	484.2	477.9
57.5°	585.5	559.5	531.3	508.8	483.7	468.4	455.4	440.5	430.9	422.2	416.1
60°	541.5	511.7	487.3	466.1	444.1	424.4	412.6	400.8	390.6	382.0	376.5
62.5°	495.6	469.5	446.4	423.3	403.2	386.1	372.4	362.5	353.5	348.0	342.5
65°	425.2	404.8	381.2	362.3	343.5	330.9	319.9	311.2	305.0	301.0	296.3
67.5°	360.4	340.6	320.0	301.5	288.9	279.3	272.1	264.7	261.6	256.5	253.4
70°	318.3	297.9	279.8	265.7	253.1	246.0	241.3	235.8	232.6	226.4	223.2
72.5°	272.4	257.6	244.6	233.0	222.9	216.5	210.5	203.7	198.7	191.8	188.6
75°	214.6	201.2	191.0	183.1	176.8	168.2	159.6	152.5	150.1	147.8	147.0
77.5°	158.9	150.4	143.0	136.4	128.6	122.3	120.4	118.8	118.4	117.1	117.1
80°	125.0	117.1	111.6	103.7	99.0	99.0	99.0	97.5	98.2	98.2	98.2
82.5°	92.9	85.7	82.7	79.9	78.9	79.5	79.5	79.9	79.4	80.6	80.0
85°	47.9	48.7	50.3	49.5	50.3	50.3	51.9	51.1	51.9	50.3	51.9
87.5°	19.9	22.4	23.7	25.0	26.3	26.3	27.2	27.4	28.2	28.4	28.6
90°	11.5	14.5	17.8	21.2	24.5	27.9	28.9	30.0	31.0	32.0	32.8
92.5°	35.1	37.0	38.9	40.8	42.7	44.6	45.4	46.3	47.1	47.9	48.2
95°	75.8	77.7	79.8	81.8	83.9	86.0	87.0	88.0	89.1	90.1	90.6
97.5°	127.1	128.6	130.1	131.6	133.0	134.5	135.7	136.9	138.1	139.3	139.8
100°	164.2	165.6	166.9	168.2	169.5	170.8	171.6	172.3	173.1	173.9	174.5
102.5°	203.6	204.9	206.6	208.3	210.0	211.7	212.5	213.2	214.0	214.8	215.1
105°	263.5	264.9	267.2	269.6	271.9	274.2	274.2	274.2	274.2	274.2	274.5
107.5°	334.2	334.9	335.8	336.7	337.6	338.6	339.4	340.2	341.1	341.9	342.1
110°	379.7	380.2	380.7	381.2	381.7	382.3	383.3	384.3	385.4	386.4	386.6



TEST NUMBER: P332385

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	425.3	425.5	425.6	425.7	425.8	425.9	427.2	428.4	429.7	430.9	431.5
115°	496.9	497.0	496.5	496.0	495.5	495.0	495.2	495.5	495.7	496.0	496.0
117.5°	566.0	566.0	565.3	564.6	564.0	563.3	563.2	563.2	563.1	563.1	562.7
120°	613.9	614.0	612.7	611.4	610.1	608.8	608.6	608.3	608.1	607.8	607.4
122.5°	657.8	658.0	657.3	656.6	656.0	655.3	654.6	654.0	653.3	652.6	651.9
125°	725.8	725.9	725.4	724.9	724.4	723.9	722.8	721.8	720.8	719.7	718.7
127.5°	793.4	794.0	793.4	792.8	792.3	791.7	790.3	788.8	787.4	785.9	784.6
130°	837.8	838.5	837.7	836.9	836.2	835.4	834.4	833.3	832.3	831.3	829.8
132.5°	880.6	881.4	880.8	880.2	879.6	879.1	877.8	876.6	875.4	874.1	872.8
135°	943.8	944.5	944.2	944.0	943.7	943.4	942.4	941.4	940.3	939.3	938.5
137.5°	1003.2	1004.2	1004.9	1005.5	1006.2	1006.9	1005.8	1004.7	1003.6	1002.5	1001.5
140°	1045.0	1045.8	1046.1	1046.3	1046.6	1046.9	1046.6	1046.3	1046.1	1045.8	1044.8
142.5°	1083.2	1084.0	1084.5	1085.0	1085.4	1085.9	1085.6	1085.4	1085.1	1084.9	1084.0
145°	1139.5	1140.2	1141.0	1141.7	1142.5	1143.3	1143.0	1142.8	1142.5	1142.3	1141.6
147.5°	1193.3	1194.1	1194.8	1195.5	1196.2	1197.0	1197.0	1197.0	1197.0	1197.0	1196.2
150°	1227.9	1228.4	1228.9	1229.4	1229.9	1230.4	1230.4	1230.4	1230.4	1230.4	1229.7
152.5°	1258.4	1258.9	1259.2	1259.6	1259.9	1260.2	1260.6	1261.0	1261.4	1261.8	1261.4
155°	1302.5	1302.6	1302.9	1303.1	1303.4	1303.6	1304.7	1305.7	1306.7	1307.8	1307.4
157.5°	1341.2	1341.1	1341.4	1341.6	1341.8	1342.0	1343.1	1344.1	1345.2	1346.3	1346.1
160°	1365.5	1365.2	1365.2	1365.2	1365.2	1365.2	1366.5	1367.8	1369.1	1370.4	1370.5
162.5°	1387.0	1386.7	1386.9	1387.1	1387.3	1387.5	1388.8	1390.1	1391.4	1392.7	1392.5
165°	1415.6	1415.2	1415.2	1415.2	1415.2	1415.2	1416.7	1418.3	1419.8	1421.4	1421.2
167.5°	1437.5	1437.1	1437.3	1437.5	1437.7	1437.9	1439.5	1441.1	1442.7	1444.3	1444.3
170°	1450.5	1450.0	1450.0	1450.0	1450.0	1450.0	1451.8	1453.6	1455.5	1457.3	1457.3
172.5°	1460.8	1460.3	1460.3	1460.3	1460.3	1460.3	1461.9	1463.5	1465.1	1466.7	1466.6
175°	1471.5	1470.9	1470.9	1470.9	1470.9	1470.9	1472.5	1474.0	1475.6	1477.1	1477.0
177.5°	1476.7	1476.3	1476.3	1476.3	1476.3	1476.3	1477.5	1478.8	1480.0	1481.2	1481.1
180°	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1



TEST NUMBER: P332385

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1749.3	1748.6	1749.3	1746.7	1749.3	1748.6	1749.3	1756.8	1756.8	1757.4	1758.1
5°	1627.7	1627.0	1624.6	1617.5	1624.6	1627.0	1627.7	1630.1	1636.4	1647.4	1644.2
7.5°	1521.6	1520.5	1513.6	1513.8	1513.6	1520.5	1521.6	1527.8	1534.8	1541.6	1549.6
10°	1458.8	1459.5	1450.1	1444.6	1450.1	1459.5	1458.8	1464.3	1474.5	1480.0	1485.5
12.5°	1397.8	1394.2	1386.6	1380.5	1386.6	1394.2	1397.8	1402.0	1416.0	1422.1	1432.7
15°	1317.3	1309.4	1290.6	1292.1	1290.6	1309.4	1317.3	1314.1	1328.3	1336.1	1339.3
17.5°	1222.5	1216.7	1216.4	1205.4	1216.4	1216.7	1222.5	1228.8	1241.0	1249.5	1272.0
20°	1167.2	1163.2	1164.8	1153.8	1164.8	1163.2	1167.2	1179.7	1187.6	1198.6	1216.7
22.5°	1123.8	1119.8	1113.2	1109.8	1113.2	1119.8	1123.8	1132.6	1141.1	1156.5	1166.4
25°	1060.3	1054.0	1047.7	1051.6	1047.7	1054.0	1060.3	1065.0	1080.7	1087.8	1101.9
27.5°	996.8	992.1	985.8	985.0	985.8	992.1	996.8	1001.3	1010.0	1021.9	1038.9
30°	956.5	951.8	948.7	944.7	948.7	951.8	956.5	960.5	969.1	981.7	994.3
32.5°	915.7	914.7	909.1	908.3	909.1	914.7	915.7	922.1	930.7	942.7	953.4
35°	862.2	857.5	855.9	856.7	855.9	857.5	862.2	865.4	873.2	884.2	894.4
37.5°	811.4	805.1	802.3	799.5	802.3	805.1	811.4	811.9	819.9	827.3	841.1
40°	775.0	768.7	767.1	765.5	767.1	768.7	775.0	774.2	782.8	788.3	800.9
42.5°	734.1	731.6	730.6	727.8	730.6	731.6	734.1	738.3	743.2	751.2	760.7
45°	678.3	677.5	672.8	674.4	672.8	677.5	678.3	680.6	689.3	694.8	703.4
47.5°	619.5	616.0	612.7	614.9	612.7	616.0	619.5	622.6	628.5	635.2	646.7
50°	579.3	577.7	570.6	572.2	570.6	577.7	579.3	582.4	586.3	595.0	605.2
52.5°	539.0	533.0	530.4	529.4	530.4	533.0	539.0	542.2	546.7	556.6	564.3
55°	472.4	465.3	462.1	460.6	462.1	465.3	472.4	477.9	484.2	495.2	503.0
57.5°	407.0	405.1	402.6	404.3	402.6	405.1	407.0	416.1	422.2	430.9	440.5
60°	368.6	368.6	368.6	367.8	368.6	368.6	368.6	376.5	382.0	390.6	400.8
62.5°	339.1	337.2	336.6	337.7	336.6	337.2	339.1	342.5	348.0	353.5	362.5
65°	294.0	293.2	290.0	289.2	290.0	293.2	294.0	296.3	301.0	305.0	311.2
67.5°	251.4	248.5	247.6	246.5	247.6	248.5	251.4	253.4	256.5	261.6	264.7
70°	219.3	217.7	213.0	213.8	213.0	217.7	219.3	223.2	226.4	232.6	235.8
72.5°	184.7	183.1	182.2	181.1	182.2	183.1	184.7	188.6	191.8	198.7	203.7
75°	146.2	145.4	144.6	147.8	144.6	145.4	146.2	147.0	147.8	150.1	152.5
77.5°	117.1	117.1	117.6	116.3	117.6	117.1	117.1	117.1	117.1	118.4	118.8
80°	98.2	98.2	97.5	97.5	97.5	98.2	98.2	98.2	98.2	98.2	97.5
82.5°	78.8	79.4	79.9	78.6	79.9	79.4	78.8	80.0	80.6	79.4	79.9
85°	51.9	51.1	52.7	51.9	52.7	51.1	51.9	51.9	50.3	51.9	51.1
87.5°	29.9	28.8	28.9	29.6	28.9	28.8	29.9	28.6	28.4	28.2	27.4
90°	33.3	33.8	34.3	34.9	34.3	33.8	33.3	32.8	32.0	31.0	30.0
92.5°	47.9	47.6	47.2	46.9	47.2	47.6	47.9	48.2	47.9	47.1	46.3
95°	90.6	90.6	90.6	90.6	90.6	90.6	90.6	90.6	90.1	89.1	88.0
97.5°	139.7	139.6	139.5	139.4	139.5	139.6	139.7	139.8	139.3	138.1	136.9
100°	175.1	175.6	176.1	176.6	176.1	175.6	175.1	174.5	173.9	173.1	172.3
102.5°	215.0	214.9	214.8	214.7	214.8	214.9	215.0	215.1	214.8	214.0	213.2
105°	275.0	275.5	276.0	276.5	276.0	275.5	275.0	274.5	274.2	274.2	274.2
107.5°	341.8	341.5	341.2	340.9	341.2	341.5	341.8	342.1	341.9	341.1	340.2
110°	386.1	385.6	385.1	384.6	385.1	385.6	386.1	386.6	386.4	385.4	384.3



TEST NUMBER: P332385

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	431.4	431.3	431.2	431.1	431.2	431.3	431.4	431.5	430.9	429.7	428.4
115°	495.7	495.5	495.2	495.0	495.2	495.5	495.7	496.0	496.0	495.7	495.5
117.5°	562.0	561.2	560.5	559.8	560.5	561.2	562.0	562.7	563.1	563.1	563.2
120°	606.9	606.4	605.9	605.3	605.9	606.4	606.9	607.4	607.8	608.1	608.3
122.5°	651.2	650.5	649.7	649.0	649.7	650.5	651.2	651.9	652.6	653.3	654.0
125°	717.7	716.6	715.6	714.6	715.6	716.6	717.7	718.7	719.7	720.8	721.8
127.5°	783.4	782.2	781.0	779.9	781.0	782.2	783.4	784.6	785.9	787.4	788.8
130°	828.0	826.2	824.4	822.6	824.4	826.2	828.0	829.8	831.3	832.3	833.3
132.5°	871.4	870.0	868.6	867.2	868.6	870.0	871.4	872.8	874.1	875.4	876.6
135°	938.0	937.5	937.0	936.5	937.0	937.5	938.0	938.5	939.3	940.3	941.4
137.5°	1000.5	999.6	998.6	997.6	998.6	999.6	1000.5	1001.5	1002.5	1003.6	1004.7
140°	1043.0	1041.2	1039.4	1037.6	1039.4	1041.2	1043.0	1044.8	1045.8	1046.1	1046.3
142.5°	1082.6	1081.2	1079.9	1078.5	1079.9	1081.2	1082.6	1084.0	1084.9	1085.1	1085.4
145°	1140.6	1139.5	1138.5	1137.5	1138.5	1139.5	1140.6	1141.6	1142.3	1142.5	1142.8
147.5°	1194.6	1193.1	1191.5	1190.0	1191.5	1193.1	1194.6	1196.2	1197.0	1197.0	1197.0
150°	1228.1	1226.6	1225.0	1223.5	1225.0	1226.6	1228.1	1229.7	1230.4	1230.4	1230.4
152.5°	1260.0	1258.7	1257.3	1256.0	1257.3	1258.7	1260.0	1261.4	1261.8	1261.4	1261.0
155°	1305.6	1303.8	1302.0	1300.1	1302.0	1303.8	1305.6	1307.4	1307.8	1306.7	1305.7
157.5°	1344.7	1343.2	1341.8	1340.3	1341.8	1343.2	1344.7	1346.1	1346.3	1345.2	1344.1
160°	1369.5	1368.4	1367.4	1366.4	1367.4	1368.4	1369.5	1370.5	1370.4	1369.1	1367.8
162.5°	1390.8	1389.2	1387.5	1385.9	1387.5	1389.2	1390.8	1392.5	1392.7	1391.4	1390.1
165°	1419.4	1417.6	1415.8	1414.0	1415.8	1417.6	1419.4	1421.2	1421.4	1419.8	1418.3
167.5°	1442.7	1441.1	1439.5	1437.9	1439.5	1441.1	1442.7	1444.3	1444.3	1442.7	1441.1
170°	1455.5	1453.6	1451.8	1450.0	1451.8	1453.6	1455.5	1457.3	1457.3	1455.5	1453.6
172.5°	1464.7	1462.9	1461.1	1459.3	1461.1	1462.9	1464.7	1466.6	1466.7	1465.1	1463.5
175°	1475.2	1473.4	1471.6	1469.8	1471.6	1473.4	1475.2	1477.0	1477.1	1475.6	1474.0
177.5°	1479.7	1478.2	1476.8	1475.4	1476.8	1478.2	1479.7	1481.1	1481.2	1480.0	1478.8
180°	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1



TEST NUMBER: P332385

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1752.4	1761.2	1770.0	1778.2	1790.8	1796.4	1804.6	1807.7	1817.2	1831.0	1842.3
5°	1645.8	1658.4	1674.9	1688.3	1709.5	1726.0	1744.1	1761.4	1781.8	1810.9	1836.8
7.5°	1555.4	1567.9	1587.7	1612.5	1635.9	1659.3	1684.0	1707.6	1736.8	1778.5	1819.8
10°	1495.7	1510.6	1534.2	1560.9	1590.0	1612.8	1641.9	1671.8	1707.9	1755.9	1805.4
12.5°	1444.1	1455.3	1482.7	1508.1	1541.0	1570.1	1598.5	1633.4	1674.6	1725.7	1785.2
15°	1362.1	1377.8	1404.5	1432.8	1467.4	1498.1	1535.0	1577.4	1617.5	1680.4	1752.7
17.5°	1279.7	1303.6	1331.4	1363.3	1389.0	1431.2	1471.3	1514.9	1564.2	1630.9	1710.3
20°	1226.9	1245.8	1271.7	1318.1	1351.9	1384.1	1421.0	1475.3	1520.8	1596.3	1678.8
22.5°	1182.3	1196.1	1225.2	1263.4	1302.8	1340.1	1377.6	1429.4	1485.6	1557.3	1646.8
25°	1116.1	1138.1	1160.1	1187.6	1230.0	1274.8	1315.7	1359.7	1419.5	1495.7	1592.4
27.5°	1051.5	1071.4	1093.1	1126.9	1159.1	1201.0	1243.7	1294.2	1358.3	1439.0	1537.0
30°	1010.0	1024.9	1045.3	1088.6	1117.6	1153.8	1204.1	1248.9	1308.6	1394.3	1498.1
32.5°	967.2	986.5	1008.9	1042.0	1078.0	1112.3	1158.2	1206.8	1267.8	1352.2	1458.4
35°	906.2	929.0	951.8	976.2	1012.3	1047.7	1086.2	1139.7	1201.7	1283.5	1388.0
37.5°	850.1	868.5	887.0	917.2	951.5	985.1	1021.1	1073.8	1132.3	1220.5	1316.3
40°	814.3	830.8	844.9	876.4	909.4	945.5	980.9	1027.3	1090.1	1172.7	1265.4
42.5°	775.3	790.5	809.7	835.5	871.0	901.5	936.9	980.7	1039.8	1123.6	1205.0
45°	716.8	734.1	750.6	775.0	810.3	840.2	871.6	913.3	973.8	1043.0	1115.3
47.5°	656.0	673.3	692.1	715.7	746.5	776.9	808.3	845.2	900.4	968.3	1017.0
50°	617.0	631.1	650.0	673.6	701.9	734.1	762.4	802.5	855.1	908.6	951.0
52.5°	576.7	589.6	611.0	635.8	662.3	690.1	720.3	754.7	802.3	852.6	886.3
55°	514.0	529.7	547.8	572.2	598.1	621.7	650.8	686.2	723.9	761.6	784.4
57.5°	455.4	468.4	483.7	508.8	531.3	559.5	585.5	613.1	648.0	676.4	691.3
60°	412.6	424.4	444.1	466.1	487.3	511.7	541.5	569.0	595.8	618.6	630.3
62.5°	372.4	386.1	403.2	423.3	446.4	469.5	495.6	518.7	542.3	562.0	570.0
65°	319.9	330.9	343.5	362.3	381.2	404.8	425.2	448.8	466.1	477.1	484.2
67.5°	272.1	279.3	288.9	301.5	320.0	340.6	360.4	378.8	393.3	400.8	407.1
70°	241.3	246.0	253.1	265.7	279.8	297.9	318.3	331.7	344.3	350.5	356.8
72.5°	210.5	216.5	222.9	233.0	244.6	257.6	272.4	288.9	295.8	303.4	307.2
75°	159.6	168.2	176.8	183.1	191.0	201.2	214.6	224.8	228.7	235.0	235.8
77.5°	120.4	122.3	128.6	136.4	143.0	150.4	158.9	168.0	169.9	173.2	175.3
80°	99.0	99.0	99.0	103.7	111.6	117.1	125.0	129.7	132.8	133.6	134.4
82.5°	79.5	79.5	78.9	79.9	82.7	85.7	92.9	98.2	100.8	100.3	98.6
85°	51.9	50.3	50.3	49.5	50.3	48.7	47.9	51.1	55.8	55.8	54.2
87.5°	27.2	26.3	26.3	25.0	23.7	22.4	19.9	20.0	19.5	21.5	20.4
90°	28.9	27.9	24.5	21.2	17.8	14.5	11.5	8.9	6.3	3.7	1.2
92.5°	45.4	44.6	42.7	40.8	38.9	37.0	35.1	33.4	31.6	29.9	28.1
95°	87.0	86.0	83.9	81.8	79.8	77.7	75.8	74.0	72.2	70.4	68.6
97.5°	135.7	134.5	133.0	131.6	130.1	128.6	127.1	125.8	124.5	123.1	121.8
100°	171.6	170.8	169.5	168.2	166.9	165.6	164.2	162.7	161.1	159.6	158.0
102.5°	212.5	211.7	210.0	208.3	206.6	204.9	203.6	202.6	201.7	200.8	199.8
105°	274.2	274.2	271.9	269.6	267.2	264.9	263.5	263.0	262.5	261.9	261.4
107.5°	339.4	338.6	337.6	336.7	335.8	334.9	334.2	333.9	333.6	333.3	333.0
110°	383.3	382.3	381.7	381.2	380.7	380.2	379.7	379.2	378.6	378.1	377.6



TEST NUMBER: P332385

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	427.2	425.9	425.8	425.7	425.6	425.5	425.3	425.0	424.7	424.4	424.1
115°	495.2	495.0	495.5	496.0	496.5	497.0	496.9	496.1	495.3	494.6	493.8
117.5°	563.2	563.3	564.0	564.6	565.3	566.0	566.0	565.5	565.0	564.5	564.0
120°	608.6	608.8	610.1	611.4	612.7	614.0	613.9	612.3	610.8	609.2	607.7
122.5°	654.6	655.3	656.0	656.6	657.3	658.0	657.8	656.6	655.5	654.3	653.2
125°	722.8	723.9	724.4	724.9	725.4	725.9	725.8	725.0	724.2	723.5	722.7
127.5°	790.3	791.7	792.3	792.8	793.4	794.0	793.4	791.8	790.1	788.5	786.8
130°	834.4	835.4	836.2	836.9	837.7	838.5	837.8	835.8	833.7	831.6	829.6
132.5°	877.8	879.1	879.6	880.2	880.8	881.4	880.6	878.5	876.5	874.4	872.3
135°	942.4	943.4	943.7	944.0	944.2	944.5	943.8	942.3	940.7	939.2	937.6
137.5°	1005.8	1006.9	1006.2	1005.5	1004.9	1004.2	1003.2	1001.9	1000.6	999.3	998.1
140°	1046.6	1046.9	1046.6	1046.3	1046.1	1045.8	1045.0	1043.8	1042.5	1041.2	1039.9
142.5°	1085.6	1085.9	1085.4	1085.0	1084.5	1084.0	1083.2	1081.9	1080.6	1079.3	1078.0
145°	1143.0	1143.3	1142.5	1141.7	1141.0	1140.2	1139.5	1139.0	1138.5	1138.0	1137.5
147.5°	1197.0	1197.0	1196.2	1195.5	1194.8	1194.1	1193.3	1192.3	1191.4	1190.5	1189.5
150°	1230.4	1230.4	1229.9	1229.4	1228.9	1228.4	1227.9	1227.3	1226.8	1226.3	1225.8
152.5°	1260.6	1260.2	1259.9	1259.6	1259.2	1258.9	1258.4	1257.7	1257.0	1256.3	1255.5
155°	1304.7	1303.6	1303.4	1303.1	1302.9	1302.6	1302.5	1302.5	1302.5	1302.5	1302.5
157.5°	1343.1	1342.0	1341.8	1341.6	1341.4	1341.1	1341.2	1341.5	1341.8	1342.1	1342.4
160°	1366.5	1365.2	1365.2	1365.2	1365.2	1365.2	1365.5	1366.0	1366.5	1367.0	1367.5
162.5°	1388.8	1387.5	1387.3	1387.1	1386.9	1386.7	1387.0	1387.7	1388.4	1389.1	1389.8
165°	1416.7	1415.2	1415.2	1415.2	1415.2	1415.2	1415.6	1416.3	1417.1	1417.9	1418.7
167.5°	1439.5	1437.9	1437.7	1437.5	1437.3	1437.1	1437.5	1438.6	1439.6	1440.6	1441.7
170°	1451.8	1450.0	1450.0	1450.0	1450.0	1450.0	1450.5	1451.6	1452.6	1453.6	1454.7
172.5°	1461.9	1460.3	1460.3	1460.3	1460.3	1460.3	1460.8	1461.8	1462.8	1463.9	1464.9
175°	1472.5	1470.9	1470.9	1470.9	1470.9	1470.9	1471.5	1472.5	1473.5	1474.6	1475.6
177.5°	1477.5	1476.3	1476.3	1476.3	1476.3	1476.3	1476.7	1477.5	1478.4	1479.2	1480.0
180°	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1



TEST NUMBER: P332385

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1846.1	1853.0	1861.8	1875.0	1885.1	1893.9	1895.8	1898.3	1904.6	1915.2	1923.4
5°	1858.0	1876.1	1905.2	1933.5	1964.1	1989.3	2012.9	2029.4	2045.1	2078.1	2104.8
7.5°	1854.3	1894.5	1940.1	1990.9	2042.3	2092.1	2138.3	2179.6	2220.8	2268.9	2323.8
10°	1851.7	1898.9	1960.2	2025.4	2097.0	2166.9	2234.5	2287.2	2348.5	2403.5	2473.4
12.5°	1839.8	1907.7	1981.0	2064.4	2152.3	2232.9	2321.9	2394.7	2464.8	2544.3	2625.6
15°	1824.2	1906.8	1999.5	2110.3	2243.9	2341.4	2432.6	2559.1	2645.6	2732.0	2848.4
17.5°	1795.8	1896.5	2012.4	2156.4	2267.8	2398.8	2536.0	2636.0	2752.5	2874.3	2979.6
20°	1773.1	1890.3	2019.9	2161.4	2303.7	2445.9	2578.8	2698.2	2818.5	2959.2	3045.6
22.5°	1750.5	1866.4	2001.1	2151.4	2304.3	2454.1	2604.5	2744.8	2880.1	3022.1	3132.4
25°	1702.4	1840.0	1986.1	2139.4	2290.3	2455.4	2634.6	2791.0	2958.4	3104.6	3209.1
27.5°	1653.7	1779.7	1925.3	2080.8	2248.5	2443.6	2654.4	2832.2	2999.9	3104.6	3137.4
30°	1609.7	1743.3	1876.9	2034.9	2216.4	2434.1	2658.1	2861.7	2999.3	3044.8	3011.0
32.5°	1565.0	1686.1	1818.4	1980.2	2173.0	2410.9	2663.2	2844.1	2926.9	2892.1	2754.5
35°	1486.3	1595.5	1723.6	1885.5	2107.2	2398.0	2642.4	2765.0	2744.6	2548.1	2288.7
37.5°	1402.0	1491.0	1609.7	1779.0	2039.0	2346.9	2553.1	2571.2	2394.4	2092.7	1793.1
40°	1335.4	1415.5	1537.4	1714.2	1986.1	2296.6	2463.2	2390.1	2115.8	1780.2	1530.3
42.5°	1270.6	1338.2	1455.6	1646.3	1935.8	2228.1	2329.3	2170.1	1853.6	1536.3	1309.0
45°	1160.9	1224.5	1342.4	1538.1	1832.9	2097.0	2083.6	1806.9	1490.2	1234.8	1046.1
47.5°	1056.8	1112.5	1223.1	1422.9	1712.0	1900.5	1775.5	1481.1	1212.4	1007.5	872.9
50°	983.2	1038.3	1148.3	1345.6	1615.2	1752.7	1574.3	1290.6	1044.6	874.8	767.9
52.5°	912.8	966.6	1067.2	1259.4	1498.2	1580.4	1388.8	1125.8	920.7	774.2	682.4
55°	814.3	855.1	945.5	1129.4	1307.9	1326.7	1132.6	912.5	743.5	641.4	578.5
57.5°	713.8	749.0	838.3	984.8	1109.9	1100.2	916.1	725.8	612.0	536.0	490.4
60°	648.4	683.0	761.6	887.4	981.7	948.7	779.7	626.4	529.0	473.2	437.0
62.5°	587.4	614.5	688.0	779.8	847.7	810.3	666.5	539.6	462.3	415.3	386.7
65°	499.1	521.1	580.0	628.0	665.7	629.6	510.1	422.1	366.3	333.3	313.6
67.5°	415.1	429.1	466.4	483.7	510.3	470.6	383.6	324.6	292.9	265.0	251.4
70°	362.3	372.5	392.2	406.3	413.4	372.5	308.1	264.9	238.1	218.5	209.9
72.5°	309.5	318.5	322.4	334.0	330.4	292.1	247.7	213.3	194.1	180.8	169.6
75°	236.6	240.5	236.6	231.9	221.6	194.9	164.3	147.0	132.8	126.5	122.6
77.5°	172.4	171.2	165.8	158.5	141.0	124.2	107.7	101.9	95.7	92.4	91.0
80°	132.8	129.7	125.0	113.2	98.2	86.5	82.5	78.6	76.2	72.3	71.5
82.5°	98.9	97.0	89.1	79.2	68.7	63.2	59.9	58.5	56.1	54.1	53.9
85°	52.7	50.3	41.7	36.2	34.6	33.0	32.2	32.2	29.1	28.3	28.3
87.5°	17.7	14.5	14.4	13.0	13.6	13.0	14.3	13.7	13.8	14.6	13.5
90°	3.7	6.3	8.9	11.5	14.5	17.8	21.2	24.5	27.9	28.9	30.0
92.5°	29.9	31.6	33.4	35.1	37.0	38.9	40.8	42.7	44.6	45.4	46.3
95°	70.4	72.2	74.0	75.8	77.7	79.8	81.8	83.9	86.0	87.0	88.0
97.5°	123.1	124.5	125.8	127.1	128.6	130.1	131.6	133.0	134.5	135.7	136.9
100°	159.6	161.1	162.7	164.2	165.6	166.9	168.2	169.5	170.8	171.6	172.3
102.5°	200.8	201.7	202.6	203.6	204.9	206.6	208.3	210.0	211.7	212.5	213.2
105°	261.9	262.5	263.0	263.5	264.9	267.2	269.6	271.9	274.2	274.2	274.2
107.5°	333.3	333.6	333.9	334.2	334.9	335.8	336.7	337.6	338.6	339.4	340.2
110°	378.1	378.6	379.2	379.7	380.2	380.7	381.2	381.7	382.3	383.3	384.3



TEST NUMBER: P332385

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	424.4	424.7	425.0	425.3	425.5	425.6	425.7	425.8	425.9	427.2	428.4
115°	494.6	495.3	496.1	496.9	497.0	496.5	496.0	495.5	495.0	495.2	495.5
117.5°	564.5	565.0	565.5	566.0	566.0	565.3	564.6	564.0	563.3	563.2	563.2
120°	609.2	610.8	612.3	613.9	614.0	612.7	611.4	610.1	608.8	608.6	608.3
122.5°	654.3	655.5	656.6	657.8	658.0	657.3	656.6	656.0	655.3	654.6	654.0
125°	723.5	724.2	725.0	725.8	725.9	725.4	724.9	724.4	723.9	722.8	721.8
127.5°	788.5	790.1	791.8	793.4	794.0	793.4	792.8	792.3	791.7	790.3	788.8
130°	831.6	833.7	835.8	837.8	838.5	837.7	836.9	836.2	835.4	834.4	833.3
132.5°	874.4	876.5	878.5	880.6	881.4	880.8	880.2	879.6	879.1	877.8	876.6
135°	939.2	940.7	942.3	943.8	944.5	944.2	944.0	943.7	943.4	942.4	941.4
137.5°	999.3	1000.6	1001.9	1003.2	1004.2	1004.9	1005.5	1006.2	1006.9	1005.8	1004.7
140°	1041.2	1042.5	1043.8	1045.0	1045.8	1046.1	1046.3	1046.6	1046.9	1046.6	1046.3
142.5°	1079.3	1080.6	1081.9	1083.2	1084.0	1084.5	1085.0	1085.4	1085.9	1085.6	1085.4
145°	1138.0	1138.5	1139.0	1139.5	1140.2	1141.0	1141.7	1142.5	1143.3	1143.0	1142.8
147.5°	1190.5	1191.4	1192.3	1193.3	1194.1	1194.8	1195.5	1196.2	1197.0	1197.0	1197.0
150°	1226.3	1226.8	1227.3	1227.9	1228.4	1228.9	1229.4	1229.9	1230.4	1230.4	1230.4
152.5°	1256.3	1257.0	1257.7	1258.4	1258.9	1259.2	1259.6	1259.9	1260.2	1260.6	1261.0
155°	1302.5	1302.5	1302.5	1302.5	1302.6	1302.9	1303.1	1303.4	1303.6	1304.7	1305.7
157.5°	1342.1	1341.8	1341.5	1341.2	1341.1	1341.4	1341.6	1341.8	1342.0	1343.1	1344.1
160°	1367.0	1366.5	1366.0	1365.5	1365.2	1365.2	1365.2	1365.2	1365.2	1366.5	1367.8
162.5°	1389.1	1388.4	1387.7	1387.0	1386.7	1386.9	1387.1	1387.3	1387.5	1388.8	1390.1
165°	1417.9	1417.1	1416.3	1415.6	1415.2	1415.2	1415.2	1415.2	1415.2	1416.7	1418.3
167.5°	1440.6	1439.6	1438.6	1437.5	1437.1	1437.3	1437.5	1437.7	1437.9	1439.5	1441.1
170°	1453.6	1452.6	1451.6	1450.5	1450.0	1450.0	1450.0	1450.0	1450.0	1451.8	1453.6
172.5°	1463.9	1462.8	1461.8	1460.8	1460.3	1460.3	1460.3	1460.3	1460.3	1461.9	1463.5
175°	1474.6	1473.5	1472.5	1471.5	1470.9	1470.9	1470.9	1470.9	1470.9	1472.5	1474.0
177.5°	1479.2	1478.4	1477.5	1476.7	1476.3	1476.3	1476.3	1476.3	1476.3	1477.5	1478.8
180°	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1



TEST NUMBER: P332385

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1936.6	1936.6	1939.1	1948.6	1949.8	1958.0	1955.5
5°	2128.4	2143.3	2148.8	2172.4	2186.6	2192.9	2180.3
7.5°	2362.9	2405.1	2425.0	2449.7	2471.6	2478.2	2461.0
10°	2534.0	2578.0	2614.9	2637.7	2658.9	2673.1	2691.2
12.5°	2699.3	2753.4	2788.5	2820.7	2842.5	2860.5	2863.4
15°	2879.0	2960.7	3022.8	3068.4	3091.2	3103.0	3098.3
17.5°	3060.2	3136.0	3180.2	3226.7	3258.3	3259.9	3260.8
20°	3162.7	3236.6	3287.7	3322.3	3357.7	3356.1	3363.9
22.5°	3231.3	3289.4	3328.6	3353.7	3365.8	3359.9	3361.4
25°	3263.3	3280.6	3273.6	3233.5	3223.3	3186.3	3192.6
27.5°	3098.0	3016.2	2931.7	2822.9	2737.1	2668.5	2672.0
30°	2873.5	2728.9	2563.8	2425.5	2301.3	2266.7	2192.9
32.5°	2559.7	2342.8	2149.5	2020.6	1914.0	1885.1	1820.6
35°	2027.8	1817.2	1618.3	1498.8	1451.7	1385.7	1384.9
37.5°	1576.2	1390.7	1285.5	1195.9	1148.9	1109.0	1105.1
40°	1325.9	1181.3	1101.9	1037.5	991.1	961.2	954.2
42.5°	1151.1	1034.2	959.8	919.9	884.2	868.8	857.3
45°	940.0	861.4	809.5	773.4	756.9	745.1	738.8
47.5°	786.3	733.6	698.3	674.2	660.8	648.4	651.7
50°	702.7	659.4	633.5	610.7	600.5	591.8	592.6
52.5°	635.4	596.6	575.6	559.1	546.4	540.3	537.3
55°	539.2	514.8	493.6	481.8	474.7	466.1	463.7
57.5°	459.9	441.1	423.8	410.4	408.7	400.4	401.5
60°	407.1	391.4	377.3	370.2	364.7	357.6	360.0
62.5°	363.7	350.5	337.7	331.8	326.3	321.1	322.2
65°	297.9	285.3	277.4	274.3	271.9	269.6	267.2
67.5°	237.4	229.7	224.8	218.0	213.2	212.4	210.0
70°	199.6	189.4	180.8	172.1	169.8	169.0	169.8
72.5°	160.0	153.6	151.2	147.0	146.5	144.5	145.9
75°	120.3	117.9	116.3	113.2	113.2	113.2	113.2
77.5°	88.7	87.2	86.3	85.7	84.9	83.8	83.6
80°	69.2	68.4	66.8	66.8	66.0	66.8	66.0
82.5°	52.2	52.0	50.5	50.5	49.7	49.2	49.7
85°	26.7	25.9	27.5	25.9	26.7	25.2	26.7
87.5°	13.7	13.9	13.5	13.6	13.1	14.4	13.3
90°	31.0	32.0	32.8	33.3	33.8	34.3	34.9
92.5°	47.1	47.9	48.2	47.9	47.6	47.2	46.9
95°	89.1	90.1	90.6	90.6	90.6	90.6	90.6
97.5°	138.1	139.3	139.8	139.7	139.6	139.5	139.4
100°	173.1	173.9	174.5	175.1	175.6	176.1	176.6
102.5°	214.0	214.8	215.1	215.0	214.9	214.8	214.7
105°	274.2	274.2	274.5	275.0	275.5	276.0	276.5
107.5°	341.1	341.9	342.1	341.8	341.5	341.2	340.9
110°	385.4	386.4	386.6	386.1	385.6	385.1	384.6



TEST NUMBER: P332385

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	429.7	430.9	431.5	431.4	431.3	431.2	431.1
115°	495.7	496.0	496.0	495.7	495.5	495.2	495.0
117.5°	563.1	563.1	562.7	562.0	561.2	560.5	559.8
120°	608.1	607.8	607.4	606.9	606.4	605.9	605.3
122.5°	653.3	652.6	651.9	651.2	650.5	649.7	649.0
125°	720.8	719.7	718.7	717.7	716.6	715.6	714.6
127.5°	787.4	785.9	784.6	783.4	782.2	781.0	779.9
130°	832.3	831.3	829.8	828.0	826.2	824.4	822.6
132.5°	875.4	874.1	872.8	871.4	870.0	868.6	867.2
135°	940.3	939.3	938.5	938.0	937.5	937.0	936.5
137.5°	1003.6	1002.5	1001.5	1000.5	999.6	998.6	997.6
140°	1046.1	1045.8	1044.8	1043.0	1041.2	1039.4	1037.6
142.5°	1085.1	1084.9	1084.0	1082.6	1081.2	1079.9	1078.5
145°	1142.5	1142.3	1141.6	1140.6	1139.5	1138.5	1137.5
147.5°	1197.0	1197.0	1196.2	1194.6	1193.1	1191.5	1190.0
150°	1230.4	1230.4	1229.7	1228.1	1226.6	1225.0	1223.5
152.5°	1261.4	1261.8	1261.4	1260.0	1258.7	1257.3	1256.0
155°	1306.7	1307.8	1307.4	1305.6	1303.8	1302.0	1300.1
157.5°	1345.2	1346.3	1346.1	1344.7	1343.2	1341.8	1340.3
160°	1369.1	1370.4	1370.5	1369.5	1368.4	1367.4	1366.4
162.5°	1391.4	1392.7	1392.5	1390.8	1389.2	1387.5	1385.9
165°	1419.8	1421.4	1421.2	1419.4	1417.6	1415.8	1414.0
167.5°	1442.7	1444.3	1444.3	1442.7	1441.1	1439.5	1437.9
170°	1455.5	1457.3	1457.3	1455.5	1453.6	1451.8	1450.0
172.5°	1465.1	1466.7	1466.6	1464.7	1462.9	1461.1	1459.3
175°	1475.6	1477.1	1477.0	1475.2	1473.4	1471.6	1469.8
177.5°	1480.0	1481.2	1481.1	1479.7	1478.2	1476.8	1475.4
180°	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1

(END OF REPORT)