

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332341-830

Luminaire Tested: **S123RDIP-S1000D585U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332341-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D585U830-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5573.4 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332341-830

CATALOG NUMBER: S123RDIP-S1000D585U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332341-830

CATALOG NUMBER: S123RDIP-S1000D585U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	62	60	59
2	93	85	79	74	87	80	75	70	71	67	64	63	60	57	55	53	51
3	85	75	68	62	79	71	65	59	63	58	54	56	52	49	49	46	43
4	78	67	59	53	73	63	56	51	56	51	46	50	46	42	44	41	38
5	72	60	52	46	67	57	49	44	51	45	40	45	40	37	40	36	33
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29
7	61	49	41	35	58	47	39	34	42	36	31	37	32	29	33	29	26
8	57	45	37	31	54	42	35	30	38	32	28	34	29	26	31	27	24
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	28	24	21
10	50	38	30	26	47	36	29	25	33	27	23	29	25	21	26	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17026	17026	17026
5°	17091	16855	16953
10°	16994	16644	16587
15°	16811	16254	16082
20°	16561	15767	15400
25°	16302	15221	14733
30°	15960	14589	13793
35°	15609	13958	12929
40°	15286	13212	11861
45°	14862	12478	10898
50°	14393	11643	9818
55°	13915	10689	8811
60°	13476	9666	7705
65°	12905	8560	6599
70°	12192	7188	5331
75°	11154	5656	5016
80°	9937	5009	4612
85°	8398	4434	4125



TEST NUMBER: P332341-830

CATALOG NUMBER: S123RDIP-S1000D585U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.5	2.7
10°-20°	413.3	7.4
20°-30°	595.1	10.7
30°-40°	670.3	12.0
40°-50°	641.3	11.5
50°-60°	525.1	9.4
60°-70°	354.3	6.4
70°-80°	178.2	3.2
80°-90°	49.2	0.9
90°-100°	147.8	2.7
100°-110°	418.5	7.5
110°-120°	411.7	7.4
120°-130°	328.4	5.9
130°-140°	258.9	4.6
140°-150°	193.2	3.5
150°-160°	134.7	2.4
160°-170°	79.1	1.4
170°-180°	25.7	0.5
0°-30°	1156.9	20.8
0°-40°	1827.2	32.8
0°-60°	2993.6	53.7
0°-90°	3575.4	64.2
90°-120°	978.0	17.5
90°-150°	1758.5	31.6
90°-180°	1998.0	35.8
0°-180°	5573.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1582	1582	1582	1582	1582	
5°	1582	1575	1560	1571	1569	150
15°	1509	1493	1459	1452	1443	425
25°	1373	1339	1282	1255	1240	631
35°	1188	1140	1062	1009	984	743
45°	976	916	820	749	716	753
55°	742	676	570	498	470	665
65°	507	435	336	276	259	501
75°	268	206	136	124	121	286
85°	68	41	36	34	33	76
90°	1	6	14	15	16	5
95°	18	59	319	93	62	20
105°	62	92	432	756	684	66
115°	110	137	331	725	832	109
125°	153	181	309	559	656	136
135°	180	214	304	460	532	139
145°	205	235	300	378	416	128
155°	233	251	291	331	345	107
165°	254	262	278	295	300	72
175°	265	265	267	271	270	25
180°	266	266	266	266	266	



TEST NUMBER: P332341-830

CATALOG NUMBER: S123RDIP-S1000D585U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8
2.5°	1586.9	1585.9	1585.1	1584.1	1583.2	1581.4	1578.7	1575.9	1573.2	1570.5	1572.9
5°	1581.8	1580.3	1578.9	1577.4	1576.0	1573.6	1570.2	1566.8	1563.4	1559.9	1562.5
7.5°	1567.1	1565.6	1564.1	1562.5	1560.9	1557.9	1553.5	1549.1	1544.6	1540.2	1541.6
10°	1554.8	1552.8	1550.8	1548.8	1546.8	1543.2	1538.1	1533.0	1527.9	1522.8	1523.1
12.5°	1537.4	1535.1	1533.0	1530.7	1528.4	1524.2	1518.0	1511.6	1505.4	1499.1	1498.9
15°	1508.6	1505.5	1502.3	1499.2	1496.1	1490.5	1482.5	1474.5	1466.6	1458.6	1457.2
17.5°	1472.4	1468.8	1465.2	1461.5	1457.8	1451.0	1440.8	1430.7	1420.5	1410.3	1407.3
20°	1445.8	1441.2	1436.6	1432.1	1427.5	1419.8	1409.0	1398.2	1387.3	1376.5	1372.8
22.5°	1416.0	1410.8	1405.5	1400.2	1395.1	1386.7	1375.1	1363.6	1352.1	1340.6	1336.0
25°	1372.6	1365.6	1358.4	1351.2	1344.2	1334.0	1320.9	1307.8	1294.7	1281.6	1275.5
27.5°	1320.0	1312.2	1304.3	1296.5	1288.5	1277.3	1262.7	1248.1	1233.5	1219.0	1210.6
30°	1284.1	1275.5	1267.1	1258.5	1249.9	1237.7	1221.7	1205.7	1189.8	1173.8	1164.1
32.5°	1248.2	1238.5	1228.8	1219.1	1209.5	1196.2	1179.3	1162.4	1145.5	1128.6	1118.0
35°	1187.9	1177.6	1167.3	1157.2	1146.9	1132.8	1115.2	1097.5	1079.9	1062.2	1049.9
37.5°	1126.8	1115.4	1104.0	1092.6	1081.2	1066.1	1047.3	1028.3	1009.5	990.6	976.7
40°	1087.9	1075.3	1062.7	1050.2	1037.6	1021.2	1001.1	980.8	960.5	940.3	925.5
42.5°	1043.7	1031.1	1018.6	1006.1	993.5	976.9	955.9	935.0	914.1	893.2	876.9
45°	976.3	963.4	950.6	937.7	924.9	907.6	885.6	863.7	841.7	819.7	803.5
47.5°	908.8	894.7	880.6	866.5	852.4	834.4	812.5	790.5	768.5	746.6	729.0
50°	859.5	846.1	832.7	819.4	805.9	787.7	764.6	741.5	718.4	695.3	677.6
52.5°	815.4	800.9	786.3	771.8	757.2	738.5	715.7	692.8	670.0	647.1	628.7
55°	741.5	727.5	713.5	699.6	685.6	666.5	642.2	618.0	593.8	569.6	553.1
57.5°	673.3	658.0	642.8	627.5	612.4	592.6	568.2	543.8	519.5	495.2	479.6
60°	626.0	610.4	594.7	579.0	563.3	543.7	520.0	496.3	472.7	449.0	433.6
62.5°	578.8	563.2	547.4	531.8	516.1	496.4	472.8	449.1	425.5	401.8	387.3
65°	506.7	491.1	475.3	459.7	444.0	425.1	402.8	380.6	358.4	336.1	322.2
67.5°	434.6	418.8	402.9	387.1	371.3	352.6	331.3	310.0	288.7	267.3	256.9
70°	387.4	372.0	356.7	341.2	325.8	308.2	288.2	268.2	248.3	228.4	218.4
72.5°	340.2	325.1	309.9	294.7	279.6	262.9	244.8	226.7	208.5	190.4	182.2
75°	268.2	254.4	240.7	227.1	213.4	198.7	183.0	167.3	151.7	136.0	133.1
77.5°	202.5	190.0	177.7	165.3	153.0	141.7	131.6	121.5	111.4	101.3	99.8
80°	160.3	148.6	137.0	125.3	113.6	104.8	98.8	92.7	86.8	80.8	79.9
82.5°	120.4	110.3	100.2	90.0	79.9	73.5	70.7	68.0	65.1	62.3	61.5
85°	68.0	61.7	55.4	49.2	42.9	39.3	38.5	37.6	36.8	35.9	35.3
87.5°	24.9	22.5	20.3	18.1	15.7	14.7	15.1	15.4	15.7	16.0	15.7
90°	1.0	2.2	3.2	4.8	5.9	7.0	8.6	10.2	11.8	13.5	12.9
92.5°	6.7	9.9	14.4	18.6	23.1	31.1	45.1	68.2	91.0	82.7	62.4
95°	18.3	19.9	25.8	35.0	48.9	69.8	115.6	195.7	283.9	318.8	258.5
97.5°	31.2	31.8	36.4	44.3	58.1	80.8	124.4	214.7	361.7	494.1	528.6
100°	39.8	40.3	44.1	51.7	64.5	85.5	123.1	202.6	344.0	509.1	615.0
102.5°	48.8	49.8	53.2	60.2	71.8	91.0	124.8	192.4	318.3	481.2	619.3
105°	62.4	64.0	67.2	73.6	83.9	100.6	129.6	184.9	286.5	432.3	586.5
107.5°	76.7	78.4	81.5	87.8	97.5	112.9	138.4	184.4	266.4	389.0	529.1
110°	87.1	88.7	91.4	97.3	106.4	121.5	145.7	186.5	258.5	364.5	492.9



TEST NUMBER: P332341-830

CATALOG NUMBER: S123RDIP-S1000D585U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	96.5	98.2	100.9	106.8	115.9	130.5	153.0	190.9	254.3	348.2	461.6
115°	110.2	112.4	115.6	120.9	130.1	144.6	165.0	197.8	252.7	330.6	423.7
117.5°	123.9	126.3	129.0	133.9	144.2	157.6	177.9	207.1	253.6	320.3	400.8
120°	133.4	135.0	137.6	143.0	153.3	166.6	186.0	214.0	255.3	315.6	388.7
122.5°	141.5	143.1	145.8	151.6	161.4	175.7	194.6	220.5	258.4	312.5	378.8
125°	153.3	154.3	157.5	163.4	173.6	188.1	207.0	230.6	262.9	308.6	366.1
127.5°	162.1	163.7	167.8	173.7	185.0	199.5	217.7	239.0	268.1	306.6	355.0
130°	167.8	169.4	174.2	180.6	191.9	206.4	224.1	244.6	271.5	305.4	348.9
132.5°	172.0	174.1	179.4	187.1	198.4	212.4	229.8	249.8	274.1	304.9	343.3
135°	179.6	181.7	187.7	195.7	207.0	221.5	238.2	256.5	278.0	304.3	336.0
137.5°	186.6	188.9	194.7	203.3	214.5	227.9	243.9	261.4	280.5	303.1	329.7
140°	191.4	194.1	199.4	208.0	218.8	232.2	247.8	264.0	282.2	302.7	325.7
142.5°	196.5	198.8	204.6	212.4	223.1	235.7	250.8	266.6	283.5	301.8	322.3
145°	204.8	206.4	211.3	219.3	228.5	240.8	254.9	269.4	284.4	300.5	317.7
147.5°	213.2	214.1	219.0	225.9	234.7	245.2	258.1	271.1	284.4	298.5	313.2
150°	218.8	219.3	223.7	230.6	238.2	247.8	260.2	271.5	284.4	296.7	310.2
152.5°	224.4	224.5	228.8	235.0	241.6	250.8	261.5	272.4	283.1	294.6	306.8
155°	232.8	232.8	236.0	241.4	247.3	254.9	264.0	272.6	281.7	290.9	301.6
157.5°	239.4	239.9	242.4	247.2	252.2	258.1	265.3	273.1	279.8	287.5	295.8
160°	244.6	244.6	246.8	251.1	254.9	260.2	266.6	273.1	279.0	284.9	291.9
162.5°	248.5	248.5	250.2	253.6	256.9	261.5	267.1	272.7	277.3	282.4	288.0
165°	254.3	253.7	254.9	257.5	259.7	263.4	267.7	271.5	274.8	278.5	282.8
167.5°	258.7	258.1	258.5	260.6	262.1	264.5	267.6	270.6	272.1	274.6	277.8
170°	261.3	260.2	260.7	262.3	263.4	264.5	267.2	269.4	270.4	272.0	274.8
172.5°	263.0	262.3	262.5	263.6	264.3	264.9	267.2	268.9	269.1	269.8	271.7
175°	265.0	264.5	264.0	265.0	265.0	265.6	266.6	267.7	267.2	267.2	268.2
177.5°	266.0	265.6	265.1	265.6	265.6	265.6	266.0	266.8	266.0	265.6	266.0
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6



TEST NUMBER: P332341-830

CATALOG NUMBER: S123RDIP-S1000D585U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8
2.5°	1575.5	1578.0	1580.5	1581.5	1581.0	1580.6	1580.2	1579.7
5°	1565.1	1567.6	1570.2	1571.2	1570.7	1570.1	1569.5	1569.0
7.5°	1543.0	1544.5	1545.9	1546.1	1545.1	1544.2	1543.2	1542.2
10°	1523.3	1523.6	1523.9	1523.3	1521.8	1520.4	1519.0	1517.6
12.5°	1498.7	1498.6	1498.5	1497.5	1495.9	1494.2	1492.6	1490.9
15°	1455.8	1454.3	1452.9	1451.1	1449.2	1447.2	1445.2	1443.2
17.5°	1404.3	1401.3	1398.3	1395.2	1392.3	1389.3	1386.4	1383.4
20°	1369.0	1365.4	1361.7	1358.1	1354.7	1351.2	1347.8	1344.4
22.5°	1331.3	1326.7	1322.1	1318.1	1315.0	1311.8	1308.6	1305.4
25°	1269.6	1263.6	1257.6	1253.0	1249.9	1246.8	1243.7	1240.5
27.5°	1202.3	1194.0	1185.6	1179.1	1174.3	1169.5	1164.7	1160.0
30°	1154.4	1144.7	1135.0	1127.9	1123.3	1118.8	1114.2	1109.7
32.5°	1107.4	1096.8	1086.2	1078.6	1073.7	1068.9	1064.1	1059.3
35°	1037.6	1025.4	1013.1	1004.5	999.4	994.2	989.1	983.9
37.5°	962.8	948.9	935.0	924.8	918.5	912.2	905.9	899.6
40°	910.7	895.9	881.0	870.3	863.7	857.2	850.6	844.1
42.5°	860.7	844.5	828.3	817.3	811.4	805.6	799.7	793.8
45°	787.2	771.0	754.7	743.2	736.3	729.5	722.6	715.9
47.5°	711.2	693.6	675.9	664.0	657.9	651.9	645.7	639.6
50°	660.0	642.2	624.6	612.5	606.0	599.4	592.9	586.3
52.5°	610.4	592.0	573.6	561.5	555.6	549.8	543.9	538.0
55°	536.5	520.0	503.4	492.3	486.6	480.9	475.2	469.5
57.5°	463.9	448.3	432.7	422.4	417.6	412.7	407.9	403.0
60°	418.2	402.8	387.4	377.3	372.5	367.6	362.8	357.9
62.5°	372.8	358.4	343.8	334.0	329.0	324.0	318.9	313.8
65°	308.2	294.2	280.2	271.6	268.5	265.4	262.3	259.1
67.5°	246.5	236.0	225.6	218.7	215.4	212.0	208.6	205.3
70°	208.4	198.4	188.4	181.9	178.7	175.6	172.5	169.4
72.5°	174.1	165.9	157.8	153.1	151.7	150.4	149.1	147.8
75°	130.3	127.4	124.6	122.9	122.3	121.7	121.1	120.6
77.5°	98.3	96.7	95.2	94.2	93.6	93.0	92.5	91.9
80°	79.1	78.2	77.4	76.7	76.2	75.6	74.9	74.4
82.5°	60.6	59.8	58.9	58.4	58.3	58.2	58.1	58.0
85°	34.8	34.2	33.6	33.4	33.4	33.4	33.4	33.4
87.5°	15.6	15.5	15.4	15.4	15.0	14.9	14.7	14.4
90°	13.5	13.9	14.5	15.6	15.1	15.6	16.1	15.6
92.5°	45.2	35.9	31.8	28.9	28.0	26.3	26.9	25.9
95°	193.5	131.2	102.6	83.3	73.1	68.2	64.5	62.4
97.5°	482.5	386.4	317.1	252.8	213.1	188.9	174.4	169.8
100°	633.9	590.3	527.4	451.0	396.7	357.5	336.6	337.1
102.5°	684.2	682.8	646.1	597.7	555.4	524.3	506.8	494.5
105°	698.9	752.6	762.9	748.9	724.2	703.7	686.5	683.8
107.5°	656.5	743.9	790.9	810.0	810.5	803.6	797.8	792.9
110°	616.0	715.0	782.8	820.4	835.5	839.7	838.7	837.5



TEST NUMBER: P332341-830

CATALOG NUMBER: S123RDIP-S1000D585U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	576.1	677.1	753.1	801.4	829.0	842.4	846.4	846.6
115°	523.1	616.6	695.7	754.2	794.6	818.2	829.0	831.7
117.5°	484.7	565.4	636.4	695.9	737.9	765.0	780.5	784.1
120°	464.5	537.1	601.5	655.9	698.3	728.5	741.3	744.6
122.5°	448.6	514.3	574.0	624.4	662.2	689.3	703.5	707.6
125°	427.3	486.0	537.6	580.6	615.0	638.7	652.1	655.9
127.5°	408.9	461.2	507.7	546.9	577.5	597.7	609.8	613.3
130°	397.3	445.6	489.2	525.8	554.3	573.6	584.9	589.2
132.5°	386.5	431.0	471.6	506.4	533.2	552.5	562.5	565.5
135°	372.0	410.2	445.2	475.8	502.1	518.2	527.9	531.7
137.5°	358.8	390.1	420.2	446.8	468.9	485.2	493.4	495.9
140°	351.1	378.4	404.3	427.3	447.8	462.9	471.5	470.9
142.5°	343.7	367.3	389.6	409.7	427.2	440.5	448.3	447.7
145°	334.9	352.7	369.9	385.5	398.9	410.2	414.5	415.6
147.5°	327.7	341.8	355.7	366.7	376.9	384.6	388.7	389.1
150°	322.5	334.9	346.2	356.5	364.5	370.4	373.6	373.6
152.5°	317.8	328.5	338.5	346.9	353.3	358.8	360.7	360.7
155°	310.8	319.3	327.4	333.8	338.7	343.0	344.0	344.6
157.5°	303.2	310.4	316.7	321.7	325.9	329.1	330.0	329.9
160°	298.9	304.8	310.2	314.0	317.7	320.9	320.9	320.4
162.5°	293.8	298.8	303.8	307.1	309.5	312.4	312.4	311.8
165°	287.1	290.3	294.1	296.7	298.9	301.0	300.5	300.5
167.5°	281.3	283.7	285.9	287.9	288.8	290.3	289.7	289.7
170°	277.4	279.0	281.2	282.2	282.8	283.9	283.3	283.3
172.5°	274.0	275.1	276.8	277.5	277.6	278.7	277.8	277.3
175°	269.4	269.8	271.0	271.0	271.0	271.5	271.0	270.4
177.5°	266.5	266.8	267.3	267.3	266.8	267.3	266.5	266.5
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6

(END OF REPORT)