

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332387

Luminaire Tested: **S123RDIP-S1165D1195U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332387
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D1195U835-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9151.7 lumens
Efficiency: N/A
Efficacy: 127.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332387

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332387

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48	48	48	48	48														
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41	41	41	41	41	41	41														
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	40	35	35	35	35	35	35	35														
3	81	72	65	59	75	67	61	56	57	52	48	47	44	41	38	36	34	30	30	30	30	30	30	30														
4	75	64	56	51	68	59	53	47	50	45	41	42	38	35	34	32	29	26	26	26	26	26	26	26														
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23	23	23	23	23	23	23														
6	63	51	43	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20	20	20	20	20	20	20														
7	59	47	39	33	54	43	36	31	37	32	28	31	27	24	26	23	20	18	18	18	18	18	18	18														
8	54	42	35	29	50	39	33	28	34	28	25	29	25	21	24	21	18	16	16	16	16	16	16	16														
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17	15	15	15	15	15	15	15														
10	47	35	28	24	44	33	27	22	29	24	20	24	20	18	20	17	15	13	13	13	13	13	13	13														

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20863	20863	20863
5°	20942	20653	20772
10°	20824	20394	20325
15°	20600	19917	19706
20°	20292	19321	18871
25°	19975	18650	18053
30°	19557	17877	16900
35°	19127	17102	15843
40°	18730	16190	14533
45°	18209	15289	13352
50°	17637	14267	12030
55°	17051	13097	10796
60°	16514	11845	9442
65°	15814	10488	8087
70°	14940	8806	6530
75°	13662	6929	6147
80°	12180	6137	5653
85°	10288	5434	5051



TEST NUMBER: P332387

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.0	2.0
10°-20°	506.4	5.5
20°-30°	729.2	8.0
30°-40°	821.3	9.0
40°-50°	785.8	8.6
50°-60°	643.5	7.0
60°-70°	434.1	4.7
70°-80°	218.4	2.4
80°-90°	62.2	0.7
90°-100°	56.9	0.6
100°-110°	271.0	3.0
110°-120°	650.9	7.1
120°-130°	828.8	9.1
130°-140°	885.6	9.7
140°-150°	828.1	9.0
150°-160°	668.0	7.3
160°-170°	431.1	4.7
170°-180°	148.6	1.6
0°-30°	1417.6	15.5
0°-40°	2238.9	24.5
0°-60°	3668.1	40.1
0°-90°	4382.9	47.9
90°-120°	978.7	10.7
90°-150°	3521.2	38.5
90°-180°	4769.0	52.1
0°-180°	9151.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1938	1938	1938	1938	1938	
5°	1938	1930	1911	1925	1922	184
15°	1849	1830	1787	1779	1768	521
25°	1682	1641	1570	1538	1520	773
35°	1456	1397	1302	1236	1206	911
45°	1196	1123	1004	918	877	923
55°	909	828	698	610	575	814
65°	621	532	412	338	318	614
75°	328	252	167	152	148	350
85°	83	50	44	41	41	94
90°	1	13	28	32	35	7
95°	71	27	36	44	44	88
105°	346	352	254	60	51	367
115°	650	657	667	678	683	641
125°	916	925	929	932	934	817
135°	1140	1147	1151	1154	1151	877
145°	1315	1323	1326	1328	1328	823
155°	1449	1447	1448	1453	1446	667
165°	1528	1524	1523	1531	1524	431
175°	1564	1558	1559	1566	1558	149
180°	1564	1564	1564	1564	1564	



TEST NUMBER: P332387

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2
2.5°	1944.5	1943.3	1942.2	1941.1	1940.0	1937.7	1934.4	1931.0	1927.7	1924.3	1927.4
5°	1938.2	1936.4	1934.7	1932.9	1931.2	1928.2	1924.0	1919.8	1915.6	1911.4	1914.6
7.5°	1920.2	1918.4	1916.5	1914.6	1912.7	1909.0	1903.6	1898.1	1892.7	1887.2	1889.0
10°	1905.2	1902.7	1900.3	1897.8	1895.4	1891.0	1884.7	1878.4	1872.1	1865.9	1866.2
12.5°	1883.8	1881.1	1878.3	1875.6	1872.9	1867.7	1860.0	1852.3	1844.6	1836.9	1836.7
15°	1848.6	1844.7	1840.9	1837.0	1833.2	1826.4	1816.6	1806.8	1797.0	1787.3	1785.5
17.5°	1804.2	1799.8	1795.3	1790.8	1786.4	1777.9	1765.5	1753.0	1740.6	1728.2	1724.5
20°	1771.5	1766.0	1760.4	1754.8	1749.2	1739.8	1726.5	1713.2	1699.9	1686.7	1682.1
22.5°	1735.1	1728.6	1722.2	1715.8	1709.4	1699.1	1685.0	1670.9	1656.8	1642.6	1637.0
25°	1681.9	1673.2	1664.5	1655.7	1647.0	1634.6	1618.5	1602.5	1586.4	1570.3	1563.0
27.5°	1617.5	1607.9	1598.2	1588.6	1578.9	1565.2	1547.3	1529.4	1511.5	1493.6	1483.4
30°	1573.5	1563.0	1552.5	1542.0	1531.6	1516.5	1497.0	1477.4	1457.9	1438.3	1426.4
32.5°	1529.5	1517.6	1505.7	1493.8	1482.0	1465.7	1445.0	1424.3	1403.6	1383.0	1370.0
35°	1455.6	1443.0	1430.4	1417.9	1405.3	1388.2	1366.5	1344.9	1323.2	1301.5	1286.5
37.5°	1380.8	1366.8	1352.8	1338.8	1324.9	1306.3	1283.2	1260.1	1237.0	1213.8	1196.8
40°	1333.0	1317.6	1302.2	1286.9	1271.5	1251.4	1226.6	1201.8	1177.0	1152.2	1134.0
42.5°	1278.9	1263.5	1248.2	1232.8	1217.4	1196.9	1171.3	1145.6	1120.0	1094.4	1074.5
45°	1196.2	1180.5	1164.8	1149.1	1133.3	1112.0	1085.1	1058.2	1031.3	1004.4	984.5
47.5°	1113.5	1096.3	1079.0	1061.8	1044.5	1022.4	995.5	968.6	941.7	914.9	893.2
50°	1053.2	1036.8	1020.3	1003.9	987.5	965.2	936.9	908.6	880.3	852.0	830.3
52.5°	999.1	981.3	963.5	945.7	927.8	904.9	876.9	848.9	820.9	792.9	770.4
55°	908.6	891.4	874.3	857.2	840.1	816.7	787.0	757.3	727.6	697.9	677.7
57.5°	824.9	806.3	787.6	769.0	750.3	726.1	696.3	666.4	636.6	606.8	587.6
60°	767.1	747.9	728.7	709.5	690.2	666.1	637.1	608.2	579.2	550.2	531.3
62.5°	709.2	690.0	670.8	651.6	632.4	608.3	579.3	550.3	521.3	492.3	474.6
65°	620.9	601.7	582.5	563.3	544.1	520.8	493.6	466.3	439.1	411.8	394.7
67.5°	532.6	513.1	493.7	474.3	454.9	432.1	406.0	379.8	353.7	327.6	314.8
70°	474.7	455.9	437.0	418.1	399.3	377.6	353.2	328.7	304.3	279.8	267.6
72.5°	416.9	398.3	379.7	361.1	342.5	322.1	299.9	277.7	255.5	233.3	223.3
75°	328.5	311.8	295.0	278.2	261.5	243.5	224.3	205.0	185.8	166.6	163.1
77.5°	248.0	232.9	217.7	202.6	187.4	173.6	161.3	148.9	136.5	124.2	122.3
80°	196.5	182.2	167.8	153.5	139.2	128.4	121.0	113.7	106.4	99.0	98.0
82.5°	147.4	135.1	122.7	110.3	98.0	90.1	86.7	83.2	79.8	76.4	75.3
85°	83.3	75.6	67.9	60.3	52.6	48.2	47.2	46.1	45.1	44.0	43.3
87.5°	30.4	27.9	25.3	22.7	20.2	19.2	19.9	20.6	21.3	21.9	21.9
90°	1.2	3.7	6.3	8.9	11.5	14.5	17.8	21.2	24.5	27.9	28.9
92.5°	21.6	20.9	20.2	19.4	18.7	19.6	22.2	24.7	27.2	29.7	31.4
95°	70.9	60.3	49.7	39.1	28.5	24.7	27.5	30.3	33.2	36.0	37.8
97.5°	142.4	137.7	132.9	128.2	123.4	111.8	93.2	74.6	56.0	37.4	39.5
100°	196.3	201.5	206.7	211.8	217.0	199.4	159.2	118.9	78.6	38.3	40.4
102.5°	257.7	261.4	265.1	268.8	272.6	252.4	208.4	164.4	120.4	76.4	70.0
105°	346.2	349.1	351.9	354.7	357.6	347.4	324.1	300.9	277.7	254.4	208.7
107.5°	439.6	441.9	444.2	446.4	448.7	451.7	455.4	459.0	462.7	466.4	432.8
110°	501.9	504.0	506.0	508.1	510.2	512.6	515.5	518.3	521.1	524.0	515.5



TEST NUMBER: P332387

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	561.4	563.2	565.1	567.0	568.8	571.2	574.0	576.9	579.7	582.5	582.7
115°	649.5	651.0	652.5	654.1	655.6	657.6	659.9	662.2	664.6	666.9	669.5
117.5°	734.7	736.6	738.5	740.5	742.4	743.9	745.1	746.3	747.5	748.7	750.7
120°	787.7	790.0	792.4	794.7	797.0	798.6	799.3	800.1	800.9	801.6	803.7
122.5°	841.6	843.5	845.4	847.3	849.3	850.7	851.7	852.7	853.6	854.6	856.1
125°	915.5	917.6	919.6	921.7	923.8	925.3	926.3	927.4	928.4	929.4	930.0
127.5°	987.1	989.1	991.2	993.3	995.3	997.0	998.2	999.5	1000.7	1001.9	1002.8
130°	1031.7	1033.8	1035.8	1037.9	1039.9	1041.5	1042.5	1043.6	1044.6	1045.6	1046.7
132.5°	1074.4	1076.5	1078.6	1080.6	1082.7	1084.1	1085.0	1085.8	1086.6	1087.5	1088.5
135°	1139.7	1141.3	1142.8	1144.4	1145.9	1147.2	1148.3	1149.3	1150.3	1151.4	1152.1
137.5°	1195.5	1197.5	1199.4	1201.4	1203.4	1204.6	1205.2	1205.8	1206.3	1206.9	1208.1
140°	1232.7	1234.2	1235.8	1237.3	1238.9	1240.0	1240.8	1241.6	1242.4	1243.1	1244.2
142.5°	1267.1	1268.6	1270.2	1271.7	1273.3	1274.4	1275.2	1276.0	1276.8	1277.5	1278.4
145°	1315.2	1317.0	1318.8	1320.6	1322.4	1323.6	1324.1	1324.6	1325.1	1325.6	1326.1
147.5°	1360.5	1361.7	1362.9	1364.0	1365.2	1366.1	1366.6	1367.1	1367.6	1368.1	1368.7
150°	1388.4	1389.1	1389.9	1390.7	1391.5	1392.1	1392.6	1393.1	1393.7	1394.2	1394.7
152.5°	1413.5	1413.8	1414.2	1414.5	1414.9	1415.2	1415.5	1415.9	1416.2	1416.5	1417.4
155°	1448.8	1448.3	1447.7	1447.2	1446.7	1446.6	1446.8	1447.1	1447.4	1447.6	1448.9
157.5°	1476.2	1476.1	1476.1	1476.0	1476.0	1475.8	1475.6	1475.3	1475.1	1474.8	1476.4
160°	1492.9	1492.7	1492.4	1492.2	1491.9	1491.6	1491.4	1491.1	1490.9	1490.6	1492.2
162.5°	1508.7	1508.1	1507.4	1506.7	1506.0	1505.6	1505.3	1505.1	1504.8	1504.5	1506.3
165°	1527.8	1527.0	1526.2	1525.5	1524.7	1524.2	1523.9	1523.6	1523.4	1523.1	1525.2
167.5°	1542.7	1541.6	1540.6	1539.6	1538.5	1538.0	1538.0	1538.0	1538.0	1538.0	1540.1
170°	1551.0	1550.0	1549.0	1547.9	1546.9	1546.4	1546.4	1546.4	1546.4	1546.4	1548.4
172.5°	1556.6	1555.4	1554.1	1552.9	1551.6	1551.1	1551.3	1551.5	1551.7	1551.9	1554.0
175°	1563.8	1562.5	1561.2	1559.9	1558.6	1558.1	1558.4	1558.6	1558.9	1559.1	1561.0
177.5°	1565.7	1564.6	1563.6	1562.6	1561.5	1561.1	1561.3	1561.5	1561.7	1561.9	1563.6
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P332387

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2
2.5°	1930.5	1933.6	1936.6	1937.9	1937.3	1936.8	1936.2	1935.6
5°	1917.7	1920.9	1924.0	1925.2	1924.5	1923.8	1923.1	1922.4
7.5°	1890.7	1892.5	1894.2	1894.5	1893.3	1892.1	1890.9	1889.7
10°	1866.6	1866.9	1867.3	1866.6	1864.8	1863.1	1861.3	1859.6
12.5°	1836.5	1836.3	1836.1	1835.0	1833.0	1830.9	1828.9	1826.9
15°	1783.8	1782.0	1780.3	1778.2	1775.7	1773.3	1770.8	1768.4
17.5°	1720.8	1717.0	1713.3	1709.7	1706.0	1702.4	1698.8	1695.1
20°	1677.6	1673.0	1668.5	1664.1	1659.9	1655.7	1651.6	1647.4
22.5°	1631.3	1625.7	1620.0	1615.2	1611.3	1607.4	1603.5	1599.6
25°	1555.7	1548.3	1541.0	1535.4	1531.6	1527.7	1523.9	1520.0
27.5°	1473.2	1463.0	1452.8	1444.8	1438.9	1433.1	1427.2	1421.3
30°	1414.5	1402.7	1390.8	1382.1	1376.5	1370.9	1365.3	1359.7
32.5°	1357.0	1344.0	1331.0	1321.6	1315.7	1309.8	1304.0	1298.1
35°	1271.5	1256.5	1241.5	1230.8	1224.5	1218.2	1211.9	1205.7
37.5°	1179.7	1162.7	1145.6	1133.2	1125.5	1117.7	1110.0	1102.2
40°	1115.9	1097.7	1079.6	1066.5	1058.4	1050.4	1042.4	1034.3
42.5°	1054.7	1034.8	1015.0	1001.5	994.3	987.1	979.9	972.7
45°	964.6	944.7	924.8	910.7	902.3	893.9	885.5	877.1
47.5°	871.5	849.9	828.2	813.7	806.2	798.7	791.2	783.8
50°	808.7	787.0	765.3	750.5	742.5	734.4	726.4	718.4
52.5°	747.9	725.4	702.9	688.0	680.8	673.7	666.5	659.3
55°	657.4	637.1	616.9	603.3	596.3	589.3	582.3	575.3
57.5°	568.5	549.3	530.2	517.6	511.7	505.8	499.8	493.9
60°	512.4	493.6	474.7	462.3	456.4	450.4	444.5	438.6
62.5°	456.8	439.1	421.3	409.4	403.1	396.9	390.7	384.5
65°	377.6	360.5	343.4	332.9	329.1	325.2	321.4	317.5
67.5°	302.0	289.2	276.4	268.0	263.9	259.7	255.6	251.5
70°	255.3	243.1	230.9	222.9	219.0	215.2	211.3	207.5
72.5°	213.3	203.3	193.3	187.5	185.9	184.3	182.7	181.1
75°	159.6	156.1	152.6	150.6	149.9	149.2	148.5	147.8
77.5°	120.4	118.5	116.6	115.3	114.6	113.9	113.2	112.5
80°	96.9	95.9	94.8	94.0	93.3	92.6	91.9	91.2
82.5°	74.3	73.3	72.2	71.6	71.5	71.3	71.2	71.1
85°	42.6	41.9	41.2	40.9	40.9	40.9	40.9	40.9
87.5°	21.8	21.7	21.6	21.5	21.3	21.2	21.0	20.8
90°	29.9	31.0	32.0	32.8	33.3	33.8	34.3	34.9
92.5°	33.0	34.7	36.4	37.3	37.6	38.0	38.3	38.6
95°	39.6	41.4	43.2	44.1	44.1	44.1	44.1	44.1
97.5°	41.5	43.6	45.7	46.8	47.1	47.4	47.6	47.9
100°	42.5	44.5	46.6	47.8	48.0	48.3	48.5	48.8
102.5°	63.6	57.2	50.8	47.9	48.3	48.8	49.3	49.7
105°	163.0	117.3	71.6	49.1	49.6	50.1	50.6	51.1
107.5°	399.3	365.8	332.3	298.3	263.9	229.4	195.0	160.6
110°	506.9	498.4	489.9	467.2	430.3	393.3	356.4	319.5



TEST NUMBER: P332387

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	582.8	583.0	583.2	579.3	571.5	563.7	555.9	548.1
115°	672.0	674.6	677.2	679.0	680.0	681.1	682.1	683.1
117.5°	752.8	754.9	756.9	758.1	758.3	758.5	758.7	758.9
120°	805.8	807.8	809.9	810.9	810.9	810.9	810.9	810.9
122.5°	857.5	859.0	860.4	861.2	861.4	861.6	861.9	862.1
125°	930.5	931.0	931.5	932.0	932.5	933.1	933.6	934.1
127.5°	1003.6	1004.4	1005.2	1005.4	1004.9	1004.4	1003.9	1003.3
130°	1047.7	1048.7	1049.8	1050.0	1049.5	1049.0	1048.5	1048.0
132.5°	1089.5	1090.6	1091.6	1091.7	1091.0	1090.3	1089.6	1088.8
135°	1152.9	1153.7	1154.5	1154.5	1153.7	1152.9	1152.1	1151.4
137.5°	1209.4	1210.6	1211.8	1212.2	1211.7	1211.2	1210.7	1210.1
140°	1245.2	1246.2	1247.3	1247.5	1247.0	1246.5	1246.0	1245.5
142.5°	1279.2	1280.0	1280.8	1280.9	1280.2	1279.4	1278.7	1278.0
145°	1326.7	1327.2	1327.7	1327.9	1327.9	1327.9	1327.9	1327.9
147.5°	1369.2	1369.7	1370.2	1369.9	1368.7	1367.5	1366.3	1365.1
150°	1395.2	1395.7	1396.2	1396.1	1395.3	1394.6	1393.8	1393.0
152.5°	1418.3	1419.3	1420.2	1420.1	1418.9	1417.7	1416.5	1415.3
155°	1450.2	1451.5	1452.8	1452.6	1451.1	1449.6	1448.0	1446.5
157.5°	1477.9	1479.4	1481.0	1480.8	1478.8	1476.7	1474.7	1472.7
160°	1493.7	1495.2	1496.8	1496.7	1494.9	1493.1	1491.2	1489.4
162.5°	1508.1	1509.8	1511.6	1511.6	1510.0	1508.4	1506.8	1505.2
165°	1527.3	1529.3	1531.4	1531.5	1529.7	1527.9	1526.1	1524.3
167.5°	1542.1	1544.2	1546.3	1546.3	1544.2	1542.1	1540.1	1538.0
170°	1550.5	1552.6	1554.6	1554.6	1552.6	1550.5	1548.4	1546.4
172.5°	1556.1	1558.1	1560.2	1560.1	1557.8	1555.6	1553.3	1551.0
175°	1562.8	1564.6	1566.4	1566.2	1564.2	1562.1	1560.1	1558.0
177.5°	1565.2	1566.9	1568.5	1568.3	1566.3	1564.2	1562.1	1560.1
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8

(END OF REPORT)