

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332388

Luminaire Tested: **S123RDIP-S1165D1195U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332388
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D1195U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8480.8 lumens
Efficiency: N/A
Efficacy: 118.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332388

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332388

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	98	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	67	66	62	58	55	52	50	46	44	42	38
3	82	73	66	60	76	68	62	56	58	53	49	49	46	43	41	38	36	32
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	31	28
5	69	58	50	44	64	54	47	42	47	41	37	40	35	32	33	30	28	24
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	30	27	24	22
7	59	47	39	34	55	44	37	32	38	33	29	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	25	22	20	17
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20863	20863	20863
5°	20942	20653	20772
10°	20824	20394	20325
15°	20600	19917	19706
20°	20292	19321	18871
25°	19975	18650	18053
30°	19557	17877	16900
35°	19127	17102	15843
40°	18730	16190	14533
45°	18209	15289	13352
50°	17637	14267	12030
55°	17051	13097	10796
60°	16514	11845	9442
65°	15814	10488	8087
70°	14940	8806	6530
75°	13662	6929	6147
80°	12180	6137	5653
85°	10288	5434	5051



TEST NUMBER: P332388

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.0	2.1
10°-20°	506.4	6.0
20°-30°	729.2	8.6
30°-40°	821.3	9.7
40°-50°	785.8	9.3
50°-60°	643.5	7.6
60°-70°	434.1	5.1
70°-80°	218.4	2.6
80°-90°	62.2	0.7
90°-100°	96.4	1.1
100°-110°	288.4	3.4
110°-120°	490.5	5.8
120°-130°	645.2	7.6
130°-140°	725.2	8.6
140°-150°	712.8	8.4
150°-160°	600.1	7.1
160°-170°	399.5	4.7
170°-180°	139.9	1.6
0°-30°	1417.6	16.7
0°-40°	2238.9	26.4
0°-60°	3668.1	43.3
0°-90°	4382.9	51.7
90°-120°	875.3	10.3
90°-150°	2958.5	34.9
90°-180°	4098.0	48.3
0°-180°	8480.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1938	1938	1938	1938	1938	
5°	1938	1930	1911	1925	1922	184
15°	1849	1830	1787	1779	1768	521
25°	1682	1641	1570	1538	1520	773
35°	1456	1397	1302	1236	1206	911
45°	1196	1123	1004	918	877	923
55°	909	828	698	610	575	814
65°	621	532	412	338	318	614
75°	328	252	167	152	148	350
85°	83	50	44	41	41	94
90°	1	13	28	32	35	8
95°	69	77	86	90	91	77
105°	261	264	274	274	276	280
115°	494	497	495	496	495	488
125°	723	726	724	719	715	644
135°	938	944	943	939	936	722
145°	1138	1140	1143	1142	1138	710
155°	1302	1303	1304	1308	1300	599
165°	1419	1415	1415	1421	1414	400
175°	1476	1471	1471	1477	1470	140
180°	1479	1479	1479	1479	1479	



TEST NUMBER: P332388

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2
2.5°	1944.5	1943.3	1942.2	1941.1	1940.0	1937.7	1934.4	1931.0	1927.7	1924.3	1927.4
5°	1938.2	1936.4	1934.7	1932.9	1931.2	1928.2	1924.0	1919.8	1915.6	1911.4	1914.6
7.5°	1920.2	1918.4	1916.5	1914.6	1912.7	1909.0	1903.6	1898.1	1892.7	1887.2	1889.0
10°	1905.2	1902.7	1900.3	1897.8	1895.4	1891.0	1884.7	1878.4	1872.1	1865.9	1866.2
12.5°	1883.8	1881.1	1878.3	1875.6	1872.9	1867.7	1860.0	1852.3	1844.6	1836.9	1836.7
15°	1848.6	1844.7	1840.9	1837.0	1833.2	1826.4	1816.6	1806.8	1797.0	1787.3	1785.5
17.5°	1804.2	1799.8	1795.3	1790.8	1786.4	1777.9	1765.5	1753.0	1740.6	1728.2	1724.5
20°	1771.5	1766.0	1760.4	1754.8	1749.2	1739.8	1726.5	1713.2	1699.9	1686.7	1682.1
22.5°	1735.1	1728.6	1722.2	1715.8	1709.4	1699.1	1685.0	1670.9	1656.8	1642.6	1637.0
25°	1681.9	1673.2	1664.5	1655.7	1647.0	1634.6	1618.5	1602.5	1586.4	1570.3	1563.0
27.5°	1617.5	1607.9	1598.2	1588.6	1578.9	1565.2	1547.3	1529.4	1511.5	1493.6	1483.4
30°	1573.5	1563.0	1552.5	1542.0	1531.6	1516.5	1497.0	1477.4	1457.9	1438.3	1426.4
32.5°	1529.5	1517.6	1505.7	1493.8	1482.0	1465.7	1445.0	1424.3	1403.6	1383.0	1370.0
35°	1455.6	1443.0	1430.4	1417.9	1405.3	1388.2	1366.5	1344.9	1323.2	1301.5	1286.5
37.5°	1380.8	1366.8	1352.8	1338.8	1324.9	1306.3	1283.2	1260.1	1237.0	1213.8	1196.8
40°	1333.0	1317.6	1302.2	1286.9	1271.5	1251.4	1226.6	1201.8	1177.0	1152.2	1134.0
42.5°	1278.9	1263.5	1248.2	1232.8	1217.4	1196.9	1171.3	1145.6	1120.0	1094.4	1074.5
45°	1196.2	1180.5	1164.8	1149.1	1133.3	1112.0	1085.1	1058.2	1031.3	1004.4	984.5
47.5°	1113.5	1096.3	1079.0	1061.8	1044.5	1022.4	995.5	968.6	941.7	914.9	893.2
50°	1053.2	1036.8	1020.3	1003.9	987.5	965.2	936.9	908.6	880.3	852.0	830.3
52.5°	999.1	981.3	963.5	945.7	927.8	904.9	876.9	848.9	820.9	792.9	770.4
55°	908.6	891.4	874.3	857.2	840.1	816.7	787.0	757.3	727.6	697.9	677.7
57.5°	824.9	806.3	787.6	769.0	750.3	726.1	696.3	666.4	636.6	606.8	587.6
60°	767.1	747.9	728.7	709.5	690.2	666.1	637.1	608.2	579.2	550.2	531.3
62.5°	709.2	690.0	670.8	651.6	632.4	608.3	579.3	550.3	521.3	492.3	474.6
65°	620.9	601.7	582.5	563.3	544.1	520.8	493.6	466.3	439.1	411.8	394.7
67.5°	532.6	513.1	493.7	474.3	454.9	432.1	406.0	379.8	353.7	327.6	314.8
70°	474.7	455.9	437.0	418.1	399.3	377.6	353.2	328.7	304.3	279.8	267.6
72.5°	416.9	398.3	379.7	361.1	342.5	322.1	299.9	277.7	255.5	233.3	223.3
75°	328.5	311.8	295.0	278.2	261.5	243.5	224.3	205.0	185.8	166.6	163.1
77.5°	248.0	232.9	217.7	202.6	187.4	173.6	161.3	148.9	136.5	124.2	122.3
80°	196.5	182.2	167.8	153.5	139.2	128.4	121.0	113.7	106.4	99.0	98.0
82.5°	147.4	135.1	122.7	110.3	98.0	90.1	86.7	83.2	79.8	76.4	75.3
85°	83.3	75.6	67.9	60.3	52.6	48.2	47.2	46.1	45.1	44.0	43.3
87.5°	30.4	27.9	25.3	22.7	20.2	19.2	19.9	20.6	21.3	21.9	21.9
90°	1.2	3.7	6.3	8.9	11.5	14.5	17.8	21.2	24.5	27.9	28.9
92.5°	28.1	29.9	31.6	33.4	35.1	37.0	38.9	40.8	42.7	44.6	45.4
95°	68.6	70.4	72.2	74.0	75.8	77.7	79.8	81.8	83.9	86.0	87.0
97.5°	121.8	123.1	124.5	125.8	127.1	128.6	130.1	131.6	133.0	134.5	135.7
100°	158.0	159.6	161.1	162.7	164.2	165.6	166.9	168.2	169.5	170.8	171.6
102.5°	199.8	200.8	201.7	202.6	203.6	204.9	206.6	208.3	210.0	211.7	212.5
105°	261.4	261.9	262.5	263.0	263.5	264.9	267.2	269.6	271.9	274.2	274.2
107.5°	333.0	333.3	333.6	333.9	334.2	334.9	335.8	336.7	337.6	338.6	339.4
110°	377.6	378.1	378.6	379.2	379.7	380.2	380.7	381.2	381.7	382.3	383.3



TEST NUMBER: P332388

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	424.1	424.4	424.7	425.0	425.3	425.5	425.6	425.7	425.8	425.9	427.2
115°	493.8	494.6	495.3	496.1	496.9	497.0	496.5	496.0	495.5	495.0	495.2
117.5°	564.0	564.5	565.0	565.5	566.0	566.0	565.3	564.6	564.0	563.3	563.2
120°	607.7	609.2	610.8	612.3	613.9	614.0	612.7	611.4	610.1	608.8	608.6
122.5°	653.2	654.3	655.5	656.6	657.8	658.0	657.3	656.6	656.0	655.3	654.6
125°	722.7	723.5	724.2	725.0	725.8	725.9	725.4	724.9	724.4	723.9	722.8
127.5°	786.8	788.5	790.1	791.8	793.4	794.0	793.4	792.8	792.3	791.7	790.3
130°	829.6	831.6	833.7	835.8	837.8	838.5	837.7	836.9	836.2	835.4	834.4
132.5°	872.3	874.4	876.5	878.5	880.6	881.4	880.8	880.2	879.6	879.1	877.8
135°	937.6	939.2	940.7	942.3	943.8	944.5	944.2	944.0	943.7	943.4	942.4
137.5°	998.1	999.3	1000.6	1001.9	1003.2	1004.2	1004.9	1005.5	1006.2	1006.9	1005.8
140°	1039.9	1041.2	1042.5	1043.8	1045.0	1045.8	1046.1	1046.3	1046.6	1046.9	1046.6
142.5°	1078.0	1079.3	1080.6	1081.9	1083.2	1084.0	1084.5	1085.0	1085.4	1085.9	1085.6
145°	1137.5	1138.0	1138.5	1139.0	1139.5	1140.2	1141.0	1141.7	1142.5	1143.3	1143.0
147.5°	1189.5	1190.5	1191.4	1192.3	1193.3	1194.1	1194.8	1195.5	1196.2	1197.0	1197.0
150°	1225.8	1226.3	1226.8	1227.3	1227.9	1228.4	1228.9	1229.4	1229.9	1230.4	1230.4
152.5°	1255.5	1256.3	1257.0	1257.7	1258.4	1258.9	1259.2	1259.6	1259.9	1260.2	1260.6
155°	1302.5	1302.5	1302.5	1302.5	1302.5	1302.6	1302.9	1303.1	1303.4	1303.6	1304.7
157.5°	1342.4	1342.1	1341.8	1341.5	1341.2	1341.1	1341.4	1341.6	1341.8	1342.0	1343.1
160°	1367.5	1367.0	1366.5	1366.0	1365.5	1365.2	1365.2	1365.2	1365.2	1365.2	1366.5
162.5°	1389.8	1389.1	1388.4	1387.7	1387.0	1386.7	1386.9	1387.1	1387.3	1387.5	1388.8
165°	1418.7	1417.9	1417.1	1416.3	1415.6	1415.2	1415.2	1415.2	1415.2	1415.2	1416.7
167.5°	1441.7	1440.6	1439.6	1438.6	1437.5	1437.1	1437.3	1437.5	1437.7	1437.9	1439.5
170°	1454.7	1453.6	1452.6	1451.6	1450.5	1450.0	1450.0	1450.0	1450.0	1450.0	1451.8
172.5°	1464.9	1463.9	1462.8	1461.8	1460.8	1460.3	1460.3	1460.3	1460.3	1460.3	1461.9
175°	1475.6	1474.6	1473.5	1472.5	1471.5	1470.9	1470.9	1470.9	1470.9	1470.9	1472.5
177.5°	1480.0	1479.2	1478.4	1477.5	1476.7	1476.3	1476.3	1476.3	1476.3	1476.3	1477.5
180°	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1



TEST NUMBER: P332388

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2
2.5°	1930.5	1933.6	1936.6	1937.9	1937.3	1936.8	1936.2	1935.6
5°	1917.7	1920.9	1924.0	1925.2	1924.5	1923.8	1923.1	1922.4
7.5°	1890.7	1892.5	1894.2	1894.5	1893.3	1892.1	1890.9	1889.7
10°	1866.6	1866.9	1867.3	1866.6	1864.8	1863.1	1861.3	1859.6
12.5°	1836.5	1836.3	1836.1	1835.0	1833.0	1830.9	1828.9	1826.9
15°	1783.8	1782.0	1780.3	1778.2	1775.7	1773.3	1770.8	1768.4
17.5°	1720.8	1717.0	1713.3	1709.7	1706.0	1702.4	1698.8	1695.1
20°	1677.6	1673.0	1668.5	1664.1	1659.9	1655.7	1651.6	1647.4
22.5°	1631.3	1625.7	1620.0	1615.2	1611.3	1607.4	1603.5	1599.6
25°	1555.7	1548.3	1541.0	1535.4	1531.6	1527.7	1523.9	1520.0
27.5°	1473.2	1463.0	1452.8	1444.8	1438.9	1433.1	1427.2	1421.3
30°	1414.5	1402.7	1390.8	1382.1	1376.5	1370.9	1365.3	1359.7
32.5°	1357.0	1344.0	1331.0	1321.6	1315.7	1309.8	1304.0	1298.1
35°	1271.5	1256.5	1241.5	1230.8	1224.5	1218.2	1211.9	1205.7
37.5°	1179.7	1162.7	1145.6	1133.2	1125.5	1117.7	1110.0	1102.2
40°	1115.9	1097.7	1079.6	1066.5	1058.4	1050.4	1042.4	1034.3
42.5°	1054.7	1034.8	1015.0	1001.5	994.3	987.1	979.9	972.7
45°	964.6	944.7	924.8	910.7	902.3	893.9	885.5	877.1
47.5°	871.5	849.9	828.2	813.7	806.2	798.7	791.2	783.8
50°	808.7	787.0	765.3	750.5	742.5	734.4	726.4	718.4
52.5°	747.9	725.4	702.9	688.0	680.8	673.7	666.5	659.3
55°	657.4	637.1	616.9	603.3	596.3	589.3	582.3	575.3
57.5°	568.5	549.3	530.2	517.6	511.7	505.8	499.8	493.9
60°	512.4	493.6	474.7	462.3	456.4	450.4	444.5	438.6
62.5°	456.8	439.1	421.3	409.4	403.1	396.9	390.7	384.5
65°	377.6	360.5	343.4	332.9	329.1	325.2	321.4	317.5
67.5°	302.0	289.2	276.4	268.0	263.9	259.7	255.6	251.5
70°	255.3	243.1	230.9	222.9	219.0	215.2	211.3	207.5
72.5°	213.3	203.3	193.3	187.5	185.9	184.3	182.7	181.1
75°	159.6	156.1	152.6	150.6	149.9	149.2	148.5	147.8
77.5°	120.4	118.5	116.6	115.3	114.6	113.9	113.2	112.5
80°	96.9	95.9	94.8	94.0	93.3	92.6	91.9	91.2
82.5°	74.3	73.3	72.2	71.6	71.5	71.3	71.2	71.1
85°	42.6	41.9	41.2	40.9	40.9	40.9	40.9	40.9
87.5°	21.8	21.7	21.6	21.5	21.3	21.2	21.0	20.8
90°	30.0	31.0	32.0	32.8	33.3	33.8	34.3	34.9
92.5°	46.3	47.1	47.9	48.2	47.9	47.6	47.2	46.9
95°	88.0	89.1	90.1	90.6	90.6	90.6	90.6	90.6
97.5°	136.9	138.1	139.3	139.8	139.7	139.6	139.5	139.4
100°	172.3	173.1	173.9	174.5	175.1	175.6	176.1	176.6
102.5°	213.2	214.0	214.8	215.1	215.0	214.9	214.8	214.7
105°	274.2	274.2	274.2	274.5	275.0	275.5	276.0	276.5
107.5°	340.2	341.1	341.9	342.1	341.8	341.5	341.2	340.9
110°	384.3	385.4	386.4	386.6	386.1	385.6	385.1	384.6



TEST NUMBER: P332388

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	428.4	429.7	430.9	431.5	431.4	431.3	431.2	431.1
115°	495.5	495.7	496.0	496.0	495.7	495.5	495.2	495.0
117.5°	563.2	563.1	563.1	562.7	562.0	561.2	560.5	559.8
120°	608.3	608.1	607.8	607.4	606.9	606.4	605.9	605.3
122.5°	654.0	653.3	652.6	651.9	651.2	650.5	649.7	649.0
125°	721.8	720.8	719.7	718.7	717.7	716.6	715.6	714.6
127.5°	788.8	787.4	785.9	784.6	783.4	782.2	781.0	779.9
130°	833.3	832.3	831.3	829.8	828.0	826.2	824.4	822.6
132.5°	876.6	875.4	874.1	872.8	871.4	870.0	868.6	867.2
135°	941.4	940.3	939.3	938.5	938.0	937.5	937.0	936.5
137.5°	1004.7	1003.6	1002.5	1001.5	1000.5	999.6	998.6	997.6
140°	1046.3	1046.1	1045.8	1044.8	1043.0	1041.2	1039.4	1037.6
142.5°	1085.4	1085.1	1084.9	1084.0	1082.6	1081.2	1079.9	1078.5
145°	1142.8	1142.5	1142.3	1141.6	1140.6	1139.5	1138.5	1137.5
147.5°	1197.0	1197.0	1197.0	1196.2	1194.6	1193.1	1191.5	1190.0
150°	1230.4	1230.4	1230.4	1229.7	1228.1	1226.6	1225.0	1223.5
152.5°	1261.0	1261.4	1261.8	1261.4	1260.0	1258.7	1257.3	1256.0
155°	1305.7	1306.7	1307.8	1307.4	1305.6	1303.8	1302.0	1300.1
157.5°	1344.1	1345.2	1346.3	1346.1	1344.7	1343.2	1341.8	1340.3
160°	1367.8	1369.1	1370.4	1370.5	1369.5	1368.4	1367.4	1366.4
162.5°	1390.1	1391.4	1392.7	1392.5	1390.8	1389.2	1387.5	1385.9
165°	1418.3	1419.8	1421.4	1421.2	1419.4	1417.6	1415.8	1414.0
167.5°	1441.1	1442.7	1444.3	1444.3	1442.7	1441.1	1439.5	1437.9
170°	1453.6	1455.5	1457.3	1457.3	1455.5	1453.6	1451.8	1450.0
172.5°	1463.5	1465.1	1466.7	1466.6	1464.7	1462.9	1461.1	1459.3
175°	1474.0	1475.6	1477.1	1477.0	1475.2	1473.4	1471.6	1469.8
177.5°	1478.8	1480.0	1481.2	1481.1	1479.7	1478.2	1476.8	1475.4
180°	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1

(END OF REPORT)