

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332389

Luminaire Tested: **S123RDIP-S1165D1195U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332389  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1165D1195U835-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8701.1 lumens  
Efficiency: N/A  
Efficacy: 121.4 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332389

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332389

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	56	56	56	50
1	98	94	90	87	91	87	84	81	74	71	69	62	60	58	50	49	48	43
2	90	82	76	71	83	76	71	67	65	61	58	54	52	49	45	43	41	37
3	82	73	66	60	75	67	61	56	58	53	49	48	45	42	40	37	35	31
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31	27
5	69	58	50	44	64	54	47	41	46	41	36	39	35	32	32	29	27	24
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	30	26	24	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	24	21	19
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19	17
9	51	39	32	27	47	36	30	25	32	26	23	27	23	20	23	20	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	20863	20863	20863
5°	20942	20653	20772
10°	20824	20394	20325
15°	20600	19917	19706
20°	20292	19321	18871
25°	19975	18650	18053
30°	19557	17877	16900
35°	19127	17102	15843
40°	18730	16190	14533
45°	18209	15289	13352
50°	17637	14267	12030
55°	17051	13097	10796
60°	16514	11845	9442
65°	15814	10488	8087
70°	14940	8806	6530
75°	13662	6929	6147
80°	12180	6137	5653
85°	10288	5434	5051



TEST NUMBER: P332389

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	182.0	2.1
10°-20°	506.4	5.8
20°-30°	729.2	8.4
30°-40°	821.3	9.4
40°-50°	785.8	9.0
50°-60°	643.5	7.4
60°-70°	434.1	5.0
70°-80°	218.4	2.5
80°-90°	62.2	0.7
90°-100°	319.4	3.7
100°-110°	904.4	10.4
110°-120°	889.7	10.2
120°-130°	709.7	8.2
130°-140°	559.5	6.4
140°-150°	417.6	4.8
150°-160°	291.1	3.3
160°-170°	171.0	2.0
170°-180°	55.6	0.6
0°-30°	1417.6	16.3
0°-40°	2238.9	25.7
0°-60°	3668.1	42.2
0°-90°	4382.9	50.4
90°-120°	2113.6	24.3
90°-150°	3800.4	43.7
90°-180°	4318.0	49.6
0°-180°	8701.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1938	1938	1938	1938	1938	
5°	1938	1930	1911	1925	1922	184
15°	1849	1830	1787	1779	1768	521
25°	1682	1641	1570	1538	1520	773
35°	1456	1397	1302	1236	1206	911
45°	1196	1123	1004	918	877	923
55°	909	828	698	610	575	814
65°	621	532	412	338	318	614
75°	328	252	167	152	148	350
85°	83	50	44	41	41	94
90°	2	14	29	33	34	7
95°	40	128	689	201	135	43
105°	135	199	934	1634	1478	143
115°	238	297	714	1567	1797	236
125°	331	391	667	1208	1418	294
135°	388	463	658	995	1149	300
145°	443	507	650	816	898	277
155°	503	543	629	715	745	231
165°	550	565	602	638	650	155
175°	573	573	577	586	584	54
180°	574	574	574	574	574	



TEST NUMBER: P332389

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2
2.5°	1944.5	1943.3	1942.2	1941.1	1940.0	1937.7	1934.4	1931.0	1927.7	1924.3	1927.4
5°	1938.2	1936.4	1934.7	1932.9	1931.2	1928.2	1924.0	1919.8	1915.6	1911.4	1914.6
7.5°	1920.2	1918.4	1916.5	1914.6	1912.7	1909.0	1903.6	1898.1	1892.7	1887.2	1889.0
10°	1905.2	1902.7	1900.3	1897.8	1895.4	1891.0	1884.7	1878.4	1872.1	1865.9	1866.2
12.5°	1883.8	1881.1	1878.3	1875.6	1872.9	1867.7	1860.0	1852.3	1844.6	1836.9	1836.7
15°	1848.6	1844.7	1840.9	1837.0	1833.2	1826.4	1816.6	1806.8	1797.0	1787.3	1785.5
17.5°	1804.2	1799.8	1795.3	1790.8	1786.4	1777.9	1765.5	1753.0	1740.6	1728.2	1724.5
20°	1771.5	1766.0	1760.4	1754.8	1749.2	1739.8	1726.5	1713.2	1699.9	1686.7	1682.1
22.5°	1735.1	1728.6	1722.2	1715.8	1709.4	1699.1	1685.0	1670.9	1656.8	1642.6	1637.0
25°	1681.9	1673.2	1664.5	1655.7	1647.0	1634.6	1618.5	1602.5	1586.4	1570.3	1563.0
27.5°	1617.5	1607.9	1598.2	1588.6	1578.9	1565.2	1547.3	1529.4	1511.5	1493.6	1483.4
30°	1573.5	1563.0	1552.5	1542.0	1531.6	1516.5	1497.0	1477.4	1457.9	1438.3	1426.4
32.5°	1529.5	1517.6	1505.7	1493.8	1482.0	1465.7	1445.0	1424.3	1403.6	1383.0	1370.0
35°	1455.6	1443.0	1430.4	1417.9	1405.3	1388.2	1366.5	1344.9	1323.2	1301.5	1286.5
37.5°	1380.8	1366.8	1352.8	1338.8	1324.9	1306.3	1283.2	1260.1	1237.0	1213.8	1196.8
40°	1333.0	1317.6	1302.2	1286.9	1271.5	1251.4	1226.6	1201.8	1177.0	1152.2	1134.0
42.5°	1278.9	1263.5	1248.2	1232.8	1217.4	1196.9	1171.3	1145.6	1120.0	1094.4	1074.5
45°	1196.2	1180.5	1164.8	1149.1	1133.3	1112.0	1085.1	1058.2	1031.3	1004.4	984.5
47.5°	1113.5	1096.3	1079.0	1061.8	1044.5	1022.4	995.5	968.6	941.7	914.9	893.2
50°	1053.2	1036.8	1020.3	1003.9	987.5	965.2	936.9	908.6	880.3	852.0	830.3
52.5°	999.1	981.3	963.5	945.7	927.8	904.9	876.9	848.9	820.9	792.9	770.4
55°	908.6	891.4	874.3	857.2	840.1	816.7	787.0	757.3	727.6	697.9	677.7
57.5°	824.9	806.3	787.6	769.0	750.3	726.1	696.3	666.4	636.6	606.8	587.6
60°	767.1	747.9	728.7	709.5	690.2	666.1	637.1	608.2	579.2	550.2	531.3
62.5°	709.2	690.0	670.8	651.6	632.4	608.3	579.3	550.3	521.3	492.3	474.6
65°	620.9	601.7	582.5	563.3	544.1	520.8	493.6	466.3	439.1	411.8	394.7
67.5°	532.6	513.1	493.7	474.3	454.9	432.1	406.0	379.8	353.7	327.6	314.8
70°	474.7	455.9	437.0	418.1	399.3	377.6	353.2	328.7	304.3	279.8	267.6
72.5°	416.9	398.3	379.7	361.1	342.5	322.1	299.9	277.7	255.5	233.3	223.3
75°	328.5	311.8	295.0	278.2	261.5	243.5	224.3	205.0	185.8	166.6	163.1
77.5°	248.0	232.9	217.7	202.6	187.4	173.6	161.3	148.9	136.5	124.2	122.3
80°	196.5	182.2	167.8	153.5	139.2	128.4	121.0	113.7	106.4	99.0	98.0
82.5°	147.4	135.1	122.7	110.3	98.0	90.1	86.7	83.2	79.8	76.4	75.3
85°	83.3	75.6	67.9	60.3	52.6	48.2	47.2	46.1	45.1	44.0	43.3
87.5°	30.6	28.0	25.4	23.1	20.4	19.4	20.1	20.8	21.5	22.2	21.6
90°	2.3	4.6	7.0	10.5	12.8	15.1	18.6	22.1	25.6	29.0	27.9
92.5°	14.4	21.4	31.1	40.2	50.0	67.2	97.6	147.6	196.6	178.7	134.8
95°	39.5	43.0	55.8	75.5	105.7	151.0	249.8	422.9	613.5	689.0	558.8
97.5°	67.4	68.5	78.5	95.7	125.5	174.5	268.9	464.0	781.7	1067.7	1142.3
100°	86.0	87.1	95.3	111.5	139.4	184.7	266.1	438.0	743.6	1100.3	1329.2
102.5°	105.5	107.6	114.8	130.1	155.2	196.8	269.8	415.7	687.8	1039.9	1338.4
105°	134.8	138.3	145.2	159.2	181.2	217.3	280.0	399.7	619.3	934.1	1267.6
107.5°	165.9	169.4	176.1	189.8	210.5	244.0	299.1	398.5	575.6	840.7	1143.5
110°	188.2	191.7	197.5	210.3	230.0	262.6	314.9	403.2	558.8	787.7	1065.4



TEST NUMBER: P332389

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	208.7	212.2	218.0	230.7	250.5	282.1	330.7	412.5	549.6	752.4	997.6
115°	238.2	242.8	249.8	261.4	281.2	312.5	356.7	427.6	546.1	714.5	915.5
117.5°	267.7	273.0	278.8	289.5	311.6	340.7	384.3	447.5	548.2	692.2	866.0
120°	288.1	291.6	297.4	309.1	331.1	360.2	402.0	462.4	551.9	682.0	840.0
122.5°	305.8	309.3	315.1	327.6	348.8	379.7	420.6	476.4	558.4	675.5	818.6
125°	331.1	333.5	340.4	353.2	375.3	406.6	447.3	498.4	568.1	666.9	791.2
127.5°	350.4	353.9	362.5	375.5	399.9	431.3	470.5	516.6	579.3	662.7	767.1
130°	362.5	366.0	376.4	390.4	414.8	446.1	484.5	528.6	586.7	659.9	754.0
132.5°	371.8	376.2	387.6	404.3	428.7	459.2	496.6	539.8	592.3	659.0	742.0
135°	388.1	392.7	405.5	422.9	447.3	478.7	514.7	554.2	600.7	657.6	726.2
137.5°	403.4	408.3	420.8	439.4	463.6	492.6	527.2	564.9	606.3	655.0	712.4
140°	413.6	419.4	431.0	449.6	472.9	501.9	535.6	570.5	610.0	654.1	704.1
142.5°	424.8	429.7	442.2	458.9	482.2	509.4	542.1	576.0	612.8	652.3	696.6
145°	442.7	446.1	456.6	474.0	493.8	520.5	550.7	582.1	614.6	649.5	686.7
147.5°	460.8	462.9	473.1	488.2	507.3	530.0	557.7	585.8	614.6	645.1	676.9
150°	472.9	474.0	483.3	498.4	514.7	535.6	562.3	586.7	614.6	641.3	670.4
152.5°	485.0	485.2	494.5	507.7	522.1	542.1	565.1	588.6	611.8	636.7	663.0
155°	503.1	503.1	510.1	521.7	534.4	550.7	570.5	589.1	608.8	628.6	651.8
157.5°	517.5	518.4	524.0	534.2	545.1	557.7	573.5	590.2	604.9	621.4	639.2
160°	528.6	528.6	533.3	542.6	550.7	562.3	576.3	590.2	603.0	615.8	630.9
162.5°	537.0	537.0	540.7	548.2	555.4	565.1	577.2	589.3	599.3	610.2	622.5
165°	549.6	548.4	550.7	556.5	561.2	569.3	578.6	586.7	593.7	601.8	611.1
167.5°	559.1	557.7	558.8	563.3	566.5	571.6	578.4	584.9	588.1	593.5	600.2
170°	564.7	562.3	563.5	567.0	569.3	571.6	577.4	582.1	584.4	587.9	593.7
172.5°	568.4	567.0	567.2	569.8	571.2	572.6	577.4	581.2	581.6	583.2	587.2
175°	572.8	571.6	570.5	572.8	572.8	574.0	576.3	578.6	577.4	577.4	579.8
177.5°	574.9	574.0	573.0	574.0	574.0	574.0	574.9	576.7	574.9	574.0	574.9
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0



TEST NUMBER: P332389

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2
2.5°	1930.5	1933.6	1936.6	1937.9	1937.3	1936.8	1936.2	1935.6
5°	1917.7	1920.9	1924.0	1925.2	1924.5	1923.8	1923.1	1922.4
7.5°	1890.7	1892.5	1894.2	1894.5	1893.3	1892.1	1890.9	1889.7
10°	1866.6	1866.9	1867.3	1866.6	1864.8	1863.1	1861.3	1859.6
12.5°	1836.5	1836.3	1836.1	1835.0	1833.0	1830.9	1828.9	1826.9
15°	1783.8	1782.0	1780.3	1778.2	1775.7	1773.3	1770.8	1768.4
17.5°	1720.8	1717.0	1713.3	1709.7	1706.0	1702.4	1698.8	1695.1
20°	1677.6	1673.0	1668.5	1664.1	1659.9	1655.7	1651.6	1647.4
22.5°	1631.3	1625.7	1620.0	1615.2	1611.3	1607.4	1603.5	1599.6
25°	1555.7	1548.3	1541.0	1535.4	1531.6	1527.7	1523.9	1520.0
27.5°	1473.2	1463.0	1452.8	1444.8	1438.9	1433.1	1427.2	1421.3
30°	1414.5	1402.7	1390.8	1382.1	1376.5	1370.9	1365.3	1359.7
32.5°	1357.0	1344.0	1331.0	1321.6	1315.7	1309.8	1304.0	1298.1
35°	1271.5	1256.5	1241.5	1230.8	1224.5	1218.2	1211.9	1205.7
37.5°	1179.7	1162.7	1145.6	1133.2	1125.5	1117.7	1110.0	1102.2
40°	1115.9	1097.7	1079.6	1066.5	1058.4	1050.4	1042.4	1034.3
42.5°	1054.7	1034.8	1015.0	1001.5	994.3	987.1	979.9	972.7
45°	964.6	944.7	924.8	910.7	902.3	893.9	885.5	877.1
47.5°	871.5	849.9	828.2	813.7	806.2	798.7	791.2	783.8
50°	808.7	787.0	765.3	750.5	742.5	734.4	726.4	718.4
52.5°	747.9	725.4	702.9	688.0	680.8	673.7	666.5	659.3
55°	657.4	637.1	616.9	603.3	596.3	589.3	582.3	575.3
57.5°	568.5	549.3	530.2	517.6	511.7	505.8	499.8	493.9
60°	512.4	493.6	474.7	462.3	456.4	450.4	444.5	438.6
62.5°	456.8	439.1	421.3	409.4	403.1	396.9	390.7	384.5
65°	377.6	360.5	343.4	332.9	329.1	325.2	321.4	317.5
67.5°	302.0	289.2	276.4	268.0	263.9	259.7	255.6	251.5
70°	255.3	243.1	230.9	222.9	219.0	215.2	211.3	207.5
72.5°	213.3	203.3	193.3	187.5	185.9	184.3	182.7	181.1
75°	159.6	156.1	152.6	150.6	149.9	149.2	148.5	147.8
77.5°	120.4	118.5	116.6	115.3	114.6	113.9	113.2	112.5
80°	96.9	95.9	94.8	94.0	93.3	92.6	91.9	91.2
82.5°	74.3	73.3	72.2	71.6	71.5	71.3	71.2	71.1
85°	42.6	41.9	41.2	40.9	40.9	40.9	40.9	40.9
87.5°	21.6	21.6	21.5	21.7	21.2	21.1	21.1	20.6
90°	29.0	30.2	31.4	33.7	32.5	33.7	34.9	33.7
92.5°	97.8	77.6	68.5	62.5	60.4	56.9	58.1	56.0
95°	418.3	283.5	221.9	180.1	158.0	147.6	139.4	134.8
97.5°	1042.6	835.1	685.3	546.3	460.6	408.3	376.9	366.9
100°	1369.8	1275.7	1139.8	974.8	857.4	772.6	727.3	728.5
102.5°	1478.6	1475.5	1396.3	1291.7	1200.4	1133.3	1095.4	1068.7
105°	1510.4	1626.6	1648.7	1618.5	1565.0	1520.9	1483.7	1477.9
107.5°	1418.8	1607.5	1709.3	1750.7	1751.6	1736.7	1724.2	1713.5
110°	1331.5	1545.3	1691.7	1773.0	1805.5	1814.8	1812.5	1810.2





TEST NUMBER: P332389

CATALOG NUMBER: S123RDIP-S1165D1195U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1245.0	1463.5	1627.5	1732.1	1791.6	1820.4	1829.2	1829.7
115°	1130.5	1332.6	1503.4	1630.1	1717.2	1768.3	1791.6	1797.4
117.5°	1047.5	1222.0	1375.4	1503.9	1594.8	1653.3	1686.8	1694.7
120°	1003.8	1160.7	1300.1	1417.5	1509.2	1574.3	1602.2	1609.2
122.5°	969.4	1111.4	1240.6	1349.6	1431.2	1489.7	1520.4	1529.2
125°	923.7	1050.3	1161.8	1254.8	1329.2	1380.3	1409.3	1417.5
127.5°	883.7	996.6	1097.2	1181.8	1248.1	1291.7	1318.0	1325.4
130°	858.6	963.2	1057.3	1136.3	1197.9	1239.7	1264.1	1273.4
132.5°	835.4	931.6	1019.2	1094.5	1152.3	1194.1	1215.8	1222.3
135°	804.0	886.5	962.0	1028.2	1085.2	1120.0	1140.9	1149.1
137.5°	775.4	843.0	908.1	965.5	1013.4	1048.7	1066.3	1071.7
140°	758.7	817.9	873.7	923.7	967.8	1000.4	1018.9	1017.8
142.5°	742.9	793.8	842.1	885.6	923.2	952.0	968.7	967.6
145°	723.8	762.2	799.4	833.0	862.1	886.5	895.8	898.1
147.5°	708.3	738.7	768.7	792.6	814.7	831.2	840.0	840.9
150°	697.1	723.8	748.2	770.3	787.7	800.5	807.5	807.5
152.5°	686.9	709.9	731.5	749.9	763.6	775.4	779.6	779.6
155°	671.5	690.1	707.6	721.5	732.0	741.3	743.6	744.7
157.5°	655.3	670.9	684.3	695.2	704.3	711.3	713.1	712.9
160°	646.0	658.8	670.4	678.5	686.7	693.6	693.6	692.5
162.5°	634.8	645.8	656.4	663.6	669.0	675.0	675.0	673.9
165°	620.4	627.4	635.5	641.3	646.0	650.6	649.5	649.5
167.5°	607.9	613.2	617.9	622.1	624.1	627.4	626.2	626.2
170°	599.5	603.0	607.6	610.0	611.1	613.5	612.3	612.3
172.5°	592.1	594.6	598.4	599.7	600.0	602.3	600.2	599.3
175°	582.1	583.2	585.6	585.6	585.6	586.7	585.6	584.4
177.5°	575.8	576.7	577.7	577.7	576.7	577.7	575.8	575.8
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0

(END OF REPORT)