

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831874

Luminaire Tested: S123RDIP-S1000D805U830-4F0-1E-UDD-G1

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831874
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D805U830-4F0-1E-UDD-G1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6656.5 lumens
Efficiency: N/A
Efficacy: 119.5 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 55.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831874

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-G1

Luminous Intensity Polar Plot





TEST NUMBER: P831874

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-G1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	66	66	66	61	
1	101	97	94	90	95	91	88	85	80	78	75	70	68	66	60	59	58	58	58	58	53	
2	93	86	80	76	87	81	76	72	71	67	64	62	60	57	54	52	50	50	50	50	46	
3	86	77	70	64	80	72	66	61	64	59	55	56	53	50	49	46	44	44	44	44	41	
4	79	69	61	56	74	65	58	53	58	52	48	51	47	44	45	42	39	39	39	39	36	
5	73	62	54	49	68	59	52	47	52	47	43	46	42	39	41	38	35	35	35	35	32	
6	68	56	49	43	63	53	46	41	48	42	38	42	38	35	38	34	31	31	31	31	29	
7	63	51	44	38	59	49	42	37	44	38	34	39	35	31	35	31	29	29	29	29	26	
8	59	47	40	35	55	45	38	33	40	35	31	36	32	28	32	29	26	26	26	26	24	
9	55	43	36	31	52	41	35	30	37	32	28	34	29	26	30	27	24	24	24	24	22	
10	52	40	33	29	49	38	32	28	35	30	26	31	27	24	28	25	22	22	22	22	20	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	32923	32923	32923	32923	32923
5°	39092	37845	33129	26781	24863
10°	35417	38440	32964	21458	18408
15°	24386	32958	32616	17538	14561
20°	16964	25374	31961	14788	12798
25°	12928	19340	31009	13144	11796
30°	11253	15462	29817	12204	10926
35°	10332	13043	28128	11411	10134
40°	9427	11647	25920	10634	9409
45°	8514	10651	23537	9898	8686
50°	7728	9828	20726	9177	7790
55°	6989	9025	18027	8471	6683
60°	6262	8206	15657	7694	6316
65°	5782	7282	13479	6915	5973
70°	4696	6294	11761	6257	4853
75°	4121	5007	9960	5190	4275
80°	3732	4234	8164	4351	4042
85°	3409	3717	6200	3952	3717

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 24835 cd/sqm



TEST NUMBER: P831874

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-G1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	278.8	4.2
10°-20°	645.1	9.7
20°-30°	740.2	11.1
30°-40°	729.6	11.0
40°-50°	643.4	9.7
50°-60°	495.0	7.4
60°-70°	325.4	4.9
70°-80°	158.0	2.4
80°-90°	41.8	0.6
90°-100°	60.4	0.9
100°-110°	182.8	2.7
110°-120°	311.2	4.7
120°-130°	409.3	6.1
130°-140°	460.1	6.9
140°-150°	452.4	6.8
150°-160°	380.8	5.7
160°-170°	253.5	3.8
170°-180°	88.8	1.3
0°-30°	1664.0	25.0
0°-40°	2393.6	36.0
0°-60°	3531.9	53.1
0°-90°	4057.2	61.0
90°-120°	554.3	8.3
90°-150°	1876.1	28.2
90°-180°	2599.0	39.0
0°-180°	6656.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	3059	3059	3059	3059	3059	
5°	3618	3502	3066	2479	2301	331
15°	2188	2958	2927	1574	1307	618
25°	1088	1628	2611	1107	993	514
35°	786	993	2141	868	771	490
45°	559	700	1546	650	571	434
55°	372	481	961	451	356	334
65°	227	286	529	272	234	222
75°	99	120	240	125	103	107
85°	28	30	50	32	30	29
90°	22	18	1	18	22	12
95°	58	54	44	54	58	58
105°	175	174	166	174	175	186
115°	314	314	313	314	314	311
125°	453	459	458	459	453	405
135°	594	598	595	598	594	457
145°	721	725	721	725	721	451
155°	825	827	826	827	825	380
165°	897	898	900	898	897	253
175°	932	933	936	933	932	89
180°	938	938	938	938	938	



TEST NUMBER: P831874

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3058.6	3058.6	3058.6	3058.6	3058.6	3058.6	3058.6	3058.6	3058.6	3058.6	3058.6
2.5°	3389.6	3379.0	3368.3	3365.2	3362.0	3352.0	3342.0	3319.4	3296.8	3273.6	3250.4
5°	3617.9	3619.1	3620.4	3617.2	3614.1	3600.9	3587.8	3560.2	3532.6	3502.5	3472.4
7.5°	3547.6	3567.7	3587.8	3591.5	3595.3	3605.3	3615.4	3609.1	3602.8	3591.5	3580.2
10°	3240.4	3239.1	3237.9	3260.5	3283.0	3350.1	3417.2	3451.7	3486.2	3516.9	3547.6
12.5°	2738.8	2740.7	2742.6	2816.5	2890.5	2953.9	3017.2	3105.0	3192.7	3287.4	3382.1
15°	2188.3	2219.0	2249.7	2315.6	2381.4	2476.7	2572.0	2689.9	2807.8	2957.6	3107.5
17.5°	1797.0	1810.2	1823.4	1886.7	1950.0	2040.3	2130.6	2264.1	2397.7	2590.8	2783.9
20°	1481.0	1492.9	1504.8	1550.6	1596.4	1682.9	1769.4	1896.7	2024.0	2215.2	2406.5
22.5°	1236.5	1259.7	1282.9	1313.6	1344.3	1407.0	1469.7	1599.5	1729.3	1903.6	2077.9
25°	1088.5	1099.2	1109.8	1136.1	1162.5	1222.7	1282.9	1368.8	1454.7	1628.4	1802.0
27.5°	988.2	991.3	994.4	1013.9	1033.3	1072.2	1111.1	1190.7	1270.3	1413.3	1556.2
30°	905.4	911.0	916.7	931.7	946.8	975.0	1003.2	1059.7	1116.1	1244.0	1371.9
32.5°	841.5	844.6	847.7	860.3	872.8	893.5	914.2	958.7	1003.2	1101.0	1198.8
35°	786.3	786.9	787.5	796.9	806.3	826.4	846.5	883.5	920.5	992.6	1064.7
37.5°	723.6	728.0	732.4	739.2	746.1	763.7	781.3	811.4	841.5	901.0	960.6
40°	670.9	674.7	678.4	686.6	694.7	708.5	722.3	749.9	777.5	828.9	880.3
42.5°	618.2	620.7	623.3	631.4	639.6	656.5	673.4	695.4	717.3	759.9	802.6
45°	559.3	565.6	571.8	580.6	589.4	603.8	618.2	640.8	663.4	699.7	736.1
47.5°	510.4	513.5	516.7	524.2	531.7	549.3	566.8	586.9	606.9	640.8	674.7
50°	461.5	462.7	464.0	470.9	477.8	493.5	509.1	532.3	555.5	586.9	618.2
52.5°	415.1	418.2	421.4	428.2	435.1	445.8	456.5	480.3	504.1	534.8	565.6
55°	372.4	374.3	376.2	381.2	386.2	398.8	411.3	432.0	452.7	480.9	509.1
57.5°	332.3	334.8	337.3	341.1	344.9	356.1	367.4	385.6	403.8	432.0	460.2
60°	290.9	294.1	297.2	301.6	306.0	314.8	323.5	339.8	356.1	381.2	406.3
62.5°	260.8	261.5	262.1	265.9	269.6	275.9	282.2	295.3	308.5	333.6	358.7
65°	227.0	228.9	230.7	232.6	234.5	239.5	244.5	255.8	267.1	285.9	304.7
67.5°	191.9	193.7	195.6	198.8	201.9	206.3	210.7	218.2	225.7	243.3	260.8
70°	149.2	149.2	149.2	154.2	159.3	166.8	174.3	180.0	185.6	200.0	214.4
72.5°	121.6	122.3	122.9	123.5	124.1	128.5	132.9	142.3	151.7	160.5	169.3
75°	99.1	99.7	100.3	100.9	101.6	102.8	104.1	107.2	110.4	120.4	130.4
77.5°	79.0	79.6	80.3	80.9	81.5	82.8	84.0	85.3	86.5	90.3	94.1
80°	60.2	60.8	61.4	62.1	62.7	63.3	64.0	65.2	66.5	68.3	70.2
82.5°	43.9	43.9	43.9	43.9	43.9	45.1	46.4	46.4	46.4	47.7	48.9
85°	27.6	27.6	27.6	28.2	28.8	28.8	28.8	29.5	30.1	30.1	30.1
87.5°	12.5	11.9	11.3	11.9	12.5	12.5	12.5	13.2	13.8	13.8	13.8
90°	22.1	21.8	21.5	21.1	20.8	20.3	19.7	19.0	18.3	17.7	15.6
92.5°	31.7	32.0	32.3	32.7	33.0	32.9	32.4	31.9	31.4	31.0	30.0
95°	57.5	57.5	57.5	57.5	57.5	57.2	56.5	55.8	55.2	54.5	53.2
97.5°	82.5	82.7	82.9	83.0	83.2	82.9	82.0	81.2	80.4	79.6	78.6
100°	112.0	111.7	111.4	111.0	110.7	110.3	109.8	109.3	108.8	108.3	107.5
102.5°	142.2	142.4	142.6	142.7	142.9	142.7	142.2	141.7	141.2	140.8	139.6
105°	175.4	175.1	174.7	174.4	174.1	173.9	173.9	173.9	173.9	173.9	172.4
107.5°	209.3	209.4	209.6	209.8	209.9	209.8	209.3	208.8	208.3	207.8	207.2
110°	243.9	244.2	244.6	244.9	245.2	245.1	244.4	243.8	243.1	242.4	242.1



TEST NUMBER: P831874

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	280.8	280.8	280.8	280.8	280.8	280.4	279.5	278.7	277.9	277.1	277.1
115°	313.9	314.1	314.3	314.4	314.6	314.6	314.4	314.3	314.1	313.9	314.3
117.5°	347.8	348.3	348.8	349.3	349.8	350.0	350.0	350.0	350.0	350.0	350.4
120°	383.9	384.3	384.6	384.9	385.2	385.5	385.7	385.8	386.0	386.1	387.0
122.5°	418.6	419.1	419.6	420.0	420.5	421.0	421.5	422.0	422.5	423.0	423.3
125°	453.2	453.9	454.5	455.2	455.8	456.5	457.1	457.8	458.4	459.1	459.4
127.5°	487.8	488.5	489.2	489.8	490.5	491.3	492.3	493.2	494.2	495.2	495.5
130°	521.7	522.9	524.0	525.2	526.3	527.2	527.9	528.5	529.2	529.8	530.3
132.5°	557.1	557.9	558.7	559.6	560.4	561.2	562.0	562.8	563.7	564.5	564.8
135°	594.0	594.3	594.6	594.9	595.3	595.8	596.4	597.1	597.7	598.4	598.5
137.5°	626.4	626.9	627.4	627.9	628.3	629.0	629.8	630.6	631.5	632.3	631.8
140°	658.1	659.2	660.4	661.5	662.7	663.3	663.5	663.6	663.8	664.0	663.8
142.5°	690.5	691.3	692.1	693.0	693.8	694.3	694.4	694.6	694.8	694.9	694.6
145°	721.4	722.1	722.8	723.4	724.1	724.5	724.6	724.8	725.0	725.1	724.6
147.5°	749.4	750.4	751.4	752.4	753.4	753.9	753.9	753.9	753.9	753.9	753.4
150°	776.0	777.0	777.9	778.9	779.9	780.4	780.4	780.4	780.4	780.4	780.1
152.5°	801.8	802.6	803.4	804.2	805.0	805.3	805.0	804.6	804.3	804.0	803.8
155°	824.6	825.8	826.9	828.1	829.2	829.4	828.8	828.1	827.5	826.8	826.7
157.5°	846.0	847.0	847.9	848.9	849.9	850.1	849.4	848.8	848.1	847.5	847.3
160°	866.6	867.3	867.9	868.6	869.2	869.2	868.3	867.5	866.7	865.9	865.9
162.5°	882.1	883.2	884.4	885.5	886.7	886.8	886.0	885.2	884.4	883.6	883.4
165°	896.8	898.0	899.1	900.3	901.4	901.5	900.5	899.5	898.6	897.6	897.6
167.5°	910.1	911.1	912.1	913.0	914.0	914.0	913.0	912.1	911.1	910.1	909.9
170°	919.7	920.8	922.0	923.1	924.3	924.3	923.1	922.0	920.8	919.7	919.7
172.5°	927.0	928.2	929.3	930.5	931.6	931.7	930.7	929.7	928.8	927.8	927.8
175°	932.2	933.3	934.5	935.6	936.8	936.9	935.9	934.9	933.9	932.9	932.9
177.5°	935.2	936.3	937.4	938.6	939.7	939.8	938.8	937.9	936.9	935.9	935.9
180°	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1



TEST NUMBER: P831874

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3058.6	3058.6	3058.6	3058.6	3058.6	3058.6	3058.6	3058.6	3058.6	3058.6	3058.6
2.5°	3247.3	3244.2	3214.1	3184.0	3154.5	3125.0	3103.1	3081.1	3044.1	3007.2	2984.0
5°	3448.6	3424.7	3377.1	3329.4	3258.0	3186.5	3126.3	3066.1	2989.6	2913.1	2849.1
7.5°	3560.8	3541.4	3483.7	3426.0	3331.3	3236.6	3142.6	3048.5	2935.7	2822.8	2726.3
10°	3563.9	3580.2	3532.6	3484.9	3378.3	3271.8	3143.8	3015.9	2864.2	2712.5	2587.7
12.5°	3452.3	3522.6	3512.5	3502.5	3394.0	3285.5	3130.0	2974.5	2788.3	2602.1	2446.0
15°	3243.5	3379.6	3419.7	3459.9	3370.2	3280.5	3103.7	2926.9	2708.1	2489.2	2309.9
17.5°	2974.5	3165.2	3271.1	3377.1	3311.9	3246.7	3052.9	2859.2	2612.8	2366.3	2171.3
20°	2656.0	2905.6	3071.7	3237.9	3214.1	3190.2	2990.2	2790.2	2524.4	2258.5	2047.2
22.5°	2341.3	2604.6	2834.1	3063.6	3088.0	3112.5	2910.6	2708.7	2417.8	2126.8	1911.8
25°	2069.8	2337.5	2610.9	2884.3	2939.4	2994.6	2802.7	2610.9	2309.3	2007.7	1793.9
27.5°	1810.8	2065.4	2366.3	2667.3	2767.6	2868.0	2692.4	2516.8	2202.7	1888.6	1675.4
30°	1599.5	1827.1	2134.4	2441.6	2581.4	2721.2	2560.1	2399.0	2087.3	1775.7	1566.9
32.5°	1402.6	1606.4	1914.9	2223.4	2385.8	2548.2	2409.0	2269.8	1970.1	1670.4	1464.1
35°	1247.1	1429.6	1717.4	2005.2	2187.0	2368.9	2254.7	2140.6	1847.8	1555.0	1360.0
37.5°	1113.6	1266.6	1536.8	1807.1	2000.2	2193.3	2098.0	2002.7	1727.4	1452.2	1267.8
40°	1003.2	1126.1	1377.5	1629.0	1818.3	2007.7	1926.2	1844.7	1598.3	1351.8	1179.4
42.5°	908.5	1014.5	1240.2	1466.0	1639.6	1813.3	1759.4	1705.5	1482.3	1259.0	1099.2
45°	825.1	914.2	1112.9	1311.7	1471.6	1631.5	1588.9	1546.2	1353.7	1161.2	1014.5
47.5°	751.2	827.7	1005.1	1182.5	1326.1	1469.7	1430.2	1390.7	1231.5	1072.2	938.6
50°	683.4	748.7	896.6	1044.6	1173.8	1302.9	1270.3	1237.7	1106.1	974.4	859.0
52.5°	619.5	673.4	806.3	939.3	1043.3	1147.4	1122.4	1097.3	995.7	894.1	789.4
55°	558.7	608.2	720.4	832.7	921.7	1010.7	985.7	960.6	881.6	802.6	710.4
57.5°	503.5	546.8	637.7	728.6	799.4	870.3	858.4	846.5	780.6	714.8	638.9
60°	445.2	484.1	562.4	640.8	697.9	754.9	741.1	727.3	680.3	633.3	568.1
62.5°	393.1	427.6	490.3	553.0	599.4	645.8	635.8	625.8	590.0	554.3	500.4
65°	338.6	372.4	423.2	474.0	510.4	546.8	538.0	529.2	502.2	475.3	432.0
67.5°	289.1	317.3	361.2	405.1	429.5	454.0	448.9	443.9	423.2	402.5	368.7
70°	238.9	263.3	299.7	336.1	353.0	369.9	371.8	373.7	354.9	336.1	311.0
72.5°	188.7	208.2	242.0	275.9	289.1	302.2	301.6	301.0	289.7	278.4	255.8
75°	144.8	159.3	185.6	211.9	223.2	234.5	237.0	239.5	228.9	218.2	205.7
77.5°	104.1	114.1	134.2	154.2	166.8	179.3	180.6	181.8	176.8	171.8	159.9
80°	73.4	76.5	89.0	101.6	114.7	127.9	129.8	131.7	126.7	121.6	114.1
82.5°	50.8	52.7	57.1	61.4	72.1	82.8	85.3	87.8	85.3	82.8	74.6
85°	30.7	31.4	33.2	35.1	40.1	45.1	47.7	50.2	48.9	47.7	43.3
87.5°	13.8	13.8	14.4	15.0	16.3	17.6	20.7	23.8	21.9	20.1	18.2
90°	13.4	11.3	9.2	7.3	5.6	4.0	2.4	0.7	2.4	4.0	5.6
92.5°	29.0	28.0	27.0	26.0	25.1	24.1	23.1	22.1	23.1	24.1	25.1
95°	51.9	50.6	49.3	48.1	46.9	45.8	44.6	43.5	44.6	45.8	46.9
97.5°	77.6	76.6	75.7	74.8	73.9	73.1	72.3	71.5	72.3	73.1	73.9
100°	106.7	105.9	105.1	104.2	103.2	102.2	101.2	100.2	101.2	102.2	103.2
102.5°	138.5	137.3	136.2	135.3	134.9	134.4	133.9	133.4	133.9	134.4	134.9
105°	171.0	169.5	168.0	167.1	166.8	166.5	166.1	165.8	166.1	166.5	166.8
107.5°	206.5	205.8	205.2	204.8	204.6	204.5	204.3	204.1	204.3	204.5	204.6
110°	241.8	241.5	241.1	240.8	240.5	240.2	239.8	239.5	239.8	240.2	240.5



TEST NUMBER: P831874

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	277.1	277.1	277.1	277.0	276.8	276.7	276.5	276.3	276.5	276.7	276.8
115°	314.6	314.9	315.2	315.2	314.7	314.2	313.7	313.2	313.7	314.2	314.7
117.5°	350.7	351.0	351.3	351.4	351.3	351.1	350.9	350.8	350.9	351.1	351.3
120°	387.8	388.6	389.4	389.3	388.4	387.4	386.4	385.4	386.4	387.4	388.4
122.5°	423.6	424.0	424.3	424.1	423.5	422.8	422.2	421.5	422.2	422.8	423.5
125°	459.8	460.1	460.4	460.3	459.8	459.3	458.9	458.4	458.9	459.3	459.8
127.5°	495.9	496.2	496.5	496.2	495.2	494.2	493.2	492.3	493.2	494.2	495.2
130°	530.8	531.3	531.8	531.4	530.1	528.8	527.5	526.2	527.5	528.8	530.1
132.5°	565.1	565.5	565.8	565.3	564.0	562.7	561.4	560.1	561.4	562.7	564.0
135°	598.7	598.9	599.0	598.6	597.6	596.7	595.7	594.7	595.7	596.7	597.6
137.5°	631.3	630.8	630.3	629.7	628.8	628.0	627.2	626.4	627.2	628.0	628.8
140°	663.6	663.5	663.3	662.8	662.0	661.2	660.4	659.5	660.4	661.2	662.0
142.5°	694.3	693.9	693.6	693.0	692.2	691.4	690.6	689.8	690.6	691.4	692.2
145°	724.1	723.7	723.2	722.8	722.4	722.1	721.8	721.4	721.8	722.1	722.4
147.5°	752.9	752.4	751.9	751.3	750.7	750.0	749.4	748.7	749.4	750.0	750.7
150°	779.7	779.4	779.1	778.8	778.4	778.1	777.8	777.5	777.8	778.1	778.4
152.5°	803.7	803.5	803.3	803.0	802.5	802.0	801.5	801.0	801.5	802.0	802.5
155°	826.5	826.3	826.2	826.1	826.1	826.1	826.1	826.1	826.1	826.1	826.1
157.5°	847.1	847.0	846.8	846.8	847.0	847.1	847.3	847.5	847.3	847.1	847.0
160°	865.9	865.9	865.9	866.0	866.4	866.7	867.0	867.4	867.0	866.7	866.4
162.5°	883.2	883.1	882.9	883.1	883.6	884.1	884.5	885.0	884.5	884.1	883.6
165°	897.6	897.6	897.6	897.8	898.3	898.8	899.3	899.8	899.3	898.8	898.3
167.5°	909.8	909.6	909.4	909.7	910.3	911.0	911.7	912.3	911.7	911.0	910.3
170°	919.7	919.7	919.7	920.0	920.7	921.3	922.0	922.6	922.0	921.3	920.7
172.5°	927.8	927.8	927.8	928.1	928.8	929.4	930.1	930.7	930.1	929.4	928.8
175°	932.9	932.9	932.9	933.3	933.9	934.6	935.2	935.9	935.2	934.6	933.9
177.5°	935.9	935.9	935.9	936.2	936.9	937.5	938.2	938.8	938.2	937.5	936.9
180°	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1



TEST NUMBER: P831874

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3058.6	3058.6	3058.6	3058.6	3058.6	3058.6	3058.6	3058.6	3058.6	3058.6	3058.6
2.5°	2960.8	2925.0	2889.3	2863.6	2837.9	2805.9	2773.9	2772.7	2771.4	2747.6	2723.7
5°	2785.2	2723.1	2661.0	2600.2	2539.4	2478.6	2417.8	2404.0	2390.2	2369.5	2348.8
7.5°	2629.7	2530.6	2431.6	2353.8	2276.1	2215.2	2154.4	2113.0	2071.7	2039.7	2007.7
10°	2462.9	2340.0	2217.1	2123.1	2029.0	1963.2	1897.3	1849.7	1802.0	1779.5	1756.9
12.5°	2289.9	2156.3	2022.7	1930.6	1838.4	1759.4	1680.4	1637.1	1593.9	1562.5	1531.2
15°	2130.6	1987.0	1843.4	1745.6	1647.8	1573.8	1499.8	1456.6	1413.3	1381.9	1350.6
17.5°	1976.3	1831.5	1686.7	1587.6	1488.5	1421.4	1354.3	1312.3	1270.3	1250.9	1231.5
20°	1835.9	1689.8	1543.7	1450.3	1356.9	1291.0	1225.2	1202.6	1180.0	1161.9	1143.7
22.5°	1696.7	1556.2	1415.8	1326.1	1236.5	1188.8	1141.2	1123.0	1104.8	1091.0	1077.2
25°	1580.1	1440.2	1300.4	1222.0	1143.7	1106.7	1069.7	1057.8	1045.9	1032.1	1018.3
27.5°	1462.2	1329.3	1196.3	1133.6	1070.9	1040.8	1010.7	995.7	980.6	969.4	958.1
30°	1358.1	1235.2	1112.3	1060.3	1008.2	981.9	955.6	939.3	923.0	912.3	901.6
32.5°	1257.8	1148.7	1039.6	995.1	950.6	924.8	899.1	883.5	867.8	855.2	842.7
35°	1165.0	1070.3	975.6	934.9	894.1	868.4	842.7	827.0	811.4	798.8	786.3
37.5°	1083.5	997.6	911.7	873.4	835.2	812.6	790.0	773.7	757.4	744.3	731.1
40°	1007.0	931.1	855.2	818.3	781.3	756.8	732.4	717.9	703.5	691.6	679.7
42.5°	939.3	869.7	800.1	763.7	727.3	704.1	680.9	664.0	647.1	640.2	633.3
45°	867.8	806.3	744.9	709.8	674.7	650.2	625.8	611.3	596.9	590.6	584.4
47.5°	805.1	748.0	691.0	656.5	622.0	600.1	578.1	566.8	555.5	546.8	538.0
50°	743.6	688.5	633.3	600.1	566.8	548.0	529.2	515.4	501.6	495.3	489.1
52.5°	684.7	634.5	584.4	550.5	516.7	498.5	480.3	468.4	456.5	443.3	430.1
55°	618.2	574.3	530.5	500.4	470.3	451.4	432.6	418.8	405.1	391.3	377.5
57.5°	563.1	519.8	476.5	449.6	422.6	404.4	386.2	371.2	356.1	344.9	333.6
60°	502.9	465.2	427.6	401.3	375.0	357.4	339.8	325.4	311.0	305.4	299.7
62.5°	446.4	411.3	376.2	353.0	329.8	312.9	296.0	286.5	277.1	273.4	269.6
65°	388.7	358.7	328.6	307.2	285.9	271.5	257.1	252.7	248.3	245.2	242.0
67.5°	334.8	309.1	283.4	264.6	245.8	235.8	225.7	220.7	215.7	211.9	208.2
70°	285.9	263.3	240.8	224.5	208.2	198.8	189.4	185.0	180.6	173.7	166.8
72.5°	233.2	215.7	198.1	185.6	173.1	164.9	156.8	148.0	139.2	132.9	126.7
75°	193.1	175.6	158.0	146.1	134.2	124.8	115.4	112.2	109.1	107.2	105.3
77.5°	148.0	132.9	117.9	108.5	99.1	94.7	90.3	88.4	86.5	85.9	85.3
80°	106.6	94.1	81.5	76.5	71.5	70.2	69.0	67.7	66.5	65.8	65.2
82.5°	66.5	60.2	53.9	52.7	51.4	50.8	50.2	49.5	48.9	48.3	47.7
85°	38.9	36.4	33.9	33.2	32.6	32.0	31.4	31.4	31.4	31.4	31.4
87.5°	16.3	16.3	16.3	16.3	16.3	16.3	16.3	16.3	16.3	15.7	15.0
90°	7.3	9.2	11.3	13.4	15.6	17.7	18.3	19.0	19.7	20.3	20.8
92.5°	26.0	27.0	28.0	29.0	30.0	31.0	31.4	31.9	32.4	32.9	33.0
95°	48.1	49.3	50.6	51.9	53.2	54.5	55.2	55.8	56.5	57.2	57.5
97.5°	74.8	75.7	76.6	77.6	78.6	79.6	80.4	81.2	82.0	82.9	83.2
100°	104.2	105.1	105.9	106.7	107.5	108.3	108.8	109.3	109.8	110.3	110.7
102.5°	135.3	136.2	137.3	138.5	139.6	140.8	141.2	141.7	142.2	142.7	142.9
105°	167.1	168.0	169.5	171.0	172.4	173.9	173.9	173.9	173.9	173.9	174.1
107.5°	204.8	205.2	205.8	206.5	207.2	207.8	208.3	208.8	209.3	209.8	209.9
110°	240.8	241.1	241.5	241.8	242.1	242.4	243.1	243.8	244.4	245.1	245.2



TEST NUMBER: P831874

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	277.0	277.1	277.1	277.1	277.1	277.1	277.9	278.7	279.5	280.4	280.8
115°	315.2	315.2	314.9	314.6	314.3	313.9	314.1	314.3	314.4	314.6	314.6
117.5°	351.4	351.3	351.0	350.7	350.4	350.0	350.0	350.0	350.0	350.0	349.8
120°	389.3	389.4	388.6	387.8	387.0	386.1	386.0	385.8	385.7	385.5	385.2
122.5°	424.1	424.3	424.0	423.6	423.3	423.0	422.5	422.0	421.5	421.0	420.5
125°	460.3	460.4	460.1	459.8	459.4	459.1	458.4	457.8	457.1	456.5	455.8
127.5°	496.2	496.5	496.2	495.9	495.5	495.2	494.2	493.2	492.3	491.3	490.5
130°	531.4	531.8	531.3	530.8	530.3	529.8	529.2	528.5	527.9	527.2	526.3
132.5°	565.3	565.8	565.5	565.1	564.8	564.5	563.7	562.8	562.0	561.2	560.4
135°	598.6	599.0	598.9	598.7	598.5	598.4	597.7	597.1	596.4	595.8	595.3
137.5°	629.7	630.3	630.8	631.3	631.8	632.3	631.5	630.6	629.8	629.0	628.3
140°	662.8	663.3	663.5	663.6	663.8	664.0	663.8	663.6	663.5	663.3	662.7
142.5°	693.0	693.6	693.9	694.3	694.6	694.9	694.8	694.6	694.4	694.3	693.8
145°	722.8	723.2	723.7	724.1	724.6	725.1	725.0	724.8	724.6	724.5	724.1
147.5°	751.3	751.9	752.4	752.9	753.4	753.9	753.9	753.9	753.9	753.9	753.4
150°	778.8	779.1	779.4	779.7	780.1	780.4	780.4	780.4	780.4	780.4	779.9
152.5°	803.0	803.3	803.5	803.7	803.8	804.0	804.3	804.6	805.0	805.3	805.0
155°	826.1	826.2	826.3	826.5	826.7	826.8	827.5	828.1	828.8	829.4	829.2
157.5°	846.8	846.8	847.0	847.1	847.3	847.5	848.1	848.8	849.4	850.1	849.9
160°	866.0	865.9	865.9	865.9	865.9	865.9	866.7	867.5	868.3	869.2	869.2
162.5°	883.1	882.9	883.1	883.2	883.4	883.6	884.4	885.2	886.0	886.8	886.7
165°	897.8	897.6	897.6	897.6	897.6	897.6	898.6	899.5	900.5	901.5	901.4
167.5°	909.7	909.4	909.6	909.8	909.9	910.1	911.1	912.1	913.0	914.0	914.0
170°	920.0	919.7	919.7	919.7	919.7	919.7	920.8	922.0	923.1	924.3	924.3
172.5°	928.1	927.8	927.8	927.8	927.8	927.8	928.8	929.7	930.7	931.7	931.6
175°	933.3	932.9	932.9	932.9	932.9	932.9	933.9	934.9	935.9	936.9	936.8
177.5°	936.2	935.9	935.9	935.9	935.9	935.9	936.9	937.9	938.8	939.8	939.7
180°	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1



TEST NUMBER: P831874

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	3058.6	3058.6	3058.6	3058.6
2.5°	2717.5	2711.2	2708.7	2706.2
5°	2329.4	2309.9	2305.5	2301.1
7.5°	1999.5	1991.4	1964.4	1937.5
10°	1731.8	1706.7	1695.4	1684.2
12.5°	1508.0	1484.8	1481.0	1477.2
15°	1334.3	1318.0	1312.3	1306.7
17.5°	1220.2	1208.9	1202.0	1195.1
20°	1135.5	1127.4	1122.4	1117.3
22.5°	1070.9	1064.7	1060.9	1057.1
25°	1008.9	999.5	996.3	993.2
27.5°	949.9	941.8	938.6	935.5
30°	894.7	887.9	883.5	879.1
32.5°	834.6	826.4	823.9	821.4
35°	781.3	776.2	773.7	771.2
37.5°	724.8	718.6	714.8	711.0
40°	676.5	673.4	671.5	669.6
42.5°	627.6	622.0	621.4	620.7
45°	578.7	573.1	571.8	570.6
47.5°	533.0	527.9	527.3	526.7
50°	482.2	475.3	470.3	465.2
52.5°	423.9	417.6	413.2	408.8
55°	370.6	363.7	359.9	356.1
57.5°	330.4	327.3	325.4	323.5
60°	297.8	296.0	294.7	293.4
62.5°	267.7	265.9	265.9	265.9
65°	240.1	238.3	236.4	234.5
67.5°	204.4	200.6	200.0	199.4
70°	161.1	155.5	154.9	154.2
72.5°	126.0	125.4	124.1	122.9
75°	104.1	102.8	102.8	102.8
77.5°	84.0	82.8	82.8	82.8
80°	64.6	64.0	64.6	65.2
82.5°	47.7	47.7	47.0	46.4
85°	30.7	30.1	30.1	30.1
87.5°	15.0	15.0	15.0	15.0
90°	21.1	21.5	21.8	22.1
92.5°	32.7	32.3	32.0	31.7
95°	57.5	57.5	57.5	57.5
97.5°	83.0	82.9	82.7	82.5
100°	111.0	111.4	111.7	112.0
102.5°	142.7	142.6	142.4	142.2
105°	174.4	174.7	175.1	175.4
107.5°	209.8	209.6	209.4	209.3
110°	244.9	244.6	244.2	243.9



TEST NUMBER: P831874

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	280.8	280.8	280.8	280.8
115°	314.4	314.3	314.1	313.9
117.5°	349.3	348.8	348.3	347.8
120°	384.9	384.6	384.3	383.9
122.5°	420.0	419.6	419.1	418.6
125°	455.2	454.5	453.9	453.2
127.5°	489.8	489.2	488.5	487.8
130°	525.2	524.0	522.9	521.7
132.5°	559.6	558.7	557.9	557.1
135°	594.9	594.6	594.3	594.0
137.5°	627.9	627.4	626.9	626.4
140°	661.5	660.4	659.2	658.1
142.5°	693.0	692.1	691.3	690.5
145°	723.4	722.8	722.1	721.4
147.5°	752.4	751.4	750.4	749.4
150°	778.9	777.9	777.0	776.0
152.5°	804.2	803.4	802.6	801.8
155°	828.1	826.9	825.8	824.6
157.5°	848.9	847.9	847.0	846.0
160°	868.6	867.9	867.3	866.6
162.5°	885.5	884.4	883.2	882.1
165°	900.3	899.1	898.0	896.8
167.5°	913.0	912.1	911.1	910.1
170°	923.1	922.0	920.8	919.7
172.5°	930.5	929.3	928.2	927.0
175°	935.6	934.5	933.3	932.2
177.5°	938.6	937.4	936.3	935.2
180°	938.1	938.1	938.1	938.1



TEST NUMBER: P831874

CATALOG NUMBER: S123RDIP-S1000D805U830-4F0-1E-UDD-G1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.86	14.76	14.73	15.64	16.75	18.52	19.42	19.39	20.30	21.41
	3H	15.08	15.89	15.97	16.78	17.92	20.03	20.83	20.91	21.72	22.86
	4H	15.47	16.23	16.37	17.12	18.27	20.52	21.28	21.42	22.18	23.32
	6H	15.75	16.45	16.66	17.36	18.52	20.84	21.53	21.74	22.44	23.60
	8H	15.84	16.51	16.76	17.43	18.59	20.92	21.58	21.83	22.50	23.66
	12H	15.90	16.53	16.82	17.44	18.63	20.95	21.58	21.87	22.50	23.68
4H	2H	14.59	15.35	15.49	16.24	17.39	18.53	19.28	19.43	20.18	21.33
	3H	15.97	16.59	16.88	17.52	18.68	20.19	20.82	21.10	21.75	22.91
	4H	16.42	17.00	17.35	17.92	19.11	20.80	21.37	21.72	22.30	23.48
	6H	16.79	17.29	17.73	18.23	19.42	21.24	21.73	22.18	22.68	23.87
	8H	16.92	17.38	17.86	18.32	19.52	21.37	21.83	22.31	22.77	23.98
	12H	17.00	17.41	17.96	18.37	19.58	21.44	21.85	22.40	22.81	24.02
8H	4H	16.74	17.20	17.68	18.14	19.34	20.77	21.23	21.71	22.17	23.37
	6H	17.21	17.59	18.17	18.57	19.77	21.27	21.65	22.23	22.63	23.83
	8H	17.40	17.74	18.38	18.71	19.93	21.46	21.79	22.43	22.76	23.98
	12H	17.54	17.84	18.52	18.80	20.07	21.58	21.87	22.55	22.84	24.10
12H	4H	16.76	17.17	17.71	18.13	19.34	20.72	21.14	21.68	22.10	23.30
	6H	17.27	17.60	18.24	18.58	19.79	21.24	21.58	22.22	22.55	23.77
	8H	17.49	17.78	18.46	18.75	20.02	21.44	21.73	22.42	22.70	23.97