

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332370

Luminaire Tested: **S123RDIP-S1165D585U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332370
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D585U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6392.4 lumens
Efficiency: N/A
Efficacy: 116.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332370

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332370

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69																				
1	102	98	94	91	97	93	89	86	83	80	78	74	72	70	65	64	63	59																				
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	58	56	53	50																				
3	86	76	69	63	81	72	66	60	65	60	55	58	54	51	52	49	46	43																				
4	79	68	60	54	74	64	57	52	58	52	48	52	48	44	47	43	40	37																				
5	72	61	53	46	68	58	50	45	52	46	42	47	42	38	42	38	35	32																				
6	67	55	47	41	63	52	45	39	47	41	37	43	38	34	38	34	31	29																				
7	62	50	42	36	59	47	40	35	43	37	32	39	34	30	35	31	28	26																				
8	58	45	37	32	55	43	36	31	39	33	29	36	31	27	32	28	25	23																				
9	54	42	34	29	51	40	33	28	36	30	26	33	28	24	30	26	23	21																				
10	51	38	31	26	48	37	30	25	34	28	24	31	26	22	28	24	21	19																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20863	20863	20863
5°	20942	20653	20772
10°	20824	20394	20325
15°	20600	19917	19706
20°	20292	19321	18871
25°	19975	18650	18053
30°	19557	17877	16900
35°	19127	17102	15843
40°	18730	16190	14533
45°	18209	15289	13352
50°	17637	14267	12030
55°	17051	13097	10796
60°	16514	11845	9442
65°	15814	10488	8087
70°	14940	8806	6530
75°	13662	6929	6147
80°	12180	6137	5653
85°	10288	5434	5051



TEST NUMBER: P332370

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.0	2.8
10°-20°	506.4	7.9
20°-30°	729.2	11.4
30°-40°	821.3	12.8
40°-50°	785.8	12.3
50°-60°	643.5	10.1
60°-70°	434.1	6.8
70°-80°	218.4	3.4
80°-90°	59.9	0.9
90°-100°	47.3	0.7
100°-110°	141.6	2.2
110°-120°	240.8	3.8
120°-130°	316.7	5.0
130°-140°	356.0	5.6
140°-150°	349.9	5.5
150°-160°	294.6	4.6
160°-170°	196.1	3.1
170°-180°	68.7	1.1
0°-30°	1417.6	22.2
0°-40°	2238.9	35.0
0°-60°	3668.1	57.4
0°-90°	4380.6	68.5
90°-120°	429.7	6.7
90°-150°	1452.4	22.7
90°-180°	2012.0	31.5
0°-180°	6392.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1938	1938	1938	1938	1938	
5°	1938	1930	1911	1925	1922	184
15°	1849	1830	1787	1779	1768	521
25°	1682	1641	1570	1538	1520	773
35°	1456	1397	1302	1236	1206	911
45°	1196	1123	1004	918	877	923
55°	909	828	698	610	575	814
65°	621	532	412	338	318	614
75°	328	252	167	152	148	350
85°	83	50	44	41	41	94
90°	1	6	14	16	17	6
95°	34	38	42	44	44	38
105°	128	130	135	135	136	137
115°	242	244	243	244	243	240
125°	355	356	355	353	351	316
135°	460	464	463	461	460	355
145°	558	560	561	561	558	349
155°	639	639	640	642	638	294
165°	696	695	695	698	694	196
175°	724	722	722	725	722	69
180°	726	726	726	726	726	



TEST NUMBER: P332370

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2
2.5°	1944.5	1943.3	1942.2	1941.1	1940.0	1937.7	1934.4	1931.0	1927.7	1924.3	1927.4
5°	1938.2	1936.4	1934.7	1932.9	1931.2	1928.2	1924.0	1919.8	1915.6	1911.4	1914.6
7.5°	1920.2	1918.4	1916.5	1914.6	1912.7	1909.0	1903.6	1898.1	1892.7	1887.2	1889.0
10°	1905.2	1902.7	1900.3	1897.8	1895.4	1891.0	1884.7	1878.4	1872.1	1865.9	1866.2
12.5°	1883.8	1881.1	1878.3	1875.6	1872.9	1867.7	1860.0	1852.3	1844.6	1836.9	1836.7
15°	1848.6	1844.7	1840.9	1837.0	1833.2	1826.4	1816.6	1806.8	1797.0	1787.3	1785.5
17.5°	1804.2	1799.8	1795.3	1790.8	1786.4	1777.9	1765.5	1753.0	1740.6	1728.2	1724.5
20°	1771.5	1766.0	1760.4	1754.8	1749.2	1739.8	1726.5	1713.2	1699.9	1686.7	1682.1
22.5°	1735.1	1728.6	1722.2	1715.8	1709.4	1699.1	1685.0	1670.9	1656.8	1642.6	1637.0
25°	1681.9	1673.2	1664.5	1655.7	1647.0	1634.6	1618.5	1602.5	1586.4	1570.3	1563.0
27.5°	1617.5	1607.9	1598.2	1588.6	1578.9	1565.2	1547.3	1529.4	1511.5	1493.6	1483.4
30°	1573.5	1563.0	1552.5	1542.0	1531.6	1516.5	1497.0	1477.4	1457.9	1438.3	1426.4
32.5°	1529.5	1517.6	1505.7	1493.8	1482.0	1465.7	1445.0	1424.3	1403.6	1383.0	1370.0
35°	1455.6	1443.0	1430.4	1417.9	1405.3	1388.2	1366.5	1344.9	1323.2	1301.5	1286.5
37.5°	1380.8	1366.8	1352.8	1338.8	1324.9	1306.3	1283.2	1260.1	1237.0	1213.8	1196.8
40°	1333.0	1317.6	1302.2	1286.9	1271.5	1251.4	1226.6	1201.8	1177.0	1152.2	1134.0
42.5°	1278.9	1263.5	1248.2	1232.8	1217.4	1196.9	1171.3	1145.6	1120.0	1094.4	1074.5
45°	1196.2	1180.5	1164.8	1149.1	1133.3	1112.0	1085.1	1058.2	1031.3	1004.4	984.5
47.5°	1113.5	1096.3	1079.0	1061.8	1044.5	1022.4	995.5	968.6	941.7	914.9	893.2
50°	1053.2	1036.8	1020.3	1003.9	987.5	965.2	936.9	908.6	880.3	852.0	830.3
52.5°	999.1	981.3	963.5	945.7	927.8	904.9	876.9	848.9	820.9	792.9	770.4
55°	908.6	891.4	874.3	857.2	840.1	816.7	787.0	757.3	727.6	697.9	677.7
57.5°	824.9	806.3	787.6	769.0	750.3	726.1	696.3	666.4	636.6	606.8	587.6
60°	767.1	747.9	728.7	709.5	690.2	666.1	637.1	608.2	579.2	550.2	531.3
62.5°	709.2	690.0	670.8	651.6	632.4	608.3	579.3	550.3	521.3	492.3	474.6
65°	620.9	601.7	582.5	563.3	544.1	520.8	493.6	466.3	439.1	411.8	394.7
67.5°	532.6	513.1	493.7	474.3	454.9	432.1	406.0	379.8	353.7	327.6	314.8
70°	474.7	455.9	437.0	418.1	399.3	377.6	353.2	328.7	304.3	279.8	267.6
72.5°	416.9	398.3	379.7	361.1	342.5	322.1	299.9	277.7	255.5	233.3	223.3
75°	328.5	311.8	295.0	278.2	261.5	243.5	224.3	205.0	185.8	166.6	163.1
77.5°	248.0	232.9	217.7	202.6	187.4	173.6	161.3	148.9	136.5	124.2	122.3
80°	196.5	182.2	167.8	153.5	139.2	128.4	121.0	113.7	106.4	99.0	98.0
82.5°	147.4	135.1	122.7	110.3	98.0	90.1	86.7	83.2	79.8	76.4	75.3
85°	83.3	75.6	67.9	60.3	52.6	48.2	47.2	46.1	45.1	44.0	43.3
87.5°	30.3	27.5	24.7	21.8	19.0	17.8	18.1	18.4	18.8	19.1	18.9
90°	0.6	1.8	3.1	4.4	5.6	7.1	8.7	10.4	12.0	13.7	14.2
92.5°	13.8	14.7	15.5	16.4	17.3	18.2	19.1	20.0	21.0	21.9	22.3
95°	33.7	34.5	35.4	36.3	37.2	38.2	39.2	40.2	41.2	42.2	42.7
97.5°	59.8	60.4	61.1	61.8	62.4	63.1	63.8	64.6	65.3	66.1	66.6
100°	77.6	78.3	79.1	79.9	80.6	81.3	81.9	82.6	83.2	83.8	84.2
102.5°	98.1	98.6	99.0	99.5	99.9	100.6	101.4	102.3	103.1	103.9	104.3
105°	128.3	128.6	128.8	129.1	129.4	130.0	131.2	132.3	133.5	134.6	134.6
107.5°	163.5	163.6	163.8	163.9	164.1	164.4	164.8	165.3	165.8	166.2	166.6
110°	185.4	185.6	185.9	186.1	186.4	186.6	186.9	187.2	187.4	187.7	188.2



TEST NUMBER: P332370

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	208.2	208.3	208.5	208.6	208.8	208.9	209.0	209.0	209.1	209.1	209.7
115°	242.4	242.8	243.2	243.6	243.9	244.0	243.7	243.5	243.2	243.0	243.1
117.5°	276.9	277.1	277.4	277.6	277.9	277.8	277.5	277.2	276.9	276.5	276.5
120°	298.3	299.1	299.8	300.6	301.4	301.4	300.8	300.2	299.5	298.9	298.8
122.5°	320.7	321.2	321.8	322.3	322.9	323.0	322.7	322.4	322.0	321.7	321.4
125°	354.8	355.2	355.5	355.9	356.3	356.4	356.1	355.9	355.6	355.4	354.8
127.5°	386.3	387.1	387.9	388.7	389.5	389.8	389.5	389.2	388.9	388.7	388.0
130°	407.3	408.3	409.3	410.3	411.3	411.6	411.3	410.9	410.5	410.1	409.6
132.5°	428.2	429.3	430.3	431.3	432.3	432.7	432.4	432.1	431.8	431.6	430.9
135°	460.3	461.1	461.8	462.6	463.3	463.7	463.5	463.4	463.3	463.2	462.7
137.5°	490.0	490.6	491.2	491.9	492.5	493.0	493.3	493.6	494.0	494.3	493.8
140°	510.5	511.1	511.8	512.4	513.0	513.4	513.5	513.7	513.8	513.9	513.8
142.5°	529.2	529.8	530.5	531.1	531.7	532.2	532.4	532.6	532.9	533.1	533.0
145°	558.4	558.7	558.9	559.2	559.4	559.7	560.1	560.5	560.9	561.3	561.1
147.5°	584.0	584.4	584.9	585.3	585.8	586.2	586.6	586.9	587.3	587.6	587.6
150°	601.8	602.0	602.3	602.5	602.8	603.0	603.3	603.5	603.8	604.0	604.0
152.5°	616.4	616.7	617.1	617.4	617.8	618.0	618.2	618.3	618.5	618.6	618.8
155°	639.4	639.4	639.4	639.4	639.4	639.5	639.6	639.7	639.9	640.0	640.5
157.5°	659.0	658.9	658.7	658.6	658.4	658.4	658.5	658.6	658.7	658.8	659.3
160°	671.3	671.1	670.8	670.6	670.3	670.2	670.2	670.2	670.2	670.2	670.8
162.5°	682.3	681.9	681.6	681.2	680.9	680.8	680.9	681.0	681.1	681.2	681.8
165°	696.4	696.1	695.7	695.3	694.9	694.7	694.7	694.7	694.7	694.7	695.5
167.5°	707.7	707.2	706.7	706.2	705.7	705.5	705.6	705.7	705.8	705.9	706.7
170°	714.1	713.6	713.1	712.6	712.1	711.8	711.8	711.8	711.8	711.8	712.7
172.5°	719.1	718.6	718.1	717.6	717.1	716.9	716.9	716.9	716.9	716.9	717.7
175°	724.4	723.9	723.4	722.9	722.4	722.1	722.1	722.1	722.1	722.1	722.9
177.5°	726.6	726.2	725.8	725.3	724.9	724.7	724.7	724.7	724.7	724.7	725.3
180°	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1



TEST NUMBER: P332370

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2
2.5°	1930.5	1933.6	1936.6	1937.9	1937.3	1936.8	1936.2	1935.6
5°	1917.7	1920.9	1924.0	1925.2	1924.5	1923.8	1923.1	1922.4
7.5°	1890.7	1892.5	1894.2	1894.5	1893.3	1892.1	1890.9	1889.7
10°	1866.6	1866.9	1867.3	1866.6	1864.8	1863.1	1861.3	1859.6
12.5°	1836.5	1836.3	1836.1	1835.0	1833.0	1830.9	1828.9	1826.9
15°	1783.8	1782.0	1780.3	1778.2	1775.7	1773.3	1770.8	1768.4
17.5°	1720.8	1717.0	1713.3	1709.7	1706.0	1702.4	1698.8	1695.1
20°	1677.6	1673.0	1668.5	1664.1	1659.9	1655.7	1651.6	1647.4
22.5°	1631.3	1625.7	1620.0	1615.2	1611.3	1607.4	1603.5	1599.6
25°	1555.7	1548.3	1541.0	1535.4	1531.6	1527.7	1523.9	1520.0
27.5°	1473.2	1463.0	1452.8	1444.8	1438.9	1433.1	1427.2	1421.3
30°	1414.5	1402.7	1390.8	1382.1	1376.5	1370.9	1365.3	1359.7
32.5°	1357.0	1344.0	1331.0	1321.6	1315.7	1309.8	1304.0	1298.1
35°	1271.5	1256.5	1241.5	1230.8	1224.5	1218.2	1211.9	1205.7
37.5°	1179.7	1162.7	1145.6	1133.2	1125.5	1117.7	1110.0	1102.2
40°	1115.9	1097.7	1079.6	1066.5	1058.4	1050.4	1042.4	1034.3
42.5°	1054.7	1034.8	1015.0	1001.5	994.3	987.1	979.9	972.7
45°	964.6	944.7	924.8	910.7	902.3	893.9	885.5	877.1
47.5°	871.5	849.9	828.2	813.7	806.2	798.7	791.2	783.8
50°	808.7	787.0	765.3	750.5	742.5	734.4	726.4	718.4
52.5°	747.9	725.4	702.9	688.0	680.8	673.7	666.5	659.3
55°	657.4	637.1	616.9	603.3	596.3	589.3	582.3	575.3
57.5°	568.5	549.3	530.2	517.6	511.7	505.8	499.8	493.9
60°	512.4	493.6	474.7	462.3	456.4	450.4	444.5	438.6
62.5°	456.8	439.1	421.3	409.4	403.1	396.9	390.7	384.5
65°	377.6	360.5	343.4	332.9	329.1	325.2	321.4	317.5
67.5°	302.0	289.2	276.4	268.0	263.9	259.7	255.6	251.5
70°	255.3	243.1	230.9	222.9	219.0	215.2	211.3	207.5
72.5°	213.3	203.3	193.3	187.5	185.9	184.3	182.7	181.1
75°	159.6	156.1	152.6	150.6	149.9	149.2	148.5	147.8
77.5°	120.4	118.5	116.6	115.3	114.6	113.9	113.2	112.5
80°	96.9	95.9	94.8	94.0	93.3	92.6	91.9	91.2
82.5°	74.3	73.3	72.2	71.6	71.5	71.3	71.2	71.1
85°	42.6	41.9	41.2	40.9	40.9	40.9	40.9	40.9
87.5°	18.7	18.6	18.4	18.2	17.9	17.7	17.5	17.3
90°	14.7	15.2	15.7	16.1	16.4	16.6	16.9	17.1
92.5°	22.7	23.1	23.5	23.7	23.5	23.3	23.2	23.0
95°	43.2	43.7	44.2	44.5	44.5	44.5	44.5	44.5
97.5°	67.2	67.8	68.4	68.6	68.6	68.5	68.5	68.4
100°	84.6	85.0	85.4	85.7	85.9	86.2	86.4	86.7
102.5°	104.7	105.1	105.4	105.6	105.6	105.5	105.5	105.4
105°	134.6	134.6	134.6	134.7	135.0	135.2	135.5	135.8
107.5°	167.0	167.4	167.8	168.0	167.8	167.7	167.5	167.4
110°	188.7	189.2	189.7	189.8	189.6	189.3	189.1	188.8



TEST NUMBER: P332370

CATALOG NUMBER: S123RDIP-S1165D585U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	210.3	210.9	211.5	211.8	211.8	211.7	211.7	211.6
115°	243.2	243.4	243.5	243.5	243.4	243.2	243.1	243.0
117.5°	276.5	276.4	276.4	276.2	275.9	275.5	275.2	274.8
120°	298.6	298.5	298.4	298.2	297.9	297.7	297.4	297.2
122.5°	321.0	320.7	320.4	320.0	319.7	319.3	319.0	318.6
125°	354.3	353.8	353.3	352.8	352.3	351.8	351.3	350.8
127.5°	387.2	386.5	385.8	385.2	384.6	384.0	383.4	382.8
130°	409.1	408.6	408.1	407.4	406.5	405.6	404.7	403.8
132.5°	430.3	429.7	429.1	428.5	427.8	427.1	426.4	425.7
135°	462.1	461.6	461.1	460.7	460.5	460.2	460.0	459.7
137.5°	493.2	492.7	492.2	491.7	491.2	490.7	490.2	489.7
140°	513.7	513.5	513.4	512.9	512.0	511.1	510.2	509.4
142.5°	532.8	532.7	532.6	532.2	531.5	530.8	530.1	529.4
145°	561.0	560.9	560.8	560.4	559.9	559.4	558.9	558.4
147.5°	587.6	587.6	587.6	587.2	586.5	585.7	585.0	584.2
150°	604.0	604.0	604.0	603.7	602.9	602.1	601.4	600.6
152.5°	619.1	619.3	619.5	619.2	618.6	617.9	617.3	616.6
155°	641.0	641.5	642.0	641.8	640.9	640.0	639.2	638.3
157.5°	659.9	660.4	660.9	660.8	660.1	659.4	658.7	658.0
160°	671.5	672.1	672.7	672.8	672.3	671.8	671.3	670.8
162.5°	682.4	683.1	683.7	683.6	682.8	682.0	681.2	680.4
165°	696.3	697.0	697.8	697.7	696.8	695.9	695.1	694.2
167.5°	707.5	708.3	709.1	709.1	708.3	707.5	706.7	705.9
170°	713.6	714.5	715.4	715.4	714.5	713.6	712.7	711.8
172.5°	718.4	719.2	720.0	720.0	719.1	718.2	717.3	716.4
175°	723.6	724.4	725.2	725.1	724.2	723.3	722.4	721.5
177.5°	726.0	726.6	727.2	727.1	726.4	725.7	725.0	724.3
180°	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1

(END OF REPORT)