

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332363-830

Luminaire Tested: **S123RDIP-S1165D365U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332363-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D365U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5495.3 lumens
Efficiency: N/A
Efficacy: 110.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332363-830

CATALOG NUMBER: S123RDIP-S1165D365U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332363-830

CATALOG NUMBER: S123RDIP-S1165D365U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75
1	104	100	96	92	99	95	92	88	86	84	81	78	76	74	71	69	68	64
2	95	88	81	76	90	84	78	73	76	72	68	69	66	63	63	60	58	55
3	87	77	70	64	83	74	67	62	68	62	58	62	57	54	56	53	50	47
4	80	69	61	55	76	66	59	53	60	55	50	55	50	47	51	47	43	41
5	74	62	54	47	70	59	52	46	54	48	43	50	45	41	46	42	38	35
6	68	56	48	42	65	54	46	40	49	43	38	45	40	36	42	37	34	31
7	63	51	43	37	60	49	41	36	45	39	34	41	36	32	38	34	30	28
8	59	46	38	33	56	45	37	32	41	35	30	38	33	29	35	31	27	25
9	55	42	35	30	52	41	34	29	38	32	27	35	30	26	33	28	25	23
10	52	39	32	27	49	38	31	26	35	29	25	33	27	24	30	26	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19664	19664	19664
5°	19739	19466	19578
10°	19627	19223	19158
15°	19417	18773	18574
20°	19126	18211	17786
25°	18828	17579	17016
30°	18434	16850	15929
35°	18029	16119	14933
40°	17654	15260	13699
45°	17163	14411	12584
50°	16623	13447	11338
55°	16071	12344	10175
60°	15565	11164	8900
65°	14905	9885	7623
70°	14080	8299	6156
75°	12876	6529	5793
80°	11480	5783	5331
85°	9695	5125	4755



TEST NUMBER: P332363-830

CATALOG NUMBER: S123RDIP-S1165D365U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.5	3.1
10°-20°	477.3	8.7
20°-30°	687.3	12.5
30°-40°	774.2	14.1
40°-50°	740.6	13.5
50°-60°	606.5	11.0
60°-70°	409.2	7.4
70°-80°	205.9	3.7
80°-90°	55.7	1.0
90°-100°	16.3	0.3
100°-110°	77.7	1.4
110°-120°	186.6	3.4
120°-130°	237.6	4.3
130°-140°	253.9	4.6
140°-150°	237.4	4.3
150°-160°	191.5	3.5
160°-170°	123.6	2.2
170°-180°	42.6	0.8
0°-30°	1336.1	24.3
0°-40°	2110.3	38.4
0°-60°	3457.4	62.9
0°-90°	4128.1	75.1
90°-120°	280.6	5.1
90°-150°	1009.4	18.4
90°-180°	1367.0	24.9
0°-180°	5495.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1827	1827	1827	1827	1827	
5°	1827	1819	1802	1814	1812	173
15°	1742	1725	1685	1677	1667	491
25°	1585	1547	1480	1450	1433	729
35°	1372	1316	1227	1165	1136	858
45°	1128	1058	947	865	827	870
55°	856	781	658	575	542	768
65°	585	502	388	319	299	579
75°	310	238	157	143	139	330
85°	78	48	42	39	38	88
90°	0	4	8	9	10	5
95°	20	8	10	12	13	25
105°	99	101	73	17	15	105
115°	186	188	191	194	196	184
125°	262	265	266	267	268	234
135°	327	329	330	331	330	251
145°	377	379	380	381	381	236
155°	415	415	415	416	415	191
165°	438	437	437	439	437	124
175°	448	447	447	449	447	43
180°	448	448	448	448	448	



TEST NUMBER: P332363-830

CATALOG NUMBER: S123RDIP-S1165D365U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8
2.5°	1832.8	1831.6	1830.6	1829.6	1828.5	1826.4	1823.3	1820.0	1816.9	1813.7	1816.7
5°	1826.8	1825.1	1823.5	1821.8	1820.2	1817.4	1813.5	1809.5	1805.5	1801.6	1804.6
7.5°	1809.9	1808.2	1806.4	1804.6	1802.8	1799.3	1794.2	1789.0	1784.0	1778.8	1780.5
10°	1795.7	1793.4	1791.1	1788.8	1786.5	1782.3	1776.4	1770.5	1764.5	1758.7	1759.0
12.5°	1775.6	1773.0	1770.4	1767.8	1765.3	1760.4	1753.1	1745.9	1738.6	1731.4	1731.2
15°	1742.4	1738.7	1735.1	1731.5	1727.9	1721.5	1712.2	1703.0	1693.7	1684.6	1682.9
17.5°	1700.5	1696.4	1692.1	1687.9	1683.8	1675.7	1664.1	1652.3	1640.6	1628.9	1625.4
20°	1669.7	1664.5	1659.3	1654.0	1648.7	1639.8	1627.3	1614.8	1602.2	1589.8	1585.5
22.5°	1635.4	1629.3	1623.2	1617.2	1611.2	1601.5	1588.2	1574.9	1561.6	1548.2	1542.9
25°	1585.3	1577.1	1568.9	1560.6	1552.4	1540.7	1525.5	1510.4	1495.2	1480.1	1473.2
27.5°	1524.6	1515.5	1506.4	1497.3	1488.2	1475.3	1458.4	1441.5	1424.7	1407.8	1398.2
30°	1483.1	1473.2	1463.3	1453.4	1443.6	1429.4	1411.0	1392.5	1374.1	1355.7	1344.4
32.5°	1441.6	1430.4	1419.2	1408.0	1396.8	1381.5	1362.0	1342.5	1323.0	1303.5	1291.3
35°	1372.0	1360.1	1348.2	1336.4	1324.6	1308.4	1288.0	1267.6	1247.2	1226.7	1212.6
37.5°	1301.5	1288.3	1275.1	1261.9	1248.8	1231.2	1209.5	1187.7	1165.9	1144.1	1128.0
40°	1256.4	1241.9	1227.4	1213.0	1198.4	1179.5	1156.1	1132.7	1109.4	1086.0	1068.8
42.5°	1205.4	1190.9	1176.5	1162.0	1147.5	1128.1	1104.0	1079.8	1055.6	1031.5	1012.8
45°	1127.5	1112.7	1097.9	1083.1	1068.2	1048.1	1022.8	997.4	972.0	946.7	927.9
47.5°	1049.5	1033.3	1017.0	1000.8	984.5	963.7	938.3	912.9	887.6	862.3	841.9
50°	992.7	977.2	961.7	946.2	930.8	909.7	883.1	856.4	829.7	803.0	782.6
52.5°	941.7	924.9	908.1	891.4	874.5	852.9	826.5	800.1	773.7	747.3	726.1
55°	856.4	840.2	824.1	807.9	791.8	769.8	741.8	713.8	685.8	657.8	638.8
57.5°	777.5	760.0	742.3	724.8	707.2	684.4	656.3	628.1	600.0	571.9	553.8
60°	723.0	704.9	686.8	668.7	650.5	627.8	600.5	573.3	545.9	518.6	500.8
62.5°	668.5	650.4	632.3	614.2	596.1	573.3	546.0	518.7	491.3	464.0	447.3
65°	585.2	567.1	549.0	530.9	512.8	490.9	465.2	439.5	413.9	388.1	372.0
67.5°	502.0	483.6	465.3	447.0	428.8	407.3	382.7	358.0	333.4	308.8	296.7
70°	447.4	429.7	411.9	394.1	376.4	355.9	332.9	309.8	286.8	263.7	252.2
72.5°	392.9	375.4	357.9	340.4	322.8	303.6	282.7	261.7	240.8	219.9	210.5
75°	309.6	293.9	278.1	262.2	246.5	229.5	211.4	193.2	175.1	157.0	153.7
77.5°	233.8	219.5	205.2	191.0	176.6	163.6	152.0	140.3	128.7	117.1	115.3
80°	185.2	171.7	158.2	144.7	131.2	121.0	114.0	107.2	100.3	93.3	92.4
82.5°	138.9	127.3	115.6	104.0	92.4	84.9	81.7	78.4	75.2	72.0	71.0
85°	78.5	71.3	64.0	56.8	49.6	45.4	44.5	43.5	42.5	41.5	40.8
87.5°	28.6	25.7	23.0	20.3	17.5	16.2	16.4	16.6	16.8	17.0	16.8
90°	0.4	1.0	1.8	2.5	3.3	4.1	5.1	6.0	7.1	8.0	8.3
92.5°	6.2	6.0	5.7	5.6	5.4	5.7	6.3	7.1	7.8	8.5	9.0
95°	20.4	17.2	14.2	11.2	8.2	7.1	7.9	8.7	9.5	10.4	10.8
97.5°	40.8	39.5	38.1	36.8	35.3	32.0	26.7	21.4	16.0	10.7	11.3
100°	56.3	57.8	59.3	60.7	62.2	57.2	45.6	34.1	22.5	11.0	11.6
102.5°	73.9	74.9	76.0	77.1	78.1	72.4	59.8	47.1	34.5	22.0	20.1
105°	99.2	100.1	100.9	101.7	102.5	99.6	92.9	86.2	79.6	73.0	59.9
107.5°	126.0	126.7	127.3	128.0	128.7	129.5	130.5	131.6	132.6	133.7	124.0
110°	143.9	144.5	145.1	145.6	146.3	146.9	147.8	148.5	149.4	150.2	147.8



TEST NUMBER: P332363-830

CATALOG NUMBER: S123RDIP-S1165D365U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	160.9	161.5	162.0	162.5	163.1	163.7	164.6	165.4	166.2	167.0	167.0
115°	186.2	186.6	187.1	187.5	187.9	188.5	189.2	189.8	190.5	191.1	191.9
117.5°	210.7	211.2	211.7	212.3	212.8	213.3	213.6	214.0	214.3	214.6	215.2
120°	225.8	226.5	227.2	227.8	228.5	228.9	229.1	229.4	229.6	229.8	230.5
122.5°	241.3	241.9	242.3	242.9	243.5	243.8	244.1	244.4	244.7	245.0	245.4
125°	262.5	263.1	263.6	264.2	264.9	265.2	265.6	265.9	266.2	266.5	266.6
127.5°	283.0	283.6	284.2	284.7	285.3	285.8	286.2	286.5	286.9	287.2	287.5
130°	295.8	296.3	296.9	297.6	298.1	298.6	298.9	299.2	299.4	299.7	300.0
132.5°	308.0	308.6	309.2	309.8	310.4	310.8	311.0	311.3	311.5	311.8	312.1
135°	326.8	327.2	327.6	328.1	328.5	328.9	329.1	329.5	329.8	330.1	330.3
137.5°	342.7	343.3	343.8	344.4	345.0	345.3	345.5	345.6	345.8	346.0	346.4
140°	353.4	353.8	354.3	354.7	355.2	355.5	355.7	355.9	356.2	356.4	356.7
142.5°	363.3	363.7	364.1	364.6	365.0	365.3	365.6	365.8	366.0	366.3	366.5
145°	377.0	377.6	378.1	378.6	379.1	379.5	379.6	379.8	379.8	380.0	380.2
147.5°	390.0	390.4	390.7	391.1	391.3	391.6	391.8	391.9	392.1	392.2	392.4
150°	398.0	398.2	398.4	398.7	398.9	399.1	399.3	399.4	399.5	399.6	399.8
152.5°	405.2	405.3	405.4	405.5	405.6	405.8	405.8	405.9	406.0	406.0	406.3
155°	415.4	415.2	415.0	414.9	414.7	414.7	414.8	414.8	414.9	415.0	415.4
157.5°	423.2	423.2	423.2	423.1	423.1	423.1	423.0	422.9	422.8	422.8	423.2
160°	428.0	427.9	427.8	427.7	427.7	427.6	427.5	427.4	427.4	427.3	427.7
162.5°	432.5	432.3	432.2	432.0	431.8	431.6	431.5	431.5	431.4	431.3	431.8
165°	438.0	437.7	437.5	437.3	437.1	437.0	436.9	436.8	436.7	436.7	437.2
167.5°	442.2	442.0	441.7	441.4	441.0	440.9	440.9	440.9	440.9	440.9	441.5
170°	444.6	444.3	444.0	443.7	443.5	443.3	443.3	443.3	443.3	443.3	443.9
172.5°	446.2	445.9	445.5	445.2	444.8	444.7	444.7	444.8	444.9	444.9	445.5
175°	448.3	447.9	447.5	447.2	446.9	446.7	446.8	446.9	446.9	447.0	447.5
177.5°	448.8	448.6	448.3	448.0	447.6	447.5	447.6	447.6	447.7	447.8	448.3
180°	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3



TEST NUMBER: P332363-830

CATALOG NUMBER: S123RDIP-S1165D365U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8
2.5°	1819.6	1822.5	1825.3	1826.6	1826.0	1825.5	1825.0	1824.4
5°	1807.5	1810.5	1813.5	1814.6	1813.9	1813.3	1812.6	1811.9
7.5°	1782.1	1783.8	1785.4	1785.6	1784.5	1783.4	1782.3	1781.1
10°	1759.3	1759.6	1760.0	1759.3	1757.7	1756.1	1754.4	1752.8
12.5°	1731.0	1730.8	1730.6	1729.6	1727.7	1725.7	1723.8	1721.9
15°	1681.3	1679.6	1678.0	1676.0	1673.7	1671.4	1669.1	1666.8
17.5°	1621.9	1618.3	1614.9	1611.5	1608.0	1604.6	1601.2	1597.7
20°	1581.2	1576.9	1572.6	1568.5	1564.5	1560.6	1556.7	1552.7
22.5°	1537.6	1532.3	1526.9	1522.4	1518.7	1515.0	1511.4	1507.7
25°	1466.3	1459.3	1452.5	1447.2	1443.6	1439.9	1436.3	1432.7
27.5°	1388.6	1378.9	1369.3	1361.8	1356.2	1350.8	1345.2	1339.6
30°	1333.2	1322.1	1310.9	1302.7	1297.4	1292.1	1286.9	1281.6
32.5°	1279.0	1266.8	1254.5	1245.7	1240.1	1234.5	1229.1	1223.5
35°	1198.4	1184.3	1170.2	1160.1	1154.1	1148.2	1142.3	1136.4
37.5°	1111.9	1095.9	1079.8	1068.1	1060.8	1053.5	1046.2	1038.9
40°	1051.8	1034.6	1017.6	1005.2	997.6	990.0	982.5	974.9
42.5°	994.1	975.3	956.7	944.0	937.2	930.4	923.6	916.8
45°	909.2	890.4	871.7	858.4	850.5	842.5	834.6	826.7
47.5°	821.4	801.1	780.6	766.9	759.9	752.8	745.7	738.8
50°	762.2	741.8	721.3	707.4	699.8	692.2	684.7	677.1
52.5°	704.9	683.7	662.5	648.5	641.7	635.0	628.2	621.4
55°	619.6	600.5	581.5	568.6	562.0	555.4	548.8	542.2
57.5°	535.8	517.7	499.7	487.9	482.3	476.7	471.1	465.5
60°	483.0	465.2	447.4	435.7	430.2	424.5	419.0	413.4
62.5°	430.6	413.9	397.1	385.9	379.9	374.1	368.3	362.4
65°	355.9	339.8	323.7	313.8	310.2	306.5	302.9	299.3
67.5°	284.6	272.6	260.5	252.6	248.7	244.8	240.9	237.0
70°	240.6	229.1	217.6	210.1	206.4	202.8	199.2	195.6
72.5°	201.0	191.6	182.2	176.7	175.2	173.7	172.2	170.7
75°	150.4	147.1	143.8	141.9	141.3	140.6	140.0	139.3
77.5°	113.5	111.7	109.9	108.7	108.0	107.4	106.7	106.0
80°	91.3	90.4	89.4	88.6	87.9	87.3	86.6	86.0
82.5°	70.0	69.1	68.1	67.5	67.4	67.2	67.1	67.0
85°	40.2	39.5	38.8	38.5	38.5	38.5	38.5	38.5
87.5°	16.6	16.4	16.2	15.9	15.7	15.5	15.3	15.1
90°	8.6	8.9	9.1	9.4	9.5	9.7	9.8	10.0
92.5°	9.5	10.0	10.5	10.7	10.7	10.8	10.9	11.0
95°	11.4	11.9	12.4	12.6	12.6	12.6	12.6	12.6
97.5°	11.9	12.5	13.1	13.4	13.5	13.6	13.7	13.8
100°	12.2	12.7	13.4	13.7	13.8	13.9	13.9	13.9
102.5°	18.3	16.4	14.6	13.8	13.9	13.9	14.1	14.2
105°	46.8	33.6	20.5	14.0	14.2	14.3	14.5	14.6
107.5°	114.5	104.9	95.3	85.5	75.7	65.8	55.9	46.0
110°	145.3	142.9	140.4	133.9	123.4	112.7	102.2	91.6



TEST NUMBER: P332363-830

CATALOG NUMBER: S123RDIP-S1165D365U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	167.1	167.1	167.2	166.1	163.8	161.6	159.4	157.1
115°	192.7	193.4	194.2	194.6	194.9	195.3	195.6	195.9
117.5°	215.8	216.4	217.0	217.4	217.4	217.4	217.5	217.5
120°	231.0	231.6	232.1	232.5	232.5	232.5	232.5	232.5
122.5°	245.8	246.3	246.7	246.9	246.9	247.0	247.0	247.1
125°	266.7	266.9	267.0	267.2	267.3	267.5	267.7	267.8
127.5°	287.7	287.9	288.2	288.2	288.0	287.9	287.8	287.7
130°	300.4	300.7	301.0	301.0	300.9	300.8	300.6	300.4
132.5°	312.4	312.6	312.9	313.0	312.7	312.5	312.4	312.2
135°	330.5	330.7	330.9	330.9	330.7	330.5	330.3	330.1
137.5°	346.7	347.0	347.4	347.5	347.3	347.2	347.0	346.9
140°	356.9	357.2	357.6	357.6	357.5	357.3	357.2	357.0
142.5°	366.7	366.9	367.2	367.2	367.0	366.7	366.6	366.4
145°	380.3	380.5	380.6	380.7	380.7	380.7	380.7	380.7
147.5°	392.5	392.7	392.9	392.8	392.4	392.0	391.7	391.3
150°	400.0	400.1	400.3	400.2	400.0	399.8	399.5	399.4
152.5°	406.6	406.9	407.2	407.1	406.8	406.4	406.0	405.8
155°	415.8	416.1	416.5	416.4	416.0	415.6	415.1	414.6
157.5°	423.7	424.1	424.6	424.5	424.0	423.4	422.7	422.2
160°	428.2	428.7	429.1	429.0	428.6	428.0	427.5	427.0
162.5°	432.3	432.8	433.3	433.4	432.9	432.4	432.0	431.5
165°	437.8	438.5	439.0	439.0	438.6	438.0	437.5	437.0
167.5°	442.1	442.7	443.3	443.3	442.7	442.1	441.5	440.9
170°	444.5	445.1	445.6	445.6	445.1	444.5	443.9	443.3
172.5°	446.1	446.7	447.2	447.2	446.6	445.9	445.3	444.6
175°	448.0	448.6	449.0	449.0	448.5	447.8	447.2	446.7
177.5°	448.7	449.2	449.7	449.6	449.0	448.5	447.8	447.2
180°	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3

(END OF REPORT)